

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831440

Luminaire Tested: S123DIP-S340D805U930-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831440
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D805U930-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3657.1 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 33
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831440

CATALOG NUMBER: S123DIP-S340D805U930-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831440

CATALOG NUMBER: S123DIP-S340D805U930-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35				
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30				
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	31	26				
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27	23				
4	73	63	55	49	66	57	51	46	46	42	38	37	33	31	28	26	24	20				
5	67	56	48	43	60	51	44	39	42	37	33	33	30	27	25	23	21	18				
6	62	50	43	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16				
7	57	45	38	33	52	42	35	30	34	29	26	28	24	21	21	19	17	14				
8	53	41	34	29	48	38	31	27	31	27	23	25	22	19	20	17	15	13				
9	49	38	31	26	45	35	28	24	29	24	21	23	20	17	18	16	14	12				
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	8617	8617	8617	8617	8617
5°	10897	10284	8694	7006	6438
10°	11002	11335	8636	5584	4880
15°	8286	10524	8576	4729	4126
20°	5774	8517	8467	4136	3748
25°	4403	6549	8280	3805	3515
30°	3808	5203	7982	3571	3329
35°	3533	4393	7638	3402	3197
40°	3346	3940	7156	3242	3153
45°	3235	3647	6543	3116	3133
50°	3178	3414	5816	3001	3116
55°	3061	3245	5103	2894	3130
60°	2951	3063	4398	2790	3078
65°	2771	2891	3795	2682	3018
70°	2559	2672	3226	2502	2842
75°	2316	2396	2766	2325	2595
80°	1909	2095	2188	2027	2188
85°	1519	1692	1606	1717	1741

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 7470 cd/sqm



TEST NUMBER: P831440

CATALOG NUMBER: S123DIP-S340D805U930-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.7	2.1
10°-20°	188.3	5.1
20°-30°	222.9	6.1
30°-40°	224.1	6.1
40°-50°	205.6	5.6
50°-60°	169.7	4.6
60°-70°	120.1	3.3
70°-80°	64.1	1.8
80°-90°	18.0	0.5
90°-100°	170.9	4.7
100°-110°	500.3	13.7
110°-120°	488.5	13.4
120°-130°	389.1	10.6
130°-140°	307.0	8.4
140°-150°	229.0	6.3
150°-160°	159.7	4.4
160°-170°	93.8	2.6
170°-180°	30.5	0.8
0°-30°	486.9	13.3
0°-40°	711.0	19.4
0°-60°	1086.4	29.7
0°-90°	1288.5	35.2
90°-120°	1159.6	31.7
90°-150°	2084.6	57.0
90°-180°	2369.0	64.8
0°-180°	3657.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	800	800	800	800	800	
5°	1008	952	805	648	596	96
15°	744	944	770	424	370	205
25°	371	551	697	320	296	175
35°	269	334	581	259	243	169
45°	212	240	430	205	206	165
55°	163	173	272	154	167	146
65°	109	114	149	105	118	108
75°	56	58	66	56	62	59
85°	12	14	13	14	14	14
90°	18	16	1	16	18	11
95°	74	378	22	378	74	120
105°	811	512	74	512	811	809
115°	986	392	131	392	986	962
125°	778	366	182	366	778	704
135°	630	361	213	361	630	489
145°	493	356	243	356	493	313
155°	409	345	276	345	409	190
165°	356	330	302	330	356	102
175°	321	317	314	317	321	31
180°	315	315	315	315	315	



TEST NUMBER: P831440

CATALOG NUMBER: S123DIP-S340D805U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5
2.5°	902.3	901.3	900.4	895.8	891.1	888.9	886.7	880.0	873.3	865.9	858.4
5°	1008.5	1011.1	1013.7	1010.7	1007.8	998.7	989.5	977.5	965.4	951.8	938.3
7.5°	1057.5	1059.0	1060.5	1058.6	1056.8	1054.4	1052.0	1041.2	1030.4	1016.5	1002.6
10°	1006.6	1010.0	1013.3	1020.6	1027.8	1036.0	1044.2	1042.7	1041.2	1037.1	1033.0
12.5°	894.8	898.9	903.0	917.5	932.0	950.5	969.1	985.1	1001.1	1012.2	1023.4
15°	743.6	755.0	766.3	779.5	792.7	820.0	847.3	880.9	914.5	944.4	974.3
17.5°	612.5	616.8	621.1	635.2	649.3	683.7	718.0	756.8	795.7	845.2	894.8
20°	504.1	508.0	511.9	530.4	549.0	575.9	602.9	646.5	690.2	743.5	796.8
22.5°	423.5	429.6	435.7	446.1	456.5	482.3	508.1	547.0	585.8	644.7	703.5
25°	370.7	375.2	379.6	385.9	392.3	412.9	433.5	465.4	497.4	551.4	605.5
27.5°	334.7	336.5	338.4	344.7	351.0	364.4	377.8	405.3	432.7	478.6	524.5
30°	306.4	307.7	309.0	314.6	320.2	329.3	338.4	358.3	378.1	418.6	459.1
32.5°	286.8	287.7	288.6	292.9	297.2	303.7	310.2	324.6	339.1	372.6	406.0
35°	268.9	269.5	270.0	273.2	276.4	281.2	286.0	297.0	307.9	334.3	360.7
37.5°	253.3	254.1	254.8	256.7	258.5	262.8	267.1	275.8	284.5	304.8	325.0
40°	238.1	239.4	240.7	242.0	243.3	246.8	250.4	257.0	263.7	280.4	297.2
42.5°	225.1	226.4	227.7	228.3	228.8	230.9	232.9	239.0	245.2	257.6	270.0
45°	212.5	213.0	213.6	214.1	214.7	216.4	218.0	223.4	228.8	239.6	250.4
47.5°	201.0	201.0	201.0	201.3	201.7	203.2	204.7	208.6	212.5	220.8	229.2
50°	189.8	189.8	189.8	189.3	188.7	189.6	190.6	193.5	196.5	203.9	211.4
52.5°	176.4	176.4	176.4	176.6	176.8	176.8	176.8	179.4	182.0	188.7	195.4
55°	163.1	163.8	164.6	164.0	163.4	163.8	164.2	165.9	167.5	172.9	178.3
57.5°	149.7	150.1	150.4	150.3	150.1	150.3	150.4	151.9	153.4	157.5	161.6
60°	137.1	137.1	137.1	136.7	136.3	136.7	137.1	137.8	138.6	142.3	146.0
62.5°	123.0	123.1	123.3	123.5	123.7	123.3	123.0	123.9	124.8	127.6	130.4
65°	108.8	109.0	109.2	109.8	110.3	109.9	109.6	110.5	111.4	113.5	115.5
67.5°	96.2	95.8	95.5	95.6	95.8	96.4	96.9	97.1	97.3	99.5	101.8
70°	81.3	81.7	82.1	81.9	81.7	81.9	82.1	82.6	83.2	84.9	86.5
72.5°	68.0	68.2	68.3	68.3	68.3	68.7	69.1	69.6	70.2	71.1	72.1
75°	55.7	55.7	55.7	56.1	56.5	56.6	56.8	56.8	56.8	57.6	58.3
77.5°	42.3	43.3	44.2	44.0	43.8	44.2	44.6	45.1	45.7	46.1	46.4
80°	30.8	30.8	30.8	31.0	31.2	31.8	32.3	32.7	33.1	33.8	34.5
82.5°	19.7	19.9	20.1	20.6	21.2	21.5	21.9	22.5	23.0	23.0	23.0
85°	12.3	11.9	11.5	11.9	12.3	12.6	13.0	13.2	13.4	13.7	14.1
87.5°	5.9	5.9	5.9	5.9	5.9	6.1	6.3	6.3	6.3	6.3	6.3
90°	18.5	19.1	18.5	17.8	18.5	17.2	16.6	15.9	15.3	15.9	14.0
92.5°	33.8	35.1	34.4	37.0	38.2	42.7	49.1	63.1	88.6	118.6	131.3
95°	73.9	76.5	81.0	86.7	98.8	121.7	155.5	229.5	306.6	378.0	336.6
97.5°	151.7	158.7	174.0	198.2	240.9	313.6	397.7	527.1	601.1	581.3	434.1
100°	399.7	399.0	423.9	470.4	534.8	625.3	699.9	751.5	729.2	603.6	407.9
102.5°	633.0	651.4	671.2	705.6	752.2	801.2	836.9	826.1	735.6	562.2	369.7
105°	810.8	814.0	834.4	858.6	887.9	904.5	892.4	828.6	695.4	512.5	339.7
107.5°	926.8	933.8	942.1	953.6	957.4	940.2	890.5	790.4	638.1	468.5	318.1
110°	993.1	994.4	995.6	990.5	972.7	928.1	847.8	730.5	584.5	432.2	306.6



TEST NUMBER: P831440

CATALOG NUMBER: S123DIP-S340D805U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1006.5	1005.8	999.5	981.0	944.7	884.1	791.7	671.2	538.0	407.9	300.2
115°	986.1	982.9	970.1	942.1	894.3	824.8	731.1	620.2	502.3	392.0	299.6
117.5°	941.5	937.0	917.9	886.6	836.9	764.9	678.8	580.7	478.7	381.2	300.2
120°	882.8	879.0	863.7	828.0	777.6	713.3	636.8	550.7	460.9	374.2	302.8
122.5°	828.0	822.9	805.7	774.5	731.1	672.5	603.0	527.1	446.2	369.7	307.2
125°	777.6	773.2	757.3	729.2	688.4	637.4	576.2	506.7	434.1	365.9	311.7
127.5°	734.3	730.5	715.8	691.6	654.6	607.5	551.4	488.3	422.6	364.0	316.8
130°	698.6	693.5	680.1	657.2	623.4	580.0	528.4	471.1	413.7	362.1	321.9
132.5°	663.6	660.4	648.9	625.9	594.7	553.9	506.7	455.1	405.4	361.4	325.7
135°	630.4	625.9	614.5	595.3	564.1	527.8	486.3	441.1	398.4	360.8	329.5
137.5°	595.3	591.5	582.0	562.2	535.4	502.9	466.0	427.7	392.0	359.5	332.1
140°	558.4	559.0	548.8	531.0	506.7	479.3	448.7	416.2	386.3	358.9	334.6
142.5°	524.0	524.6	515.7	500.4	480.6	457.7	432.2	405.4	381.2	357.6	336.6
145°	492.7	491.4	486.3	473.0	457.0	438.5	418.1	397.1	376.7	356.3	337.2
147.5°	466.0	465.3	460.2	450.7	437.9	424.5	407.3	390.1	372.3	354.4	337.2
150°	443.0	443.0	439.2	432.2	422.6	410.5	397.1	382.4	367.8	351.9	337.2
152.5°	423.9	423.9	422.0	415.6	408.6	399.0	387.5	375.4	362.7	348.7	335.3
155°	408.6	407.9	406.7	401.6	395.8	388.2	378.6	368.4	357.6	344.8	334.0
157.5°	393.9	393.9	392.6	388.8	383.7	377.4	369.7	360.8	351.9	341.7	332.1
160°	379.9	380.5	380.5	376.7	372.3	367.8	361.4	354.4	346.1	337.8	330.8
162.5°	367.2	367.8	367.8	364.6	362.1	358.2	352.5	346.8	340.4	334.0	328.3
165°	356.3	356.3	357.0	354.4	351.9	348.7	344.2	340.4	335.3	330.2	325.7
167.5°	345.5	345.5	346.1	344.2	342.9	340.4	337.8	334.6	330.2	326.4	323.2
170°	335.9	335.9	336.6	335.3	334.6	333.4	330.8	328.9	325.7	322.5	320.6
172.5°	327.0	327.6	328.9	327.6	327.6	327.0	325.1	323.8	321.3	319.3	318.7
175°	320.6	321.3	321.9	321.3	321.3	321.3	320.0	319.3	318.1	316.8	316.8
177.5°	316.2	316.2	317.4	316.8	317.4	317.4	316.8	316.2	315.5	314.9	315.5
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P831440

CATALOG NUMBER: S123DIP-S340D805U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5
2.5°	856.2	854.0	845.8	837.6	828.3	819.1	812.2	805.3	795.1	784.9	776.5
5°	927.9	917.5	900.2	882.9	859.5	836.1	820.4	804.6	783.4	762.2	745.3
7.5°	984.7	966.9	942.7	918.6	888.0	857.3	828.3	799.4	767.0	734.7	708.4
10°	1020.9	1008.9	981.0	953.1	912.1	871.1	830.6	790.1	748.5	706.9	672.0
12.5°	1024.5	1025.6	1000.0	974.3	927.9	881.5	832.2	783.0	730.6	678.3	637.6
15°	993.4	1012.6	998.5	984.3	937.5	890.7	830.2	769.6	709.3	648.9	601.9
17.5°	935.9	976.9	979.0	981.0	934.2	887.4	820.4	753.3	685.0	616.6	567.2
20°	857.3	917.9	938.7	959.5	921.4	883.3	811.3	739.2	662.7	586.2	534.3
22.5°	777.1	850.6	888.7	926.8	898.5	870.3	793.6	716.9	636.1	555.3	502.8
25°	685.7	765.9	824.4	882.9	865.7	848.4	772.8	697.2	611.2	525.2	471.6
27.5°	606.0	687.6	758.1	828.7	825.0	821.3	746.2	671.2	583.2	495.1	443.3
30°	535.1	611.0	690.0	768.9	778.0	787.1	714.7	642.2	554.0	465.8	415.8
32.5°	472.3	538.6	623.3	708.0	725.8	743.6	678.3	612.9	525.6	438.3	390.2
35°	420.9	481.0	565.7	650.4	672.7	695.0	638.2	581.3	496.3	411.2	365.3
37.5°	375.4	425.7	508.3	591.0	618.3	645.6	594.7	543.8	464.1	384.5	342.3
40°	337.7	378.1	454.1	530.1	561.6	593.2	551.2	509.3	433.7	358.1	319.3
42.5°	306.1	342.1	411.0	479.9	510.2	540.5	505.0	469.5	402.3	335.1	299.6
45°	279.1	307.9	370.5	433.1	461.9	490.7	460.2	429.8	370.5	311.3	278.2
47.5°	253.9	278.6	332.1	385.6	411.2	436.8	413.1	389.3	339.1	289.0	259.1
50°	231.2	251.1	297.9	344.7	367.0	389.3	368.3	347.3	306.1	264.8	238.8
52.5°	211.5	227.7	266.9	306.1	325.2	344.3	326.3	308.3	275.6	242.9	220.3
55°	192.0	205.8	239.8	273.8	286.8	299.8	285.8	271.9	245.5	219.2	200.0
57.5°	173.8	186.1	214.0	241.8	251.8	261.9	249.2	236.6	216.7	196.9	180.9
60°	156.0	166.0	189.3	212.5	218.6	224.7	214.5	204.3	190.4	176.4	162.1
62.5°	139.5	148.6	165.9	183.1	187.2	191.3	183.5	175.7	165.1	154.5	143.4
65°	122.4	129.3	143.4	157.5	160.1	162.7	155.8	149.0	141.0	133.0	124.8
67.5°	106.6	111.4	123.0	134.5	134.7	134.8	129.3	123.7	119.2	114.8	108.3
70°	91.2	95.8	103.4	111.1	111.3	111.4	107.0	102.5	99.2	95.8	91.0
72.5°	75.4	78.7	84.5	90.3	89.9	89.5	86.7	83.9	81.3	78.7	75.2
75°	61.1	63.9	67.8	71.7	70.6	69.5	68.0	66.5	64.3	62.0	59.8
77.5°	48.1	49.8	52.0	54.2	53.5	52.7	51.4	50.1	48.5	46.8	45.9
80°	35.3	36.0	37.5	39.0	38.6	38.3	36.8	35.3	34.9	34.5	33.2
82.5°	24.0	24.9	25.3	25.6	25.4	25.3	24.1	23.0	22.7	22.3	22.1
85°	14.3	14.5	14.7	14.9	14.3	13.7	13.4	13.0	13.0	13.0	12.8
87.5°	6.5	6.7	6.7	6.7	6.5	6.3	5.9	5.6	5.8	5.9	5.9
90°	12.1	10.2	8.3	7.0	5.7	3.8	2.5	1.3	2.5	3.8	5.7
92.5°	98.2	64.4	44.0	32.5	26.1	20.4	14.0	9.6	14.0	20.4	26.1
95°	232.0	137.0	82.9	58.0	41.4	30.6	23.6	21.7	23.6	30.6	41.4
97.5°	258.2	147.9	94.3	66.9	50.4	40.8	35.1	34.4	35.1	40.8	50.4
100°	240.3	146.0	101.3	76.5	61.2	52.3	47.8	47.2	47.8	52.3	61.2
102.5°	225.0	148.5	109.6	87.3	73.9	65.7	61.8	60.6	61.8	65.7	73.9
105°	219.3	153.6	119.2	99.4	87.3	79.7	75.9	73.9	75.9	79.7	87.3
107.5°	218.0	161.9	131.3	112.8	101.3	93.7	89.9	88.0	89.9	93.7	101.3
110°	221.2	172.7	144.1	126.2	115.4	108.4	105.2	103.3	105.2	108.4	115.4



TEST NUMBER: P831440

CATALOG NUMBER: S123DIP-S340D805U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	227.6	183.6	157.4	140.2	129.4	122.4	119.2	117.3	119.2	122.4	129.4
115°	234.6	195.7	171.5	154.3	143.4	137.0	133.2	130.7	133.2	137.0	143.4
117.5°	243.5	208.4	184.2	168.3	156.2	150.4	147.2	144.1	147.2	150.4	156.2
120°	253.7	220.5	197.6	181.7	169.6	163.2	160.0	158.1	160.0	163.2	169.6
122.5°	263.3	233.3	211.0	193.8	182.3	175.3	172.1	170.2	172.1	175.3	182.3
125°	273.5	245.4	223.1	205.9	193.8	186.8	182.9	181.7	182.9	186.8	193.8
127.5°	281.7	256.2	234.6	217.4	204.0	197.0	192.5	190.6	192.5	197.0	204.0
130°	290.0	265.8	244.8	227.6	214.2	206.5	200.8	198.9	200.8	206.5	214.2
132.5°	297.7	274.1	253.7	237.1	223.7	214.2	207.8	205.2	207.8	214.2	223.7
135°	304.0	282.4	262.6	245.4	232.0	222.5	215.4	212.9	215.4	222.5	232.0
137.5°	309.1	288.1	269.0	253.1	239.7	229.5	222.5	219.9	222.5	229.5	239.7
140°	313.0	293.8	275.4	259.4	246.7	236.5	230.1	226.9	230.1	236.5	246.7
142.5°	316.8	298.3	280.5	265.8	253.1	244.1	237.1	234.6	237.1	244.1	253.1
145°	319.3	302.1	285.6	270.9	260.1	250.5	244.8	242.9	244.8	250.5	260.1
147.5°	321.3	305.3	290.0	277.3	266.4	258.2	252.4	251.1	252.4	258.2	266.4
150°	321.9	308.5	293.8	282.4	273.5	265.2	260.1	259.4	260.1	265.2	273.5
152.5°	323.2	310.4	298.3	287.5	279.8	272.8	267.7	267.7	267.7	272.8	279.8
155°	323.2	313.0	302.1	293.2	286.2	279.8	276.0	276.0	276.0	279.8	286.2
157.5°	323.8	314.2	305.3	298.3	291.9	286.2	283.0	282.4	283.0	286.2	291.9
160°	323.8	316.2	308.5	302.1	297.7	292.6	290.0	290.0	290.0	292.6	297.7
162.5°	323.2	316.8	310.4	305.3	301.5	297.7	295.8	295.8	295.8	297.7	301.5
165°	321.9	317.4	312.3	307.9	305.3	302.1	300.9	301.5	300.9	302.1	305.3
167.5°	321.3	317.4	313.6	310.4	308.5	306.0	305.3	306.0	305.3	306.0	308.5
170°	319.3	316.8	313.6	312.3	311.1	309.1	308.5	309.8	308.5	309.1	311.1
172.5°	318.7	316.8	314.2	313.6	313.0	311.7	311.7	312.3	311.7	311.7	313.0
175°	317.4	316.2	314.9	314.2	314.2	313.0	313.6	314.2	313.6	313.0	314.2
177.5°	316.8	315.5	314.9	314.9	314.9	314.2	314.9	315.5	314.9	314.2	314.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P831440

CATALOG NUMBER: S123DIP-S340D805U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5	800.5
2.5°	768.2	760.9	753.7	748.1	742.5	733.1	723.6	721.4	719.1	716.0	712.8
5°	728.4	710.6	692.8	676.8	660.8	648.4	635.9	627.8	619.6	613.6	607.7
7.5°	682.0	655.2	628.5	609.6	590.6	572.6	554.6	548.8	543.1	535.3	527.5
10°	637.0	607.5	578.0	553.3	528.6	510.9	493.3	486.2	479.2	469.3	459.5
12.5°	596.9	564.6	532.3	507.4	482.5	465.4	448.3	438.1	427.9	422.3	416.8
15°	555.0	520.4	485.9	462.8	439.8	424.4	409.0	400.1	391.1	385.8	380.4
17.5°	517.8	483.6	449.5	427.4	405.3	391.1	377.0	369.2	361.4	357.3	353.3
20°	482.5	449.1	415.7	394.1	372.6	361.1	349.5	344.5	339.5	336.2	332.8
22.5°	450.2	417.3	384.5	366.1	347.7	338.4	329.1	325.6	322.0	319.3	316.5
25°	417.9	388.5	359.2	343.6	328.0	320.4	312.8	309.2	305.7	302.9	300.1
27.5°	391.5	363.5	335.4	322.0	308.7	302.7	296.8	294.0	291.2	288.6	286.0
30°	365.9	340.8	315.7	304.2	292.7	287.3	281.9	279.1	276.4	273.9	271.5
32.5°	342.1	320.6	299.0	288.4	277.8	273.4	268.9	265.6	262.2	260.4	258.5
35°	319.4	300.1	280.8	272.1	263.4	258.9	254.4	251.7	248.9	247.4	245.9
37.5°	300.1	282.9	265.6	257.2	248.9	244.6	240.3	237.9	235.5	234.9	234.4
40°	280.4	265.6	250.7	242.6	234.4	230.7	227.0	225.5	224.0	223.6	223.2
42.5°	264.1	249.6	235.1	227.7	220.3	217.1	214.0	213.2	212.5	213.0	213.6
45°	245.2	233.1	221.0	214.1	207.3	204.7	202.1	201.5	201.0	202.1	203.2
47.5°	229.2	218.0	206.9	200.4	193.9	192.0	190.2	190.0	189.8	191.3	192.8
50°	212.8	202.1	191.3	186.1	180.9	179.2	177.6	178.1	178.7	181.1	183.5
52.5°	197.6	187.6	177.6	172.7	167.9	166.8	165.7	167.0	168.3	170.9	173.5
55°	180.9	171.8	162.7	159.0	155.3	154.2	153.0	155.6	158.2	160.7	163.1
57.5°	164.9	156.9	149.0	145.6	142.3	142.1	141.9	144.3	146.7	149.3	151.9
60°	147.8	141.2	134.5	131.9	129.3	129.6	130.0	132.8	135.6	137.6	139.7
62.5°	132.2	126.7	121.1	118.7	116.3	117.2	118.1	120.9	123.7	126.1	128.5
65°	116.6	112.0	107.3	105.7	104.0	105.3	106.6	109.0	111.4	113.1	114.8
67.5°	101.8	97.9	94.0	92.7	91.4	92.7	94.0	96.4	98.8	100.5	102.1
70°	86.2	83.0	79.9	78.9	78.0	79.5	81.0	83.0	85.1	86.7	88.4
72.5°	71.7	69.3	66.9	66.7	66.5	67.8	69.1	71.1	73.2	74.3	75.4
75°	57.6	56.3	55.0	54.8	54.6	55.9	57.2	58.3	59.4	60.4	61.3
77.5°	44.9	43.8	42.7	42.9	43.1	44.0	44.9	46.1	47.2	47.7	48.3
80°	31.9	31.6	31.2	31.6	31.9	32.7	33.4	34.2	34.9	35.3	35.7
82.5°	21.9	21.5	21.2	21.7	22.3	22.8	23.4	24.0	24.5	24.7	24.9
85°	12.6	13.2	13.7	13.7	13.7	13.9	14.1	14.3	14.5	14.3	14.1
87.5°	5.9	6.1	6.3	6.3	6.3	6.5	6.7	6.7	6.7	6.5	6.3
90°	7.0	8.3	10.2	12.1	14.0	15.9	15.3	15.9	16.6	17.2	18.5
92.5°	32.5	44.0	64.4	98.2	131.3	118.6	88.6	63.1	49.1	42.7	38.2
95°	58.0	82.9	137.0	232.0	336.6	378.0	306.6	229.5	155.5	121.7	98.8
97.5°	66.9	94.3	147.9	258.2	434.1	581.3	601.1	527.1	397.7	313.6	240.9
100°	76.5	101.3	146.0	240.3	407.9	603.6	729.2	751.5	699.9	625.3	534.8
102.5°	87.3	109.6	148.5	225.0	369.7	562.2	735.6	826.1	836.9	801.2	752.2
105°	99.4	119.2	153.6	219.3	339.7	512.5	695.4	828.6	892.4	904.5	887.9
107.5°	112.8	131.3	161.9	218.0	318.1	468.5	638.1	790.4	890.5	940.2	957.4
110°	126.2	144.1	172.7	221.2	306.6	432.2	584.5	730.5	847.8	928.1	972.7



TEST NUMBER: P831440

CATALOG NUMBER: S123DIP-S340D805U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	140.2	157.4	183.6	227.6	300.2	407.9	538.0	671.2	791.7	884.1	944.7
115°	154.3	171.5	195.7	234.6	299.6	392.0	502.3	620.2	731.1	824.8	894.3
117.5°	168.3	184.2	208.4	243.5	300.2	381.2	478.7	580.7	678.8	764.9	836.9
120°	181.7	197.6	220.5	253.7	302.8	374.2	460.9	550.7	636.8	713.3	777.6
122.5°	193.8	211.0	233.3	263.3	307.2	369.7	446.2	527.1	603.0	672.5	731.1
125°	205.9	223.1	245.4	273.5	311.7	365.9	434.1	506.7	576.2	637.4	688.4
127.5°	217.4	234.6	256.2	281.7	316.8	364.0	422.6	488.3	551.4	607.5	654.6
130°	227.6	244.8	265.8	290.0	321.9	362.1	413.7	471.1	528.4	580.0	623.4
132.5°	237.1	253.7	274.1	297.7	325.7	361.4	405.4	455.1	506.7	553.9	594.7
135°	245.4	262.6	282.4	304.0	329.5	360.8	398.4	441.1	486.3	527.8	564.1
137.5°	253.1	269.0	288.1	309.1	332.1	359.5	392.0	427.7	466.0	502.9	535.4
140°	259.4	275.4	293.8	313.0	334.6	358.9	386.3	416.2	448.7	479.3	506.7
142.5°	265.8	280.5	298.3	316.8	336.6	357.6	381.2	405.4	432.2	457.7	480.6
145°	270.9	285.6	302.1	319.3	337.2	356.3	376.7	397.1	418.1	438.5	457.0
147.5°	277.3	290.0	305.3	321.3	337.2	354.4	372.3	390.1	407.3	424.5	437.9
150°	282.4	293.8	308.5	321.9	337.2	351.9	367.8	382.4	397.1	410.5	422.6
152.5°	287.5	298.3	310.4	323.2	335.3	348.7	362.7	375.4	387.5	399.0	408.6
155°	293.2	302.1	313.0	323.2	334.0	344.8	357.6	368.4	378.6	388.2	395.8
157.5°	298.3	305.3	314.2	323.8	332.1	341.7	351.9	360.8	369.7	377.4	383.7
160°	302.1	308.5	316.2	323.8	330.8	337.8	346.1	354.4	361.4	367.8	372.3
162.5°	305.3	310.4	316.8	323.2	328.3	334.0	340.4	346.8	352.5	358.2	362.1
165°	307.9	312.3	317.4	321.9	325.7	330.2	335.3	340.4	344.2	348.7	351.9
167.5°	310.4	313.6	317.4	321.3	323.2	326.4	330.2	334.6	337.8	340.4	342.9
170°	312.3	313.6	316.8	319.3	320.6	322.5	325.7	328.9	330.8	333.4	334.6
172.5°	313.6	314.2	316.8	318.7	318.7	319.3	321.3	323.8	325.1	327.0	327.6
175°	314.2	314.9	316.2	317.4	316.8	316.8	318.1	319.3	320.0	321.3	321.3
177.5°	314.9	314.9	315.5	316.8	315.5	314.9	315.5	316.2	316.8	317.4	317.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P831440

CATALOG NUMBER: S123DIP-S340D805U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	800.5	800.5	800.5	800.5
2.5°	711.5	710.2	705.0	699.8
5°	603.2	598.8	597.3	595.8
7.5°	527.1	526.7	518.9	511.1
10°	460.0	460.6	453.5	446.5
12.5°	412.1	407.5	406.9	406.4
15°	376.1	371.8	371.1	370.3
17.5°	350.7	348.1	347.3	346.6
20°	331.3	329.8	328.5	327.2
22.5°	314.6	312.8	311.6	310.5
25°	298.5	296.8	296.4	296.0
27.5°	284.0	281.9	281.9	281.9
30°	270.2	268.9	268.4	267.8
32.5°	257.4	256.3	256.3	256.3
35°	245.3	244.8	244.0	243.3
37.5°	234.4	234.4	234.0	233.6
40°	223.8	224.4	224.4	224.4
42.5°	214.1	214.7	214.7	214.7
45°	204.1	205.0	205.4	205.8
47.5°	194.3	195.8	196.1	196.5
50°	184.6	185.7	185.9	186.1
52.5°	174.8	176.1	177.0	177.9
55°	164.4	165.7	166.2	166.8
57.5°	153.2	154.5	154.7	154.9
60°	141.0	142.3	142.6	143.0
62.5°	129.3	130.0	130.4	130.8
65°	115.9	117.0	117.8	118.5
67.5°	103.1	104.0	104.0	104.0
70°	88.8	89.1	89.7	90.3
72.5°	75.6	75.8	75.8	75.8
75°	61.7	62.0	62.2	62.4
77.5°	48.5	48.7	48.7	48.7
80°	35.5	35.3	35.3	35.3
82.5°	24.3	23.8	23.8	23.8
85°	13.9	13.7	13.9	14.1
87.5°	6.3	6.3	6.3	6.3
90°	17.8	18.5	19.1	18.5
92.5°	37.0	34.4	35.1	33.8
95°	86.7	81.0	76.5	73.9
97.5°	198.2	174.0	158.7	151.7
100°	470.4	423.9	399.0	399.7
102.5°	705.6	671.2	651.4	633.0
105°	858.6	834.4	814.0	810.8
107.5°	953.6	942.1	933.8	926.8
110°	990.5	995.6	994.4	993.1



TEST NUMBER: P831440

CATALOG NUMBER: S123DIP-S340D805U930-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	981.0	999.5	1005.8	1006.5
115°	942.1	970.1	982.9	986.1
117.5°	886.6	917.9	937.0	941.5
120°	828.0	863.7	879.0	882.8
122.5°	774.5	805.7	822.9	828.0
125°	729.2	757.3	773.2	777.6
127.5°	691.6	715.8	730.5	734.3
130°	657.2	680.1	693.5	698.6
132.5°	625.9	648.9	660.4	663.6
135°	595.3	614.5	625.9	630.4
137.5°	562.2	582.0	591.5	595.3
140°	531.0	548.8	559.0	558.4
142.5°	500.4	515.7	524.6	524.0
145°	473.0	486.3	491.4	492.7
147.5°	450.7	460.2	465.3	466.0
150°	432.2	439.2	443.0	443.0
152.5°	415.6	422.0	423.9	423.9
155°	401.6	406.7	407.9	408.6
157.5°	388.8	392.6	393.9	393.9
160°	376.7	380.5	380.5	379.9
162.5°	364.6	367.8	367.8	367.2
165°	354.4	357.0	356.3	356.3
167.5°	344.2	346.1	345.5	345.5
170°	335.3	336.6	335.9	335.9
172.5°	327.6	328.9	327.6	327.0
175°	321.3	321.9	321.3	320.6
177.5°	316.8	317.4	316.2	316.2
180°	314.9	314.9	314.9	314.9



TEST NUMBER: P831440

CATALOG NUMBER: S123DIP-S340D805U930-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.49	10.21	10.57	11.28	12.76	11.72	12.44	12.81	13.52	14.99
	3H	11.13	11.77	12.21	12.85	14.34	13.14	13.78	14.23	14.87	16.36
	4H	11.70	12.31	12.80	13.39	14.89	13.58	14.19	14.68	15.28	16.77
	6H	12.06	12.62	13.17	13.71	15.22	13.85	14.41	14.96	15.50	17.01
	8H	12.15	12.69	13.26	13.79	15.29	13.91	14.44	15.02	15.55	17.05
	12H	12.19	12.70	13.31	13.80	15.32	13.93	14.43	15.04	15.53	17.05
4H	2H	10.05	10.66	11.15	11.74	13.24	11.87	12.48	12.98	13.57	15.06
	3H	11.86	12.37	12.98	13.49	14.99	13.48	13.99	14.59	15.10	16.61
	4H	12.56	13.02	13.67	14.13	15.65	14.06	14.52	15.17	15.63	17.15
	6H	13.02	13.42	14.15	14.55	16.07	14.45	14.85	15.58	15.98	17.50
	8H	13.16	13.53	14.28	14.65	16.18	14.56	14.94	15.69	16.05	17.59
	12H	13.22	13.56	14.36	14.69	16.23	14.60	14.94	15.74	16.07	17.61
8H	4H	12.81	13.18	13.94	14.30	15.84	14.15	14.53	15.28	15.64	17.18
	6H	13.39	13.70	14.54	14.86	16.39	14.65	14.96	15.79	16.12	17.65
	8H	13.60	13.87	14.75	15.01	16.56	14.83	15.10	15.98	16.24	17.79
	12H	13.72	13.96	14.87	15.09	16.68	14.92	15.16	16.08	16.30	17.88
12H	4H	12.81	13.14	13.95	14.27	15.81	14.12	14.46	15.26	15.59	17.13
	6H	13.44	13.71	14.60	14.85	16.41	14.66	14.93	15.81	16.07	17.62
	8H	13.67	13.91	14.83	15.05	16.63	14.86	15.09	16.01	16.23	17.82