

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331945-930

Luminaire Tested: **S123DIP-S560D1025U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020


Test Information

Test Method: LM-79-08
Report Number: P331945-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1025U930-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4917.7 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331945-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331945-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77		61	61	61		46	46	46	38
1	95	91	87	84	86	83	79	76	67	65	63		53	52	50		40	39	38	32
2	87	79	73	68	78	72	67	63	59	55	52		47	44	42		35	34	32	27
3	79	70	62	57	71	63	57	52	52	47	44		41	38	35		31	29	27	23
4	72	62	54	48	65	56	49	44	46	41	37		37	33	30		28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32		33	29	26		25	23	20	17
6	61	49	41	35	55	45	38	33	37	32	28		30	26	23		23	20	18	15
7	56	44	36	31	51	40	34	29	33	28	24		27	23	20		21	18	16	13
8	52	40	32	27	47	37	30	25	30	25	22		25	21	18		19	16	14	12
9	48	36	29	24	44	34	27	23	28	23	19		23	19	16		18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17		21	17	14		16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7854	7747	7800
10°	7803	7679	7726
15°	7710	7592	7608
20°	7605	7468	7475
25°	7462	7321	7305
30°	7305	7157	7102
35°	7139	6984	6893
40°	6968	6792	6687
45°	6779	6616	6454
50°	6589	6400	6223
55°	6341	6176	5988
60°	6090	5916	5726
65°	5871	5631	5456
70°	5542	5306	5070
75°	5065	4882	4675
80°	4568	4376	4339
85°	4001	3853	3705



TEST NUMBER: P331945-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	1.4
10°-20°	193.2	3.9
20°-30°	285.4	5.8
30°-40°	333.3	6.8
40°-50°	335.1	6.8
50°-60°	294.4	6.0
60°-70°	219.3	4.5
70°-80°	124.9	2.5
80°-90°	39.0	0.8
90°-100°	223.7	4.5
100°-110°	633.5	12.9
110°-120°	623.2	12.7
120°-130°	497.1	10.1
130°-140°	391.9	8.0
140°-150°	292.5	5.9
150°-160°	203.9	4.1
160°-170°	119.8	2.4
170°-180°	39.0	0.8
0°-30°	547.0	11.1
0°-40°	880.3	17.9
0°-60°	1509.9	30.7
0°-90°	1893.1	38.5
90°-120°	1480.5	30.1
90°-150°	2662.0	54.1
90°-180°	3025.0	61.5
0°-180°	4917.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	727	724	717	723	722	69
15°	692	689	681	686	683	195
25°	628	624	616	617	615	289
35°	543	539	532	528	525	340
45°	445	442	435	427	424	344
55°	338	337	329	322	319	303
65°	230	227	221	216	214	227
75°	122	119	117	114	112	130
85°	32	31	31	30	30	36
90°	2	10	20	23	24	4
95°	28	90	483	141	94	30
105°	94	140	654	1144	1035	100
115°	167	208	500	1097	1259	165
125°	232	274	467	846	993	206
135°	272	324	461	697	805	210
145°	310	355	455	572	629	194
155°	352	380	440	500	522	162
165°	385	396	422	447	455	108
175°	401	402	404	410	409	38
180°	402	402	402	402	402	



TEST NUMBER: P331945-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	728.8	728.4	728.0	727.5	727.1	726.2	725.0	723.7	722.6	721.4	722.4
5°	726.9	726.3	725.5	724.9	724.1	723.1	721.5	720.0	718.5	717.0	718.4
7.5°	719.8	719.2	718.4	717.8	717.1	715.9	714.4	712.7	711.2	709.6	710.9
10°	713.9	713.1	712.5	711.8	711.1	709.8	708.0	706.2	704.4	702.6	703.8
12.5°	705.9	705.2	704.7	704.1	703.5	702.4	700.7	699.0	697.3	695.6	696.5
15°	691.9	691.5	690.9	690.3	689.7	688.6	686.8	685.0	683.1	681.3	682.5
17.5°	675.9	675.1	674.4	673.7	672.9	671.7	669.9	668.1	666.3	664.5	665.3
20°	663.9	663.1	662.2	661.4	660.6	659.3	657.5	655.7	653.8	652.0	652.6
22.5°	650.4	649.5	648.7	647.9	647.0	645.7	643.9	642.1	640.3	638.5	639.0
25°	628.3	627.5	626.6	625.8	624.9	623.6	621.8	620.0	618.2	616.4	616.5
27.5°	604.7	603.9	603.1	602.3	601.4	600.1	598.1	596.2	594.3	592.3	592.4
30°	587.7	587.0	586.3	585.6	584.9	583.6	581.6	579.7	577.8	575.8	575.8
32.5°	570.7	569.8	568.8	567.9	567.0	565.8	564.4	562.8	561.3	559.9	559.1
35°	543.3	542.5	541.7	540.9	540.1	538.7	536.9	535.1	533.3	531.5	530.7
37.5°	515.4	514.3	513.2	512.2	511.1	509.7	507.8	506.1	504.2	502.4	501.4
40°	495.9	495.0	494.2	493.4	492.5	491.1	489.2	487.3	485.3	483.4	482.2
42.5°	476.4	475.5	474.5	473.5	472.6	471.2	469.2	467.3	465.4	463.4	462.3
45°	445.3	444.7	444.2	443.6	443.0	441.9	440.1	438.3	436.5	434.6	433.0
47.5°	414.4	413.6	412.9	412.1	411.2	409.9	408.3	406.6	404.9	403.2	401.5
50°	393.5	392.7	392.1	391.3	390.7	389.5	387.6	385.8	384.0	382.2	380.7
52.5°	371.5	371.0	370.6	370.1	369.6	368.4	366.5	364.6	362.6	360.8	359.5
55°	337.9	337.7	337.6	337.5	337.3	336.3	334.5	332.7	330.9	329.1	327.6
57.5°	305.9	305.4	304.9	304.5	304.0	303.0	301.6	300.2	298.7	297.3	296.0
60°	282.9	282.7	282.7	282.5	282.3	281.4	279.8	278.1	276.5	274.8	273.5
62.5°	262.4	262.0	261.7	261.4	261.0	260.0	258.3	256.7	254.9	253.3	252.1
65°	230.5	229.8	229.1	228.4	227.7	226.7	225.3	223.9	222.5	221.1	220.0
67.5°	196.6	196.0	195.3	194.8	194.1	193.3	192.2	191.2	190.1	189.1	188.2
70°	176.1	175.3	174.5	173.7	172.8	171.9	171.1	170.3	169.4	168.6	167.6
72.5°	154.7	154.0	153.4	152.8	152.2	151.4	150.5	149.5	148.5	147.7	146.8
75°	121.8	121.2	120.7	120.1	119.6	119.1	118.6	118.2	117.8	117.4	116.8
77.5°	92.7	92.4	92.0	91.8	91.5	91.1	90.6	90.1	89.5	89.0	88.6
80°	73.7	73.3	72.9	72.5	72.0	71.7	71.4	71.1	70.8	70.6	70.4
82.5°	55.2	55.1	55.0	55.0	54.9	54.8	54.8	54.7	54.6	54.6	54.3
85°	32.4	32.2	32.0	31.6	31.4	31.2	31.2	31.2	31.2	31.2	31.0
87.5°	13.3	13.3	13.3	13.5	13.5	13.5	13.9	14.3	14.7	15.1	14.8
90°	1.6	3.3	4.9	7.3	9.0	10.6	13.0	15.5	17.9	20.4	19.6
92.5°	10.1	15.0	21.9	28.1	35.0	47.0	68.3	103.4	137.7	125.1	94.4
95°	27.6	30.1	39.1	52.9	74.0	105.8	175.0	296.2	429.7	482.6	391.4
97.5°	47.2	48.0	55.0	67.0	87.9	122.2	188.3	325.1	547.6	747.9	800.1
100°	60.3	61.1	66.8	78.1	97.7	129.4	186.4	306.8	520.8	770.7	931.0
102.5°	73.9	75.3	80.4	91.2	108.8	137.9	189.0	291.1	481.8	728.4	937.5
105°	94.4	96.9	101.7	111.5	126.9	152.2	196.2	280.0	433.7	654.3	887.9
107.5°	116.2	118.6	123.4	133.0	147.5	170.9	209.5	279.2	403.2	588.9	801.0
110°	131.8	134.3	138.4	147.3	161.1	183.9	220.5	282.4	391.4	551.8	746.2



TEST NUMBER: P331945-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.2	148.6	152.7	161.6	175.5	197.6	231.6	288.9	384.9	527.0	698.7
115°	166.8	170.1	175.0	183.1	197.0	218.9	249.8	299.5	382.5	500.5	641.3
117.5°	187.5	191.3	195.3	202.8	218.3	238.6	269.2	313.5	383.9	484.9	606.6
120°	201.8	204.2	208.3	216.5	232.0	252.3	281.6	323.9	386.5	477.7	588.4
122.5°	214.2	216.6	220.7	229.5	244.3	266.0	294.6	333.7	391.1	473.1	573.4
125°	232.0	233.6	238.5	247.4	262.9	284.9	313.3	349.1	397.9	467.2	554.2
127.5°	245.5	247.9	253.9	263.0	280.1	302.1	329.6	361.8	405.8	464.2	537.3
130°	253.9	256.3	263.7	273.5	290.5	312.5	339.3	370.3	411.0	462.3	528.2
132.5°	260.4	263.5	271.5	283.2	300.3	321.6	347.8	378.1	414.9	461.6	519.7
135°	271.8	275.1	284.1	296.2	313.3	335.3	360.5	388.2	420.8	460.6	508.7
137.5°	282.6	286.0	294.7	307.8	324.7	345.0	369.3	395.7	424.6	458.9	499.0
140°	289.8	293.8	301.9	315.0	331.3	351.6	375.2	399.6	427.2	458.2	493.2
142.5°	297.5	300.9	309.7	321.5	337.7	356.8	379.8	403.5	429.2	456.9	488.0
145°	310.1	312.5	319.8	332.1	345.8	364.6	385.7	407.7	430.5	454.9	480.9
147.5°	322.8	324.2	331.4	341.9	355.3	371.3	390.6	410.3	430.5	451.8	474.1
150°	331.3	332.1	338.5	349.1	360.5	375.2	393.9	411.0	430.5	449.2	469.5
152.5°	339.7	339.8	346.3	355.6	365.7	379.8	395.8	412.3	428.5	446.0	464.4
155°	352.4	352.4	357.3	365.4	374.4	385.7	399.6	412.6	426.4	440.3	456.6
157.5°	362.5	363.1	367.0	374.2	381.8	390.6	401.7	413.4	423.7	435.2	447.8
160°	370.3	370.3	373.6	380.0	385.7	393.9	403.7	413.4	422.4	431.3	441.9
162.5°	376.2	376.2	378.8	383.9	389.0	395.8	404.3	412.8	419.8	427.4	436.0
165°	384.9	384.1	385.7	389.8	393.1	398.8	405.3	411.0	415.9	421.6	428.0
167.5°	391.6	390.6	391.4	394.5	396.8	400.4	405.1	409.7	412.0	415.7	420.4
170°	395.5	393.9	394.7	397.1	398.8	400.4	404.5	407.7	409.4	411.8	415.9
172.5°	398.1	397.1	397.3	399.1	400.1	401.0	404.5	407.1	407.4	408.5	411.3
175°	401.2	400.4	399.6	401.2	401.2	402.0	403.7	405.3	404.5	404.5	406.1
177.5°	402.7	402.0	401.4	402.0	402.0	402.0	402.7	404.0	402.7	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331945-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	723.6	724.6	725.8	726.3	726.2	726.0	725.9	725.9
5°	719.7	721.1	722.5	723.1	722.8	722.5	722.3	721.9
7.5°	712.1	713.3	714.6	715.1	714.9	714.8	714.6	714.4
10°	705.1	706.4	707.6	708.1	707.8	707.5	707.3	706.9
12.5°	697.4	698.4	699.3	699.6	699.4	699.3	699.1	699.0
15°	683.6	684.7	685.8	685.9	685.1	684.3	683.5	682.7
17.5°	666.1	666.8	667.6	667.8	667.6	667.2	666.9	666.6
20°	653.1	653.7	654.2	654.3	653.9	653.5	653.1	652.6
22.5°	639.4	639.8	640.3	640.3	639.8	639.2	638.7	638.1
25°	616.7	616.9	616.9	616.9	616.4	616.0	615.6	615.1
27.5°	592.6	592.6	592.7	592.6	592.0	591.5	590.9	590.4
30°	575.8	575.8	575.8	575.4	574.4	573.4	572.4	571.4
32.5°	558.3	557.5	556.7	556.0	555.5	555.1	554.5	554.0
35°	529.8	529.0	528.2	527.4	526.7	526.0	525.3	524.6
37.5°	500.3	499.4	498.4	497.7	497.3	496.8	496.4	495.9
40°	481.2	480.0	479.0	478.1	477.5	477.0	476.5	475.9
42.5°	461.2	460.1	458.9	458.1	457.5	457.1	456.5	455.9
45°	431.4	429.7	428.0	426.8	426.2	425.4	424.8	424.0
47.5°	399.9	398.3	396.6	395.5	394.9	394.3	393.7	393.1
50°	379.2	377.6	376.1	375.0	374.1	373.2	372.4	371.6
52.5°	358.2	356.9	355.6	354.4	353.6	352.8	352.0	351.1
55°	326.0	324.6	323.0	321.9	321.2	320.5	319.8	319.1
57.5°	294.6	293.2	291.9	290.7	289.9	289.2	288.4	287.6
60°	272.3	271.1	269.8	268.8	268.2	267.4	266.8	266.0
62.5°	250.8	249.6	248.3	247.4	247.0	246.5	246.1	245.6
65°	218.8	217.8	216.6	215.9	215.5	215.1	214.7	214.2
67.5°	187.2	186.2	185.2	184.4	183.8	183.3	182.7	182.1
70°	166.6	165.8	164.8	163.9	163.2	162.5	161.8	161.1
72.5°	145.9	145.0	144.2	143.6	143.2	142.8	142.5	142.1
75°	116.0	115.4	114.6	114.1	113.7	113.2	112.8	112.4
77.5°	88.1	87.6	87.2	86.9	86.9	86.9	86.9	86.9
80°	70.3	70.1	70.0	70.0	70.0	70.0	70.0	70.0
82.5°	54.1	53.8	53.6	53.4	53.3	53.2	53.1	53.0
85°	30.7	30.4	30.1	30.0	30.0	30.0	30.0	30.0
87.5°	14.8	14.9	14.9	15.2	15.1	15.2	15.4	15.2
90°	20.4	21.2	22.0	23.6	22.7	23.6	24.4	23.6
92.5°	68.5	54.4	48.0	43.8	42.3	39.9	40.7	39.2
95°	292.9	198.6	155.5	126.1	110.7	103.4	97.7	94.4
97.5°	730.3	585.0	480.0	382.6	322.6	286.0	264.0	257.0
100°	959.5	893.6	798.3	682.8	600.6	541.2	509.5	510.3
102.5°	1035.7	1033.6	978.0	904.8	840.8	793.8	767.3	748.5
105°	1057.9	1139.4	1154.8	1133.7	1096.2	1065.3	1039.3	1035.2
107.5°	993.8	1126.0	1197.3	1226.3	1226.9	1216.5	1207.7	1200.2
110°	932.6	1082.4	1184.9	1241.9	1264.7	1271.2	1269.6	1268.0



TEST NUMBER: P331945-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	872.0	1025.1	1140.0	1213.2	1254.9	1275.0	1281.2	1281.6
115°	791.8	933.4	1053.0	1141.7	1202.8	1238.6	1254.9	1259.0
117.5°	733.8	856.0	963.4	1053.4	1117.0	1158.1	1181.5	1187.0
120°	703.1	813.0	910.7	992.9	1057.1	1102.7	1122.3	1127.2
122.5°	679.1	778.5	869.0	945.3	1002.5	1043.5	1064.9	1071.1
125°	647.0	735.7	813.8	878.9	931.0	966.8	987.2	992.9
127.5°	619.0	698.1	768.6	827.8	874.2	904.8	923.2	928.4
130°	601.4	674.7	740.5	795.9	839.0	868.4	885.4	891.9
132.5°	585.1	652.5	713.9	766.6	807.1	836.4	851.6	856.1
135°	563.1	620.9	673.8	720.2	760.1	784.5	799.2	804.9
137.5°	543.2	590.5	636.1	676.3	709.8	734.6	746.9	750.6
140°	531.4	572.9	612.0	647.0	677.9	700.7	713.7	712.9
142.5°	520.3	556.0	589.9	620.3	646.7	666.8	678.6	677.8
145°	507.0	533.9	559.9	583.5	603.8	620.9	627.5	629.1
147.5°	496.1	517.4	538.4	555.2	570.6	582.2	588.4	589.1
150°	488.3	507.0	524.1	539.6	551.8	560.7	565.6	565.6
152.5°	481.1	497.3	512.4	525.2	534.8	543.2	546.1	546.1
155°	470.3	483.4	495.6	505.4	512.7	519.2	520.8	521.6
157.5°	459.0	469.9	479.3	487.0	493.3	498.2	499.5	499.4
160°	452.5	461.5	469.5	475.2	480.9	485.8	485.8	485.0
162.5°	444.7	452.3	459.8	464.9	468.6	472.8	472.8	472.0
165°	434.6	439.4	445.2	449.2	452.5	455.8	454.9	454.9
167.5°	425.7	429.5	432.8	435.7	437.2	439.4	438.6	438.6
170°	420.0	422.4	425.6	427.2	428.0	429.7	428.8	428.8
172.5°	414.7	416.5	419.1	420.1	420.3	421.9	420.4	419.8
175°	407.7	408.5	410.2	410.2	410.2	411.0	410.2	409.4
177.5°	403.3	404.0	404.6	404.6	404.0	404.6	403.3	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0

(END OF REPORT)