

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331908-935

Luminaire Tested: **S123DIP-S340D1195U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331908-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1195U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4746.2 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331908-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331908-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	88	84	81	82	79	76	73	61	59	57	45	43	42	30	29	28	22
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	67	60	55	68	60	54	50	47	43	39	35	32	30	23	22	20	15
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	21	19	17	13
5	64	53	45	39	57	47	41	36	37	32	29	28	24	22	19	17	15	11
6	59	47	39	34	52	42	36	31	33	28	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	31	25	21	25	20	17	19	16	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5022	5022	5022
5°	5046	4976	5010
10°	5012	4933	4964
15°	4953	4878	4886
20°	4885	4798	4802
25°	4793	4703	4694
30°	4692	4598	4561
35°	4586	4486	4428
40°	4477	4363	4295
45°	4354	4250	4147
50°	4232	4113	3997
55°	4074	3969	3847
60°	3914	3800	3679
65°	3769	3617	3505
70°	3559	3408	3257
75°	3256	3136	3003
80°	2938	2814	2783
85°	2569	2482	2384



TEST NUMBER: P331908-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	0.9
10°-20°	124.1	2.6
20°-30°	183.3	3.9
30°-40°	214.1	4.5
40°-50°	215.3	4.5
50°-60°	189.1	4.0
60°-70°	140.9	3.0
70°-80°	80.3	1.7
80°-90°	26.8	0.6
90°-100°	83.0	1.7
100°-110°	248.3	5.2
110°-120°	422.3	8.9
120°-130°	555.5	11.7
130°-140°	624.4	13.2
140°-150°	613.8	12.9
150°-160°	516.7	10.9
160°-170°	343.9	7.2
170°-180°	120.4	2.5
0°-30°	351.4	7.4
0°-40°	565.5	11.9
0°-60°	969.9	20.4
0°-90°	1217.8	25.7
90°-120°	753.6	15.9
90°-150°	2547.3	53.7
90°-180°	3528.0	74.3
0°-180°	4746.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	467	467	467	467	467	
5°	467	465	460	464	464	44
15°	444	443	438	441	438	125
25°	404	401	396	396	395	186
35°	349	346	341	339	337	218
45°	286	284	279	275	272	221
55°	217	216	212	207	205	194
65°	148	146	142	139	138	146
75°	78	77	75	73	72	84
85°	21	20	20	19	19	23
90°	1	11	24	28	30	5
95°	59	66	74	78	78	66
105°	225	228	236	236	238	241
115°	425	428	426	427	426	421
125°	622	625	623	619	615	555
135°	807	813	812	808	806	622
145°	979	981	984	983	979	612
155°	1122	1122	1122	1126	1119	516
165°	1222	1219	1218	1224	1218	344
175°	1270	1267	1266	1272	1266	121
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P331908-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	468.2	467.9	467.6	467.4	467.0	466.5	465.7	464.9	464.2	463.4	464.1
5°	467.0	466.5	466.1	465.6	465.2	464.5	463.5	462.5	461.5	460.5	461.4
7.5°	462.4	461.9	461.5	461.1	460.6	459.9	458.9	457.9	456.8	455.8	456.6
10°	458.6	458.1	457.6	457.2	456.8	456.0	454.8	453.7	452.5	451.3	452.1
12.5°	453.4	453.1	452.6	452.3	451.9	451.2	450.1	449.0	447.9	446.9	447.5
15°	444.5	444.2	443.8	443.4	443.1	442.3	441.2	440.0	438.9	437.7	438.4
17.5°	434.1	433.7	433.3	432.7	432.3	431.5	430.3	429.2	428.0	426.9	427.3
20°	426.5	425.9	425.4	424.8	424.3	423.4	422.3	421.1	420.0	418.9	419.2
22.5°	417.8	417.2	416.7	416.2	415.7	414.8	413.6	412.5	411.3	410.2	410.4
25°	403.6	403.0	402.5	402.0	401.5	400.6	399.4	398.3	397.1	396.0	396.1
27.5°	388.4	387.9	387.4	386.8	386.3	385.5	384.3	383.0	381.8	380.5	380.6
30°	377.5	377.0	376.6	376.2	375.7	374.9	373.7	372.4	371.2	369.9	369.9
32.5°	366.6	366.0	365.4	364.8	364.3	363.4	362.5	361.5	360.6	359.6	359.1
35°	349.0	348.5	347.9	347.4	346.9	346.0	344.9	343.7	342.6	341.4	340.9
37.5°	331.1	330.4	329.7	329.0	328.4	327.4	326.2	325.0	323.9	322.7	322.1
40°	318.6	318.0	317.5	316.9	316.4	315.5	314.3	313.0	311.8	310.5	309.8
42.5°	306.0	305.4	304.8	304.2	303.6	302.6	301.4	300.1	298.9	297.6	297.0
45°	286.0	285.7	285.3	285.0	284.6	283.9	282.7	281.5	280.3	279.2	278.2
47.5°	266.2	265.7	265.2	264.7	264.2	263.4	262.3	261.1	260.1	259.0	258.0
50°	252.7	252.3	251.8	251.4	251.0	250.1	249.0	247.9	246.7	245.6	244.5
52.5°	238.6	238.3	238.0	237.7	237.4	236.6	235.4	234.2	233.0	231.7	230.9
55°	217.1	217.0	216.9	216.8	216.7	216.0	214.9	213.7	212.6	211.5	210.4
57.5°	196.5	196.2	195.9	195.6	195.3	194.7	193.7	192.8	191.9	191.0	190.1
60°	181.8	181.7	181.6	181.5	181.4	180.8	179.7	178.7	177.6	176.5	175.7
62.5°	168.6	168.3	168.2	167.9	167.6	167.0	165.9	164.9	163.8	162.7	162.0
65°	148.0	147.6	147.1	146.7	146.3	145.6	144.7	143.8	142.9	142.0	141.3
67.5°	126.3	125.9	125.5	125.1	124.8	124.2	123.6	122.9	122.2	121.5	120.9
70°	113.1	112.6	112.1	111.5	111.0	110.5	109.9	109.3	108.8	108.3	107.7
72.5°	99.4	98.9	98.6	98.2	97.7	97.3	96.7	96.1	95.5	94.9	94.3
75°	78.3	77.8	77.5	77.1	76.8	76.5	76.2	75.9	75.7	75.4	75.0
77.5°	59.5	59.3	59.2	59.0	58.7	58.5	58.2	57.9	57.5	57.2	56.9
80°	47.4	47.1	46.8	46.6	46.2	46.1	45.9	45.7	45.5	45.4	45.2
82.5°	35.5	35.4	35.4	35.3	35.2	35.2	35.1	35.1	35.1	35.0	34.9
85°	20.8	20.7	20.5	20.3	20.1	20.1	20.1	20.1	20.1	20.1	19.9
87.5°	8.5	8.8	9.0	9.2	9.5	9.8	10.3	10.8	11.4	11.9	12.0
90°	1.0	3.2	5.4	7.7	9.9	12.5	15.3	18.3	21.1	24.0	24.9
92.5°	24.2	25.7	27.2	28.8	30.2	31.9	33.5	35.1	36.8	38.4	39.1
95°	59.1	60.6	62.2	63.7	65.3	66.9	68.7	70.4	72.2	74.0	74.9
97.5°	104.9	106.0	107.2	108.3	109.4	110.7	112.0	113.3	114.5	115.8	116.8
100°	136.0	137.4	138.7	140.1	141.4	142.6	143.7	144.8	145.9	147.1	147.7
102.5°	172.0	172.9	173.7	174.4	175.3	176.4	177.9	179.3	180.8	182.3	183.0
105°	225.1	225.5	226.0	226.4	226.9	228.1	230.1	232.1	234.1	236.1	236.1
107.5°	286.7	287.0	287.2	287.5	287.7	288.3	289.1	289.9	290.7	291.5	292.2
110°	325.1	325.5	326.0	326.5	326.9	327.4	327.8	328.2	328.6	329.2	330.0



TEST NUMBER: P331908-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	365.2	365.4	365.7	365.9	366.2	366.4	366.4	366.5	366.6	366.7	367.8
115°	425.2	425.9	426.5	427.1	427.8	427.9	427.5	427.1	426.6	426.2	426.4
117.5°	485.6	486.0	486.5	486.9	487.3	487.3	486.7	486.1	485.6	485.0	484.9
120°	523.2	524.5	525.9	527.2	528.6	528.7	527.5	526.4	525.3	524.2	524.0
122.5°	562.4	563.4	564.4	565.3	566.4	566.5	565.9	565.3	564.8	564.2	563.6
125°	622.2	622.9	623.5	624.2	624.9	625.0	624.6	624.1	623.7	623.3	622.3
127.5°	677.4	678.9	680.3	681.7	683.1	683.6	683.1	682.6	682.2	681.7	680.4
130°	714.3	716.0	717.8	719.6	721.3	721.9	721.3	720.6	720.0	719.3	718.4
132.5°	751.1	752.9	754.7	756.4	758.2	758.9	758.4	757.9	757.3	756.9	755.8
135°	807.3	808.7	809.9	811.3	812.6	813.2	813.0	812.8	812.5	812.3	811.4
137.5°	859.4	860.4	861.5	862.6	863.8	864.6	865.2	865.7	866.3	866.9	866.0
140°	895.4	896.5	897.6	898.7	899.7	900.4	900.7	900.9	901.1	901.4	901.1
142.5°	928.2	929.3	930.4	931.5	932.6	933.3	933.8	934.2	934.5	935.0	934.7
145°	979.4	979.8	980.2	980.7	981.1	981.7	982.4	983.0	983.7	984.4	984.1
147.5°	1024.2	1025.0	1025.8	1026.6	1027.4	1028.1	1028.7	1029.3	1029.9	1030.6	1030.6
150°	1055.4	1055.8	1056.3	1056.7	1057.2	1057.7	1058.1	1058.5	1058.9	1059.4	1059.4
152.5°	1081.0	1081.7	1082.3	1082.9	1083.5	1083.9	1084.2	1084.5	1084.8	1085.0	1085.4
155°	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.8	1122.0	1122.2	1122.4	1123.3
157.5°	1155.8	1155.5	1155.3	1155.0	1154.8	1154.7	1154.9	1155.1	1155.3	1155.5	1156.4
160°	1177.4	1177.0	1176.6	1176.1	1175.7	1175.4	1175.4	1175.4	1175.4	1175.4	1176.6
162.5°	1196.6	1196.0	1195.4	1194.8	1194.2	1193.9	1194.1	1194.3	1194.5	1194.6	1195.8
165°	1221.5	1220.8	1220.1	1219.4	1218.8	1218.5	1218.5	1218.5	1218.5	1218.5	1219.8
167.5°	1241.3	1240.4	1239.5	1238.6	1237.7	1237.3	1237.5	1237.7	1237.9	1238.0	1239.4
170°	1252.5	1251.5	1250.7	1249.8	1248.9	1248.4	1248.4	1248.4	1248.4	1248.4	1250.0
172.5°	1261.3	1260.4	1259.5	1258.6	1257.7	1257.3	1257.3	1257.3	1257.3	1257.3	1258.7
175°	1270.5	1269.6	1268.7	1267.8	1267.0	1266.4	1266.4	1266.4	1266.4	1266.4	1267.8
177.5°	1274.3	1273.6	1272.9	1272.1	1271.4	1271.1	1271.1	1271.1	1271.1	1271.1	1272.1
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P331908-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	464.8	465.5	466.2	466.6	466.5	466.4	466.3	466.2
5°	462.4	463.2	464.2	464.5	464.3	464.2	463.9	463.7
7.5°	457.4	458.2	459.0	459.3	459.3	459.2	459.1	458.9
10°	453.0	453.7	454.5	454.9	454.7	454.5	454.3	454.2
12.5°	448.0	448.6	449.2	449.4	449.4	449.2	449.1	449.0
15°	439.1	439.8	440.6	440.7	440.1	439.5	439.0	438.5
17.5°	427.8	428.3	428.9	429.0	428.8	428.6	428.4	428.3
20°	419.6	419.9	420.3	420.3	420.0	419.7	419.5	419.2
22.5°	410.7	411.0	411.3	411.3	411.0	410.6	410.3	409.9
25°	396.1	396.2	396.3	396.2	396.0	395.7	395.5	395.2
27.5°	380.6	380.7	380.7	380.6	380.3	380.0	379.6	379.3
30°	369.9	369.9	369.9	369.5	368.9	368.3	367.7	367.0
32.5°	358.6	358.1	357.7	357.2	356.9	356.5	356.2	355.9
35°	340.4	339.8	339.2	338.8	338.4	337.9	337.4	337.0
37.5°	321.4	320.8	320.1	319.7	319.4	319.1	318.8	318.6
40°	309.1	308.4	307.6	307.1	306.8	306.4	306.1	305.7
42.5°	296.3	295.5	294.8	294.3	293.9	293.6	293.3	292.8
45°	277.1	276.0	274.9	274.2	273.7	273.3	272.9	272.4
47.5°	256.9	255.9	254.8	254.1	253.7	253.3	252.9	252.5
50°	243.6	242.5	241.6	240.8	240.3	239.8	239.3	238.7
52.5°	230.1	229.2	228.3	227.6	227.1	226.6	226.1	225.6
55°	209.5	208.4	207.5	206.8	206.4	205.9	205.4	205.0
57.5°	189.2	188.3	187.4	186.8	186.2	185.7	185.2	184.7
60°	175.0	174.1	173.3	172.7	172.2	171.8	171.3	170.9
62.5°	161.1	160.3	159.5	158.9	158.7	158.3	158.1	157.7
65°	140.6	139.9	139.1	138.7	138.4	138.1	137.8	137.6
67.5°	120.2	119.6	119.0	118.5	118.1	117.7	117.4	117.0
70°	107.1	106.4	105.8	105.3	104.9	104.4	103.9	103.5
72.5°	93.8	93.2	92.6	92.2	92.0	91.8	91.5	91.3
75°	74.6	74.0	73.6	73.3	73.0	72.8	72.5	72.2
77.5°	56.6	56.3	56.0	55.9	55.9	55.9	55.9	55.9
80°	45.1	45.0	44.9	44.9	44.9	44.9	44.9	44.9
82.5°	34.8	34.6	34.4	34.3	34.3	34.2	34.1	34.0
85°	19.7	19.5	19.4	19.3	19.3	19.3	19.3	19.3
87.5°	12.1	12.1	12.3	12.4	12.5	12.6	12.7	12.7
90°	25.8	26.7	27.6	28.2	28.7	29.1	29.5	30.0
92.5°	39.9	40.6	41.2	41.5	41.2	41.0	40.6	40.4
95°	75.8	76.7	77.6	78.0	78.0	78.0	78.0	78.0
97.5°	117.9	118.9	119.9	120.4	120.3	120.2	120.1	120.0
100°	148.4	149.0	149.7	150.2	150.8	151.2	151.6	152.1
102.5°	183.6	184.3	184.9	185.2	185.1	185.0	184.9	184.9
105°	236.1	236.1	236.1	236.3	236.8	237.2	237.6	238.1
107.5°	292.9	293.7	294.4	294.5	294.3	294.0	293.8	293.5
110°	330.9	331.8	332.7	332.9	332.4	332.0	331.6	331.1



TEST NUMBER: P331908-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	368.9	370.0	371.0	371.5	371.4	371.3	371.3	371.2
115°	426.6	426.8	427.1	427.1	426.8	426.6	426.4	426.2
117.5°	484.9	484.8	484.8	484.5	483.9	483.2	482.6	482.0
120°	523.7	523.6	523.3	523.0	522.5	522.1	521.7	521.2
122.5°	563.1	562.5	561.9	561.3	560.7	560.1	559.4	558.8
125°	621.5	620.6	619.7	618.8	617.9	617.0	616.1	615.3
127.5°	679.2	678.0	676.7	675.5	674.5	673.5	672.4	671.5
130°	717.5	716.6	715.7	714.5	712.9	711.4	709.8	708.3
132.5°	754.8	753.7	752.6	751.5	750.3	749.1	747.9	746.7
135°	810.5	809.6	808.7	808.0	807.6	807.2	806.8	806.3
137.5°	865.0	864.1	863.2	862.3	861.4	860.7	859.8	858.9
140°	900.9	900.7	900.4	899.6	898.0	896.5	894.9	893.4
142.5°	934.5	934.3	934.1	933.3	932.1	930.9	929.8	928.6
145°	984.0	983.7	983.5	982.9	982.1	981.1	980.2	979.4
147.5°	1030.6	1030.6	1030.6	1029.9	1028.6	1027.3	1025.9	1024.6
150°	1059.4	1059.4	1059.4	1058.8	1057.4	1056.1	1054.7	1053.4
152.5°	1085.7	1086.1	1086.4	1086.1	1084.9	1083.7	1082.5	1081.4
155°	1124.2	1125.1	1126.0	1125.7	1124.1	1122.6	1121.0	1119.4
157.5°	1157.3	1158.2	1159.2	1159.0	1157.8	1156.5	1155.3	1154.0
160°	1177.7	1178.8	1179.9	1180.0	1179.1	1178.2	1177.3	1176.5
162.5°	1196.9	1198.0	1199.1	1198.9	1197.5	1196.1	1194.6	1193.3
165°	1221.2	1222.4	1223.8	1223.7	1222.1	1220.6	1219.0	1217.5
167.5°	1240.8	1242.2	1243.5	1243.5	1242.2	1240.8	1239.4	1238.0
170°	1251.5	1253.2	1254.7	1254.7	1253.2	1251.5	1250.0	1248.4
172.5°	1260.1	1261.5	1262.8	1262.7	1261.1	1259.6	1258.0	1256.5
175°	1269.1	1270.5	1271.8	1271.7	1270.1	1268.6	1267.0	1265.5
177.5°	1273.2	1274.3	1275.3	1275.2	1274.0	1272.7	1271.5	1270.3
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5

(END OF REPORT)