

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331953-930

Luminaire Tested: **S123DIP-S560D1195U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331953-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1195U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5234.6 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331953-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331953-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31	25
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	21
4	72	61	53	48	65	56	49	44	45	40	36	36	32	29	27	24	22	18
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	21	20	16
6	61	49	41	35	55	44	37	32	36	31	27	29	25	22	22	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7854	7747	7800
10°	7803	7679	7726
15°	7710	7592	7608
20°	7605	7468	7475
25°	7462	7321	7305
30°	7305	7157	7102
35°	7139	6984	6893
40°	6968	6792	6687
45°	6779	6616	6454
50°	6589	6400	6223
55°	6341	6176	5988
60°	6090	5916	5726
65°	5871	5631	5456
70°	5542	5306	5070
75°	5065	4882	4675
80°	4568	4376	4339
85°	4001	3853	3705



TEST NUMBER: P331953-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	1.3
10°-20°	193.2	3.7
20°-30°	285.4	5.5
30°-40°	333.3	6.4
40°-50°	335.1	6.4
50°-60°	294.4	5.6
60°-70°	219.3	4.2
70°-80°	124.9	2.4
80°-90°	39.4	0.8
90°-100°	78.6	1.5
100°-110°	235.1	4.5
110°-120°	399.9	7.6
120°-130°	526.0	10.0
130°-140°	591.2	11.3
140°-150°	581.2	11.1
150°-160°	489.3	9.3
160°-170°	325.7	6.2
170°-180°	114.0	2.2
0°-30°	547.0	10.4
0°-40°	880.3	16.8
0°-60°	1509.9	28.8
0°-90°	1893.6	36.2
90°-120°	713.6	13.6
90°-150°	2412.1	46.1
90°-180°	3341.0	63.8
0°-180°	5234.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	727	724	717	723	722	69
15°	692	689	681	686	683	195
25°	628	624	616	617	615	289
35°	543	539	532	528	525	340
45°	445	442	435	427	424	344
55°	338	337	329	322	319	303
65°	230	227	221	216	214	227
75°	122	119	117	114	112	130
85°	32	31	31	30	30	36
90°	1	11	23	26	28	5
95°	56	63	70	74	74	63
105°	213	215	224	224	225	228
115°	403	405	404	404	404	398
125°	589	592	590	586	583	525
135°	764	770	769	766	764	589
145°	927	929	932	931	927	579
155°	1062	1062	1063	1066	1060	489
165°	1157	1154	1154	1159	1153	326
175°	1203	1199	1199	1204	1198	114
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P331953-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	728.8	728.4	728.0	727.5	727.1	726.2	725.0	723.7	722.6	721.4	722.4
5°	726.9	726.3	725.5	724.9	724.1	723.1	721.5	720.0	718.5	717.0	718.4
7.5°	719.8	719.2	718.4	717.8	717.1	715.9	714.4	712.7	711.2	709.6	710.9
10°	713.9	713.1	712.5	711.8	711.1	709.8	708.0	706.2	704.4	702.6	703.8
12.5°	705.9	705.2	704.7	704.1	703.5	702.4	700.7	699.0	697.3	695.6	696.5
15°	691.9	691.5	690.9	690.3	689.7	688.6	686.8	685.0	683.1	681.3	682.5
17.5°	675.9	675.1	674.4	673.7	672.9	671.7	669.9	668.1	666.3	664.5	665.3
20°	663.9	663.1	662.2	661.4	660.6	659.3	657.5	655.7	653.8	652.0	652.6
22.5°	650.4	649.5	648.7	647.9	647.0	645.7	643.9	642.1	640.3	638.5	639.0
25°	628.3	627.5	626.6	625.8	624.9	623.6	621.8	620.0	618.2	616.4	616.5
27.5°	604.7	603.9	603.1	602.3	601.4	600.1	598.1	596.2	594.3	592.3	592.4
30°	587.7	587.0	586.3	585.6	584.9	583.6	581.6	579.7	577.8	575.8	575.8
32.5°	570.7	569.8	568.8	567.9	567.0	565.8	564.4	562.8	561.3	559.9	559.1
35°	543.3	542.5	541.7	540.9	540.1	538.7	536.9	535.1	533.3	531.5	530.7
37.5°	515.4	514.3	513.2	512.2	511.1	509.7	507.8	506.1	504.2	502.4	501.4
40°	495.9	495.0	494.2	493.4	492.5	491.1	489.2	487.3	485.3	483.4	482.2
42.5°	476.4	475.5	474.5	473.5	472.6	471.2	469.2	467.3	465.4	463.4	462.3
45°	445.3	444.7	444.2	443.6	443.0	441.9	440.1	438.3	436.5	434.6	433.0
47.5°	414.4	413.6	412.9	412.1	411.2	409.9	408.3	406.6	404.9	403.2	401.5
50°	393.5	392.7	392.1	391.3	390.7	389.5	387.6	385.8	384.0	382.2	380.7
52.5°	371.5	371.0	370.6	370.1	369.6	368.4	366.5	364.6	362.6	360.8	359.5
55°	337.9	337.7	337.6	337.5	337.3	336.3	334.5	332.7	330.9	329.1	327.6
57.5°	305.9	305.4	304.9	304.5	304.0	303.0	301.6	300.2	298.7	297.3	296.0
60°	282.9	282.7	282.7	282.5	282.3	281.4	279.8	278.1	276.5	274.8	273.5
62.5°	262.4	262.0	261.7	261.4	261.0	260.0	258.3	256.7	254.9	253.3	252.1
65°	230.5	229.8	229.1	228.4	227.7	226.7	225.3	223.9	222.5	221.1	220.0
67.5°	196.6	196.0	195.3	194.8	194.1	193.3	192.2	191.2	190.1	189.1	188.2
70°	176.1	175.3	174.5	173.7	172.8	171.9	171.1	170.3	169.4	168.6	167.6
72.5°	154.7	154.0	153.4	152.8	152.2	151.4	150.5	149.5	148.5	147.7	146.8
75°	121.8	121.2	120.7	120.1	119.6	119.1	118.6	118.2	117.8	117.4	116.8
77.5°	92.7	92.4	92.0	91.8	91.5	91.1	90.6	90.1	89.5	89.0	88.6
80°	73.7	73.3	72.9	72.5	72.0	71.7	71.4	71.1	70.8	70.6	70.4
82.5°	55.2	55.1	55.0	55.0	54.9	54.8	54.8	54.7	54.6	54.6	54.3
85°	32.4	32.2	32.0	31.6	31.4	31.2	31.2	31.2	31.2	31.2	31.0
87.5°	13.2	13.3	13.4	13.5	13.5	13.8	14.3	14.7	15.1	15.6	15.6
90°	1.0	3.0	5.1	7.3	9.4	11.8	14.5	17.3	20.0	22.7	23.6
92.5°	22.9	24.4	25.8	27.2	28.6	30.2	31.7	33.3	34.8	36.4	37.0
95°	55.9	57.4	58.9	60.3	61.8	63.3	65.1	66.7	68.4	70.1	70.9
97.5°	99.3	100.4	101.5	102.6	103.6	104.8	106.1	107.3	108.4	109.7	110.6
100°	128.8	130.1	131.3	132.6	133.9	135.0	136.1	137.1	138.2	139.3	139.9
102.5°	162.9	163.7	164.4	165.2	166.0	167.1	168.4	169.8	171.2	172.6	173.3
105°	213.1	213.5	214.0	214.4	214.8	216.0	217.8	219.8	221.7	223.6	223.6
107.5°	271.5	271.7	272.0	272.2	272.5	273.0	273.8	274.5	275.2	276.1	276.7
110°	307.9	308.3	308.7	309.2	309.6	310.0	310.4	310.8	311.2	311.7	312.5



TEST NUMBER: P331953-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	345.8	346.0	346.3	346.5	346.7	346.9	347.0	347.1	347.2	347.2	348.3
115°	402.6	403.2	403.8	404.5	405.1	405.2	404.8	404.4	404.0	403.6	403.7
117.5°	459.8	460.2	460.6	461.1	461.5	461.5	460.9	460.3	459.8	459.3	459.2
120°	495.5	496.7	498.0	499.2	500.5	500.6	499.5	498.5	497.4	496.4	496.2
122.5°	532.6	533.5	534.4	535.3	536.3	536.5	535.9	535.3	534.8	534.3	533.7
125°	589.2	589.9	590.4	591.1	591.7	591.8	591.4	591.0	590.6	590.2	589.3
127.5°	641.5	642.9	644.2	645.6	646.9	647.3	646.9	646.4	646.0	645.5	644.3
130°	676.4	678.0	679.7	681.4	683.1	683.6	683.0	682.3	681.8	681.1	680.3
132.5°	711.2	712.9	714.6	716.2	718.0	718.6	718.1	717.6	717.1	716.7	715.7
135°	764.4	765.7	767.0	768.3	769.5	770.1	769.8	769.6	769.4	769.2	768.3
137.5°	813.8	814.7	815.8	816.8	817.9	818.7	819.3	819.8	820.4	820.9	820.0
140°	847.8	848.9	849.9	851.0	852.0	852.6	852.9	853.0	853.3	853.5	853.3
142.5°	878.9	880.0	881.0	882.1	883.1	883.8	884.2	884.6	884.9	885.3	885.1
145°	927.4	927.8	928.2	928.6	929.0	929.6	930.3	930.8	931.5	932.1	931.9
147.5°	969.8	970.6	971.3	972.1	972.9	973.5	974.1	974.7	975.3	975.9	975.9
150°	999.4	999.8	1000.2	1000.6	1001.1	1001.5	1001.9	1002.3	1002.7	1003.1	1003.1
152.5°	1023.6	1024.3	1024.8	1025.4	1026.0	1026.4	1026.6	1027.0	1027.2	1027.4	1027.8
155°	1061.9	1061.9	1061.9	1061.9	1061.9	1062.0	1062.3	1062.4	1062.7	1062.8	1063.7
157.5°	1094.5	1094.2	1094.0	1093.7	1093.5	1093.4	1093.6	1093.8	1094.0	1094.1	1095.0
160°	1114.9	1114.5	1114.1	1113.7	1113.3	1113.0	1113.0	1113.0	1113.0	1113.0	1114.1
162.5°	1133.1	1132.5	1132.0	1131.4	1130.8	1130.6	1130.7	1130.9	1131.1	1131.2	1132.3
165°	1156.7	1156.0	1155.4	1154.7	1154.1	1153.8	1153.8	1153.8	1153.8	1153.8	1155.0
167.5°	1175.4	1174.5	1173.7	1172.9	1172.0	1171.7	1171.8	1172.0	1172.2	1172.3	1173.6
170°	1186.0	1185.1	1184.3	1183.5	1182.6	1182.2	1182.2	1182.2	1182.2	1182.2	1183.7
172.5°	1194.3	1193.5	1192.6	1191.8	1191.0	1190.6	1190.6	1190.6	1190.6	1190.6	1191.9
175°	1203.1	1202.2	1201.3	1200.5	1199.7	1199.2	1199.2	1199.2	1199.2	1199.2	1200.5
177.5°	1206.6	1206.0	1205.3	1204.6	1204.0	1203.6	1203.6	1203.6	1203.6	1203.6	1204.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P331953-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	723.6	724.6	725.8	726.3	726.2	726.0	725.9	725.9
5°	719.7	721.1	722.5	723.1	722.8	722.5	722.3	721.9
7.5°	712.1	713.3	714.6	715.1	714.9	714.8	714.6	714.4
10°	705.1	706.4	707.6	708.1	707.8	707.5	707.3	706.9
12.5°	697.4	698.4	699.3	699.6	699.4	699.3	699.1	699.0
15°	683.6	684.7	685.8	685.9	685.1	684.3	683.5	682.7
17.5°	666.1	666.8	667.6	667.8	667.6	667.2	666.9	666.6
20°	653.1	653.7	654.2	654.3	653.9	653.5	653.1	652.6
22.5°	639.4	639.8	640.3	640.3	639.8	639.2	638.7	638.1
25°	616.7	616.9	616.9	616.9	616.4	616.0	615.6	615.1
27.5°	592.6	592.6	592.7	592.6	592.0	591.5	590.9	590.4
30°	575.8	575.8	575.8	575.4	574.4	573.4	572.4	571.4
32.5°	558.3	557.5	556.7	556.0	555.5	555.1	554.5	554.0
35°	529.8	529.0	528.2	527.4	526.7	526.0	525.3	524.6
37.5°	500.3	499.4	498.4	497.7	497.3	496.8	496.4	495.9
40°	481.2	480.0	479.0	478.1	477.5	477.0	476.5	475.9
42.5°	461.2	460.1	458.9	458.1	457.5	457.1	456.5	455.9
45°	431.4	429.7	428.0	426.8	426.2	425.4	424.8	424.0
47.5°	399.9	398.3	396.6	395.5	394.9	394.3	393.7	393.1
50°	379.2	377.6	376.1	375.0	374.1	373.2	372.4	371.6
52.5°	358.2	356.9	355.6	354.4	353.6	352.8	352.0	351.1
55°	326.0	324.6	323.0	321.9	321.2	320.5	319.8	319.1
57.5°	294.6	293.2	291.9	290.7	289.9	289.2	288.4	287.6
60°	272.3	271.1	269.8	268.8	268.2	267.4	266.8	266.0
62.5°	250.8	249.6	248.3	247.4	247.0	246.5	246.1	245.6
65°	218.8	217.8	216.6	215.9	215.5	215.1	214.7	214.2
67.5°	187.2	186.2	185.2	184.4	183.8	183.3	182.7	182.1
70°	166.6	165.8	164.8	163.9	163.2	162.5	161.8	161.1
72.5°	145.9	145.0	144.2	143.6	143.2	142.8	142.5	142.1
75°	116.0	115.4	114.6	114.1	113.7	113.2	112.8	112.4
77.5°	88.1	87.6	87.2	86.9	86.9	86.9	86.9	86.9
80°	70.3	70.1	70.0	70.0	70.0	70.0	70.0	70.0
82.5°	54.1	53.8	53.6	53.4	53.3	53.2	53.1	53.0
85°	30.7	30.4	30.1	30.0	30.0	30.0	30.0	30.0
87.5°	15.7	15.7	15.7	15.8	15.9	16.0	16.1	16.1
90°	24.5	25.3	26.1	26.7	27.1	27.6	28.0	28.5
92.5°	37.7	38.4	39.1	39.3	39.1	38.8	38.5	38.2
95°	71.7	72.6	73.5	73.9	73.9	73.9	73.9	73.9
97.5°	111.6	112.6	113.6	114.0	113.9	113.8	113.7	113.7
100°	140.5	141.1	141.8	142.3	142.8	143.2	143.6	144.0
102.5°	173.8	174.5	175.1	175.4	175.3	175.2	175.1	175.0
105°	223.6	223.6	223.6	223.8	224.2	224.6	225.0	225.4
107.5°	277.4	278.1	278.8	278.9	278.7	278.4	278.2	277.9
110°	313.3	314.2	315.0	315.2	314.8	314.4	314.0	313.6



TEST NUMBER: P331953-930

CATALOG NUMBER: S123DIP-S560D1195U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	349.3	350.3	351.3	351.8	351.7	351.6	351.6	351.5
115°	404.0	404.1	404.4	404.4	404.1	404.0	403.7	403.6
117.5°	459.2	459.1	459.1	458.8	458.2	457.5	457.0	456.4
120°	495.9	495.8	495.5	495.2	494.8	494.4	494.0	493.5
122.5°	533.2	532.6	532.1	531.5	530.9	530.4	529.7	529.1
125°	588.5	587.7	586.8	586.0	585.1	584.2	583.4	582.6
127.5°	643.1	642.0	640.7	639.7	638.7	637.7	636.7	635.9
130°	679.4	678.6	677.8	676.5	675.1	673.6	672.1	670.7
132.5°	714.7	713.7	712.7	711.6	710.5	709.3	708.2	707.0
135°	767.5	766.6	765.8	765.2	764.8	764.3	763.9	763.5
137.5°	819.1	818.2	817.3	816.5	815.7	815.0	814.2	813.3
140°	853.0	852.9	852.6	851.8	850.4	848.9	847.4	846.0
142.5°	884.9	884.7	884.5	883.8	882.6	881.5	880.4	879.3
145°	931.7	931.5	931.3	930.7	929.9	929.0	928.2	927.4
147.5°	975.9	975.9	975.9	975.3	974.0	972.7	971.4	970.2
150°	1003.1	1003.1	1003.1	1002.6	1001.3	1000.0	998.7	997.5
152.5°	1028.1	1028.4	1028.7	1028.4	1027.3	1026.2	1025.1	1024.0
155°	1064.5	1065.4	1066.2	1065.9	1064.5	1063.0	1061.5	1060.0
157.5°	1095.8	1096.7	1097.6	1097.5	1096.3	1095.1	1094.0	1092.7
160°	1115.2	1116.2	1117.3	1117.4	1116.6	1115.7	1114.8	1114.0
162.5°	1133.3	1134.4	1135.5	1135.3	1133.9	1132.6	1131.2	1129.9
165°	1156.3	1157.6	1158.9	1158.7	1157.2	1155.8	1154.3	1152.8
167.5°	1174.9	1176.2	1177.5	1177.5	1176.2	1174.9	1173.6	1172.3
170°	1185.1	1186.7	1188.1	1188.1	1186.7	1185.1	1183.7	1182.2
172.5°	1193.2	1194.5	1195.8	1195.7	1194.2	1192.7	1191.2	1189.8
175°	1201.8	1203.1	1204.3	1204.2	1202.7	1201.3	1199.8	1198.3
177.5°	1205.7	1206.6	1207.6	1207.5	1206.4	1205.2	1204.0	1202.9
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9

(END OF REPORT)