

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331918-930

Luminaire Tested: **S123DIP-S560D365U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331918-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D365U930-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2961.9 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331918-930
CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331918-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58	54
2	92	84	78	72	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	74	66	60	78	70	63	58	62	56	52	54	50	47	47	44	41	38
4	77	65	57	51	72	62	54	49	55	49	44	48	44	40	42	39	36	33
5	70	58	50	44	66	55	48	42	49	43	38	43	39	35	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	35	31	27	25
7	60	47	39	34	56	45	38	32	40	34	30	36	31	27	32	28	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	39	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7854	7747	7800
10°	7803	7679	7726
15°	7710	7592	7608
20°	7605	7468	7475
25°	7462	7321	7305
30°	7305	7157	7102
35°	7139	6984	6893
40°	6968	6792	6687
45°	6779	6616	6454
50°	6589	6400	6223
55°	6341	6176	5988
60°	6090	5916	5726
65°	5871	5631	5456
70°	5542	5306	5070
75°	5065	4882	4675
80°	4568	4376	4339
85°	4001	3853	3705



TEST NUMBER: P331918-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	2.3
10°-20°	193.2	6.5
20°-30°	285.4	9.6
30°-40°	333.3	11.3
40°-50°	335.1	11.3
50°-60°	294.4	9.9
60°-70°	219.3	7.4
70°-80°	124.9	4.2
80°-90°	37.0	1.2
90°-100°	79.2	2.7
100°-110°	224.3	7.6
110°-120°	220.6	7.4
120°-130°	176.0	5.9
130°-140°	138.8	4.7
140°-150°	103.6	3.5
150°-160°	72.2	2.4
160°-170°	42.4	1.4
170°-180°	13.8	0.5
0°-30°	547.0	18.5
0°-40°	880.3	29.7
0°-60°	1509.9	51.0
0°-90°	1891.1	63.8
90°-120°	524.1	17.7
90°-150°	942.4	31.8
90°-180°	1071.0	36.2
0°-180°	2961.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	727	724	717	723	722	69
15°	692	689	681	686	683	195
25°	628	624	616	617	615	289
35°	543	539	532	528	525	340
45°	445	442	435	427	424	344
55°	338	337	329	322	319	303
65°	230	227	221	216	214	227
75°	122	119	117	114	112	130
85°	32	31	31	30	30	36
90°	1	4	7	8	8	2
95°	10	32	171	50	33	11
105°	33	49	232	405	366	36
115°	59	74	177	388	446	58
125°	82	97	165	300	352	73
135°	96	115	163	247	285	74
145°	110	126	161	202	223	69
155°	125	135	156	177	185	57
165°	136	140	149	158	161	38
175°	142	142	143	145	145	13
180°	142	142	142	142	142	



TEST NUMBER: P331918-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	728.8	728.4	728.0	727.5	727.1	726.2	725.0	723.7	722.6	721.4	722.4
5°	726.9	726.3	725.5	724.9	724.1	723.1	721.5	720.0	718.5	717.0	718.4
7.5°	719.8	719.2	718.4	717.8	717.1	715.9	714.4	712.7	711.2	709.6	710.9
10°	713.9	713.1	712.5	711.8	711.1	709.8	708.0	706.2	704.4	702.6	703.8
12.5°	705.9	705.2	704.7	704.1	703.5	702.4	700.7	699.0	697.3	695.6	696.5
15°	691.9	691.5	690.9	690.3	689.7	688.6	686.8	685.0	683.1	681.3	682.5
17.5°	675.9	675.1	674.4	673.7	672.9	671.7	669.9	668.1	666.3	664.5	665.3
20°	663.9	663.1	662.2	661.4	660.6	659.3	657.5	655.7	653.8	652.0	652.6
22.5°	650.4	649.5	648.7	647.9	647.0	645.7	643.9	642.1	640.3	638.5	639.0
25°	628.3	627.5	626.6	625.8	624.9	623.6	621.8	620.0	618.2	616.4	616.5
27.5°	604.7	603.9	603.1	602.3	601.4	600.1	598.1	596.2	594.3	592.3	592.4
30°	587.7	587.0	586.3	585.6	584.9	583.6	581.6	579.7	577.8	575.8	575.8
32.5°	570.7	569.8	568.8	567.9	567.0	565.8	564.4	562.8	561.3	559.9	559.1
35°	543.3	542.5	541.7	540.9	540.1	538.7	536.9	535.1	533.3	531.5	530.7
37.5°	515.4	514.3	513.2	512.2	511.1	509.7	507.8	506.1	504.2	502.4	501.4
40°	495.9	495.0	494.2	493.4	492.5	491.1	489.2	487.3	485.3	483.4	482.2
42.5°	476.4	475.5	474.5	473.5	472.6	471.2	469.2	467.3	465.4	463.4	462.3
45°	445.3	444.7	444.2	443.6	443.0	441.9	440.1	438.3	436.5	434.6	433.0
47.5°	414.4	413.6	412.9	412.1	411.2	409.9	408.3	406.6	404.9	403.2	401.5
50°	393.5	392.7	392.1	391.3	390.7	389.5	387.6	385.8	384.0	382.2	380.7
52.5°	371.5	371.0	370.6	370.1	369.6	368.4	366.5	364.6	362.6	360.8	359.5
55°	337.9	337.7	337.6	337.5	337.3	336.3	334.5	332.7	330.9	329.1	327.6
57.5°	305.9	305.4	304.9	304.5	304.0	303.0	301.6	300.2	298.7	297.3	296.0
60°	282.9	282.7	282.7	282.5	282.3	281.4	279.8	278.1	276.5	274.8	273.5
62.5°	262.4	262.0	261.7	261.4	261.0	260.0	258.3	256.7	254.9	253.3	252.1
65°	230.5	229.8	229.1	228.4	227.7	226.7	225.3	223.9	222.5	221.1	220.0
67.5°	196.6	196.0	195.3	194.8	194.1	193.3	192.2	191.2	190.1	189.1	188.2
70°	176.1	175.3	174.5	173.7	172.8	171.9	171.1	170.3	169.4	168.6	167.6
72.5°	154.7	154.0	153.4	152.8	152.2	151.4	150.5	149.5	148.5	147.7	146.8
75°	121.8	121.2	120.7	120.1	119.6	119.1	118.6	118.2	117.8	117.4	116.8
77.5°	92.7	92.4	92.0	91.8	91.5	91.1	90.6	90.1	89.5	89.0	88.6
80°	73.7	73.3	72.9	72.5	72.0	71.7	71.4	71.1	70.8	70.6	70.4
82.5°	55.2	55.1	55.0	55.0	54.9	54.8	54.8	54.7	54.6	54.6	54.3
85°	32.4	32.2	32.0	31.6	31.4	31.2	31.2	31.2	31.2	31.2	31.0
87.5°	13.1	12.9	12.6	12.5	12.3	12.1	12.2	12.3	12.4	12.4	12.2
90°	0.6	1.1	1.7	2.6	3.2	3.8	4.6	5.5	6.4	7.2	6.9
92.5°	3.6	5.3	7.7	9.9	12.4	16.6	24.2	36.6	48.8	44.3	33.4
95°	9.8	10.7	13.9	18.8	26.3	37.4	62.0	104.8	152.1	170.9	138.6
97.5°	16.7	17.0	19.5	23.7	31.1	43.3	66.7	115.0	193.9	264.8	283.2
100°	21.4	21.6	23.6	27.6	34.6	45.8	66.0	108.6	184.4	272.9	329.6
102.5°	26.2	26.7	28.5	32.3	38.5	48.8	66.9	103.1	170.6	257.9	331.9
105°	33.4	34.3	36.0	39.5	44.9	53.9	69.5	99.1	153.6	231.6	314.3
107.5°	41.2	42.0	43.7	47.0	52.2	60.5	74.2	98.8	142.8	208.5	283.6
110°	46.6	47.5	49.0	52.2	57.1	65.1	78.1	100.0	138.6	195.3	264.2



TEST NUMBER: P331918-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	51.8	52.6	54.1	57.2	62.1	70.0	82.0	102.3	136.2	186.5	247.4
115°	59.0	60.3	62.0	64.8	69.7	77.5	88.5	106.0	135.4	177.2	227.1
117.5°	66.4	67.7	69.1	71.8	77.3	84.5	95.3	111.0	135.9	171.6	214.7
120°	71.4	72.3	73.8	76.6	82.1	89.3	99.7	114.6	136.9	169.1	208.3
122.5°	75.8	76.7	78.1	81.3	86.5	94.2	104.3	118.1	138.4	167.5	203.0
125°	82.1	82.7	84.4	87.6	93.0	100.9	111.0	123.6	140.9	165.3	196.2
127.5°	86.9	87.7	89.9	93.1	99.1	107.0	116.7	128.1	143.7	164.4	190.2
130°	89.9	90.7	93.4	96.8	102.9	110.6	120.2	131.1	145.5	163.6	186.9
132.5°	92.2	93.3	96.1	100.3	106.3	113.9	123.1	133.9	146.9	163.4	184.0
135°	96.2	97.3	100.5	104.8	111.0	118.7	127.6	137.5	149.0	163.1	180.1
137.5°	100.0	101.3	104.4	108.9	115.0	122.1	130.8	140.1	150.3	162.4	176.7
140°	102.6	104.0	106.9	111.5	117.2	124.5	132.8	141.5	151.2	162.2	174.6
142.5°	105.3	106.6	109.7	113.8	119.6	126.3	134.4	142.8	152.0	161.8	172.8
145°	109.7	110.6	113.2	117.6	122.5	129.1	136.6	144.3	152.4	161.0	170.2
147.5°	114.3	114.8	117.3	121.1	125.8	131.4	138.3	145.3	152.4	160.0	167.9
150°	117.2	117.6	119.8	123.6	127.6	132.8	139.4	145.5	152.4	159.1	166.2
152.5°	120.3	120.3	122.6	125.9	129.5	134.4	140.1	145.9	151.7	157.9	164.4
155°	124.7	124.7	126.5	129.4	132.6	136.6	141.5	146.1	151.0	155.9	161.6
157.5°	128.3	128.6	130.0	132.5	135.2	138.3	142.2	146.3	150.0	154.1	158.5
160°	131.1	131.1	132.2	134.5	136.6	139.4	142.9	146.3	149.5	152.7	156.5
162.5°	133.1	133.1	134.1	135.9	137.7	140.1	143.2	146.1	148.6	151.3	154.3
165°	136.2	136.0	136.6	138.0	139.2	141.2	143.5	145.5	147.2	149.3	151.6
167.5°	138.6	138.3	138.6	139.7	140.5	141.8	143.4	145.0	145.9	147.2	148.9
170°	140.0	139.4	139.7	140.6	141.2	141.8	143.2	144.3	145.0	145.8	147.2
172.5°	141.0	140.6	140.6	141.3	141.6	141.9	143.2	144.1	144.2	144.6	145.6
175°	142.0	141.8	141.5	142.0	142.0	142.4	142.9	143.5	143.2	143.2	143.7
177.5°	142.6	142.4	142.1	142.4	142.4	142.4	142.6	143.0	142.6	142.4	142.6
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P331918-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	723.6	724.6	725.8	726.3	726.2	726.0	725.9	725.9
5°	719.7	721.1	722.5	723.1	722.8	722.5	722.3	721.9
7.5°	712.1	713.3	714.6	715.1	714.9	714.8	714.6	714.4
10°	705.1	706.4	707.6	708.1	707.8	707.5	707.3	706.9
12.5°	697.4	698.4	699.3	699.6	699.4	699.3	699.1	699.0
15°	683.6	684.7	685.8	685.9	685.1	684.3	683.5	682.7
17.5°	666.1	666.8	667.6	667.8	667.6	667.2	666.9	666.6
20°	653.1	653.7	654.2	654.3	653.9	653.5	653.1	652.6
22.5°	639.4	639.8	640.3	640.3	639.8	639.2	638.7	638.1
25°	616.7	616.9	616.9	616.9	616.4	616.0	615.6	615.1
27.5°	592.6	592.6	592.7	592.6	592.0	591.5	590.9	590.4
30°	575.8	575.8	575.8	575.4	574.4	573.4	572.4	571.4
32.5°	558.3	557.5	556.7	556.0	555.5	555.1	554.5	554.0
35°	529.8	529.0	528.2	527.4	526.7	526.0	525.3	524.6
37.5°	500.3	499.4	498.4	497.7	497.3	496.8	496.4	495.9
40°	481.2	480.0	479.0	478.1	477.5	477.0	476.5	475.9
42.5°	461.2	460.1	458.9	458.1	457.5	457.1	456.5	455.9
45°	431.4	429.7	428.0	426.8	426.2	425.4	424.8	424.0
47.5°	399.9	398.3	396.6	395.5	394.9	394.3	393.7	393.1
50°	379.2	377.6	376.1	375.0	374.1	373.2	372.4	371.6
52.5°	358.2	356.9	355.6	354.4	353.6	352.8	352.0	351.1
55°	326.0	324.6	323.0	321.9	321.2	320.5	319.8	319.1
57.5°	294.6	293.2	291.9	290.7	289.9	289.2	288.4	287.6
60°	272.3	271.1	269.8	268.8	268.2	267.4	266.8	266.0
62.5°	250.8	249.6	248.3	247.4	247.0	246.5	246.1	245.6
65°	218.8	217.8	216.6	215.9	215.5	215.1	214.7	214.2
67.5°	187.2	186.2	185.2	184.4	183.8	183.3	182.7	182.1
70°	166.6	165.8	164.8	163.9	163.2	162.5	161.8	161.1
72.5°	145.9	145.0	144.2	143.6	143.2	142.8	142.5	142.1
75°	116.0	115.4	114.6	114.1	113.7	113.2	112.8	112.4
77.5°	88.1	87.6	87.2	86.9	86.9	86.9	86.9	86.9
80°	70.3	70.1	70.0	70.0	70.0	70.0	70.0	70.0
82.5°	54.1	53.8	53.6	53.4	53.3	53.2	53.1	53.0
85°	30.7	30.4	30.1	30.0	30.0	30.0	30.0	30.0
87.5°	12.2	12.1	12.1	12.1	12.1	12.1	12.2	12.1
90°	7.2	7.5	7.7	8.3	8.1	8.3	8.6	8.3
92.5°	24.3	19.2	17.0	15.5	15.0	14.1	14.4	13.9
95°	103.7	70.3	55.0	44.7	39.2	36.6	34.6	33.4
97.5°	258.5	207.1	169.9	135.5	114.2	101.3	93.4	91.0
100°	339.7	316.3	282.7	241.7	212.6	191.6	180.3	180.7
102.5°	366.6	365.9	346.3	320.3	297.7	281.0	271.7	265.0
105°	374.5	403.3	408.8	401.4	388.1	377.2	367.9	366.5
107.5°	351.8	398.6	423.9	434.1	434.4	430.6	427.5	424.9
110°	330.2	383.2	419.5	439.7	447.8	450.0	449.5	448.9



TEST NUMBER: P331918-930

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	308.8	362.9	403.6	429.5	444.3	451.4	453.6	453.7
115°	280.3	330.4	372.8	404.2	425.8	438.5	444.3	445.7
117.5°	259.8	303.0	341.0	372.9	395.5	410.0	418.2	420.2
120°	248.9	287.8	322.4	351.5	374.2	390.4	397.3	399.0
122.5°	240.4	275.6	307.6	334.7	354.9	369.4	377.0	379.2
125°	229.0	260.5	288.1	311.2	329.6	342.3	349.5	351.5
127.5°	219.2	247.1	272.1	293.1	309.5	320.3	326.9	328.6
130°	212.9	238.9	262.2	281.8	297.0	307.4	313.5	315.8
132.5°	207.2	231.0	252.7	271.4	285.8	296.1	301.5	303.1
135°	199.3	219.8	238.6	254.9	269.1	277.8	282.9	284.9
137.5°	192.2	209.0	225.2	239.5	251.3	260.1	264.4	265.8
140°	188.2	202.8	216.6	229.0	240.0	248.1	252.7	252.4
142.5°	184.3	196.8	208.8	219.6	228.9	236.1	240.2	239.9
145°	179.5	189.0	198.2	206.6	213.8	219.8	222.2	222.7
147.5°	175.6	183.2	190.6	196.6	202.0	206.1	208.3	208.6
150°	172.8	179.5	185.6	191.0	195.3	198.5	200.2	200.2
152.5°	170.3	176.0	181.4	186.0	189.3	192.2	193.3	193.3
155°	166.6	171.1	175.5	178.9	181.5	183.8	184.4	184.7
157.5°	162.5	166.3	169.7	172.4	174.6	176.3	176.8	176.8
160°	160.2	163.4	166.2	168.3	170.2	172.0	172.0	171.7
162.5°	157.4	160.1	162.8	164.6	165.9	167.4	167.4	167.1
165°	153.8	155.6	157.6	159.1	160.2	161.3	161.0	161.0
167.5°	150.7	152.1	153.2	154.3	154.7	155.6	155.3	155.3
170°	148.6	149.5	150.7	151.2	151.6	152.1	151.8	151.8
172.5°	146.8	147.5	148.4	148.7	148.8	149.4	148.9	148.6
175°	144.3	144.6	145.2	145.2	145.2	145.5	145.2	145.0
177.5°	142.8	143.0	143.2	143.2	143.0	143.2	142.8	142.8
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4

(END OF REPORT)