

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831519

Luminaire Tested: S123DIP-S560D365U930-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831519  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D365U930-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3298.4 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 29.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831519

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P831519

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64				
1	102	97	94	90	95	92	88	86	81	79	76	71	69	68	62	61	60	55				
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51	48				
3	86	76	69	64	80	72	66	61	64	59	55	57	53	50	50	47	45	41				
4	79	68	60	55	74	65	58	52	58	52	48	51	47	44	45	42	39	36				
5	73	61	53	48	68	58	51	46	52	46	42	47	42	38	41	38	35	32				
6	67	56	48	42	63	53	46	40	47	42	37	43	38	34	38	34	31	29				
7	63	51	43	37	59	48	41	36	43	38	33	39	34	31	35	31	28	26				
8	58	46	39	34	55	44	37	32	40	34	30	36	31	28	32	29	26	24				
9	55	43	35	30	52	41	34	29	37	31	27	34	29	26	30	26	24	22				
10	51	40	32	28	49	38	31	27	34	29	25	31	27	23	28	24	22	20				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	14165	14165	14165	14165	14165
5°	17915	16908	14292	11517	10584
10°	18088	18636	14197	9181	8023
15°	13624	17302	14100	7775	6784
20°	9493	14001	13920	6800	6163
25°	7238	10766	13613	6255	5780
30°	6262	8554	13123	5872	5473
35°	5809	7222	12558	5593	5256
40°	5500	6479	11764	5328	5182
45°	5317	5996	10755	5122	5150
50°	5226	5615	9562	4933	5123
55°	5031	5335	8389	4755	5146
60°	4850	5035	7231	4588	5061
65°	4557	4753	6238	4409	4961
70°	4208	4390	5303	4113	4670
75°	3810	3938	4546	3822	4267
80°	3143	3446	3595	3329	3595
85°	2495	2791	2643	2828	2865

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 12280 cd/sqm



TEST NUMBER: P831519

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.4	3.8
10°-20°	309.5	9.4
20°-30°	366.5	11.1
30°-40°	368.5	11.2
40°-50°	338.1	10.2
50°-60°	279.0	8.5
60°-70°	197.4	6.0
70°-80°	105.4	3.2
80°-90°	27.5	0.8
90°-100°	13.7	0.4
100°-110°	66.1	2.0
110°-120°	162.0	4.9
120°-130°	205.7	6.2
130°-140°	219.7	6.7
140°-150°	205.5	6.2
150°-160°	165.7	5.0
160°-170°	106.9	3.2
170°-180°	36.9	1.1
0°-30°	800.4	24.3
0°-40°	1168.9	35.4
0°-60°	1786.0	54.1
0°-90°	2116.3	64.2
90°-120°	241.8	7.3
90°-150°	872.6	26.5
90°-180°	1182.0	35.8
0°-180°	3298.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1316	1316	1316	1316	1316	
5°	1658	1565	1323	1066	980	158
15°	1223	1553	1265	698	609	338
25°	609	906	1146	527	487	288
35°	442	550	956	426	400	278
45°	349	394	706	336	338	271
55°	268	284	447	253	274	240
65°	179	187	245	173	195	178
75°	92	95	109	92	103	96
85°	20	23	21	23	23	23
90°	9	7	0	7	9	5
95°	11	9	18	9	11	9
105°	13	63	86	63	13	26
115°	169	165	161	165	169	159
125°	232	230	227	230	232	207
135°	286	286	283	286	286	220
145°	329	329	326	329	329	206
155°	359	359	359	359	359	165
165°	378	378	379	378	378	107
175°	386	387	388	387	386	37
180°	388	388	388	388	388	



TEST NUMBER: P831519

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0
2.5°	1483.3	1481.8	1480.3	1472.6	1465.0	1461.3	1457.7	1446.7	1435.7	1423.5	1411.3
5°	1658.0	1662.2	1666.5	1661.6	1656.7	1641.8	1626.8	1607.0	1587.1	1564.8	1542.5
7.5°	1738.6	1741.0	1743.5	1740.4	1737.4	1733.4	1729.4	1711.7	1694.0	1671.1	1648.2
10°	1654.9	1660.4	1665.9	1677.8	1689.7	1703.2	1716.6	1714.1	1711.7	1705.0	1698.3
12.5°	1471.1	1477.8	1484.5	1508.4	1532.2	1562.7	1593.2	1619.5	1645.8	1664.1	1682.4
15°	1222.6	1241.2	1259.8	1281.5	1303.2	1348.0	1392.9	1448.2	1503.5	1552.6	1601.8
17.5°	1007.0	1014.0	1021.0	1044.2	1067.4	1123.9	1180.4	1244.2	1308.1	1389.6	1471.1
20°	828.7	835.1	841.5	872.0	902.6	946.8	991.1	1062.9	1134.6	1222.3	1309.9
22.5°	696.2	706.2	716.3	733.4	750.5	793.0	835.4	899.2	963.0	1059.8	1156.6
25°	609.4	616.8	624.1	634.5	644.9	678.8	712.6	765.2	817.7	906.5	995.4
27.5°	550.2	553.3	556.3	566.7	577.1	599.1	621.0	666.2	711.4	786.8	862.3
30°	503.8	505.9	508.1	517.2	526.4	541.4	556.3	589.0	621.7	688.2	754.8
32.5°	471.4	473.0	474.5	481.5	488.5	499.2	509.9	533.7	557.5	612.5	667.5
35°	442.1	443.0	444.0	449.1	454.3	462.3	470.2	488.2	506.2	549.6	593.0
37.5°	416.5	417.7	418.9	422.0	425.0	432.0	439.1	453.4	467.8	501.1	534.3
40°	391.4	393.6	395.7	397.9	400.0	405.8	411.6	422.6	433.6	461.1	488.5
42.5°	370.1	372.2	374.3	375.3	376.2	379.5	382.9	393.0	403.0	423.5	444.0
45°	349.3	350.2	351.1	352.1	353.0	355.7	358.5	367.3	376.2	393.9	411.6
47.5°	330.4	330.4	330.4	331.0	331.6	334.0	336.5	342.9	349.3	363.0	376.8
50°	312.1	312.1	312.1	311.1	310.2	311.7	313.3	318.2	323.0	335.3	347.5
52.5°	290.1	290.1	290.1	290.4	290.7	290.7	290.7	295.0	299.2	310.2	321.2
55°	268.1	269.3	270.5	269.6	268.7	269.3	269.9	272.7	275.4	284.3	293.1
57.5°	246.1	246.7	247.3	247.0	246.7	247.0	247.3	249.8	252.2	258.9	265.6
60°	225.3	225.3	225.3	224.7	224.1	224.7	225.3	226.6	227.8	233.9	240.0
62.5°	202.1	202.4	202.7	203.0	203.4	202.7	202.1	203.7	205.2	209.8	214.3
65°	178.9	179.2	179.5	180.5	181.4	180.8	180.1	181.7	183.2	186.6	189.9
67.5°	158.2	157.6	156.9	157.2	157.6	158.5	159.4	159.7	160.0	163.7	167.3
70°	133.7	134.3	135.0	134.7	134.3	134.7	135.0	135.9	136.8	139.5	142.3
72.5°	111.8	112.1	112.4	112.4	112.4	113.0	113.6	114.5	115.4	116.9	118.5
75°	91.6	91.6	91.6	92.2	92.8	93.1	93.4	93.4	93.4	94.7	95.9
77.5°	69.6	71.1	72.7	72.4	72.1	72.7	73.3	74.2	75.1	75.7	76.3
80°	50.7	50.7	50.7	51.0	51.3	52.2	53.1	53.7	54.3	55.6	56.8
82.5°	32.4	32.7	33.0	33.9	34.8	35.4	36.0	36.9	37.9	37.9	37.9
85°	20.2	19.5	18.9	19.5	20.2	20.8	21.4	21.7	22.0	22.6	23.2
87.5°	9.8	9.8	9.8	9.8	9.8	10.1	10.4	10.4	10.4	10.4	10.4
90°	8.6	8.5	8.4	8.3	8.1	7.9	7.7	7.4	7.2	6.9	6.1
92.5°	9.8	9.7	9.7	9.6	9.5	9.3	8.8	8.4	7.9	7.5	6.9
95°	10.9	10.9	10.9	10.9	10.9	10.7	10.3	9.8	9.4	8.9	8.2
97.5°	11.8	11.7	11.7	11.6	11.6	11.3	10.8	10.2	9.7	9.2	12.5
100°	12.1	12.0	12.0	11.9	11.8	11.6	11.0	10.5	10.0	9.5	19.5
102.5°	12.4	12.3	12.1	12.0	11.9	12.9	15.0	17.1	19.2	21.3	32.5
105°	12.7	12.5	12.4	12.3	12.2	17.8	29.1	40.4	51.8	63.1	68.9
107.5°	30.0	38.3	46.7	55.1	63.5	72.6	82.5	92.4	102.2	112.1	111.1
110°	79.2	88.4	97.5	106.7	115.8	121.5	123.6	125.7	127.8	129.9	129.2



TEST NUMBER: P831519

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	150.1	150.2	150.4	150.5	150.6	150.4	149.8	149.2	148.7	148.1	147.4
115°	169.4	169.1	168.9	168.6	168.4	167.9	167.3	166.7	166.0	165.4	164.8
117.5°	185.0	184.9	184.8	184.8	184.7	184.4	183.9	183.4	182.9	182.4	182.0
120°	201.1	201.1	201.1	201.1	201.1	200.8	200.3	199.8	199.3	198.8	198.6
122.5°	216.9	216.9	216.8	216.7	216.7	216.5	216.2	215.9	215.5	215.2	215.0
125°	231.6	231.5	231.4	231.2	231.1	231.0	230.9	230.7	230.6	230.5	230.2
127.5°	246.0	246.2	246.3	246.4	246.6	246.5	246.3	246.1	245.9	245.8	245.4
130°	259.9	260.0	260.1	260.3	260.4	260.3	260.1	259.8	259.5	259.3	259.0
132.5°	272.5	272.7	272.9	273.1	273.3	273.3	273.0	272.8	272.5	272.3	272.1
135°	285.5	285.7	285.9	286.1	286.3	286.3	286.1	285.9	285.7	285.5	285.3
137.5°	297.9	298.0	298.2	298.3	298.4	298.3	298.0	297.7	297.4	297.0	296.9
140°	308.8	309.0	309.1	309.2	309.4	309.3	309.0	308.8	308.5	308.3	308.1
142.5°	318.9	319.1	319.3	319.5	319.7	319.7	319.5	319.3	319.1	318.9	318.7
145°	329.3	329.3	329.3	329.3	329.3	329.2	329.1	329.0	328.9	328.7	328.6
147.5°	336.8	337.1	337.4	337.8	338.1	338.2	338.0	337.9	337.8	337.7	337.5
150°	345.4	345.6	345.8	346.0	346.2	346.2	346.1	346.0	345.8	345.7	345.6
152.5°	352.3	352.7	353.0	353.3	353.6	353.7	353.4	353.1	352.9	352.6	352.6
155°	358.7	359.1	359.5	359.8	360.2	360.3	359.9	359.6	359.3	359.0	358.9
157.5°	364.2	364.7	365.2	365.7	366.2	366.3	365.9	365.5	365.1	364.7	364.8
160°	369.3	369.8	370.2	370.7	371.1	371.2	370.8	370.4	370.0	369.6	369.7
162.5°	374.2	374.6	375.0	375.4	375.8	375.7	375.3	374.9	374.4	374.0	374.0
165°	378.0	378.4	378.9	379.3	379.8	379.7	379.2	378.7	378.2	377.7	377.8
167.5°	380.9	381.4	381.9	382.4	382.9	382.9	382.4	381.9	381.4	380.9	380.9
170°	383.5	384.0	384.5	385.0	385.5	385.5	385.0	384.5	384.0	383.5	383.5
172.5°	384.9	385.5	386.1	386.6	387.2	387.2	386.7	386.2	385.7	385.2	385.1
175°	386.3	386.9	387.4	387.9	388.4	388.4	388.0	387.5	387.1	386.6	386.6
177.5°	386.6	387.3	387.9	388.6	389.2	389.3	388.7	388.2	387.7	387.2	387.1
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P831519

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0
2.5°	1407.6	1403.9	1390.5	1377.1	1361.8	1346.5	1335.2	1323.9	1307.1	1290.3	1276.6
5°	1525.4	1508.4	1480.0	1451.6	1413.1	1374.6	1348.7	1322.7	1287.9	1253.1	1225.3
7.5°	1618.9	1589.6	1549.9	1510.2	1459.8	1409.4	1361.8	1314.2	1261.0	1207.9	1164.5
10°	1678.4	1658.6	1612.8	1567.0	1499.5	1432.0	1365.5	1298.9	1230.5	1162.1	1104.7
12.5°	1684.2	1686.1	1643.9	1601.8	1525.4	1449.1	1368.2	1287.3	1201.2	1115.1	1048.2
15°	1633.2	1664.7	1641.5	1618.3	1541.3	1464.4	1364.8	1265.3	1166.1	1066.8	989.6
17.5°	1538.6	1606.1	1609.4	1612.8	1535.8	1458.9	1348.7	1238.4	1126.1	1013.7	932.5
20°	1409.4	1509.0	1543.2	1577.4	1514.8	1452.2	1333.7	1215.2	1089.4	963.6	878.4
22.5°	1277.5	1398.4	1461.0	1523.6	1477.2	1430.8	1304.7	1178.6	1045.8	912.9	826.5
25°	1127.3	1259.2	1355.4	1451.6	1423.2	1394.8	1270.5	1146.2	1004.9	863.5	775.2
27.5°	996.3	1130.3	1246.4	1362.4	1356.3	1350.2	1226.8	1103.5	958.7	814.0	728.8
30°	879.7	1004.5	1134.3	1264.1	1279.0	1294.0	1174.9	1055.8	910.8	765.8	683.6
32.5°	776.5	885.5	1024.7	1163.9	1193.2	1222.6	1115.1	1007.6	864.1	720.6	641.5
35°	691.9	790.8	930.0	1069.3	1105.9	1142.6	1049.1	955.7	815.9	676.0	600.6
37.5°	617.1	699.8	835.7	971.6	1016.5	1061.3	977.7	894.0	763.0	632.0	562.7
40°	555.1	621.7	746.5	871.4	923.3	975.2	906.2	837.2	713.0	588.7	524.9
42.5°	503.2	562.4	675.7	789.0	838.8	888.5	830.2	771.9	661.4	550.8	492.5
45°	458.9	506.2	609.1	712.0	759.4	806.7	756.6	706.5	609.1	511.7	457.4
47.5°	417.4	458.0	545.9	633.9	676.0	718.1	679.1	640.0	557.5	475.1	425.9
50°	380.1	412.8	489.8	566.7	603.3	640.0	605.5	571.0	503.2	435.4	392.7
52.5°	347.8	374.3	438.8	503.2	534.6	566.1	536.5	506.9	453.1	399.4	362.1
55°	315.7	338.3	394.2	450.1	471.4	492.8	469.9	447.0	403.7	360.3	328.8
57.5°	285.8	305.9	351.7	397.5	414.0	430.5	409.8	389.0	356.3	323.7	297.4
60°	256.5	273.0	311.1	349.3	359.4	369.5	352.7	335.9	313.0	290.1	266.6
62.5°	229.3	244.3	272.7	301.1	307.8	314.5	301.7	288.8	271.4	254.0	235.7
65°	201.2	212.5	235.7	258.9	263.2	267.5	256.2	244.9	231.7	218.6	205.2
67.5°	175.3	183.2	202.1	221.1	221.4	221.7	212.5	203.4	196.0	188.7	178.0
70°	149.9	157.6	170.1	182.6	182.9	183.2	175.9	168.5	163.0	157.6	149.6
72.5°	124.0	129.5	138.9	148.4	147.8	147.2	142.6	138.0	133.7	129.5	123.7
75°	100.5	105.0	111.4	117.9	116.0	114.2	111.8	109.3	105.6	102.0	98.3
77.5°	79.1	81.8	85.5	89.2	87.9	86.7	84.6	82.4	79.7	76.9	75.4
80°	58.0	59.2	61.7	64.1	63.5	62.9	60.5	58.0	57.4	56.8	54.7
82.5°	39.4	40.9	41.5	42.1	41.8	41.5	39.7	37.9	37.3	36.6	36.3
85°	23.5	23.8	24.1	24.4	23.5	22.6	22.0	21.4	21.4	21.4	21.1
87.5°	10.7	11.0	11.0	11.0	10.7	10.4	9.8	9.2	9.5	9.8	9.8
90°	5.2	4.4	3.6	2.8	2.2	1.6	0.9	0.3	0.9	1.6	2.2
92.5°	6.3	5.8	5.2	5.1	5.5	5.9	6.2	6.6	6.2	5.9	5.5
95°	7.5	6.8	6.1	7.1	9.7	12.3	14.9	17.6	14.9	12.3	9.7
97.5°	15.7	19.0	22.3	24.8	26.6	28.4	30.2	32.0	30.2	28.4	26.6
100°	29.5	39.5	49.5	53.8	52.5	51.3	50.0	48.7	50.0	51.3	52.5
102.5°	43.6	54.7	65.9	71.0	70.2	69.4	68.5	67.7	68.5	69.4	70.2
105°	74.6	80.4	86.1	88.7	88.0	87.3	86.6	85.9	86.6	87.3	88.0
107.5°	110.2	109.2	108.2	107.5	106.9	106.3	105.7	105.2	105.7	106.3	106.9
110°	128.5	127.8	127.1	126.5	126.0	125.5	125.0	124.5	125.0	125.5	126.0





TEST NUMBER: P831519

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	146.7	146.0	145.3	144.7	144.2	143.8	143.3	142.9	143.3	143.8	144.2
115°	164.2	163.6	163.1	162.6	162.2	161.8	161.4	161.0	161.4	161.8	162.2
117.5°	181.7	181.4	181.1	180.7	180.3	179.8	179.4	178.9	179.4	179.8	180.3
120°	198.4	198.2	198.0	197.6	197.1	196.5	195.9	195.3	195.9	196.5	197.1
122.5°	214.7	214.4	214.2	213.8	213.4	212.9	212.5	212.0	212.5	212.9	213.4
125°	230.0	229.7	229.5	229.1	228.6	228.0	227.5	227.0	227.5	228.0	228.6
127.5°	245.1	244.8	244.5	244.1	243.5	243.0	242.5	242.0	242.5	243.0	243.5
130°	258.8	258.5	258.3	257.9	257.4	256.9	256.3	255.8	256.3	256.9	257.4
132.5°	271.9	271.7	271.5	271.1	270.6	270.1	269.6	269.1	269.6	270.1	270.6
135°	285.0	284.7	284.5	284.2	283.8	283.4	283.0	282.6	283.0	283.4	283.8
137.5°	296.8	296.6	296.5	296.2	295.7	295.2	294.7	294.2	294.7	295.2	295.7
140°	307.9	307.7	307.5	307.2	306.8	306.4	306.1	305.7	306.1	306.4	306.8
142.5°	318.5	318.4	318.2	317.9	317.5	317.1	316.7	316.3	316.7	317.1	317.5
145°	328.5	328.3	328.2	327.9	327.5	327.0	326.6	326.1	326.6	327.0	327.5
147.5°	337.4	337.3	337.1	336.9	336.6	336.3	336.0	335.6	336.0	336.3	336.6
150°	345.5	345.3	345.2	345.0	344.9	344.7	344.5	344.3	344.5	344.7	344.9
152.5°	352.5	352.4	352.4	352.3	352.3	352.2	352.1	352.1	352.1	352.2	352.3
155°	358.8	358.8	358.7	358.8	358.9	359.0	359.1	359.3	359.1	359.0	358.9
157.5°	364.9	364.9	365.0	365.0	365.0	365.0	365.0	365.0	365.0	365.0	365.0
160°	369.8	369.8	369.9	370.0	370.0	370.1	370.1	370.2	370.1	370.1	370.0
162.5°	374.1	374.1	374.2	374.3	374.5	374.7	374.9	375.1	374.9	374.7	374.5
165°	377.8	377.9	378.0	378.1	378.3	378.5	378.7	378.9	378.7	378.5	378.3
167.5°	380.9	380.9	380.9	381.0	381.3	381.5	381.8	382.0	381.8	381.5	381.3
170°	383.5	383.5	383.5	383.6	383.8	384.1	384.4	384.6	384.4	384.1	383.8
172.5°	385.1	385.0	384.9	385.1	385.4	385.7	386.0	386.3	386.0	385.7	385.4
175°	386.5	386.4	386.4	386.5	386.8	387.1	387.5	387.8	387.5	387.1	386.8
177.5°	387.1	387.0	387.0	387.1	387.4	387.7	388.0	388.4	388.0	387.7	387.4
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P831519

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0	1316.0
2.5°	1262.9	1251.0	1239.0	1229.9	1220.7	1205.2	1189.6	1185.9	1182.3	1177.1	1171.9
5°	1197.5	1168.2	1138.9	1112.6	1086.4	1065.9	1045.5	1032.0	1018.6	1008.8	999.1
7.5°	1121.2	1077.2	1033.3	1002.1	971.0	941.3	911.7	902.3	892.8	880.0	867.1
10°	1047.3	998.7	950.2	909.6	869.0	840.0	811.0	799.4	787.8	771.6	755.4
12.5°	981.3	928.2	875.1	834.2	793.3	765.2	737.1	720.3	703.5	694.3	685.2
15°	912.3	855.5	798.8	760.9	723.0	697.7	672.3	657.7	643.0	634.2	625.3
17.5°	851.3	795.1	738.9	702.6	666.2	643.0	619.8	607.0	594.2	587.5	580.7
20°	793.3	738.3	683.3	647.9	612.5	593.6	574.6	566.4	558.2	552.7	547.2
22.5°	740.1	686.1	632.0	601.8	571.6	556.3	541.1	535.3	529.4	524.9	520.3
25°	687.0	638.8	590.5	564.9	539.2	526.7	514.2	508.4	502.6	498.0	493.4
27.5°	643.6	597.5	551.4	529.4	507.5	497.7	487.9	483.3	478.8	474.5	470.2
30°	601.5	560.3	519.1	500.1	481.2	472.4	463.5	458.9	454.3	450.4	446.4
32.5°	562.4	527.0	491.6	474.2	456.8	449.5	442.1	436.6	431.1	428.1	425.0
35°	525.2	493.4	461.7	447.3	433.0	425.6	418.3	413.7	409.1	406.7	404.3
37.5°	493.4	465.0	436.6	422.9	409.1	402.1	395.1	391.1	387.2	386.2	385.3
40°	461.1	436.6	412.2	398.8	385.3	379.2	373.1	370.7	368.2	367.6	367.0
42.5°	434.2	410.4	386.6	374.3	362.1	356.9	351.7	350.5	349.3	350.2	351.1
45°	403.0	383.2	363.3	352.1	340.8	336.5	332.2	331.3	330.4	332.2	334.0
47.5°	376.8	358.5	340.1	329.5	318.8	315.7	312.7	312.4	312.1	314.5	316.9
50°	349.9	332.2	314.5	305.9	297.4	294.6	291.9	292.8	293.7	297.7	301.7
52.5°	324.9	308.4	291.9	284.0	276.0	274.2	272.4	274.5	276.6	280.9	285.2
55°	297.4	282.4	267.5	261.4	255.3	253.4	251.6	255.9	260.1	264.1	268.1
57.5°	271.1	258.0	244.9	239.4	233.9	233.6	233.3	237.2	241.2	245.5	249.8
60°	243.0	232.1	221.1	216.8	212.5	213.1	213.7	218.3	222.9	226.3	229.6
62.5°	217.4	208.2	199.1	195.1	191.1	192.7	194.2	198.8	203.4	207.3	211.3
65°	191.7	184.1	176.5	173.7	171.0	173.1	175.3	179.2	183.2	185.9	188.7
67.5°	167.3	160.9	154.5	152.4	150.2	152.4	154.5	158.5	162.4	165.2	167.9
70°	141.7	136.5	131.3	129.8	128.2	130.7	133.1	136.5	139.8	142.6	145.3
72.5°	117.9	113.9	109.9	109.6	109.3	111.4	113.6	116.9	120.3	122.1	124.0
75°	94.7	92.5	90.4	90.1	89.8	91.9	94.0	95.9	97.7	99.2	100.8
77.5°	73.9	72.1	70.2	70.5	70.8	72.4	73.9	75.7	77.6	78.5	79.4
80°	52.5	51.9	51.3	51.9	52.5	53.7	55.0	56.2	57.4	58.0	58.6
82.5°	36.0	35.4	34.8	35.7	36.6	37.6	38.5	39.4	40.3	40.6	40.9
85°	20.8	21.7	22.6	22.6	22.6	22.9	23.2	23.5	23.8	23.5	23.2
87.5°	9.8	10.1	10.4	10.4	10.4	10.7	11.0	11.0	11.0	10.7	10.4
90°	2.8	3.6	4.4	5.2	6.1	6.9	7.2	7.4	7.7	7.9	8.1
92.5°	5.1	5.2	5.8	6.3	6.9	7.5	7.9	8.4	8.8	9.3	9.5
95°	7.1	6.1	6.8	7.5	8.2	8.9	9.4	9.8	10.3	10.7	10.9
97.5°	24.8	22.3	19.0	15.7	12.5	9.2	9.7	10.2	10.8	11.3	11.6
100°	53.8	49.5	39.5	29.5	19.5	9.5	10.0	10.5	11.0	11.6	11.8
102.5°	71.0	65.9	54.7	43.6	32.5	21.3	19.2	17.1	15.0	12.9	11.9
105°	88.7	86.1	80.4	74.6	68.9	63.1	51.8	40.4	29.1	17.8	12.2
107.5°	107.5	108.2	109.2	110.2	111.1	112.1	102.2	92.4	82.5	72.6	63.5
110°	126.5	127.1	127.8	128.5	129.2	129.9	127.8	125.7	123.6	121.5	115.8



TEST NUMBER: P831519

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	144.7	145.3	146.0	146.7	147.4	148.1	148.7	149.2	149.8	150.4	150.6
115°	162.6	163.1	163.6	164.2	164.8	165.4	166.0	166.7	167.3	167.9	168.4
117.5°	180.7	181.1	181.4	181.7	182.0	182.4	182.9	183.4	183.9	184.4	184.7
120°	197.6	198.0	198.2	198.4	198.6	198.8	199.3	199.8	200.3	200.8	201.1
122.5°	213.8	214.2	214.4	214.7	215.0	215.2	215.5	215.9	216.2	216.5	216.7
125°	229.1	229.5	229.7	230.0	230.2	230.5	230.6	230.7	230.9	231.0	231.1
127.5°	244.1	244.5	244.8	245.1	245.4	245.8	245.9	246.1	246.3	246.5	246.6
130°	257.9	258.3	258.5	258.8	259.0	259.3	259.5	259.8	260.1	260.3	260.4
132.5°	271.1	271.5	271.7	271.9	272.1	272.3	272.5	272.8	273.0	273.3	273.3
135°	284.2	284.5	284.7	285.0	285.3	285.5	285.7	285.9	286.1	286.3	286.3
137.5°	296.2	296.5	296.6	296.8	296.9	297.0	297.4	297.7	298.0	298.3	298.4
140°	307.2	307.5	307.7	307.9	308.1	308.3	308.5	308.8	309.0	309.3	309.4
142.5°	317.9	318.2	318.4	318.5	318.7	318.9	319.1	319.3	319.5	319.7	319.7
145°	327.9	328.2	328.3	328.5	328.6	328.7	328.9	329.0	329.1	329.2	329.3
147.5°	336.9	337.1	337.3	337.4	337.5	337.7	337.8	337.9	338.0	338.2	338.1
150°	345.0	345.2	345.3	345.5	345.6	345.7	345.8	346.0	346.1	346.2	346.2
152.5°	352.3	352.4	352.4	352.5	352.6	352.6	352.9	353.1	353.4	353.7	353.6
155°	358.8	358.7	358.8	358.8	358.9	359.0	359.3	359.6	359.9	360.3	360.2
157.5°	365.0	365.0	364.9	364.9	364.8	364.7	365.1	365.5	365.9	366.3	366.2
160°	370.0	369.9	369.8	369.8	369.7	369.6	370.0	370.4	370.8	371.2	371.1
162.5°	374.3	374.2	374.1	374.1	374.0	374.0	374.4	374.9	375.3	375.7	375.8
165°	378.1	378.0	377.9	377.8	377.8	377.7	378.2	378.7	379.2	379.7	379.8
167.5°	381.0	380.9	380.9	380.9	380.9	380.9	381.4	381.9	382.4	382.9	382.9
170°	383.6	383.5	383.5	383.5	383.5	383.5	384.0	384.5	385.0	385.5	385.5
172.5°	385.1	384.9	385.0	385.1	385.1	385.2	385.7	386.2	386.7	387.2	387.2
175°	386.5	386.4	386.4	386.5	386.6	386.6	387.1	387.5	388.0	388.4	388.4
177.5°	387.1	387.0	387.0	387.1	387.1	387.2	387.7	388.2	388.7	389.3	389.2
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P831519

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1316.0	1316.0	1316.0	1316.0
2.5°	1169.7	1167.6	1159.0	1150.5
5°	991.7	984.4	982.0	979.5
7.5°	866.5	865.9	853.1	840.3
10°	756.3	757.2	745.6	734.0
12.5°	677.5	669.9	669.0	668.1
15°	618.3	611.3	610.1	608.8
17.5°	576.5	572.2	571.0	569.8
20°	544.7	542.3	540.1	538.0
22.5°	517.2	514.2	512.4	510.5
25°	490.7	487.9	487.3	486.7
27.5°	466.9	463.5	463.5	463.5
30°	444.3	442.1	441.2	440.3
32.5°	423.2	421.4	421.4	421.4
35°	403.3	402.4	401.2	400.0
37.5°	385.3	385.3	384.7	384.1
40°	367.9	368.8	368.8	368.8
42.5°	352.1	353.0	353.0	353.0
45°	335.6	337.1	337.7	338.3
47.5°	319.4	321.8	322.4	323.0
50°	303.5	305.3	305.6	305.9
52.5°	287.3	289.5	291.0	292.5
55°	270.2	272.4	273.3	274.2
57.5°	251.9	254.0	254.3	254.6
60°	231.7	233.9	234.5	235.1
62.5°	212.5	213.7	214.3	215.0
65°	190.5	192.4	193.6	194.8
67.5°	169.5	171.0	171.0	171.0
70°	145.9	146.6	147.5	148.4
72.5°	124.3	124.6	124.6	124.6
75°	101.4	102.0	102.3	102.6
77.5°	79.7	80.0	80.0	80.0
80°	58.3	58.0	58.0	58.0
82.5°	40.0	39.1	39.1	39.1
85°	22.9	22.6	22.9	23.2
87.5°	10.4	10.4	10.4	10.4
90°	8.3	8.4	8.5	8.6
92.5°	9.6	9.7	9.7	9.8
95°	10.9	10.9	10.9	10.9
97.5°	11.6	11.7	11.7	11.8
100°	11.9	12.0	12.0	12.1
102.5°	12.0	12.1	12.3	12.4
105°	12.3	12.4	12.5	12.7
107.5°	55.1	46.7	38.3	30.0
110°	106.7	97.5	88.4	79.2



TEST NUMBER: P831519

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	150.5	150.4	150.2	150.1
115°	168.6	168.9	169.1	169.4
117.5°	184.8	184.8	184.9	185.0
120°	201.1	201.1	201.1	201.1
122.5°	216.7	216.8	216.9	216.9
125°	231.2	231.4	231.5	231.6
127.5°	246.4	246.3	246.2	246.0
130°	260.3	260.1	260.0	259.9
132.5°	273.1	272.9	272.7	272.5
135°	286.1	285.9	285.7	285.5
137.5°	298.3	298.2	298.0	297.9
140°	309.2	309.1	309.0	308.8
142.5°	319.5	319.3	319.1	318.9
145°	329.3	329.3	329.3	329.3
147.5°	337.8	337.4	337.1	336.8
150°	346.0	345.8	345.6	345.4
152.5°	353.3	353.0	352.7	352.3
155°	359.8	359.5	359.1	358.7
157.5°	365.7	365.2	364.7	364.2
160°	370.7	370.2	369.8	369.3
162.5°	375.4	375.0	374.6	374.2
165°	379.3	378.9	378.4	378.0
167.5°	382.4	381.9	381.4	380.9
170°	385.0	384.5	384.0	383.5
172.5°	386.6	386.1	385.5	384.9
175°	387.9	387.4	386.9	386.3
177.5°	388.6	387.9	387.3	386.6
180°	387.8	387.8	387.8	387.8



TEST NUMBER: P831519

CATALOG NUMBER: S123DIP-S560D365U930-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.01	14.96	14.84	15.81	16.87	16.24	17.20	17.08	18.05	19.11
	3H	15.66	16.52	16.51	17.38	18.46	17.68	18.53	18.52	19.39	20.48
	4H	16.24	17.05	17.11	17.92	19.01	18.13	18.94	18.99	19.80	20.90
	6H	16.62	17.36	17.49	18.24	19.34	18.41	19.15	19.29	20.03	21.14
	8H	16.72	17.43	17.60	18.32	19.42	18.48	19.18	19.36	20.07	21.18
	12H	16.77	17.44	17.66	18.32	19.46	18.50	19.17	19.39	20.06	21.19
4H	2H	14.59	15.40	15.46	16.27	17.36	16.42	17.23	17.29	18.09	19.19
	3H	16.43	17.10	17.31	18.00	19.11	18.05	18.72	18.92	19.62	20.73
	4H	17.13	17.74	18.02	18.64	19.78	18.63	19.24	19.52	20.14	21.28
	6H	17.61	18.14	18.52	19.06	20.20	19.04	19.57	19.95	20.49	21.63
	8H	17.75	18.24	18.66	19.16	20.31	19.16	19.65	20.06	20.56	21.71
	12H	17.82	18.27	18.75	19.20	20.36	19.21	19.65	20.13	20.58	21.74
8H	4H	17.41	17.90	18.31	18.81	19.96	18.75	19.24	19.65	20.15	21.30
	6H	18.00	18.40	18.93	19.36	20.51	19.25	19.66	20.19	20.61	21.77
	8H	18.21	18.57	19.15	19.51	20.68	19.43	19.79	20.38	20.74	21.91
	12H	18.33	18.65	19.28	19.59	20.81	19.54	19.85	20.48	20.79	22.01
12H	4H	17.41	17.85	18.34	18.79	19.94	18.73	19.17	19.65	20.10	21.26
	6H	18.05	18.41	18.99	19.36	20.53	19.27	19.63	20.21	20.57	21.74
	8H	18.29	18.60	19.23	19.54	20.76	19.47	19.79	20.42	20.73	21.95