

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331880-935

Luminaire Tested: **S123DIP-S340D585U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331880-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D585U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3231.6 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331880-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331880-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	39	39	38	32
2	86	79	73	68	78	72	67	62	59	55	52	46	44	41	35	33	32	26
3	79	69	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	21	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	21	41	31	24	20	25	21	17	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5022	5022	5022
5°	5046	4976	5010
10°	5012	4933	4964
15°	4953	4878	4886
20°	4885	4798	4802
25°	4793	4703	4694
30°	4692	4598	4561
35°	4586	4486	4428
40°	4477	4363	4295
45°	4354	4250	4147
50°	4232	4113	3997
55°	4074	3969	3847
60°	3914	3800	3679
65°	3769	3617	3505
70°	3559	3408	3257
75°	3256	3136	3003
80°	2938	2814	2783
85°	2569	2482	2384



TEST NUMBER: P331880-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.4
10°-20°	124.1	3.8
20°-30°	183.3	5.7
30°-40°	214.1	6.6
40°-50°	215.3	6.7
50°-60°	189.1	5.9
60°-70°	140.9	4.4
70°-80°	80.3	2.5
80°-90°	24.9	0.8
90°-100°	24.0	0.7
100°-110°	114.5	3.5
110°-120°	275.1	8.5
120°-130°	350.3	10.8
130°-140°	374.3	11.6
140°-150°	350.0	10.8
150°-160°	282.3	8.7
160°-170°	182.2	5.6
170°-180°	62.8	1.9
0°-30°	351.4	10.9
0°-40°	565.5	17.5
0°-60°	969.9	30.0
0°-90°	1215.9	37.6
90°-120°	413.7	12.8
90°-150°	1488.3	46.1
90°-180°	2016.0	62.4
0°-180°	3231.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	467	467	467	467	467	
5°	467	465	460	464	464	44
15°	444	443	438	441	438	125
25°	404	401	396	396	395	186
35°	349	346	341	339	337	218
45°	286	284	279	275	272	221
55°	217	216	212	207	205	194
65°	148	146	142	139	138	146
75°	78	77	75	73	72	84
85°	21	20	20	19	19	23
90°	0	5	12	14	15	3
95°	30	11	15	18	19	37
105°	146	149	108	26	22	155
115°	274	278	282	287	289	271
125°	387	391	393	394	395	345
135°	482	485	487	488	487	371
145°	556	559	560	561	561	348
155°	612	612	612	614	611	282
165°	646	644	644	647	644	182
175°	661	659	659	662	658	63
180°	661	661	661	661	661	



TEST NUMBER: P331880-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	468.2	467.9	467.6	467.4	467.0	466.5	465.7	464.9	464.2	463.4	464.1
5°	467.0	466.5	466.1	465.6	465.2	464.5	463.5	462.5	461.5	460.5	461.4
7.5°	462.4	461.9	461.5	461.1	460.6	459.9	458.9	457.9	456.8	455.8	456.6
10°	458.6	458.1	457.6	457.2	456.8	456.0	454.8	453.7	452.5	451.3	452.1
12.5°	453.4	453.1	452.6	452.3	451.9	451.2	450.1	449.0	447.9	446.9	447.5
15°	444.5	444.2	443.8	443.4	443.1	442.3	441.2	440.0	438.9	437.7	438.4
17.5°	434.1	433.7	433.3	432.7	432.3	431.5	430.3	429.2	428.0	426.9	427.3
20°	426.5	425.9	425.4	424.8	424.3	423.4	422.3	421.1	420.0	418.9	419.2
22.5°	417.8	417.2	416.7	416.2	415.7	414.8	413.6	412.5	411.3	410.2	410.4
25°	403.6	403.0	402.5	402.0	401.5	400.6	399.4	398.3	397.1	396.0	396.1
27.5°	388.4	387.9	387.4	386.8	386.3	385.5	384.3	383.0	381.8	380.5	380.6
30°	377.5	377.0	376.6	376.2	375.7	374.9	373.7	372.4	371.2	369.9	369.9
32.5°	366.6	366.0	365.4	364.8	364.3	363.4	362.5	361.5	360.6	359.6	359.1
35°	349.0	348.5	347.9	347.4	346.9	346.0	344.9	343.7	342.6	341.4	340.9
37.5°	331.1	330.4	329.7	329.0	328.4	327.4	326.2	325.0	323.9	322.7	322.1
40°	318.6	318.0	317.5	316.9	316.4	315.5	314.3	313.0	311.8	310.5	309.8
42.5°	306.0	305.4	304.8	304.2	303.6	302.6	301.4	300.1	298.9	297.6	297.0
45°	286.0	285.7	285.3	285.0	284.6	283.9	282.7	281.5	280.3	279.2	278.2
47.5°	266.2	265.7	265.2	264.7	264.2	263.4	262.3	261.1	260.1	259.0	258.0
50°	252.7	252.3	251.8	251.4	251.0	250.1	249.0	247.9	246.7	245.6	244.5
52.5°	238.6	238.3	238.0	237.7	237.4	236.6	235.4	234.2	233.0	231.7	230.9
55°	217.1	217.0	216.9	216.8	216.7	216.0	214.9	213.7	212.6	211.5	210.4
57.5°	196.5	196.2	195.9	195.6	195.3	194.7	193.7	192.8	191.9	191.0	190.1
60°	181.8	181.7	181.6	181.5	181.4	180.8	179.7	178.7	177.6	176.5	175.7
62.5°	168.6	168.3	168.2	167.9	167.6	167.0	165.9	164.9	163.8	162.7	162.0
65°	148.0	147.6	147.1	146.7	146.3	145.6	144.7	143.8	142.9	142.0	141.3
67.5°	126.3	125.9	125.5	125.1	124.8	124.2	123.6	122.9	122.2	121.5	120.9
70°	113.1	112.6	112.1	111.5	111.0	110.5	109.9	109.3	108.8	108.3	107.7
72.5°	99.4	98.9	98.6	98.2	97.7	97.3	96.7	96.1	95.5	94.9	94.3
75°	78.3	77.8	77.5	77.1	76.8	76.5	76.2	75.9	75.7	75.4	75.0
77.5°	59.5	59.3	59.2	59.0	58.7	58.5	58.2	57.9	57.5	57.2	56.9
80°	47.4	47.1	46.8	46.6	46.2	46.1	45.9	45.7	45.5	45.4	45.2
82.5°	35.5	35.4	35.4	35.3	35.2	35.2	35.1	35.1	35.1	35.0	34.9
85°	20.8	20.7	20.5	20.3	20.1	20.1	20.1	20.1	20.1	20.1	19.9
87.5°	8.4	8.4	8.4	8.4	8.4	8.6	8.8	9.0	9.2	9.4	9.5
90°	0.5	1.5	2.7	3.8	4.8	6.1	7.5	9.0	10.3	11.8	12.2
92.5°	9.1	8.9	8.5	8.2	7.9	8.3	9.4	10.4	11.5	12.6	13.3
95°	30.0	25.5	21.0	16.5	12.1	10.4	11.6	12.8	14.0	15.2	16.0
97.5°	60.2	58.2	56.2	54.2	52.2	47.3	39.3	31.5	23.7	15.8	16.7
100°	83.0	85.2	87.4	89.5	91.7	84.3	67.2	50.3	33.2	16.2	17.0
102.5°	108.9	110.5	112.1	113.7	115.2	106.7	88.1	69.5	50.9	32.3	29.6
105°	146.4	147.6	148.8	149.9	151.1	146.8	137.0	127.2	117.4	107.5	88.3
107.5°	185.8	186.8	187.8	188.7	189.7	190.9	192.4	194.0	195.5	197.1	183.0
110°	212.2	213.0	213.9	214.7	215.6	216.7	217.8	219.0	220.2	221.4	217.8



TEST NUMBER: P331880-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	237.3	238.1	238.8	239.6	240.4	241.4	242.6	243.8	245.0	246.2	246.3
115°	274.5	275.2	275.8	276.5	277.2	277.9	279.0	279.9	280.9	281.9	283.0
117.5°	310.6	311.3	312.2	313.0	313.7	314.4	315.0	315.5	316.0	316.4	317.4
120°	332.9	333.9	334.9	335.9	336.9	337.5	337.9	338.2	338.5	338.8	339.8
122.5°	355.8	356.5	357.3	358.2	359.0	359.6	360.0	360.4	360.8	361.3	361.9
125°	386.9	387.9	388.7	389.6	390.5	391.2	391.6	392.0	392.4	392.9	393.0
127.5°	417.2	418.1	419.0	419.8	420.7	421.4	421.9	422.5	423.0	423.5	423.9
130°	436.1	437.0	437.8	438.7	439.5	440.2	440.7	441.1	441.5	442.0	442.4
132.5°	454.2	455.0	455.9	456.8	457.6	458.2	458.6	458.9	459.3	459.7	460.1
135°	481.7	482.4	483.0	483.7	484.4	484.9	485.3	485.8	486.2	486.6	487.0
137.5°	505.3	506.2	507.0	507.8	508.6	509.2	509.4	509.6	509.9	510.1	510.7
140°	521.0	521.7	522.4	523.0	523.7	524.2	524.4	524.8	525.1	525.5	525.9
142.5°	535.5	536.2	536.9	537.5	538.2	538.6	539.0	539.3	539.7	540.0	540.4
145°	555.9	556.6	557.4	558.2	559.0	559.5	559.6	559.9	560.1	560.3	560.5
147.5°	575.1	575.6	576.1	576.5	577.0	577.4	577.6	577.8	578.1	578.3	578.5
150°	586.9	587.2	587.5	587.8	588.1	588.4	588.7	588.8	589.1	589.3	589.5
152.5°	597.4	597.6	597.7	597.9	598.1	598.2	598.3	598.5	598.6	598.7	599.1
155°	612.3	612.2	611.9	611.7	611.5	611.5	611.6	611.7	611.7	611.9	612.4
157.5°	624.0	624.0	623.9	623.9	623.9	623.8	623.7	623.6	623.5	623.4	624.1
160°	631.0	630.9	630.9	630.7	630.6	630.5	630.3	630.3	630.2	630.1	630.7
162.5°	637.7	637.4	637.1	636.9	636.5	636.4	636.3	636.2	636.0	635.9	636.7
165°	645.8	645.4	645.1	644.8	644.5	644.2	644.1	644.0	643.9	643.8	644.7
167.5°	652.0	651.6	651.2	650.7	650.3	650.1	650.1	650.1	650.1	650.1	651.0
170°	655.6	655.1	654.7	654.3	653.8	653.6	653.6	653.6	653.6	653.6	654.5
172.5°	658.0	657.5	656.9	656.3	655.8	655.7	655.7	655.8	655.9	656.0	656.9
175°	661.0	660.5	659.9	659.4	658.8	658.6	658.7	658.8	658.9	659.0	659.8
177.5°	661.8	661.3	660.9	660.5	660.0	659.9	660.0	660.0	660.1	660.2	660.9
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0



TEST NUMBER: P331880-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	464.8	465.5	466.2	466.6	466.5	466.4	466.3	466.2
5°	462.4	463.2	464.2	464.5	464.3	464.2	463.9	463.7
7.5°	457.4	458.2	459.0	459.3	459.3	459.2	459.1	458.9
10°	453.0	453.7	454.5	454.9	454.7	454.5	454.3	454.2
12.5°	448.0	448.6	449.2	449.4	449.4	449.2	449.1	449.0
15°	439.1	439.8	440.6	440.7	440.1	439.5	439.0	438.5
17.5°	427.8	428.3	428.9	429.0	428.8	428.6	428.4	428.3
20°	419.6	419.9	420.3	420.3	420.0	419.7	419.5	419.2
22.5°	410.7	411.0	411.3	411.3	411.0	410.6	410.3	409.9
25°	396.1	396.2	396.3	396.2	396.0	395.7	395.5	395.2
27.5°	380.6	380.7	380.7	380.6	380.3	380.0	379.6	379.3
30°	369.9	369.9	369.9	369.5	368.9	368.3	367.7	367.0
32.5°	358.6	358.1	357.7	357.2	356.9	356.5	356.2	355.9
35°	340.4	339.8	339.2	338.8	338.4	337.9	337.4	337.0
37.5°	321.4	320.8	320.1	319.7	319.4	319.1	318.8	318.6
40°	309.1	308.4	307.6	307.1	306.8	306.4	306.1	305.7
42.5°	296.3	295.5	294.8	294.3	293.9	293.6	293.3	292.8
45°	277.1	276.0	274.9	274.2	273.7	273.3	272.9	272.4
47.5°	256.9	255.9	254.8	254.1	253.7	253.3	252.9	252.5
50°	243.6	242.5	241.6	240.8	240.3	239.8	239.3	238.7
52.5°	230.1	229.2	228.3	227.6	227.1	226.6	226.1	225.6
55°	209.5	208.4	207.5	206.8	206.4	205.9	205.4	205.0
57.5°	189.2	188.3	187.4	186.8	186.2	185.7	185.2	184.7
60°	175.0	174.1	173.3	172.7	172.2	171.8	171.3	170.9
62.5°	161.1	160.3	159.5	158.9	158.7	158.3	158.1	157.7
65°	140.6	139.9	139.1	138.7	138.4	138.1	137.8	137.6
67.5°	120.2	119.6	119.0	118.5	118.1	117.7	117.4	117.0
70°	107.1	106.4	105.8	105.3	104.9	104.4	103.9	103.5
72.5°	93.8	93.2	92.6	92.2	92.0	91.8	91.5	91.3
75°	74.6	74.0	73.6	73.3	73.0	72.8	72.5	72.2
77.5°	56.6	56.3	56.0	55.9	55.9	55.9	55.9	55.9
80°	45.1	45.0	44.9	44.9	44.9	44.9	44.9	44.9
82.5°	34.8	34.6	34.4	34.3	34.3	34.2	34.1	34.0
85°	19.7	19.5	19.4	19.3	19.3	19.3	19.3	19.3
87.5°	9.5	9.5	9.5	9.5	9.6	9.6	9.6	9.7
90°	12.7	13.1	13.5	13.9	14.1	14.3	14.6	14.7
92.5°	13.9	14.6	15.3	15.8	15.9	16.0	16.2	16.3
95°	16.8	17.5	18.3	18.7	18.7	18.7	18.7	18.7
97.5°	17.6	18.4	19.3	19.8	19.9	20.0	20.1	20.2
100°	17.9	18.9	19.7	20.1	20.3	20.4	20.5	20.7
102.5°	26.9	24.2	21.5	20.2	20.4	20.7	20.8	21.0
105°	68.9	49.6	30.3	20.8	20.9	21.2	21.4	21.6
107.5°	168.8	154.6	140.4	126.1	111.5	96.9	82.4	67.8
110°	214.3	210.7	207.1	197.4	181.8	166.3	150.7	135.0



TEST NUMBER: P331880-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	246.3	246.4	246.5	244.9	241.6	238.2	235.0	231.7
115°	284.0	285.2	286.3	287.0	287.4	287.9	288.3	288.8
117.5°	318.2	319.1	319.9	320.5	320.6	320.6	320.7	320.8
120°	340.6	341.5	342.3	342.8	342.8	342.8	342.8	342.8
122.5°	362.5	363.1	363.7	364.0	364.1	364.2	364.3	364.4
125°	393.3	393.5	393.7	394.0	394.2	394.4	394.6	394.9
127.5°	424.2	424.6	424.9	425.0	424.7	424.6	424.3	424.1
130°	442.8	443.2	443.7	443.8	443.6	443.4	443.2	443.0
132.5°	460.5	461.0	461.4	461.5	461.2	460.8	460.5	460.2
135°	487.3	487.7	487.9	487.9	487.7	487.3	487.0	486.6
137.5°	511.2	511.7	512.2	512.4	512.1	512.0	511.7	511.5
140°	526.3	526.8	527.2	527.3	527.1	526.8	526.7	526.4
142.5°	540.7	541.1	541.4	541.4	541.1	540.8	540.4	540.2
145°	560.8	560.9	561.2	561.3	561.3	561.3	561.3	561.3
147.5°	578.8	578.9	579.2	579.0	578.5	578.0	577.6	577.0
150°	589.7	590.0	590.1	590.1	589.8	589.4	589.1	588.8
152.5°	599.5	599.9	600.3	600.2	599.8	599.3	598.7	598.2
155°	612.9	613.5	614.1	614.0	613.4	612.7	612.1	611.4
157.5°	624.7	625.3	626.0	625.9	625.0	624.2	623.4	622.5
160°	631.4	632.0	632.7	632.6	631.9	631.1	630.3	629.6
162.5°	637.4	638.2	638.9	638.9	638.3	637.6	636.9	636.3
165°	645.6	646.4	647.3	647.4	646.6	645.8	645.1	644.3
167.5°	651.9	652.7	653.6	653.6	652.7	651.9	651.0	650.1
170°	655.4	656.3	657.1	657.1	656.3	655.4	654.5	653.6
172.5°	657.7	658.6	659.4	659.4	658.5	657.5	656.5	655.6
175°	660.6	661.3	662.1	662.0	661.2	660.3	659.4	658.5
177.5°	661.6	662.3	663.0	662.9	662.0	661.2	660.3	659.4
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0

(END OF REPORT)