

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331881-935

Luminaire Tested: **S123DIP-S340D585U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331881-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D585U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2948.1 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331881-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331881-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	91	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	79	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	27	48	37	30	26	31	26	22	25	21	19	20	17	15	13
9	49	37	29	24	45	34	27	23	29	23	20	23	19	17	19	16	14	11
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5022	5022	5022
5°	5046	4976	5010
10°	5012	4933	4964
15°	4953	4878	4886
20°	4885	4798	4802
25°	4793	4703	4694
30°	4692	4598	4561
35°	4586	4486	4428
40°	4477	4363	4295
45°	4354	4250	4147
50°	4232	4113	3997
55°	4074	3969	3847
60°	3914	3800	3679
65°	3769	3617	3505
70°	3559	3408	3257
75°	3256	3136	3003
80°	2938	2814	2783
85°	2569	2482	2384



TEST NUMBER: P331881-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.5
10°-20°	124.1	4.2
20°-30°	183.3	6.2
30°-40°	214.1	7.3
40°-50°	215.3	7.3
50°-60°	189.1	6.4
60°-70°	140.9	4.8
70°-80°	80.3	2.7
80°-90°	24.9	0.8
90°-100°	40.7	1.4
100°-110°	121.9	4.1
110°-120°	207.3	7.0
120°-130°	272.7	9.3
130°-140°	306.5	10.4
140°-150°	301.3	10.2
150°-160°	253.7	8.6
160°-170°	168.9	5.7
170°-180°	59.1	2.0
0°-30°	351.4	11.9
0°-40°	565.5	19.2
0°-60°	969.9	32.9
0°-90°	1215.9	41.2
90°-120°	370.0	12.5
90°-150°	1250.5	42.4
90°-180°	1732.0	58.8
0°-180°	2948.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	467	467	467	467	467	
5°	467	465	460	464	464	44
15°	444	443	438	441	438	125
25°	404	401	396	396	395	186
35°	349	346	341	339	337	218
45°	286	284	279	275	272	221
55°	217	216	212	207	205	194
65°	148	146	142	139	138	146
75°	78	77	75	73	72	84
85°	21	20	20	19	19	23
90°	0	5	12	14	15	3
95°	29	32	36	38	38	33
105°	110	112	116	116	117	118
115°	209	210	209	210	209	206
125°	306	307	306	304	302	272
135°	396	399	399	397	396	305
145°	481	482	483	483	481	300
155°	550	551	551	553	550	253
165°	600	598	598	601	598	169
175°	624	622	622	624	621	59
180°	625	625	625	625	625	



TEST NUMBER: P331881-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	468.2	467.9	467.6	467.4	467.0	466.5	465.7	464.9	464.2	463.4	464.1
5°	467.0	466.5	466.1	465.6	465.2	464.5	463.5	462.5	461.5	460.5	461.4
7.5°	462.4	461.9	461.5	461.1	460.6	459.9	458.9	457.9	456.8	455.8	456.6
10°	458.6	458.1	457.6	457.2	456.8	456.0	454.8	453.7	452.5	451.3	452.1
12.5°	453.4	453.1	452.6	452.3	451.9	451.2	450.1	449.0	447.9	446.9	447.5
15°	444.5	444.2	443.8	443.4	443.1	442.3	441.2	440.0	438.9	437.7	438.4
17.5°	434.1	433.7	433.3	432.7	432.3	431.5	430.3	429.2	428.0	426.9	427.3
20°	426.5	425.9	425.4	424.8	424.3	423.4	422.3	421.1	420.0	418.9	419.2
22.5°	417.8	417.2	416.7	416.2	415.7	414.8	413.6	412.5	411.3	410.2	410.4
25°	403.6	403.0	402.5	402.0	401.5	400.6	399.4	398.3	397.1	396.0	396.1
27.5°	388.4	387.9	387.4	386.8	386.3	385.5	384.3	383.0	381.8	380.5	380.6
30°	377.5	377.0	376.6	376.2	375.7	374.9	373.7	372.4	371.2	369.9	369.9
32.5°	366.6	366.0	365.4	364.8	364.3	363.4	362.5	361.5	360.6	359.6	359.1
35°	349.0	348.5	347.9	347.4	346.9	346.0	344.9	343.7	342.6	341.4	340.9
37.5°	331.1	330.4	329.7	329.0	328.4	327.4	326.2	325.0	323.9	322.7	322.1
40°	318.6	318.0	317.5	316.9	316.4	315.5	314.3	313.0	311.8	310.5	309.8
42.5°	306.0	305.4	304.8	304.2	303.6	302.6	301.4	300.1	298.9	297.6	297.0
45°	286.0	285.7	285.3	285.0	284.6	283.9	282.7	281.5	280.3	279.2	278.2
47.5°	266.2	265.7	265.2	264.7	264.2	263.4	262.3	261.1	260.1	259.0	258.0
50°	252.7	252.3	251.8	251.4	251.0	250.1	249.0	247.9	246.7	245.6	244.5
52.5°	238.6	238.3	238.0	237.7	237.4	236.6	235.4	234.2	233.0	231.7	230.9
55°	217.1	217.0	216.9	216.8	216.7	216.0	214.9	213.7	212.6	211.5	210.4
57.5°	196.5	196.2	195.9	195.6	195.3	194.7	193.7	192.8	191.9	191.0	190.1
60°	181.8	181.7	181.6	181.5	181.4	180.8	179.7	178.7	177.6	176.5	175.7
62.5°	168.6	168.3	168.2	167.9	167.6	167.0	165.9	164.9	163.8	162.7	162.0
65°	148.0	147.6	147.1	146.7	146.3	145.6	144.7	143.8	142.9	142.0	141.3
67.5°	126.3	125.9	125.5	125.1	124.8	124.2	123.6	122.9	122.2	121.5	120.9
70°	113.1	112.6	112.1	111.5	111.0	110.5	109.9	109.3	108.8	108.3	107.7
72.5°	99.4	98.9	98.6	98.2	97.7	97.3	96.7	96.1	95.5	94.9	94.3
75°	78.3	77.8	77.5	77.1	76.8	76.5	76.2	75.9	75.7	75.4	75.0
77.5°	59.5	59.3	59.2	59.0	58.7	58.5	58.2	57.9	57.5	57.2	56.9
80°	47.4	47.1	46.8	46.6	46.2	46.1	45.9	45.7	45.5	45.4	45.2
82.5°	35.5	35.4	35.4	35.3	35.2	35.2	35.1	35.1	35.1	35.0	34.9
85°	20.8	20.7	20.5	20.3	20.1	20.1	20.1	20.1	20.1	20.1	19.9
87.5°	8.4	8.4	8.4	8.4	8.4	8.6	8.8	9.0	9.2	9.4	9.5
90°	0.5	1.5	2.7	3.8	4.8	6.1	7.5	9.0	10.3	11.8	12.2
92.5°	11.9	12.7	13.3	14.1	14.9	15.7	16.4	17.2	18.1	18.9	19.2
95°	29.0	29.7	30.5	31.3	32.0	32.9	33.8	34.6	35.5	36.3	36.8
97.5°	51.5	52.0	52.6	53.2	53.7	54.3	54.9	55.6	56.2	56.9	57.3
100°	66.8	67.4	68.1	68.8	69.4	70.0	70.5	71.1	71.6	72.2	72.5
102.5°	84.5	84.9	85.2	85.7	86.0	86.6	87.3	88.1	88.8	89.5	89.8
105°	110.5	110.7	110.9	111.2	111.4	111.9	113.0	113.9	114.9	115.9	115.9
107.5°	140.8	140.9	141.0	141.1	141.3	141.5	141.9	142.3	142.8	143.1	143.4
110°	159.6	159.8	160.1	160.2	160.5	160.7	160.9	161.2	161.4	161.6	162.0



TEST NUMBER: P331881-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	179.3	179.3	179.5	179.6	179.8	179.9	179.9	179.9	180.0	180.0	180.6
115°	208.7	209.1	209.4	209.7	210.0	210.1	209.8	209.7	209.4	209.2	209.3
117.5°	238.4	238.6	238.8	239.0	239.3	239.2	238.9	238.7	238.4	238.1	238.1
120°	256.8	257.5	258.1	258.8	259.5	259.5	259.0	258.5	257.9	257.4	257.3
122.5°	276.1	276.6	277.1	277.5	278.0	278.1	277.8	277.6	277.2	277.0	276.7
125°	305.5	305.8	306.1	306.4	306.8	306.9	306.6	306.4	306.2	306.0	305.5
127.5°	332.6	333.3	334.0	334.7	335.4	335.6	335.4	335.1	334.8	334.7	334.1
130°	350.7	351.5	352.4	353.3	354.1	354.4	354.1	353.8	353.4	353.1	352.7
132.5°	368.7	369.6	370.5	371.3	372.2	372.6	372.3	372.0	371.8	371.6	371.0
135°	396.3	397.0	397.6	398.3	398.9	399.2	399.1	399.0	398.9	398.8	398.4
137.5°	421.9	422.4	422.9	423.5	424.0	424.5	424.7	425.0	425.3	425.6	425.2
140°	439.5	440.1	440.7	441.2	441.7	442.0	442.1	442.3	442.4	442.5	442.4
142.5°	455.6	456.2	456.8	457.3	457.8	458.2	458.4	458.6	458.8	459.0	458.9
145°	480.8	481.0	481.2	481.5	481.6	481.9	482.2	482.6	482.9	483.3	483.1
147.5°	502.8	503.2	503.6	503.9	504.4	504.7	505.1	505.3	505.7	505.9	505.9
150°	518.1	518.3	518.6	518.8	519.0	519.2	519.4	519.6	519.9	520.0	520.0
152.5°	530.7	531.0	531.3	531.6	531.9	532.1	532.3	532.4	532.5	532.6	532.8
155°	550.5	550.5	550.5	550.5	550.5	550.6	550.7	550.8	551.0	551.0	551.5
157.5°	567.4	567.3	567.1	567.1	566.9	566.9	567.0	567.1	567.1	567.2	567.7
160°	578.0	577.8	577.6	577.4	577.1	577.0	577.0	577.0	577.0	577.0	577.6
162.5°	587.5	587.1	586.9	586.5	586.3	586.2	586.3	586.3	586.4	586.5	587.0
165°	599.6	599.3	599.0	598.7	598.3	598.1	598.1	598.1	598.1	598.1	598.8
167.5°	609.3	608.9	608.5	608.0	607.6	607.4	607.5	607.6	607.7	607.8	608.5
170°	614.8	614.4	614.0	613.5	613.1	612.9	612.9	612.9	612.9	612.9	613.6
172.5°	619.1	618.7	618.3	617.9	617.4	617.3	617.3	617.3	617.3	617.3	617.9
175°	623.7	623.3	622.8	622.4	622.0	621.7	621.7	621.7	621.7	621.7	622.4
177.5°	625.6	625.3	624.9	624.5	624.1	624.0	624.0	624.0	624.0	624.0	624.5
180°	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2



TEST NUMBER: P331881-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	464.8	465.5	466.2	466.6	466.5	466.4	466.3	466.2
5°	462.4	463.2	464.2	464.5	464.3	464.2	463.9	463.7
7.5°	457.4	458.2	459.0	459.3	459.3	459.2	459.1	458.9
10°	453.0	453.7	454.5	454.9	454.7	454.5	454.3	454.2
12.5°	448.0	448.6	449.2	449.4	449.4	449.2	449.1	449.0
15°	439.1	439.8	440.6	440.7	440.1	439.5	439.0	438.5
17.5°	427.8	428.3	428.9	429.0	428.8	428.6	428.4	428.3
20°	419.6	419.9	420.3	420.3	420.0	419.7	419.5	419.2
22.5°	410.7	411.0	411.3	411.3	411.0	410.6	410.3	409.9
25°	396.1	396.2	396.3	396.2	396.0	395.7	395.5	395.2
27.5°	380.6	380.7	380.7	380.6	380.3	380.0	379.6	379.3
30°	369.9	369.9	369.9	369.5	368.9	368.3	367.7	367.0
32.5°	358.6	358.1	357.7	357.2	356.9	356.5	356.2	355.9
35°	340.4	339.8	339.2	338.8	338.4	337.9	337.4	337.0
37.5°	321.4	320.8	320.1	319.7	319.4	319.1	318.8	318.6
40°	309.1	308.4	307.6	307.1	306.8	306.4	306.1	305.7
42.5°	296.3	295.5	294.8	294.3	293.9	293.6	293.3	292.8
45°	277.1	276.0	274.9	274.2	273.7	273.3	272.9	272.4
47.5°	256.9	255.9	254.8	254.1	253.7	253.3	252.9	252.5
50°	243.6	242.5	241.6	240.8	240.3	239.8	239.3	238.7
52.5°	230.1	229.2	228.3	227.6	227.1	226.6	226.1	225.6
55°	209.5	208.4	207.5	206.8	206.4	205.9	205.4	205.0
57.5°	189.2	188.3	187.4	186.8	186.2	185.7	185.2	184.7
60°	175.0	174.1	173.3	172.7	172.2	171.8	171.3	170.9
62.5°	161.1	160.3	159.5	158.9	158.7	158.3	158.1	157.7
65°	140.6	139.9	139.1	138.7	138.4	138.1	137.8	137.6
67.5°	120.2	119.6	119.0	118.5	118.1	117.7	117.4	117.0
70°	107.1	106.4	105.8	105.3	104.9	104.4	103.9	103.5
72.5°	93.8	93.2	92.6	92.2	92.0	91.8	91.5	91.3
75°	74.6	74.0	73.6	73.3	73.0	72.8	72.5	72.2
77.5°	56.6	56.3	56.0	55.9	55.9	55.9	55.9	55.9
80°	45.1	45.0	44.9	44.9	44.9	44.9	44.9	44.9
82.5°	34.8	34.6	34.4	34.3	34.3	34.2	34.1	34.0
85°	19.7	19.5	19.4	19.3	19.3	19.3	19.3	19.3
87.5°	9.5	9.5	9.5	9.5	9.6	9.6	9.6	9.7
90°	12.7	13.1	13.5	13.9	14.1	14.3	14.6	14.7
92.5°	19.5	19.9	20.2	20.4	20.2	20.1	20.0	19.8
95°	37.2	37.6	38.1	38.3	38.3	38.3	38.3	38.3
97.5°	57.9	58.4	58.9	59.1	59.1	59.0	59.0	58.9
100°	72.8	73.2	73.5	73.8	74.0	74.2	74.4	74.6
102.5°	90.1	90.5	90.7	90.9	90.9	90.8	90.8	90.7
105°	115.9	115.9	115.9	116.0	116.2	116.4	116.7	116.9
107.5°	143.8	144.1	144.5	144.6	144.5	144.4	144.2	144.1
110°	162.5	162.9	163.3	163.4	163.2	163.0	162.8	162.6



TEST NUMBER: P331881-935

CATALOG NUMBER: S123DIP-S340D585U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	181.1	181.6	182.1	182.4	182.4	182.3	182.3	182.2
115°	209.4	209.6	209.7	209.7	209.6	209.4	209.3	209.2
117.5°	238.1	238.0	238.0	237.8	237.5	237.2	236.9	236.6
120°	257.1	257.0	256.9	256.8	256.5	256.3	256.1	255.9
122.5°	276.4	276.1	275.9	275.5	275.3	274.9	274.7	274.3
125°	305.1	304.6	304.2	303.8	303.3	302.9	302.5	302.0
127.5°	333.4	332.8	332.2	331.7	331.1	330.6	330.1	329.6
130°	352.2	351.8	351.4	350.8	350.0	349.2	348.4	347.7
132.5°	370.5	370.0	369.5	368.9	368.3	367.7	367.1	366.5
135°	397.9	397.4	397.0	396.7	396.5	396.2	396.1	395.8
137.5°	424.6	424.2	423.8	423.4	422.9	422.5	422.1	421.6
140°	442.3	442.1	442.0	441.6	440.8	440.1	439.3	438.6
142.5°	458.7	458.7	458.6	458.2	457.6	457.0	456.4	455.8
145°	483.0	482.9	482.8	482.5	482.1	481.6	481.2	480.8
147.5°	505.9	505.9	505.9	505.6	505.0	504.3	503.7	503.0
150°	520.0	520.0	520.0	519.8	519.1	518.4	517.8	517.1
152.5°	533.0	533.2	533.4	533.1	532.6	532.0	531.5	530.9
155°	551.9	552.3	552.8	552.6	551.8	551.0	550.4	549.6
157.5°	568.2	568.6	569.0	568.9	568.3	567.7	567.1	566.5
160°	578.2	578.7	579.2	579.3	578.9	578.4	578.0	577.6
162.5°	587.5	588.1	588.7	588.6	587.9	587.2	586.5	585.8
165°	599.5	600.1	600.8	600.7	599.9	599.2	598.5	597.7
167.5°	609.2	609.8	610.5	610.5	609.8	609.2	608.5	607.8
170°	614.4	615.2	616.0	616.0	615.2	614.4	613.6	612.9
172.5°	618.5	619.2	619.9	619.9	619.1	618.4	617.6	616.8
175°	623.0	623.7	624.4	624.3	623.5	622.8	622.0	621.2
177.5°	625.1	625.6	626.1	626.0	625.4	624.8	624.2	623.6
180°	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2

(END OF REPORT)