

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331936-930

Luminaire Tested: **S123DIP-S560D805U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331936-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D805U930-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4261.5 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331936-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331936-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80		65	65	65		51	51	51	44
1	96	92	88	85	88	85	81	78	70	68	66		57	55	54		45	44	43	37
2	88	80	74	69	80	74	69	64	61	58	54		50	47	45		40	38	36	31
3	80	71	63	58	73	65	59	54	54	49	46		44	41	38		35	33	31	26
4	73	62	55	49	67	57	51	45	48	43	39		39	36	33		31	29	26	23
5	67	56	48	42	61	51	44	39	43	38	33		35	31	28		28	25	23	20
6	62	50	42	36	56	46	39	34	39	33	29		32	28	25		26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26		29	25	22		23	20	18	15
8	53	41	33	28	48	38	31	26	32	27	23		26	22	19		21	18	16	14
9	49	37	30	25	45	34	28	23	29	24	20		24	20	17		20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18		22	19	16		18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7854	7747	7800
10°	7803	7679	7726
15°	7710	7592	7608
20°	7605	7468	7475
25°	7462	7321	7305
30°	7305	7157	7102
35°	7139	6984	6893
40°	6968	6792	6687
45°	6779	6616	6454
50°	6589	6400	6223
55°	6341	6176	5988
60°	6090	5916	5726
65°	5871	5631	5456
70°	5542	5306	5070
75°	5065	4882	4675
80°	4568	4376	4339
85°	4001	3853	3705



TEST NUMBER: P331936-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	1.6
10°-20°	193.2	4.5
20°-30°	285.4	6.7
30°-40°	333.3	7.8
40°-50°	335.1	7.9
50°-60°	294.4	6.9
60°-70°	219.3	5.1
70°-80°	124.9	2.9
80°-90°	38.3	0.9
90°-100°	175.2	4.1
100°-110°	496.2	11.6
110°-120°	488.1	11.5
120°-130°	389.3	9.1
130°-140°	307.0	7.2
140°-150°	229.1	5.4
150°-160°	159.7	3.7
160°-170°	93.8	2.2
170°-180°	30.5	0.7
0°-30°	547.0	12.8
0°-40°	880.3	20.7
0°-60°	1509.9	35.4
0°-90°	1892.4	44.4
90°-120°	1159.6	27.2
90°-150°	2085.0	48.9
90°-180°	2369.0	55.6
0°-180°	4261.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	727	724	717	723	722	69
15°	692	689	681	686	683	195
25°	628	624	616	617	615	289
35°	543	539	532	528	525	340
45°	445	442	435	427	424	344
55°	338	337	329	322	319	303
65°	230	227	221	216	214	227
75°	122	119	117	114	112	130
85°	32	31	31	30	30	36
90°	1	8	16	18	18	3
95°	22	70	378	110	74	23
105°	74	109	512	896	811	79
115°	131	163	392	860	986	129
125°	182	214	366	663	778	161
135°	213	254	361	546	630	164
145°	243	278	356	448	493	152
155°	276	298	345	392	408	127
165°	302	310	330	350	356	85
175°	314	315	317	321	321	30
180°	315	315	315	315	315	



TEST NUMBER: P331936-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	728.8	728.4	728.0	727.5	727.1	726.2	725.0	723.7	722.6	721.4	722.4
5°	726.9	726.3	725.5	724.9	724.1	723.1	721.5	720.0	718.5	717.0	718.4
7.5°	719.8	719.2	718.4	717.8	717.1	715.9	714.4	712.7	711.2	709.6	710.9
10°	713.9	713.1	712.5	711.8	711.1	709.8	708.0	706.2	704.4	702.6	703.8
12.5°	705.9	705.2	704.7	704.1	703.5	702.4	700.7	699.0	697.3	695.6	696.5
15°	691.9	691.5	690.9	690.3	689.7	688.6	686.8	685.0	683.1	681.3	682.5
17.5°	675.9	675.1	674.4	673.7	672.9	671.7	669.9	668.1	666.3	664.5	665.3
20°	663.9	663.1	662.2	661.4	660.6	659.3	657.5	655.7	653.8	652.0	652.6
22.5°	650.4	649.5	648.7	647.9	647.0	645.7	643.9	642.1	640.3	638.5	639.0
25°	628.3	627.5	626.6	625.8	624.9	623.6	621.8	620.0	618.2	616.4	616.5
27.5°	604.7	603.9	603.1	602.3	601.4	600.1	598.1	596.2	594.3	592.3	592.4
30°	587.7	587.0	586.3	585.6	584.9	583.6	581.6	579.7	577.8	575.8	575.8
32.5°	570.7	569.8	568.8	567.9	567.0	565.8	564.4	562.8	561.3	559.9	559.1
35°	543.3	542.5	541.7	540.9	540.1	538.7	536.9	535.1	533.3	531.5	530.7
37.5°	515.4	514.3	513.2	512.2	511.1	509.7	507.8	506.1	504.2	502.4	501.4
40°	495.9	495.0	494.2	493.4	492.5	491.1	489.2	487.3	485.3	483.4	482.2
42.5°	476.4	475.5	474.5	473.5	472.6	471.2	469.2	467.3	465.4	463.4	462.3
45°	445.3	444.7	444.2	443.6	443.0	441.9	440.1	438.3	436.5	434.6	433.0
47.5°	414.4	413.6	412.9	412.1	411.2	409.9	408.3	406.6	404.9	403.2	401.5
50°	393.5	392.7	392.1	391.3	390.7	389.5	387.6	385.8	384.0	382.2	380.7
52.5°	371.5	371.0	370.6	370.1	369.6	368.4	366.5	364.6	362.6	360.8	359.5
55°	337.9	337.7	337.6	337.5	337.3	336.3	334.5	332.7	330.9	329.1	327.6
57.5°	305.9	305.4	304.9	304.5	304.0	303.0	301.6	300.2	298.7	297.3	296.0
60°	282.9	282.7	282.7	282.5	282.3	281.4	279.8	278.1	276.5	274.8	273.5
62.5°	262.4	262.0	261.7	261.4	261.0	260.0	258.3	256.7	254.9	253.3	252.1
65°	230.5	229.8	229.1	228.4	227.7	226.7	225.3	223.9	222.5	221.1	220.0
67.5°	196.6	196.0	195.3	194.8	194.1	193.3	192.2	191.2	190.1	189.1	188.2
70°	176.1	175.3	174.5	173.7	172.8	171.9	171.1	170.3	169.4	168.6	167.6
72.5°	154.7	154.0	153.4	152.8	152.2	151.4	150.5	149.5	148.5	147.7	146.8
75°	121.8	121.2	120.7	120.1	119.6	119.1	118.6	118.2	117.8	117.4	116.8
77.5°	92.7	92.4	92.0	91.8	91.5	91.1	90.6	90.1	89.5	89.0	88.6
80°	73.7	73.3	72.9	72.5	72.0	71.7	71.4	71.1	70.8	70.6	70.4
82.5°	55.2	55.1	55.0	55.0	54.9	54.8	54.8	54.7	54.6	54.6	54.3
85°	32.4	32.2	32.0	31.6	31.4	31.2	31.2	31.2	31.2	31.2	31.0
87.5°	13.2	13.2	13.1	13.1	13.0	13.1	13.4	13.6	13.9	14.2	13.9
90°	1.3	2.5	3.8	5.7	7.0	8.3	10.2	12.1	14.0	15.9	15.3
92.5°	7.9	11.7	17.1	22.1	27.4	36.9	53.6	81.0	107.9	98.0	73.9
95°	21.7	23.6	30.6	41.4	58.0	82.8	137.1	232.0	336.6	378.0	306.6
97.5°	36.9	37.6	43.1	52.5	68.8	95.7	147.5	254.6	428.8	585.8	626.7
100°	47.2	47.8	52.3	61.2	76.5	101.3	145.9	240.3	408.0	603.6	729.2
102.5°	57.9	59.0	62.9	71.4	85.2	107.9	148.0	228.0	377.3	570.5	734.3
105°	73.9	75.8	79.7	87.3	99.5	119.2	153.6	219.2	339.7	512.5	695.5
107.5°	91.0	92.9	96.6	104.1	115.5	133.9	164.0	218.7	315.8	461.2	627.4
110°	103.3	105.2	108.4	115.4	126.2	144.1	172.8	221.2	306.6	432.2	584.5



TEST NUMBER: P331936-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	114.5	116.4	119.6	126.6	137.5	154.7	181.4	226.2	301.5	412.8	547.3
115°	130.7	133.2	137.1	143.4	154.3	171.5	195.7	234.6	299.6	392.0	502.3
117.5°	146.8	149.8	153.0	158.8	171.0	186.9	210.8	245.6	300.8	379.8	475.2
120°	158.1	160.0	163.1	169.6	181.6	197.6	220.5	253.7	302.8	374.1	460.9
122.5°	167.8	169.7	172.8	179.8	191.4	208.3	230.7	261.3	306.3	370.6	449.1
125°	181.6	183.0	186.8	193.8	205.9	223.1	245.4	273.5	311.7	365.9	434.1
127.5°	192.2	194.1	198.9	206.0	219.4	236.6	258.1	283.4	317.8	363.6	420.9
130°	198.9	200.8	206.5	214.2	227.6	244.8	265.8	290.0	321.9	362.1	413.7
132.5°	204.0	206.4	212.6	221.8	235.2	251.9	272.4	296.1	325.0	361.5	407.1
135°	212.9	215.5	222.5	232.0	245.4	262.6	282.3	304.0	329.5	360.8	398.4
137.5°	221.3	224.0	230.9	241.1	254.3	270.3	289.3	309.9	332.6	359.4	390.9
140°	226.9	230.1	236.5	246.7	259.4	275.3	293.8	313.0	334.7	358.9	386.3
142.5°	233.0	235.7	242.6	251.8	264.6	279.4	297.4	316.0	336.1	357.8	382.2
145°	242.9	244.8	250.5	260.1	270.9	285.6	302.1	319.4	337.2	356.3	376.7
147.5°	252.8	254.0	259.6	267.8	278.3	290.8	306.0	321.4	337.2	353.9	371.4
150°	259.4	260.1	265.1	273.5	282.3	293.8	308.5	321.9	337.2	351.9	367.8
152.5°	266.0	266.2	271.3	278.6	286.4	297.4	310.1	322.9	335.7	349.3	363.7
155°	276.0	276.0	279.8	286.2	293.2	302.1	313.0	323.2	334.0	344.9	357.6
157.5°	283.9	284.4	287.5	293.1	299.1	306.0	314.6	323.8	331.8	340.9	350.7
160°	290.0	290.0	292.6	297.7	302.1	308.5	316.2	323.8	330.8	337.9	346.1
162.5°	294.6	294.6	296.7	300.8	304.7	310.1	316.7	323.3	328.8	334.8	341.5
165°	301.5	300.8	302.1	305.3	307.9	312.3	317.4	321.9	325.7	330.2	335.3
167.5°	306.7	306.0	306.6	309.0	310.8	313.6	317.3	320.9	322.7	325.6	329.3
170°	309.8	308.5	309.2	311.0	312.3	313.6	316.8	319.4	320.7	322.5	325.7
172.5°	311.9	311.0	311.2	312.6	313.3	314.1	316.8	318.9	319.1	320.0	322.1
175°	314.2	313.6	313.0	314.2	314.2	314.9	316.2	317.4	316.8	316.8	318.0
177.5°	315.4	314.9	314.4	314.9	314.9	314.9	315.4	316.4	315.4	314.9	315.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P331936-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	726.4	726.4	726.4	726.4	726.4	726.4	726.4	726.4
2.5°	723.6	724.6	725.8	726.3	726.2	726.0	725.9	725.9
5°	719.7	721.1	722.5	723.1	722.8	722.5	722.3	721.9
7.5°	712.1	713.3	714.6	715.1	714.9	714.8	714.6	714.4
10°	705.1	706.4	707.6	708.1	707.8	707.5	707.3	706.9
12.5°	697.4	698.4	699.3	699.6	699.4	699.3	699.1	699.0
15°	683.6	684.7	685.8	685.9	685.1	684.3	683.5	682.7
17.5°	666.1	666.8	667.6	667.8	667.6	667.2	666.9	666.6
20°	653.1	653.7	654.2	654.3	653.9	653.5	653.1	652.6
22.5°	639.4	639.8	640.3	640.3	639.8	639.2	638.7	638.1
25°	616.7	616.9	616.9	616.9	616.4	616.0	615.6	615.1
27.5°	592.6	592.6	592.7	592.6	592.0	591.5	590.9	590.4
30°	575.8	575.8	575.8	575.4	574.4	573.4	572.4	571.4
32.5°	558.3	557.5	556.7	556.0	555.5	555.1	554.5	554.0
35°	529.8	529.0	528.2	527.4	526.7	526.0	525.3	524.6
37.5°	500.3	499.4	498.4	497.7	497.3	496.8	496.4	495.9
40°	481.2	480.0	479.0	478.1	477.5	477.0	476.5	475.9
42.5°	461.2	460.1	458.9	458.1	457.5	457.1	456.5	455.9
45°	431.4	429.7	428.0	426.8	426.2	425.4	424.8	424.0
47.5°	399.9	398.3	396.6	395.5	394.9	394.3	393.7	393.1
50°	379.2	377.6	376.1	375.0	374.1	373.2	372.4	371.6
52.5°	358.2	356.9	355.6	354.4	353.6	352.8	352.0	351.1
55°	326.0	324.6	323.0	321.9	321.2	320.5	319.8	319.1
57.5°	294.6	293.2	291.9	290.7	289.9	289.2	288.4	287.6
60°	272.3	271.1	269.8	268.8	268.2	267.4	266.8	266.0
62.5°	250.8	249.6	248.3	247.4	247.0	246.5	246.1	245.6
65°	218.8	217.8	216.6	215.9	215.5	215.1	214.7	214.2
67.5°	187.2	186.2	185.2	184.4	183.8	183.3	182.7	182.1
70°	166.6	165.8	164.8	163.9	163.2	162.5	161.8	161.1
72.5°	145.9	145.0	144.2	143.6	143.2	142.8	142.5	142.1
75°	116.0	115.4	114.6	114.1	113.7	113.2	112.8	112.4
77.5°	88.1	87.6	87.2	86.9	86.9	86.9	86.9	86.9
80°	70.3	70.1	70.0	70.0	70.0	70.0	70.0	70.0
82.5°	54.1	53.8	53.6	53.4	53.3	53.2	53.1	53.0
85°	30.7	30.4	30.1	30.0	30.0	30.0	30.0	30.0
87.5°	13.9	13.9	14.0	14.2	14.0	14.2	14.3	14.2
90°	15.9	16.6	17.2	18.5	17.9	18.5	19.2	18.5
92.5°	53.6	42.6	37.6	34.3	33.2	31.2	31.9	30.7
95°	229.5	155.6	121.7	98.8	86.7	81.0	76.5	73.9
97.5°	572.0	458.2	375.9	299.7	252.7	224.0	206.8	201.3
100°	751.5	699.9	625.3	534.8	470.4	423.9	399.0	399.7
102.5°	811.1	809.5	766.1	708.7	658.6	621.7	601.0	586.3
105°	828.7	892.3	904.5	887.9	858.6	834.4	814.0	810.8
107.5°	778.4	881.9	937.8	960.4	961.0	952.8	945.9	940.0
110°	730.5	847.7	928.1	972.7	990.5	995.6	994.3	993.1



TEST NUMBER: P331936-930

CATALOG NUMBER: S123DIP-S560D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	683.1	802.9	892.9	950.2	982.9	998.7	1003.6	1003.8
115°	620.2	731.1	824.8	894.3	942.1	970.1	982.9	986.1
117.5°	574.7	670.4	754.6	825.1	874.9	907.0	925.4	929.8
120°	550.7	636.7	713.3	777.6	828.0	863.7	879.0	882.8
122.5°	531.9	609.8	680.6	740.5	785.1	817.3	834.1	838.9
125°	506.7	576.3	637.4	688.4	729.2	757.2	773.1	777.6
127.5°	484.9	546.7	602.0	648.4	684.7	708.7	723.1	727.2
130°	471.1	528.4	580.1	623.4	657.2	680.1	693.5	698.6
132.5°	458.3	511.1	559.1	600.5	632.2	655.2	667.0	670.6
135°	441.1	486.3	527.7	564.1	595.3	614.5	625.9	630.4
137.5°	425.4	462.5	498.2	529.7	556.0	575.4	585.1	588.0
140°	416.2	448.7	479.3	506.7	531.0	548.8	559.1	558.4
142.5°	407.6	435.5	462.0	485.8	506.5	522.3	531.5	530.8
145°	397.1	418.2	438.5	457.1	473.0	486.3	491.5	492.7
147.5°	388.6	405.3	421.8	434.9	446.9	456.0	460.9	461.4
150°	382.5	397.1	410.5	422.6	432.2	439.2	443.0	443.0
152.5°	376.8	389.5	401.3	411.4	418.9	425.4	427.7	427.7
155°	368.4	378.6	388.2	395.8	401.5	406.7	408.0	408.5
157.5°	359.5	368.0	375.4	381.4	386.4	390.2	391.3	391.1
160°	354.4	361.4	367.8	372.3	376.7	380.5	380.5	379.9
162.5°	348.3	354.2	360.1	364.1	367.0	370.3	370.3	369.7
165°	340.4	344.2	348.7	351.9	354.4	356.9	356.3	356.3
167.5°	333.5	336.4	339.0	341.3	342.4	344.2	343.6	343.6
170°	328.9	330.8	333.4	334.7	335.3	336.6	335.9	335.9
172.5°	324.8	326.2	328.2	329.1	329.1	330.4	329.3	328.8
175°	319.4	320.0	321.2	321.2	321.2	321.9	321.2	320.7
177.5°	315.9	316.4	316.9	316.9	316.4	316.9	315.9	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9

(END OF REPORT)