

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331885-935

Luminaire Tested: **S123DIP-S340D805U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331885-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D805U935-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3753.9 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	36	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	16
6	61	49	41	36	54	44	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4456	4456	4456	4456
5°	5314	4475	3965	4475
10°	6652	4453	3583	4453
15°	8158	4416	3335	4416
20°	9718	4361	3175	4361
25°	10320	4292	3139	4292
30°	8846	4243	3156	4243
35°	6151	4172	3189	4172
40°	4634	4089	3180	4089
45°	3847	3965	3139	3965
50°	3446	3716	3110	3716
55°	3222	3445	3072	3445
60°	3023	3160	3040	3160
65°	2840	2881	2942	2881
70°	2662	2565	2801	2565
75°	2383	2246	2570	2246
80°	2089	1841	2213	1841
85°	1643	1334	1494	1334



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.8	1.1
10°-20°	130.8	3.5
20°-30°	219.5	5.8
30°-40°	248.5	6.6
40°-50°	222.9	5.9
50°-60°	179.8	4.8
60°-70°	125.3	3.3
70°-80°	65.9	1.8
80°-90°	18.7	0.5
90°-100°	185.1	4.9
100°-110°	524.0	14.0
110°-120°	515.5	13.7
120°-130°	411.2	11.0
130°-140°	324.2	8.6
140°-150°	242.0	6.4
150°-160°	168.6	4.5
160°-170°	99.1	2.6
170°-180°	32.2	0.9
0°-30°	391.0	10.4
0°-40°	639.5	17.0
0°-60°	1042.2	27.8
0°-90°	1252.1	33.4
90°-120°	1224.6	32.6
90°-150°	2201.9	58.7
90°-180°	2502.0	66.6
0°-180°	3753.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	414	414	414	414	414	
5°	492	414	367	414	492	51
15°	732	396	299	396	732	211
25°	869	361	264	361	869	381
35°	468	318	243	318	468	304
45°	253	260	206	260	253	200
55°	172	184	164	184	172	154
65°	112	113	116	113	112	111
75°	57	54	62	54	57	61
85°	13	11	12	11	13	16
90°	20	1	20	1	20	11
95°	78	23	78	23	78	141
105°	856	78	856	78	856	845
115°	1041	138	1041	138	1041	1012
125°	821	192	821	192	821	744
135°	666	225	666	225	666	516
145°	520	256	520	256	520	331
155°	431	291	431	291	431	201
165°	376	318	376	318	376	108
175°	339	332	339	332	339	33
180°	332	332	332	332	332	



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	439.4	439.0	438.2	438.9	437.6	435.8	435.7	434.0	429.4	429.1	427.8
5°	491.8	490.3	490.0	489.8	487.0	483.2	476.0	475.4	465.7	461.0	455.1
7.5°	559.8	560.6	557.7	555.2	546.6	540.9	533.1	523.2	511.4	499.4	491.5
10°	608.6	615.2	607.0	601.3	596.2	586.3	574.9	560.6	546.4	529.8	517.1
12.5°	660.9	664.1	662.5	657.2	649.1	634.1	613.9	598.1	585.0	557.3	546.1
15°	732.1	744.3	736.5	718.5	718.8	704.6	678.2	649.1	633.6	609.3	576.3
17.5°	808.0	809.5	806.2	791.2	781.2	761.6	737.1	709.3	678.0	648.6	613.5
20°	848.4	847.2	840.2	832.4	815.2	800.0	773.3	742.2	702.1	673.1	634.8
22.5°	870.9	868.9	865.6	859.0	844.7	828.4	804.3	770.4	732.2	692.4	648.2
25°	868.9	871.5	871.9	870.1	865.1	855.3	836.5	809.3	771.3	720.1	674.0
27.5°	790.3	794.0	804.7	814.2	824.8	835.7	834.2	820.8	792.6	748.4	692.0
30°	711.7	703.6	723.5	748.6	765.6	795.7	812.5	813.6	797.7	759.8	704.8
32.5°	602.5	611.4	620.2	651.0	688.3	722.0	755.6	782.6	785.7	760.4	712.4
35°	468.1	479.2	495.2	511.3	551.4	585.9	644.9	696.2	737.1	742.5	713.1
37.5°	377.3	382.7	392.9	409.0	435.1	476.1	521.7	586.6	645.9	690.0	691.9
40°	329.8	331.4	342.8	355.0	376.3	410.0	451.1	508.5	579.5	641.1	666.8
42.5°	294.1	297.6	302.6	314.3	331.2	356.5	394.8	442.2	507.3	578.2	628.4
45°	252.7	256.8	259.8	267.6	279.7	296.7	323.3	366.7	416.2	489.4	557.0
47.5°	225.4	225.7	227.9	233.8	242.0	254.9	273.7	301.5	347.0	406.4	475.8
50°	205.8	209.0	209.8	214.4	220.8	230.2	245.9	269.6	306.9	359.0	422.8
52.5°	192.0	193.0	195.2	198.5	204.1	211.5	225.1	243.6	272.9	317.4	376.0
55°	171.7	171.7	173.9	176.5	179.7	186.3	195.4	209.0	231.3	265.8	314.4
57.5°	152.9	153.9	155.5	156.3	159.0	163.4	170.9	181.3	197.9	224.5	263.0
60°	140.4	142.2	142.0	143.6	146.0	149.5	155.8	164.3	179.1	200.4	232.9
62.5°	129.5	129.4	129.3	131.3	133.6	136.9	141.1	148.4	161.0	179.9	207.5
65°	111.5	111.2	112.5	113.7	114.5	116.9	120.1	126.6	135.0	149.0	170.5
67.5°	95.6	94.4	95.1	95.6	96.9	98.8	101.9	105.8	112.4	123.7	139.9
70°	84.6	83.6	83.4	83.9	85.1	86.4	88.7	92.5	98.7	107.7	119.5
72.5°	73.4	72.8	72.7	73.6	74.1	75.1	76.6	80.1	85.1	91.9	102.9
75°	57.3	57.3	57.3	57.6	58.2	59.0	60.2	62.0	65.8	70.6	78.0
77.5°	43.0	43.0	42.7	42.7	43.6	43.9	44.2	45.9	48.0	51.2	56.7
80°	33.7	32.7	33.1	33.7	34.1	34.3	34.9	35.3	37.1	38.9	42.7
82.5°	25.1	24.2	24.3	25.2	25.3	25.5	26.1	26.6	27.3	28.9	31.0
85°	13.3	13.3	13.4	13.4	13.6	13.4	14.0	14.2	14.2	15.2	16.4
87.5°	8.7	8.5	8.5	8.6	8.5	8.4	8.4	8.5	8.5	8.8	8.6
90°	19.5	20.2	19.5	18.9	19.5	18.2	17.5	16.8	16.2	16.8	14.8
92.5°	32.5	33.7	33.0	35.0	36.2	39.7	44.9	56.7	78.1	103.5	113.9
95°	78.1	80.8	85.5	91.5	104.4	128.5	164.3	242.4	323.8	399.2	355.4
97.5°	212.6	218.3	236.5	266.8	316.5	397.0	483.9	604.1	661.9	618.6	452.9
100°	422.1	421.4	447.6	496.8	564.7	660.4	739.1	793.7	770.1	637.5	430.8
102.5°	619.1	634.6	656.6	695.5	748.4	809.0	854.9	856.6	775.5	602.4	398.5
105°	856.3	859.6	881.1	906.7	937.7	955.2	942.4	875.1	734.4	541.2	358.8
107.5°	992.7	998.9	1006.3	1014.9	1014.3	990.3	931.3	822.1	662.5	487.1	333.5
110°	1048.8	1050.1	1051.5	1046.0	1027.3	980.1	895.3	771.5	617.3	456.4	323.8



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1060.1	1059.8	1054.7	1038.0	1003.5	943.0	847.9	721.3	578.0	435.9	318.4
115°	1041.4	1038.0	1024.5	994.9	944.4	871.1	772.1	655.0	530.5	414.0	316.4
117.5°	981.9	977.2	957.9	923.9	871.3	796.9	708.0	606.9	501.8	401.1	317.6
120°	932.3	928.2	912.1	874.4	821.2	753.3	672.4	581.6	486.7	395.1	319.8
122.5°	886.0	880.9	863.1	829.1	782.0	718.8	643.9	561.7	474.3	391.4	323.5
125°	821.2	816.5	799.7	770.1	727.0	673.1	608.6	535.1	458.4	386.4	329.2
127.5°	767.9	763.6	748.4	723.1	684.8	635.8	577.4	512.0	444.4	384.0	335.6
130°	737.8	732.4	718.2	694.1	658.3	612.6	558.0	497.5	436.9	382.4	339.9
132.5°	708.2	704.4	691.9	667.6	634.1	590.5	539.8	484.0	429.9	381.8	343.2
135°	665.7	661.0	648.9	628.7	595.7	557.3	513.6	465.8	420.7	381.0	348.0
137.5°	621.0	617.9	607.6	587.1	559.4	526.2	488.4	449.3	412.8	379.5	351.3
140°	589.7	590.4	579.5	560.8	535.1	506.2	473.9	439.5	407.9	379.0	353.4
142.5°	560.6	561.3	551.6	534.9	513.1	487.9	459.9	430.4	403.6	377.9	355.0
145°	520.3	519.0	513.6	499.5	482.7	463.1	441.6	419.4	397.9	376.3	356.1
147.5°	487.2	486.7	481.6	472.0	459.3	445.4	428.0	410.4	392.2	373.8	356.1
150°	467.9	467.9	463.8	456.4	446.3	433.5	419.4	403.9	388.4	371.6	356.1
152.5°	451.7	451.7	449.3	442.4	434.5	423.8	411.3	398.0	384.1	368.9	354.5
155°	431.4	430.8	429.5	424.0	418.0	409.9	399.8	389.1	377.6	364.2	352.8
157.5°	413.0	413.2	412.1	408.0	402.8	396.5	388.7	379.6	370.4	360.0	350.4
160°	401.2	401.8	401.8	397.9	393.1	388.4	381.7	374.3	365.5	356.8	349.4
162.5°	390.5	391.1	391.1	387.6	384.5	380.3	374.1	367.8	360.7	353.5	347.2
165°	376.3	376.3	376.9	374.3	371.6	368.2	363.5	359.5	354.0	348.7	344.0
167.5°	362.8	362.8	363.5	361.6	360.4	358.0	355.2	352.1	347.8	343.9	340.8
170°	354.7	354.7	355.4	354.0	353.4	352.1	349.4	347.3	344.0	340.6	338.6
172.5°	347.2	347.8	349.0	347.6	347.5	346.6	344.5	343.0	340.2	337.9	337.0
175°	338.6	339.2	339.9	339.2	339.2	339.2	337.9	337.3	335.9	334.6	334.6
177.5°	333.6	333.6	334.7	334.2	334.7	334.7	334.2	333.6	333.0	332.5	333.0
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	426.8	425.6	424.3	422.1	420.1	417.4	416.6	415.6	412.7	410.2	408.2
5°	452.9	448.1	441.1	434.6	429.5	422.4	418.4	414.2	408.2	402.8	398.4
7.5°	480.2	470.7	459.8	448.1	437.0	426.5	417.9	410.3	401.8	393.9	387.6
10°	501.9	488.2	472.9	456.5	442.5	428.9	417.4	407.4	396.6	387.1	379.3
12.5°	526.6	506.4	485.3	465.4	448.8	429.8	415.9	403.2	390.9	379.6	370.8
15°	555.8	530.1	505.2	477.8	452.5	428.9	412.4	396.3	382.1	370.5	359.2
17.5°	582.5	553.4	520.6	487.2	456.7	428.6	405.6	387.4	369.6	355.4	344.2
20°	597.5	564.5	527.4	492.7	458.9	427.7	402.3	380.7	361.4	346.4	333.8
22.5°	610.5	571.8	533.4	496.3	458.7	425.1	396.4	374.1	353.3	338.5	325.1
25°	624.1	577.6	539.2	495.7	453.7	418.8	386.8	361.4	340.6	323.3	309.5
27.5°	635.6	577.3	531.6	484.7	445.7	410.8	376.5	349.4	327.3	308.5	294.5
30°	643.3	578.1	523.7	477.4	438.1	402.0	368.7	341.4	318.1	299.1	285.9
32.5°	648.1	577.6	516.5	467.1	425.9	393.9	360.2	331.9	308.0	289.3	276.6
35°	650.9	574.0	504.0	445.9	406.2	375.1	346.8	317.5	292.5	275.0	260.5
37.5°	645.2	566.6	489.7	425.4	381.9	351.4	327.5	302.6	278.6	259.4	246.9
40°	636.5	561.8	478.4	411.0	365.2	335.8	315.6	291.0	267.3	249.1	237.5
42.5°	619.6	552.1	466.1	394.9	347.9	318.5	299.8	279.3	256.9	239.8	228.2
45°	578.5	530.7	447.5	370.9	322.4	291.9	275.4	260.5	240.3	223.7	213.6
47.5°	521.4	498.7	420.7	345.5	295.6	266.3	249.2	237.3	222.5	209.0	199.4
50°	481.8	472.3	402.6	328.1	277.8	249.1	232.6	221.9	211.2	197.8	189.0
52.5°	436.1	441.9	381.4	310.2	259.7	231.4	216.0	207.4	197.8	186.7	179.0
55°	371.7	392.7	344.8	280.0	232.6	205.8	191.1	183.6	177.9	169.7	163.1
57.5°	311.4	338.2	305.2	248.9	206.1	183.0	168.9	160.7	157.0	152.7	147.5
60°	275.6	302.0	277.0	228.1	188.4	166.3	153.9	146.8	143.2	140.2	135.8
62.5°	243.7	270.4	249.4	206.9	170.8	150.4	139.6	132.7	129.9	128.4	124.6
65°	199.8	222.8	208.8	173.9	145.9	127.8	118.0	113.1	110.6	109.9	107.5
67.5°	162.6	180.1	170.0	144.2	122.2	106.6	98.2	94.1	92.1	91.9	90.1
70°	138.2	154.6	146.8	123.6	104.5	92.3	85.1	81.5	80.2	80.1	79.0
72.5°	119.2	130.7	124.5	105.1	90.4	79.3	74.0	70.2	68.9	69.1	68.4
75°	88.3	96.9	93.2	79.8	68.0	60.8	56.4	54.0	52.8	53.4	52.5
77.5°	63.5	69.0	65.7	56.4	49.1	43.9	40.6	39.2	38.1	38.1	37.7
80°	48.0	51.1	49.3	43.7	37.7	33.3	30.7	29.7	29.1	28.8	28.7
82.5°	34.2	36.9	34.7	30.9	26.8	24.1	22.6	21.4	20.9	21.0	20.8
85°	17.2	18.3	17.5	15.1	13.4	12.2	11.5	10.8	10.4	10.6	10.2
87.5°	8.5	8.3	7.4	6.5	5.9	5.0	4.7	4.1	4.0	4.3	4.6
90°	12.8	10.8	8.8	7.4	6.0	4.0	2.7	1.4	2.7	4.0	6.0
92.5°	85.5	56.6	38.9	28.9	23.3	18.1	12.4	8.4	12.4	18.1	23.3
95°	245.0	144.7	87.5	61.2	43.7	32.3	24.9	22.9	24.9	32.3	43.7
97.5°	268.9	155.8	101.1	72.7	55.4	45.5	39.7	39.0	39.7	45.5	55.4
100°	253.7	154.1	107.0	80.8	64.7	55.2	50.5	49.9	50.5	55.2	64.7
102.5°	240.8	156.3	114.0	90.0	75.4	66.5	62.3	61.1	62.3	66.5	75.4
105°	231.5	162.2	125.9	105.0	92.2	84.1	80.1	78.1	80.1	84.1	92.2
107.5°	230.9	173.2	141.4	122.0	109.9	102.0	98.2	96.1	98.2	102.0	109.9
110°	233.6	182.4	152.1	133.3	121.8	114.4	111.1	109.1	111.1	114.4	121.8



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	238.9	191.6	163.4	145.2	133.7	126.3	123.0	120.9	123.0	126.3	133.7
115°	247.7	206.6	181.1	162.9	151.4	144.7	140.7	138.0	140.7	144.7	151.4
117.5°	259.3	222.7	197.3	180.6	167.7	161.5	158.2	155.1	158.2	161.5	167.7
120°	267.9	232.9	208.7	191.8	179.1	172.3	168.9	166.9	168.9	172.3	179.1
122.5°	276.0	243.7	220.0	202.1	189.9	182.5	179.2	177.2	179.2	182.5	189.9
125°	288.8	259.2	235.6	217.4	204.7	197.3	193.2	191.8	193.2	197.3	204.7
127.5°	299.3	272.6	249.9	231.7	217.6	210.0	205.0	203.0	205.0	210.0	217.6
130°	306.3	280.7	258.5	240.3	226.2	218.1	212.1	210.0	212.1	218.1	226.2
132.5°	312.7	287.7	266.0	248.4	234.3	224.5	218.0	215.4	218.0	224.5	234.3
135°	321.1	298.2	277.3	259.2	245.0	235.0	227.6	224.8	227.6	235.0	245.0
137.5°	327.3	305.5	285.4	268.5	254.6	243.8	236.5	233.7	236.5	243.8	254.6
140°	330.5	310.3	290.8	274.0	260.5	249.8	243.0	239.6	243.0	249.8	260.5
142.5°	333.7	314.1	295.1	279.4	265.9	256.2	248.9	246.1	248.9	256.2	265.9
145°	337.3	319.1	301.6	286.1	274.7	264.6	258.5	256.5	258.5	264.6	274.7
147.5°	339.4	323.1	307.1	293.9	282.8	274.1	268.2	267.0	268.2	274.1	282.8
150°	339.9	325.8	310.3	298.2	288.8	280.0	274.7	274.0	274.7	280.0	288.8
152.5°	341.0	327.4	314.1	302.5	294.2	286.5	281.1	280.9	281.1	286.5	294.2
155°	341.3	330.5	319.1	309.6	302.2	295.5	291.4	291.4	291.4	295.5	302.2
157.5°	342.0	332.3	323.1	315.8	309.5	303.6	300.3	299.8	300.3	303.6	309.5
160°	342.0	333.9	325.8	319.1	314.4	309.0	306.3	306.3	306.3	309.0	314.4
162.5°	341.4	334.4	327.4	321.8	317.6	313.3	311.2	311.2	311.2	313.3	317.6
165°	339.9	335.2	329.8	325.1	322.4	319.1	317.7	318.4	317.7	319.1	322.4
167.5°	338.9	335.1	331.2	328.2	326.3	323.8	323.1	323.9	323.1	323.8	326.3
170°	337.3	334.6	331.2	329.8	328.5	326.5	325.8	327.2	325.8	326.5	328.5
172.5°	336.7	334.6	331.7	330.9	330.1	328.6	328.5	329.3	328.5	328.6	330.1
175°	335.2	333.9	332.5	331.8	331.8	330.5	331.2	331.8	331.2	330.5	331.8
177.5°	334.2	333.0	332.5	332.5	332.5	332.0	332.5	333.0	332.5	332.0	332.5
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	407.1	406.0	404.4	402.0	400.0	397.0	397.0	397.4	397.4	397.4	397.0
5°	394.8	391.8	388.1	383.9	379.5	375.1	374.3	372.6	371.5	370.7	369.7
7.5°	381.7	376.3	371.1	365.2	359.8	355.4	352.3	349.7	348.1	346.3	345.0
10°	372.9	366.3	360.1	353.9	347.0	341.6	338.2	335.8	334.0	332.3	331.6
12.5°	362.5	354.9	348.0	342.1	334.7	329.1	325.8	324.7	322.6	319.2	317.5
15°	347.2	340.2	332.0	323.0	319.3	312.5	308.7	306.9	305.7	303.1	302.3
17.5°	334.2	325.0	315.7	309.0	302.3	296.8	294.6	292.4	290.8	288.7	288.0
20°	323.7	315.6	307.1	299.9	292.8	286.8	285.0	283.4	281.8	280.9	280.0
22.5°	313.1	305.0	297.9	291.2	283.7	279.7	277.8	276.0	274.9	274.2	273.5
25°	298.3	291.0	283.2	277.2	271.2	268.5	267.3	266.4	265.5	264.6	264.3
27.5°	285.0	277.1	270.8	265.1	260.8	258.6	257.4	257.0	257.2	257.5	257.8
30°	275.0	267.8	262.6	257.8	253.7	251.8	251.5	251.5	252.4	252.5	253.0
32.5°	265.9	259.9	254.7	250.0	247.0	245.6	246.4	246.4	247.0	247.5	248.3
35°	252.5	247.3	243.3	239.3	236.7	237.3	237.7	238.1	239.1	240.3	241.1
37.5°	239.8	235.3	231.1	228.0	226.8	227.8	228.9	229.6	230.8	231.8	232.6
40°	230.7	227.2	223.3	220.4	220.8	221.4	222.2	223.3	224.3	224.9	225.7
42.5°	222.1	218.6	215.5	213.2	213.8	214.6	215.0	215.5	216.7	217.8	218.3
45°	209.2	206.4	203.6	202.2	202.6	203.0	203.4	204.0	205.0	205.8	206.0
47.5°	194.7	192.7	190.8	189.4	190.1	189.9	190.5	191.7	192.0	192.5	193.6
50°	185.4	183.6	181.3	180.9	180.9	180.9	181.2	182.7	182.7	183.6	184.3
52.5°	175.0	173.9	172.5	171.8	171.4	171.4	172.3	173.1	173.4	174.5	175.4
55°	159.9	158.7	157.5	156.9	156.4	156.9	158.4	158.9	159.9	160.5	161.1
57.5°	144.0	143.1	142.2	141.8	141.7	142.2	143.1	144.3	144.6	146.5	147.3
60°	133.6	132.2	131.4	131.4	131.0	132.8	132.4	134.4	134.8	136.0	137.4
62.5°	122.9	121.0	120.6	120.6	121.2	121.7	122.3	123.1	124.2	125.7	126.8
65°	105.5	104.5	105.9	105.7	105.3	106.5	106.5	107.5	108.7	110.1	112.4
67.5°	89.1	88.6	88.7	88.7	89.3	90.0	90.6	91.4	92.9	94.4	95.8
70°	78.0	78.6	77.7	78.4	79.0	79.2	79.6	80.8	82.4	83.4	85.1
72.5°	67.2	67.2	67.3	67.7	68.3	68.6	69.1	70.4	72.2	73.0	74.3
75°	51.7	51.6	52.2	52.2	53.1	53.6	54.0	54.6	56.1	57.3	58.4
77.5°	37.8	38.1	37.9	38.6	38.3	38.4	39.6	40.2	40.4	42.8	43.3
80°	28.5	28.8	29.1	29.3	29.4	29.1	30.5	31.1	31.1	32.5	33.5
82.5°	20.5	20.7	21.2	21.4	21.4	21.9	22.0	22.4	22.9	23.5	24.8
85°	10.2	10.8	11.0	10.8	11.0	10.6	11.2	11.5	11.6	11.6	11.6
87.5°	4.6	5.1	5.3	5.9	6.2	6.7	6.6	6.5	6.5	7.1	6.8
90°	7.4	8.8	10.8	12.8	14.8	16.8	16.2	16.8	17.5	18.2	19.5
92.5°	28.9	38.9	56.6	85.5	113.9	103.5	78.1	56.7	44.9	39.7	36.2
95°	61.2	87.5	144.7	245.0	355.4	399.2	323.8	242.4	164.3	128.5	104.4
97.5°	72.7	101.1	155.8	268.9	452.9	618.6	661.9	604.1	483.9	397.0	316.5
100°	80.8	107.0	154.1	253.7	430.8	637.5	770.1	793.7	739.1	660.4	564.7
102.5°	90.0	114.0	156.3	240.8	398.5	602.4	775.5	856.6	854.9	809.0	748.4
105°	105.0	125.9	162.2	231.5	358.8	541.2	734.4	875.1	942.4	955.2	937.7
107.5°	122.0	141.4	173.2	230.9	333.5	487.1	662.5	822.1	931.3	990.3	1014.3
110°	133.3	152.1	182.4	233.6	323.8	456.4	617.3	771.5	895.3	980.1	1027.3



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	145.2	163.4	191.6	238.9	318.4	435.9	578.0	721.3	847.9	943.0	1003.5
115°	162.9	181.1	206.6	247.7	316.4	414.0	530.5	655.0	772.1	871.1	944.4
117.5°	180.6	197.3	222.7	259.3	317.6	401.1	501.8	606.9	708.0	796.9	871.3
120°	191.8	208.7	232.9	267.9	319.8	395.1	486.7	581.6	672.4	753.3	821.2
122.5°	202.1	220.0	243.7	276.0	323.5	391.4	474.3	561.7	643.9	718.8	782.0
125°	217.4	235.6	259.2	288.8	329.2	386.4	458.4	535.1	608.6	673.1	727.0
127.5°	231.7	249.9	272.6	299.3	335.6	384.0	444.4	512.0	577.4	635.8	684.8
130°	240.3	258.5	280.7	306.3	339.9	382.4	436.9	497.5	558.0	612.6	658.3
132.5°	248.4	266.0	287.7	312.7	343.2	381.8	429.9	484.0	539.8	590.5	634.1
135°	259.2	277.3	298.2	321.1	348.0	381.0	420.7	465.8	513.6	557.3	595.7
137.5°	268.5	285.4	305.5	327.3	351.3	379.5	412.8	449.3	488.4	526.2	559.4
140°	274.0	290.8	310.3	330.5	353.4	379.0	407.9	439.5	473.9	506.2	535.1
142.5°	279.4	295.1	314.1	333.7	355.0	377.9	403.6	430.4	459.9	487.9	513.1
145°	286.1	301.6	319.1	337.3	356.1	376.3	397.9	419.4	441.6	463.1	482.7
147.5°	293.9	307.1	323.1	339.4	356.1	373.8	392.2	410.4	428.0	445.4	459.3
150°	298.2	310.3	325.8	339.9	356.1	371.6	388.4	403.9	419.4	433.5	446.3
152.5°	302.5	314.1	327.4	341.0	354.5	368.9	384.1	398.0	411.3	423.8	434.5
155°	309.6	319.1	330.5	341.3	352.8	364.2	377.6	389.1	399.8	409.9	418.0
157.5°	315.8	323.1	332.3	342.0	350.4	360.0	370.4	379.6	388.7	396.5	402.8
160°	319.1	325.8	333.9	342.0	349.4	356.8	365.5	374.3	381.7	388.4	393.1
162.5°	321.8	327.4	334.4	341.4	347.2	353.5	360.7	367.8	374.1	380.3	384.5
165°	325.1	329.8	335.2	339.9	344.0	348.7	354.0	359.5	363.5	368.2	371.6
167.5°	328.2	331.2	335.1	338.9	340.8	343.9	347.8	352.1	355.2	358.0	360.4
170°	329.8	331.2	334.6	337.3	338.6	340.6	344.0	347.3	349.4	352.1	353.4
172.5°	330.9	331.7	334.6	336.7	337.0	337.9	340.2	343.0	344.5	346.6	347.5
175°	331.8	332.5	333.9	335.2	334.6	334.6	335.9	337.3	337.9	339.2	339.2
177.5°	332.5	332.5	333.0	334.2	333.0	332.5	333.0	333.6	334.2	334.7	334.7
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	395.9	395.7	396.8	396.1	396.8	395.7	395.9	397.0	397.4	397.4	397.4
5°	368.5	369.1	367.0	367.0	367.0	369.1	368.5	369.7	370.7	371.5	372.6
7.5°	344.1	343.2	343.3	342.2	343.3	343.2	344.1	345.0	346.3	348.1	349.7
10°	329.2	328.0	327.5	327.8	327.5	328.0	329.2	331.6	332.3	334.0	335.8
12.5°	316.8	316.6	313.9	313.9	313.9	316.6	316.8	317.5	319.2	322.6	324.7
15°	302.3	298.5	298.1	299.3	298.1	298.5	302.3	302.3	303.1	305.7	306.9
17.5°	287.7	285.7	285.9	285.2	285.9	285.7	287.7	288.0	288.7	290.8	292.4
20°	280.0	278.8	278.6	277.2	278.6	278.8	280.0	280.0	280.9	281.8	283.4
22.5°	272.9	272.6	272.7	271.1	272.7	272.6	272.9	273.5	274.2	274.9	276.0
25°	264.2	265.2	264.3	264.3	264.3	265.2	264.2	264.3	264.6	265.5	266.4
27.5°	258.2	258.2	257.8	257.8	257.8	258.2	258.2	257.8	257.5	257.2	257.0
30°	253.7	253.6	253.9	253.9	253.9	253.6	253.7	253.0	252.5	252.4	251.5
32.5°	249.3	249.5	249.6	249.8	249.6	249.5	249.3	248.3	247.5	247.0	246.4
35°	242.3	242.5	243.1	242.7	243.1	242.5	242.3	241.1	240.3	239.1	238.1
37.5°	232.9	233.8	233.7	233.9	233.7	233.8	232.9	232.6	231.8	230.8	229.6
40°	225.8	226.4	226.3	226.3	226.3	226.4	225.8	225.7	224.9	224.3	223.3
42.5°	218.6	219.0	218.5	218.3	218.5	219.0	218.6	218.3	217.8	216.7	215.5
45°	206.8	206.4	207.0	206.2	207.0	206.4	206.8	206.0	205.8	205.0	204.0
47.5°	193.6	194.0	194.2	194.8	194.2	194.0	193.6	193.6	192.5	192.0	191.7
50°	184.8	186.0	186.0	185.7	186.0	186.0	184.8	184.3	183.6	182.7	182.7
52.5°	176.1	176.6	177.5	177.4	177.5	176.6	176.1	175.4	174.5	173.4	173.1
55°	162.6	163.1	163.5	163.7	163.5	163.1	162.6	161.1	160.5	159.9	158.9
57.5°	148.8	148.6	149.6	149.9	149.6	148.6	148.8	147.3	146.5	144.6	144.3
60°	139.0	139.0	140.6	141.2	140.6	139.0	139.0	137.4	136.0	134.8	134.4
62.5°	128.5	129.2	130.8	130.0	130.8	129.2	128.5	126.8	125.7	124.2	123.1
65°	113.3	114.9	114.8	115.5	114.8	114.9	113.3	112.4	110.1	108.7	107.5
67.5°	97.4	98.4	99.9	100.0	99.9	98.4	97.4	95.8	94.4	92.9	91.4
70°	86.6	87.6	88.4	89.0	88.4	87.6	86.6	85.1	83.4	82.4	80.8
72.5°	76.2	76.7	78.7	77.8	78.7	76.7	76.2	74.3	73.0	72.2	70.4
75°	59.8	61.2	62.4	61.8	62.4	61.2	59.8	58.4	57.3	56.1	54.6
77.5°	44.2	45.6	46.1	45.6	46.1	45.6	44.2	43.3	42.8	40.4	40.2
80°	34.9	34.7	35.9	35.7	35.9	34.7	34.9	33.5	32.5	31.1	31.1
82.5°	25.6	25.4	25.9	26.1	25.9	25.4	25.6	24.8	23.5	22.9	22.4
85°	12.4	13.0	12.2	12.1	12.2	13.0	12.4	11.6	11.6	11.6	11.5
87.5°	6.6	6.8	6.8	6.5	6.8	6.8	6.6	6.8	7.1	6.5	6.5
90°	18.9	19.5	20.2	19.5	20.2	19.5	18.9	19.5	18.2	17.5	16.8
92.5°	35.0	33.0	33.7	32.5	33.7	33.0	35.0	36.2	39.7	44.9	56.7
95°	91.5	85.5	80.8	78.1	80.8	85.5	91.5	104.4	128.5	164.3	242.4
97.5°	266.8	236.5	218.3	212.6	218.3	236.5	266.8	316.5	397.0	483.9	604.1
100°	496.8	447.6	421.4	422.1	421.4	447.6	496.8	564.7	660.4	739.1	793.7
102.5°	695.5	656.6	634.6	619.1	634.6	656.6	695.5	748.4	809.0	854.9	856.6
105°	906.7	881.1	859.6	856.3	859.6	881.1	906.7	937.7	955.2	942.4	875.1
107.5°	1014.9	1006.3	998.9	992.7	998.9	1006.3	1014.9	1014.3	990.3	931.3	822.1
110°	1046.0	1051.5	1050.1	1048.8	1050.1	1051.5	1046.0	1027.3	980.1	895.3	771.5



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1038.0	1054.7	1059.8	1060.1	1059.8	1054.7	1038.0	1003.5	943.0	847.9	721.3
115°	994.9	1024.5	1038.0	1041.4	1038.0	1024.5	994.9	944.4	871.1	772.1	655.0
117.5°	923.9	957.9	977.2	981.9	977.2	957.9	923.9	871.3	796.9	708.0	606.9
120°	874.4	912.1	928.2	932.3	928.2	912.1	874.4	821.2	753.3	672.4	581.6
122.5°	829.1	863.1	880.9	886.0	880.9	863.1	829.1	782.0	718.8	643.9	561.7
125°	770.1	799.7	816.5	821.2	816.5	799.7	770.1	727.0	673.1	608.6	535.1
127.5°	723.1	748.4	763.6	767.9	763.6	748.4	723.1	684.8	635.8	577.4	512.0
130°	694.1	718.2	732.4	737.8	732.4	718.2	694.1	658.3	612.6	558.0	497.5
132.5°	667.6	691.9	704.4	708.2	704.4	691.9	667.6	634.1	590.5	539.8	484.0
135°	628.7	648.9	661.0	665.7	661.0	648.9	628.7	595.7	557.3	513.6	465.8
137.5°	587.1	607.6	617.9	621.0	617.9	607.6	587.1	559.4	526.2	488.4	449.3
140°	560.8	579.5	590.4	589.7	590.4	579.5	560.8	535.1	506.2	473.9	439.5
142.5°	534.9	551.6	561.3	560.6	561.3	551.6	534.9	513.1	487.9	459.9	430.4
145°	499.5	513.6	519.0	520.3	519.0	513.6	499.5	482.7	463.1	441.6	419.4
147.5°	472.0	481.6	486.7	487.2	486.7	481.6	472.0	459.3	445.4	428.0	410.4
150°	456.4	463.8	467.9	467.9	467.9	463.8	456.4	446.3	433.5	419.4	403.9
152.5°	442.4	449.3	451.7	451.7	451.7	449.3	442.4	434.5	423.8	411.3	398.0
155°	424.0	429.5	430.8	431.4	430.8	429.5	424.0	418.0	409.9	399.8	389.1
157.5°	408.0	412.1	413.2	413.0	413.2	412.1	408.0	402.8	396.5	388.7	379.6
160°	397.9	401.8	401.8	401.2	401.8	401.8	397.9	393.1	388.4	381.7	374.3
162.5°	387.6	391.1	391.1	390.5	391.1	391.1	387.6	384.5	380.3	374.1	367.8
165°	374.3	376.9	376.3	376.3	376.3	376.9	374.3	371.6	368.2	363.5	359.5
167.5°	361.6	363.5	362.8	362.8	362.8	363.5	361.6	360.4	358.0	355.2	352.1
170°	354.0	355.4	354.7	354.7	354.7	355.4	354.0	353.4	352.1	349.4	347.3
172.5°	347.6	349.0	347.8	347.2	347.8	349.0	347.6	347.5	346.6	344.5	343.0
175°	339.2	339.9	339.2	338.6	339.2	339.9	339.2	339.2	339.2	337.9	337.3
177.5°	334.2	334.7	333.6	333.6	333.6	334.7	334.2	334.7	334.7	334.2	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	397.0	397.0	400.0	402.0	404.4	406.0	407.1	408.2	410.2	412.7	415.6
5°	374.3	375.1	379.5	383.9	388.1	391.8	394.8	398.4	402.8	408.2	414.2
7.5°	352.3	355.4	359.8	365.2	371.1	376.3	381.7	387.6	393.9	401.8	410.3
10°	338.2	341.6	347.0	353.9	360.1	366.3	372.9	379.3	387.1	396.6	407.4
12.5°	325.8	329.1	334.7	342.1	348.0	354.9	362.5	370.8	379.6	390.9	403.2
15°	308.7	312.5	319.3	323.0	332.0	340.2	347.2	359.2	370.5	382.1	396.3
17.5°	294.6	296.8	302.3	309.0	315.7	325.0	334.2	344.2	355.4	369.6	387.4
20°	285.0	286.8	292.8	299.9	307.1	315.6	323.7	333.8	346.4	361.4	380.7
22.5°	277.8	279.7	283.7	291.2	297.9	305.0	313.1	325.1	338.5	353.3	374.1
25°	267.3	268.5	271.2	277.2	283.2	291.0	298.3	309.5	323.3	340.6	361.4
27.5°	257.4	258.6	260.8	265.1	270.8	277.1	285.0	294.5	308.5	327.3	349.4
30°	251.5	251.8	253.7	257.8	262.6	267.8	275.0	285.9	299.1	318.1	341.4
32.5°	246.4	245.6	247.0	250.0	254.7	259.9	265.9	276.6	289.3	308.0	331.9
35°	237.7	237.3	236.7	239.3	243.3	247.3	252.5	260.5	275.0	292.5	317.5
37.5°	228.9	227.8	226.8	228.0	231.1	235.3	239.8	246.9	259.4	278.6	302.6
40°	222.2	221.4	220.8	220.4	223.3	227.2	230.7	237.5	249.1	267.3	291.0
42.5°	215.0	214.6	213.8	213.2	215.5	218.6	222.1	228.2	239.8	256.9	279.3
45°	203.4	203.0	202.6	202.2	203.6	206.4	209.2	213.6	223.7	240.3	260.5
47.5°	190.5	189.9	190.1	189.4	190.8	192.7	194.7	199.4	209.0	222.5	237.3
50°	181.2	180.9	180.9	180.9	181.3	183.6	185.4	189.0	197.8	211.2	221.9
52.5°	172.3	171.4	171.4	171.8	172.5	173.9	175.0	179.0	186.7	197.8	207.4
55°	158.4	156.9	156.4	156.9	157.5	158.7	159.9	163.1	169.7	177.9	183.6
57.5°	143.1	142.2	141.7	141.8	142.2	143.1	144.0	147.5	152.7	157.0	160.7
60°	132.4	132.8	131.0	131.4	131.4	132.2	133.6	135.8	140.2	143.2	146.8
62.5°	122.3	121.7	121.2	120.6	120.6	121.0	122.9	124.6	128.4	129.9	132.7
65°	106.5	106.5	105.3	105.7	105.9	104.5	105.5	107.5	109.9	110.6	113.1
67.5°	90.6	90.0	89.3	88.7	88.7	88.6	89.1	90.1	91.9	92.1	94.1
70°	79.6	79.2	79.0	78.4	77.7	78.6	78.0	79.0	80.1	80.2	81.5
72.5°	69.1	68.6	68.3	67.7	67.3	67.2	67.2	68.4	69.1	68.9	70.2
75°	54.0	53.6	53.1	52.2	52.2	51.6	51.7	52.5	53.4	52.8	54.0
77.5°	39.6	38.4	38.3	38.6	37.9	38.1	37.8	37.7	38.1	38.1	39.2
80°	30.5	29.1	29.4	29.3	29.1	28.8	28.5	28.7	28.8	29.1	29.7
82.5°	22.0	21.9	21.4	21.4	21.2	20.7	20.5	20.8	21.0	20.9	21.4
85°	11.2	10.6	11.0	10.8	11.0	10.8	10.2	10.2	10.6	10.4	10.8
87.5°	6.6	6.7	6.2	5.9	5.3	5.1	4.6	4.6	4.3	4.0	4.1
90°	16.2	16.8	14.8	12.8	10.8	8.8	7.4	6.0	4.0	2.7	1.4
92.5°	78.1	103.5	113.9	85.5	56.6	38.9	28.9	23.3	18.1	12.4	8.4
95°	323.8	399.2	355.4	245.0	144.7	87.5	61.2	43.7	32.3	24.9	22.9
97.5°	661.9	618.6	452.9	268.9	155.8	101.1	72.7	55.4	45.5	39.7	39.0
100°	770.1	637.5	430.8	253.7	154.1	107.0	80.8	64.7	55.2	50.5	49.9
102.5°	775.5	602.4	398.5	240.8	156.3	114.0	90.0	75.4	66.5	62.3	61.1
105°	734.4	541.2	358.8	231.5	162.2	125.9	105.0	92.2	84.1	80.1	78.1
107.5°	662.5	487.1	333.5	230.9	173.2	141.4	122.0	109.9	102.0	98.2	96.1
110°	617.3	456.4	323.8	233.6	182.4	152.1	133.3	121.8	114.4	111.1	109.1



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	578.0	435.9	318.4	238.9	191.6	163.4	145.2	133.7	126.3	123.0	120.9
115°	530.5	414.0	316.4	247.7	206.6	181.1	162.9	151.4	144.7	140.7	138.0
117.5°	501.8	401.1	317.6	259.3	222.7	197.3	180.6	167.7	161.5	158.2	155.1
120°	486.7	395.1	319.8	267.9	232.9	208.7	191.8	179.1	172.3	168.9	166.9
122.5°	474.3	391.4	323.5	276.0	243.7	220.0	202.1	189.9	182.5	179.2	177.2
125°	458.4	386.4	329.2	288.8	259.2	235.6	217.4	204.7	197.3	193.2	191.8
127.5°	444.4	384.0	335.6	299.3	272.6	249.9	231.7	217.6	210.0	205.0	203.0
130°	436.9	382.4	339.9	306.3	280.7	258.5	240.3	226.2	218.1	212.1	210.0
132.5°	429.9	381.8	343.2	312.7	287.7	266.0	248.4	234.3	224.5	218.0	215.4
135°	420.7	381.0	348.0	321.1	298.2	277.3	259.2	245.0	235.0	227.6	224.8
137.5°	412.8	379.5	351.3	327.3	305.5	285.4	268.5	254.6	243.8	236.5	233.7
140°	407.9	379.0	353.4	330.5	310.3	290.8	274.0	260.5	249.8	243.0	239.6
142.5°	403.6	377.9	355.0	333.7	314.1	295.1	279.4	265.9	256.2	248.9	246.1
145°	397.9	376.3	356.1	337.3	319.1	301.6	286.1	274.7	264.6	258.5	256.5
147.5°	392.2	373.8	356.1	339.4	323.1	307.1	293.9	282.8	274.1	268.2	267.0
150°	388.4	371.6	356.1	339.9	325.8	310.3	298.2	288.8	280.0	274.7	274.0
152.5°	384.1	368.9	354.5	341.0	327.4	314.1	302.5	294.2	286.5	281.1	280.9
155°	377.6	364.2	352.8	341.3	330.5	319.1	309.6	302.2	295.5	291.4	291.4
157.5°	370.4	360.0	350.4	342.0	332.3	323.1	315.8	309.5	303.6	300.3	299.8
160°	365.5	356.8	349.4	342.0	333.9	325.8	319.1	314.4	309.0	306.3	306.3
162.5°	360.7	353.5	347.2	341.4	334.4	327.4	321.8	317.6	313.3	311.2	311.2
165°	354.0	348.7	344.0	339.9	335.2	329.8	325.1	322.4	319.1	317.7	318.4
167.5°	347.8	343.9	340.8	338.9	335.1	331.2	328.2	326.3	323.8	323.1	323.9
170°	344.0	340.6	338.6	337.3	334.6	331.2	329.8	328.5	326.5	325.8	327.2
172.5°	340.2	337.9	337.0	336.7	334.6	331.7	330.9	330.1	328.6	328.5	329.3
175°	335.9	334.6	334.6	335.2	333.9	332.5	331.8	331.8	330.5	331.2	331.8
177.5°	333.0	332.5	333.0	334.2	333.0	332.5	332.5	332.5	332.0	332.5	333.0
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	416.6	417.4	420.1	422.1	424.3	425.6	426.8	427.8	429.1	429.4	434.0
5°	418.4	422.4	429.5	434.6	441.1	448.1	452.9	455.1	461.0	465.7	475.4
7.5°	417.9	426.5	437.0	448.1	459.8	470.7	480.2	491.5	499.4	511.4	523.2
10°	417.4	428.9	442.5	456.5	472.9	488.2	501.9	517.1	529.8	546.4	560.6
12.5°	415.9	429.8	448.8	465.4	485.3	506.4	526.6	546.1	557.3	585.0	598.1
15°	412.4	428.9	452.5	477.8	505.2	530.1	555.8	576.3	609.3	633.6	649.1
17.5°	405.6	428.6	456.7	487.2	520.6	553.4	582.5	613.5	648.6	678.0	709.3
20°	402.3	427.7	458.9	492.7	527.4	564.5	597.5	634.8	673.1	702.1	742.2
22.5°	396.4	425.1	458.7	496.3	533.4	571.8	610.5	648.2	692.4	732.2	770.4
25°	386.8	418.8	453.7	495.7	539.2	577.6	624.1	674.0	720.1	771.3	809.3
27.5°	376.5	410.8	445.7	484.7	531.6	577.3	635.6	692.0	748.4	792.6	820.8
30°	368.7	402.0	438.1	477.4	523.7	578.1	643.3	704.8	759.8	797.7	813.6
32.5°	360.2	393.9	425.9	467.1	516.5	577.6	648.1	712.4	760.4	785.7	782.6
35°	346.8	375.1	406.2	445.9	504.0	574.0	650.9	713.1	742.5	737.1	696.2
37.5°	327.5	351.4	381.9	425.4	489.7	566.6	645.2	691.9	690.0	645.9	586.6
40°	315.6	335.8	365.2	411.0	478.4	561.8	636.5	666.8	641.1	579.5	508.5
42.5°	299.8	318.5	347.9	394.9	466.1	552.1	619.6	628.4	578.2	507.3	442.2
45°	275.4	291.9	322.4	370.9	447.5	530.7	578.5	557.0	489.4	416.2	366.7
47.5°	249.2	266.3	295.6	345.5	420.7	498.7	521.4	475.8	406.4	347.0	301.5
50°	232.6	249.1	277.8	328.1	402.6	472.3	481.8	422.8	359.0	306.9	269.6
52.5°	216.0	231.4	259.7	310.2	381.4	441.9	436.1	376.0	317.4	272.9	243.6
55°	191.1	205.8	232.6	280.0	344.8	392.7	371.7	314.4	265.8	231.3	209.0
57.5°	168.9	183.0	206.1	248.9	305.2	338.2	311.4	263.0	224.5	197.9	181.3
60°	153.9	166.3	188.4	228.1	277.0	302.0	275.6	232.9	200.4	179.1	164.3
62.5°	139.6	150.4	170.8	206.9	249.4	270.4	243.7	207.5	179.9	161.0	148.4
65°	118.0	127.8	145.9	173.9	208.8	222.8	199.8	170.5	149.0	135.0	126.6
67.5°	98.2	106.6	122.2	144.2	170.0	180.1	162.6	139.9	123.7	112.4	105.8
70°	85.1	92.3	104.5	123.6	146.8	154.6	138.2	119.5	107.7	98.7	92.5
72.5°	74.0	79.3	90.4	105.1	124.5	130.7	119.2	102.9	91.9	85.1	80.1
75°	56.4	60.8	68.0	79.8	93.2	96.9	88.3	78.0	70.6	65.8	62.0
77.5°	40.6	43.9	49.1	56.4	65.7	69.0	63.5	56.7	51.2	48.0	45.9
80°	30.7	33.3	37.7	43.7	49.3	51.1	48.0	42.7	38.9	37.1	35.3
82.5°	22.6	24.1	26.8	30.9	34.7	36.9	34.2	31.0	28.9	27.3	26.6
85°	11.5	12.2	13.4	15.1	17.5	18.3	17.2	16.4	15.2	14.2	14.2
87.5°	4.7	5.0	5.9	6.5	7.4	8.3	8.5	8.6	8.8	8.5	8.5
90°	2.7	4.0	6.0	7.4	8.8	10.8	12.8	14.8	16.8	16.2	16.8
92.5°	12.4	18.1	23.3	28.9	38.9	56.6	85.5	113.9	103.5	78.1	56.7
95°	24.9	32.3	43.7	61.2	87.5	144.7	245.0	355.4	399.2	323.8	242.4
97.5°	39.7	45.5	55.4	72.7	101.1	155.8	268.9	452.9	618.6	661.9	604.1
100°	50.5	55.2	64.7	80.8	107.0	154.1	253.7	430.8	637.5	770.1	793.7
102.5°	62.3	66.5	75.4	90.0	114.0	156.3	240.8	398.5	602.4	775.5	856.6
105°	80.1	84.1	92.2	105.0	125.9	162.2	231.5	358.8	541.2	734.4	875.1
107.5°	98.2	102.0	109.9	122.0	141.4	173.2	230.9	333.5	487.1	662.5	822.1
110°	111.1	114.4	121.8	133.3	152.1	182.4	233.6	323.8	456.4	617.3	771.5



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.0	126.3	133.7	145.2	163.4	191.6	238.9	318.4	435.9	578.0	721.3
115°	140.7	144.7	151.4	162.9	181.1	206.6	247.7	316.4	414.0	530.5	655.0
117.5°	158.2	161.5	167.7	180.6	197.3	222.7	259.3	317.6	401.1	501.8	606.9
120°	168.9	172.3	179.1	191.8	208.7	232.9	267.9	319.8	395.1	486.7	581.6
122.5°	179.2	182.5	189.9	202.1	220.0	243.7	276.0	323.5	391.4	474.3	561.7
125°	193.2	197.3	204.7	217.4	235.6	259.2	288.8	329.2	386.4	458.4	535.1
127.5°	205.0	210.0	217.6	231.7	249.9	272.6	299.3	335.6	384.0	444.4	512.0
130°	212.1	218.1	226.2	240.3	258.5	280.7	306.3	339.9	382.4	436.9	497.5
132.5°	218.0	224.5	234.3	248.4	266.0	287.7	312.7	343.2	381.8	429.9	484.0
135°	227.6	235.0	245.0	259.2	277.3	298.2	321.1	348.0	381.0	420.7	465.8
137.5°	236.5	243.8	254.6	268.5	285.4	305.5	327.3	351.3	379.5	412.8	449.3
140°	243.0	249.8	260.5	274.0	290.8	310.3	330.5	353.4	379.0	407.9	439.5
142.5°	248.9	256.2	265.9	279.4	295.1	314.1	333.7	355.0	377.9	403.6	430.4
145°	258.5	264.6	274.7	286.1	301.6	319.1	337.3	356.1	376.3	397.9	419.4
147.5°	268.2	274.1	282.8	293.9	307.1	323.1	339.4	356.1	373.8	392.2	410.4
150°	274.7	280.0	288.8	298.2	310.3	325.8	339.9	356.1	371.6	388.4	403.9
152.5°	281.1	286.5	294.2	302.5	314.1	327.4	341.0	354.5	368.9	384.1	398.0
155°	291.4	295.5	302.2	309.6	319.1	330.5	341.3	352.8	364.2	377.6	389.1
157.5°	300.3	303.6	309.5	315.8	323.1	332.3	342.0	350.4	360.0	370.4	379.6
160°	306.3	309.0	314.4	319.1	325.8	333.9	342.0	349.4	356.8	365.5	374.3
162.5°	311.2	313.3	317.6	321.8	327.4	334.4	341.4	347.2	353.5	360.7	367.8
165°	317.7	319.1	322.4	325.1	329.8	335.2	339.9	344.0	348.7	354.0	359.5
167.5°	323.1	323.8	326.3	328.2	331.2	335.1	338.9	340.8	343.9	347.8	352.1
170°	325.8	326.5	328.5	329.8	331.2	334.6	337.3	338.6	340.6	344.0	347.3
172.5°	328.5	328.6	330.1	330.9	331.7	334.6	336.7	337.0	337.9	340.2	343.0
175°	331.2	330.5	331.8	331.8	332.5	333.9	335.2	334.6	334.6	335.9	337.3
177.5°	332.5	332.0	332.5	332.5	332.5	333.0	334.2	333.0	332.5	333.0	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	435.7	435.8	437.6	438.9	438.2	439.0	439.4
5°	476.0	483.2	487.0	489.8	490.0	490.3	491.8
7.5°	533.1	540.9	546.6	555.2	557.7	560.6	559.8
10°	574.9	586.3	596.2	601.3	607.0	615.2	608.6
12.5°	613.9	634.1	649.1	657.2	662.5	664.1	660.9
15°	678.2	704.6	718.8	718.5	736.5	744.3	732.1
17.5°	737.1	761.6	781.2	791.2	806.2	809.5	808.0
20°	773.3	800.0	815.2	832.4	840.2	847.2	848.4
22.5°	804.3	828.4	844.7	859.0	865.6	868.9	870.9
25°	836.5	855.3	865.1	870.1	871.9	871.5	868.9
27.5°	834.2	835.7	824.8	814.2	804.7	794.0	790.3
30°	812.5	795.7	765.6	748.6	723.5	703.6	711.7
32.5°	755.6	722.0	688.3	651.0	620.2	611.4	602.5
35°	644.9	585.9	551.4	511.3	495.2	479.2	468.1
37.5°	521.7	476.1	435.1	409.0	392.9	382.7	377.3
40°	451.1	410.0	376.3	355.0	342.8	331.4	329.8
42.5°	394.8	356.5	331.2	314.3	302.6	297.6	294.1
45°	323.3	296.7	279.7	267.6	259.8	256.8	252.7
47.5°	273.7	254.9	242.0	233.8	227.9	225.7	225.4
50°	245.9	230.2	220.8	214.4	209.8	209.0	205.8
52.5°	225.1	211.5	204.1	198.5	195.2	193.0	192.0
55°	195.4	186.3	179.7	176.5	173.9	171.7	171.7
57.5°	170.9	163.4	159.0	156.3	155.5	153.9	152.9
60°	155.8	149.5	146.0	143.6	142.0	142.2	140.4
62.5°	141.1	136.9	133.6	131.3	129.3	129.4	129.5
65°	120.1	116.9	114.5	113.7	112.5	111.2	111.5
67.5°	101.9	98.8	96.9	95.6	95.1	94.4	95.6
70°	88.7	86.4	85.1	83.9	83.4	83.6	84.6
72.5°	76.6	75.1	74.1	73.6	72.7	72.8	73.4
75°	60.2	59.0	58.2	57.6	57.3	57.3	57.3
77.5°	44.2	43.9	43.6	42.7	42.7	43.0	43.0
80°	34.9	34.3	34.1	33.7	33.1	32.7	33.7
82.5°	26.1	25.5	25.3	25.2	24.3	24.2	25.1
85°	14.0	13.4	13.6	13.4	13.4	13.3	13.3
87.5°	8.4	8.4	8.5	8.6	8.5	8.5	8.7
90°	17.5	18.2	19.5	18.9	19.5	20.2	19.5
92.5°	44.9	39.7	36.2	35.0	33.0	33.7	32.5
95°	164.3	128.5	104.4	91.5	85.5	80.8	78.1
97.5°	483.9	397.0	316.5	266.8	236.5	218.3	212.6
100°	739.1	660.4	564.7	496.8	447.6	421.4	422.1
102.5°	854.9	809.0	748.4	695.5	656.6	634.6	619.1
105°	942.4	955.2	937.7	906.7	881.1	859.6	856.3
107.5°	931.3	990.3	1014.3	1014.9	1006.3	998.9	992.7
110°	895.3	980.1	1027.3	1046.0	1051.5	1050.1	1048.8



TEST NUMBER: P331885-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	847.9	943.0	1003.5	1038.0	1054.7	1059.8	1060.1
115°	772.1	871.1	944.4	994.9	1024.5	1038.0	1041.4
117.5°	708.0	796.9	871.3	923.9	957.9	977.2	981.9
120°	672.4	753.3	821.2	874.4	912.1	928.2	932.3
122.5°	643.9	718.8	782.0	829.1	863.1	880.9	886.0
125°	608.6	673.1	727.0	770.1	799.7	816.5	821.2
127.5°	577.4	635.8	684.8	723.1	748.4	763.6	767.9
130°	558.0	612.6	658.3	694.1	718.2	732.4	737.8
132.5°	539.8	590.5	634.1	667.6	691.9	704.4	708.2
135°	513.6	557.3	595.7	628.7	648.9	661.0	665.7
137.5°	488.4	526.2	559.4	587.1	607.6	617.9	621.0
140°	473.9	506.2	535.1	560.8	579.5	590.4	589.7
142.5°	459.9	487.9	513.1	534.9	551.6	561.3	560.6
145°	441.6	463.1	482.7	499.5	513.6	519.0	520.3
147.5°	428.0	445.4	459.3	472.0	481.6	486.7	487.2
150°	419.4	433.5	446.3	456.4	463.8	467.9	467.9
152.5°	411.3	423.8	434.5	442.4	449.3	451.7	451.7
155°	399.8	409.9	418.0	424.0	429.5	430.8	431.4
157.5°	388.7	396.5	402.8	408.0	412.1	413.2	413.0
160°	381.7	388.4	393.1	397.9	401.8	401.8	401.2
162.5°	374.1	380.3	384.5	387.6	391.1	391.1	390.5
165°	363.5	368.2	371.6	374.3	376.9	376.3	376.3
167.5°	355.2	358.0	360.4	361.6	363.5	362.8	362.8
170°	349.4	352.1	353.4	354.0	355.4	354.7	354.7
172.5°	344.5	346.6	347.5	347.6	349.0	347.8	347.2
175°	337.9	339.2	339.2	339.2	339.9	339.2	338.6
177.5°	334.2	334.7	334.7	334.2	334.7	333.6	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5

(END OF REPORT)