

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831600

Luminaire Tested: S123DIP-S775D1025U930-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831600
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U930-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6233.0 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 51.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831600
CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P831600

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46				
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	46	40				
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39	34				
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30				
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26				
5	69	58	50	44	63	54	47	42	46	41	37	38	34	31	31	29	26	23				
6	64	52	45	39	59	49	42	37	42	36	32	35	31	28	29	26	24	21				
7	59	47	40	34	54	44	37	33	38	33	29	32	28	25	27	24	21	19				
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	19	17				
9	52	40	33	28	47	37	31	26	32	27	23	27	23	21	23	20	18	16				
10	48	37	30	25	45	34	28	24	30	25	21	25	22	19	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	19362	19362	19362	19362	19362
5°	24487	23112	19535	15743	14467
10°	24725	25473	19406	12550	10966
15°	18622	23650	19274	10628	9274
20°	12975	19137	19027	9294	8424
25°	9894	14718	18608	8551	7902
30°	8559	11692	17938	8025	7480
35°	7941	9872	17165	7645	7184
40°	7519	8855	16080	7284	7085
45°	7269	8196	14702	7001	7039
50°	7142	7675	13070	6745	7003
55°	6876	7293	11466	6501	7034
60°	6631	6882	9883	6271	6919
65°	6230	6495	8525	6026	6783
70°	5753	6002	7251	5621	6382
75°	5207	5382	6213	5224	5831
80°	4296	4711	4916	4556	4916
85°	3396	3816	3606	3866	3915

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 16786 cd/sqm



TEST NUMBER: P831600

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.1	2.7
10°-20°	423.1	6.8
20°-30°	500.9	8.0
30°-40°	503.7	8.1
40°-50°	462.1	7.4
50°-60°	381.4	6.1
60°-70°	269.8	4.3
70°-80°	144.0	2.3
80°-90°	38.7	0.6
90°-100°	38.6	0.6
100°-110°	186.7	3.0
110°-120°	457.6	7.3
120°-130°	581.0	9.3
130°-140°	620.6	10.0
140°-150°	580.4	9.3
150°-160°	468.1	7.5
160°-170°	302.1	4.8
170°-180°	104.1	1.7
0°-30°	1094.1	17.6
0°-40°	1597.8	25.6
0°-60°	2441.3	39.2
0°-90°	2893.9	46.4
90°-120°	682.9	11.0
90°-150°	2464.8	39.5
90°-180°	3339.0	53.6
0°-180°	6233.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1799	1799	1799	1799	1799	
5°	2266	2139	1808	1457	1339	216
15°	1671	2122	1730	954	832	462
25°	833	1239	1567	720	665	393
35°	604	751	1306	582	547	380
45°	478	538	966	460	462	370
55°	366	389	611	346	375	328
65°	245	255	335	237	266	243
75°	125	129	149	126	140	132
85°	28	31	29	31	32	31
90°	24	20	1	20	24	12
95°	31	25	50	25	31	26
105°	36	178	242	178	36	75
115°	478	467	455	467	478	450
125°	654	651	641	651	654	585
135°	806	806	798	806	806	622
145°	930	928	921	928	930	581
155°	1013	1014	1015	1014	1013	467
165°	1068	1067	1070	1067	1068	302
175°	1091	1092	1095	1092	1091	104
180°	1095	1095	1095	1095	1095	



TEST NUMBER: P831600

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8
2.5°	2027.6	2025.5	2023.4	2012.9	2002.5	1997.5	1992.5	1977.5	1962.4	1945.7	1929.1
5°	2266.3	2272.1	2278.0	2271.3	2264.6	2244.2	2223.7	2196.6	2169.5	2139.0	2108.5
7.5°	2376.5	2379.8	2383.1	2379.0	2374.8	2369.4	2363.9	2339.7	2315.5	2284.2	2252.9
10°	2262.1	2269.6	2277.1	2293.4	2309.7	2328.1	2346.4	2343.1	2339.7	2330.6	2321.4
12.5°	2010.9	2020.0	2029.2	2061.8	2094.3	2136.1	2177.8	2213.7	2249.6	2274.6	2299.7
15°	1671.1	1696.6	1722.0	1751.7	1781.3	1842.7	1904.0	1979.6	2055.1	2122.3	2189.5
17.5°	1376.5	1386.1	1395.7	1427.4	1459.1	1536.3	1613.5	1700.8	1788.0	1899.4	2010.9
20°	1132.7	1141.5	1150.3	1192.0	1233.7	1294.2	1354.8	1452.8	1550.9	1670.7	1790.5
22.5°	951.6	965.4	979.1	1002.5	1025.9	1083.9	1141.9	1229.1	1316.4	1448.7	1581.0
25°	833.1	843.1	853.1	867.3	881.5	927.8	974.1	1045.9	1117.7	1239.2	1360.6
27.5°	752.1	756.3	760.4	774.6	788.8	818.9	848.9	910.7	972.5	1075.5	1178.6
30°	688.6	691.6	694.5	707.0	719.5	740.0	760.4	805.1	849.8	940.7	1031.7
32.5°	644.4	646.5	648.6	658.2	667.8	682.4	697.0	729.6	762.1	837.2	912.4
35°	604.3	605.6	606.8	613.9	621.0	631.9	642.7	667.4	692.0	751.3	810.5
37.5°	569.3	571.0	572.6	576.8	581.0	590.6	600.2	619.8	639.4	684.9	730.4
40°	535.1	538.0	540.9	543.8	546.7	554.7	562.6	577.6	592.7	630.2	667.8
42.5°	505.8	508.8	511.7	512.9	514.2	518.8	523.4	537.1	550.9	578.9	606.8
45°	477.5	478.7	480.0	481.2	482.5	486.2	490.0	502.1	514.2	538.4	562.6
47.5°	451.6	451.6	451.6	452.4	453.3	456.6	459.9	468.7	477.5	496.2	515.0
50°	426.5	426.5	426.5	425.3	424.0	426.1	428.2	434.9	441.6	458.3	475.0
52.5°	396.5	396.5	396.5	396.9	397.3	397.3	397.3	403.2	409.0	424.0	439.1
55°	366.4	368.1	369.8	368.5	367.3	368.1	368.9	372.7	376.5	388.6	400.7
57.5°	336.4	337.2	338.1	337.6	337.2	337.6	338.1	341.4	344.7	353.9	363.1
60°	308.0	308.0	308.0	307.2	306.3	307.2	308.0	309.7	311.4	319.7	328.0
62.5°	276.3	276.7	277.1	277.5	278.0	277.1	276.3	278.4	280.5	286.7	293.0
65°	244.6	245.0	245.4	246.7	247.9	247.1	246.2	248.3	250.4	255.0	259.6
67.5°	216.2	215.4	214.5	214.9	215.4	216.6	217.9	218.3	218.7	223.7	228.7
70°	182.8	183.6	184.5	184.1	183.6	184.1	184.5	185.7	187.0	190.7	194.5
72.5°	152.8	153.2	153.6	153.6	153.6	154.4	155.3	156.5	157.8	159.9	161.9
75°	125.2	125.2	125.2	126.0	126.9	127.3	127.7	127.7	127.7	129.4	131.1
77.5°	95.2	97.2	99.3	98.9	98.5	99.3	100.2	101.4	102.7	103.5	104.3
80°	69.3	69.3	69.3	69.7	70.1	71.4	72.6	73.5	74.3	76.0	77.6
82.5°	44.2	44.7	45.1	46.3	47.6	48.4	49.2	50.5	51.8	51.8	51.8
85°	27.5	26.7	25.9	26.7	27.5	28.4	29.2	29.6	30.1	30.9	31.7
87.5°	13.4	13.4	13.4	13.4	13.4	13.8	14.2	14.2	14.2	14.2	14.2
90°	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0	20.3	19.5	17.2
92.5°	27.7	27.5	27.3	27.1	26.9	26.2	25.0	23.7	22.4	21.2	19.5
95°	30.9	30.9	30.9	30.9	30.9	30.3	29.0	27.8	26.5	25.2	23.2
97.5°	33.4	33.2	33.0	32.8	32.6	31.8	30.4	28.9	27.5	26.0	35.3
100°	34.2	34.0	33.8	33.6	33.5	32.6	31.2	29.7	28.3	26.9	55.1
102.5°	35.0	34.6	34.3	33.9	33.5	36.3	42.3	48.3	54.3	60.2	91.7
105°	35.8	35.4	35.1	34.7	34.4	50.2	82.2	114.2	146.2	178.2	194.5
107.5°	84.6	108.3	132.0	155.7	179.4	205.2	233.0	260.9	288.7	316.6	313.9
110°	223.8	249.7	275.5	301.4	327.2	343.1	349.1	355.1	361.1	367.0	365.0



TEST NUMBER: P831600

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	424.0	424.3	424.7	425.1	425.4	424.8	423.2	421.5	419.9	418.3	416.3
115°	478.5	477.8	477.1	476.3	475.6	474.3	472.5	470.7	468.9	467.1	465.5
117.5°	522.5	522.3	522.1	521.9	521.7	520.9	519.5	518.0	516.6	515.1	514.2
120°	568.0	568.0	568.0	568.0	568.0	567.3	565.9	564.4	563.0	561.5	561.0
122.5°	612.8	612.6	612.4	612.2	612.1	611.5	610.6	609.7	608.8	607.9	607.2
125°	654.3	653.9	653.6	653.2	652.8	652.5	652.1	651.8	651.4	651.0	650.3
127.5°	695.0	695.3	695.7	696.1	696.4	696.3	695.8	695.2	694.7	694.2	693.3
130°	734.0	734.4	734.8	735.1	735.5	735.3	734.6	733.9	733.1	732.4	731.7
132.5°	769.8	770.4	770.9	771.5	772.0	771.9	771.2	770.5	769.8	769.0	768.5
135°	806.5	807.0	807.5	808.1	808.6	808.6	808.1	807.5	807.0	806.5	805.7
137.5°	841.5	841.8	842.2	842.5	842.9	842.6	841.7	840.8	839.9	839.0	838.7
140°	872.4	872.7	873.1	873.5	873.8	873.6	872.9	872.2	871.5	870.8	870.2
142.5°	900.9	901.4	901.9	902.5	903.0	903.0	902.5	901.9	901.4	900.9	900.3
145°	930.2	930.2	930.2	930.2	930.2	930.0	929.6	929.3	928.9	928.5	928.2
147.5°	951.3	952.2	953.1	954.0	954.9	955.2	954.8	954.5	954.1	953.8	953.4
150°	975.7	976.3	976.8	977.4	977.9	978.0	977.6	977.3	976.9	976.5	976.2
152.5°	995.3	996.2	997.1	998.0	998.9	999.0	998.2	997.5	996.8	996.1	995.9
155°	1013.2	1014.3	1015.3	1016.4	1017.5	1017.6	1016.7	1015.8	1014.9	1014.0	1013.8
157.5°	1028.6	1030.1	1031.5	1033.0	1034.4	1034.6	1033.5	1032.4	1031.3	1030.3	1030.4
160°	1043.3	1044.5	1045.8	1047.1	1048.3	1048.4	1047.3	1046.3	1045.2	1044.1	1044.3
162.5°	1057.1	1058.2	1059.3	1060.4	1061.4	1061.4	1060.1	1058.8	1057.6	1056.3	1056.5
165°	1067.7	1069.0	1070.2	1071.5	1072.8	1072.7	1071.2	1069.8	1068.3	1066.9	1067.1
167.5°	1075.8	1077.3	1078.7	1080.2	1081.6	1081.6	1080.2	1078.7	1077.3	1075.8	1075.8
170°	1083.2	1084.6	1086.0	1087.5	1088.9	1088.9	1087.5	1086.0	1084.6	1083.2	1083.2
172.5°	1087.2	1088.8	1090.5	1092.1	1093.7	1093.8	1092.4	1090.9	1089.5	1088.0	1087.9
175°	1091.3	1092.7	1094.2	1095.6	1097.1	1097.2	1095.9	1094.6	1093.4	1092.1	1091.9
177.5°	1092.1	1093.9	1095.7	1097.5	1099.3	1099.5	1098.1	1096.6	1095.2	1093.7	1093.5
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P831600

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8
2.5°	1924.0	1919.0	1900.7	1882.3	1861.4	1840.6	1825.1	1809.7	1786.7	1763.8	1745.0
5°	2085.1	2061.8	2023.0	1984.1	1931.6	1879.0	1843.5	1808.0	1760.4	1712.9	1674.9
7.5°	2212.9	2172.8	2118.5	2064.3	1995.4	1926.5	1861.4	1796.3	1723.7	1651.1	1591.8
10°	2294.2	2267.1	2204.5	2141.9	2049.7	1957.4	1866.4	1775.5	1682.0	1588.5	1510.0
12.5°	2302.2	2304.7	2247.1	2189.5	2085.1	1980.8	1870.2	1759.6	1641.9	1524.2	1432.8
15°	2232.5	2275.5	2243.7	2212.0	2106.8	2001.7	1865.6	1729.6	1593.9	1458.3	1352.7
17.5°	2103.1	2195.3	2199.9	2204.5	2099.3	1994.2	1843.5	1692.8	1539.2	1385.6	1274.6
20°	1926.5	2062.6	2109.4	2156.1	2070.5	1985.0	1823.0	1661.1	1489.2	1317.2	1200.8
22.5°	1746.2	1911.5	1997.1	2082.6	2019.2	1955.8	1783.4	1611.0	1429.5	1247.9	1129.8
25°	1540.9	1721.2	1852.7	1984.1	1945.3	1906.5	1736.6	1566.8	1373.5	1180.3	1059.7
27.5°	1361.9	1545.1	1703.7	1862.3	1853.9	1845.6	1677.0	1508.4	1310.5	1112.7	996.2
30°	1202.4	1373.1	1550.5	1727.9	1748.3	1768.8	1606.0	1443.2	1245.0	1046.7	934.5
32.5°	1061.4	1210.4	1400.7	1591.0	1631.1	1671.1	1524.2	1377.3	1181.1	985.0	876.9
35°	945.7	1081.0	1271.3	1461.6	1511.7	1561.8	1434.1	1306.3	1115.2	924.0	821.0
37.5°	843.5	956.6	1142.3	1328.1	1389.4	1450.8	1336.4	1222.0	1043.0	863.9	769.2
40°	758.8	849.8	1020.5	1191.2	1262.1	1333.1	1238.7	1144.4	974.5	804.7	717.4
42.5°	687.8	768.8	923.6	1078.5	1146.5	1214.5	1134.8	1055.1	904.0	752.9	673.2
45°	627.3	692.0	832.6	973.3	1038.0	1102.7	1034.2	965.8	832.6	699.5	625.2
47.5°	570.5	626.0	746.2	866.4	924.0	981.6	928.2	874.8	762.1	649.4	582.2
50°	519.6	564.3	669.5	774.6	824.7	874.8	827.6	780.5	687.8	595.2	536.7
52.5°	475.4	511.7	599.8	687.8	730.8	773.8	733.3	692.8	619.4	545.9	495.0
55°	431.6	462.4	538.8	615.2	644.4	673.6	642.3	611.0	551.8	492.5	449.5
57.5°	390.7	418.2	480.8	543.4	565.9	588.5	560.1	531.7	487.1	442.4	406.5
60°	350.6	373.1	425.3	477.5	491.2	505.0	482.1	459.1	427.8	396.5	364.4
62.5°	313.4	333.9	372.7	411.5	420.7	429.9	412.4	394.8	371.0	347.2	322.2
65°	275.0	290.5	322.2	353.9	359.8	365.6	350.2	334.7	316.8	298.8	280.5
67.5°	239.6	250.4	276.3	302.2	302.6	303.0	290.5	278.0	267.9	257.9	243.3
70°	204.9	215.4	232.5	249.6	250.0	250.4	240.4	230.4	222.9	215.4	204.5
72.5°	169.4	177.0	189.9	202.8	202.0	201.2	194.9	188.6	182.8	177.0	169.0
75°	137.3	143.6	152.3	161.1	158.6	156.1	152.8	149.4	144.4	139.4	134.4
77.5°	108.1	111.9	116.9	121.9	120.2	118.5	115.6	112.7	108.9	105.2	103.1
80°	79.3	81.0	84.3	87.6	86.8	86.0	82.6	79.3	78.5	77.6	74.7
82.5°	53.8	55.9	56.8	57.6	57.2	56.8	54.3	51.8	50.9	50.1	49.7
85°	32.1	32.6	33.0	33.4	32.1	30.9	30.1	29.2	29.2	29.2	28.8
87.5°	14.6	15.0	15.0	15.0	14.6	14.2	13.4	12.5	12.9	13.4	13.4
90°	14.8	12.5	10.1	8.0	6.2	4.4	2.6	0.8	2.6	4.4	6.2
92.5°	17.9	16.3	14.6	14.4	15.5	16.5	17.6	18.7	17.6	16.5	15.5
95°	21.2	19.3	17.3	20.0	27.4	34.8	42.2	49.6	42.2	34.8	27.4
97.5°	44.5	53.7	62.9	70.1	75.1	80.2	85.3	90.3	85.3	80.2	75.1
100°	83.3	111.5	139.7	152.0	148.4	144.8	141.1	137.5	141.1	144.8	148.4
102.5°	123.2	154.6	186.1	200.6	198.3	195.9	193.6	191.2	193.6	195.9	198.3
105°	210.8	227.0	243.3	250.5	248.5	246.5	244.5	242.5	244.5	246.5	248.5
107.5°	311.1	308.4	305.7	303.5	301.9	300.3	298.7	297.0	298.7	300.3	301.9
110°	363.0	361.1	359.1	357.3	355.9	354.4	353.0	351.6	353.0	354.4	355.9



TEST NUMBER: P831600

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	414.3	412.3	410.3	408.7	407.4	406.2	404.9	403.6	404.9	406.2	407.4
115°	463.9	462.2	460.6	459.2	458.2	457.1	456.0	454.9	456.0	457.1	458.2
117.5°	513.3	512.4	511.5	510.4	509.2	507.9	506.6	505.4	506.6	507.9	509.2
120°	560.4	559.9	559.3	558.3	556.6	555.0	553.4	551.7	553.4	555.0	556.6
122.5°	606.5	605.7	605.0	604.0	602.7	601.5	600.2	598.9	600.2	601.5	602.7
125°	649.6	648.9	648.1	647.1	645.6	644.2	642.7	641.3	642.7	644.2	645.6
127.5°	692.4	691.4	690.5	689.4	687.9	686.5	685.0	683.6	685.0	686.5	687.9
130°	731.0	730.2	729.5	728.4	727.0	725.5	724.1	722.6	724.1	725.5	727.0
132.5°	767.9	767.4	766.9	765.9	764.4	763.0	761.5	760.1	761.5	763.0	764.4
135°	805.0	804.3	803.6	802.7	801.6	800.5	799.4	798.3	799.4	800.5	801.6
137.5°	838.3	837.9	837.6	836.7	835.2	833.8	832.3	830.9	832.3	833.8	835.2
140°	869.7	869.1	868.6	867.8	866.7	865.6	864.5	863.4	864.5	865.6	866.7
142.5°	899.8	899.2	898.7	897.9	896.8	895.7	894.6	893.5	894.6	895.7	896.8
145°	927.8	927.4	927.1	926.3	925.0	923.7	922.5	921.2	922.5	923.7	925.0
147.5°	953.0	952.7	952.3	951.7	950.8	949.9	949.0	948.1	949.0	949.9	950.8
150°	975.8	975.5	975.1	974.6	974.1	973.6	973.0	972.5	973.0	973.6	974.1
152.5°	995.7	995.5	995.4	995.2	995.0	994.8	994.6	994.4	994.6	994.8	995.0
155°	1013.6	1013.4	1013.3	1013.3	1013.7	1014.1	1014.4	1014.8	1014.4	1014.1	1013.7
157.5°	1030.6	1030.8	1031.0	1031.1	1031.1	1031.1	1031.1	1031.1	1031.1	1031.1	1031.1
160°	1044.5	1044.6	1044.8	1045.0	1045.2	1045.4	1045.5	1045.7	1045.5	1045.4	1045.2
162.5°	1056.7	1056.8	1057.0	1057.4	1057.9	1058.5	1059.0	1059.6	1059.0	1058.5	1057.9
165°	1067.2	1067.4	1067.6	1068.0	1068.5	1069.0	1069.6	1070.1	1069.6	1069.0	1068.5
167.5°	1075.8	1075.8	1075.8	1076.2	1076.9	1077.6	1078.4	1079.1	1078.4	1077.6	1076.9
170°	1083.2	1083.2	1083.2	1083.5	1084.2	1085.0	1085.7	1086.4	1085.7	1085.0	1084.2
172.5°	1087.7	1087.5	1087.3	1087.7	1088.6	1089.5	1090.4	1091.3	1090.4	1089.5	1088.6
175°	1091.7	1091.6	1091.4	1091.7	1092.6	1093.5	1094.5	1095.4	1094.5	1093.5	1092.6
177.5°	1093.4	1093.2	1093.0	1093.4	1094.3	1095.2	1096.1	1097.0	1096.1	1095.2	1094.3
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P831600

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8	1798.8
2.5°	1726.2	1709.9	1693.7	1681.1	1668.6	1647.3	1626.0	1621.0	1616.0	1608.9	1601.8
5°	1636.9	1596.8	1556.8	1520.9	1485.0	1457.0	1429.1	1410.7	1392.3	1379.0	1365.6
7.5°	1532.6	1472.5	1412.4	1369.8	1327.2	1286.7	1246.2	1233.3	1220.4	1202.8	1185.3
10°	1431.6	1365.2	1298.8	1243.3	1187.8	1148.2	1108.5	1092.7	1076.8	1054.7	1032.6
12.5°	1341.4	1268.8	1196.2	1140.2	1084.3	1045.9	1007.5	984.6	961.6	949.1	936.6
15°	1247.1	1169.5	1091.8	1040.1	988.3	953.7	919.0	899.0	879.0	866.9	854.8
17.5°	1163.6	1086.8	1010.0	960.4	910.7	879.0	847.2	829.7	812.2	803.0	793.8
20°	1084.3	1009.2	934.1	885.6	837.2	811.4	785.5	774.2	762.9	755.4	747.9
22.5°	1011.7	937.8	863.9	822.6	781.3	760.4	739.6	731.6	723.7	717.4	711.2
25°	939.1	873.1	807.2	772.1	737.1	720.0	702.8	694.9	687.0	680.7	674.5
27.5°	879.8	816.8	753.8	723.7	693.7	680.3	666.9	660.7	654.4	648.6	642.7
30°	822.2	765.9	709.5	683.6	657.8	645.7	633.6	627.3	621.0	615.6	610.2
32.5°	768.8	720.4	672.0	648.2	624.4	614.4	604.3	596.8	589.3	585.1	581.0
35°	717.9	674.5	631.1	611.4	591.8	581.8	571.8	565.5	559.3	555.9	552.6
37.5°	674.5	635.6	596.8	578.0	559.3	549.7	540.1	534.6	529.2	528.0	526.7
40°	630.2	596.8	563.4	545.1	526.7	518.4	510.0	506.7	503.3	502.5	501.7
42.5°	593.5	560.9	528.4	511.7	495.0	487.9	480.8	479.1	477.5	478.7	480.0
45°	550.9	523.8	496.7	481.2	465.8	459.9	454.1	452.8	451.6	454.1	456.6
47.5°	515.0	490.0	464.9	450.3	435.7	431.6	427.4	427.0	426.5	429.9	433.2
50°	478.3	454.1	429.9	418.2	406.5	402.8	399.0	400.3	401.5	406.9	412.4
52.5°	444.1	421.5	399.0	388.1	377.3	374.8	372.3	375.2	378.1	384.0	389.8
55°	406.5	386.1	365.6	357.3	348.9	346.4	343.9	349.8	355.6	361.0	366.4
57.5°	370.6	352.7	334.7	327.2	319.7	319.3	318.9	324.3	329.7	335.6	341.4
60°	332.2	317.2	302.2	296.3	290.5	291.3	292.2	298.4	304.7	309.3	313.9
62.5°	297.2	284.6	272.1	266.7	261.3	263.4	265.4	271.7	278.0	283.4	288.8
65°	262.1	251.7	241.2	237.5	233.7	236.6	239.6	245.0	250.4	254.2	257.9
67.5°	228.7	220.0	211.2	208.3	205.3	208.3	211.2	216.6	222.0	225.8	229.5
70°	193.7	186.6	179.5	177.4	175.3	178.6	182.0	186.6	191.2	194.9	198.7
72.5°	161.1	155.7	150.3	149.8	149.4	152.3	155.3	159.9	164.4	166.9	169.4
75°	129.4	126.5	123.5	123.1	122.7	125.6	128.5	131.1	133.6	135.6	137.7
77.5°	101.0	98.5	96.0	96.4	96.8	98.9	101.0	103.5	106.0	107.3	108.5
80°	71.8	71.0	70.1	71.0	71.8	73.5	75.1	76.8	78.5	79.3	80.1
82.5°	49.2	48.4	47.6	48.8	50.1	51.3	52.6	53.8	55.1	55.5	55.9
85°	28.4	29.6	30.9	30.9	30.9	31.3	31.7	32.1	32.6	32.1	31.7
87.5°	13.4	13.8	14.2	14.2	14.2	14.6	15.0	15.0	15.0	14.6	14.2
90°	8.0	10.1	12.5	14.8	17.2	19.5	20.3	21.0	21.7	22.4	23.0
92.5°	14.4	14.6	16.3	17.9	19.5	21.2	22.4	23.7	25.0	26.2	26.9
95°	20.0	17.3	19.3	21.2	23.2	25.2	26.5	27.8	29.0	30.3	30.9
97.5°	70.1	62.9	53.7	44.5	35.3	26.0	27.5	28.9	30.4	31.8	32.6
100°	152.0	139.7	111.5	83.3	55.1	26.9	28.3	29.7	31.2	32.6	33.5
102.5°	200.6	186.1	154.6	123.2	91.7	60.2	54.3	48.3	42.3	36.3	33.5
105°	250.5	243.3	227.0	210.8	194.5	178.2	146.2	114.2	82.2	50.2	34.4
107.5°	303.5	305.7	308.4	311.1	313.9	316.6	288.7	260.9	233.0	205.2	179.4
110°	357.3	359.1	361.1	363.0	365.0	367.0	361.1	355.1	349.1	343.1	327.2



TEST NUMBER: P831600

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	408.7	410.3	412.3	414.3	416.3	418.3	419.9	421.5	423.2	424.8	425.4
115°	459.2	460.6	462.2	463.9	465.5	467.1	468.9	470.7	472.5	474.3	475.6
117.5°	510.4	511.5	512.4	513.3	514.2	515.1	516.6	518.0	519.5	520.9	521.7
120°	558.3	559.3	559.9	560.4	561.0	561.5	563.0	564.4	565.9	567.3	568.0
122.5°	604.0	605.0	605.7	606.5	607.2	607.9	608.8	609.7	610.6	611.5	612.1
125°	647.1	648.1	648.9	649.6	650.3	651.0	651.4	651.8	652.1	652.5	652.8
127.5°	689.4	690.5	691.4	692.4	693.3	694.2	694.7	695.2	695.8	696.3	696.4
130°	728.4	729.5	730.2	731.0	731.7	732.4	733.1	733.9	734.6	735.3	735.5
132.5°	765.9	766.9	767.4	767.9	768.5	769.0	769.8	770.5	771.2	771.9	772.0
135°	802.7	803.6	804.3	805.0	805.7	806.5	807.0	807.5	808.1	808.6	808.6
137.5°	836.7	837.6	837.9	838.3	838.7	839.0	839.9	840.8	841.7	842.6	842.9
140°	867.8	868.6	869.1	869.7	870.2	870.8	871.5	872.2	872.9	873.6	873.8
142.5°	897.9	898.7	899.2	899.8	900.3	900.9	901.4	901.9	902.5	903.0	903.0
145°	926.3	927.1	927.4	927.8	928.2	928.5	928.9	929.3	929.6	930.0	930.2
147.5°	951.7	952.3	952.7	953.0	953.4	953.8	954.1	954.5	954.8	955.2	954.9
150°	974.6	975.1	975.5	975.8	976.2	976.5	976.9	977.3	977.6	978.0	977.9
152.5°	995.2	995.4	995.5	995.7	995.9	996.1	996.8	997.5	998.2	999.0	998.9
155°	1013.3	1013.3	1013.4	1013.6	1013.8	1014.0	1014.9	1015.8	1016.7	1017.6	1017.5
157.5°	1031.1	1031.0	1030.8	1030.6	1030.4	1030.3	1031.3	1032.4	1033.5	1034.6	1034.4
160°	1045.0	1044.8	1044.6	1044.5	1044.3	1044.1	1045.2	1046.3	1047.3	1048.4	1048.3
162.5°	1057.4	1057.0	1056.8	1056.7	1056.5	1056.3	1057.6	1058.8	1060.1	1061.4	1061.4
165°	1068.0	1067.6	1067.4	1067.2	1067.1	1066.9	1068.3	1069.8	1071.2	1072.7	1072.8
167.5°	1076.2	1075.8	1075.8	1075.8	1075.8	1075.8	1077.3	1078.7	1080.2	1081.6	1081.6
170°	1083.5	1083.2	1083.2	1083.2	1083.2	1083.2	1084.6	1086.0	1087.5	1088.9	1088.9
172.5°	1087.7	1087.3	1087.5	1087.7	1087.9	1088.0	1089.5	1090.9	1092.4	1093.8	1093.7
175°	1091.7	1091.4	1091.6	1091.7	1091.9	1092.1	1093.4	1094.6	1095.9	1097.2	1097.1
177.5°	1093.4	1093.0	1093.2	1093.4	1093.5	1093.7	1095.2	1096.6	1098.1	1099.5	1099.3
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P831600

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1798.8	1798.8	1798.8	1798.8
2.5°	1598.9	1596.0	1584.3	1572.6
5°	1355.6	1345.6	1342.2	1338.9
7.5°	1184.5	1183.6	1166.1	1148.6
10°	1033.8	1035.1	1019.2	1003.3
12.5°	926.1	915.7	914.4	913.2
15°	845.2	835.6	833.9	832.2
17.5°	788.0	782.1	780.5	778.8
20°	744.6	741.2	738.3	735.4
22.5°	707.0	702.8	700.3	697.8
25°	670.7	666.9	666.1	665.3
27.5°	638.1	633.6	633.6	633.6
30°	607.3	604.3	603.1	601.8
32.5°	578.5	576.0	576.0	576.0
35°	551.3	550.1	548.4	546.7
37.5°	526.7	526.7	525.9	525.0
40°	502.9	504.2	504.2	504.2
42.5°	481.2	482.5	482.5	482.5
45°	458.7	460.8	461.6	462.4
47.5°	436.6	439.9	440.7	441.6
50°	414.9	417.4	417.8	418.2
52.5°	392.7	395.7	397.7	399.8
55°	369.4	372.3	373.5	374.8
57.5°	344.3	347.2	347.7	348.1
60°	316.8	319.7	320.5	321.4
62.5°	290.5	292.2	293.0	293.8
65°	260.4	262.9	264.6	266.3
67.5°	231.6	233.7	233.7	233.7
70°	199.5	200.3	201.6	202.8
72.5°	169.9	170.3	170.3	170.3
75°	138.6	139.4	139.8	140.2
77.5°	108.9	109.3	109.3	109.3
80°	79.7	79.3	79.3	79.3
82.5°	54.7	53.4	53.4	53.4
85°	31.3	30.9	31.3	31.7
87.5°	14.2	14.2	14.2	14.2
90°	23.3	23.7	24.1	24.4
92.5°	27.1	27.3	27.5	27.7
95°	30.9	30.9	30.9	30.9
97.5°	32.8	33.0	33.2	33.4
100°	33.6	33.8	34.0	34.2
102.5°	33.9	34.3	34.6	35.0
105°	34.7	35.1	35.4	35.8
107.5°	155.7	132.0	108.3	84.6
110°	301.4	275.5	249.7	223.8



TEST NUMBER: P831600

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	425.1	424.7	424.3	424.0
115°	476.3	477.1	477.8	478.5
117.5°	521.9	522.1	522.3	522.5
120°	568.0	568.0	568.0	568.0
122.5°	612.2	612.4	612.6	612.8
125°	653.2	653.6	653.9	654.3
127.5°	696.1	695.7	695.3	695.0
130°	735.1	734.8	734.4	734.0
132.5°	771.5	770.9	770.4	769.8
135°	808.1	807.5	807.0	806.5
137.5°	842.5	842.2	841.8	841.5
140°	873.5	873.1	872.7	872.4
142.5°	902.5	901.9	901.4	900.9
145°	930.2	930.2	930.2	930.2
147.5°	954.0	953.1	952.2	951.3
150°	977.4	976.8	976.3	975.7
152.5°	998.0	997.1	996.2	995.3
155°	1016.4	1015.3	1014.3	1013.2
157.5°	1033.0	1031.5	1030.1	1028.6
160°	1047.1	1045.8	1044.5	1043.3
162.5°	1060.4	1059.3	1058.2	1057.1
165°	1071.5	1070.2	1069.0	1067.7
167.5°	1080.2	1078.7	1077.3	1075.8
170°	1087.5	1086.0	1084.6	1083.2
172.5°	1092.1	1090.5	1088.8	1087.2
175°	1095.6	1094.2	1092.7	1091.3
177.5°	1097.5	1095.7	1093.9	1092.1
180°	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P831600

CATALOG NUMBER: S123DIP-S775D1025U930-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.52	14.32	14.51	15.32	16.64	15.76	16.55	16.75	17.55	18.88
	3H	15.16	15.88	16.17	16.89	18.23	17.18	17.89	18.18	18.90	20.25
	4H	15.74	16.41	16.75	17.43	18.78	17.62	18.30	18.64	19.31	20.67
	6H	16.10	16.73	17.13	17.74	19.11	17.90	18.52	18.92	19.54	20.90
	8H	16.20	16.79	17.23	17.82	19.19	17.96	18.55	18.99	19.58	20.94
	12H	16.24	16.80	17.28	17.83	19.22	17.97	18.54	19.01	19.56	20.95
4H	2H	14.09	14.76	15.11	15.78	17.13	15.91	16.59	16.94	17.60	18.95
	3H	15.91	16.47	16.94	17.51	18.88	17.53	18.09	18.56	19.13	20.50
	4H	16.61	17.12	17.64	18.15	19.54	18.11	18.62	19.15	19.66	21.04
	6H	17.08	17.52	18.13	18.58	19.96	18.51	18.95	19.56	20.01	21.39
	8H	17.21	17.63	18.26	18.68	20.08	18.62	19.03	19.67	20.08	21.48
	12H	17.28	17.65	18.34	18.71	20.12	18.66	19.03	19.73	20.10	21.50
8H	4H	16.87	17.28	17.92	18.33	19.73	18.21	18.62	19.26	19.67	21.07
	6H	17.45	17.79	18.53	18.89	20.28	18.71	19.05	19.78	20.14	21.54
	8H	17.66	17.96	18.74	19.04	20.45	18.89	19.19	19.97	20.26	21.68
	12H	17.78	18.04	18.87	19.11	20.57	18.99	19.25	20.07	20.32	21.78
12H	4H	16.87	17.24	17.93	18.30	19.71	18.18	18.55	19.25	19.62	21.02
	6H	17.50	17.80	18.58	18.88	20.30	18.72	19.02	19.80	20.10	21.51
	8H	17.74	18.00	18.82	19.07	20.53	18.92	19.18	20.00	20.25	21.71