

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331937-935

Luminaire Tested: **S123DIP-S560D1025U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331937-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1025U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5585.1 lumens
Efficiency: N/A
Efficacy: 125.5 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37																				
1	95	91	87	84	86	83	79	77	67	65	63	52	51	50	39	38	38	31																				
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	35	33	32	27																				
3	79	70	63	57	71	64	58	53	52	48	44	41	38	36	31	29	27	23																				
4	72	62	54	49	65	57	50	45	46	41	38	37	33	31	28	25	24	20																				
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	23	21	17																				
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15																				
7	56	45	37	31	51	41	34	29	34	29	25	27	23	20	21	18	16	13																				
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	14	12																				
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	18	15	13	11																				
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7326	7326	7326	7326
5°	8737	7358	6521	7358
10°	10935	7321	5889	7321
15°	13412	7261	5483	7261
20°	15978	7170	5220	7170
25°	16966	7058	5162	7058
30°	14542	6976	5189	6976
35°	10113	6859	5243	6859
40°	7617	6724	5227	6724
45°	6325	6520	5160	6520
50°	5667	6107	5114	6107
55°	5296	5662	5050	5662
60°	4969	5197	4997	5197
65°	4669	4737	4837	4737
70°	4378	4214	4607	4214
75°	3922	3689	4225	3689
80°	3434	3025	3639	3025
85°	2692	2198	2445	2198



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.0	1.2
10°-20°	215.0	3.8
20°-30°	360.8	6.5
30°-40°	408.6	7.3
40°-50°	366.4	6.6
50°-60°	295.7	5.3
60°-70°	206.0	3.7
70°-80°	108.3	1.9
80°-90°	29.7	0.5
90°-100°	42.1	0.8
100°-110°	200.4	3.6
110°-120°	481.5	8.6
120°-130°	613.1	11.0
130°-140°	655.1	11.7
140°-150°	612.6	11.0
150°-160°	494.1	8.8
160°-170°	318.9	5.7
170°-180°	109.9	2.0
0°-30°	642.9	11.5
0°-40°	1051.4	18.8
0°-60°	1713.5	30.7
0°-90°	2057.5	36.8
90°-120°	724.0	13.0
90°-150°	2604.6	46.6
90°-180°	3528.0	63.2
0°-180°	5585.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	681	681	681	681	681	
5°	809	681	604	681	809	84
15°	1204	652	492	652	1204	348
25°	1428	594	435	594	1428	626
35°	770	522	399	522	770	500
45°	416	428	339	428	416	329
55°	282	302	269	302	282	253
65°	183	186	190	186	183	183
75°	94	89	102	89	94	101
85°	22	18	20	18	22	26
90°	26	1	26	1	26	13
95°	33	52	33	52	33	27
105°	38	256	38	256	38	86
115°	505	480	505	480	505	467
125°	691	677	691	677	691	617
135°	852	843	852	843	852	657
145°	982	973	982	973	982	613
155°	1070	1072	1070	1072	1070	493
165°	1128	1130	1128	1130	1128	318
175°	1152	1157	1152	1157	1152	110
180°	1157	1157	1157	1157	1157	



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	722.3	721.8	720.5	721.5	719.4	716.5	716.3	713.6	705.9	705.4	703.4
5°	808.6	805.9	805.6	805.3	800.6	794.4	782.5	781.5	765.7	757.8	748.2
7.5°	920.3	921.7	916.9	912.7	898.5	889.2	876.5	860.2	840.8	821.0	807.9
10°	1000.5	1011.3	997.8	988.6	980.1	963.9	945.1	921.7	898.3	870.9	850.2
12.5°	1086.5	1091.8	1089.2	1080.4	1067.1	1042.5	1009.2	983.4	961.8	916.3	897.9
15°	1203.6	1223.7	1210.9	1181.2	1181.9	1158.5	1114.9	1067.1	1041.7	1001.8	947.4
17.5°	1328.4	1330.9	1325.4	1300.7	1284.2	1252.1	1211.9	1166.1	1114.6	1066.3	1008.6
20°	1394.9	1392.9	1381.4	1368.5	1340.1	1315.1	1271.2	1220.1	1154.2	1106.6	1043.7
22.5°	1431.8	1428.5	1423.1	1412.3	1388.7	1361.8	1322.4	1266.5	1203.8	1138.3	1065.6
25°	1428.5	1432.8	1433.5	1430.5	1422.3	1406.1	1375.1	1330.6	1267.9	1183.9	1108.0
27.5°	1299.2	1305.3	1322.9	1338.6	1356.1	1373.8	1371.5	1349.4	1303.0	1230.4	1137.6
30°	1170.0	1156.8	1189.5	1230.6	1258.7	1308.1	1335.8	1337.5	1311.5	1249.1	1158.7
32.5°	990.6	1005.1	1019.5	1070.2	1131.5	1187.1	1242.2	1286.6	1291.7	1250.2	1171.1
35°	769.6	787.8	814.2	840.6	906.5	963.2	1060.1	1144.6	1211.9	1220.7	1172.3
37.5°	620.2	629.2	645.8	672.3	715.4	782.7	857.7	964.4	1061.9	1134.4	1137.6
40°	542.1	544.8	563.5	583.7	618.6	674.0	741.7	835.9	952.7	1054.0	1096.1
42.5°	483.5	489.4	497.3	516.7	544.5	586.2	649.0	727.0	834.0	950.5	1033.0
45°	415.5	422.1	427.1	439.9	459.7	487.7	531.6	602.8	684.2	804.6	915.8
47.5°	370.5	371.0	374.7	384.4	397.9	419.0	450.0	495.7	570.5	668.0	782.2
50°	338.4	343.6	344.9	352.5	363.1	378.6	404.3	443.2	504.5	590.3	695.2
52.5°	315.6	317.2	320.9	326.4	335.6	347.7	370.0	400.5	448.6	521.7	618.1
55°	282.2	282.2	285.9	290.2	295.5	306.3	321.2	343.6	380.2	437.0	516.8
57.5°	251.4	253.0	255.6	256.9	261.4	268.6	281.0	298.1	325.4	369.0	432.5
60°	230.8	233.8	233.5	236.1	240.0	245.6	256.2	270.1	294.5	329.4	382.9
62.5°	212.9	212.7	212.7	215.8	219.7	225.1	232.0	243.9	264.7	295.7	341.1
65°	183.3	182.7	185.0	187.0	188.3	192.3	197.5	208.1	222.0	245.0	280.3
67.5°	157.1	155.2	156.4	157.1	159.4	162.5	167.4	173.9	184.9	203.5	230.1
70°	139.1	137.5	137.2	137.8	139.8	142.2	145.8	152.1	162.2	177.1	196.6
72.5°	120.7	119.6	119.5	121.0	121.9	123.4	126.0	131.7	139.8	150.9	169.1
75°	94.3	94.3	94.3	94.6	95.7	96.9	98.9	101.9	108.1	116.1	128.3
77.5°	70.7	70.6	70.3	70.2	71.6	72.2	72.7	75.4	79.0	84.3	93.2
80°	55.4	53.7	54.4	55.4	56.1	56.4	57.3	58.0	61.0	64.0	70.3
82.5°	41.2	39.8	39.9	41.4	41.6	41.8	42.9	43.8	44.9	47.6	51.0
85°	21.8	21.8	22.1	22.1	22.4	22.1	23.1	23.4	23.4	25.1	27.0
87.5°	13.1	12.5	12.7	12.8	12.5	12.7	12.7	12.9	13.0	13.1	12.8
90°	25.7	25.4	25.1	24.6	24.3	23.7	22.9	22.1	21.4	20.7	18.2
92.5°	28.5	28.3	28.1	27.8	27.6	26.9	25.7	24.5	23.2	22.0	20.1
95°	32.6	32.6	32.6	32.6	32.6	32.0	30.7	29.3	28.0	26.6	24.5
97.5°	35.4	35.2	35.0	34.9	34.6	33.8	32.3	30.7	29.2	27.6	41.4
100°	36.1	35.9	35.7	35.6	35.3	34.4	33.0	31.4	29.9	28.3	58.1
102.5°	36.8	36.4	36.1	35.7	35.4	37.6	42.4	47.1	51.8	56.6	89.1
105°	37.8	37.5	37.0	36.7	36.2	53.0	86.8	120.6	154.4	188.2	205.4
107.5°	118.7	144.2	169.7	195.2	220.7	245.8	270.6	295.4	320.2	345.0	342.2
110°	236.3	263.6	290.9	318.2	345.6	362.4	368.7	375.0	381.3	387.6	385.5



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	405.4	411.2	417.0	422.8	428.5	431.4	431.3	431.1	431.0	430.9	428.8
115°	505.3	504.5	503.8	503.0	502.3	500.9	499.0	497.1	495.2	493.3	491.5
117.5°	561.4	561.2	561.0	560.9	560.8	559.9	558.4	556.9	555.3	553.8	552.9
120°	599.9	599.9	599.9	599.9	599.9	599.1	597.5	596.1	594.5	593.0	592.5
122.5°	637.7	637.5	637.4	637.2	637.1	636.5	635.4	634.3	633.3	632.1	631.5
125°	691.0	690.6	690.2	689.8	689.4	689.1	688.6	688.3	687.9	687.5	686.7
127.5°	742.2	742.5	743.0	743.3	743.7	743.6	743.0	742.4	741.8	741.1	740.2
130°	775.2	775.6	775.9	776.4	776.7	776.5	775.8	775.0	774.2	773.4	772.7
132.5°	805.5	806.0	806.5	807.0	807.5	807.4	806.7	805.9	805.2	804.4	803.8
135°	851.7	852.2	852.8	853.4	853.9	853.9	853.4	852.8	852.2	851.7	850.9
137.5°	895.2	895.5	896.0	896.3	896.6	896.4	895.5	894.6	893.6	892.8	892.3
140°	921.3	921.7	922.0	922.4	922.8	922.6	921.9	921.1	920.3	919.5	919.0
142.5°	945.4	945.9	946.4	946.9	947.4	947.4	946.8	946.2	945.6	945.0	944.4
145°	982.3	982.3	982.3	982.3	982.3	982.1	981.7	981.4	980.9	980.6	980.2
147.5°	1009.8	1010.6	1011.6	1012.4	1013.3	1013.6	1013.1	1012.8	1012.4	1012.0	1011.7
150°	1030.4	1031.0	1031.6	1032.2	1032.7	1032.9	1032.4	1032.1	1031.7	1031.3	1030.9
152.5°	1046.9	1047.8	1048.7	1049.6	1050.4	1050.5	1049.8	1049.1	1048.4	1047.8	1047.6
155°	1070.0	1071.1	1072.3	1073.4	1074.5	1074.6	1073.7	1072.7	1071.8	1070.8	1070.7
157.5°	1089.4	1090.9	1092.4	1093.8	1095.4	1095.5	1094.3	1093.2	1092.1	1090.9	1091.1
160°	1101.7	1103.1	1104.4	1105.8	1107.1	1107.2	1106.0	1104.9	1103.8	1102.6	1102.8
162.5°	1113.4	1114.7	1115.8	1117.0	1118.2	1118.1	1116.8	1115.5	1114.2	1112.9	1113.1
165°	1127.6	1128.9	1130.2	1131.5	1132.9	1132.8	1131.3	1129.7	1128.2	1126.7	1126.9
167.5°	1137.6	1139.2	1140.7	1142.3	1143.8	1143.8	1142.3	1140.7	1139.2	1137.6	1137.6
170°	1143.8	1145.4	1146.9	1148.5	1150.0	1150.0	1148.5	1146.9	1145.4	1143.8	1143.8
172.5°	1147.3	1149.0	1150.6	1152.4	1154.0	1154.1	1152.5	1151.1	1149.5	1148.0	1147.8
175°	1152.4	1154.0	1155.5	1157.0	1158.6	1158.6	1157.4	1156.0	1154.7	1153.3	1153.1
177.5°	1154.0	1155.5	1157.1	1158.6	1160.1	1160.3	1159.1	1157.8	1156.6	1155.4	1155.2
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	701.7	699.6	697.5	693.8	690.6	686.1	684.8	683.3	678.6	674.2	671.1
5°	744.6	736.7	725.1	714.5	706.0	694.5	687.9	681.0	671.1	662.2	654.9
7.5°	789.5	773.9	756.0	736.6	718.5	701.0	687.0	674.5	660.6	647.5	637.3
10°	825.1	802.6	777.6	750.5	727.5	705.0	686.2	669.8	651.9	636.5	623.5
12.5°	865.6	832.4	797.9	765.0	737.7	706.6	683.9	662.9	642.7	624.1	609.6
15°	913.8	871.6	830.7	785.5	743.9	705.0	678.0	651.6	628.2	609.1	590.6
17.5°	957.5	909.7	855.8	800.9	750.8	704.6	666.8	637.0	607.7	584.3	565.8
20°	982.3	927.9	866.9	809.9	754.5	703.0	661.5	625.9	594.3	569.5	548.7
22.5°	1003.8	940.0	876.9	816.0	754.2	698.8	651.8	615.1	580.7	556.6	534.5
25°	1025.9	949.7	886.4	814.9	745.9	688.5	635.8	594.3	559.9	531.6	508.9
27.5°	1044.9	949.1	873.9	796.9	732.9	675.4	619.1	574.5	538.0	507.2	484.1
30°	1057.6	950.4	861.0	784.8	720.2	660.8	606.1	561.3	523.0	491.6	469.9
32.5°	1065.5	949.6	849.1	767.9	700.2	647.6	592.1	545.7	506.4	475.6	454.6
35°	1070.1	943.7	828.7	733.1	667.8	616.6	570.2	522.0	480.8	452.1	428.3
37.5°	1060.8	931.6	804.9	699.4	627.9	577.6	538.5	497.5	458.1	426.5	406.0
40°	1046.3	923.7	786.4	675.7	600.5	552.0	518.8	478.5	439.5	409.6	390.5
42.5°	1018.6	907.6	766.2	649.3	572.0	523.5	492.8	459.3	422.4	394.3	375.1
45°	951.1	872.5	735.7	609.8	529.9	479.8	452.8	428.3	395.0	367.6	351.2
47.5°	857.2	819.8	691.6	568.0	486.0	437.8	409.7	390.0	365.7	343.6	327.8
50°	792.1	776.6	661.9	539.5	456.7	409.6	382.5	364.7	347.2	325.1	310.6
52.5°	716.9	726.4	627.0	510.0	426.9	380.6	355.1	341.0	325.1	306.9	294.3
55°	611.1	645.7	566.9	460.4	382.5	338.4	314.3	301.7	292.5	279.0	268.1
57.5°	512.0	555.9	501.8	409.2	338.9	300.8	277.8	264.1	258.1	251.1	242.5
60°	453.1	496.6	455.4	375.0	309.6	273.4	253.0	241.4	235.5	230.5	223.3
62.5°	400.6	444.6	410.0	340.1	280.9	247.3	229.5	218.2	213.5	210.9	204.7
65°	328.5	366.4	343.3	285.9	239.7	210.1	193.9	186.0	181.7	180.7	176.8
67.5°	267.3	296.2	279.4	237.1	200.8	175.1	161.4	154.7	151.4	151.1	148.1
70°	227.2	254.3	241.4	203.1	171.8	151.7	139.8	133.9	131.9	131.6	129.9
72.5°	196.0	214.9	204.7	172.8	148.6	130.4	121.6	115.4	113.1	113.7	112.5
75°	145.1	159.3	153.3	131.2	111.8	99.9	92.6	88.7	86.7	87.7	86.4
77.5°	104.4	113.4	108.1	92.7	80.8	72.2	66.8	64.4	62.6	62.5	61.9
80°	78.8	84.1	81.1	71.9	62.0	54.8	50.5	48.8	47.8	47.5	47.2
82.5°	56.1	60.6	57.1	50.8	44.1	39.7	37.3	35.1	34.4	34.5	34.3
85°	28.3	30.0	28.7	24.7	22.1	20.1	18.8	17.8	17.1	17.5	16.8
87.5°	12.9	12.7	11.4	9.9	9.0	7.8	7.4	6.5	6.4	6.7	6.9
90°	15.7	13.2	10.7	8.5	6.6	4.6	2.8	0.9	2.8	4.6	6.6
92.5°	18.3	16.4	14.6	13.9	14.4	14.9	15.4	16.0	15.4	14.9	14.4
95°	22.5	20.3	18.3	21.1	28.9	36.8	44.6	52.4	44.6	36.8	28.9
97.5°	55.2	69.0	82.7	91.3	94.8	98.3	101.9	105.4	101.9	98.3	94.8
100°	87.9	117.7	147.5	160.5	156.7	152.9	149.0	145.3	149.0	152.9	156.7
102.5°	121.7	154.2	186.8	201.6	198.9	196.1	193.4	190.6	193.4	196.1	198.9
105°	222.6	239.8	256.9	264.5	262.4	260.3	258.2	256.1	258.2	260.3	262.4
107.5°	339.6	336.8	334.2	331.9	330.3	328.6	326.9	325.2	326.9	328.6	330.3
110°	383.4	381.3	379.2	377.4	375.8	374.3	372.8	371.3	372.8	374.3	375.8



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	426.7	424.6	422.5	420.8	419.4	418.0	416.6	415.3	416.6	418.0	419.4
115°	489.8	488.1	486.5	485.0	483.9	482.7	481.6	480.4	481.6	482.7	483.9
117.5°	552.1	551.1	550.3	549.1	547.8	546.3	544.9	543.5	544.9	546.3	547.8
120°	591.9	591.2	590.7	589.5	587.8	586.1	584.4	582.6	584.4	586.1	587.8
122.5°	630.8	630.0	629.3	628.2	626.8	625.3	624.0	622.6	624.0	625.3	626.8
125°	686.0	685.3	684.5	683.3	681.8	680.3	678.7	677.2	678.7	680.3	681.8
127.5°	739.3	738.4	737.4	736.2	734.7	733.2	731.7	730.1	731.7	733.2	734.7
130°	772.0	771.2	770.4	769.3	767.8	766.2	764.7	763.2	764.7	766.2	767.8
132.5°	803.1	802.5	801.9	800.9	799.4	797.8	796.3	794.8	796.3	797.8	799.4
135°	850.2	849.4	848.6	847.7	846.5	845.3	844.2	843.1	844.2	845.3	846.5
137.5°	891.9	891.5	891.0	890.1	888.7	887.3	885.8	884.3	885.8	887.3	888.7
140°	918.4	917.8	917.3	916.4	915.2	914.1	913.0	911.8	913.0	914.1	915.2
142.5°	943.8	943.3	942.7	941.8	940.7	939.5	938.4	937.3	938.4	939.5	940.7
145°	979.8	979.5	979.0	978.2	976.9	975.5	974.2	972.8	974.2	975.5	976.9
147.5°	1011.2	1010.9	1010.5	1009.9	1009.0	1008.1	1007.3	1006.3	1007.3	1008.1	1009.0
150°	1030.5	1030.1	1029.8	1029.2	1028.7	1028.1	1027.6	1027.0	1027.6	1028.1	1028.7
152.5°	1047.3	1047.1	1046.9	1046.6	1046.4	1046.1	1045.9	1045.5	1045.9	1046.1	1046.4
155°	1070.4	1070.2	1070.1	1070.1	1070.6	1070.9	1071.3	1071.7	1071.3	1070.9	1070.6
157.5°	1091.3	1091.5	1091.7	1091.8	1091.8	1091.9	1091.9	1091.9	1091.9	1091.9	1091.8
160°	1103.0	1103.2	1103.4	1103.5	1103.8	1104.0	1104.1	1104.3	1104.1	1104.0	1103.8
162.5°	1113.3	1113.5	1113.7	1114.0	1114.6	1115.0	1115.5	1116.0	1115.5	1115.0	1114.6
165°	1127.0	1127.2	1127.5	1127.8	1128.4	1128.9	1129.5	1130.1	1129.5	1128.9	1128.4
167.5°	1137.6	1137.6	1137.6	1138.1	1138.8	1139.6	1140.4	1141.1	1140.4	1139.6	1138.8
170°	1143.8	1143.8	1143.8	1144.3	1145.0	1145.8	1146.5	1147.3	1146.5	1145.8	1145.0
172.5°	1147.7	1147.5	1147.4	1147.8	1148.7	1149.6	1150.6	1151.4	1150.6	1149.6	1148.7
175°	1153.0	1152.7	1152.5	1153.0	1153.9	1154.9	1155.8	1156.8	1155.8	1154.9	1153.9
177.5°	1155.1	1154.9	1154.8	1155.1	1155.8	1156.6	1157.4	1158.1	1157.4	1156.6	1155.8
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	669.3	667.4	664.8	660.8	657.6	652.6	652.6	653.4	653.4	653.2	652.6
5°	648.9	644.0	638.1	631.2	623.9	616.6	615.4	612.7	610.7	609.4	607.8
7.5°	627.5	618.8	610.1	600.5	591.6	584.3	579.2	575.0	572.2	569.4	567.2
10°	613.0	602.1	591.9	581.7	570.5	561.5	555.9	552.0	549.1	546.4	545.1
12.5°	595.9	583.4	572.1	562.4	550.2	541.0	535.6	533.8	530.3	524.8	521.9
15°	570.8	559.3	545.8	530.9	525.0	513.8	507.5	504.5	502.6	498.3	497.0
17.5°	549.4	534.3	519.1	508.0	497.0	487.9	484.4	480.7	478.1	474.6	473.6
20°	532.3	518.8	504.9	493.0	481.5	471.6	468.6	466.0	463.3	461.7	460.4
22.5°	514.8	501.3	489.8	478.7	466.4	459.9	456.7	453.8	451.9	450.8	449.5
25°	490.3	478.5	465.6	455.7	445.8	441.5	439.5	437.9	436.6	435.0	434.6
27.5°	468.5	455.6	445.1	435.8	428.8	425.2	423.3	422.5	422.8	423.4	423.7
30°	452.1	440.2	431.6	423.7	417.2	413.9	413.5	413.5	414.8	415.2	415.9
32.5°	437.0	427.3	418.7	411.0	406.0	403.8	405.1	405.1	406.1	407.0	408.2
35°	415.2	406.6	400.0	393.4	389.1	390.1	390.7	391.4	393.0	395.0	396.4
37.5°	394.3	386.8	380.0	374.8	372.8	374.6	376.2	377.5	379.5	381.0	382.3
40°	379.2	373.6	367.0	362.4	363.1	364.0	365.4	367.0	368.7	369.6	371.0
42.5°	365.2	359.4	354.4	350.5	351.5	352.8	353.5	354.4	356.3	358.1	358.9
45°	344.0	339.3	334.7	332.4	333.0	333.7	334.4	335.4	337.0	338.4	338.6
47.5°	320.0	316.8	313.7	311.4	312.5	312.2	313.1	315.2	315.7	316.5	318.3
50°	304.7	301.7	298.1	297.5	297.5	297.5	297.7	300.4	300.4	301.7	303.1
52.5°	287.8	285.9	283.6	282.4	281.9	281.9	283.3	284.6	285.1	287.0	288.3
55°	262.8	260.8	258.9	257.9	257.2	257.9	260.5	261.1	262.8	263.8	264.8
57.5°	236.8	235.2	233.7	233.2	233.0	233.8	235.3	237.3	237.7	240.7	242.2
60°	219.6	217.3	216.0	216.0	215.3	218.3	217.7	220.9	221.6	223.6	225.9
62.5°	201.9	198.8	198.3	198.3	199.2	200.1	201.0	202.5	204.2	206.7	208.4
65°	173.5	171.8	174.1	173.7	173.1	175.1	175.1	176.8	178.7	181.1	184.7
67.5°	146.5	145.6	145.9	145.9	146.8	147.9	148.9	150.3	152.7	155.2	157.5
70°	128.3	129.2	127.6	129.0	129.9	130.3	130.9	132.9	135.5	137.2	139.8
72.5°	110.6	110.6	110.7	111.2	112.3	112.9	113.5	115.7	118.6	120.0	122.2
75°	85.1	84.7	85.8	85.8	87.4	88.1	88.7	89.7	92.3	94.3	96.0
77.5°	62.2	62.5	62.3	63.5	63.0	63.1	65.2	66.1	66.4	70.3	71.2
80°	46.8	47.5	47.8	48.1	48.5	47.8	50.1	51.1	51.1	53.4	55.1
82.5°	33.7	34.0	34.9	35.2	35.3	35.9	36.2	36.9	37.6	38.7	40.8
85°	16.8	17.8	18.2	17.8	18.2	17.5	18.4	18.8	19.1	19.1	19.1
87.5°	7.0	7.7	7.9	8.7	8.9	9.6	9.8	9.5	9.6	10.5	9.6
90°	8.5	10.7	13.2	15.7	18.2	20.7	21.4	22.1	22.9	23.7	24.3
92.5°	13.9	14.6	16.4	18.3	20.1	22.0	23.2	24.5	25.7	26.9	27.6
95°	21.1	18.3	20.3	22.5	24.5	26.6	28.0	29.3	30.7	32.0	32.6
97.5°	91.3	82.7	69.0	55.2	41.4	27.6	29.2	30.7	32.3	33.8	34.6
100°	160.5	147.5	117.7	87.9	58.1	28.3	29.9	31.4	33.0	34.4	35.3
102.5°	201.6	186.8	154.2	121.7	89.1	56.6	51.8	47.1	42.4	37.6	35.4
105°	264.5	256.9	239.8	222.6	205.4	188.2	154.4	120.6	86.8	53.0	36.2
107.5°	331.9	334.2	336.8	339.6	342.2	345.0	320.2	295.4	270.6	245.8	220.7
110°	377.4	379.2	381.3	383.4	385.5	387.6	381.3	375.0	368.7	362.4	345.6



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	420.8	422.5	424.6	426.7	428.8	430.9	431.0	431.1	431.3	431.4	428.5
115°	485.0	486.5	488.1	489.8	491.5	493.3	495.2	497.1	499.0	500.9	502.3
117.5°	549.1	550.3	551.1	552.1	552.9	553.8	555.3	556.9	558.4	559.9	560.8
120°	589.5	590.7	591.2	591.9	592.5	593.0	594.5	596.1	597.5	599.1	599.9
122.5°	628.2	629.3	630.0	630.8	631.5	632.1	633.3	634.3	635.4	636.5	637.1
125°	683.3	684.5	685.3	686.0	686.7	687.5	687.9	688.3	688.6	689.1	689.4
127.5°	736.2	737.4	738.4	739.3	740.2	741.1	741.8	742.4	743.0	743.6	743.7
130°	769.3	770.4	771.2	772.0	772.7	773.4	774.2	775.0	775.8	776.5	776.7
132.5°	800.9	801.9	802.5	803.1	803.8	804.4	805.2	805.9	806.7	807.4	807.5
135°	847.7	848.6	849.4	850.2	850.9	851.7	852.2	852.8	853.4	853.9	853.9
137.5°	890.1	891.0	891.5	891.9	892.3	892.8	893.6	894.6	895.5	896.4	896.6
140°	916.4	917.3	917.8	918.4	919.0	919.5	920.3	921.1	921.9	922.6	922.8
142.5°	941.8	942.7	943.3	943.8	944.4	945.0	945.6	946.2	946.8	947.4	947.4
145°	978.2	979.0	979.5	979.8	980.2	980.6	980.9	981.4	981.7	982.1	982.3
147.5°	1009.9	1010.5	1010.9	1011.2	1011.7	1012.0	1012.4	1012.8	1013.1	1013.6	1013.3
150°	1029.2	1029.8	1030.1	1030.5	1030.9	1031.3	1031.7	1032.1	1032.4	1032.9	1032.7
152.5°	1046.6	1046.9	1047.1	1047.3	1047.6	1047.8	1048.4	1049.1	1049.8	1050.5	1050.4
155°	1070.1	1070.1	1070.2	1070.4	1070.7	1070.8	1071.8	1072.7	1073.7	1074.6	1074.5
157.5°	1091.8	1091.7	1091.5	1091.3	1091.1	1090.9	1092.1	1093.2	1094.3	1095.5	1095.4
160°	1103.5	1103.4	1103.2	1103.0	1102.8	1102.6	1103.8	1104.9	1106.0	1107.2	1107.1
162.5°	1114.0	1113.7	1113.5	1113.3	1113.1	1112.9	1114.2	1115.5	1116.8	1118.1	1118.2
165°	1127.8	1127.5	1127.2	1127.0	1126.9	1126.7	1128.2	1129.7	1131.3	1132.8	1132.9
167.5°	1138.1	1137.6	1137.6	1137.6	1137.6	1137.6	1139.2	1140.7	1142.3	1143.8	1143.8
170°	1144.3	1143.8	1143.8	1143.8	1143.8	1143.8	1145.4	1146.9	1148.5	1150.0	1150.0
172.5°	1147.8	1147.4	1147.5	1147.7	1147.8	1148.0	1149.5	1151.1	1152.5	1154.1	1154.0
175°	1153.0	1152.5	1152.7	1153.0	1153.1	1153.3	1154.7	1156.0	1157.4	1158.6	1158.6
177.5°	1155.1	1154.8	1154.9	1155.1	1155.2	1155.4	1156.6	1157.8	1159.1	1160.3	1160.1
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	650.8	650.6	652.4	651.1	652.4	650.6	650.8	652.6	653.2	653.4	653.4
5°	605.8	606.7	603.5	603.5	603.5	606.7	605.8	607.8	609.4	610.7	612.7
7.5°	565.7	564.2	564.4	562.6	564.4	564.2	565.7	567.2	569.4	572.2	575.0
10°	541.1	539.2	538.5	538.8	538.5	539.2	541.1	545.1	546.4	549.1	552.0
12.5°	520.8	520.4	516.1	516.2	516.1	520.4	520.8	521.9	524.8	530.3	533.8
15°	497.0	490.7	490.0	492.0	490.0	490.7	497.0	497.0	498.3	502.6	504.5
17.5°	473.0	469.7	469.9	468.9	469.9	469.7	473.0	473.6	474.6	478.1	480.7
20°	460.4	458.4	458.1	455.7	458.1	458.4	460.4	460.4	461.7	463.3	466.0
22.5°	448.8	448.1	448.2	445.7	448.2	448.1	448.8	449.5	450.8	451.9	453.8
25°	434.3	435.9	434.6	434.6	434.6	435.9	434.3	434.6	435.0	436.6	437.9
27.5°	424.6	424.5	423.8	423.8	423.8	424.5	424.6	423.7	423.4	422.8	422.5
30°	417.2	416.8	417.5	417.5	417.5	416.8	417.2	415.9	415.2	414.8	413.5
32.5°	409.7	410.2	410.4	410.6	410.4	410.2	409.7	408.2	407.0	406.1	405.1
35°	398.4	398.6	399.7	399.0	399.7	398.6	398.4	396.4	395.0	393.0	391.4
37.5°	382.9	384.4	384.1	384.6	384.1	384.4	382.9	382.3	381.0	379.5	377.5
40°	371.3	372.3	372.0	372.0	372.0	372.3	371.3	371.0	369.6	368.7	367.0
42.5°	359.5	360.2	359.3	358.8	359.3	360.2	359.5	358.9	358.1	356.3	354.4
45°	340.0	339.3	340.4	339.0	340.4	339.3	340.0	338.6	338.4	337.0	335.4
47.5°	318.2	318.9	319.2	320.1	319.2	318.9	318.2	318.3	316.5	315.7	315.2
50°	303.7	305.7	305.7	305.4	305.7	305.7	303.7	303.1	301.7	300.4	300.4
52.5°	289.5	290.4	291.7	291.6	291.7	290.4	289.5	288.3	287.0	285.1	284.6
55°	267.4	268.1	268.7	269.1	268.7	268.1	267.4	264.8	263.8	262.8	261.1
57.5°	244.6	244.4	245.9	246.4	245.9	244.4	244.6	242.2	240.7	237.7	237.3
60°	228.5	228.5	231.2	232.1	231.2	228.5	228.5	225.9	223.6	221.6	220.9
62.5°	211.4	212.4	215.1	213.7	215.1	212.4	211.4	208.4	206.7	204.2	202.5
65°	186.3	189.0	188.6	189.9	188.6	189.0	186.3	184.7	181.1	178.7	176.8
67.5°	160.1	161.8	164.2	164.4	164.2	161.8	160.1	157.5	155.2	152.7	150.3
70°	142.5	144.1	145.4	146.4	145.4	144.1	142.5	139.8	137.2	135.5	132.9
72.5°	125.3	126.1	129.3	127.9	129.3	126.1	125.3	122.2	120.0	118.6	115.7
75°	98.2	100.6	102.5	101.6	102.5	100.6	98.2	96.0	94.3	92.3	89.7
77.5°	72.7	75.0	75.9	75.1	75.9	75.0	72.7	71.2	70.3	66.4	66.1
80°	57.3	57.1	59.1	58.7	59.1	57.1	57.3	55.1	53.4	51.1	51.1
82.5°	42.1	41.8	42.7	42.9	42.7	41.8	42.1	40.8	38.7	37.6	36.9
85°	20.4	21.4	20.1	19.8	20.1	21.4	20.4	19.1	19.1	19.1	18.8
87.5°	9.6	9.7	9.6	9.4	9.6	9.7	9.6	9.6	10.5	9.6	9.5
90°	24.6	25.1	25.4	25.7	25.4	25.1	24.6	24.3	23.7	22.9	22.1
92.5°	27.8	28.1	28.3	28.5	28.3	28.1	27.8	27.6	26.9	25.7	24.5
95°	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.0	30.7	29.3
97.5°	34.9	35.0	35.2	35.4	35.2	35.0	34.9	34.6	33.8	32.3	30.7
100°	35.6	35.7	35.9	36.1	35.9	35.7	35.6	35.3	34.4	33.0	31.4
102.5°	35.7	36.1	36.4	36.8	36.4	36.1	35.7	35.4	37.6	42.4	47.1
105°	36.7	37.0	37.5	37.8	37.5	37.0	36.7	36.2	53.0	86.8	120.6
107.5°	195.2	169.7	144.2	118.7	144.2	169.7	195.2	220.7	245.8	270.6	295.4
110°	318.2	290.9	263.6	236.3	263.6	290.9	318.2	345.6	362.4	368.7	375.0



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	422.8	417.0	411.2	405.4	411.2	417.0	422.8	428.5	431.4	431.3	431.1
115°	503.0	503.8	504.5	505.3	504.5	503.8	503.0	502.3	500.9	499.0	497.1
117.5°	560.9	561.0	561.2	561.4	561.2	561.0	560.9	560.8	559.9	558.4	556.9
120°	599.9	599.9	599.9	599.9	599.9	599.9	599.9	599.9	599.1	597.5	596.1
122.5°	637.2	637.4	637.5	637.7	637.5	637.4	637.2	637.1	636.5	635.4	634.3
125°	689.8	690.2	690.6	691.0	690.6	690.2	689.8	689.4	689.1	688.6	688.3
127.5°	743.3	743.0	742.5	742.2	742.5	743.0	743.3	743.7	743.6	743.0	742.4
130°	776.4	775.9	775.6	775.2	775.6	775.9	776.4	776.7	776.5	775.8	775.0
132.5°	807.0	806.5	806.0	805.5	806.0	806.5	807.0	807.5	807.4	806.7	805.9
135°	853.4	852.8	852.2	851.7	852.2	852.8	853.4	853.9	853.9	853.4	852.8
137.5°	896.3	896.0	895.5	895.2	895.5	896.0	896.3	896.6	896.4	895.5	894.6
140°	922.4	922.0	921.7	921.3	921.7	922.0	922.4	922.8	922.6	921.9	921.1
142.5°	946.9	946.4	945.9	945.4	945.9	946.4	946.9	947.4	947.4	946.8	946.2
145°	982.3	982.3	982.3	982.3	982.3	982.3	982.3	982.3	982.1	981.7	981.4
147.5°	1012.4	1011.6	1010.6	1009.8	1010.6	1011.6	1012.4	1013.3	1013.6	1013.1	1012.8
150°	1032.2	1031.6	1031.0	1030.4	1031.0	1031.6	1032.2	1032.7	1032.9	1032.4	1032.1
152.5°	1049.6	1048.7	1047.8	1046.9	1047.8	1048.7	1049.6	1050.4	1050.5	1049.8	1049.1
155°	1073.4	1072.3	1071.1	1070.0	1071.1	1072.3	1073.4	1074.5	1074.6	1073.7	1072.7
157.5°	1093.8	1092.4	1090.9	1089.4	1090.9	1092.4	1093.8	1095.4	1095.5	1094.3	1093.2
160°	1105.8	1104.4	1103.1	1101.7	1103.1	1104.4	1105.8	1107.1	1107.2	1106.0	1104.9
162.5°	1117.0	1115.8	1114.7	1113.4	1114.7	1115.8	1117.0	1118.2	1118.1	1116.8	1115.5
165°	1131.5	1130.2	1128.9	1127.6	1128.9	1130.2	1131.5	1132.9	1132.8	1131.3	1129.7
167.5°	1142.3	1140.7	1139.2	1137.6	1139.2	1140.7	1142.3	1143.8	1143.8	1142.3	1140.7
170°	1148.5	1146.9	1145.4	1143.8	1145.4	1146.9	1148.5	1150.0	1150.0	1148.5	1146.9
172.5°	1152.4	1150.6	1149.0	1147.3	1149.0	1150.6	1152.4	1154.0	1154.1	1152.5	1151.1
175°	1157.0	1155.5	1154.0	1152.4	1154.0	1155.5	1157.0	1158.6	1158.6	1157.4	1156.0
177.5°	1158.6	1157.1	1155.5	1154.0	1155.5	1157.1	1158.6	1160.1	1160.3	1159.1	1157.8
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	652.6	652.6	657.6	660.8	664.8	667.4	669.3	671.1	674.2	678.6	683.3
5°	615.4	616.6	623.9	631.2	638.1	644.0	648.9	654.9	662.2	671.1	681.0
7.5°	579.2	584.3	591.6	600.5	610.1	618.8	627.5	637.3	647.5	660.6	674.5
10°	555.9	561.5	570.5	581.7	591.9	602.1	613.0	623.5	636.5	651.9	669.8
12.5°	535.6	541.0	550.2	562.4	572.1	583.4	595.9	609.6	624.1	642.7	662.9
15°	507.5	513.8	525.0	530.9	545.8	559.3	570.8	590.6	609.1	628.2	651.6
17.5°	484.4	487.9	497.0	508.0	519.1	534.3	549.4	565.8	584.3	607.7	637.0
20°	468.6	471.6	481.5	493.0	504.9	518.8	532.3	548.7	569.5	594.3	625.9
22.5°	456.7	459.9	466.4	478.7	489.8	501.3	514.8	534.5	556.6	580.7	615.1
25°	439.5	441.5	445.8	455.7	465.6	478.5	490.3	508.9	531.6	559.9	594.3
27.5°	423.3	425.2	428.8	435.8	445.1	455.6	468.5	484.1	507.2	538.0	574.5
30°	413.5	413.9	417.2	423.7	431.6	440.2	452.1	469.9	491.6	523.0	561.3
32.5°	405.1	403.8	406.0	411.0	418.7	427.3	437.0	454.6	475.6	506.4	545.7
35°	390.7	390.1	389.1	393.4	400.0	406.6	415.2	428.3	452.1	480.8	522.0
37.5°	376.2	374.6	372.8	374.8	380.0	386.8	394.3	406.0	426.5	458.1	497.5
40°	365.4	364.0	363.1	362.4	367.0	373.6	379.2	390.5	409.6	439.5	478.5
42.5°	353.5	352.8	351.5	350.5	354.4	359.4	365.2	375.1	394.3	422.4	459.3
45°	334.4	333.7	333.0	332.4	334.7	339.3	344.0	351.2	367.6	395.0	428.3
47.5°	313.1	312.2	312.5	311.4	313.7	316.8	320.0	327.8	343.6	365.7	390.0
50°	297.7	297.5	297.5	297.5	298.1	301.7	304.7	310.6	325.1	347.2	364.7
52.5°	283.3	281.9	281.9	282.4	283.6	285.9	287.8	294.3	306.9	325.1	341.0
55°	260.5	257.9	257.2	257.9	258.9	260.8	262.8	268.1	279.0	292.5	301.7
57.5°	235.3	233.8	233.0	233.2	233.7	235.2	236.8	242.5	251.1	258.1	264.1
60°	217.7	218.3	215.3	216.0	216.0	217.3	219.6	223.3	230.5	235.5	241.4
62.5°	201.0	200.1	199.2	198.3	198.3	198.8	201.9	204.7	210.9	213.5	218.2
65°	175.1	175.1	173.1	173.7	174.1	171.8	173.5	176.8	180.7	181.7	186.0
67.5°	148.9	147.9	146.8	145.9	145.9	145.6	146.5	148.1	151.1	151.4	154.7
70°	130.9	130.3	129.9	129.0	127.6	129.2	128.3	129.9	131.6	131.9	133.9
72.5°	113.5	112.9	112.3	111.2	110.7	110.6	110.6	112.5	113.7	113.1	115.4
75°	88.7	88.1	87.4	85.8	85.8	84.7	85.1	86.4	87.7	86.7	88.7
77.5°	65.2	63.1	63.0	63.5	62.3	62.5	62.2	61.9	62.5	62.6	64.4
80°	50.1	47.8	48.5	48.1	47.8	47.5	46.8	47.2	47.5	47.8	48.8
82.5°	36.2	35.9	35.3	35.2	34.9	34.0	33.7	34.3	34.5	34.4	35.1
85°	18.4	17.5	18.2	17.8	18.2	17.8	16.8	16.8	17.5	17.1	17.8
87.5°	9.8	9.6	8.9	8.7	7.9	7.7	7.0	6.9	6.7	6.4	6.5
90°	21.4	20.7	18.2	15.7	13.2	10.7	8.5	6.6	4.6	2.8	0.9
92.5°	23.2	22.0	20.1	18.3	16.4	14.6	13.9	14.4	14.9	15.4	16.0
95°	28.0	26.6	24.5	22.5	20.3	18.3	21.1	28.9	36.8	44.6	52.4
97.5°	29.2	27.6	41.4	55.2	69.0	82.7	91.3	94.8	98.3	101.9	105.4
100°	29.9	28.3	58.1	87.9	117.7	147.5	160.5	156.7	152.9	149.0	145.3
102.5°	51.8	56.6	89.1	121.7	154.2	186.8	201.6	198.9	196.1	193.4	190.6
105°	154.4	188.2	205.4	222.6	239.8	256.9	264.5	262.4	260.3	258.2	256.1
107.5°	320.2	345.0	342.2	339.6	336.8	334.2	331.9	330.3	328.6	326.9	325.2
110°	381.3	387.6	385.5	383.4	381.3	379.2	377.4	375.8	374.3	372.8	371.3



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	431.0	430.9	428.8	426.7	424.6	422.5	420.8	419.4	418.0	416.6	415.3
115°	495.2	493.3	491.5	489.8	488.1	486.5	485.0	483.9	482.7	481.6	480.4
117.5°	555.3	553.8	552.9	552.1	551.1	550.3	549.1	547.8	546.3	544.9	543.5
120°	594.5	593.0	592.5	591.9	591.2	590.7	589.5	587.8	586.1	584.4	582.6
122.5°	633.3	632.1	631.5	630.8	630.0	629.3	628.2	626.8	625.3	624.0	622.6
125°	687.9	687.5	686.7	686.0	685.3	684.5	683.3	681.8	680.3	678.7	677.2
127.5°	741.8	741.1	740.2	739.3	738.4	737.4	736.2	734.7	733.2	731.7	730.1
130°	774.2	773.4	772.7	772.0	771.2	770.4	769.3	767.8	766.2	764.7	763.2
132.5°	805.2	804.4	803.8	803.1	802.5	801.9	800.9	799.4	797.8	796.3	794.8
135°	852.2	851.7	850.9	850.2	849.4	848.6	847.7	846.5	845.3	844.2	843.1
137.5°	893.6	892.8	892.3	891.9	891.5	891.0	890.1	888.7	887.3	885.8	884.3
140°	920.3	919.5	919.0	918.4	917.8	917.3	916.4	915.2	914.1	913.0	911.8
142.5°	945.6	945.0	944.4	943.8	943.3	942.7	941.8	940.7	939.5	938.4	937.3
145°	980.9	980.6	980.2	979.8	979.5	979.0	978.2	976.9	975.5	974.2	972.8
147.5°	1012.4	1012.0	1011.7	1011.2	1010.9	1010.5	1009.9	1009.0	1008.1	1007.3	1006.3
150°	1031.7	1031.3	1030.9	1030.5	1030.1	1029.8	1029.2	1028.7	1028.1	1027.6	1027.0
152.5°	1048.4	1047.8	1047.6	1047.3	1047.1	1046.9	1046.6	1046.4	1046.1	1045.9	1045.5
155°	1071.8	1070.8	1070.7	1070.4	1070.2	1070.1	1070.1	1070.6	1070.9	1071.3	1071.7
157.5°	1092.1	1090.9	1091.1	1091.3	1091.5	1091.7	1091.8	1091.8	1091.9	1091.9	1091.9
160°	1103.8	1102.6	1102.8	1103.0	1103.2	1103.4	1103.5	1103.8	1104.0	1104.1	1104.3
162.5°	1114.2	1112.9	1113.1	1113.3	1113.5	1113.7	1114.0	1114.6	1115.0	1115.5	1116.0
165°	1128.2	1126.7	1126.9	1127.0	1127.2	1127.5	1127.8	1128.4	1128.9	1129.5	1130.1
167.5°	1139.2	1137.6	1137.6	1137.6	1137.6	1137.6	1138.1	1138.8	1139.6	1140.4	1141.1
170°	1145.4	1143.8	1143.8	1143.8	1143.8	1143.8	1144.3	1145.0	1145.8	1146.5	1147.3
172.5°	1149.5	1148.0	1147.8	1147.7	1147.5	1147.4	1147.8	1148.7	1149.6	1150.6	1151.4
175°	1154.7	1153.3	1153.1	1153.0	1152.7	1152.5	1153.0	1153.9	1154.9	1155.8	1156.8
177.5°	1156.6	1155.4	1155.2	1155.1	1154.9	1154.8	1155.1	1155.8	1156.6	1157.4	1158.1
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	684.8	686.1	690.6	693.8	697.5	699.6	701.7	703.4	705.4	705.9	713.6
5°	687.9	694.5	706.0	714.5	725.1	736.7	744.6	748.2	757.8	765.7	781.5
7.5°	687.0	701.0	718.5	736.6	756.0	773.9	789.5	807.9	821.0	840.8	860.2
10°	686.2	705.0	727.5	750.5	777.6	802.6	825.1	850.2	870.9	898.3	921.7
12.5°	683.9	706.6	737.7	765.0	797.9	832.4	865.6	897.9	916.3	961.8	983.4
15°	678.0	705.0	743.9	785.5	830.7	871.6	913.8	947.4	1001.8	1041.7	1067.1
17.5°	666.8	704.6	750.8	800.9	855.8	909.7	957.5	1008.6	1066.3	1114.6	1166.1
20°	661.5	703.0	754.5	809.9	866.9	927.9	982.3	1043.7	1106.6	1154.2	1220.1
22.5°	651.8	698.8	754.2	816.0	876.9	940.0	1003.8	1065.6	1138.3	1203.8	1266.5
25°	635.8	688.5	745.9	814.9	886.4	949.7	1025.9	1108.0	1183.9	1267.9	1330.6
27.5°	619.1	675.4	732.9	796.9	873.9	949.1	1044.9	1137.6	1230.4	1303.0	1349.4
30°	606.1	660.8	720.2	784.8	861.0	950.4	1057.6	1158.7	1249.1	1311.5	1337.5
32.5°	592.1	647.6	700.2	767.9	849.1	949.6	1065.5	1171.1	1250.2	1291.7	1286.6
35°	570.2	616.6	667.8	733.1	828.7	943.7	1070.1	1172.3	1220.7	1211.9	1144.6
37.5°	538.5	577.6	627.9	699.4	804.9	931.6	1060.8	1137.6	1134.4	1061.9	964.4
40°	518.8	552.0	600.5	675.7	786.4	923.7	1046.3	1096.1	1054.0	952.7	835.9
42.5°	492.8	523.5	572.0	649.3	766.2	907.6	1018.6	1033.0	950.5	834.0	727.0
45°	452.8	479.8	529.9	609.8	735.7	872.5	951.1	915.8	804.6	684.2	602.8
47.5°	409.7	437.8	486.0	568.0	691.6	819.8	857.2	782.2	668.0	570.5	495.7
50°	382.5	409.6	456.7	539.5	661.9	776.6	792.1	695.2	590.3	504.5	443.2
52.5°	355.1	380.6	426.9	510.0	627.0	726.4	716.9	618.1	521.7	448.6	400.5
55°	314.3	338.4	382.5	460.4	566.9	645.7	611.1	516.8	437.0	380.2	343.6
57.5°	277.8	300.8	338.9	409.2	501.8	555.9	512.0	432.5	369.0	325.4	298.1
60°	253.0	273.4	309.6	375.0	455.4	496.6	453.1	382.9	329.4	294.5	270.1
62.5°	229.5	247.3	280.9	340.1	410.0	444.6	400.6	341.1	295.7	264.7	243.9
65°	193.9	210.1	239.7	285.9	343.3	366.4	328.5	280.3	245.0	222.0	208.1
67.5°	161.4	175.1	200.8	237.1	279.4	296.2	267.3	230.1	203.5	184.9	173.9
70°	139.8	151.7	171.8	203.1	241.4	254.3	227.2	196.6	177.1	162.2	152.1
72.5°	121.6	130.4	148.6	172.8	204.7	214.9	196.0	169.1	150.9	139.8	131.7
75°	92.6	99.9	111.8	131.2	153.3	159.3	145.1	128.3	116.1	108.1	101.9
77.5°	66.8	72.2	80.8	92.7	108.1	113.4	104.4	93.2	84.3	79.0	75.4
80°	50.5	54.8	62.0	71.9	81.1	84.1	78.8	70.3	64.0	61.0	58.0
82.5°	37.3	39.7	44.1	50.8	57.1	60.6	56.1	51.0	47.6	44.9	43.8
85°	18.8	20.1	22.1	24.7	28.7	30.0	28.3	27.0	25.1	23.4	23.4
87.5°	7.4	7.8	9.0	9.9	11.4	12.7	12.9	12.8	13.1	13.0	12.9
90°	2.8	4.6	6.6	8.5	10.7	13.2	15.7	18.2	20.7	21.4	22.1
92.5°	15.4	14.9	14.4	13.9	14.6	16.4	18.3	20.1	22.0	23.2	24.5
95°	44.6	36.8	28.9	21.1	18.3	20.3	22.5	24.5	26.6	28.0	29.3
97.5°	101.9	98.3	94.8	91.3	82.7	69.0	55.2	41.4	27.6	29.2	30.7
100°	149.0	152.9	156.7	160.5	147.5	117.7	87.9	58.1	28.3	29.9	31.4
102.5°	193.4	196.1	198.9	201.6	186.8	154.2	121.7	89.1	56.6	51.8	47.1
105°	258.2	260.3	262.4	264.5	256.9	239.8	222.6	205.4	188.2	154.4	120.6
107.5°	326.9	328.6	330.3	331.9	334.2	336.8	339.6	342.2	345.0	320.2	295.4
110°	372.8	374.3	375.8	377.4	379.2	381.3	383.4	385.5	387.6	381.3	375.0



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	416.6	418.0	419.4	420.8	422.5	424.6	426.7	428.8	430.9	431.0	431.1
115°	481.6	482.7	483.9	485.0	486.5	488.1	489.8	491.5	493.3	495.2	497.1
117.5°	544.9	546.3	547.8	549.1	550.3	551.1	552.1	552.9	553.8	555.3	556.9
120°	584.4	586.1	587.8	589.5	590.7	591.2	591.9	592.5	593.0	594.5	596.1
122.5°	624.0	625.3	626.8	628.2	629.3	630.0	630.8	631.5	632.1	633.3	634.3
125°	678.7	680.3	681.8	683.3	684.5	685.3	686.0	686.7	687.5	687.9	688.3
127.5°	731.7	733.2	734.7	736.2	737.4	738.4	739.3	740.2	741.1	741.8	742.4
130°	764.7	766.2	767.8	769.3	770.4	771.2	772.0	772.7	773.4	774.2	775.0
132.5°	796.3	797.8	799.4	800.9	801.9	802.5	803.1	803.8	804.4	805.2	805.9
135°	844.2	845.3	846.5	847.7	848.6	849.4	850.2	850.9	851.7	852.2	852.8
137.5°	885.8	887.3	888.7	890.1	891.0	891.5	891.9	892.3	892.8	893.6	894.6
140°	913.0	914.1	915.2	916.4	917.3	917.8	918.4	919.0	919.5	920.3	921.1
142.5°	938.4	939.5	940.7	941.8	942.7	943.3	943.8	944.4	945.0	945.6	946.2
145°	974.2	975.5	976.9	978.2	979.0	979.5	979.8	980.2	980.6	980.9	981.4
147.5°	1007.3	1008.1	1009.0	1009.9	1010.5	1010.9	1011.2	1011.7	1012.0	1012.4	1012.8
150°	1027.6	1028.1	1028.7	1029.2	1029.8	1030.1	1030.5	1030.9	1031.3	1031.7	1032.1
152.5°	1045.9	1046.1	1046.4	1046.6	1046.9	1047.1	1047.3	1047.6	1047.8	1048.4	1049.1
155°	1071.3	1070.9	1070.6	1070.1	1070.1	1070.2	1070.4	1070.7	1070.8	1071.8	1072.7
157.5°	1091.9	1091.9	1091.8	1091.8	1091.7	1091.5	1091.3	1091.1	1090.9	1092.1	1093.2
160°	1104.1	1104.0	1103.8	1103.5	1103.4	1103.2	1103.0	1102.8	1102.6	1103.8	1104.9
162.5°	1115.5	1115.0	1114.6	1114.0	1113.7	1113.5	1113.3	1113.1	1112.9	1114.2	1115.5
165°	1129.5	1128.9	1128.4	1127.8	1127.5	1127.2	1127.0	1126.9	1126.7	1128.2	1129.7
167.5°	1140.4	1139.6	1138.8	1138.1	1137.6	1137.6	1137.6	1137.6	1137.6	1139.2	1140.7
170°	1146.5	1145.8	1145.0	1144.3	1143.8	1143.8	1143.8	1143.8	1143.8	1145.4	1146.9
172.5°	1150.6	1149.6	1148.7	1147.8	1147.4	1147.5	1147.7	1147.8	1148.0	1149.5	1151.1
175°	1155.8	1154.9	1153.9	1153.0	1152.5	1152.7	1153.0	1153.1	1153.3	1154.7	1156.0
177.5°	1157.4	1156.6	1155.8	1155.1	1154.8	1154.9	1155.1	1155.2	1155.4	1156.6	1157.8
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	716.3	716.5	719.4	721.5	720.5	721.8	722.3
5°	782.5	794.4	800.6	805.3	805.6	805.9	808.6
7.5°	876.5	889.2	898.5	912.7	916.9	921.7	920.3
10°	945.1	963.9	980.1	988.6	997.8	1011.3	1000.5
12.5°	1009.2	1042.5	1067.1	1080.4	1089.2	1091.8	1086.5
15°	1114.9	1158.5	1181.9	1181.2	1210.9	1223.7	1203.6
17.5°	1211.9	1252.1	1284.2	1300.7	1325.4	1330.9	1328.4
20°	1271.2	1315.1	1340.1	1368.5	1381.4	1392.9	1394.9
22.5°	1322.4	1361.8	1388.7	1412.3	1423.1	1428.5	1431.8
25°	1375.1	1406.1	1422.3	1430.5	1433.5	1432.8	1428.5
27.5°	1371.5	1373.8	1356.1	1338.6	1322.9	1305.3	1299.2
30°	1335.8	1308.1	1258.7	1230.6	1189.5	1156.8	1170.0
32.5°	1242.2	1187.1	1131.5	1070.2	1019.5	1005.1	990.6
35°	1060.1	963.2	906.5	840.6	814.2	787.8	769.6
37.5°	857.7	782.7	715.4	672.3	645.8	629.2	620.2
40°	741.7	674.0	618.6	583.7	563.5	544.8	542.1
42.5°	649.0	586.2	544.5	516.7	497.3	489.4	483.5
45°	531.6	487.7	459.7	439.9	427.1	422.1	415.5
47.5°	450.0	419.0	397.9	384.4	374.7	371.0	370.5
50°	404.3	378.6	363.1	352.5	344.9	343.6	338.4
52.5°	370.0	347.7	335.6	326.4	320.9	317.2	315.6
55°	321.2	306.3	295.5	290.2	285.9	282.2	282.2
57.5°	281.0	268.6	261.4	256.9	255.6	253.0	251.4
60°	256.2	245.6	240.0	236.1	233.5	233.8	230.8
62.5°	232.0	225.1	219.7	215.8	212.7	212.7	212.9
65°	197.5	192.3	188.3	187.0	185.0	182.7	183.3
67.5°	167.4	162.5	159.4	157.1	156.4	155.2	157.1
70°	145.8	142.2	139.8	137.8	137.2	137.5	139.1
72.5°	126.0	123.4	121.9	121.0	119.5	119.6	120.7
75°	98.9	96.9	95.7	94.6	94.3	94.3	94.3
77.5°	72.7	72.2	71.6	70.2	70.3	70.6	70.7
80°	57.3	56.4	56.1	55.4	54.4	53.7	55.4
82.5°	42.9	41.8	41.6	41.4	39.9	39.8	41.2
85°	23.1	22.1	22.4	22.1	22.1	21.8	21.8
87.5°	12.7	12.7	12.5	12.8	12.7	12.5	13.1
90°	22.9	23.7	24.3	24.6	25.1	25.4	25.7
92.5°	25.7	26.9	27.6	27.8	28.1	28.3	28.5
95°	30.7	32.0	32.6	32.6	32.6	32.6	32.6
97.5°	32.3	33.8	34.6	34.9	35.0	35.2	35.4
100°	33.0	34.4	35.3	35.6	35.7	35.9	36.1
102.5°	42.4	37.6	35.4	35.7	36.1	36.4	36.8
105°	86.8	53.0	36.2	36.7	37.0	37.5	37.8
107.5°	270.6	245.8	220.7	195.2	169.7	144.2	118.7
110°	368.7	362.4	345.6	318.2	290.9	263.6	236.3



TEST NUMBER: P331937-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	431.3	431.4	428.5	422.8	417.0	411.2	405.4
115°	499.0	500.9	502.3	503.0	503.8	504.5	505.3
117.5°	558.4	559.9	560.8	560.9	561.0	561.2	561.4
120°	597.5	599.1	599.9	599.9	599.9	599.9	599.9
122.5°	635.4	636.5	637.1	637.2	637.4	637.5	637.7
125°	688.6	689.1	689.4	689.8	690.2	690.6	691.0
127.5°	743.0	743.6	743.7	743.3	743.0	742.5	742.2
130°	775.8	776.5	776.7	776.4	775.9	775.6	775.2
132.5°	806.7	807.4	807.5	807.0	806.5	806.0	805.5
135°	853.4	853.9	853.9	853.4	852.8	852.2	851.7
137.5°	895.5	896.4	896.6	896.3	896.0	895.5	895.2
140°	921.9	922.6	922.8	922.4	922.0	921.7	921.3
142.5°	946.8	947.4	947.4	946.9	946.4	945.9	945.4
145°	981.7	982.1	982.3	982.3	982.3	982.3	982.3
147.5°	1013.1	1013.6	1013.3	1012.4	1011.6	1010.6	1009.8
150°	1032.4	1032.9	1032.7	1032.2	1031.6	1031.0	1030.4
152.5°	1049.8	1050.5	1050.4	1049.6	1048.7	1047.8	1046.9
155°	1073.7	1074.6	1074.5	1073.4	1072.3	1071.1	1070.0
157.5°	1094.3	1095.5	1095.4	1093.8	1092.4	1090.9	1089.4
160°	1106.0	1107.2	1107.1	1105.8	1104.4	1103.1	1101.7
162.5°	1116.8	1118.1	1118.2	1117.0	1115.8	1114.7	1113.4
165°	1131.3	1132.8	1132.9	1131.5	1130.2	1128.9	1127.6
167.5°	1142.3	1143.8	1143.8	1142.3	1140.7	1139.2	1137.6
170°	1148.5	1150.0	1150.0	1148.5	1146.9	1145.4	1143.8
172.5°	1152.5	1154.1	1154.0	1152.4	1150.6	1149.0	1147.3
175°	1157.4	1158.6	1158.6	1157.0	1155.5	1154.0	1152.4
177.5°	1159.1	1160.3	1160.1	1158.6	1157.1	1155.5	1154.0
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8

(END OF REPORT)