

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331963-930

Luminaire Tested: **S123DIP-S775D365U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331963-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D365U930-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3655.4 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331963-930
CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331963-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	65	63	59
2	93	85	79	74	88	81	75	70	73	68	64	65	62	59	58	56	53	50
3	85	75	67	61	80	71	64	59	64	59	54	58	53	50	52	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39	36
5	72	59	51	45	67	57	49	43	51	45	40	46	41	37	42	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	37	32	38	33	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	24
8	57	44	36	30	54	42	35	29	38	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	22	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10687	10687	10687
5°	10737	10589	10662
10°	10665	10497	10563
15°	10541	10379	10398
20°	10394	10208	10219
25°	10200	10007	9987
30°	9984	9783	9708
35°	9759	9546	9423
40°	9524	9284	9140
45°	9266	9045	8824
50°	9008	8748	8505
55°	8668	8443	8188
60°	8325	8086	7830
65°	8023	7697	7457
70°	7578	7254	6930
75°	6924	6675	6392
80°	6248	5976	5926
85°	5483	5274	5064



TEST NUMBER: P331963-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	2.6
10°-20°	264.1	7.2
20°-30°	390.1	10.7
30°-40°	455.7	12.5
40°-50°	458.1	12.5
50°-60°	402.4	11.0
60°-70°	299.8	8.2
70°-80°	170.8	4.7
80°-90°	50.1	1.4
90°-100°	79.2	2.2
100°-110°	224.3	6.1
110°-120°	220.6	6.0
120°-130°	176.0	4.8
130°-140°	138.8	3.8
140°-150°	103.6	2.8
150°-160°	72.2	2.0
160°-170°	42.4	1.2
170°-180°	13.8	0.4
0°-30°	747.7	20.5
0°-40°	1203.3	32.9
0°-60°	2063.8	56.5
0°-90°	2584.6	70.7
90°-120°	524.1	14.3
90°-150°	942.4	25.8
90°-180°	1071.0	29.3
0°-180°	3655.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	994	989	980	988	987	94
15°	946	942	931	938	933	267
25°	859	853	843	843	841	395
35°	743	737	726	721	717	464
45°	609	605	594	584	580	470
55°	462	460	450	441	436	414
65°	315	310	302	296	293	311
75°	166	163	160	156	154	178
85°	44	43	43	41	41	49
90°	1	4	7	8	8	3
95°	10	32	171	50	33	11
105°	33	49	232	405	366	36
115°	59	74	177	388	446	58
125°	82	97	165	300	352	73
135°	96	115	163	247	285	74
145°	110	126	161	202	223	69
155°	125	135	156	177	185	57
165°	136	140	149	158	161	38
175°	142	142	143	145	145	13
180°	142	142	142	142	142	



TEST NUMBER: P331963-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	996.2	995.6	995.1	994.4	993.8	992.7	991.0	989.4	987.7	986.0	987.5
5°	993.7	992.7	991.8	990.8	989.9	988.4	986.3	984.2	982.1	980.0	981.9
7.5°	984.0	983.0	982.0	981.1	980.2	978.6	976.4	974.3	972.1	970.0	971.7
10°	975.8	974.8	973.9	972.9	972.0	970.3	967.8	965.3	962.9	960.4	962.1
12.5°	964.8	964.0	963.3	962.5	961.6	960.1	957.8	955.4	953.2	950.8	952.1
15°	945.9	945.1	944.4	943.6	942.8	941.3	938.7	936.3	933.8	931.4	932.9
17.5°	923.8	922.8	921.9	920.9	919.9	918.2	915.7	913.2	910.8	908.3	909.4
20°	907.4	906.3	905.2	904.1	902.9	901.1	898.6	896.2	893.7	891.2	892.0
22.5°	889.0	887.9	886.7	885.6	884.4	882.6	880.2	877.8	875.3	872.8	873.4
25°	858.8	857.7	856.6	855.4	854.3	852.5	849.9	847.5	845.1	842.6	842.8
27.5°	826.6	825.4	824.3	823.2	822.1	820.3	817.6	815.0	812.3	809.6	809.8
30°	803.3	802.3	801.4	800.5	799.5	797.7	795.1	792.4	789.8	787.1	787.1
32.5°	780.1	778.9	777.6	776.3	775.1	773.5	771.4	769.3	767.3	765.2	764.2
35°	742.7	741.6	740.5	739.3	738.2	736.4	733.9	731.4	729.0	726.5	725.4
37.5°	704.4	703.0	701.6	700.1	698.7	696.8	694.2	691.7	689.2	686.7	685.3
40°	677.8	676.7	675.6	674.4	673.3	671.4	668.7	666.1	663.4	660.7	659.3
42.5°	651.2	649.9	648.6	647.3	646.0	644.1	641.4	638.7	636.1	633.4	631.9
45°	608.7	607.9	607.2	606.4	605.6	604.1	601.5	599.1	596.6	594.2	591.9
47.5°	566.5	565.4	564.3	563.2	562.1	560.4	558.1	555.8	553.4	551.1	548.9
50°	537.9	536.9	535.9	535.0	534.0	532.3	529.9	527.4	524.9	522.4	520.4
52.5°	507.8	507.1	506.5	505.8	505.2	503.5	500.9	498.3	495.7	493.1	491.3
55°	461.9	461.6	461.5	461.3	461.1	459.7	457.3	454.9	452.3	449.9	447.8
57.5°	418.2	417.5	416.9	416.2	415.6	414.3	412.3	410.3	408.3	406.3	404.5
60°	386.7	386.5	386.4	386.1	386.0	384.7	382.5	380.2	377.9	375.6	373.9
62.5°	358.7	358.2	357.8	357.3	356.8	355.4	353.1	350.8	348.5	346.3	344.5
65°	315.0	314.1	313.1	312.2	311.2	309.8	307.9	306.0	304.1	302.2	300.7
67.5°	268.7	267.9	267.1	266.2	265.4	264.2	262.9	261.4	259.9	258.5	257.1
70°	240.8	239.6	238.5	237.3	236.2	235.1	233.9	232.8	231.6	230.5	229.2
72.5°	211.4	210.5	209.7	208.9	208.1	207.0	205.7	204.4	203.1	201.8	200.6
75°	166.5	165.7	164.9	164.2	163.5	162.7	162.2	161.6	161.0	160.5	159.6
77.5°	126.7	126.3	125.9	125.5	125.0	124.5	123.8	123.1	122.5	121.7	121.1
80°	100.8	100.2	99.6	99.1	98.5	98.0	97.6	97.3	96.9	96.4	96.3
82.5°	75.5	75.3	75.3	75.1	75.0	74.9	74.8	74.8	74.7	74.6	74.3
85°	44.4	44.0	43.6	43.3	42.9	42.7	42.7	42.7	42.7	42.7	42.3
87.5°	17.9	17.5	17.2	16.9	16.6	16.4	16.4	16.4	16.5	16.5	16.2
90°	0.6	1.1	1.7	2.6	3.2	3.8	4.6	5.5	6.4	7.2	6.9
92.5°	3.6	5.3	7.7	9.9	12.4	16.6	24.2	36.6	48.8	44.3	33.4
95°	9.8	10.7	13.9	18.8	26.3	37.4	62.0	104.8	152.1	170.9	138.6
97.5°	16.7	17.0	19.5	23.7	31.1	43.3	66.7	115.0	193.9	264.8	283.2
100°	21.4	21.6	23.6	27.6	34.6	45.8	66.0	108.6	184.4	272.9	329.6
102.5°	26.2	26.7	28.5	32.3	38.5	48.8	66.9	103.1	170.6	257.9	331.9
105°	33.4	34.3	36.0	39.5	44.9	53.9	69.5	99.1	153.6	231.6	314.3
107.5°	41.2	42.0	43.7	47.0	52.2	60.5	74.2	98.8	142.8	208.5	283.6
110°	46.6	47.5	49.0	52.2	57.1	65.1	78.1	100.0	138.6	195.3	264.2



TEST NUMBER: P331963-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	51.8	52.6	54.1	57.2	62.1	70.0	82.0	102.3	136.2	186.5	247.4
115°	59.0	60.3	62.0	64.8	69.7	77.5	88.5	106.0	135.4	177.2	227.1
117.5°	66.4	67.7	69.1	71.8	77.3	84.5	95.3	111.0	135.9	171.6	214.7
120°	71.4	72.3	73.8	76.6	82.1	89.3	99.7	114.6	136.9	169.1	208.3
122.5°	75.8	76.7	78.1	81.3	86.5	94.2	104.3	118.1	138.4	167.5	203.0
125°	82.1	82.7	84.4	87.6	93.0	100.9	111.0	123.6	140.9	165.3	196.2
127.5°	86.9	87.7	89.9	93.1	99.1	107.0	116.7	128.1	143.7	164.4	190.2
130°	89.9	90.7	93.4	96.8	102.9	110.6	120.2	131.1	145.5	163.6	186.9
132.5°	92.2	93.3	96.1	100.3	106.3	113.9	123.1	133.9	146.9	163.4	184.0
135°	96.2	97.3	100.5	104.8	111.0	118.7	127.6	137.5	149.0	163.1	180.1
137.5°	100.0	101.3	104.4	108.9	115.0	122.1	130.8	140.1	150.3	162.4	176.7
140°	102.6	104.0	106.9	111.5	117.2	124.5	132.8	141.5	151.2	162.2	174.6
142.5°	105.3	106.6	109.7	113.8	119.6	126.3	134.4	142.8	152.0	161.8	172.8
145°	109.7	110.6	113.2	117.6	122.5	129.1	136.6	144.3	152.4	161.0	170.2
147.5°	114.3	114.8	117.3	121.1	125.8	131.4	138.3	145.3	152.4	160.0	167.9
150°	117.2	117.6	119.8	123.6	127.6	132.8	139.4	145.5	152.4	159.1	166.2
152.5°	120.3	120.3	122.6	125.9	129.5	134.4	140.1	145.9	151.7	157.9	164.4
155°	124.7	124.7	126.5	129.4	132.6	136.6	141.5	146.1	151.0	155.9	161.6
157.5°	128.3	128.6	130.0	132.5	135.2	138.3	142.2	146.3	150.0	154.1	158.5
160°	131.1	131.1	132.2	134.5	136.6	139.4	142.9	146.3	149.5	152.7	156.5
162.5°	133.1	133.1	134.1	135.9	137.7	140.1	143.2	146.1	148.6	151.3	154.3
165°	136.2	136.0	136.6	138.0	139.2	141.2	143.5	145.5	147.2	149.3	151.6
167.5°	138.6	138.3	138.6	139.7	140.5	141.8	143.4	145.0	145.9	147.2	148.9
170°	140.0	139.4	139.7	140.6	141.2	141.8	143.2	144.3	145.0	145.8	147.2
172.5°	141.0	140.6	140.6	141.3	141.6	141.9	143.2	144.1	144.2	144.6	145.6
175°	142.0	141.8	141.5	142.0	142.0	142.4	142.9	143.5	143.2	143.2	143.7
177.5°	142.6	142.4	142.1	142.4	142.4	142.4	142.6	143.0	142.6	142.4	142.6
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P331963-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	992.9	992.9	992.9	992.9	992.9	992.9	992.9	992.9
2.5°	989.0	990.6	992.1	992.8	992.6	992.5	992.3	992.1
5°	983.8	985.7	987.7	988.4	988.0	987.7	987.2	986.8
7.5°	973.4	975.1	976.8	977.5	977.3	977.1	976.8	976.6
10°	963.8	965.5	967.2	967.9	967.5	967.1	966.8	966.4
12.5°	953.3	954.6	955.9	956.3	956.1	955.9	955.7	955.4
15°	934.4	935.9	937.4	937.6	936.5	935.3	934.3	933.1
17.5°	910.4	911.5	912.6	912.9	912.5	912.1	911.7	911.3
20°	892.8	893.5	894.3	894.4	893.8	893.2	892.7	892.1
22.5°	874.0	874.7	875.2	875.1	874.5	873.8	873.0	872.3
25°	842.9	843.2	843.3	843.2	842.6	842.0	841.5	840.9
27.5°	809.9	810.1	810.2	809.9	809.3	808.5	807.8	807.1
30°	787.1	787.1	787.1	786.4	785.1	783.7	782.4	781.1
32.5°	763.1	762.1	761.0	760.1	759.4	758.6	757.9	757.2
35°	724.2	723.1	721.9	720.9	719.9	719.0	718.0	717.1
37.5°	684.0	682.6	681.3	680.3	679.6	679.1	678.4	677.8
40°	657.7	656.2	654.7	653.5	652.8	652.0	651.3	650.5
42.5°	630.4	628.8	627.4	626.2	625.5	624.7	623.9	623.2
45°	589.6	587.3	585.1	583.4	582.5	581.6	580.6	579.7
47.5°	546.7	544.5	542.2	540.6	539.8	539.0	538.2	537.3
50°	518.3	516.2	514.1	512.5	511.4	510.2	509.1	507.9
52.5°	489.5	487.7	485.9	484.5	483.4	482.2	481.1	480.0
55°	445.7	443.6	441.6	440.0	439.0	438.1	437.2	436.3
57.5°	402.6	400.8	398.9	397.5	396.3	395.3	394.1	393.1
60°	372.2	370.5	368.8	367.5	366.5	365.6	364.6	363.7
62.5°	342.8	341.1	339.4	338.3	337.6	337.0	336.3	335.7
65°	299.1	297.7	296.1	295.1	294.5	293.9	293.3	292.8
67.5°	255.8	254.5	253.2	252.1	251.4	250.5	249.7	248.9
70°	227.9	226.5	225.2	224.0	223.1	222.2	221.2	220.2
72.5°	199.4	198.3	197.1	196.2	195.8	195.3	194.8	194.3
75°	158.6	157.7	156.7	156.0	155.4	154.8	154.3	153.7
77.5°	120.4	119.8	119.1	118.9	118.9	118.9	118.9	118.9
80°	96.1	95.9	95.7	95.6	95.6	95.6	95.6	95.6
82.5°	73.9	73.6	73.2	73.0	72.9	72.7	72.6	72.4
85°	41.9	41.6	41.2	41.0	41.0	41.0	41.0	41.0
87.5°	16.1	16.1	16.0	16.0	16.0	16.0	16.1	16.0
90°	7.2	7.5	7.7	8.3	8.1	8.3	8.6	8.3
92.5°	24.3	19.2	17.0	15.5	15.0	14.1	14.4	13.9
95°	103.7	70.3	55.0	44.7	39.2	36.6	34.6	33.4
97.5°	258.5	207.1	169.9	135.5	114.2	101.3	93.4	91.0
100°	339.7	316.3	282.7	241.7	212.6	191.6	180.3	180.7
102.5°	366.6	365.9	346.3	320.3	297.7	281.0	271.7	265.0
105°	374.5	403.3	408.8	401.4	388.1	377.2	367.9	366.5
107.5°	351.8	398.6	423.9	434.1	434.4	430.6	427.5	424.9
110°	330.2	383.2	419.5	439.7	447.8	450.0	449.5	448.9



TEST NUMBER: P331963-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	308.8	362.9	403.6	429.5	444.3	451.4	453.6	453.7
115°	280.3	330.4	372.8	404.2	425.8	438.5	444.3	445.7
117.5°	259.8	303.0	341.0	372.9	395.5	410.0	418.2	420.2
120°	248.9	287.8	322.4	351.5	374.2	390.4	397.3	399.0
122.5°	240.4	275.6	307.6	334.7	354.9	369.4	377.0	379.2
125°	229.0	260.5	288.1	311.2	329.6	342.3	349.5	351.5
127.5°	219.2	247.1	272.1	293.1	309.5	320.3	326.9	328.6
130°	212.9	238.9	262.2	281.8	297.0	307.4	313.5	315.8
132.5°	207.2	231.0	252.7	271.4	285.8	296.1	301.5	303.1
135°	199.3	219.8	238.6	254.9	269.1	277.8	282.9	284.9
137.5°	192.2	209.0	225.2	239.5	251.3	260.1	264.4	265.8
140°	188.2	202.8	216.6	229.0	240.0	248.1	252.7	252.4
142.5°	184.3	196.8	208.8	219.6	228.9	236.1	240.2	239.9
145°	179.5	189.0	198.2	206.6	213.8	219.8	222.2	222.7
147.5°	175.6	183.2	190.6	196.6	202.0	206.1	208.3	208.6
150°	172.8	179.5	185.6	191.0	195.3	198.5	200.2	200.2
152.5°	170.3	176.0	181.4	186.0	189.3	192.2	193.3	193.3
155°	166.6	171.1	175.5	178.9	181.5	183.8	184.4	184.7
157.5°	162.5	166.3	169.7	172.4	174.6	176.3	176.8	176.8
160°	160.2	163.4	166.2	168.3	170.2	172.0	172.0	171.7
162.5°	157.4	160.1	162.8	164.6	165.9	167.4	167.4	167.1
165°	153.8	155.6	157.6	159.1	160.2	161.3	161.0	161.0
167.5°	150.7	152.1	153.2	154.3	154.7	155.6	155.3	155.3
170°	148.6	149.5	150.7	151.2	151.6	152.1	151.8	151.8
172.5°	146.8	147.5	148.4	148.7	148.8	149.4	148.9	148.6
175°	144.3	144.6	145.2	145.2	145.2	145.5	145.2	145.0
177.5°	142.8	143.0	143.2	143.2	143.0	143.2	142.8	142.8
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4

(END OF REPORT)