

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332354-930

Luminaire Tested: **S123RDIP-S1000D1195U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332354-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U930-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7118.7 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	90	86	89	86	83	80	72	69	67	59	57	56	47	46	45	39
2	89	82	76	71	81	75	70	66	63	60	57	52	50	47	42	40	39	34
3	82	72	66	60	75	67	61	56	56	52	48	47	43	41	37	35	33	29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29	26
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26	22
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	24	21	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13951	13951	13951	13951
5°	16630	14011	12337	14011
10°	20764	13930	11146	13930
15°	24373	13788	10165	13788
20°	27202	13575	9330	13575
25°	26766	13351	8817	13351
30°	19240	13144	8289	13144
35°	12846	12875	7947	12875
40°	9465	12552	7593	12552
45°	7939	11985	7247	11985
50°	7005	11241	6764	11241
55°	6142	10393	6101	10393
60°	5470	9580	5591	9580
65°	4806	8706	5201	8706
70°	3770	7928	4749	7928
75°	3323	6924	4338	6924
80°	2889	5883	4265	5883
85°	2322	4730	4520	4730



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.5	1.8
10°-20°	398.2	5.6
20°-30°	625.6	8.8
30°-40°	652.7	9.2
40°-50°	558.6	7.8
50°-60°	425.7	6.0
60°-70°	272.9	3.8
70°-80°	131.3	1.8
80°-90°	38.3	0.5
90°-100°	46.4	0.7
100°-110°	220.9	3.1
110°-120°	530.6	7.5
120°-130°	675.7	9.5
130°-140°	722.0	10.1
140°-150°	675.1	9.5
150°-160°	544.6	7.7
160°-170°	351.5	4.9
170°-180°	121.1	1.7
0°-30°	1151.2	16.2
0°-40°	1803.9	25.3
0°-60°	2788.2	39.2
0°-90°	3230.6	45.4
90°-120°	797.9	11.2
90°-150°	2870.8	40.3
90°-180°	3888.0	54.6
0°-180°	7118.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1296	1296	1296	1296	1296	
5°	1539	1297	1142	1297	1539	159
15°	2187	1237	912	1237	2187	620
25°	2254	1124	742	1124	2254	969
35°	978	980	605	980	978	641
45°	522	787	476	787	522	410
55°	327	554	325	554	327	296
65°	189	342	204	342	189	186
75°	80	166	104	166	80	86
85°	19	38	37	38	19	22
90°	28	1	28	1	28	14
95°	36	58	36	58	36	30
105°	42	282	42	282	42	95
115°	557	530	557	530	557	515
125°	762	746	762	746	762	680
135°	939	929	939	929	939	724
145°	1083	1072	1083	1072	1083	676
155°	1179	1181	1179	1181	1179	544
165°	1243	1246	1243	1246	1243	351
175°	1270	1275	1270	1275	1270	121
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1380.5	1382.2	1376.5	1375.6	1368.9	1367.1	1367.1	1357.8	1352.0	1344.5	1340.0
5°	1539.1	1548.0	1543.5	1533.6	1516.9	1513.0	1502.5	1485.9	1467.0	1443.7	1432.6
7.5°	1737.3	1749.4	1744.7	1729.3	1711.9	1697.8	1668.1	1640.5	1601.7	1567.7	1538.7
10°	1899.7	1887.0	1877.0	1862.1	1845.9	1819.8	1788.8	1746.0	1696.7	1657.8	1614.6
12.5°	2021.4	2019.3	2006.6	1991.2	1968.5	1943.7	1905.5	1853.5	1796.1	1740.0	1690.4
15°	2187.2	2190.5	2182.1	2166.1	2133.9	2090.1	2032.4	2010.8	1928.6	1867.6	1806.5
17.5°	2301.9	2301.3	2300.1	2277.9	2245.0	2213.8	2160.3	2103.4	2029.0	1943.0	1860.8
20°	2374.7	2369.2	2370.2	2345.3	2320.9	2284.8	2232.7	2150.0	2089.0	1989.7	1904.8
22.5°	2372.9	2371.8	2376.0	2367.5	2349.8	2322.1	2281.0	2211.3	2133.3	2033.1	1937.6
25°	2253.7	2249.3	2275.4	2282.6	2310.9	2315.9	2303.7	2265.4	2191.6	2088.4	1970.3
27.5°	1886.2	1883.7	1932.2	1992.8	2069.6	2129.2	2187.0	2214.8	2191.6	2117.7	1999.3
30°	1548.0	1600.2	1624.6	1712.2	1809.9	1926.4	2028.5	2125.6	2149.5	2117.3	2020.1
32.5°	1285.2	1330.7	1351.1	1426.4	1517.4	1653.8	1807.0	1944.5	2041.6	2066.2	2007.8
35°	977.6	978.2	1024.7	1058.1	1142.4	1282.8	1431.5	1615.7	1798.8	1937.5	1951.9
37.5°	780.1	782.9	811.1	844.2	907.5	981.7	1112.6	1265.8	1477.3	1690.3	1815.1
40°	673.6	678.6	699.7	732.4	777.9	833.9	936.0	1080.3	1256.7	1493.6	1687.3
42.5°	605.2	613.3	624.2	649.4	677.6	730.0	812.6	924.1	1084.5	1308.6	1531.9
45°	521.5	525.9	534.3	545.9	571.4	608.1	663.6	738.5	871.6	1052.0	1275.5
47.5°	460.1	457.7	466.5	476.0	492.9	517.9	555.1	616.2	711.2	855.9	1045.5
50°	418.3	417.8	423.9	431.1	447.2	465.5	496.0	542.1	617.5	737.4	911.0
52.5°	379.3	381.4	385.7	394.7	406.3	421.1	448.5	481.7	546.5	650.0	794.8
55°	327.3	329.1	335.1	340.1	348.5	363.4	380.6	408.4	452.7	524.9	644.2
57.5°	283.4	282.7	288.5	289.8	299.1	311.4	324.7	346.3	378.4	432.0	512.3
60°	254.1	252.4	257.5	261.3	266.4	276.3	287.4	308.5	334.0	373.4	442.2
62.5°	227.5	226.7	230.4	234.2	238.4	247.4	256.8	273.0	293.2	326.4	381.0
65°	188.7	190.3	192.0	193.6	195.8	201.4	210.3	221.4	235.2	258.5	297.9
67.5°	148.2	149.9	150.5	153.9	158.7	162.2	167.5	177.4	187.1	206.8	229.2
70°	119.8	119.3	119.8	121.5	127.6	133.7	141.0	148.1	154.3	168.1	186.9
72.5°	103.0	102.0	103.5	103.8	106.7	108.4	113.0	119.8	127.6	137.1	150.6
75°	79.9	79.9	79.9	79.9	82.1	83.2	84.9	86.6	89.4	93.8	103.8
77.5°	59.0	59.1	59.9	60.5	60.9	61.6	62.6	64.2	65.2	67.6	71.9
80°	46.6	47.1	46.6	47.1	47.1	48.3	48.8	50.5	51.0	53.8	55.5
82.5°	35.1	34.7	35.1	35.6	35.6	36.8	36.9	38.1	38.2	39.6	41.3
85°	18.8	17.8	18.8	18.3	19.4	18.3	18.8	20.0	20.0	20.5	22.7
87.5°	10.1	10.9	9.9	10.3	10.2	10.5	10.4	10.2	10.9	10.4	10.2
90°	28.5	28.0	27.6	27.1	26.7	26.1	25.3	24.4	23.6	22.7	20.0
92.5°	31.5	31.2	31.0	30.7	30.4	29.7	28.3	26.9	25.6	24.2	22.2
95°	36.0	36.0	36.0	36.0	36.0	35.2	33.8	32.3	30.8	29.4	27.1
97.5°	39.1	38.8	38.6	38.4	38.2	37.3	35.5	33.8	32.2	30.5	45.7
100°	39.8	39.5	39.4	39.1	39.0	38.0	36.3	34.7	32.9	31.2	64.1
102.5°	40.5	40.2	39.8	39.4	39.1	41.4	46.6	51.9	57.1	62.3	98.2
105°	41.7	41.3	40.8	40.4	40.0	58.4	95.6	132.9	170.2	207.4	226.4
107.5°	130.9	159.0	187.0	215.2	243.2	270.9	298.2	325.5	352.9	380.3	377.2
110°	260.5	290.6	320.7	350.8	380.9	399.4	406.3	413.3	420.3	427.2	424.9



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.9	453.2	459.6	465.9	472.3	475.5	475.3	475.2	475.1	474.9	472.6
115°	556.9	556.1	555.3	554.4	553.6	552.1	550.0	547.9	545.8	543.7	541.8
117.5°	618.7	618.6	618.4	618.2	618.1	617.1	615.5	613.8	612.0	610.4	609.4
120°	661.1	661.1	661.1	661.1	661.1	660.3	658.6	657.0	655.3	653.5	653.0
122.5°	702.9	702.7	702.5	702.3	702.1	701.5	700.3	699.1	698.0	696.8	695.9
125°	761.6	761.2	760.8	760.3	759.9	759.5	759.0	758.6	758.2	757.7	756.9
127.5°	818.0	818.5	818.9	819.3	819.7	819.5	818.9	818.2	817.6	816.8	815.9
130°	854.4	854.8	855.2	855.7	856.1	855.9	855.0	854.2	853.4	852.5	851.7
132.5°	887.7	888.4	888.9	889.5	890.1	890.0	889.2	888.3	887.5	886.6	885.9
135°	938.7	939.3	940.0	940.6	941.3	941.3	940.6	940.0	939.3	938.7	937.8
137.5°	986.6	987.1	987.5	987.9	988.3	988.0	987.0	986.0	985.0	984.0	983.5
140°	1015.5	1015.9	1016.3	1016.7	1017.1	1016.9	1016.0	1015.2	1014.4	1013.5	1012.9
142.5°	1042.0	1042.5	1043.1	1043.7	1044.3	1044.2	1043.6	1042.9	1042.3	1041.5	1041.0
145°	1082.6	1082.6	1082.6	1082.6	1082.6	1082.5	1082.1	1081.7	1081.2	1080.8	1080.4
147.5°	1113.0	1113.9	1114.9	1115.9	1116.9	1117.1	1116.7	1116.3	1115.9	1115.4	1115.0
150°	1135.7	1136.4	1137.0	1137.6	1138.2	1138.3	1137.9	1137.5	1137.1	1136.7	1136.3
152.5°	1153.9	1154.9	1155.8	1156.8	1157.8	1157.9	1157.2	1156.3	1155.6	1154.9	1154.6
155°	1179.3	1180.6	1181.9	1183.1	1184.3	1184.5	1183.4	1182.3	1181.3	1180.2	1180.1
157.5°	1200.7	1202.3	1204.0	1205.7	1207.3	1207.5	1206.2	1204.9	1203.7	1202.4	1202.6
160°	1214.3	1215.8	1217.3	1218.8	1220.3	1220.3	1219.0	1217.8	1216.6	1215.3	1215.5
162.5°	1227.2	1228.5	1229.8	1231.1	1232.4	1232.4	1230.9	1229.6	1228.1	1226.6	1226.9
165°	1242.8	1244.2	1245.7	1247.2	1248.6	1248.5	1246.8	1245.2	1243.5	1241.8	1242.0
167.5°	1253.9	1255.6	1257.3	1259.0	1260.7	1260.7	1259.0	1257.3	1255.6	1253.9	1253.9
170°	1260.8	1262.4	1264.1	1265.8	1267.5	1267.5	1265.8	1264.1	1262.4	1260.8	1260.8
172.5°	1264.5	1266.4	1268.3	1270.1	1271.9	1272.0	1270.3	1268.7	1267.0	1265.3	1265.1
175°	1270.2	1271.9	1273.6	1275.3	1276.9	1277.1	1275.6	1274.1	1272.7	1271.1	1271.0
177.5°	1271.9	1273.6	1275.3	1277.0	1278.6	1278.8	1277.5	1276.1	1274.8	1273.4	1273.3
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1338.2	1336.9	1330.7	1323.6	1314.3	1308.1	1303.2	1300.6	1292.6	1282.8	1276.1
5°	1420.9	1404.3	1386.6	1364.9	1344.9	1324.4	1311.7	1296.7	1278.3	1257.8	1243.4
7.5°	1509.5	1476.8	1441.7	1405.4	1369.5	1337.4	1309.0	1284.7	1255.5	1226.0	1205.4
10°	1577.4	1529.7	1480.3	1429.8	1383.7	1340.5	1307.2	1274.5	1239.5	1205.7	1180.1
12.5°	1639.1	1576.3	1519.4	1457.3	1398.4	1346.7	1298.8	1260.3	1218.2	1182.1	1153.1
15°	1717.2	1652.9	1584.0	1489.7	1411.5	1346.1	1287.8	1237.3	1186.3	1141.8	1113.5
17.5°	1790.2	1693.4	1600.9	1522.2	1420.6	1338.8	1267.7	1207.3	1151.3	1104.2	1069.4
20°	1820.4	1726.6	1626.2	1525.8	1426.0	1334.4	1251.7	1185.1	1126.9	1073.6	1041.5
22.5°	1838.6	1732.4	1626.7	1518.7	1412.6	1317.5	1235.7	1162.5	1099.3	1048.7	1009.0
25°	1859.8	1733.3	1616.8	1510.3	1402.1	1298.9	1201.8	1124.1	1055.9	1002.0	959.9
27.5°	1873.8	1725.0	1587.3	1468.8	1359.1	1256.4	1167.3	1085.0	1015.8	958.9	913.6
30°	1876.5	1718.3	1564.6	1436.5	1324.9	1230.6	1136.3	1057.5	984.3	923.8	881.7
32.5°	1880.0	1701.9	1534.0	1397.8	1283.7	1190.3	1104.8	1029.6	954.6	895.0	851.9
35°	1865.4	1692.8	1487.5	1331.1	1216.8	1126.3	1049.2	979.8	906.0	848.3	804.5
37.5°	1802.3	1656.8	1439.3	1255.8	1136.3	1052.6	989.7	929.3	861.5	799.3	758.0
40°	1738.9	1621.2	1402.1	1210.1	1085.2	999.2	942.6	893.3	827.9	769.6	725.2
42.5°	1644.3	1572.9	1366.6	1162.1	1027.5	944.7	896.9	850.7	793.2	734.0	692.4
45°	1470.9	1480.3	1293.9	1085.8	947.6	864.5	819.5	787.3	736.3	687.5	644.7
47.5°	1253.4	1341.6	1208.5	1004.4	863.4	785.3	746.0	718.0	683.5	635.6	596.6
50°	1111.3	1237.3	1140.2	949.9	810.7	733.0	694.1	671.3	641.4	603.6	566.5
52.5°	980.4	1115.7	1057.6	889.1	753.3	682.3	644.4	625.7	601.9	566.4	532.7
55°	799.5	936.5	923.2	797.3	667.5	603.6	574.8	553.8	537.6	511.0	484.4
57.5°	646.7	776.7	783.5	695.2	591.8	528.7	503.9	488.0	477.5	457.4	432.8
60°	550.4	669.7	693.0	626.4	537.6	482.2	457.7	445.0	436.7	420.5	401.7
62.5°	470.5	572.0	598.4	550.5	485.7	433.7	414.7	402.4	396.7	382.9	366.2
65°	360.1	444.4	469.9	443.3	409.4	367.9	352.3	341.8	336.8	329.1	316.8
67.5°	270.8	332.2	360.2	341.4	329.2	303.0	293.1	287.4	283.0	277.6	267.4
70°	217.5	263.0	291.9	286.8	276.9	263.0	255.8	251.9	247.4	243.0	234.2
72.5°	174.9	206.2	233.3	235.8	227.6	224.9	218.5	216.9	214.2	208.9	204.0
75°	115.9	137.6	156.5	163.7	167.0	169.7	167.0	166.5	165.9	161.4	158.7
77.5°	76.0	87.6	99.5	111.9	117.1	120.8	121.7	123.8	122.3	119.9	118.6
80°	58.3	61.1	69.4	79.9	88.2	91.6	93.8	94.9	94.3	93.8	91.6
82.5°	42.3	44.6	48.5	55.9	62.9	68.5	69.8	69.5	70.8	71.1	69.4
85°	22.7	23.3	24.4	25.5	29.4	35.5	37.2	38.3	39.4	39.4	36.0
87.5°	10.5	9.5	9.9	9.5	10.4	10.4	12.6	14.4	15.2	13.9	14.3
90°	17.3	14.5	11.8	9.4	7.3	5.1	3.0	1.0	3.0	5.1	7.3
92.5°	20.1	18.1	16.0	15.2	15.8	16.5	17.0	17.6	17.0	16.5	15.8
95°	24.7	22.4	20.1	23.2	31.9	40.5	49.2	57.8	49.2	40.5	31.9
97.5°	60.8	76.0	91.2	100.6	104.5	108.4	112.3	116.1	112.3	108.4	104.5
100°	96.9	129.8	162.6	176.9	172.7	168.5	164.3	160.0	164.3	168.5	172.7
102.5°	134.0	169.9	205.8	222.3	219.2	216.1	213.1	210.1	213.1	216.1	219.2
105°	245.3	264.2	283.2	291.6	289.2	286.9	284.6	282.3	284.6	286.9	289.2
107.5°	374.2	371.3	368.3	365.8	363.9	362.2	360.3	358.4	360.3	362.2	363.9
110°	422.6	420.3	417.9	416.0	414.3	412.5	410.9	409.2	410.9	412.5	414.3



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	470.3	468.0	465.7	463.7	462.3	460.7	459.2	457.7	459.2	460.7	462.3
115°	539.9	538.0	536.1	534.5	533.3	532.0	530.8	529.5	530.8	532.0	533.3
117.5°	608.5	607.5	606.5	605.3	603.7	602.1	600.5	599.0	600.5	602.1	603.7
120°	652.3	651.7	651.1	649.8	647.9	646.0	644.1	642.2	644.1	646.0	647.9
122.5°	695.2	694.4	693.6	692.4	690.8	689.3	687.7	686.2	687.7	689.3	690.8
125°	756.1	755.2	754.4	753.2	751.5	749.7	748.1	746.4	748.1	749.7	751.5
127.5°	814.9	813.8	812.9	811.5	809.8	808.1	806.4	804.8	806.4	808.1	809.8
130°	850.8	849.9	849.1	847.8	846.2	844.5	842.9	841.1	842.9	844.5	846.2
132.5°	885.3	884.6	883.9	882.7	881.0	879.4	877.7	876.0	877.7	879.4	881.0
135°	937.0	936.2	935.3	934.3	933.0	931.7	930.5	929.2	930.5	931.7	933.0
137.5°	983.1	982.6	982.1	981.1	979.5	977.9	976.3	974.7	976.3	977.9	979.5
140°	1012.3	1011.6	1011.0	1010.1	1008.8	1007.5	1006.2	1005.0	1006.2	1007.5	1008.8
142.5°	1040.3	1039.7	1039.0	1038.1	1036.8	1035.6	1034.3	1033.1	1034.3	1035.6	1036.8
145°	1079.9	1079.5	1079.1	1078.2	1076.7	1075.2	1073.7	1072.3	1073.7	1075.2	1076.7
147.5°	1114.6	1114.2	1113.8	1113.0	1112.1	1111.2	1110.2	1109.2	1110.2	1111.2	1112.1
150°	1135.8	1135.4	1135.0	1134.5	1133.8	1133.2	1132.5	1132.0	1132.5	1133.2	1133.8
152.5°	1154.4	1154.1	1153.8	1153.6	1153.2	1153.0	1152.7	1152.4	1152.7	1153.0	1153.2
155°	1179.8	1179.6	1179.4	1179.5	1179.9	1180.3	1180.8	1181.2	1180.8	1180.3	1179.9
157.5°	1202.8	1203.1	1203.2	1203.4	1203.4	1203.5	1203.5	1203.5	1203.5	1203.5	1203.4
160°	1215.7	1215.9	1216.1	1216.3	1216.6	1216.8	1217.0	1217.2	1217.0	1216.8	1216.6
162.5°	1227.1	1227.3	1227.5	1227.8	1228.4	1229.0	1229.6	1230.0	1229.6	1229.0	1228.4
165°	1242.2	1242.4	1242.7	1243.1	1243.7	1244.3	1245.0	1245.6	1245.0	1244.3	1243.7
167.5°	1253.9	1253.9	1253.9	1254.3	1255.2	1256.1	1256.9	1257.8	1256.9	1256.1	1255.2
170°	1260.8	1260.8	1260.8	1261.2	1262.0	1262.9	1263.7	1264.5	1263.7	1262.9	1262.0
172.5°	1264.9	1264.8	1264.6	1265.0	1266.1	1267.1	1268.1	1269.1	1268.1	1267.1	1266.1
175°	1270.7	1270.6	1270.3	1270.7	1271.8	1272.8	1273.9	1275.0	1273.9	1272.8	1271.8
177.5°	1273.1	1272.9	1272.8	1273.1	1274.0	1274.8	1275.6	1276.5	1275.6	1274.8	1274.0
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1273.9	1268.1	1264.1	1255.2	1249.5	1243.2	1237.1	1241.0	1240.6	1240.2	1240.2
5°	1231.2	1218.4	1206.8	1191.8	1182.3	1170.7	1161.8	1160.7	1162.9	1155.2	1150.7
7.5°	1188.8	1171.3	1154.9	1138.3	1120.8	1106.8	1098.0	1093.9	1088.3	1083.5	1078.5
10°	1159.0	1138.6	1122.4	1101.9	1083.0	1066.4	1055.9	1048.6	1044.7	1040.9	1033.6
12.5°	1128.5	1108.3	1087.9	1064.6	1046.7	1027.4	1019.5	1011.4	1004.0	999.6	989.7
15°	1083.6	1057.5	1035.9	1011.5	991.5	972.7	961.6	945.4	943.2	937.7	927.7
17.5°	1038.7	1010.3	980.5	962.5	939.9	920.2	903.4	898.0	882.1	876.1	867.4
20°	1003.1	977.1	954.3	930.5	897.7	879.4	866.1	858.9	846.1	838.4	832.8
22.5°	972.5	946.0	919.7	891.9	864.9	844.3	834.6	823.4	816.4	805.5	799.5
25°	928.8	899.9	868.3	838.4	819.0	803.4	787.9	777.9	767.9	762.9	751.8
27.5°	878.0	847.8	818.2	795.5	771.7	756.4	742.2	733.4	721.4	713.0	706.9
30°	850.0	814.5	789.0	768.4	737.9	723.5	713.0	701.9	693.0	684.1	678.0
32.5°	817.6	785.2	761.0	735.6	712.2	696.4	682.8	673.0	665.4	657.0	650.9
35°	766.8	739.6	714.6	689.1	671.9	655.8	639.8	631.4	624.2	616.4	610.9
37.5°	720.8	695.5	671.7	647.5	626.1	613.1	600.1	593.8	584.0	578.8	573.2
40°	692.4	667.5	642.0	618.6	596.5	586.4	574.8	565.4	556.5	552.6	546.5
42.5°	661.4	636.4	614.9	589.8	571.6	558.1	547.3	537.0	530.4	524.6	521.2
45°	615.3	593.1	572.0	547.1	529.9	518.2	506.0	496.6	490.5	486.6	480.5
47.5°	570.6	548.4	527.0	505.2	488.6	475.2	463.1	456.5	448.4	443.7	439.5
50°	538.2	518.2	495.5	475.5	458.9	445.6	435.5	427.2	420.0	413.9	411.2
52.5°	508.4	487.1	467.5	448.9	431.3	416.2	407.2	398.4	393.0	386.0	382.7
55°	459.4	438.9	422.2	403.9	386.7	374.0	362.9	355.1	349.5	341.8	337.4
57.5°	413.4	394.9	375.0	359.2	341.4	330.7	321.5	311.0	304.2	298.1	293.8
60°	382.3	361.2	344.0	329.1	313.5	299.6	291.3	283.0	275.7	269.6	265.8
62.5°	349.8	331.5	315.1	298.8	284.6	272.6	262.9	255.9	249.6	245.6	241.8
65°	300.2	285.8	269.1	255.8	242.5	233.6	225.8	219.7	215.2	212.5	209.2
67.5°	254.5	240.4	225.9	212.9	204.0	197.2	192.1	186.9	184.7	181.1	178.9
70°	224.7	210.3	197.5	187.5	178.6	173.7	170.3	166.5	164.2	159.8	157.6
72.5°	192.3	181.9	172.7	164.4	157.4	152.8	148.5	143.8	140.2	135.3	133.1
75°	151.5	142.0	134.9	129.3	124.8	118.7	112.6	107.6	106.0	104.3	103.8
77.5°	112.2	106.2	101.0	96.3	90.7	86.3	85.0	83.9	83.6	82.7	82.7
80°	88.2	82.7	78.8	73.2	69.9	69.9	69.9	68.8	69.4	69.4	69.4
82.5°	65.6	60.5	58.4	56.3	55.7	56.2	56.2	56.3	56.0	56.9	56.5
85°	33.8	34.4	35.5	35.0	35.5	35.5	36.6	36.0	36.6	35.5	36.6
87.5°	14.3	16.1	17.1	18.1	19.1	19.2	19.8	20.0	20.6	20.8	20.9
90°	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.4	25.3	26.1	26.7
92.5°	15.2	16.0	18.1	20.1	22.2	24.2	25.6	26.9	28.3	29.7	30.4
95°	23.2	20.1	22.4	24.7	27.1	29.4	30.8	32.3	33.8	35.2	36.0
97.5°	100.6	91.2	76.0	60.8	45.7	30.5	32.2	33.8	35.5	37.3	38.2
100°	176.9	162.6	129.8	96.9	64.1	31.2	32.9	34.7	36.3	38.0	39.0
102.5°	222.3	205.8	169.9	134.0	98.2	62.3	57.1	51.9	46.6	41.4	39.1
105°	291.6	283.2	264.2	245.3	226.4	207.4	170.2	132.9	95.6	58.4	40.0
107.5°	365.8	368.3	371.3	374.2	377.2	380.3	352.9	325.5	298.2	270.9	243.2
110°	416.0	417.9	420.3	422.6	424.9	427.2	420.3	413.3	406.3	399.4	380.9



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	463.7	465.7	468.0	470.3	472.6	474.9	475.1	475.2	475.3	475.5	472.3
115°	534.5	536.1	538.0	539.9	541.8	543.7	545.8	547.9	550.0	552.1	553.6
117.5°	605.3	606.5	607.5	608.5	609.4	610.4	612.0	613.8	615.5	617.1	618.1
120°	649.8	651.1	651.7	652.3	653.0	653.5	655.3	657.0	658.6	660.3	661.1
122.5°	692.4	693.6	694.4	695.2	695.9	696.8	698.0	699.1	700.3	701.5	702.1
125°	753.2	754.4	755.2	756.1	756.9	757.7	758.2	758.6	759.0	759.5	759.9
127.5°	811.5	812.9	813.8	814.9	815.9	816.8	817.6	818.2	818.9	819.5	819.7
130°	847.8	849.1	849.9	850.8	851.7	852.5	853.4	854.2	855.0	855.9	856.1
132.5°	882.7	883.9	884.6	885.3	885.9	886.6	887.5	888.3	889.2	890.0	890.1
135°	934.3	935.3	936.2	937.0	937.8	938.7	939.3	940.0	940.6	941.3	941.3
137.5°	981.1	982.1	982.6	983.1	983.5	984.0	985.0	986.0	987.0	988.0	988.3
140°	1010.1	1011.0	1011.6	1012.3	1012.9	1013.5	1014.4	1015.2	1016.0	1016.9	1017.1
142.5°	1038.1	1039.0	1039.7	1040.3	1041.0	1041.5	1042.3	1042.9	1043.6	1044.2	1044.3
145°	1078.2	1079.1	1079.5	1079.9	1080.4	1080.8	1081.2	1081.7	1082.1	1082.5	1082.6
147.5°	1113.0	1113.8	1114.2	1114.6	1115.0	1115.4	1115.9	1116.3	1116.7	1117.1	1116.9
150°	1134.5	1135.0	1135.4	1135.8	1136.3	1136.7	1137.1	1137.5	1137.9	1138.3	1138.2
152.5°	1153.6	1153.8	1154.1	1154.4	1154.6	1154.9	1155.6	1156.3	1157.2	1157.9	1157.8
155°	1179.5	1179.4	1179.6	1179.8	1180.1	1180.2	1181.3	1182.3	1183.4	1184.5	1184.3
157.5°	1203.4	1203.2	1203.1	1202.8	1202.6	1202.4	1203.7	1204.9	1206.2	1207.5	1207.3
160°	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3	1216.6	1217.8	1219.0	1220.3	1220.3
162.5°	1227.8	1227.5	1227.3	1227.1	1226.9	1226.6	1228.1	1229.6	1230.9	1232.4	1232.4
165°	1243.1	1242.7	1242.4	1242.2	1242.0	1241.8	1243.5	1245.2	1246.8	1248.5	1248.6
167.5°	1254.3	1253.9	1253.9	1253.9	1253.9	1253.9	1255.6	1257.3	1259.0	1260.7	1260.7
170°	1261.2	1260.8	1260.8	1260.8	1260.8	1260.8	1262.4	1264.1	1265.8	1267.5	1267.5
172.5°	1265.0	1264.6	1264.8	1264.9	1265.1	1265.3	1267.0	1268.7	1270.3	1272.0	1271.9
175°	1270.7	1270.3	1270.6	1270.7	1271.0	1271.1	1272.7	1274.1	1275.6	1277.1	1276.9
177.5°	1273.1	1272.8	1272.9	1273.1	1273.3	1273.4	1274.8	1276.1	1277.5	1278.8	1278.6
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1234.9	1234.4	1234.9	1233.1	1234.9	1234.4	1234.9	1240.2	1240.2	1240.6	1241.0
5°	1149.1	1148.5	1146.9	1141.8	1146.9	1148.5	1149.1	1150.7	1155.2	1162.9	1160.7
7.5°	1074.2	1073.4	1068.5	1068.6	1068.5	1073.4	1074.2	1078.5	1083.5	1088.3	1093.9
10°	1029.8	1030.3	1023.7	1019.8	1023.7	1030.3	1029.8	1033.6	1040.9	1044.7	1048.6
12.5°	986.8	984.1	978.8	974.5	978.8	984.1	986.8	989.7	999.6	1004.0	1011.4
15°	929.9	924.4	911.0	912.2	911.0	924.4	929.9	927.7	937.7	943.2	945.4
17.5°	863.0	858.9	858.7	850.9	858.7	858.9	863.0	867.4	876.1	882.1	898.0
20°	823.9	821.2	822.2	814.5	822.2	821.2	823.9	832.8	838.4	846.1	858.9
22.5°	793.3	790.5	785.9	783.4	785.9	790.5	793.3	799.5	805.5	816.4	823.4
25°	748.4	744.0	739.6	742.4	739.6	744.0	748.4	751.8	762.9	767.9	777.9
27.5°	703.7	700.3	695.9	695.3	695.9	700.3	703.7	706.9	713.0	721.4	733.4
30°	675.2	671.9	669.7	666.9	669.7	671.9	675.2	678.0	684.1	693.0	701.9
32.5°	646.4	645.7	641.7	641.2	641.7	645.7	646.4	650.9	657.0	665.4	673.0
35°	608.6	605.4	604.2	604.8	604.2	605.4	608.6	610.9	616.4	624.2	631.4
37.5°	572.8	568.3	566.4	564.4	566.4	568.3	572.8	573.2	578.8	584.0	593.8
40°	547.1	542.7	541.5	540.4	541.5	542.7	547.1	546.5	552.6	556.5	565.4
42.5°	518.2	516.4	515.8	513.8	515.8	516.4	518.2	521.2	524.6	530.4	537.0
45°	478.8	478.3	474.9	476.1	474.9	478.3	478.8	480.5	486.6	490.5	496.6
47.5°	437.3	434.9	432.5	434.1	432.5	434.9	437.3	439.5	443.7	448.4	456.5
50°	409.0	407.8	402.8	403.9	402.8	407.8	409.0	411.2	413.9	420.0	427.2
52.5°	380.5	376.3	374.4	373.7	374.4	376.3	380.5	382.7	386.0	393.0	398.4
55°	333.5	328.5	326.3	325.1	326.3	328.5	333.5	337.4	341.8	349.5	355.1
57.5°	287.3	285.9	284.2	285.4	284.2	285.9	287.3	293.8	298.1	304.2	311.0
60°	260.2	260.2	260.2	259.7	260.2	260.2	260.2	265.8	269.6	275.7	283.0
62.5°	239.4	238.0	237.6	238.4	237.6	238.0	239.4	241.8	245.6	249.6	255.9
65°	207.5	206.9	204.7	204.2	204.7	206.9	207.5	209.2	212.5	215.2	219.7
67.5°	177.4	175.5	174.8	174.0	174.8	175.5	177.4	178.9	181.1	184.7	186.9
70°	154.8	153.7	150.3	150.9	150.3	153.7	154.8	157.6	159.8	164.2	166.5
72.5°	130.4	129.3	128.6	127.8	128.6	129.3	130.4	133.1	135.3	140.2	143.8
75°	103.2	102.6	102.1	104.3	102.1	102.6	103.2	103.8	104.3	106.0	107.6
77.5°	82.7	82.7	83.0	82.1	83.0	82.7	82.7	82.7	82.7	83.6	83.9
80°	69.4	69.4	68.8	68.8	68.8	69.4	69.4	69.4	69.4	69.4	68.8
82.5°	55.6	56.0	56.3	55.5	56.3	56.0	55.6	56.5	56.9	56.0	56.3
85°	36.6	36.0	37.2	36.6	37.2	36.0	36.6	36.6	35.5	36.6	36.0
87.5°	21.9	21.0	21.1	21.7	21.1	21.0	21.9	20.9	20.8	20.6	20.0
90°	27.1	27.6	28.0	28.5	28.0	27.6	27.1	26.7	26.1	25.3	24.4
92.5°	30.7	31.0	31.2	31.5	31.2	31.0	30.7	30.4	29.7	28.3	26.9
95°	36.0	36.0	36.0	36.0	36.0	36.0	36.0	36.0	35.2	33.8	32.3
97.5°	38.4	38.6	38.8	39.1	38.8	38.6	38.4	38.2	37.3	35.5	33.8
100°	39.1	39.4	39.5	39.8	39.5	39.4	39.1	39.0	38.0	36.3	34.7
102.5°	39.4	39.8	40.2	40.5	40.2	39.8	39.4	39.1	41.4	46.6	51.9
105°	40.4	40.8	41.3	41.7	41.3	40.8	40.4	40.0	58.4	95.6	132.9
107.5°	215.2	187.0	159.0	130.9	159.0	187.0	215.2	243.2	270.9	298.2	325.5
110°	350.8	320.7	290.6	260.5	290.6	320.7	350.8	380.9	399.4	406.3	413.3



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	465.9	459.6	453.2	446.9	453.2	459.6	465.9	472.3	475.5	475.3	475.2
115°	554.4	555.3	556.1	556.9	556.1	555.3	554.4	553.6	552.1	550.0	547.9
117.5°	618.2	618.4	618.6	618.7	618.6	618.4	618.2	618.1	617.1	615.5	613.8
120°	661.1	661.1	661.1	661.1	661.1	661.1	661.1	661.1	660.3	658.6	657.0
122.5°	702.3	702.5	702.7	702.9	702.7	702.5	702.3	702.1	701.5	700.3	699.1
125°	760.3	760.8	761.2	761.6	761.2	760.8	760.3	759.9	759.5	759.0	758.6
127.5°	819.3	818.9	818.5	818.0	818.5	818.9	819.3	819.7	819.5	818.9	818.2
130°	855.7	855.2	854.8	854.4	854.8	855.2	855.7	856.1	855.9	855.0	854.2
132.5°	889.5	888.9	888.4	887.7	888.4	888.9	889.5	890.1	890.0	889.2	888.3
135°	940.6	940.0	939.3	938.7	939.3	940.0	940.6	941.3	941.3	940.6	940.0
137.5°	987.9	987.5	987.1	986.6	987.1	987.5	987.9	988.3	988.0	987.0	986.0
140°	1016.7	1016.3	1015.9	1015.5	1015.9	1016.3	1016.7	1017.1	1016.9	1016.0	1015.2
142.5°	1043.7	1043.1	1042.5	1042.0	1042.5	1043.1	1043.7	1044.3	1044.2	1043.6	1042.9
145°	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.6	1082.5	1082.1	1081.7
147.5°	1115.9	1114.9	1113.9	1113.0	1113.9	1114.9	1115.9	1116.9	1117.1	1116.7	1116.3
150°	1137.6	1137.0	1136.4	1135.7	1136.4	1137.0	1137.6	1138.2	1138.3	1137.9	1137.5
152.5°	1156.8	1155.8	1154.9	1153.9	1154.9	1155.8	1156.8	1157.8	1157.9	1157.2	1156.3
155°	1183.1	1181.9	1180.6	1179.3	1180.6	1181.9	1183.1	1184.3	1184.5	1183.4	1182.3
157.5°	1205.7	1204.0	1202.3	1200.7	1202.3	1204.0	1205.7	1207.3	1207.5	1206.2	1204.9
160°	1218.8	1217.3	1215.8	1214.3	1215.8	1217.3	1218.8	1220.3	1220.3	1219.0	1217.8
162.5°	1231.1	1229.8	1228.5	1227.2	1228.5	1229.8	1231.1	1232.4	1232.4	1230.9	1229.6
165°	1247.2	1245.7	1244.2	1242.8	1244.2	1245.7	1247.2	1248.6	1248.5	1246.8	1245.2
167.5°	1259.0	1257.3	1255.6	1253.9	1255.6	1257.3	1259.0	1260.7	1260.7	1259.0	1257.3
170°	1265.8	1264.1	1262.4	1260.8	1262.4	1264.1	1265.8	1267.5	1267.5	1265.8	1264.1
172.5°	1270.1	1268.3	1266.4	1264.5	1266.4	1268.3	1270.1	1271.9	1272.0	1270.3	1268.7
175°	1275.3	1273.6	1271.9	1270.2	1271.9	1273.6	1275.3	1276.9	1277.1	1275.6	1274.1
177.5°	1277.0	1275.3	1273.6	1271.9	1273.6	1275.3	1277.0	1278.6	1278.8	1277.5	1276.1
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1237.1	1243.2	1249.5	1255.2	1264.1	1268.1	1273.9	1276.1	1282.8	1292.6	1300.6
5°	1161.8	1170.7	1182.3	1191.8	1206.8	1218.4	1231.2	1243.4	1257.8	1278.3	1296.7
7.5°	1098.0	1106.8	1120.8	1138.3	1154.9	1171.3	1188.8	1205.4	1226.0	1255.5	1284.7
10°	1055.9	1066.4	1083.0	1101.9	1122.4	1138.6	1159.0	1180.1	1205.7	1239.5	1274.5
12.5°	1019.5	1027.4	1046.7	1064.6	1087.9	1108.3	1128.5	1153.1	1182.1	1218.2	1260.3
15°	961.6	972.7	991.5	1011.5	1035.9	1057.5	1083.6	1113.5	1141.8	1186.3	1237.3
17.5°	903.4	920.2	939.9	962.5	980.5	1010.3	1038.7	1069.4	1104.2	1151.3	1207.3
20°	866.1	879.4	897.7	930.5	954.3	977.1	1003.1	1041.5	1073.6	1126.9	1185.1
22.5°	834.6	844.3	864.9	891.9	919.7	946.0	972.5	1009.0	1048.7	1099.3	1162.5
25°	787.9	803.4	819.0	838.4	868.3	899.9	928.8	959.9	1002.0	1055.9	1124.1
27.5°	742.2	756.4	771.7	795.5	818.2	847.8	878.0	913.6	958.9	1015.8	1085.0
30°	713.0	723.5	737.9	768.4	789.0	814.5	850.0	881.7	923.8	984.3	1057.5
32.5°	682.8	696.4	712.2	735.6	761.0	785.2	817.6	851.9	895.0	954.6	1029.6
35°	639.8	655.8	671.9	689.1	714.6	739.6	766.8	804.5	848.3	906.0	979.8
37.5°	600.1	613.1	626.1	647.5	671.7	695.5	720.8	758.0	799.3	861.5	929.3
40°	574.8	586.4	596.5	618.6	642.0	667.5	692.4	725.2	769.6	827.9	893.3
42.5°	547.3	558.1	571.6	589.8	614.9	636.4	661.4	692.4	734.0	793.2	850.7
45°	506.0	518.2	529.9	547.1	572.0	593.1	615.3	644.7	687.5	736.3	787.3
47.5°	463.1	475.2	488.6	505.2	527.0	548.4	570.6	596.6	635.6	683.5	718.0
50°	435.5	445.6	458.9	475.5	495.5	518.2	538.2	566.5	603.6	641.4	671.3
52.5°	407.2	416.2	431.3	448.9	467.5	487.1	508.4	532.7	566.4	601.9	625.7
55°	362.9	374.0	386.7	403.9	422.2	438.9	459.4	484.4	511.0	537.6	553.8
57.5°	321.5	330.7	341.4	359.2	375.0	394.9	413.4	432.8	457.4	477.5	488.0
60°	291.3	299.6	313.5	329.1	344.0	361.2	382.3	401.7	420.5	436.7	445.0
62.5°	262.9	272.6	284.6	298.8	315.1	331.5	349.8	366.2	382.9	396.7	402.4
65°	225.8	233.6	242.5	255.8	269.1	285.8	300.2	316.8	329.1	336.8	341.8
67.5°	192.1	197.2	204.0	212.9	225.9	240.4	254.5	267.4	277.6	283.0	287.4
70°	170.3	173.7	178.6	187.5	197.5	210.3	224.7	234.2	243.0	247.4	251.9
72.5°	148.5	152.8	157.4	164.4	172.7	181.9	192.3	204.0	208.9	214.2	216.9
75°	112.6	118.7	124.8	129.3	134.9	142.0	151.5	158.7	161.4	165.9	166.5
77.5°	85.0	86.3	90.7	96.3	101.0	106.2	112.2	118.6	119.9	122.3	123.8
80°	69.9	69.9	69.9	73.2	78.8	82.7	88.2	91.6	93.8	94.3	94.9
82.5°	56.2	56.2	55.7	56.3	58.4	60.5	65.6	69.4	71.1	70.8	69.5
85°	36.6	35.5	35.5	35.0	35.5	34.4	33.8	36.0	39.4	39.4	38.3
87.5°	19.8	19.2	19.1	18.1	17.1	16.1	14.3	14.3	13.9	15.2	14.4
90°	23.6	22.7	20.0	17.3	14.5	11.8	9.4	7.3	5.1	3.0	1.0
92.5°	25.6	24.2	22.2	20.1	18.1	16.0	15.2	15.8	16.5	17.0	17.6
95°	30.8	29.4	27.1	24.7	22.4	20.1	23.2	31.9	40.5	49.2	57.8
97.5°	32.2	30.5	45.7	60.8	76.0	91.2	100.6	104.5	108.4	112.3	116.1
100°	32.9	31.2	64.1	96.9	129.8	162.6	176.9	172.7	168.5	164.3	160.0
102.5°	57.1	62.3	98.2	134.0	169.9	205.8	222.3	219.2	216.1	213.1	210.1
105°	170.2	207.4	226.4	245.3	264.2	283.2	291.6	289.2	286.9	284.6	282.3
107.5°	352.9	380.3	377.2	374.2	371.3	368.3	365.8	363.9	362.2	360.3	358.4
110°	420.3	427.2	424.9	422.6	420.3	417.9	416.0	414.3	412.5	410.9	409.2



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	475.1	474.9	472.6	470.3	468.0	465.7	463.7	462.3	460.7	459.2	457.7
115°	545.8	543.7	541.8	539.9	538.0	536.1	534.5	533.3	532.0	530.8	529.5
117.5°	612.0	610.4	609.4	608.5	607.5	606.5	605.3	603.7	602.1	600.5	599.0
120°	655.3	653.5	653.0	652.3	651.7	651.1	649.8	647.9	646.0	644.1	642.2
122.5°	698.0	696.8	695.9	695.2	694.4	693.6	692.4	690.8	689.3	687.7	686.2
125°	758.2	757.7	756.9	756.1	755.2	754.4	753.2	751.5	749.7	748.1	746.4
127.5°	817.6	816.8	815.9	814.9	813.8	812.9	811.5	809.8	808.1	806.4	804.8
130°	853.4	852.5	851.7	850.8	849.9	849.1	847.8	846.2	844.5	842.9	841.1
132.5°	887.5	886.6	885.9	885.3	884.6	883.9	882.7	881.0	879.4	877.7	876.0
135°	939.3	938.7	937.8	937.0	936.2	935.3	934.3	933.0	931.7	930.5	929.2
137.5°	985.0	984.0	983.5	983.1	982.6	982.1	981.1	979.5	977.9	976.3	974.7
140°	1014.4	1013.5	1012.9	1012.3	1011.6	1011.0	1010.1	1008.8	1007.5	1006.2	1005.0
142.5°	1042.3	1041.5	1041.0	1040.3	1039.7	1039.0	1038.1	1036.8	1035.6	1034.3	1033.1
145°	1081.2	1080.8	1080.4	1079.9	1079.5	1079.1	1078.2	1076.7	1075.2	1073.7	1072.3
147.5°	1115.9	1115.4	1115.0	1114.6	1114.2	1113.8	1113.0	1112.1	1111.2	1110.2	1109.2
150°	1137.1	1136.7	1136.3	1135.8	1135.4	1135.0	1134.5	1133.8	1133.2	1132.5	1132.0
152.5°	1155.6	1154.9	1154.6	1154.4	1154.1	1153.8	1153.6	1153.2	1153.0	1152.7	1152.4
155°	1181.3	1180.2	1180.1	1179.8	1179.6	1179.4	1179.5	1179.9	1180.3	1180.8	1181.2
157.5°	1203.7	1202.4	1202.6	1202.8	1203.1	1203.2	1203.4	1203.4	1203.5	1203.5	1203.5
160°	1216.6	1215.3	1215.5	1215.7	1215.9	1216.1	1216.3	1216.6	1216.8	1217.0	1217.2
162.5°	1228.1	1226.6	1226.9	1227.1	1227.3	1227.5	1227.8	1228.4	1229.0	1229.6	1230.0
165°	1243.5	1241.8	1242.0	1242.2	1242.4	1242.7	1243.1	1243.7	1244.3	1245.0	1245.6
167.5°	1255.6	1253.9	1253.9	1253.9	1253.9	1253.9	1254.3	1255.2	1256.1	1256.9	1257.8
170°	1262.4	1260.8	1260.8	1260.8	1260.8	1260.8	1261.2	1262.0	1262.9	1263.7	1264.5
172.5°	1267.0	1265.3	1265.1	1264.9	1264.8	1264.6	1265.0	1266.1	1267.1	1268.1	1269.1
175°	1272.7	1271.1	1271.0	1270.7	1270.6	1270.3	1270.7	1271.8	1272.8	1273.9	1275.0
177.5°	1274.8	1273.4	1273.3	1273.1	1272.9	1272.8	1273.1	1274.0	1274.8	1275.6	1276.5
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1303.2	1308.1	1314.3	1323.6	1330.7	1336.9	1338.2	1340.0	1344.5	1352.0	1357.8
5°	1311.7	1324.4	1344.9	1364.9	1386.6	1404.3	1420.9	1432.6	1443.7	1467.0	1485.9
7.5°	1309.0	1337.4	1369.5	1405.4	1441.7	1476.8	1509.5	1538.7	1567.7	1601.7	1640.5
10°	1307.2	1340.5	1383.7	1429.8	1480.3	1529.7	1577.4	1614.6	1657.8	1696.7	1746.0
12.5°	1298.8	1346.7	1398.4	1457.3	1519.4	1576.3	1639.1	1690.4	1740.0	1796.1	1853.5
15°	1287.8	1346.1	1411.5	1489.7	1584.0	1652.9	1717.2	1806.5	1867.6	1928.6	2010.8
17.5°	1267.7	1338.8	1420.6	1522.2	1600.9	1693.4	1790.2	1860.8	1943.0	2029.0	2103.4
20°	1251.7	1334.4	1426.0	1525.8	1626.2	1726.6	1820.4	1904.8	1989.7	2089.0	2150.0
22.5°	1235.7	1317.5	1412.6	1518.7	1626.7	1732.4	1838.6	1937.6	2033.1	2133.3	2211.3
25°	1201.8	1298.9	1402.1	1510.3	1616.8	1733.3	1859.8	1970.3	2088.4	2191.6	2265.4
27.5°	1167.3	1256.4	1359.1	1468.8	1587.3	1725.0	1873.8	1999.3	2117.7	2191.6	2214.8
30°	1136.3	1230.6	1324.9	1436.5	1564.6	1718.3	1876.5	2020.1	2117.3	2149.5	2125.6
32.5°	1104.8	1190.3	1283.7	1397.8	1534.0	1701.9	1880.0	2007.8	2066.2	2041.6	1944.5
35°	1049.2	1126.3	1216.8	1331.1	1487.5	1692.8	1865.4	1951.9	1937.5	1798.8	1615.7
37.5°	989.7	1052.6	1136.3	1255.8	1439.3	1656.8	1802.3	1815.1	1690.3	1477.3	1265.8
40°	942.6	999.2	1085.2	1210.1	1402.1	1621.2	1738.9	1687.3	1493.6	1256.7	1080.3
42.5°	896.9	944.7	1027.5	1162.1	1366.6	1572.9	1644.3	1531.9	1308.6	1084.5	924.1
45°	819.5	864.5	947.6	1085.8	1293.9	1480.3	1470.9	1275.5	1052.0	871.6	738.5
47.5°	746.0	785.3	863.4	1004.4	1208.5	1341.6	1253.4	1045.5	855.9	711.2	616.2
50°	694.1	733.0	810.7	949.9	1140.2	1237.3	1111.3	911.0	737.4	617.5	542.1
52.5°	644.4	682.3	753.3	889.1	1057.6	1115.7	980.4	794.8	650.0	546.5	481.7
55°	574.8	603.6	667.5	797.3	923.2	936.5	799.5	644.2	524.9	452.7	408.4
57.5°	503.9	528.7	591.8	695.2	783.5	776.7	646.7	512.3	432.0	378.4	346.3
60°	457.7	482.2	537.6	626.4	693.0	669.7	550.4	442.2	373.4	334.0	308.5
62.5°	414.7	433.7	485.7	550.5	598.4	572.0	470.5	381.0	326.4	293.2	273.0
65°	352.3	367.9	409.4	443.3	469.9	444.4	360.1	297.9	258.5	235.2	221.4
67.5°	293.1	303.0	329.2	341.4	360.2	332.2	270.8	229.2	206.8	187.1	177.4
70°	255.8	263.0	276.9	286.8	291.9	263.0	217.5	186.9	168.1	154.3	148.1
72.5°	218.5	224.9	227.6	235.8	233.3	206.2	174.9	150.6	137.1	127.6	119.8
75°	167.0	169.7	167.0	163.7	156.5	137.6	115.9	103.8	93.8	89.4	86.6
77.5°	121.7	120.8	117.1	111.9	99.5	87.6	76.0	71.9	67.6	65.2	64.2
80°	93.8	91.6	88.2	79.9	69.4	61.1	58.3	55.5	53.8	51.0	50.5
82.5°	69.8	68.5	62.9	55.9	48.5	44.6	42.3	41.3	39.6	38.2	38.1
85°	37.2	35.5	29.4	25.5	24.4	23.3	22.7	22.7	20.5	20.0	20.0
87.5°	12.6	10.4	10.4	9.5	9.9	9.5	10.5	10.2	10.4	10.9	10.2
90°	3.0	5.1	7.3	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.4
92.5°	17.0	16.5	15.8	15.2	16.0	18.1	20.1	22.2	24.2	25.6	26.9
95°	49.2	40.5	31.9	23.2	20.1	22.4	24.7	27.1	29.4	30.8	32.3
97.5°	112.3	108.4	104.5	100.6	91.2	76.0	60.8	45.7	30.5	32.2	33.8
100°	164.3	168.5	172.7	176.9	162.6	129.8	96.9	64.1	31.2	32.9	34.7
102.5°	213.1	216.1	219.2	222.3	205.8	169.9	134.0	98.2	62.3	57.1	51.9
105°	284.6	286.9	289.2	291.6	283.2	264.2	245.3	226.4	207.4	170.2	132.9
107.5°	360.3	362.2	363.9	365.8	368.3	371.3	374.2	377.2	380.3	352.9	325.5
110°	410.9	412.5	414.3	416.0	417.9	420.3	422.6	424.9	427.2	420.3	413.3



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	459.2	460.7	462.3	463.7	465.7	468.0	470.3	472.6	474.9	475.1	475.2
115°	530.8	532.0	533.3	534.5	536.1	538.0	539.9	541.8	543.7	545.8	547.9
117.5°	600.5	602.1	603.7	605.3	606.5	607.5	608.5	609.4	610.4	612.0	613.8
120°	644.1	646.0	647.9	649.8	651.1	651.7	652.3	653.0	653.5	655.3	657.0
122.5°	687.7	689.3	690.8	692.4	693.6	694.4	695.2	695.9	696.8	698.0	699.1
125°	748.1	749.7	751.5	753.2	754.4	755.2	756.1	756.9	757.7	758.2	758.6
127.5°	806.4	808.1	809.8	811.5	812.9	813.8	814.9	815.9	816.8	817.6	818.2
130°	842.9	844.5	846.2	847.8	849.1	849.9	850.8	851.7	852.5	853.4	854.2
132.5°	877.7	879.4	881.0	882.7	883.9	884.6	885.3	885.9	886.6	887.5	888.3
135°	930.5	931.7	933.0	934.3	935.3	936.2	937.0	937.8	938.7	939.3	940.0
137.5°	976.3	977.9	979.5	981.1	982.1	982.6	983.1	983.5	984.0	985.0	986.0
140°	1006.2	1007.5	1008.8	1010.1	1011.0	1011.6	1012.3	1012.9	1013.5	1014.4	1015.2
142.5°	1034.3	1035.6	1036.8	1038.1	1039.0	1039.7	1040.3	1041.0	1041.5	1042.3	1042.9
145°	1073.7	1075.2	1076.7	1078.2	1079.1	1079.5	1079.9	1080.4	1080.8	1081.2	1081.7
147.5°	1110.2	1111.2	1112.1	1113.0	1113.8	1114.2	1114.6	1115.0	1115.4	1115.9	1116.3
150°	1132.5	1133.2	1133.8	1134.5	1135.0	1135.4	1135.8	1136.3	1136.7	1137.1	1137.5
152.5°	1152.7	1153.0	1153.2	1153.6	1153.8	1154.1	1154.4	1154.6	1154.9	1155.6	1156.3
155°	1180.8	1180.3	1179.9	1179.5	1179.4	1179.6	1179.8	1180.1	1180.2	1181.3	1182.3
157.5°	1203.5	1203.5	1203.4	1203.4	1203.2	1203.1	1202.8	1202.6	1202.4	1203.7	1204.9
160°	1217.0	1216.8	1216.6	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3	1216.6	1217.8
162.5°	1229.6	1229.0	1228.4	1227.8	1227.5	1227.3	1227.1	1226.9	1226.6	1228.1	1229.6
165°	1245.0	1244.3	1243.7	1243.1	1242.7	1242.4	1242.2	1242.0	1241.8	1243.5	1245.2
167.5°	1256.9	1256.1	1255.2	1254.3	1253.9	1253.9	1253.9	1253.9	1253.9	1255.6	1257.3
170°	1263.7	1262.9	1262.0	1261.2	1260.8	1260.8	1260.8	1260.8	1260.8	1262.4	1264.1
172.5°	1268.1	1267.1	1266.1	1265.0	1264.6	1264.8	1264.9	1265.1	1265.3	1267.0	1268.7
175°	1273.9	1272.8	1271.8	1270.7	1270.3	1270.6	1270.7	1271.0	1271.1	1272.7	1274.1
177.5°	1275.6	1274.8	1274.0	1273.1	1272.8	1272.9	1273.1	1273.3	1273.4	1274.8	1276.1
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1367.1	1367.1	1368.9	1375.6	1376.5	1382.2	1380.5
5°	1502.5	1513.0	1516.9	1533.6	1543.5	1548.0	1539.1
7.5°	1668.1	1697.8	1711.9	1729.3	1744.7	1749.4	1737.3
10°	1788.8	1819.8	1845.9	1862.1	1877.0	1887.0	1899.7
12.5°	1905.5	1943.7	1968.5	1991.2	2006.6	2019.3	2021.4
15°	2032.4	2090.1	2133.9	2166.1	2182.1	2190.5	2187.2
17.5°	2160.3	2213.8	2245.0	2277.9	2300.1	2301.3	2301.9
20°	2232.7	2284.8	2320.9	2345.3	2370.2	2369.2	2374.7
22.5°	2281.0	2322.1	2349.8	2367.5	2376.0	2371.8	2372.9
25°	2303.7	2315.9	2310.9	2282.6	2275.4	2249.3	2253.7
27.5°	2187.0	2129.2	2069.6	1992.8	1932.2	1883.7	1886.2
30°	2028.5	1926.4	1809.9	1712.2	1624.6	1600.2	1548.0
32.5°	1807.0	1653.8	1517.4	1426.4	1351.1	1330.7	1285.2
35°	1431.5	1282.8	1142.4	1058.1	1024.7	978.2	977.6
37.5°	1112.6	981.7	907.5	844.2	811.1	782.9	780.1
40°	936.0	833.9	777.9	732.4	699.7	678.6	673.6
42.5°	812.6	730.0	677.6	649.4	624.2	613.3	605.2
45°	663.6	608.1	571.4	545.9	534.3	525.9	521.5
47.5°	555.1	517.9	492.9	476.0	466.5	457.7	460.1
50°	496.0	465.5	447.2	431.1	423.9	417.8	418.3
52.5°	448.5	421.1	406.3	394.7	385.7	381.4	379.3
55°	380.6	363.4	348.5	340.1	335.1	329.1	327.3
57.5°	324.7	311.4	299.1	289.8	288.5	282.7	283.4
60°	287.4	276.3	266.4	261.3	257.5	252.4	254.1
62.5°	256.8	247.4	238.4	234.2	230.4	226.7	227.5
65°	210.3	201.4	195.8	193.6	192.0	190.3	188.7
67.5°	167.5	162.2	158.7	153.9	150.5	149.9	148.2
70°	141.0	133.7	127.6	121.5	119.8	119.3	119.8
72.5°	113.0	108.4	106.7	103.8	103.5	102.0	103.0
75°	84.9	83.2	82.1	79.9	79.9	79.9	79.9
77.5°	62.6	61.6	60.9	60.5	59.9	59.1	59.0
80°	48.8	48.3	47.1	47.1	46.6	47.1	46.6
82.5°	36.9	36.8	35.6	35.6	35.1	34.7	35.1
85°	18.8	18.3	19.4	18.3	18.8	17.8	18.8
87.5°	10.4	10.5	10.2	10.3	9.9	10.9	10.1
90°	25.3	26.1	26.7	27.1	27.6	28.0	28.5
92.5°	28.3	29.7	30.4	30.7	31.0	31.2	31.5
95°	33.8	35.2	36.0	36.0	36.0	36.0	36.0
97.5°	35.5	37.3	38.2	38.4	38.6	38.8	39.1
100°	36.3	38.0	39.0	39.1	39.4	39.5	39.8
102.5°	46.6	41.4	39.1	39.4	39.8	40.2	40.5
105°	95.6	58.4	40.0	40.4	40.8	41.3	41.7
107.5°	298.2	270.9	243.2	215.2	187.0	159.0	130.9
110°	406.3	399.4	380.9	350.8	320.7	290.6	260.5



TEST NUMBER: P332354-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	475.3	475.5	472.3	465.9	459.6	453.2	446.9
115°	550.0	552.1	553.6	554.4	555.3	556.1	556.9
117.5°	615.5	617.1	618.1	618.2	618.4	618.6	618.7
120°	658.6	660.3	661.1	661.1	661.1	661.1	661.1
122.5°	700.3	701.5	702.1	702.3	702.5	702.7	702.9
125°	759.0	759.5	759.9	760.3	760.8	761.2	761.6
127.5°	818.9	819.5	819.7	819.3	818.9	818.5	818.0
130°	855.0	855.9	856.1	855.7	855.2	854.8	854.4
132.5°	889.2	890.0	890.1	889.5	888.9	888.4	887.7
135°	940.6	941.3	941.3	940.6	940.0	939.3	938.7
137.5°	987.0	988.0	988.3	987.9	987.5	987.1	986.6
140°	1016.0	1016.9	1017.1	1016.7	1016.3	1015.9	1015.5
142.5°	1043.6	1044.2	1044.3	1043.7	1043.1	1042.5	1042.0
145°	1082.1	1082.5	1082.6	1082.6	1082.6	1082.6	1082.6
147.5°	1116.7	1117.1	1116.9	1115.9	1114.9	1113.9	1113.0
150°	1137.9	1138.3	1138.2	1137.6	1137.0	1136.4	1135.7
152.5°	1157.2	1157.9	1157.8	1156.8	1155.8	1154.9	1153.9
155°	1183.4	1184.5	1184.3	1183.1	1181.9	1180.6	1179.3
157.5°	1206.2	1207.5	1207.3	1205.7	1204.0	1202.3	1200.7
160°	1219.0	1220.3	1220.3	1218.8	1217.3	1215.8	1214.3
162.5°	1230.9	1232.4	1232.4	1231.1	1229.8	1228.5	1227.2
165°	1246.8	1248.5	1248.6	1247.2	1245.7	1244.2	1242.8
167.5°	1259.0	1260.7	1260.7	1259.0	1257.3	1255.6	1253.9
170°	1265.8	1267.5	1267.5	1265.8	1264.1	1262.4	1260.8
172.5°	1270.3	1272.0	1271.9	1270.1	1268.3	1266.4	1264.5
175°	1275.6	1277.1	1276.9	1275.3	1273.6	1271.9	1270.2
177.5°	1277.5	1278.8	1278.6	1277.0	1275.3	1273.6	1271.9
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0

(END OF REPORT)