

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331944-935

Luminaire Tested: **S123DIP-S560D1025U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331944-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1025U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5030.5 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331944-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331944-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	73	68	79	73	67	63	59	56	53	47	45	43	36	35	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	56	50	44	46	41	37	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	21	18	15
7	56	44	36	31	51	41	34	29	34	29	25	27	23	20	21	19	16	14
8	52	40	33	27	47	37	30	25	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8257	8257	8257
5°	8295	8182	8238
10°	8240	8110	8160
15°	8143	8018	8033
20°	8031	7887	7895
25°	7880	7732	7715
30°	7713	7558	7501
35°	7540	7376	7281
40°	7359	7173	7062
45°	7159	6987	6817
50°	6958	6759	6571
55°	6696	6523	6324
60°	6433	6247	6047
65°	6199	5947	5761
70°	5854	5605	5353
75°	5348	5157	4937
80°	4823	4624	4581
85°	4236	4076	3915



TEST NUMBER: P331944-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	1.4
10°-20°	204.0	4.1
20°-30°	301.4	6.0
30°-40°	352.0	7.0
40°-50°	353.9	7.0
50°-60°	310.9	6.2
60°-70°	231.6	4.6
70°-80°	132.0	2.6
80°-90°	41.1	0.8
90°-100°	71.3	1.4
100°-110°	213.3	4.2
110°-120°	362.8	7.2
120°-130°	477.3	9.5
130°-140°	536.4	10.7
140°-150°	527.3	10.5
150°-160°	443.9	8.8
160°-170°	295.5	5.9
170°-180°	103.5	2.1
0°-30°	577.6	11.5
0°-40°	929.7	18.5
0°-60°	1594.5	31.7
0°-90°	1999.2	39.7
90°-120°	647.5	12.9
90°-150°	2188.5	43.5
90°-180°	3031.0	60.3
0°-180°	5030.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	768	764	757	763	762	73
15°	731	728	720	724	721	206
25°	664	659	651	651	650	305
35°	574	570	561	557	554	359
45°	470	467	459	451	448	363
55°	357	356	348	340	337	319
65°	243	240	234	228	226	240
75°	129	126	124	121	119	138
85°	34	33	33	32	32	38
90°	1	10	21	24	26	5
95°	51	57	64	67	67	57
105°	193	195	203	203	205	207
115°	365	368	366	367	366	361
125°	535	537	536	532	529	477
135°	694	698	698	694	693	534
145°	841	843	846	845	841	525
155°	964	964	964	967	962	443
165°	1049	1047	1047	1051	1046	296
175°	1092	1088	1088	1093	1087	104
180°	1094	1094	1094	1094	1094	



TEST NUMBER: P331944-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	769.6	769.2	768.8	768.3	767.8	766.9	765.6	764.3	763.1	761.8	762.9
5°	767.7	767.0	766.2	765.5	764.7	763.6	762.0	760.3	758.8	757.2	758.6
7.5°	760.2	759.5	758.7	758.0	757.2	756.0	754.4	752.7	751.1	749.4	750.7
10°	753.9	753.1	752.4	751.7	751.0	749.6	747.7	745.8	743.9	742.0	743.3
12.5°	745.5	744.8	744.2	743.6	743.0	741.8	739.9	738.1	736.4	734.6	735.6
15°	730.7	730.2	729.6	729.0	728.4	727.2	725.3	723.4	721.4	719.5	720.7
17.5°	713.8	713.0	712.2	711.4	710.7	709.4	707.5	705.6	703.7	701.7	702.6
20°	701.1	700.3	699.3	698.4	697.6	696.2	694.3	692.4	690.4	688.5	689.1
22.5°	686.8	686.0	685.1	684.2	683.3	681.9	680.0	678.1	676.2	674.3	674.8
25°	663.5	662.6	661.8	660.9	660.0	658.6	656.7	654.8	652.9	651.0	651.1
27.5°	638.6	637.7	636.9	636.0	635.2	633.7	631.6	629.6	627.6	625.5	625.6
30°	620.6	619.9	619.1	618.5	617.7	616.3	614.2	612.2	610.2	608.1	608.1
32.5°	602.7	601.8	600.7	599.8	598.8	597.5	596.0	594.3	592.8	591.2	590.4
35°	573.8	572.9	572.0	571.2	570.3	568.9	567.0	565.1	563.2	561.3	560.4
37.5°	544.2	543.1	542.0	540.9	539.8	538.3	536.3	534.4	532.4	530.5	529.5
40°	523.7	522.8	521.9	521.1	520.1	518.7	516.6	514.6	512.6	510.5	509.3
42.5°	503.1	502.1	501.1	500.1	499.1	497.6	495.5	493.5	491.5	489.4	488.2
45°	470.3	469.7	469.1	468.5	467.9	466.7	464.8	462.9	461.0	459.0	457.3
47.5°	437.6	436.8	436.0	435.1	434.3	432.9	431.2	429.4	427.6	425.8	424.0
50°	415.5	414.7	414.1	413.3	412.6	411.3	409.3	407.4	405.5	403.6	402.0
52.5°	392.3	391.8	391.3	390.8	390.3	389.0	387.0	385.0	383.0	381.0	379.6
55°	356.8	356.6	356.5	356.4	356.2	355.2	353.3	351.4	349.5	347.6	345.9
57.5°	323.0	322.5	322.0	321.6	321.1	320.0	318.5	317.0	315.5	313.9	312.5
60°	298.8	298.6	298.5	298.3	298.2	297.2	295.5	293.7	292.0	290.2	288.9
62.5°	277.2	276.7	276.4	276.0	275.6	274.6	272.8	271.0	269.2	267.5	266.2
65°	243.4	242.6	241.9	241.2	240.5	239.4	237.9	236.4	235.0	233.5	232.3
67.5°	207.6	207.0	206.3	205.7	205.0	204.1	203.0	201.9	200.8	199.8	198.7
70°	186.0	185.1	184.3	183.4	182.4	181.6	180.7	179.9	178.9	178.1	177.0
72.5°	163.3	162.6	162.0	161.4	160.7	159.9	158.9	157.9	156.9	155.9	155.0
75°	128.6	128.0	127.4	126.8	126.3	125.8	125.3	124.8	124.4	124.0	123.3
77.5°	97.9	97.6	97.2	96.9	96.6	96.2	95.7	95.1	94.5	94.0	93.6
80°	77.8	77.4	77.0	76.5	76.0	75.7	75.4	75.1	74.8	74.6	74.4
82.5°	58.3	58.2	58.1	58.0	57.9	57.9	57.9	57.8	57.7	57.7	57.3
85°	34.3	34.0	33.8	33.4	33.1	33.0	33.0	33.0	33.0	33.0	32.7
87.5°	13.9	13.9	13.9	13.9	14.0	14.2	14.6	15.0	15.3	15.8	15.8
90°	0.9	2.8	4.6	6.6	8.5	10.7	13.2	15.7	18.2	20.7	21.4
92.5°	20.8	22.1	23.4	24.7	26.0	27.4	28.8	30.1	31.6	33.0	33.6
95°	50.7	52.0	53.4	54.8	56.1	57.5	59.0	60.5	62.1	63.6	64.4
97.5°	90.1	91.1	92.0	93.1	94.0	95.1	96.2	97.3	98.4	99.5	100.4
100°	116.9	118.0	119.2	120.3	121.5	122.5	123.5	124.4	125.4	126.3	126.9
102.5°	147.8	148.5	149.2	149.9	150.6	151.5	152.8	154.0	155.3	156.6	157.1
105°	193.4	193.7	194.2	194.5	194.9	196.0	197.7	199.4	201.1	202.9	202.9
107.5°	246.3	246.6	246.8	247.0	247.3	247.7	248.4	249.1	249.8	250.5	251.1
110°	279.3	279.7	280.1	280.4	280.9	281.2	281.6	282.0	282.4	282.8	283.5



TEST NUMBER: P331944-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	313.7	313.9	314.2	314.4	314.6	314.8	314.9	315.0	315.0	315.0	316.0
115°	365.2	365.8	366.4	367.0	367.6	367.6	367.3	366.9	366.5	366.1	366.4
117.5°	417.2	417.6	417.9	418.4	418.7	418.6	418.2	417.7	417.2	416.6	416.6
120°	449.5	450.6	451.8	453.0	454.1	454.2	453.2	452.3	451.3	450.4	450.1
122.5°	483.2	484.1	484.8	485.7	486.6	486.7	486.2	485.7	485.3	484.7	484.2
125°	534.6	535.2	535.7	536.3	536.8	537.0	536.6	536.2	535.8	535.5	534.7
127.5°	582.0	583.2	584.4	585.7	586.9	587.3	586.9	586.5	586.1	585.7	584.5
130°	613.6	615.2	616.7	618.2	619.7	620.3	619.7	619.1	618.5	617.9	617.2
132.5°	645.3	646.8	648.3	649.9	651.4	651.9	651.5	651.1	650.7	650.2	649.4
135°	693.6	694.7	695.9	697.0	698.2	698.6	698.4	698.3	698.1	697.8	697.2
137.5°	738.3	739.3	740.2	741.1	742.1	742.8	743.3	743.8	744.3	744.8	744.0
140°	769.2	770.2	771.1	772.1	773.0	773.6	773.8	774.0	774.2	774.4	774.2
142.5°	797.4	798.3	799.4	800.3	801.2	801.8	802.2	802.5	802.9	803.2	803.1
145°	841.4	841.8	842.1	842.6	842.9	843.4	844.0	844.6	845.2	845.7	845.5
147.5°	879.9	880.6	881.3	882.0	882.7	883.3	883.8	884.3	884.8	885.5	885.5
150°	906.7	907.1	907.5	907.8	908.3	908.6	909.0	909.4	909.8	910.2	910.2
152.5°	928.8	929.3	929.8	930.3	930.8	931.3	931.5	931.7	931.9	932.2	932.5
155°	963.5	963.5	963.5	963.5	963.5	963.5	963.7	963.9	964.1	964.3	965.1
157.5°	993.0	992.8	992.6	992.3	992.1	992.0	992.2	992.4	992.6	992.6	993.5
160°	1011.6	1011.2	1010.8	1010.5	1010.0	1009.9	1009.9	1009.9	1009.9	1009.9	1010.8
162.5°	1028.1	1027.5	1027.0	1026.5	1026.0	1025.8	1025.9	1026.1	1026.2	1026.4	1027.3
165°	1049.4	1048.8	1048.3	1047.7	1047.1	1046.8	1046.8	1046.8	1046.8	1046.8	1047.9
167.5°	1066.4	1065.7	1064.9	1064.1	1063.3	1063.1	1063.2	1063.3	1063.5	1063.7	1064.9
170°	1076.1	1075.3	1074.5	1073.8	1073.0	1072.6	1072.6	1072.6	1072.6	1072.6	1073.9
172.5°	1083.6	1082.9	1082.1	1081.3	1080.6	1080.1	1080.1	1080.1	1080.1	1080.1	1081.3
175°	1091.5	1090.7	1089.9	1089.3	1088.5	1088.0	1088.0	1088.0	1088.0	1088.0	1089.3
177.5°	1094.8	1094.2	1093.6	1093.0	1092.4	1092.0	1092.0	1092.0	1092.0	1092.0	1093.0
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P331944-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	764.1	765.3	766.5	767.0	766.9	766.7	766.6	766.5
5°	760.1	761.6	763.0	763.6	763.3	763.0	762.8	762.4
7.5°	752.0	753.3	754.7	755.2	755.0	754.8	754.7	754.5
10°	744.6	746.0	747.3	747.8	747.5	747.2	746.9	746.6
12.5°	736.5	737.5	738.5	738.8	738.7	738.5	738.3	738.1
15°	721.9	723.1	724.3	724.4	723.5	722.6	721.8	720.9
17.5°	703.4	704.2	705.1	705.2	705.0	704.6	704.3	704.0
20°	689.7	690.3	690.9	691.0	690.5	690.1	689.7	689.2
22.5°	675.3	675.7	676.2	676.1	675.6	675.0	674.5	673.9
25°	651.3	651.4	651.5	651.4	651.0	650.6	650.1	649.6
27.5°	625.8	625.9	625.9	625.8	625.2	624.7	624.1	623.5
30°	608.1	608.1	608.1	607.6	606.6	605.5	604.5	603.5
32.5°	589.6	588.8	587.9	587.2	586.7	586.2	585.6	585.0
35°	559.5	558.6	557.8	557.0	556.2	555.5	554.7	554.1
37.5°	528.4	527.4	526.3	525.6	525.1	524.6	524.2	523.7
40°	508.2	507.0	505.8	504.9	504.3	503.8	503.2	502.6
42.5°	487.1	485.9	484.7	483.8	483.2	482.7	482.1	481.5
45°	455.6	453.7	452.0	450.7	450.0	449.3	448.6	447.8
47.5°	422.3	420.6	418.9	417.7	417.1	416.4	415.8	415.1
50°	400.5	398.8	397.2	396.0	395.0	394.2	393.3	392.4
52.5°	378.2	376.9	375.5	374.3	373.4	372.6	371.7	370.8
55°	344.3	342.8	341.1	339.9	339.2	338.5	337.8	337.0
57.5°	311.1	309.6	308.2	307.0	306.2	305.4	304.5	303.7
60°	287.6	286.3	284.9	283.9	283.2	282.4	281.7	280.9
62.5°	264.8	263.6	262.3	261.3	260.8	260.4	259.8	259.3
65°	231.1	230.0	228.8	228.0	227.6	227.1	226.7	226.2
67.5°	197.7	196.7	195.6	194.8	194.2	193.6	193.0	192.3
70°	176.0	175.0	174.0	173.1	172.4	171.6	170.9	170.1
72.5°	154.1	153.2	152.3	151.6	151.3	150.8	150.5	150.1
75°	122.5	121.8	121.1	120.5	120.0	119.6	119.2	118.7
77.5°	93.1	92.6	92.0	91.8	91.8	91.8	91.8	91.8
80°	74.2	74.0	74.0	73.9	73.9	73.9	73.9	73.9
82.5°	57.1	56.8	56.6	56.4	56.3	56.1	56.1	56.0
85°	32.4	32.1	31.8	31.7	31.7	31.7	31.7	31.7
87.5°	15.8	15.8	15.8	15.9	16.0	16.1	16.2	16.3
90°	22.1	22.9	23.7	24.3	24.6	25.1	25.4	25.7
92.5°	34.3	34.9	35.5	35.6	35.4	35.2	35.0	34.7
95°	65.1	65.9	66.6	67.1	67.1	67.1	67.1	67.1
97.5°	101.3	102.2	103.1	103.4	103.4	103.3	103.2	103.1
100°	127.5	128.0	128.6	129.2	129.5	129.8	130.3	130.6
102.5°	157.7	158.3	158.9	159.1	159.0	158.9	158.9	158.9
105°	202.9	202.9	202.9	203.0	203.4	203.8	204.1	204.6
107.5°	251.7	252.3	252.9	253.0	252.9	252.6	252.4	252.2
110°	284.3	285.1	285.9	286.0	285.6	285.2	284.9	284.5



TEST NUMBER: P331944-935

CATALOG NUMBER: S123DIP-S560D1025U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	316.9	317.8	318.7	319.2	319.1	319.0	318.9	318.8
115°	366.5	366.7	366.9	366.9	366.7	366.5	366.4	366.1
117.5°	416.6	416.6	416.6	416.2	415.7	415.2	414.7	414.1
120°	450.0	449.8	449.6	449.3	448.9	448.6	448.2	447.8
122.5°	483.7	483.3	482.8	482.2	481.7	481.1	480.6	480.1
125°	533.9	533.1	532.4	531.6	530.9	530.1	529.3	528.6
127.5°	583.5	582.5	581.3	580.4	579.5	578.6	577.7	576.9
130°	616.4	615.6	614.9	613.8	612.5	611.1	609.8	608.5
132.5°	648.4	647.6	646.6	645.7	644.6	643.6	642.6	641.5
135°	696.4	695.6	694.8	694.2	693.9	693.4	693.1	692.8
137.5°	743.2	742.4	741.6	740.8	740.1	739.3	738.7	738.0
140°	774.0	773.8	773.6	772.8	771.5	770.2	768.9	767.5
142.5°	802.9	802.7	802.5	801.8	800.8	799.8	798.7	797.7
145°	845.3	845.2	844.9	844.5	843.7	842.9	842.1	841.4
147.5°	885.5	885.5	885.5	884.8	883.7	882.5	881.4	880.3
150°	910.2	910.2	910.2	909.6	908.4	907.3	906.1	905.0
152.5°	932.8	933.1	933.4	933.1	932.0	931.1	930.1	929.1
155°	965.9	966.6	967.3	967.1	965.8	964.4	963.0	961.7
157.5°	994.3	995.1	995.9	995.7	994.7	993.6	992.6	991.4
160°	1011.8	1012.7	1013.7	1013.7	1013.1	1012.3	1011.5	1010.7
162.5°	1028.3	1029.2	1030.2	1030.0	1028.8	1027.6	1026.4	1025.2
165°	1049.1	1050.2	1051.4	1051.3	1050.0	1048.6	1047.3	1045.9
167.5°	1066.0	1067.2	1068.4	1068.4	1067.2	1066.0	1064.9	1063.7
170°	1075.3	1076.6	1078.0	1078.0	1076.6	1075.3	1073.9	1072.6
172.5°	1082.5	1083.7	1084.9	1084.9	1083.5	1082.2	1080.8	1079.4
175°	1090.4	1091.5	1092.7	1092.5	1091.2	1089.9	1088.6	1087.2
177.5°	1093.9	1094.8	1095.7	1095.6	1094.6	1093.5	1092.4	1091.3
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1

(END OF REPORT)