

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831523

Luminaire Tested: S123DIP-S560D365U935-4F0-1E-UDD-G1

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831523  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D365U935-4F0-1E-UDD-G1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3308.1 lumens  
Efficiency: N/A  
Efficacy: 111.8 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 29.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831523

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-G1

### Luminous Intensity Polar Plot





TEST NUMBER: P831523

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-G1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68								
1	102	98	94	91	96	93	90	87	83	80	78	73	72	70	65	64	62	58								
2	94	87	81	76	88	82	77	72	73	69	66	65	62	60	58	56	54	50								
3	86	77	70	64	81	73	67	62	66	61	56	59	55	51	52	49	47	43								
4	79	69	61	55	75	65	58	53	59	53	49	53	49	45	47	44	41	38								
5	73	62	54	48	69	59	52	46	53	48	43	48	43	40	43	39	36	34								
6	68	56	48	43	64	54	46	41	49	43	38	44	39	35	40	36	33	30								
7	63	51	43	38	60	49	42	37	45	39	34	40	36	32	37	33	30	27								
8	59	47	39	34	56	45	38	33	41	35	31	37	33	29	34	30	27	25								
9	55	43	36	31	52	41	35	30	38	32	28	35	30	26	32	28	25	23								
10	52	40	33	28	49	38	32	27	35	30	26	32	28	24	30	26	23	21								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	14960	14960	14960	14960	14960
5°	18919	17856	15092	12163	11177
10°	19102	19680	14993	9696	8473
15°	14388	18272	14890	8211	7165
20°	10024	14786	14700	7180	6509
25°	7644	11371	14377	6606	6105
30°	6612	9033	13858	6200	5780
35°	6135	7627	13263	5907	5550
40°	5809	6842	12424	5628	5473
45°	5616	6333	11357	5409	5439
50°	5518	5928	10098	5211	5411
55°	5313	5634	8860	5022	5435
60°	5124	5317	7636	4846	5345
65°	4814	5018	6586	4656	5239
70°	4444	4639	5602	4343	4932
75°	4022	4159	4799	4038	4504
80°	3316	3639	3800	3521	3800
85°	2631	2952	2791	2989	3026

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 12968 cd/sqm



TEST NUMBER: P831523

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-G1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.4	4.0
10°-20°	326.9	9.9
20°-30°	387.0	11.7
30°-40°	389.1	11.8
40°-50°	357.0	10.8
50°-60°	294.7	8.9
60°-70°	208.5	6.3
70°-80°	111.3	3.4
80°-90°	29.1	0.9
90°-100°	24.9	0.8
100°-110°	75.5	2.3
110°-120°	128.5	3.9
120°-130°	169.0	5.1
130°-140°	190.0	5.7
140°-150°	186.8	5.6
150°-160°	157.2	4.8
160°-170°	104.7	3.2
170°-180°	36.7	1.1
0°-30°	845.3	25.6
0°-40°	1234.4	37.3
0°-60°	1886.1	57.0
0°-90°	2234.9	67.6
90°-120°	228.9	6.9
90°-150°	774.6	23.4
90°-180°	1073.0	32.4
0°-180°	3308.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1390	1390	1390	1390	1390	
5°	1751	1653	1397	1126	1034	167
15°	1291	1640	1336	737	643	357
25°	644	957	1210	556	514	304
35°	467	580	1009	450	422	293
45°	369	416	746	355	357	286
55°	283	300	472	268	290	253
65°	189	197	259	183	206	188
75°	97	100	115	97	108	102
85°	21	24	23	24	24	24
90°	9	7	0	7	9	6
95°	24	22	18	22	24	24
105°	72	72	68	72	72	77
115°	130	130	129	130	130	128
125°	187	190	189	190	187	167
135°	245	247	246	247	245	189
145°	298	299	298	299	298	186
155°	340	341	341	341	340	157
165°	370	371	372	371	370	104
175°	385	385	386	385	385	37
180°	387	387	387	387	387	



TEST NUMBER: P831523

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8
2.5°	1566.5	1564.8	1563.2	1555.2	1547.1	1543.2	1539.4	1527.8	1516.2	1503.3	1490.4
5°	1750.9	1755.4	1759.9	1754.8	1749.6	1733.8	1718.0	1697.0	1676.1	1652.6	1629.0
7.5°	1836.0	1838.6	1841.2	1838.0	1834.7	1830.5	1826.3	1807.6	1788.9	1764.8	1740.6
10°	1747.7	1753.5	1759.3	1771.9	1784.4	1798.6	1812.8	1810.2	1807.6	1800.6	1793.5
12.5°	1553.6	1560.7	1567.7	1592.9	1618.0	1650.3	1682.5	1710.3	1738.0	1757.3	1776.7
15°	1291.1	1310.8	1330.4	1353.3	1376.2	1423.6	1471.0	1529.4	1587.7	1639.7	1691.6
17.5°	1063.4	1070.9	1078.3	1102.8	1127.3	1186.9	1246.6	1314.0	1381.4	1467.5	1553.6
20°	875.1	881.9	888.7	920.9	953.2	999.9	1046.7	1122.4	1198.2	1290.8	1383.3
22.5°	735.2	745.8	756.5	774.5	792.6	837.4	882.2	949.6	1017.0	1119.2	1221.4
25°	643.6	651.3	659.1	670.0	681.0	716.8	752.6	808.1	863.5	957.4	1051.2
27.5°	581.1	584.3	587.5	598.5	609.4	632.6	655.9	703.6	751.3	831.0	910.6
30°	532.0	534.3	536.6	546.2	555.9	571.7	587.5	622.0	656.5	726.8	797.1
32.5°	497.9	499.5	501.1	508.5	515.9	527.2	538.5	563.6	588.8	646.8	704.9
35°	466.9	467.9	468.8	474.3	479.8	488.2	496.6	515.6	534.6	580.4	626.2
37.5°	439.8	441.1	442.4	445.6	448.8	456.3	463.7	478.8	494.0	529.1	564.3
40°	413.4	415.6	417.9	420.2	422.4	428.5	434.7	446.3	457.9	486.9	515.9
42.5°	390.8	393.1	395.3	396.3	397.3	400.8	404.4	415.0	425.6	447.2	468.8
45°	368.9	369.8	370.8	371.8	372.8	375.7	378.6	387.9	397.3	416.0	434.7
47.5°	348.9	348.9	348.9	349.5	350.2	352.8	355.3	362.1	368.9	383.4	397.9
50°	329.5	329.5	329.5	328.6	327.6	329.2	330.8	336.0	341.2	354.0	366.9
52.5°	306.3	306.3	306.3	306.6	307.0	307.0	307.0	311.5	316.0	327.6	339.2
55°	283.1	284.4	285.7	284.7	283.8	284.4	285.0	287.9	290.8	300.2	309.6
57.5°	259.9	260.5	261.2	260.9	260.5	260.9	261.2	263.8	266.3	273.4	280.5
60°	238.0	238.0	238.0	237.3	236.7	237.3	238.0	239.3	240.5	247.0	253.4
62.5°	213.5	213.8	214.1	214.4	214.8	214.1	213.5	215.1	216.7	221.5	226.4
65°	189.0	189.3	189.6	190.6	191.5	190.9	190.2	191.9	193.5	197.0	200.6
67.5°	167.0	166.4	165.7	166.1	166.4	167.4	168.3	168.6	169.0	172.8	176.7
70°	141.2	141.9	142.5	142.2	141.9	142.2	142.5	143.5	144.5	147.4	150.3
72.5°	118.0	118.3	118.7	118.7	118.7	119.3	120.0	120.9	121.9	123.5	125.1
75°	96.7	96.7	96.7	97.4	98.0	98.3	98.7	98.7	98.7	100.0	101.2
77.5°	73.5	75.1	76.7	76.4	76.1	76.7	77.4	78.4	79.3	80.0	80.6
80°	53.5	53.5	53.5	53.8	54.2	55.1	56.1	56.8	57.4	58.7	60.0
82.5°	34.2	34.5	34.8	35.8	36.8	37.4	38.0	39.0	40.0	40.0	40.0
85°	21.3	20.6	20.0	20.6	21.3	21.9	22.6	22.9	23.2	23.9	24.5
87.5°	10.3	10.3	10.3	10.3	10.3	10.6	11.0	11.0	11.0	11.0	11.0
90°	9.1	9.0	8.9	8.7	8.6	8.4	8.1	7.8	7.6	7.3	6.4
92.5°	13.1	13.2	13.4	13.5	13.6	13.6	13.4	13.2	13.0	12.8	12.4
95°	23.7	23.7	23.7	23.7	23.7	23.6	23.3	23.1	22.8	22.5	22.0
97.5°	34.1	34.1	34.2	34.3	34.3	34.2	33.9	33.5	33.2	32.9	32.5
100°	46.2	46.1	46.0	45.8	45.7	45.5	45.3	45.1	44.9	44.7	44.4
102.5°	58.7	58.8	58.9	58.9	59.0	58.9	58.7	58.5	58.3	58.1	57.6
105°	72.4	72.3	72.1	72.0	71.9	71.8	71.8	71.8	71.8	71.8	71.2
107.5°	86.4	86.5	86.5	86.6	86.7	86.6	86.4	86.2	86.0	85.8	85.5
110°	100.7	100.8	101.0	101.1	101.3	101.2	100.9	100.6	100.4	100.1	100.0



TEST NUMBER: P831523

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	115.9	115.9	115.9	115.9	115.9	115.8	115.4	115.1	114.7	114.4	114.4
115°	129.6	129.7	129.8	129.8	129.9	129.9	129.8	129.8	129.7	129.6	129.8
117.5°	143.6	143.8	144.0	144.2	144.4	144.5	144.5	144.5	144.5	144.5	144.7
120°	158.5	158.7	158.8	158.9	159.1	159.2	159.2	159.3	159.4	159.4	159.8
122.5°	172.8	173.0	173.2	173.4	173.6	173.8	174.0	174.2	174.4	174.7	174.8
125°	187.1	187.4	187.7	187.9	188.2	188.5	188.7	189.0	189.3	189.6	189.7
127.5°	201.4	201.7	202.0	202.2	202.5	202.8	203.3	203.7	204.1	204.5	204.6
130°	215.4	215.9	216.4	216.8	217.3	217.7	218.0	218.2	218.5	218.8	219.0
132.5°	230.0	230.4	230.7	231.0	231.4	231.7	232.1	232.4	232.7	233.1	233.2
135°	245.2	245.4	245.5	245.6	245.8	246.0	246.3	246.5	246.8	247.1	247.1
137.5°	258.6	258.8	259.0	259.2	259.4	259.7	260.0	260.4	260.7	261.1	260.9
140°	271.7	272.2	272.7	273.1	273.6	273.9	273.9	274.0	274.1	274.1	274.1
142.5°	285.1	285.4	285.8	286.1	286.5	286.7	286.7	286.8	286.9	286.9	286.8
145°	297.9	298.1	298.4	298.7	299.0	299.1	299.2	299.3	299.3	299.4	299.2
147.5°	309.4	309.8	310.3	310.7	311.1	311.3	311.3	311.3	311.3	311.3	311.1
150°	320.4	320.8	321.2	321.6	322.0	322.2	322.2	322.2	322.2	322.2	322.1
152.5°	331.0	331.4	331.7	332.1	332.4	332.5	332.4	332.2	332.1	332.0	331.9
155°	340.5	341.0	341.4	341.9	342.4	342.5	342.2	341.9	341.7	341.4	341.3
157.5°	349.3	349.7	350.1	350.5	350.9	351.0	350.7	350.5	350.2	349.9	349.8
160°	357.8	358.1	358.4	358.6	358.9	358.9	358.5	358.2	357.9	357.5	357.5
162.5°	364.2	364.7	365.2	365.6	366.1	366.2	365.8	365.5	365.2	364.8	364.8
165°	370.3	370.8	371.2	371.7	372.2	372.2	371.8	371.4	371.0	370.6	370.6
167.5°	375.8	376.2	376.6	377.0	377.4	377.4	377.0	376.6	376.2	375.8	375.7
170°	379.7	380.2	380.7	381.1	381.6	381.6	381.1	380.7	380.2	379.7	379.7
172.5°	382.8	383.2	383.7	384.2	384.7	384.7	384.3	383.9	383.5	383.1	383.1
175°	384.9	385.4	385.8	386.3	386.8	386.8	386.4	386.0	385.6	385.2	385.2
177.5°	386.1	386.6	387.1	387.5	388.0	388.0	387.6	387.2	386.8	386.4	386.4
180°	387.3	387.3	387.3	387.3	387.3	387.3	387.3	387.3	387.3	387.3	387.3



TEST NUMBER: P831523

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8
2.5°	1486.5	1482.6	1468.4	1454.2	1438.1	1422.0	1410.1	1398.1	1380.4	1362.7	1348.2
5°	1611.0	1592.9	1562.9	1532.9	1492.3	1451.7	1424.3	1396.8	1360.1	1323.3	1294.0
7.5°	1709.6	1678.7	1636.8	1594.8	1541.6	1488.4	1438.1	1387.8	1331.7	1275.6	1229.8
10°	1772.5	1751.5	1703.2	1654.8	1583.5	1512.3	1442.0	1371.7	1299.5	1227.2	1166.6
12.5°	1778.6	1780.6	1736.1	1691.6	1611.0	1530.3	1444.9	1359.4	1268.5	1177.6	1107.0
15°	1724.8	1758.0	1733.5	1709.0	1627.7	1546.5	1441.3	1336.2	1231.4	1126.6	1045.1
17.5°	1624.8	1696.1	1699.6	1703.2	1621.9	1540.7	1424.3	1307.9	1189.2	1070.5	984.8
20°	1488.4	1593.5	1629.7	1665.8	1599.7	1533.6	1408.5	1283.3	1150.5	1017.6	927.7
22.5°	1349.1	1476.8	1542.9	1609.0	1560.0	1511.0	1377.8	1244.7	1104.4	964.1	872.9
25°	1190.5	1329.8	1431.4	1532.9	1502.9	1472.9	1341.7	1210.5	1061.2	911.9	818.7
27.5°	1052.2	1193.7	1316.2	1438.8	1432.3	1425.9	1295.6	1165.3	1012.5	859.6	769.7
30°	929.0	1060.9	1197.9	1334.9	1350.7	1366.5	1240.8	1115.0	961.9	808.7	722.0
32.5°	820.0	935.1	1082.1	1229.2	1260.1	1291.1	1177.6	1064.1	912.5	761.0	677.5
35°	730.7	835.1	982.2	1129.2	1167.9	1206.6	1107.9	1009.3	861.6	713.9	634.3
37.5°	651.7	739.1	882.5	1026.0	1073.4	1120.8	1032.5	944.1	805.8	667.5	594.3
40°	586.2	656.5	788.4	920.3	975.1	1029.9	957.0	884.2	752.9	621.7	554.3
42.5°	531.4	594.0	713.6	833.2	885.8	938.3	876.7	815.2	698.4	581.7	520.1
45°	484.6	534.6	643.3	752.0	801.9	851.9	799.0	746.1	643.3	540.4	483.0
47.5°	440.8	483.7	576.5	669.4	713.9	758.4	717.1	675.9	588.8	501.7	449.8
50°	401.4	436.0	517.2	598.5	637.2	675.9	639.4	603.0	531.4	459.8	414.7
52.5°	367.3	395.3	463.4	531.4	564.6	597.8	566.5	535.3	478.5	421.8	382.4
55°	333.4	357.3	416.3	475.3	497.9	520.4	496.2	472.1	426.3	380.5	347.3
57.5°	301.8	323.1	371.5	419.8	437.2	454.7	432.7	410.8	376.3	341.8	314.1
60°	270.9	288.3	328.6	368.9	379.5	390.2	372.4	354.7	330.5	306.3	281.5
62.5°	242.2	258.0	287.9	317.9	325.0	332.1	318.6	305.0	286.7	268.3	248.9
65°	212.5	224.4	248.9	273.4	278.0	282.5	270.5	258.6	244.7	230.9	216.7
67.5°	185.1	193.5	213.5	233.5	233.8	234.1	224.4	214.8	207.0	199.3	188.0
70°	158.3	166.4	179.6	192.8	193.1	193.5	185.7	178.0	172.2	166.4	158.0
72.5°	130.9	136.7	146.7	156.7	156.1	155.4	150.6	145.7	141.2	136.7	130.6
75°	106.1	110.9	117.7	124.5	122.5	120.6	118.0	115.4	111.6	107.7	103.8
77.5°	83.5	86.4	90.3	94.2	92.9	91.6	89.3	87.1	84.2	81.3	79.6
80°	61.3	62.6	65.1	67.7	67.1	66.4	63.8	61.3	60.6	60.0	57.7
82.5°	41.6	43.2	43.9	44.5	44.2	43.9	41.9	40.0	39.3	38.7	38.4
85°	24.8	25.2	25.5	25.8	24.8	23.9	23.2	22.6	22.6	22.6	22.2
87.5°	11.3	11.6	11.6	11.6	11.3	11.0	10.3	9.7	10.0	10.3	10.3
90°	5.5	4.7	3.8	3.0	2.3	1.7	1.0	0.3	1.0	1.7	2.3
92.5°	12.0	11.6	11.2	10.8	10.3	9.9	9.5	9.1	9.5	9.9	10.3
95°	21.4	20.9	20.4	19.8	19.4	18.9	18.4	18.0	18.4	18.9	19.4
97.5°	32.0	31.6	31.2	30.9	30.5	30.2	29.9	29.5	29.9	30.2	30.5
100°	44.1	43.7	43.4	43.0	42.6	42.2	41.8	41.4	41.8	42.2	42.6
102.5°	57.2	56.7	56.2	55.9	55.7	55.5	55.3	55.1	55.3	55.5	55.7
105°	70.6	70.0	69.4	69.0	68.9	68.7	68.6	68.5	68.6	68.7	68.9
107.5°	85.3	85.0	84.7	84.6	84.5	84.4	84.4	84.3	84.4	84.4	84.5
110°	99.8	99.7	99.6	99.4	99.3	99.2	99.0	98.9	99.0	99.2	99.3





TEST NUMBER: P831523

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	114.4	114.4	114.4	114.4	114.3	114.2	114.2	114.1	114.2	114.2	114.3
115°	129.9	130.0	130.2	130.1	129.9	129.7	129.5	129.3	129.5	129.7	129.9
117.5°	144.8	144.9	145.1	145.1	145.0	145.0	144.9	144.8	144.9	145.0	145.0
120°	160.1	160.5	160.8	160.8	160.3	159.9	159.5	159.1	159.5	159.9	160.3
122.5°	174.9	175.1	175.2	175.1	174.9	174.6	174.3	174.0	174.3	174.6	174.9
125°	189.8	190.0	190.1	190.1	189.9	189.7	189.5	189.3	189.5	189.7	189.9
127.5°	204.7	204.9	205.0	204.9	204.5	204.1	203.7	203.3	203.7	204.1	204.5
130°	219.2	219.4	219.6	219.4	218.9	218.3	217.8	217.2	217.8	218.3	218.9
132.5°	233.3	233.5	233.6	233.4	232.9	232.3	231.8	231.2	231.8	232.3	232.9
135°	247.2	247.3	247.3	247.2	246.8	246.4	246.0	245.5	246.0	246.4	246.8
137.5°	260.7	260.5	260.3	260.0	259.6	259.3	259.0	258.6	259.0	259.3	259.6
140°	274.0	273.9	273.9	273.7	273.3	273.0	272.7	272.3	272.7	273.0	273.3
142.5°	286.7	286.5	286.4	286.1	285.8	285.5	285.1	284.8	285.1	285.5	285.8
145°	299.0	298.8	298.6	298.4	298.3	298.1	298.0	297.9	298.0	298.1	298.3
147.5°	310.9	310.7	310.5	310.2	309.9	309.7	309.4	309.1	309.4	309.7	309.9
150°	322.0	321.8	321.7	321.5	321.4	321.3	321.1	321.0	321.1	321.3	321.4
152.5°	331.8	331.8	331.7	331.6	331.3	331.1	330.9	330.7	330.9	331.1	331.3
155°	341.3	341.2	341.1	341.1	341.1	341.1	341.1	341.1	341.1	341.1	341.1
157.5°	349.8	349.7	349.6	349.6	349.7	349.8	349.8	349.9	349.8	349.8	349.7
160°	357.5	357.5	357.5	357.6	357.7	357.9	358.0	358.1	358.0	357.9	357.7
162.5°	364.7	364.6	364.5	364.6	364.8	365.0	365.2	365.4	365.2	365.0	364.8
165°	370.6	370.6	370.6	370.7	370.9	371.1	371.3	371.5	371.3	371.1	370.9
167.5°	375.6	375.6	375.5	375.6	375.9	376.1	376.4	376.7	376.4	376.1	375.9
170°	379.7	379.7	379.7	379.9	380.1	380.4	380.7	380.9	380.7	380.4	380.1
172.5°	383.1	383.1	383.1	383.2	383.5	383.8	384.0	384.3	384.0	383.8	383.5
175°	385.2	385.2	385.2	385.3	385.6	385.9	386.2	386.4	386.2	385.9	385.6
177.5°	386.4	386.4	386.4	386.6	386.8	387.1	387.4	387.6	387.4	387.1	386.8
180°	387.3	387.3	387.3	387.3	387.3	387.3	387.3	387.3	387.3	387.3	387.3



TEST NUMBER: P831523

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8
2.5°	1333.6	1321.1	1308.5	1298.8	1289.2	1272.7	1256.3	1252.4	1248.5	1243.0	1237.6
5°	1264.6	1233.7	1202.7	1175.0	1147.3	1125.7	1104.1	1089.9	1075.7	1065.4	1055.1
7.5°	1184.0	1137.6	1091.2	1058.3	1025.4	994.1	962.8	952.8	942.8	929.3	915.8
10°	1106.0	1054.7	1003.5	960.6	917.7	887.1	856.4	844.2	831.9	814.8	797.7
12.5°	1036.4	980.2	924.1	880.9	837.7	808.1	778.4	760.7	742.9	733.2	723.6
15°	963.5	903.5	843.5	803.5	763.6	736.8	710.0	694.6	679.1	669.7	660.4
17.5°	899.0	839.7	780.3	742.0	703.6	679.1	654.6	641.0	627.5	620.4	613.3
20°	837.7	779.7	721.6	684.2	646.8	626.8	606.8	598.1	589.4	583.6	577.8
22.5°	781.6	724.5	667.5	635.5	603.6	587.5	571.4	565.3	559.1	554.3	549.5
25°	725.5	674.6	623.6	596.5	569.4	556.2	543.0	536.9	530.8	525.9	521.1
27.5°	679.7	631.0	582.3	559.1	535.9	525.6	515.3	510.4	505.6	501.1	496.6
30°	635.2	591.7	548.2	528.2	508.2	498.8	489.5	484.6	479.8	475.6	471.4
32.5°	594.0	556.5	519.1	500.8	482.4	474.6	466.9	461.1	455.3	452.1	448.8
35°	554.6	521.1	487.5	472.4	457.2	449.5	441.8	436.9	432.1	429.5	426.9
37.5°	521.1	491.1	461.1	446.6	432.1	424.7	417.2	413.1	408.9	407.9	406.9
40°	486.9	461.1	435.3	421.1	406.9	400.5	394.0	391.5	388.9	388.2	387.6
42.5°	458.5	433.4	408.2	395.3	382.4	376.9	371.5	370.2	368.9	369.8	370.8
45°	425.6	404.7	383.7	371.8	359.9	355.3	350.8	349.9	348.9	350.8	352.8
47.5°	397.9	378.6	359.2	347.9	336.6	333.4	330.2	329.9	329.5	332.1	334.7
50°	369.5	350.8	332.1	323.1	314.1	311.2	308.3	309.2	310.2	314.4	318.6
52.5°	343.1	325.7	308.3	299.9	291.5	289.6	287.6	289.9	292.1	296.7	301.2
55°	314.1	298.3	282.5	276.0	269.6	267.6	265.7	270.2	274.7	278.9	283.1
57.5°	286.3	272.5	258.6	252.8	247.0	246.7	246.4	250.5	254.7	259.2	263.8
60°	256.7	245.1	233.5	228.9	224.4	225.1	225.7	230.6	235.4	238.9	242.5
62.5°	229.6	219.9	210.2	206.0	201.9	203.5	205.1	209.9	214.8	218.9	223.1
65°	202.5	194.4	186.4	183.5	180.6	182.8	185.1	189.3	193.5	196.4	199.3
67.5°	176.7	169.9	163.2	160.9	158.6	160.9	163.2	167.4	171.5	174.4	177.3
70°	149.6	144.1	138.7	137.0	135.4	138.0	140.6	144.1	147.7	150.6	153.5
72.5°	124.5	120.3	116.1	115.8	115.4	117.7	120.0	123.5	127.0	129.0	130.9
75°	100.0	97.7	95.4	95.1	94.8	97.1	99.3	101.2	103.2	104.8	106.4
77.5°	78.0	76.1	74.2	74.5	74.8	76.4	78.0	80.0	81.9	82.9	83.8
80°	55.5	54.8	54.2	54.8	55.5	56.8	58.0	59.3	60.6	61.3	61.9
82.5°	38.0	37.4	36.8	37.7	38.7	39.7	40.6	41.6	42.6	42.9	43.2
85°	21.9	22.9	23.9	23.9	23.9	24.2	24.5	24.8	25.2	24.8	24.5
87.5°	10.3	10.6	11.0	11.0	11.0	11.3	11.6	11.6	11.6	11.3	11.0
90°	3.0	3.8	4.7	5.5	6.4	7.3	7.6	7.8	8.1	8.4	8.6
92.5°	10.8	11.2	11.6	12.0	12.4	12.8	13.0	13.2	13.4	13.6	13.6
95°	19.8	20.4	20.9	21.4	22.0	22.5	22.8	23.1	23.3	23.6	23.7
97.5°	30.9	31.2	31.6	32.0	32.5	32.9	33.2	33.5	33.9	34.2	34.3
100°	43.0	43.4	43.7	44.1	44.4	44.7	44.9	45.1	45.3	45.5	45.7
102.5°	55.9	56.2	56.7	57.2	57.6	58.1	58.3	58.5	58.7	58.9	59.0
105°	69.0	69.4	70.0	70.6	71.2	71.8	71.8	71.8	71.8	71.8	71.9
107.5°	84.6	84.7	85.0	85.3	85.5	85.8	86.0	86.2	86.4	86.6	86.7
110°	99.4	99.6	99.7	99.8	100.0	100.1	100.4	100.6	100.9	101.2	101.3

TEST NUMBER: P831523

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	114.4	114.4	114.4	114.4	114.4	114.4	114.7	115.1	115.4	115.8	115.9
115°	130.1	130.2	130.0	129.9	129.8	129.6	129.7	129.8	129.8	129.9	129.9
117.5°	145.1	145.1	144.9	144.8	144.7	144.5	144.5	144.5	144.5	144.5	144.4
120°	160.8	160.8	160.5	160.1	159.8	159.4	159.4	159.3	159.2	159.2	159.1
122.5°	175.1	175.2	175.1	174.9	174.8	174.7	174.4	174.2	174.0	173.8	173.6
125°	190.1	190.1	190.0	189.8	189.7	189.6	189.3	189.0	188.7	188.5	188.2
127.5°	204.9	205.0	204.9	204.7	204.6	204.5	204.1	203.7	203.3	202.8	202.5
130°	219.4	219.6	219.4	219.2	219.0	218.8	218.5	218.2	218.0	217.7	217.3
132.5°	233.4	233.6	233.5	233.3	233.2	233.1	232.7	232.4	232.1	231.7	231.4
135°	247.2	247.3	247.3	247.2	247.1	247.1	246.8	246.5	246.3	246.0	245.8
137.5°	260.0	260.3	260.5	260.7	260.9	261.1	260.7	260.4	260.0	259.7	259.4
140°	273.7	273.9	273.9	274.0	274.1	274.1	274.1	274.0	273.9	273.9	273.6
142.5°	286.1	286.4	286.5	286.7	286.8	286.9	286.9	286.8	286.7	286.7	286.5
145°	298.4	298.6	298.8	299.0	299.2	299.4	299.3	299.3	299.2	299.1	299.0
147.5°	310.2	310.5	310.7	310.9	311.1	311.3	311.3	311.3	311.3	311.3	311.1
150°	321.5	321.7	321.8	322.0	322.1	322.2	322.2	322.2	322.2	322.2	322.0
152.5°	331.6	331.7	331.8	331.8	331.9	332.0	332.1	332.2	332.4	332.5	332.4
155°	341.1	341.1	341.2	341.3	341.3	341.4	341.7	341.9	342.2	342.5	342.4
157.5°	349.6	349.6	349.7	349.8	349.8	349.9	350.2	350.5	350.7	351.0	350.9
160°	357.6	357.5	357.5	357.5	357.5	357.5	357.9	358.2	358.5	358.9	358.9
162.5°	364.6	364.5	364.6	364.7	364.8	364.8	365.2	365.5	365.8	366.2	366.1
165°	370.7	370.6	370.6	370.6	370.6	370.6	371.0	371.4	371.8	372.2	372.2
167.5°	375.6	375.5	375.6	375.6	375.7	375.8	376.2	376.6	377.0	377.4	377.4
170°	379.9	379.7	379.7	379.7	379.7	379.7	380.2	380.7	381.1	381.6	381.6
172.5°	383.2	383.1	383.1	383.1	383.1	383.1	383.5	383.9	384.3	384.7	384.7
175°	385.3	385.2	385.2	385.2	385.2	385.2	385.6	386.0	386.4	386.8	386.8
177.5°	386.6	386.4	386.4	386.4	386.4	386.4	386.8	387.2	387.6	388.0	388.0
180°	387.3	387.3	387.3	387.3	387.3	387.3	387.3	387.3	387.3	387.3	387.3



TEST NUMBER: P831523

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1389.8	1389.8	1389.8	1389.8
2.5°	1235.3	1233.0	1224.0	1215.0
5°	1047.3	1039.6	1037.0	1034.4
7.5°	915.1	914.5	900.9	887.4
10°	798.7	799.7	787.4	775.2
12.5°	715.5	707.5	706.5	705.5
15°	653.0	645.5	644.3	643.0
17.5°	608.8	604.3	603.0	601.7
20°	575.2	572.7	570.4	568.2
22.5°	546.2	543.0	541.1	539.1
25°	518.2	515.3	514.6	514.0
27.5°	493.0	489.5	489.5	489.5
30°	469.2	466.9	465.9	465.0
32.5°	446.9	445.0	445.0	445.0
35°	426.0	425.0	423.7	422.4
37.5°	406.9	406.9	406.3	405.6
40°	388.6	389.5	389.5	389.5
42.5°	371.8	372.8	372.8	372.8
45°	354.4	356.0	356.6	357.3
47.5°	337.3	339.9	340.5	341.2
50°	320.5	322.4	322.8	323.1
52.5°	303.4	305.7	307.3	308.9
55°	285.4	287.6	288.6	289.6
57.5°	266.0	268.3	268.6	268.9
60°	244.7	247.0	247.6	248.3
62.5°	224.4	225.7	226.4	227.0
65°	201.2	203.1	204.4	205.7
67.5°	179.0	180.6	180.6	180.6
70°	154.1	154.8	155.7	156.7
72.5°	131.2	131.6	131.6	131.6
75°	107.1	107.7	108.0	108.3
77.5°	84.2	84.5	84.5	84.5
80°	61.6	61.3	61.3	61.3
82.5°	42.2	41.3	41.3	41.3
85°	24.2	23.9	24.2	24.5
87.5°	11.0	11.0	11.0	11.0
90°	8.7	8.9	9.0	9.1
92.5°	13.5	13.4	13.2	13.1
95°	23.7	23.7	23.7	23.7
97.5°	34.3	34.2	34.1	34.1
100°	45.8	46.0	46.1	46.2
102.5°	58.9	58.9	58.8	58.7
105°	72.0	72.1	72.3	72.4
107.5°	86.6	86.5	86.5	86.4
110°	101.1	101.0	100.8	100.7



TEST NUMBER: P831523

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	115.9	115.9	115.9	115.9
115°	129.8	129.8	129.7	129.6
117.5°	144.2	144.0	143.8	143.6
120°	158.9	158.8	158.7	158.5
122.5°	173.4	173.2	173.0	172.8
125°	187.9	187.7	187.4	187.1
127.5°	202.2	202.0	201.7	201.4
130°	216.8	216.4	215.9	215.4
132.5°	231.0	230.7	230.4	230.0
135°	245.6	245.5	245.4	245.2
137.5°	259.2	259.0	258.8	258.6
140°	273.1	272.7	272.2	271.7
142.5°	286.1	285.8	285.4	285.1
145°	298.7	298.4	298.1	297.9
147.5°	310.7	310.3	309.8	309.4
150°	321.6	321.2	320.8	320.4
152.5°	332.1	331.7	331.4	331.0
155°	341.9	341.4	341.0	340.5
157.5°	350.5	350.1	349.7	349.3
160°	358.6	358.4	358.1	357.8
162.5°	365.6	365.2	364.7	364.2
165°	371.7	371.2	370.8	370.3
167.5°	377.0	376.6	376.2	375.8
170°	381.1	380.7	380.2	379.7
172.5°	384.2	383.7	383.2	382.8
175°	386.3	385.8	385.4	384.9
177.5°	387.5	387.1	386.6	386.1
180°	387.3	387.3	387.3	387.3

TEST NUMBER: P831523

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-G1

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.47	15.46	15.27	16.28	17.28	16.71	17.70	17.51	18.51	19.51
	3H	16.13	17.01	16.94	17.84	18.87	18.14	19.03	18.95	19.85	20.88
	4H	16.71	17.55	17.54	18.38	19.42	18.60	19.43	19.43	20.27	21.31
	6H	17.09	17.86	17.93	18.70	19.75	18.88	19.65	19.72	20.49	21.54
	8H	17.19	17.92	18.04	18.78	19.83	18.95	19.68	19.80	20.54	21.59
	12H	17.24	17.93	18.09	18.79	19.87	18.97	19.67	19.82	20.52	21.60
4H	2H	15.06	15.90	15.89	16.73	17.77	16.89	17.72	17.72	18.56	19.60
	3H	16.90	17.60	17.74	18.46	19.52	18.52	19.21	19.36	20.08	21.13
	4H	17.60	18.24	18.46	19.10	20.18	19.10	19.74	19.96	20.60	21.68
	6H	18.09	18.63	18.96	19.52	20.61	19.52	20.06	20.39	20.95	22.04
	8H	18.22	18.73	19.10	19.62	20.72	19.63	20.14	20.51	21.02	22.12
	12H	18.30	18.76	19.19	19.66	20.76	19.68	20.14	20.58	21.04	22.15
8H	4H	17.88	18.39	18.75	19.27	20.37	19.22	19.73	20.10	20.61	21.71
	6H	18.47	18.89	19.38	19.82	20.92	19.73	20.15	20.63	21.07	22.17
	8H	18.68	19.05	19.59	19.97	21.09	19.91	20.28	20.82	21.20	22.31
	12H	18.81	19.14	19.72	20.05	21.22	20.02	20.34	20.93	21.25	22.42
12H	4H	17.89	18.34	18.78	19.25	20.35	19.20	19.66	20.10	20.56	21.67
	6H	18.52	18.90	19.44	19.81	20.93	19.74	20.11	20.65	21.03	22.15
	8H	18.76	19.09	19.68	20.00	21.17	19.95	20.28	20.86	21.18	22.35