

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332357-930

Luminaire Tested: **S123RDIP-S1000D1195U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332357-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D1195U930-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6982.5 lumens  
Efficiency: N/A  
Efficacy: 106.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332357-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332357-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	45	44	44	38
2	88	81	75	70	81	75	70	65	62	59	55	51	48	46	40	39	37	32
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	63	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	28	24	27	23	21	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14727	14727	14727
5°	14783	14579	14664
10°	14700	14397	14348
15°	14542	14060	13912
20°	14325	13639	13321
25°	14101	13166	12744
30°	13806	12621	11931
35°	13502	12073	11184
40°	13222	11428	10260
45°	12855	10794	9426
50°	12450	10071	8492
55°	12037	9246	7621
60°	11657	8361	6665
65°	11163	7404	5708
70°	10546	6216	4611
75°	9649	4891	4338
80°	8598	4333	3986
85°	7262	3841	3569



TEST NUMBER: P332357-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.5	1.8
10°-20°	357.5	5.1
20°-30°	514.7	7.4
30°-40°	579.8	8.3
40°-50°	554.7	7.9
50°-60°	454.2	6.5
60°-70°	306.5	4.4
70°-80°	154.2	2.2
80°-90°	44.4	0.6
90°-100°	46.4	0.7
100°-110°	220.9	3.2
110°-120°	530.6	7.6
120°-130°	675.7	9.7
130°-140°	722.0	10.3
140°-150°	675.1	9.7
150°-160°	544.6	7.8
160°-170°	351.5	5.0
170°-180°	121.1	1.7
0°-30°	1000.7	14.3
0°-40°	1580.5	22.6
0°-60°	2589.5	37.1
0°-90°	3094.5	44.3
90°-120°	797.9	11.4
90°-150°	2870.8	41.1
90°-180°	3888.0	55.7
0°-180°	6982.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1368	1368	1368	1368	1368	
5°	1368	1362	1349	1359	1357	130
15°	1305	1292	1262	1256	1248	367
25°	1187	1158	1109	1086	1073	546
35°	1028	986	919	873	851	643
45°	844	793	709	648	619	651
55°	641	585	493	431	406	575
65°	438	376	291	239	224	434
75°	232	178	118	107	104	247
85°	59	36	31	29	29	66
90°	1	11	23	26	28	6
95°	58	22	29	36	36	71
105°	282	287	207	49	42	299
115°	530	535	544	553	557	522
125°	746	754	758	760	762	666
135°	929	935	939	941	939	715
145°	1072	1079	1081	1083	1083	671
155°	1181	1179	1180	1184	1179	544
165°	1246	1243	1242	1249	1243	352
175°	1275	1270	1271	1277	1270	121
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P332357-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1372.6	1371.8	1371.1	1370.3	1369.5	1367.9	1365.5	1363.2	1360.8	1358.5	1360.6
5°	1368.2	1366.9	1365.7	1364.5	1363.3	1361.1	1358.2	1355.3	1352.3	1349.3	1351.5
7.5°	1355.5	1354.2	1352.9	1351.5	1350.2	1347.6	1343.8	1339.9	1336.1	1332.3	1333.5
10°	1344.9	1343.2	1341.4	1339.7	1338.0	1334.9	1330.5	1326.0	1321.6	1317.2	1317.4
12.5°	1329.8	1327.9	1326.0	1324.0	1322.1	1318.4	1313.0	1307.6	1302.2	1296.7	1296.6
15°	1305.0	1302.3	1299.5	1296.8	1294.1	1289.3	1282.4	1275.5	1268.6	1261.7	1260.5
17.5°	1273.7	1270.5	1267.4	1264.2	1261.0	1255.1	1246.3	1237.5	1228.7	1219.9	1217.3
20°	1250.6	1246.7	1242.7	1238.8	1234.8	1228.2	1218.8	1209.4	1200.0	1190.7	1187.5
22.5°	1224.8	1220.3	1215.8	1211.2	1206.7	1199.5	1189.4	1179.5	1169.5	1159.6	1155.6
25°	1187.3	1181.2	1175.0	1168.8	1162.7	1153.9	1142.6	1131.2	1119.9	1108.6	1103.3
27.5°	1141.8	1135.1	1128.2	1121.4	1114.6	1104.9	1092.3	1079.6	1067.0	1054.4	1047.2
30°	1110.8	1103.3	1096.0	1088.6	1081.2	1070.6	1056.8	1042.9	1029.2	1015.4	1007.0
32.5°	1079.7	1071.3	1062.9	1054.5	1046.2	1034.7	1020.1	1005.5	990.8	976.2	967.1
35°	1027.5	1018.6	1009.7	1000.9	992.1	979.9	964.7	949.3	934.1	918.8	908.2
37.5°	974.7	964.8	955.0	945.1	935.2	922.2	905.9	889.5	873.2	856.9	844.8
40°	941.0	930.2	919.2	908.4	897.6	883.4	865.9	848.4	830.9	813.3	800.5
42.5°	902.8	891.9	881.1	870.3	859.4	845.0	826.9	808.8	790.7	772.6	758.6
45°	844.5	833.3	822.2	811.1	800.1	785.1	766.1	747.1	728.1	709.1	695.0
47.5°	786.1	773.9	761.7	749.5	737.4	721.8	702.8	683.8	664.8	645.8	630.6
50°	743.5	731.9	720.3	708.7	697.1	681.3	661.4	641.4	621.4	601.4	586.1
52.5°	705.3	692.8	680.1	667.6	655.0	638.8	619.1	599.2	579.5	559.7	543.8
55°	641.4	629.3	617.2	605.1	593.0	576.5	555.5	534.6	513.6	492.7	478.4
57.5°	582.4	569.2	556.0	542.8	529.7	512.6	491.5	470.4	449.4	428.4	414.8
60°	541.5	528.0	514.4	500.8	487.2	470.3	449.8	429.3	408.9	388.4	375.0
62.5°	500.7	487.1	473.5	460.0	446.5	429.4	409.0	388.5	368.0	347.6	335.0
65°	438.3	424.8	411.2	397.6	384.1	367.7	348.5	329.2	310.0	290.7	278.7
67.5°	375.9	362.2	348.5	334.8	321.1	305.0	286.6	268.2	249.7	231.2	222.3
70°	335.1	321.8	308.5	295.1	281.8	266.6	249.3	232.0	214.7	197.5	188.9
72.5°	294.2	281.2	268.1	254.9	241.8	227.4	211.7	196.1	180.3	164.7	157.6
75°	232.0	220.0	208.2	196.4	184.6	171.9	158.3	144.7	131.2	117.6	115.1
77.5°	175.1	164.4	153.7	143.0	132.3	122.5	113.8	105.1	96.4	87.6	86.3
80°	138.7	128.6	118.5	108.4	98.2	90.7	85.4	80.2	75.1	69.9	69.1
82.5°	104.1	95.4	86.7	77.9	69.1	63.6	61.1	58.8	56.3	53.9	53.2
85°	58.8	53.4	47.9	42.6	37.1	34.0	33.3	32.5	31.8	31.1	30.6
87.5°	21.5	19.7	18.0	16.2	14.5	13.9	14.4	15.0	15.6	16.1	16.1
90°	1.0	3.0	5.1	7.3	9.4	11.8	14.5	17.3	20.0	22.7	23.6
92.5°	17.6	17.0	16.5	15.8	15.2	16.0	18.1	20.1	22.2	24.2	25.6
95°	57.8	49.2	40.5	31.9	23.2	20.1	22.4	24.7	27.1	29.4	30.8
97.5°	116.1	112.3	108.4	104.5	100.6	91.2	76.0	60.8	45.7	30.5	32.2
100°	160.0	164.3	168.5	172.7	176.9	162.6	129.8	96.9	64.1	31.2	32.9
102.5°	210.1	213.1	216.1	219.2	222.3	205.8	169.9	134.0	98.2	62.3	57.1
105°	282.3	284.6	286.9	289.2	291.6	283.2	264.2	245.3	226.4	207.4	170.2
107.5°	358.4	360.3	362.2	363.9	365.8	368.3	371.3	374.2	377.2	380.3	352.9
110°	409.2	410.9	412.5	414.3	416.0	417.9	420.3	422.6	424.9	427.2	420.3



TEST NUMBER: P332357-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	457.7	459.2	460.7	462.3	463.7	465.7	468.0	470.3	472.6	474.9	475.1
115°	529.5	530.8	532.0	533.3	534.5	536.1	538.0	539.9	541.8	543.7	545.8
117.5°	599.0	600.5	602.1	603.7	605.3	606.5	607.5	608.5	609.4	610.4	612.0
120°	642.2	644.1	646.0	647.9	649.8	651.1	651.7	652.3	653.0	653.5	655.3
122.5°	686.2	687.7	689.3	690.8	692.4	693.6	694.4	695.2	695.9	696.8	698.0
125°	746.4	748.1	749.7	751.5	753.2	754.4	755.2	756.1	756.9	757.7	758.2
127.5°	804.8	806.4	808.1	809.8	811.5	812.9	813.8	814.9	815.9	816.8	817.6
130°	841.1	842.9	844.5	846.2	847.8	849.1	849.9	850.8	851.7	852.5	853.4
132.5°	876.0	877.7	879.4	881.0	882.7	883.9	884.6	885.3	885.9	886.6	887.5
135°	929.2	930.5	931.7	933.0	934.3	935.3	936.2	937.0	937.8	938.7	939.3
137.5°	974.7	976.3	977.9	979.5	981.1	982.1	982.6	983.1	983.5	984.0	985.0
140°	1005.0	1006.2	1007.5	1008.8	1010.1	1011.0	1011.6	1012.3	1012.9	1013.5	1014.4
142.5°	1033.1	1034.3	1035.6	1036.8	1038.1	1039.0	1039.7	1040.3	1041.0	1041.5	1042.3
145°	1072.3	1073.7	1075.2	1076.7	1078.2	1079.1	1079.5	1079.9	1080.4	1080.8	1081.2
147.5°	1109.2	1110.2	1111.2	1112.1	1113.0	1113.8	1114.2	1114.6	1115.0	1115.4	1115.9
150°	1132.0	1132.5	1133.2	1133.8	1134.5	1135.0	1135.4	1135.8	1136.3	1136.7	1137.1
152.5°	1152.4	1152.7	1153.0	1153.2	1153.6	1153.8	1154.1	1154.4	1154.6	1154.9	1155.6
155°	1181.2	1180.8	1180.3	1179.9	1179.5	1179.4	1179.6	1179.8	1180.1	1180.2	1181.3
157.5°	1203.5	1203.5	1203.5	1203.4	1203.4	1203.2	1203.1	1202.8	1202.6	1202.4	1203.7
160°	1217.2	1217.0	1216.8	1216.6	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3	1216.6
162.5°	1230.0	1229.6	1229.0	1228.4	1227.8	1227.5	1227.3	1227.1	1226.9	1226.6	1228.1
165°	1245.6	1245.0	1244.3	1243.7	1243.1	1242.7	1242.4	1242.2	1242.0	1241.8	1243.5
167.5°	1257.8	1256.9	1256.1	1255.2	1254.3	1253.9	1253.9	1253.9	1253.9	1253.9	1255.6
170°	1264.5	1263.7	1262.9	1262.0	1261.2	1260.8	1260.8	1260.8	1260.8	1260.8	1262.4
172.5°	1269.1	1268.1	1267.1	1266.1	1265.0	1264.6	1264.8	1264.9	1265.1	1265.3	1267.0
175°	1275.0	1273.9	1272.8	1271.8	1270.7	1270.3	1270.6	1270.7	1271.0	1271.1	1272.7
177.5°	1276.5	1275.6	1274.8	1274.0	1273.1	1272.8	1272.9	1273.1	1273.3	1273.4	1274.8
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P332357-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1362.8	1365.0	1367.1	1368.0	1367.6	1367.3	1366.8	1366.4
5°	1353.8	1356.0	1358.2	1359.1	1358.6	1358.1	1357.6	1357.1
7.5°	1334.7	1335.9	1337.2	1337.4	1336.5	1335.7	1334.9	1334.0
10°	1317.7	1317.9	1318.2	1317.7	1316.4	1315.2	1313.9	1312.7
12.5°	1296.4	1296.3	1296.2	1295.3	1294.0	1292.5	1291.1	1289.6
15°	1259.2	1258.0	1256.8	1255.2	1253.5	1251.8	1250.1	1248.4
17.5°	1214.7	1212.1	1209.5	1206.9	1204.4	1201.8	1199.2	1196.6
20°	1184.2	1181.0	1177.9	1174.8	1171.8	1168.8	1165.9	1162.9
22.5°	1151.6	1147.6	1143.6	1140.2	1137.5	1134.7	1132.0	1129.2
25°	1098.2	1093.0	1087.9	1083.9	1081.2	1078.5	1075.8	1073.0
27.5°	1040.0	1032.8	1025.6	1019.9	1015.8	1011.6	1007.5	1003.4
30°	998.6	990.2	981.8	975.7	971.7	967.8	963.8	959.9
32.5°	957.9	948.8	939.6	932.9	928.8	924.6	920.5	916.3
35°	897.6	887.0	876.4	868.9	864.5	860.0	855.6	851.1
37.5°	832.8	820.8	808.8	800.0	794.5	789.0	783.6	778.1
40°	787.7	774.9	762.1	752.8	747.1	741.5	735.8	730.2
42.5°	744.5	730.5	716.5	706.9	701.9	696.8	691.7	686.6
45°	680.9	666.9	652.8	642.9	636.9	631.0	625.1	619.2
47.5°	615.2	600.0	584.7	574.4	569.1	563.9	558.6	553.3
50°	570.9	555.5	540.3	529.8	524.2	518.4	512.8	507.1
52.5°	528.0	512.1	496.2	485.7	480.6	475.6	470.5	465.4
55°	464.1	449.8	435.5	425.8	420.9	416.0	411.1	406.1
57.5°	401.3	387.8	374.3	365.4	361.3	357.0	352.9	348.6
60°	361.7	348.5	335.1	326.4	322.2	318.0	313.8	309.6
62.5°	322.5	310.0	297.4	288.9	284.6	280.2	275.8	271.4
65°	266.6	254.5	242.4	235.0	232.3	229.6	226.9	224.1
67.5°	213.2	204.2	195.2	189.1	186.3	183.4	180.4	177.6
70°	180.3	171.6	163.0	157.4	154.6	151.9	149.2	146.5
72.5°	150.6	143.5	136.5	132.4	131.3	130.1	129.0	127.8
75°	112.7	110.2	107.8	106.3	105.8	105.3	104.8	104.3
77.5°	85.0	83.6	82.3	81.4	81.0	80.5	80.0	79.5
80°	68.4	67.7	66.9	66.4	65.9	65.4	64.8	64.3
82.5°	52.4	51.7	51.0	50.5	50.5	50.4	50.2	50.1
85°	30.1	29.6	29.1	28.9	28.9	28.9	28.9	28.9
87.5°	16.1	16.0	16.0	15.9	15.8	15.7	15.6	15.4
90°	24.4	25.3	26.1	26.7	27.1	27.6	28.0	28.5
92.5°	26.9	28.3	29.7	30.4	30.7	31.0	31.2	31.5
95°	32.3	33.8	35.2	36.0	36.0	36.0	36.0	36.0
97.5°	33.8	35.5	37.3	38.2	38.4	38.6	38.8	39.1
100°	34.7	36.3	38.0	39.0	39.1	39.4	39.5	39.8
102.5°	51.9	46.6	41.4	39.1	39.4	39.8	40.2	40.5
105°	132.9	95.6	58.4	40.0	40.4	40.8	41.3	41.7
107.5°	325.5	298.2	270.9	243.2	215.2	187.0	159.0	130.9
110°	413.3	406.3	399.4	380.9	350.8	320.7	290.6	260.5





TEST NUMBER: P332357-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	475.2	475.3	475.5	472.3	465.9	459.6	453.2	446.9
115°	547.9	550.0	552.1	553.6	554.4	555.3	556.1	556.9
117.5°	613.8	615.5	617.1	618.1	618.2	618.4	618.6	618.7
120°	657.0	658.6	660.3	661.1	661.1	661.1	661.1	661.1
122.5°	699.1	700.3	701.5	702.1	702.3	702.5	702.7	702.9
125°	758.6	759.0	759.5	759.9	760.3	760.8	761.2	761.6
127.5°	818.2	818.9	819.5	819.7	819.3	818.9	818.5	818.0
130°	854.2	855.0	855.9	856.1	855.7	855.2	854.8	854.4
132.5°	888.3	889.2	890.0	890.1	889.5	888.9	888.4	887.7
135°	940.0	940.6	941.3	941.3	940.6	940.0	939.3	938.7
137.5°	986.0	987.0	988.0	988.3	987.9	987.5	987.1	986.6
140°	1015.2	1016.0	1016.9	1017.1	1016.7	1016.3	1015.9	1015.5
142.5°	1042.9	1043.6	1044.2	1044.3	1043.7	1043.1	1042.5	1042.0
145°	1081.7	1082.1	1082.5	1082.6	1082.6	1082.6	1082.6	1082.6
147.5°	1116.3	1116.7	1117.1	1116.9	1115.9	1114.9	1113.9	1113.0
150°	1137.5	1137.9	1138.3	1138.2	1137.6	1137.0	1136.4	1135.7
152.5°	1156.3	1157.2	1157.9	1157.8	1156.8	1155.8	1154.9	1153.9
155°	1182.3	1183.4	1184.5	1184.3	1183.1	1181.9	1180.6	1179.3
157.5°	1204.9	1206.2	1207.5	1207.3	1205.7	1204.0	1202.3	1200.7
160°	1217.8	1219.0	1220.3	1220.3	1218.8	1217.3	1215.8	1214.3
162.5°	1229.6	1230.9	1232.4	1232.4	1231.1	1229.8	1228.5	1227.2
165°	1245.2	1246.8	1248.5	1248.6	1247.2	1245.7	1244.2	1242.8
167.5°	1257.3	1259.0	1260.7	1260.7	1259.0	1257.3	1255.6	1253.9
170°	1264.1	1265.8	1267.5	1267.5	1265.8	1264.1	1262.4	1260.8
172.5°	1268.7	1270.3	1272.0	1271.9	1270.1	1268.3	1266.4	1264.5
175°	1274.1	1275.6	1277.1	1276.9	1275.3	1273.6	1271.9	1270.2
177.5°	1276.1	1277.5	1278.8	1278.6	1277.0	1275.3	1273.6	1271.9
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0

(END OF REPORT)