

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331934-935

Luminaire Tested: **S123DIP-S560D805U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331934-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D805U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4761.4 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331934-935

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331934-935

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	84	87	84	80	77	69	67	65	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	19
6	61	49	41	36	56	46	38	33	38	33	29	31	27	24	24	22	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13
9	49	37	29	24	45	34	27	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8257	8257	8257
5°	8295	8182	8238
10°	8240	8110	8160
15°	8143	8018	8033
20°	8031	7887	7895
25°	7880	7732	7715
30°	7713	7558	7501
35°	7540	7376	7281
40°	7359	7173	7062
45°	7159	6987	6817
50°	6958	6759	6571
55°	6696	6523	6324
60°	6433	6247	6047
65°	6199	5947	5761
70°	5854	5605	5353
75°	5348	5157	4937
80°	4823	4624	4581
85°	4236	4076	3915



TEST NUMBER: P331934-935

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	1.5
10°-20°	204.0	4.3
20°-30°	301.4	6.3
30°-40°	352.0	7.4
40°-50°	353.9	7.4
50°-60°	310.9	6.5
60°-70°	231.6	4.9
70°-80°	132.0	2.8
80°-90°	40.4	0.8
90°-100°	32.9	0.7
100°-110°	157.0	3.3
110°-120°	377.1	7.9
120°-130°	480.2	10.1
130°-140°	513.1	10.8
140°-150°	479.8	10.1
150°-160°	387.0	8.1
160°-170°	249.8	5.2
170°-180°	86.1	1.8
0°-30°	577.6	12.1
0°-40°	929.7	19.5
0°-60°	1594.5	33.5
0°-90°	1998.5	42.0
90°-120°	567.0	11.9
90°-150°	2040.1	42.8
90°-180°	2763.0	58.0
0°-180°	4761.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	768	764	757	763	762	73
15°	731	728	720	724	721	206
25°	664	659	651	651	650	305
35°	574	570	561	557	554	359
45°	470	467	459	451	448	363
55°	357	356	348	340	337	319
65°	243	240	234	228	226	240
75°	129	126	124	121	119	138
85°	34	33	33	32	32	38
90°	1	8	16	19	20	4
95°	41	15	21	25	26	51
105°	201	204	147	35	30	213
115°	376	380	386	393	396	371
125°	530	536	538	540	541	474
135°	660	664	667	669	667	508
145°	762	766	768	769	769	477
155°	839	838	839	842	838	387
165°	885	883	882	887	883	250
175°	906	903	903	907	903	86
180°	906	906	906	906	906	



TEST NUMBER: P331934-935

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	769.6	769.2	768.8	768.3	767.8	766.9	765.6	764.3	763.1	761.8	762.9
5°	767.7	767.0	766.2	765.5	764.7	763.6	762.0	760.3	758.8	757.2	758.6
7.5°	760.2	759.5	758.7	758.0	757.2	756.0	754.4	752.7	751.1	749.4	750.7
10°	753.9	753.1	752.4	751.7	751.0	749.6	747.7	745.8	743.9	742.0	743.3
12.5°	745.5	744.8	744.2	743.6	743.0	741.8	739.9	738.1	736.4	734.6	735.6
15°	730.7	730.2	729.6	729.0	728.4	727.2	725.3	723.4	721.4	719.5	720.7
17.5°	713.8	713.0	712.2	711.4	710.7	709.4	707.5	705.6	703.7	701.7	702.6
20°	701.1	700.3	699.3	698.4	697.6	696.2	694.3	692.4	690.4	688.5	689.1
22.5°	686.8	686.0	685.1	684.2	683.3	681.9	680.0	678.1	676.2	674.3	674.8
25°	663.5	662.6	661.8	660.9	660.0	658.6	656.7	654.8	652.9	651.0	651.1
27.5°	638.6	637.7	636.9	636.0	635.2	633.7	631.6	629.6	627.6	625.5	625.6
30°	620.6	619.9	619.1	618.5	617.7	616.3	614.2	612.2	610.2	608.1	608.1
32.5°	602.7	601.8	600.7	599.8	598.8	597.5	596.0	594.3	592.8	591.2	590.4
35°	573.8	572.9	572.0	571.2	570.3	568.9	567.0	565.1	563.2	561.3	560.4
37.5°	544.2	543.1	542.0	540.9	539.8	538.3	536.3	534.4	532.4	530.5	529.5
40°	523.7	522.8	521.9	521.1	520.1	518.7	516.6	514.6	512.6	510.5	509.3
42.5°	503.1	502.1	501.1	500.1	499.1	497.6	495.5	493.5	491.5	489.4	488.2
45°	470.3	469.7	469.1	468.5	467.9	466.7	464.8	462.9	461.0	459.0	457.3
47.5°	437.6	436.8	436.0	435.1	434.3	432.9	431.2	429.4	427.6	425.8	424.0
50°	415.5	414.7	414.1	413.3	412.6	411.3	409.3	407.4	405.5	403.6	402.0
52.5°	392.3	391.8	391.3	390.8	390.3	389.0	387.0	385.0	383.0	381.0	379.6
55°	356.8	356.6	356.5	356.4	356.2	355.2	353.3	351.4	349.5	347.6	345.9
57.5°	323.0	322.5	322.0	321.6	321.1	320.0	318.5	317.0	315.5	313.9	312.5
60°	298.8	298.6	298.5	298.3	298.2	297.2	295.5	293.7	292.0	290.2	288.9
62.5°	277.2	276.7	276.4	276.0	275.6	274.6	272.8	271.0	269.2	267.5	266.2
65°	243.4	242.6	241.9	241.2	240.5	239.4	237.9	236.4	235.0	233.5	232.3
67.5°	207.6	207.0	206.3	205.7	205.0	204.1	203.0	201.9	200.8	199.8	198.7
70°	186.0	185.1	184.3	183.4	182.4	181.6	180.7	179.9	178.9	178.1	177.0
72.5°	163.3	162.6	162.0	161.4	160.7	159.9	158.9	157.9	156.9	155.9	155.0
75°	128.6	128.0	127.4	126.8	126.3	125.8	125.3	124.8	124.4	124.0	123.3
77.5°	97.9	97.6	97.2	96.9	96.6	96.2	95.7	95.1	94.5	94.0	93.6
80°	77.8	77.4	77.0	76.5	76.0	75.7	75.4	75.1	74.8	74.6	74.4
82.5°	58.3	58.2	58.1	58.0	57.9	57.9	57.9	57.8	57.7	57.7	57.3
85°	34.3	34.0	33.8	33.4	33.1	33.0	33.0	33.0	33.0	33.0	32.7
87.5°	13.9	13.8	13.8	13.7	13.6	13.8	14.0	14.3	14.6	14.8	14.8
90°	0.7	2.2	3.7	5.2	6.6	8.4	10.3	12.2	14.2	16.2	16.8
92.5°	12.5	12.1	11.7	11.3	10.8	11.4	12.8	14.3	15.8	17.2	18.2
95°	41.1	35.0	28.8	22.6	16.5	14.3	15.9	17.6	19.2	20.8	22.0
97.5°	82.5	79.8	77.1	74.3	71.5	64.7	54.0	43.2	32.5	21.7	22.9
100°	113.7	116.8	119.8	122.7	125.7	115.5	92.2	68.9	45.5	22.2	23.4
102.5°	149.3	151.4	153.6	155.8	157.9	146.3	120.8	95.2	69.7	44.3	40.6
105°	200.6	202.2	203.9	205.5	207.2	201.3	187.8	174.4	160.8	147.4	121.0
107.5°	254.7	256.1	257.4	258.6	259.9	261.7	263.8	266.0	268.0	270.2	250.8
110°	290.8	292.0	293.2	294.4	295.6	297.0	298.7	300.3	302.0	303.6	298.7



TEST NUMBER: P331934-935

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.3	326.3	327.4	328.5	329.6	330.9	332.6	334.2	335.9	337.5	337.6
115°	376.3	377.2	378.1	379.0	379.9	381.0	382.4	383.7	385.0	386.4	387.9
117.5°	425.7	426.8	427.9	429.0	430.1	431.0	431.7	432.4	433.1	433.8	435.0
120°	456.4	457.7	459.1	460.4	461.8	462.7	463.1	463.6	464.0	464.4	465.6
122.5°	487.6	488.7	489.8	490.9	492.1	492.8	493.4	494.0	494.6	495.2	496.0
125°	530.5	531.6	532.8	534.0	535.2	536.1	536.7	537.3	537.9	538.5	538.8
127.5°	571.9	573.1	574.3	575.5	576.7	577.6	578.3	579.1	579.8	580.5	581.0
130°	597.7	598.9	600.1	601.3	602.5	603.4	604.0	604.6	605.2	605.8	606.4
132.5°	622.5	623.7	624.9	626.1	627.3	628.1	628.6	629.0	629.6	630.1	630.7
135°	660.3	661.2	662.1	663.1	663.9	664.7	665.3	665.9	666.5	667.1	667.5
137.5°	692.7	693.8	694.9	696.0	697.2	697.9	698.3	698.6	698.9	699.2	700.0
140°	714.2	715.1	716.0	716.9	717.8	718.4	718.9	719.4	719.8	720.2	720.8
142.5°	734.1	735.0	735.9	736.8	737.7	738.4	738.8	739.3	739.7	740.2	740.6
145°	762.0	763.0	764.1	765.1	766.2	766.8	767.2	767.4	767.8	768.0	768.4
147.5°	788.2	788.9	789.6	790.3	791.0	791.5	791.8	792.0	792.4	792.6	793.0
150°	804.3	804.9	805.3	805.7	806.2	806.6	806.8	807.2	807.4	807.8	808.0
152.5°	818.9	819.2	819.3	819.6	819.8	819.9	820.1	820.3	820.5	820.7	821.2
155°	839.4	839.1	838.8	838.5	838.2	838.1	838.3	838.4	838.5	838.7	839.5
157.5°	855.2	855.2	855.2	855.1	855.1	855.1	854.9	854.8	854.6	854.5	855.4
160°	865.0	864.8	864.7	864.5	864.4	864.2	864.1	863.9	863.8	863.6	864.5
162.5°	874.1	873.7	873.3	873.0	872.5	872.3	872.1	872.0	871.8	871.7	872.7
165°	885.2	884.7	884.2	883.8	883.4	883.0	883.0	882.8	882.6	882.4	883.6
167.5°	893.8	893.2	892.6	892.0	891.4	891.0	891.0	891.0	891.0	891.0	892.3
170°	898.6	898.0	897.4	896.8	896.2	896.0	896.0	896.0	896.0	896.0	897.2
172.5°	901.8	901.1	900.4	899.7	899.0	898.7	898.8	898.9	899.1	899.1	900.3
175°	906.0	905.3	904.6	903.8	903.0	902.8	902.8	903.0	903.2	903.4	904.4
177.5°	907.1	906.5	905.9	905.3	904.7	904.5	904.6	904.7	904.8	904.9	905.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P331934-935

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	764.1	765.3	766.5	767.0	766.9	766.7	766.6	766.5
5°	760.1	761.6	763.0	763.6	763.3	763.0	762.8	762.4
7.5°	752.0	753.3	754.7	755.2	755.0	754.8	754.7	754.5
10°	744.6	746.0	747.3	747.8	747.5	747.2	746.9	746.6
12.5°	736.5	737.5	738.5	738.8	738.7	738.5	738.3	738.1
15°	721.9	723.1	724.3	724.4	723.5	722.6	721.8	720.9
17.5°	703.4	704.2	705.1	705.2	705.0	704.6	704.3	704.0
20°	689.7	690.3	690.9	691.0	690.5	690.1	689.7	689.2
22.5°	675.3	675.7	676.2	676.1	675.6	675.0	674.5	673.9
25°	651.3	651.4	651.5	651.4	651.0	650.6	650.1	649.6
27.5°	625.8	625.9	625.9	625.8	625.2	624.7	624.1	623.5
30°	608.1	608.1	608.1	607.6	606.6	605.5	604.5	603.5
32.5°	589.6	588.8	587.9	587.2	586.7	586.2	585.6	585.0
35°	559.5	558.6	557.8	557.0	556.2	555.5	554.7	554.1
37.5°	528.4	527.4	526.3	525.6	525.1	524.6	524.2	523.7
40°	508.2	507.0	505.8	504.9	504.3	503.8	503.2	502.6
42.5°	487.1	485.9	484.7	483.8	483.2	482.7	482.1	481.5
45°	455.6	453.7	452.0	450.7	450.0	449.3	448.6	447.8
47.5°	422.3	420.6	418.9	417.7	417.1	416.4	415.8	415.1
50°	400.5	398.8	397.2	396.0	395.0	394.2	393.3	392.4
52.5°	378.2	376.9	375.5	374.3	373.4	372.6	371.7	370.8
55°	344.3	342.8	341.1	339.9	339.2	338.5	337.8	337.0
57.5°	311.1	309.6	308.2	307.0	306.2	305.4	304.5	303.7
60°	287.6	286.3	284.9	283.9	283.2	282.4	281.7	280.9
62.5°	264.8	263.6	262.3	261.3	260.8	260.4	259.8	259.3
65°	231.1	230.0	228.8	228.0	227.6	227.1	226.7	226.2
67.5°	197.7	196.7	195.6	194.8	194.2	193.6	193.0	192.3
70°	176.0	175.0	174.0	173.1	172.4	171.6	170.9	170.1
72.5°	154.1	153.2	152.3	151.6	151.3	150.8	150.5	150.1
75°	122.5	121.8	121.1	120.5	120.0	119.6	119.2	118.7
77.5°	93.1	92.6	92.0	91.8	91.8	91.8	91.8	91.8
80°	74.2	74.0	74.0	73.9	73.9	73.9	73.9	73.9
82.5°	57.1	56.8	56.6	56.4	56.3	56.1	56.1	56.0
85°	32.4	32.1	31.8	31.7	31.7	31.7	31.7	31.7
87.5°	14.8	14.8	14.8	14.9	15.0	15.0	15.1	15.2
90°	17.4	17.9	18.5	19.0	19.3	19.6	19.9	20.2
92.5°	19.1	20.1	21.1	21.6	21.8	22.0	22.1	22.4
95°	23.0	24.0	25.1	25.6	25.6	25.6	25.6	25.6
97.5°	24.1	25.2	26.4	27.1	27.3	27.5	27.6	27.7
100°	24.6	25.8	27.0	27.6	27.8	28.0	28.2	28.2
102.5°	36.9	33.1	29.4	27.7	28.0	28.2	28.5	28.8
105°	94.5	68.0	41.5	28.4	28.8	29.0	29.4	29.6
107.5°	231.4	212.0	192.5	172.8	152.9	132.9	113.0	93.0
110°	293.7	288.8	283.9	270.7	249.3	227.9	206.5	185.1



TEST NUMBER: P331934-935

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	337.7	337.8	337.9	335.6	331.1	326.6	322.1	317.6
115°	389.3	390.9	392.4	393.4	394.0	394.6	395.2	395.8
117.5°	436.2	437.4	438.5	439.2	439.4	439.5	439.5	439.7
120°	466.8	468.0	469.2	469.8	469.8	469.8	469.8	469.8
122.5°	496.8	497.7	498.5	498.9	499.1	499.2	499.4	499.5
125°	539.1	539.4	539.7	540.0	540.3	540.6	540.9	541.2
127.5°	581.4	581.9	582.4	582.5	582.2	581.9	581.6	581.3
130°	607.0	607.6	608.2	608.4	608.0	607.8	607.4	607.2
132.5°	631.2	631.8	632.4	632.5	632.1	631.7	631.3	630.9
135°	668.0	668.4	668.8	668.8	668.4	668.0	667.5	667.1
137.5°	700.7	701.4	702.1	702.3	702.1	701.7	701.5	701.1
140°	721.4	722.0	722.6	722.8	722.5	722.2	721.9	721.6
142.5°	741.1	741.6	742.1	742.1	741.7	741.2	740.9	740.5
145°	768.6	769.0	769.2	769.4	769.4	769.4	769.4	769.4
147.5°	793.2	793.6	793.8	793.7	793.0	792.3	791.6	790.9
150°	808.3	808.7	808.9	808.9	808.4	808.0	807.5	807.1
152.5°	821.7	822.3	822.9	822.8	822.1	821.4	820.7	820.0
155°	840.2	840.9	841.7	841.6	840.8	839.8	839.0	838.0
157.5°	856.3	857.1	858.1	857.9	856.8	855.6	854.5	853.3
160°	865.4	866.3	867.2	867.1	866.1	865.0	864.0	863.0
162.5°	873.7	874.8	875.7	875.8	874.9	873.9	873.1	872.1
165°	884.8	886.1	887.3	887.3	886.3	885.2	884.2	883.1
167.5°	893.5	894.7	895.9	895.9	894.7	893.5	892.3	891.0
170°	898.3	899.5	900.7	900.7	899.5	898.3	897.2	896.0
172.5°	901.6	902.8	904.0	903.9	902.6	901.3	899.9	898.6
175°	905.4	906.5	907.5	907.4	906.3	905.1	903.9	902.7
177.5°	906.9	907.8	908.8	908.7	907.5	906.3	905.1	903.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0

(END OF REPORT)