

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332342-930

Luminaire Tested: **S123RDIP-S1000D805U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332342-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D805U930-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 805 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5845.8 lumens  
Efficiency: N/A  
Efficacy: 107.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	100	95	92	88	92	89	86	83	77	74	72	65	64	62	55	54	53	48
2	91	84	78	73	85	78	73	69	68	64	61	58	55	53	49	47	45	41
3	84	75	67	62	78	70	63	58	60	56	52	52	48	46	44	42	39	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	34	31
5	71	59	52	46	66	56	49	44	49	43	39	42	38	35	36	33	30	27
6	65	54	46	40	61	50	43	38	44	39	34	38	34	31	33	30	27	24
7	61	49	41	35	56	46	39	34	40	35	31	35	31	27	30	27	24	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	24	22	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	22	20	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13951	13951	13951	13951
5°	16630	14011	12337	14011
10°	20764	13930	11146	13930
15°	24373	13788	10165	13788
20°	27202	13575	9330	13575
25°	26766	13351	8817	13351
30°	19240	13144	8289	13144
35°	12846	12875	7947	12875
40°	9465	12552	7593	12552
45°	7939	11985	7247	11985
50°	7005	11241	6764	11241
55°	6142	10393	6101	10393
60°	5470	9580	5591	9580
65°	4806	8706	5201	8706
70°	3770	7928	4749	7928
75°	3323	6924	4338	6924
80°	2889	5883	4265	5883
85°	2322	4730	4520	4730



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.5	2.2
10°-20°	398.2	6.8
20°-30°	625.6	10.7
30°-40°	652.7	11.2
40°-50°	558.6	9.6
50°-60°	425.7	7.3
60°-70°	272.9	4.7
70°-80°	131.3	2.2
80°-90°	37.1	0.6
90°-100°	31.2	0.5
100°-110°	148.7	2.5
110°-120°	357.1	6.1
120°-130°	454.7	7.8
130°-140°	485.8	8.3
140°-150°	454.3	7.8
150°-160°	366.5	6.3
160°-170°	236.5	4.0
170°-180°	81.5	1.4
0°-30°	1151.2	19.7
0°-40°	1803.9	30.9
0°-60°	2788.2	47.7
0°-90°	3229.5	55.2
90°-120°	536.9	9.2
90°-150°	1931.8	33.0
90°-180°	2616.0	44.8
0°-180°	5845.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1296	1296	1296	1296	1296	
5°	1539	1297	1142	1297	1539	159
15°	2187	1237	912	1237	2187	620
25°	2254	1124	742	1124	2254	969
35°	978	980	605	980	978	641
45°	522	787	476	787	522	410
55°	327	554	325	554	327	296
65°	189	342	204	342	189	186
75°	80	166	104	166	80	86
85°	19	38	37	38	19	22
90°	19	1	19	1	19	9
95°	24	39	24	39	24	20
105°	28	190	28	190	28	64
115°	375	356	375	356	375	346
125°	512	502	512	502	512	458
135°	632	625	632	625	632	487
145°	729	722	729	722	729	455
155°	794	795	794	795	794	366
165°	836	838	836	838	836	236
175°	855	858	855	858	855	81
180°	858	858	858	858	858	



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1380.5	1382.2	1376.5	1375.6	1368.9	1367.1	1367.1	1357.8	1352.0	1344.5	1340.0
5°	1539.1	1548.0	1543.5	1533.6	1516.9	1513.0	1502.5	1485.9	1467.0	1443.7	1432.6
7.5°	1737.3	1749.4	1744.7	1729.3	1711.9	1697.8	1668.1	1640.5	1601.7	1567.7	1538.7
10°	1899.7	1887.0	1877.0	1862.1	1845.9	1819.8	1788.8	1746.0	1696.7	1657.8	1614.6
12.5°	2021.4	2019.3	2006.6	1991.2	1968.5	1943.7	1905.5	1853.5	1796.1	1740.0	1690.4
15°	2187.2	2190.5	2182.1	2166.1	2133.9	2090.1	2032.4	2010.8	1928.6	1867.6	1806.5
17.5°	2301.9	2301.3	2300.1	2277.9	2245.0	2213.8	2160.3	2103.4	2029.0	1943.0	1860.8
20°	2374.7	2369.2	2370.2	2345.3	2320.9	2284.8	2232.7	2150.0	2089.0	1989.7	1904.8
22.5°	2372.9	2371.8	2376.0	2367.5	2349.8	2322.1	2281.0	2211.3	2133.3	2033.1	1937.6
25°	2253.7	2249.3	2275.4	2282.6	2310.9	2315.9	2303.7	2265.4	2191.6	2088.4	1970.3
27.5°	1886.2	1883.7	1932.2	1992.8	2069.6	2129.2	2187.0	2214.8	2191.6	2117.7	1999.3
30°	1548.0	1600.2	1624.6	1712.2	1809.9	1926.4	2028.5	2125.6	2149.5	2117.3	2020.1
32.5°	1285.2	1330.7	1351.1	1426.4	1517.4	1653.8	1807.0	1944.5	2041.6	2066.2	2007.8
35°	977.6	978.2	1024.7	1058.1	1142.4	1282.8	1431.5	1615.7	1798.8	1937.5	1951.9
37.5°	780.1	782.9	811.1	844.2	907.5	981.7	1112.6	1265.8	1477.3	1690.3	1815.1
40°	673.6	678.6	699.7	732.4	777.9	833.9	936.0	1080.3	1256.7	1493.6	1687.3
42.5°	605.2	613.3	624.2	649.4	677.6	730.0	812.6	924.1	1084.5	1308.6	1531.9
45°	521.5	525.9	534.3	545.9	571.4	608.1	663.6	738.5	871.6	1052.0	1275.5
47.5°	460.1	457.7	466.5	476.0	492.9	517.9	555.1	616.2	711.2	855.9	1045.5
50°	418.3	417.8	423.9	431.1	447.2	465.5	496.0	542.1	617.5	737.4	911.0
52.5°	379.3	381.4	385.7	394.7	406.3	421.1	448.5	481.7	546.5	650.0	794.8
55°	327.3	329.1	335.1	340.1	348.5	363.4	380.6	408.4	452.7	524.9	644.2
57.5°	283.4	282.7	288.5	289.8	299.1	311.4	324.7	346.3	378.4	432.0	512.3
60°	254.1	252.4	257.5	261.3	266.4	276.3	287.4	308.5	334.0	373.4	442.2
62.5°	227.5	226.7	230.4	234.2	238.4	247.4	256.8	273.0	293.2	326.4	381.0
65°	188.7	190.3	192.0	193.6	195.8	201.4	210.3	221.4	235.2	258.5	297.9
67.5°	148.2	149.9	150.5	153.9	158.7	162.2	167.5	177.4	187.1	206.8	229.2
70°	119.8	119.3	119.8	121.5	127.6	133.7	141.0	148.1	154.3	168.1	186.9
72.5°	103.0	102.0	103.5	103.8	106.7	108.4	113.0	119.8	127.6	137.1	150.6
75°	79.9	79.9	79.9	79.9	82.1	83.2	84.9	86.6	89.4	93.8	103.8
77.5°	59.0	59.1	59.9	60.5	60.9	61.6	62.6	64.2	65.2	67.6	71.9
80°	46.6	47.1	46.6	47.1	47.1	48.3	48.8	50.5	51.0	53.8	55.5
82.5°	35.1	34.7	35.1	35.6	35.6	36.8	36.9	38.1	38.2	39.6	41.3
85°	18.8	17.8	18.8	18.3	19.4	18.3	18.8	20.0	20.0	20.5	22.7
87.5°	8.2	9.1	8.2	8.6	8.5	8.8	8.7	8.6	9.4	8.8	8.9
90°	19.2	18.8	18.6	18.3	18.0	17.5	17.0	16.5	15.9	15.3	13.5
92.5°	21.2	21.0	20.8	20.6	20.5	20.0	19.0	18.1	17.2	16.3	14.9
95°	24.2	24.2	24.2	24.2	24.2	23.7	22.7	21.8	20.8	19.7	18.2
97.5°	26.3	26.1	26.0	25.8	25.7	25.0	23.9	22.8	21.7	20.5	30.7
100°	26.7	26.7	26.5	26.3	26.2	25.6	24.5	23.3	22.2	21.0	43.1
102.5°	27.3	27.0	26.7	26.5	26.3	27.9	31.4	34.9	38.4	41.9	66.0
105°	28.0	27.8	27.5	27.2	26.9	39.3	64.4	89.4	114.5	139.6	152.3
107.5°	88.1	107.0	125.9	144.8	163.6	182.3	200.7	219.1	237.5	255.8	253.8
110°	175.3	195.5	215.8	236.0	256.3	268.8	273.5	278.1	282.8	287.5	285.9



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	300.8	305.0	309.2	313.6	317.8	319.9	319.8	319.8	319.7	319.6	318.0
115°	374.8	374.2	373.7	373.1	372.5	371.5	370.1	368.7	367.3	365.9	364.6
117.5°	416.4	416.2	416.1	416.0	415.9	415.2	414.2	413.0	411.9	410.7	410.1
120°	444.9	444.9	444.9	444.9	444.9	444.3	443.2	442.1	440.9	439.8	439.4
122.5°	473.0	472.9	472.7	472.6	472.5	472.1	471.2	470.4	469.7	468.9	468.3
125°	512.5	512.2	511.9	511.6	511.4	511.0	510.8	510.5	510.2	509.9	509.3
127.5°	550.5	550.7	551.1	551.3	551.5	551.5	551.1	550.6	550.2	549.7	549.0
130°	574.9	575.2	575.5	575.8	576.1	575.9	575.4	574.8	574.2	573.6	573.1
132.5°	597.4	597.8	598.2	598.6	598.9	598.8	598.3	597.7	597.2	596.6	596.1
135°	631.7	632.1	632.5	632.9	633.3	633.3	632.9	632.5	632.1	631.7	631.1
137.5°	663.9	664.2	664.5	664.8	665.0	664.9	664.1	663.5	662.8	662.1	661.8
140°	683.3	683.5	683.9	684.1	684.4	684.3	683.7	683.1	682.6	682.0	681.6
142.5°	701.2	701.6	701.9	702.3	702.7	702.7	702.2	701.8	701.3	700.9	700.4
145°	728.6	728.6	728.6	728.6	728.6	728.4	728.1	727.8	727.6	727.2	727.0
147.5°	748.9	749.6	750.2	750.9	751.5	751.7	751.5	751.1	750.9	750.6	750.3
150°	764.3	764.7	765.1	765.5	766.0	766.0	765.7	765.4	765.2	764.9	764.6
152.5°	776.5	777.1	777.8	778.4	779.1	779.2	778.6	778.1	777.6	777.1	777.0
155°	793.5	794.4	795.2	796.1	797.0	797.0	796.3	795.7	794.9	794.2	794.0
157.5°	808.0	809.1	810.2	811.3	812.4	812.5	811.6	810.8	810.0	809.1	809.3
160°	817.2	818.2	819.1	820.1	821.1	821.2	820.4	819.5	818.6	817.7	817.9
162.5°	825.8	826.7	827.5	828.4	829.3	829.2	828.3	827.4	826.4	825.4	825.6
165°	836.3	837.2	838.2	839.3	840.2	840.2	839.0	837.9	836.7	835.6	835.8
167.5°	843.8	844.9	846.0	847.2	848.3	848.3	847.2	846.0	844.9	843.8	843.8
170°	848.4	849.5	850.6	851.7	852.9	852.9	851.7	850.6	849.5	848.4	848.4
172.5°	850.9	852.2	853.5	854.7	855.9	856.0	854.8	853.7	852.6	851.4	851.3
175°	854.8	855.9	857.0	858.2	859.2	859.3	858.3	857.4	856.4	855.4	855.2
177.5°	855.9	857.0	858.2	859.3	860.5	860.5	859.7	858.8	857.9	856.9	856.8
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1338.2	1336.9	1330.7	1323.6	1314.3	1308.1	1303.2	1300.6	1292.6	1282.8	1276.1
5°	1420.9	1404.3	1386.6	1364.9	1344.9	1324.4	1311.7	1296.7	1278.3	1257.8	1243.4
7.5°	1509.5	1476.8	1441.7	1405.4	1369.5	1337.4	1309.0	1284.7	1255.5	1226.0	1205.4
10°	1577.4	1529.7	1480.3	1429.8	1383.7	1340.5	1307.2	1274.5	1239.5	1205.7	1180.1
12.5°	1639.1	1576.3	1519.4	1457.3	1398.4	1346.7	1298.8	1260.3	1218.2	1182.1	1153.1
15°	1717.2	1652.9	1584.0	1489.7	1411.5	1346.1	1287.8	1237.3	1186.3	1141.8	1113.5
17.5°	1790.2	1693.4	1600.9	1522.2	1420.6	1338.8	1267.7	1207.3	1151.3	1104.2	1069.4
20°	1820.4	1726.6	1626.2	1525.8	1426.0	1334.4	1251.7	1185.1	1126.9	1073.6	1041.5
22.5°	1838.6	1732.4	1626.7	1518.7	1412.6	1317.5	1235.7	1162.5	1099.3	1048.7	1009.0
25°	1859.8	1733.3	1616.8	1510.3	1402.1	1298.9	1201.8	1124.1	1055.9	1002.0	959.9
27.5°	1873.8	1725.0	1587.3	1468.8	1359.1	1256.4	1167.3	1085.0	1015.8	958.9	913.6
30°	1876.5	1718.3	1564.6	1436.5	1324.9	1230.6	1136.3	1057.5	984.3	923.8	881.7
32.5°	1880.0	1701.9	1534.0	1397.8	1283.7	1190.3	1104.8	1029.6	954.6	895.0	851.9
35°	1865.4	1692.8	1487.5	1331.1	1216.8	1126.3	1049.2	979.8	906.0	848.3	804.5
37.5°	1802.3	1656.8	1439.3	1255.8	1136.3	1052.6	989.7	929.3	861.5	799.3	758.0
40°	1738.9	1621.2	1402.1	1210.1	1085.2	999.2	942.6	893.3	827.9	769.6	725.2
42.5°	1644.3	1572.9	1366.6	1162.1	1027.5	944.7	896.9	850.7	793.2	734.0	692.4
45°	1470.9	1480.3	1293.9	1085.8	947.6	864.5	819.5	787.3	736.3	687.5	644.7
47.5°	1253.4	1341.6	1208.5	1004.4	863.4	785.3	746.0	718.0	683.5	635.6	596.6
50°	1111.3	1237.3	1140.2	949.9	810.7	733.0	694.1	671.3	641.4	603.6	566.5
52.5°	980.4	1115.7	1057.6	889.1	753.3	682.3	644.4	625.7	601.9	566.4	532.7
55°	799.5	936.5	923.2	797.3	667.5	603.6	574.8	553.8	537.6	511.0	484.4
57.5°	646.7	776.7	783.5	695.2	591.8	528.7	503.9	488.0	477.5	457.4	432.8
60°	550.4	669.7	693.0	626.4	537.6	482.2	457.7	445.0	436.7	420.5	401.7
62.5°	470.5	572.0	598.4	550.5	485.7	433.7	414.7	402.4	396.7	382.9	366.2
65°	360.1	444.4	469.9	443.3	409.4	367.9	352.3	341.8	336.8	329.1	316.8
67.5°	270.8	332.2	360.2	341.4	329.2	303.0	293.1	287.4	283.0	277.6	267.4
70°	217.5	263.0	291.9	286.8	276.9	263.0	255.8	251.9	247.4	243.0	234.2
72.5°	174.9	206.2	233.3	235.8	227.6	224.9	218.5	216.9	214.2	208.9	204.0
75°	115.9	137.6	156.5	163.7	167.0	169.7	167.0	166.5	165.9	161.4	158.7
77.5°	76.0	87.6	99.5	111.9	117.1	120.8	121.7	123.8	122.3	119.9	118.6
80°	58.3	61.1	69.4	79.9	88.2	91.6	93.8	94.9	94.3	93.8	91.6
82.5°	42.3	44.6	48.5	55.9	62.9	68.5	69.8	69.5	70.8	71.1	69.4
85°	22.7	23.3	24.4	25.5	29.4	35.5	37.2	38.3	39.4	39.4	36.0
87.5°	9.5	8.6	9.1	8.8	9.9	10.0	12.4	14.3	15.1	13.5	13.9
90°	11.6	9.8	7.9	6.3	4.9	3.5	2.0	0.7	2.0	3.5	4.9
92.5°	13.5	12.1	10.8	10.3	10.7	11.1	11.5	11.8	11.5	11.1	10.7
95°	16.6	15.1	13.5	15.7	21.4	27.2	33.1	38.9	33.1	27.2	21.4
97.5°	40.9	51.1	61.3	67.8	70.4	73.0	75.6	78.1	75.6	73.0	70.4
100°	65.2	87.3	109.4	119.0	116.2	113.4	110.6	107.7	110.6	113.4	116.2
102.5°	90.2	114.4	138.5	149.5	147.5	145.4	143.4	141.4	143.4	145.4	147.5
105°	165.1	177.8	190.6	196.2	194.6	193.1	191.5	190.0	191.5	193.1	194.6
107.5°	251.8	249.8	247.8	246.1	244.9	243.7	242.5	241.2	242.5	243.7	244.9
110°	284.4	282.8	281.2	279.9	278.8	277.6	276.5	275.3	276.5	277.6	278.8





TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	316.5	315.0	313.3	312.1	311.0	310.1	309.0	308.0	309.0	310.1	311.0
115°	363.3	362.1	360.8	359.7	358.9	358.0	357.2	356.3	357.2	358.0	358.9
117.5°	409.4	408.8	408.1	407.2	406.3	405.2	404.1	403.1	404.1	405.2	406.3
120°	439.0	438.5	438.1	437.2	435.9	434.7	433.4	432.2	433.4	434.7	435.9
122.5°	467.8	467.2	466.7	465.9	464.9	463.8	462.8	461.7	462.8	463.8	464.9
125°	508.7	508.3	507.7	506.8	505.6	504.5	503.4	502.3	503.4	504.5	505.6
127.5°	548.4	547.6	547.0	546.1	544.9	543.8	542.7	541.5	542.7	543.8	544.9
130°	572.5	571.9	571.4	570.5	569.4	568.3	567.1	566.0	567.1	568.3	569.4
132.5°	595.7	595.3	594.8	594.0	592.9	591.7	590.6	589.5	590.6	591.7	592.9
135°	630.6	630.0	629.4	628.7	627.9	627.0	626.1	625.3	626.1	627.0	627.9
137.5°	661.5	661.2	660.9	660.1	659.1	658.0	657.0	655.9	657.0	658.0	659.1
140°	681.2	680.8	680.3	679.7	678.8	678.0	677.1	676.3	677.1	678.0	678.8
142.5°	700.0	699.6	699.2	698.5	697.7	696.8	696.0	695.1	696.0	696.8	697.7
145°	726.7	726.4	726.1	725.5	724.5	723.5	722.5	721.5	722.5	723.5	724.5
147.5°	750.0	749.7	749.5	749.0	748.4	747.7	747.1	746.4	747.1	747.7	748.4
150°	764.3	764.0	763.8	763.4	763.0	762.5	762.1	761.7	762.1	762.5	763.0
152.5°	776.7	776.6	776.4	776.2	776.1	775.8	775.7	775.4	775.7	775.8	776.1
155°	793.9	793.8	793.6	793.7	794.0	794.3	794.6	794.8	794.6	794.3	794.0
157.5°	809.4	809.5	809.7	809.8	809.8	809.8	809.8	809.8	809.8	809.8	809.8
160°	818.1	818.2	818.3	818.5	818.6	818.8	818.9	819.0	818.9	818.8	818.6
162.5°	825.7	825.8	826.0	826.2	826.6	827.0	827.4	827.7	827.4	827.0	826.6
165°	835.9	836.1	836.2	836.5	836.9	837.3	837.7	838.2	837.7	837.3	836.9
167.5°	843.8	843.8	843.8	844.1	844.7	845.2	845.8	846.4	845.8	845.2	844.7
170°	848.4	848.4	848.4	848.6	849.2	849.8	850.4	850.9	850.4	849.8	849.2
172.5°	851.2	851.1	851.0	851.3	851.9	852.6	853.3	853.9	853.3	852.6	851.9
175°	855.1	854.9	854.8	855.1	855.8	856.6	857.2	857.9	857.2	856.6	855.8
177.5°	856.7	856.6	856.5	856.7	857.3	857.9	858.4	858.9	858.4	857.9	857.3
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1273.9	1268.1	1264.1	1255.2	1249.5	1243.2	1237.1	1241.0	1240.6	1240.2	1240.2
5°	1231.2	1218.4	1206.8	1191.8	1182.3	1170.7	1161.8	1160.7	1162.9	1155.2	1150.7
7.5°	1188.8	1171.3	1154.9	1138.3	1120.8	1106.8	1098.0	1093.9	1088.3	1083.5	1078.5
10°	1159.0	1138.6	1122.4	1101.9	1083.0	1066.4	1055.9	1048.6	1044.7	1040.9	1033.6
12.5°	1128.5	1108.3	1087.9	1064.6	1046.7	1027.4	1019.5	1011.4	1004.0	999.6	989.7
15°	1083.6	1057.5	1035.9	1011.5	991.5	972.7	961.6	945.4	943.2	937.7	927.7
17.5°	1038.7	1010.3	980.5	962.5	939.9	920.2	903.4	898.0	882.1	876.1	867.4
20°	1003.1	977.1	954.3	930.5	897.7	879.4	866.1	858.9	846.1	838.4	832.8
22.5°	972.5	946.0	919.7	891.9	864.9	844.3	834.6	823.4	816.4	805.5	799.5
25°	928.8	899.9	868.3	838.4	819.0	803.4	787.9	777.9	767.9	762.9	751.8
27.5°	878.0	847.8	818.2	795.5	771.7	756.4	742.2	733.4	721.4	713.0	706.9
30°	850.0	814.5	789.0	768.4	737.9	723.5	713.0	701.9	693.0	684.1	678.0
32.5°	817.6	785.2	761.0	735.6	712.2	696.4	682.8	673.0	665.4	657.0	650.9
35°	766.8	739.6	714.6	689.1	671.9	655.8	639.8	631.4	624.2	616.4	610.9
37.5°	720.8	695.5	671.7	647.5	626.1	613.1	600.1	593.8	584.0	578.8	573.2
40°	692.4	667.5	642.0	618.6	596.5	586.4	574.8	565.4	556.5	552.6	546.5
42.5°	661.4	636.4	614.9	589.8	571.6	558.1	547.3	537.0	530.4	524.6	521.2
45°	615.3	593.1	572.0	547.1	529.9	518.2	506.0	496.6	490.5	486.6	480.5
47.5°	570.6	548.4	527.0	505.2	488.6	475.2	463.1	456.5	448.4	443.7	439.5
50°	538.2	518.2	495.5	475.5	458.9	445.6	435.5	427.2	420.0	413.9	411.2
52.5°	508.4	487.1	467.5	448.9	431.3	416.2	407.2	398.4	393.0	386.0	382.7
55°	459.4	438.9	422.2	403.9	386.7	374.0	362.9	355.1	349.5	341.8	337.4
57.5°	413.4	394.9	375.0	359.2	341.4	330.7	321.5	311.0	304.2	298.1	293.8
60°	382.3	361.2	344.0	329.1	313.5	299.6	291.3	283.0	275.7	269.6	265.8
62.5°	349.8	331.5	315.1	298.8	284.6	272.6	262.9	255.9	249.6	245.6	241.8
65°	300.2	285.8	269.1	255.8	242.5	233.6	225.8	219.7	215.2	212.5	209.2
67.5°	254.5	240.4	225.9	212.9	204.0	197.2	192.1	186.9	184.7	181.1	178.9
70°	224.7	210.3	197.5	187.5	178.6	173.7	170.3	166.5	164.2	159.8	157.6
72.5°	192.3	181.9	172.7	164.4	157.4	152.8	148.5	143.8	140.2	135.3	133.1
75°	151.5	142.0	134.9	129.3	124.8	118.7	112.6	107.6	106.0	104.3	103.8
77.5°	112.2	106.2	101.0	96.3	90.7	86.3	85.0	83.9	83.6	82.7	82.7
80°	88.2	82.7	78.8	73.2	69.9	69.9	69.9	68.8	69.4	69.4	69.4
82.5°	65.6	60.5	58.4	56.3	55.7	56.2	56.2	56.3	56.0	56.9	56.5
85°	33.8	34.4	35.5	35.0	35.5	35.5	36.6	36.0	36.6	35.5	36.6
87.5°	13.7	15.3	16.1	17.0	17.8	17.7	18.3	18.3	18.9	19.1	19.2
90°	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.5	17.0	17.5	18.0
92.5°	10.3	10.8	12.1	13.5	14.9	16.3	17.2	18.1	19.0	20.0	20.5
95°	15.7	13.5	15.1	16.6	18.2	19.7	20.8	21.8	22.7	23.7	24.2
97.5°	67.8	61.3	51.1	40.9	30.7	20.5	21.7	22.8	23.9	25.0	25.7
100°	119.0	109.4	87.3	65.2	43.1	21.0	22.2	23.3	24.5	25.6	26.2
102.5°	149.5	138.5	114.4	90.2	66.0	41.9	38.4	34.9	31.4	27.9	26.3
105°	196.2	190.6	177.8	165.1	152.3	139.6	114.5	89.4	64.4	39.3	26.9
107.5°	246.1	247.8	249.8	251.8	253.8	255.8	237.5	219.1	200.7	182.3	163.6
110°	279.9	281.2	282.8	284.4	285.9	287.5	282.8	278.1	273.5	268.8	256.3



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	312.1	313.3	315.0	316.5	318.0	319.6	319.7	319.8	319.8	319.9	317.8
115°	359.7	360.8	362.1	363.3	364.6	365.9	367.3	368.7	370.1	371.5	372.5
117.5°	407.2	408.1	408.8	409.4	410.1	410.7	411.9	413.0	414.2	415.2	415.9
120°	437.2	438.1	438.5	439.0	439.4	439.8	440.9	442.1	443.2	444.3	444.9
122.5°	465.9	466.7	467.2	467.8	468.3	468.9	469.7	470.4	471.2	472.1	472.5
125°	506.8	507.7	508.3	508.7	509.3	509.9	510.2	510.5	510.8	511.0	511.4
127.5°	546.1	547.0	547.6	548.4	549.0	549.7	550.2	550.6	551.1	551.5	551.5
130°	570.5	571.4	571.9	572.5	573.1	573.6	574.2	574.8	575.4	575.9	576.1
132.5°	594.0	594.8	595.3	595.7	596.1	596.6	597.2	597.7	598.3	598.8	598.9
135°	628.7	629.4	630.0	630.6	631.1	631.7	632.1	632.5	632.9	633.3	633.3
137.5°	660.1	660.9	661.2	661.5	661.8	662.1	662.8	663.5	664.1	664.9	665.0
140°	679.7	680.3	680.8	681.2	681.6	682.0	682.6	683.1	683.7	684.3	684.4
142.5°	698.5	699.2	699.6	700.0	700.4	700.9	701.3	701.8	702.2	702.7	702.7
145°	725.5	726.1	726.4	726.7	727.0	727.2	727.6	727.8	728.1	728.4	728.6
147.5°	749.0	749.5	749.7	750.0	750.3	750.6	750.9	751.1	751.5	751.7	751.5
150°	763.4	763.8	764.0	764.3	764.6	764.9	765.2	765.4	765.7	766.0	766.0
152.5°	776.2	776.4	776.6	776.7	777.0	777.1	777.6	778.1	778.6	779.2	779.1
155°	793.7	793.6	793.8	793.9	794.0	794.2	794.9	795.7	796.3	797.0	797.0
157.5°	809.8	809.7	809.5	809.4	809.3	809.1	810.0	810.8	811.6	812.5	812.4
160°	818.5	818.3	818.2	818.1	817.9	817.7	818.6	819.5	820.4	821.2	821.1
162.5°	826.2	826.0	825.8	825.7	825.6	825.4	826.4	827.4	828.3	829.2	829.3
165°	836.5	836.2	836.1	835.9	835.8	835.6	836.7	837.9	839.0	840.2	840.2
167.5°	844.1	843.8	843.8	843.8	843.8	843.8	844.9	846.0	847.2	848.3	848.3
170°	848.6	848.4	848.4	848.4	848.4	848.4	849.5	850.6	851.7	852.9	852.9
172.5°	851.3	851.0	851.1	851.2	851.3	851.4	852.6	853.7	854.8	856.0	855.9
175°	855.1	854.8	854.9	855.1	855.2	855.4	856.4	857.4	858.3	859.3	859.2
177.5°	856.7	856.5	856.6	856.7	856.8	856.9	857.9	858.8	859.7	860.5	860.5
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1234.9	1234.4	1234.9	1233.1	1234.9	1234.4	1234.9	1240.2	1240.2	1240.6	1241.0
5°	1149.1	1148.5	1146.9	1141.8	1146.9	1148.5	1149.1	1150.7	1155.2	1162.9	1160.7
7.5°	1074.2	1073.4	1068.5	1068.6	1068.5	1073.4	1074.2	1078.5	1083.5	1088.3	1093.9
10°	1029.8	1030.3	1023.7	1019.8	1023.7	1030.3	1029.8	1033.6	1040.9	1044.7	1048.6
12.5°	986.8	984.1	978.8	974.5	978.8	984.1	986.8	989.7	999.6	1004.0	1011.4
15°	929.9	924.4	911.0	912.2	911.0	924.4	929.9	927.7	937.7	943.2	945.4
17.5°	863.0	858.9	858.7	850.9	858.7	858.9	863.0	867.4	876.1	882.1	898.0
20°	823.9	821.2	822.2	814.5	822.2	821.2	823.9	832.8	838.4	846.1	858.9
22.5°	793.3	790.5	785.9	783.4	785.9	790.5	793.3	799.5	805.5	816.4	823.4
25°	748.4	744.0	739.6	742.4	739.6	744.0	748.4	751.8	762.9	767.9	777.9
27.5°	703.7	700.3	695.9	695.3	695.9	700.3	703.7	706.9	713.0	721.4	733.4
30°	675.2	671.9	669.7	666.9	669.7	671.9	675.2	678.0	684.1	693.0	701.9
32.5°	646.4	645.7	641.7	641.2	641.7	645.7	646.4	650.9	657.0	665.4	673.0
35°	608.6	605.4	604.2	604.8	604.2	605.4	608.6	610.9	616.4	624.2	631.4
37.5°	572.8	568.3	566.4	564.4	566.4	568.3	572.8	573.2	578.8	584.0	593.8
40°	547.1	542.7	541.5	540.4	541.5	542.7	547.1	546.5	552.6	556.5	565.4
42.5°	518.2	516.4	515.8	513.8	515.8	516.4	518.2	521.2	524.6	530.4	537.0
45°	478.8	478.3	474.9	476.1	474.9	478.3	478.8	480.5	486.6	490.5	496.6
47.5°	437.3	434.9	432.5	434.1	432.5	434.9	437.3	439.5	443.7	448.4	456.5
50°	409.0	407.8	402.8	403.9	402.8	407.8	409.0	411.2	413.9	420.0	427.2
52.5°	380.5	376.3	374.4	373.7	374.4	376.3	380.5	382.7	386.0	393.0	398.4
55°	333.5	328.5	326.3	325.1	326.3	328.5	333.5	337.4	341.8	349.5	355.1
57.5°	287.3	285.9	284.2	285.4	284.2	285.9	287.3	293.8	298.1	304.2	311.0
60°	260.2	260.2	260.2	259.7	260.2	260.2	260.2	265.8	269.6	275.7	283.0
62.5°	239.4	238.0	237.6	238.4	237.6	238.0	239.4	241.8	245.6	249.6	255.9
65°	207.5	206.9	204.7	204.2	204.7	206.9	207.5	209.2	212.5	215.2	219.7
67.5°	177.4	175.5	174.8	174.0	174.8	175.5	177.4	178.9	181.1	184.7	186.9
70°	154.8	153.7	150.3	150.9	150.3	153.7	154.8	157.6	159.8	164.2	166.5
72.5°	130.4	129.3	128.6	127.8	128.6	129.3	130.4	133.1	135.3	140.2	143.8
75°	103.2	102.6	102.1	104.3	102.1	102.6	103.2	103.8	104.3	106.0	107.6
77.5°	82.7	82.7	83.0	82.1	83.0	82.7	82.7	82.7	82.7	83.6	83.9
80°	69.4	69.4	68.8	68.8	68.8	69.4	69.4	69.4	69.4	69.4	68.8
82.5°	55.6	56.0	56.3	55.5	56.3	56.0	55.6	56.5	56.9	56.0	56.3
85°	36.6	36.0	37.2	36.6	37.2	36.0	36.6	36.6	35.5	36.6	36.0
87.5°	20.1	19.2	19.3	19.8	19.3	19.2	20.1	19.2	19.1	18.9	18.3
90°	18.3	18.6	18.8	19.2	18.8	18.6	18.3	18.0	17.5	17.0	16.5
92.5°	20.6	20.8	21.0	21.2	21.0	20.8	20.6	20.5	20.0	19.0	18.1
95°	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	23.7	22.7	21.8
97.5°	25.8	26.0	26.1	26.3	26.1	26.0	25.8	25.7	25.0	23.9	22.8
100°	26.3	26.5	26.7	26.7	26.7	26.5	26.3	26.2	25.6	24.5	23.3
102.5°	26.5	26.7	27.0	27.3	27.0	26.7	26.5	26.3	27.9	31.4	34.9
105°	27.2	27.5	27.8	28.0	27.8	27.5	27.2	26.9	39.3	64.4	89.4
107.5°	144.8	125.9	107.0	88.1	107.0	125.9	144.8	163.6	182.3	200.7	219.1
110°	236.0	215.8	195.5	175.3	195.5	215.8	236.0	256.3	268.8	273.5	278.1



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	313.6	309.2	305.0	300.8	305.0	309.2	313.6	317.8	319.9	319.8	319.8
115°	373.1	373.7	374.2	374.8	374.2	373.7	373.1	372.5	371.5	370.1	368.7
117.5°	416.0	416.1	416.2	416.4	416.2	416.1	416.0	415.9	415.2	414.2	413.0
120°	444.9	444.9	444.9	444.9	444.9	444.9	444.9	444.9	444.3	443.2	442.1
122.5°	472.6	472.7	472.9	473.0	472.9	472.7	472.6	472.5	472.1	471.2	470.4
125°	511.6	511.9	512.2	512.5	512.2	511.9	511.6	511.4	511.0	510.8	510.5
127.5°	551.3	551.1	550.7	550.5	550.7	551.1	551.3	551.5	551.5	551.1	550.6
130°	575.8	575.5	575.2	574.9	575.2	575.5	575.8	576.1	575.9	575.4	574.8
132.5°	598.6	598.2	597.8	597.4	597.8	598.2	598.6	598.9	598.8	598.3	597.7
135°	632.9	632.5	632.1	631.7	632.1	632.5	632.9	633.3	633.3	632.9	632.5
137.5°	664.8	664.5	664.2	663.9	664.2	664.5	664.8	665.0	664.9	664.1	663.5
140°	684.1	683.9	683.5	683.3	683.5	683.9	684.1	684.4	684.3	683.7	683.1
142.5°	702.3	701.9	701.6	701.2	701.6	701.9	702.3	702.7	702.7	702.2	701.8
145°	728.6	728.6	728.6	728.6	728.6	728.6	728.6	728.6	728.4	728.1	727.8
147.5°	750.9	750.2	749.6	748.9	749.6	750.2	750.9	751.5	751.7	751.5	751.1
150°	765.5	765.1	764.7	764.3	764.7	765.1	765.5	766.0	766.0	765.7	765.4
152.5°	778.4	777.8	777.1	776.5	777.1	777.8	778.4	779.1	779.2	778.6	778.1
155°	796.1	795.2	794.4	793.5	794.4	795.2	796.1	797.0	797.0	796.3	795.7
157.5°	811.3	810.2	809.1	808.0	809.1	810.2	811.3	812.4	812.5	811.6	810.8
160°	820.1	819.1	818.2	817.2	818.2	819.1	820.1	821.1	821.2	820.4	819.5
162.5°	828.4	827.5	826.7	825.8	826.7	827.5	828.4	829.3	829.2	828.3	827.4
165°	839.3	838.2	837.2	836.3	837.2	838.2	839.3	840.2	840.2	839.0	837.9
167.5°	847.2	846.0	844.9	843.8	844.9	846.0	847.2	848.3	848.3	847.2	846.0
170°	851.7	850.6	849.5	848.4	849.5	850.6	851.7	852.9	852.9	851.7	850.6
172.5°	854.7	853.5	852.2	850.9	852.2	853.5	854.7	855.9	856.0	854.8	853.7
175°	858.2	857.0	855.9	854.8	855.9	857.0	858.2	859.2	859.3	858.3	857.4
177.5°	859.3	858.2	857.0	855.9	857.0	858.2	859.3	860.5	860.5	859.7	858.8
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1237.1	1243.2	1249.5	1255.2	1264.1	1268.1	1273.9	1276.1	1282.8	1292.6	1300.6
5°	1161.8	1170.7	1182.3	1191.8	1206.8	1218.4	1231.2	1243.4	1257.8	1278.3	1296.7
7.5°	1098.0	1106.8	1120.8	1138.3	1154.9	1171.3	1188.8	1205.4	1226.0	1255.5	1284.7
10°	1055.9	1066.4	1083.0	1101.9	1122.4	1138.6	1159.0	1180.1	1205.7	1239.5	1274.5
12.5°	1019.5	1027.4	1046.7	1064.6	1087.9	1108.3	1128.5	1153.1	1182.1	1218.2	1260.3
15°	961.6	972.7	991.5	1011.5	1035.9	1057.5	1083.6	1113.5	1141.8	1186.3	1237.3
17.5°	903.4	920.2	939.9	962.5	980.5	1010.3	1038.7	1069.4	1104.2	1151.3	1207.3
20°	866.1	879.4	897.7	930.5	954.3	977.1	1003.1	1041.5	1073.6	1126.9	1185.1
22.5°	834.6	844.3	864.9	891.9	919.7	946.0	972.5	1009.0	1048.7	1099.3	1162.5
25°	787.9	803.4	819.0	838.4	868.3	899.9	928.8	959.9	1002.0	1055.9	1124.1
27.5°	742.2	756.4	771.7	795.5	818.2	847.8	878.0	913.6	958.9	1015.8	1085.0
30°	713.0	723.5	737.9	768.4	789.0	814.5	850.0	881.7	923.8	984.3	1057.5
32.5°	682.8	696.4	712.2	735.6	761.0	785.2	817.6	851.9	895.0	954.6	1029.6
35°	639.8	655.8	671.9	689.1	714.6	739.6	766.8	804.5	848.3	906.0	979.8
37.5°	600.1	613.1	626.1	647.5	671.7	695.5	720.8	758.0	799.3	861.5	929.3
40°	574.8	586.4	596.5	618.6	642.0	667.5	692.4	725.2	769.6	827.9	893.3
42.5°	547.3	558.1	571.6	589.8	614.9	636.4	661.4	692.4	734.0	793.2	850.7
45°	506.0	518.2	529.9	547.1	572.0	593.1	615.3	644.7	687.5	736.3	787.3
47.5°	463.1	475.2	488.6	505.2	527.0	548.4	570.6	596.6	635.6	683.5	718.0
50°	435.5	445.6	458.9	475.5	495.5	518.2	538.2	566.5	603.6	641.4	671.3
52.5°	407.2	416.2	431.3	448.9	467.5	487.1	508.4	532.7	566.4	601.9	625.7
55°	362.9	374.0	386.7	403.9	422.2	438.9	459.4	484.4	511.0	537.6	553.8
57.5°	321.5	330.7	341.4	359.2	375.0	394.9	413.4	432.8	457.4	477.5	488.0
60°	291.3	299.6	313.5	329.1	344.0	361.2	382.3	401.7	420.5	436.7	445.0
62.5°	262.9	272.6	284.6	298.8	315.1	331.5	349.8	366.2	382.9	396.7	402.4
65°	225.8	233.6	242.5	255.8	269.1	285.8	300.2	316.8	329.1	336.8	341.8
67.5°	192.1	197.2	204.0	212.9	225.9	240.4	254.5	267.4	277.6	283.0	287.4
70°	170.3	173.7	178.6	187.5	197.5	210.3	224.7	234.2	243.0	247.4	251.9
72.5°	148.5	152.8	157.4	164.4	172.7	181.9	192.3	204.0	208.9	214.2	216.9
75°	112.6	118.7	124.8	129.3	134.9	142.0	151.5	158.7	161.4	165.9	166.5
77.5°	85.0	86.3	90.7	96.3	101.0	106.2	112.2	118.6	119.9	122.3	123.8
80°	69.9	69.9	69.9	73.2	78.8	82.7	88.2	91.6	93.8	94.3	94.9
82.5°	56.2	56.2	55.7	56.3	58.4	60.5	65.6	69.4	71.1	70.8	69.5
85°	36.6	35.5	35.5	35.0	35.5	34.4	33.8	36.0	39.4	39.4	38.3
87.5°	18.3	17.7	17.8	17.0	16.1	15.3	13.7	13.9	13.5	15.1	14.3
90°	15.9	15.3	13.5	11.6	9.8	7.9	6.3	4.9	3.5	2.0	0.7
92.5°	17.2	16.3	14.9	13.5	12.1	10.8	10.3	10.7	11.1	11.5	11.8
95°	20.8	19.7	18.2	16.6	15.1	13.5	15.7	21.4	27.2	33.1	38.9
97.5°	21.7	20.5	30.7	40.9	51.1	61.3	67.8	70.4	73.0	75.6	78.1
100°	22.2	21.0	43.1	65.2	87.3	109.4	119.0	116.2	113.4	110.6	107.7
102.5°	38.4	41.9	66.0	90.2	114.4	138.5	149.5	147.5	145.4	143.4	141.4
105°	114.5	139.6	152.3	165.1	177.8	190.6	196.2	194.6	193.1	191.5	190.0
107.5°	237.5	255.8	253.8	251.8	249.8	247.8	246.1	244.9	243.7	242.5	241.2
110°	282.8	287.5	285.9	284.4	282.8	281.2	279.9	278.8	277.6	276.5	275.3



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	319.7	319.6	318.0	316.5	315.0	313.3	312.1	311.0	310.1	309.0	308.0
115°	367.3	365.9	364.6	363.3	362.1	360.8	359.7	358.9	358.0	357.2	356.3
117.5°	411.9	410.7	410.1	409.4	408.8	408.1	407.2	406.3	405.2	404.1	403.1
120°	440.9	439.8	439.4	439.0	438.5	438.1	437.2	435.9	434.7	433.4	432.2
122.5°	469.7	468.9	468.3	467.8	467.2	466.7	465.9	464.9	463.8	462.8	461.7
125°	510.2	509.9	509.3	508.7	508.3	507.7	506.8	505.6	504.5	503.4	502.3
127.5°	550.2	549.7	549.0	548.4	547.6	547.0	546.1	544.9	543.8	542.7	541.5
130°	574.2	573.6	573.1	572.5	571.9	571.4	570.5	569.4	568.3	567.1	566.0
132.5°	597.2	596.6	596.1	595.7	595.3	594.8	594.0	592.9	591.7	590.6	589.5
135°	632.1	631.7	631.1	630.6	630.0	629.4	628.7	627.9	627.0	626.1	625.3
137.5°	662.8	662.1	661.8	661.5	661.2	660.9	660.1	659.1	658.0	657.0	655.9
140°	682.6	682.0	681.6	681.2	680.8	680.3	679.7	678.8	678.0	677.1	676.3
142.5°	701.3	700.9	700.4	700.0	699.6	699.2	698.5	697.7	696.8	696.0	695.1
145°	727.6	727.2	727.0	726.7	726.4	726.1	725.5	724.5	723.5	722.5	721.5
147.5°	750.9	750.6	750.3	750.0	749.7	749.5	749.0	748.4	747.7	747.1	746.4
150°	765.2	764.9	764.6	764.3	764.0	763.8	763.4	763.0	762.5	762.1	761.7
152.5°	777.6	777.1	777.0	776.7	776.6	776.4	776.2	776.1	775.8	775.7	775.4
155°	794.9	794.2	794.0	793.9	793.8	793.6	793.7	794.0	794.3	794.6	794.8
157.5°	810.0	809.1	809.3	809.4	809.5	809.7	809.8	809.8	809.8	809.8	809.8
160°	818.6	817.7	817.9	818.1	818.2	818.3	818.5	818.6	818.8	818.9	819.0
162.5°	826.4	825.4	825.6	825.7	825.8	826.0	826.2	826.6	827.0	827.4	827.7
165°	836.7	835.6	835.8	835.9	836.1	836.2	836.5	836.9	837.3	837.7	838.2
167.5°	844.9	843.8	843.8	843.8	843.8	843.8	844.1	844.7	845.2	845.8	846.4
170°	849.5	848.4	848.4	848.4	848.4	848.4	848.6	849.2	849.8	850.4	850.9
172.5°	852.6	851.4	851.3	851.2	851.1	851.0	851.3	851.9	852.6	853.3	853.9
175°	856.4	855.4	855.2	855.1	854.9	854.8	855.1	855.8	856.6	857.2	857.9
177.5°	857.9	856.9	856.8	856.7	856.6	856.5	856.7	857.3	857.9	858.4	858.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1303.2	1308.1	1314.3	1323.6	1330.7	1336.9	1338.2	1340.0	1344.5	1352.0	1357.8
5°	1311.7	1324.4	1344.9	1364.9	1386.6	1404.3	1420.9	1432.6	1443.7	1467.0	1485.9
7.5°	1309.0	1337.4	1369.5	1405.4	1441.7	1476.8	1509.5	1538.7	1567.7	1601.7	1640.5
10°	1307.2	1340.5	1383.7	1429.8	1480.3	1529.7	1577.4	1614.6	1657.8	1696.7	1746.0
12.5°	1298.8	1346.7	1398.4	1457.3	1519.4	1576.3	1639.1	1690.4	1740.0	1796.1	1853.5
15°	1287.8	1346.1	1411.5	1489.7	1584.0	1652.9	1717.2	1806.5	1867.6	1928.6	2010.8
17.5°	1267.7	1338.8	1420.6	1522.2	1600.9	1693.4	1790.2	1860.8	1943.0	2029.0	2103.4
20°	1251.7	1334.4	1426.0	1525.8	1626.2	1726.6	1820.4	1904.8	1989.7	2089.0	2150.0
22.5°	1235.7	1317.5	1412.6	1518.7	1626.7	1732.4	1838.6	1937.6	2033.1	2133.3	2211.3
25°	1201.8	1298.9	1402.1	1510.3	1616.8	1733.3	1859.8	1970.3	2088.4	2191.6	2265.4
27.5°	1167.3	1256.4	1359.1	1468.8	1587.3	1725.0	1873.8	1999.3	2117.7	2191.6	2214.8
30°	1136.3	1230.6	1324.9	1436.5	1564.6	1718.3	1876.5	2020.1	2117.3	2149.5	2125.6
32.5°	1104.8	1190.3	1283.7	1397.8	1534.0	1701.9	1880.0	2007.8	2066.2	2041.6	1944.5
35°	1049.2	1126.3	1216.8	1331.1	1487.5	1692.8	1865.4	1951.9	1937.5	1798.8	1615.7
37.5°	989.7	1052.6	1136.3	1255.8	1439.3	1656.8	1802.3	1815.1	1690.3	1477.3	1265.8
40°	942.6	999.2	1085.2	1210.1	1402.1	1621.2	1738.9	1687.3	1493.6	1256.7	1080.3
42.5°	896.9	944.7	1027.5	1162.1	1366.6	1572.9	1644.3	1531.9	1308.6	1084.5	924.1
45°	819.5	864.5	947.6	1085.8	1293.9	1480.3	1470.9	1275.5	1052.0	871.6	738.5
47.5°	746.0	785.3	863.4	1004.4	1208.5	1341.6	1253.4	1045.5	855.9	711.2	616.2
50°	694.1	733.0	810.7	949.9	1140.2	1237.3	1111.3	911.0	737.4	617.5	542.1
52.5°	644.4	682.3	753.3	889.1	1057.6	1115.7	980.4	794.8	650.0	546.5	481.7
55°	574.8	603.6	667.5	797.3	923.2	936.5	799.5	644.2	524.9	452.7	408.4
57.5°	503.9	528.7	591.8	695.2	783.5	776.7	646.7	512.3	432.0	378.4	346.3
60°	457.7	482.2	537.6	626.4	693.0	669.7	550.4	442.2	373.4	334.0	308.5
62.5°	414.7	433.7	485.7	550.5	598.4	572.0	470.5	381.0	326.4	293.2	273.0
65°	352.3	367.9	409.4	443.3	469.9	444.4	360.1	297.9	258.5	235.2	221.4
67.5°	293.1	303.0	329.2	341.4	360.2	332.2	270.8	229.2	206.8	187.1	177.4
70°	255.8	263.0	276.9	286.8	291.9	263.0	217.5	186.9	168.1	154.3	148.1
72.5°	218.5	224.9	227.6	235.8	233.3	206.2	174.9	150.6	137.1	127.6	119.8
75°	167.0	169.7	167.0	163.7	156.5	137.6	115.9	103.8	93.8	89.4	86.6
77.5°	121.7	120.8	117.1	111.9	99.5	87.6	76.0	71.9	67.6	65.2	64.2
80°	93.8	91.6	88.2	79.9	69.4	61.1	58.3	55.5	53.8	51.0	50.5
82.5°	69.8	68.5	62.9	55.9	48.5	44.6	42.3	41.3	39.6	38.2	38.1
85°	37.2	35.5	29.4	25.5	24.4	23.3	22.7	22.7	20.5	20.0	20.0
87.5°	12.4	10.0	9.9	8.8	9.1	8.6	9.5	8.9	8.8	9.4	8.6
90°	2.0	3.5	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.5
92.5°	11.5	11.1	10.7	10.3	10.8	12.1	13.5	14.9	16.3	17.2	18.1
95°	33.1	27.2	21.4	15.7	13.5	15.1	16.6	18.2	19.7	20.8	21.8
97.5°	75.6	73.0	70.4	67.8	61.3	51.1	40.9	30.7	20.5	21.7	22.8
100°	110.6	113.4	116.2	119.0	109.4	87.3	65.2	43.1	21.0	22.2	23.3
102.5°	143.4	145.4	147.5	149.5	138.5	114.4	90.2	66.0	41.9	38.4	34.9
105°	191.5	193.1	194.6	196.2	190.6	177.8	165.1	152.3	139.6	114.5	89.4
107.5°	242.5	243.7	244.9	246.1	247.8	249.8	251.8	253.8	255.8	237.5	219.1
110°	276.5	277.6	278.8	279.9	281.2	282.8	284.4	285.9	287.5	282.8	278.1





TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	309.0	310.1	311.0	312.1	313.3	315.0	316.5	318.0	319.6	319.7	319.8
115°	357.2	358.0	358.9	359.7	360.8	362.1	363.3	364.6	365.9	367.3	368.7
117.5°	404.1	405.2	406.3	407.2	408.1	408.8	409.4	410.1	410.7	411.9	413.0
120°	433.4	434.7	435.9	437.2	438.1	438.5	439.0	439.4	439.8	440.9	442.1
122.5°	462.8	463.8	464.9	465.9	466.7	467.2	467.8	468.3	468.9	469.7	470.4
125°	503.4	504.5	505.6	506.8	507.7	508.3	508.7	509.3	509.9	510.2	510.5
127.5°	542.7	543.8	544.9	546.1	547.0	547.6	548.4	549.0	549.7	550.2	550.6
130°	567.1	568.3	569.4	570.5	571.4	571.9	572.5	573.1	573.6	574.2	574.8
132.5°	590.6	591.7	592.9	594.0	594.8	595.3	595.7	596.1	596.6	597.2	597.7
135°	626.1	627.0	627.9	628.7	629.4	630.0	630.6	631.1	631.7	632.1	632.5
137.5°	657.0	658.0	659.1	660.1	660.9	661.2	661.5	661.8	662.1	662.8	663.5
140°	677.1	678.0	678.8	679.7	680.3	680.8	681.2	681.6	682.0	682.6	683.1
142.5°	696.0	696.8	697.7	698.5	699.2	699.6	700.0	700.4	700.9	701.3	701.8
145°	722.5	723.5	724.5	725.5	726.1	726.4	726.7	727.0	727.2	727.6	727.8
147.5°	747.1	747.7	748.4	749.0	749.5	749.7	750.0	750.3	750.6	750.9	751.1
150°	762.1	762.5	763.0	763.4	763.8	764.0	764.3	764.6	764.9	765.2	765.4
152.5°	775.7	775.8	776.1	776.2	776.4	776.6	776.7	777.0	777.1	777.6	778.1
155°	794.6	794.3	794.0	793.7	793.6	793.8	793.9	794.0	794.2	794.9	795.7
157.5°	809.8	809.8	809.8	809.8	809.7	809.5	809.4	809.3	809.1	810.0	810.8
160°	818.9	818.8	818.6	818.5	818.3	818.2	818.1	817.9	817.7	818.6	819.5
162.5°	827.4	827.0	826.6	826.2	826.0	825.8	825.7	825.6	825.4	826.4	827.4
165°	837.7	837.3	836.9	836.5	836.2	836.1	835.9	835.8	835.6	836.7	837.9
167.5°	845.8	845.2	844.7	844.1	843.8	843.8	843.8	843.8	843.8	844.9	846.0
170°	850.4	849.8	849.2	848.6	848.4	848.4	848.4	848.4	848.4	849.5	850.6
172.5°	853.3	852.6	851.9	851.3	851.0	851.1	851.2	851.3	851.4	852.6	853.7
175°	857.2	856.6	855.8	855.1	854.8	854.9	855.1	855.2	855.4	856.4	857.4
177.5°	858.4	857.9	857.3	856.7	856.5	856.6	856.7	856.8	856.9	857.9	858.8
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1367.1	1367.1	1368.9	1375.6	1376.5	1382.2	1380.5
5°	1502.5	1513.0	1516.9	1533.6	1543.5	1548.0	1539.1
7.5°	1668.1	1697.8	1711.9	1729.3	1744.7	1749.4	1737.3
10°	1788.8	1819.8	1845.9	1862.1	1877.0	1887.0	1899.7
12.5°	1905.5	1943.7	1968.5	1991.2	2006.6	2019.3	2021.4
15°	2032.4	2090.1	2133.9	2166.1	2182.1	2190.5	2187.2
17.5°	2160.3	2213.8	2245.0	2277.9	2300.1	2301.3	2301.9
20°	2232.7	2284.8	2320.9	2345.3	2370.2	2369.2	2374.7
22.5°	2281.0	2322.1	2349.8	2367.5	2376.0	2371.8	2372.9
25°	2303.7	2315.9	2310.9	2282.6	2275.4	2249.3	2253.7
27.5°	2187.0	2129.2	2069.6	1992.8	1932.2	1883.7	1886.2
30°	2028.5	1926.4	1809.9	1712.2	1624.6	1600.2	1548.0
32.5°	1807.0	1653.8	1517.4	1426.4	1351.1	1330.7	1285.2
35°	1431.5	1282.8	1142.4	1058.1	1024.7	978.2	977.6
37.5°	1112.6	981.7	907.5	844.2	811.1	782.9	780.1
40°	936.0	833.9	777.9	732.4	699.7	678.6	673.6
42.5°	812.6	730.0	677.6	649.4	624.2	613.3	605.2
45°	663.6	608.1	571.4	545.9	534.3	525.9	521.5
47.5°	555.1	517.9	492.9	476.0	466.5	457.7	460.1
50°	496.0	465.5	447.2	431.1	423.9	417.8	418.3
52.5°	448.5	421.1	406.3	394.7	385.7	381.4	379.3
55°	380.6	363.4	348.5	340.1	335.1	329.1	327.3
57.5°	324.7	311.4	299.1	289.8	288.5	282.7	283.4
60°	287.4	276.3	266.4	261.3	257.5	252.4	254.1
62.5°	256.8	247.4	238.4	234.2	230.4	226.7	227.5
65°	210.3	201.4	195.8	193.6	192.0	190.3	188.7
67.5°	167.5	162.2	158.7	153.9	150.5	149.9	148.2
70°	141.0	133.7	127.6	121.5	119.8	119.3	119.8
72.5°	113.0	108.4	106.7	103.8	103.5	102.0	103.0
75°	84.9	83.2	82.1	79.9	79.9	79.9	79.9
77.5°	62.6	61.6	60.9	60.5	59.9	59.1	59.0
80°	48.8	48.3	47.1	47.1	46.6	47.1	46.6
82.5°	36.9	36.8	35.6	35.6	35.1	34.7	35.1
85°	18.8	18.3	19.4	18.3	18.8	17.8	18.8
87.5°	8.7	8.8	8.5	8.6	8.2	9.1	8.2
90°	17.0	17.5	18.0	18.3	18.6	18.8	19.2
92.5°	19.0	20.0	20.5	20.6	20.8	21.0	21.2
95°	22.7	23.7	24.2	24.2	24.2	24.2	24.2
97.5°	23.9	25.0	25.7	25.8	26.0	26.1	26.3
100°	24.5	25.6	26.2	26.3	26.5	26.7	26.7
102.5°	31.4	27.9	26.3	26.5	26.7	27.0	27.3
105°	64.4	39.3	26.9	27.2	27.5	27.8	28.0
107.5°	200.7	182.3	163.6	144.8	125.9	107.0	88.1
110°	273.5	268.8	256.3	236.0	215.8	195.5	175.3



TEST NUMBER: P332342-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	319.8	319.9	317.8	313.6	309.2	305.0	300.8
115°	370.1	371.5	372.5	373.1	373.7	374.2	374.8
117.5°	414.2	415.2	415.9	416.0	416.1	416.2	416.4
120°	443.2	444.3	444.9	444.9	444.9	444.9	444.9
122.5°	471.2	472.1	472.5	472.6	472.7	472.9	473.0
125°	510.8	511.0	511.4	511.6	511.9	512.2	512.5
127.5°	551.1	551.5	551.5	551.3	551.1	550.7	550.5
130°	575.4	575.9	576.1	575.8	575.5	575.2	574.9
132.5°	598.3	598.8	598.9	598.6	598.2	597.8	597.4
135°	632.9	633.3	633.3	632.9	632.5	632.1	631.7
137.5°	664.1	664.9	665.0	664.8	664.5	664.2	663.9
140°	683.7	684.3	684.4	684.1	683.9	683.5	683.3
142.5°	702.2	702.7	702.7	702.3	701.9	701.6	701.2
145°	728.1	728.4	728.6	728.6	728.6	728.6	728.6
147.5°	751.5	751.7	751.5	750.9	750.2	749.6	748.9
150°	765.7	766.0	766.0	765.5	765.1	764.7	764.3
152.5°	778.6	779.2	779.1	778.4	777.8	777.1	776.5
155°	796.3	797.0	797.0	796.1	795.2	794.4	793.5
157.5°	811.6	812.5	812.4	811.3	810.2	809.1	808.0
160°	820.4	821.2	821.1	820.1	819.1	818.2	817.2
162.5°	828.3	829.2	829.3	828.4	827.5	826.7	825.8
165°	839.0	840.2	840.2	839.3	838.2	837.2	836.3
167.5°	847.2	848.3	848.3	847.2	846.0	844.9	843.8
170°	851.7	852.9	852.9	851.7	850.6	849.5	848.4
172.5°	854.8	856.0	855.9	854.7	853.5	852.2	850.9
175°	858.3	859.3	859.2	858.2	857.0	855.9	854.8
177.5°	859.7	860.5	860.5	859.3	858.2	857.0	855.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9

(END OF REPORT)