

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331991-935

Luminaire Tested: **S123DIP-S775D1195U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331991-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1195U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6917.7 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35
2	87	80	74	69	79	73	68	64	60	57	54	49	46	44	37	36	34	29
3	80	71	64	58	73	65	59	54	53	49	45	43	40	37	33	31	30	25
4	73	63	55	49	66	57	51	46	48	43	39	38	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17
7	57	45	37	32	52	42	35	30	35	29	26	28	24	22	22	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10014	10014	10014	10014
5°	11943	10057	8912	10057
10°	14948	10006	8050	10006
15°	18333	9926	7494	9926
20°	21841	9800	7135	9800
25°	23192	9647	7056	9647
30°	19877	9536	7093	9536
35°	13825	9376	7167	9376
40°	10413	9190	7144	9190
45°	8645	8914	7054	8914
50°	7743	8348	6990	8348
55°	7240	7739	6902	7739
60°	6794	7102	6833	7102
65°	6383	6477	6612	6477
70°	5986	5759	6297	5759
75°	5361	5041	5772	5041
80°	4699	4135	4971	4135
85°	3680	3013	3335	3013



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.6	1.3
10°-20°	293.9	4.2
20°-30°	493.2	7.1
30°-40°	558.5	8.1
40°-50°	500.8	7.2
50°-60°	404.1	5.8
60°-70°	281.6	4.1
70°-80°	148.0	2.1
80°-90°	40.0	0.6
90°-100°	48.9	0.7
100°-110°	233.3	3.4
110°-120°	560.4	8.1
120°-130°	713.6	10.3
130°-140°	762.5	11.0
140°-150°	713.0	10.3
150°-160°	575.1	8.3
160°-170°	371.2	5.4
170°-180°	127.9	1.8
0°-30°	878.7	12.7
0°-40°	1437.2	20.8
0°-60°	2342.1	33.9
0°-90°	2811.7	40.6
90°-120°	842.6	12.2
90°-150°	3031.7	43.8
90°-180°	4106.0	59.4
0°-180°	6917.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	1105	931	825	931	1105	115
15°	1645	891	672	891	1645	475
25°	1953	812	594	812	1953	856
35°	1052	714	545	714	1052	684
45°	568	586	463	586	568	449
55°	386	412	368	412	386	346
65°	251	254	260	254	251	250
75°	129	121	139	121	129	138
85°	30	24	27	24	30	36
90°	30	1	30	1	30	15
95°	38	61	38	61	38	32
105°	44	298	44	298	44	101
115°	588	559	588	559	588	543
125°	804	788	804	788	804	718
135°	991	981	991	981	991	764
145°	1143	1132	1143	1132	1143	714
155°	1245	1247	1245	1247	1245	574
165°	1312	1315	1312	1315	1312	371
175°	1341	1346	1341	1346	1341	128
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	987.3	986.6	984.8	986.3	983.3	979.4	979.0	975.4	964.9	964.2	961.4
5°	1105.3	1101.6	1101.2	1100.7	1094.4	1085.9	1069.6	1068.2	1046.6	1035.8	1022.8
7.5°	1257.9	1259.8	1253.3	1247.5	1228.2	1215.5	1198.1	1175.8	1149.3	1122.3	1104.3
10°	1367.6	1382.4	1364.0	1351.3	1339.6	1317.5	1291.8	1259.8	1227.9	1190.4	1162.0
12.5°	1485.1	1492.5	1488.8	1476.9	1458.6	1425.0	1379.5	1344.2	1314.7	1252.4	1227.3
15°	1645.2	1672.8	1655.2	1614.5	1615.5	1583.5	1524.0	1458.6	1423.9	1369.3	1295.0
17.5°	1815.8	1819.2	1811.7	1778.0	1755.4	1711.4	1656.5	1593.9	1523.5	1457.5	1378.6
20°	1906.7	1903.9	1888.2	1870.6	1831.9	1797.6	1737.7	1667.8	1577.6	1512.7	1426.6
22.5°	1957.1	1952.7	1945.2	1930.4	1898.2	1861.4	1807.6	1731.2	1645.5	1556.0	1456.6
25°	1952.7	1958.5	1959.4	1955.3	1944.1	1922.0	1879.6	1818.8	1733.1	1618.2	1514.5
27.5°	1776.0	1784.3	1808.4	1829.7	1853.6	1877.9	1874.7	1844.4	1781.1	1681.9	1555.1
30°	1599.2	1581.2	1625.8	1682.2	1720.5	1788.1	1826.0	1828.2	1792.6	1707.4	1583.9
32.5°	1354.0	1373.9	1393.6	1462.9	1546.7	1622.6	1698.0	1758.7	1765.6	1708.9	1600.9
35°	1052.1	1076.9	1112.9	1148.9	1239.2	1316.6	1449.1	1564.5	1656.5	1668.7	1602.4
37.5°	847.7	860.1	882.9	918.9	977.9	1069.9	1172.4	1318.3	1451.5	1550.6	1554.9
40°	741.1	744.7	770.3	797.8	845.6	921.4	1013.7	1142.6	1302.2	1440.6	1498.3
42.5°	661.0	668.9	679.8	706.2	744.2	801.2	887.2	993.7	1140.0	1299.2	1412.1
45°	567.9	577.0	583.8	601.3	628.4	666.7	726.6	824.0	935.3	1099.8	1251.7
47.5°	506.4	507.2	512.2	525.5	543.9	572.7	615.0	677.6	779.8	913.2	1069.2
50°	462.4	469.7	471.5	481.8	496.3	517.5	552.6	605.8	689.7	806.8	950.2
52.5°	431.4	433.6	438.7	446.2	458.7	475.3	505.8	547.4	613.2	713.1	844.9
55°	385.8	385.8	390.8	396.7	403.9	418.7	439.0	469.7	519.7	597.3	706.4
57.5°	343.6	345.9	349.4	351.2	357.3	367.2	384.1	407.4	444.7	504.4	591.1
60°	315.6	319.6	319.2	322.7	328.1	335.8	350.3	369.2	402.5	450.3	523.3
62.5°	291.0	290.8	290.7	295.0	300.4	307.7	317.0	333.5	361.8	404.2	466.3
65°	250.6	249.7	252.9	255.5	257.4	262.8	270.0	284.4	303.3	334.9	383.1
67.5°	214.7	212.2	213.9	214.7	217.8	222.1	228.8	237.7	252.8	278.1	314.4
70°	190.2	188.0	187.5	188.4	191.1	194.2	199.2	207.8	221.8	242.0	268.6
72.5°	165.0	163.4	163.3	165.3	166.6	168.7	172.2	180.0	191.1	206.4	231.2
75°	128.9	128.9	128.9	129.3	130.7	132.5	135.3	139.3	147.8	158.7	175.3
77.5°	96.6	96.5	96.0	95.9	97.9	98.8	99.4	103.1	107.9	115.2	127.3
80°	75.8	73.4	74.4	75.8	76.6	77.1	78.4	79.3	83.4	87.5	96.0
82.5°	56.2	54.3	54.5	56.7	56.8	57.3	58.6	59.8	61.4	65.1	69.7
85°	29.8	29.8	30.2	30.2	30.7	30.2	31.5	32.0	32.0	34.3	36.9
87.5°	16.8	16.0	16.3	16.5	16.1	16.4	16.5	16.7	16.9	17.0	16.9
90°	30.0	29.5	29.1	28.7	28.2	27.6	26.7	25.7	24.9	24.0	21.1
92.5°	33.2	33.0	32.7	32.4	32.1	31.3	29.9	28.4	27.0	25.6	23.4
95°	38.0	38.0	38.0	38.0	38.0	37.2	35.6	34.1	32.5	31.0	28.6
97.5°	41.2	41.0	40.8	40.6	40.3	39.3	37.5	35.7	34.0	32.2	48.2
100°	42.0	41.8	41.6	41.3	41.2	40.1	38.3	36.6	34.8	33.0	67.7
102.5°	42.8	42.4	42.0	41.6	41.2	43.7	49.2	54.8	60.3	65.8	103.7
105°	44.0	43.6	43.1	42.7	42.3	61.6	101.0	140.3	179.7	219.0	239.1
107.5°	138.3	167.9	197.5	227.2	256.8	286.1	315.0	343.8	372.6	401.6	398.4
110°	275.1	306.9	338.6	370.5	402.3	421.8	429.1	436.4	443.8	451.2	448.7



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	471.9	478.6	485.3	492.1	498.8	502.1	502.0	501.8	501.7	501.5	499.1
115°	588.1	587.3	586.4	585.5	584.6	583.1	580.8	578.6	576.4	574.2	572.2
117.5°	653.4	653.2	653.1	652.9	652.7	651.7	650.0	648.2	646.4	644.6	643.6
120°	698.2	698.2	698.2	698.2	698.2	697.3	695.5	693.8	692.0	690.2	689.6
122.5°	742.3	742.1	741.8	741.7	741.5	740.8	739.6	738.3	737.1	735.8	734.9
125°	804.3	803.8	803.4	802.9	802.5	802.0	801.6	801.2	800.7	800.2	799.4
127.5°	863.8	864.4	864.8	865.2	865.6	865.5	864.8	864.1	863.4	862.6	861.6
130°	902.3	902.8	903.2	903.6	904.0	903.9	902.9	902.1	901.2	900.3	899.4
132.5°	937.5	938.1	938.7	939.4	940.0	939.9	939.0	938.1	937.2	936.3	935.6
135°	991.4	992.0	992.6	993.3	994.0	994.0	993.3	992.6	992.0	991.4	990.4
137.5°	1041.9	1042.4	1042.8	1043.3	1043.7	1043.4	1042.3	1041.3	1040.2	1039.1	1038.6
140°	1072.4	1072.8	1073.2	1073.7	1074.1	1073.9	1073.0	1072.1	1071.3	1070.3	1069.7
142.5°	1100.4	1101.0	1101.6	1102.3	1102.9	1102.8	1102.1	1101.4	1100.7	1099.9	1099.3
145°	1143.3	1143.3	1143.3	1143.3	1143.3	1143.1	1142.7	1142.3	1141.8	1141.3	1140.9
147.5°	1175.4	1176.4	1177.4	1178.5	1179.5	1179.7	1179.3	1178.9	1178.5	1177.9	1177.5
150°	1199.4	1200.1	1200.8	1201.4	1202.0	1202.1	1201.7	1201.3	1200.8	1200.4	1200.0
152.5°	1218.6	1219.6	1220.6	1221.7	1222.7	1222.8	1222.0	1221.2	1220.4	1219.6	1219.3
155°	1245.4	1246.7	1248.1	1249.4	1250.7	1250.9	1249.7	1248.6	1247.5	1246.4	1246.2
157.5°	1268.0	1269.7	1271.4	1273.2	1275.0	1275.1	1273.8	1272.5	1271.2	1269.8	1270.1
160°	1282.4	1283.9	1285.6	1287.1	1288.7	1288.7	1287.4	1286.1	1284.8	1283.4	1283.7
162.5°	1296.0	1297.4	1298.7	1300.1	1301.5	1301.5	1299.9	1298.5	1296.9	1295.4	1295.6
165°	1312.4	1314.0	1315.5	1317.1	1318.6	1318.5	1316.7	1315.0	1313.2	1311.4	1311.6
167.5°	1324.2	1326.0	1327.7	1329.6	1331.4	1331.4	1329.6	1327.7	1326.0	1324.2	1324.2
170°	1331.5	1333.2	1335.0	1336.8	1338.5	1338.5	1336.8	1335.0	1333.2	1331.5	1331.5
172.5°	1335.4	1337.4	1339.4	1341.3	1343.2	1343.3	1341.5	1339.8	1338.0	1336.2	1336.0
175°	1341.4	1343.2	1345.0	1346.8	1348.5	1348.7	1347.1	1345.6	1344.0	1342.4	1342.2
177.5°	1343.2	1345.0	1346.8	1348.6	1350.3	1350.5	1349.1	1347.6	1346.3	1344.8	1344.6
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	959.2	956.3	953.4	948.4	944.1	937.9	936.1	933.9	927.5	921.7	917.4
5°	1017.8	1006.9	991.2	976.8	965.1	949.3	940.3	930.8	917.3	905.1	895.2
7.5°	1079.1	1057.8	1033.3	1006.8	982.1	958.3	939.1	922.0	903.0	885.1	871.2
10°	1127.7	1097.1	1062.9	1025.9	994.4	963.7	938.0	915.5	891.1	870.0	852.4
12.5°	1183.3	1137.9	1090.6	1045.8	1008.4	965.9	934.8	906.1	878.5	853.0	833.3
15°	1249.1	1191.4	1135.4	1073.7	1016.9	963.7	926.8	890.7	858.7	832.5	807.3
17.5°	1308.9	1243.5	1169.8	1094.8	1026.2	963.2	911.5	870.6	830.6	798.7	773.5
20°	1342.8	1268.4	1185.0	1107.1	1031.3	961.0	904.2	855.5	812.3	778.4	750.0
22.5°	1372.0	1285.0	1198.7	1115.3	1031.0	955.2	890.9	840.8	793.8	760.8	730.6
25°	1402.3	1298.1	1211.6	1113.8	1019.6	941.2	869.0	812.3	765.3	726.6	695.5
27.5°	1428.2	1297.3	1194.6	1089.3	1001.8	923.2	846.1	785.2	735.5	693.4	661.8
30°	1445.5	1299.1	1176.9	1072.8	984.5	903.3	828.5	767.2	714.9	672.1	642.3
32.5°	1456.4	1298.0	1160.7	1049.7	957.0	885.3	809.3	745.9	692.2	650.1	621.4
35°	1462.7	1290.0	1132.7	1002.0	912.7	842.9	779.4	713.5	657.2	617.9	585.6
37.5°	1450.1	1273.3	1100.3	956.1	858.3	789.5	736.1	680.0	626.1	582.9	555.0
40°	1430.2	1262.6	1075.0	923.6	820.8	754.6	709.0	654.0	600.8	559.8	533.6
42.5°	1392.3	1240.5	1047.2	887.5	781.9	715.6	673.7	627.8	577.4	538.9	512.8
45°	1299.9	1192.7	1005.6	833.4	724.4	655.8	618.9	585.6	540.0	502.6	480.0
47.5°	1171.7	1120.7	945.4	776.4	664.3	598.4	560.0	533.1	499.9	469.7	448.1
50°	1082.7	1061.5	904.7	737.4	624.3	559.8	522.9	498.5	474.7	444.4	424.6
52.5°	979.9	993.0	857.0	697.1	583.5	520.1	485.3	466.1	444.4	419.6	402.3
55°	835.3	882.5	774.8	629.2	522.9	462.4	429.6	412.4	399.8	381.3	366.4
57.5°	699.7	760.0	686.0	559.4	463.3	411.2	379.6	360.9	352.8	343.2	331.5
60°	619.3	678.8	622.5	512.5	423.3	373.7	345.7	329.9	321.8	315.0	305.1
62.5°	547.6	607.8	560.4	464.9	383.9	337.9	313.7	298.3	291.9	288.3	279.9
65°	448.9	500.8	469.2	390.8	327.7	287.1	265.0	254.3	248.4	247.0	241.6
67.5°	365.4	404.8	381.9	324.2	274.5	239.4	220.7	211.5	207.0	206.6	202.5
70°	310.6	347.5	329.9	277.7	234.9	207.3	191.1	183.0	180.3	179.9	177.6
72.5°	268.0	293.8	279.8	236.2	203.1	178.1	166.3	157.7	154.7	155.3	153.8
75°	198.3	217.7	209.6	179.4	152.8	136.6	126.7	121.2	118.6	119.9	118.1
77.5°	142.7	155.0	147.7	126.7	110.4	98.6	91.4	88.0	85.6	85.5	84.6
80°	107.7	114.9	110.9	98.2	84.7	74.8	69.0	66.7	65.3	64.9	64.5
82.5°	76.7	82.8	78.1	69.4	60.2	54.2	51.0	48.0	47.0	47.3	46.8
85°	38.7	41.0	39.2	33.8	30.2	27.5	25.7	24.4	23.4	23.8	23.0
87.5°	17.0	16.8	15.2	13.2	12.0	10.5	10.0	8.9	8.6	9.0	9.1
90°	18.3	15.3	12.5	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	21.3	19.1	16.9	16.1	16.7	17.4	18.0	18.6	18.0	17.4	16.7
95°	26.1	23.7	21.3	24.5	33.7	42.8	51.9	61.0	51.9	42.8	33.7
97.5°	64.2	80.2	96.3	106.2	110.4	114.4	118.6	122.6	118.6	114.4	110.4
100°	102.4	137.1	171.7	186.8	182.4	178.0	173.5	169.0	173.5	178.0	182.4
102.5°	141.5	179.4	217.3	234.7	231.4	228.3	225.1	221.9	225.1	228.3	231.4
105°	259.1	279.1	299.1	307.9	305.4	303.0	300.6	298.1	300.6	303.0	305.4
107.5°	395.2	392.1	388.9	386.3	384.4	382.5	380.5	378.5	380.5	382.5	384.4
110°	446.3	443.8	441.3	439.3	437.5	435.7	433.9	432.1	433.9	435.7	437.5



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	496.7	494.2	491.8	489.7	488.2	486.6	484.9	483.4	484.9	486.6	488.2
115°	570.2	568.2	566.2	564.5	563.2	561.8	560.5	559.2	560.5	561.8	563.2
117.5°	642.6	641.5	640.5	639.2	637.6	635.8	634.2	632.6	634.2	635.8	637.6
120°	688.9	688.2	687.6	686.2	684.2	682.3	680.2	678.2	680.2	682.3	684.2
122.5°	734.2	733.3	732.5	731.2	729.5	727.9	726.3	724.6	726.3	727.9	729.5
125°	798.5	797.5	796.7	795.4	793.6	791.8	790.1	788.2	790.1	791.8	793.6
127.5°	860.6	859.5	858.4	857.0	855.2	853.4	851.6	849.9	851.6	853.4	855.2
130°	898.5	897.6	896.7	895.4	893.6	891.8	890.1	888.3	890.1	891.8	893.6
132.5°	934.9	934.2	933.4	932.2	930.4	928.7	926.9	925.1	926.9	928.7	930.4
135°	989.5	988.7	987.7	986.6	985.3	984.0	982.7	981.3	982.7	984.0	985.3
137.5°	1038.2	1037.7	1037.2	1036.1	1034.4	1032.7	1031.0	1029.3	1031.0	1032.7	1034.4
140°	1069.0	1068.3	1067.6	1066.7	1065.3	1064.0	1062.6	1061.4	1062.6	1064.0	1065.3
142.5°	1098.6	1097.9	1097.3	1096.3	1094.9	1093.6	1092.3	1091.0	1092.3	1093.6	1094.9
145°	1140.5	1140.1	1139.6	1138.6	1137.0	1135.5	1133.9	1132.4	1133.9	1135.5	1137.0
147.5°	1177.1	1176.6	1176.2	1175.4	1174.4	1173.5	1172.4	1171.4	1172.4	1173.5	1174.4
150°	1199.5	1199.0	1198.6	1198.1	1197.4	1196.7	1196.0	1195.4	1196.0	1196.7	1197.4
152.5°	1219.1	1218.7	1218.5	1218.2	1217.9	1217.6	1217.3	1217.0	1217.3	1217.6	1217.9
155°	1246.0	1245.7	1245.5	1245.6	1246.0	1246.5	1247.0	1247.4	1247.0	1246.5	1246.0
157.5°	1270.2	1270.5	1270.7	1270.8	1270.8	1270.9	1270.9	1271.0	1270.9	1270.9	1270.8
160°	1283.8	1284.1	1284.3	1284.5	1284.8	1285.0	1285.2	1285.4	1285.2	1285.0	1284.8
162.5°	1295.9	1296.1	1296.3	1296.7	1297.3	1297.9	1298.5	1299.0	1298.5	1297.9	1297.3
165°	1311.8	1312.1	1312.3	1312.8	1313.5	1314.1	1314.7	1315.4	1314.7	1314.1	1313.5
167.5°	1324.2	1324.2	1324.2	1324.6	1325.6	1326.5	1327.3	1328.3	1327.3	1326.5	1325.6
170°	1331.5	1331.5	1331.5	1331.9	1332.7	1333.7	1334.6	1335.4	1334.6	1333.7	1332.7
172.5°	1335.8	1335.7	1335.5	1335.9	1337.0	1338.1	1339.2	1340.2	1339.2	1338.1	1337.0
175°	1342.0	1341.8	1341.5	1342.0	1343.1	1344.2	1345.3	1346.4	1345.3	1344.2	1343.1
177.5°	1344.5	1344.3	1344.1	1344.5	1345.4	1346.3	1347.1	1348.1	1347.1	1346.3	1345.4
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	914.8	912.3	908.7	903.3	899.0	892.1	892.1	893.2	893.2	892.9	892.1
5°	887.1	880.3	872.2	862.7	852.8	842.9	841.1	837.5	834.8	833.0	830.7
7.5°	857.8	845.8	834.0	820.7	808.7	798.7	791.7	785.9	782.2	778.3	775.4
10°	837.9	823.0	809.1	795.1	779.8	767.7	760.0	754.6	750.5	746.9	745.1
12.5°	814.5	797.5	782.0	768.8	752.0	739.5	732.2	729.7	724.9	717.3	713.3
15°	780.2	764.5	746.0	725.7	717.6	702.2	693.7	689.7	686.9	681.1	679.2
17.5°	751.0	730.3	709.6	694.4	679.3	666.9	662.1	657.1	653.5	648.7	647.3
20°	727.5	709.0	690.1	673.9	658.1	644.5	640.5	636.9	633.3	631.0	629.2
22.5°	703.7	685.3	669.5	654.4	637.6	628.7	624.3	620.4	617.8	616.3	614.5
25°	670.3	654.0	636.5	622.9	609.4	603.6	600.8	598.6	596.8	594.5	594.1
27.5°	640.3	622.7	608.4	595.8	586.1	581.2	578.6	577.5	577.9	578.7	579.2
30°	617.9	601.8	590.0	579.2	570.2	565.7	565.2	565.2	567.1	567.5	568.4
32.5°	597.4	584.1	572.4	561.9	555.1	552.0	553.7	553.7	555.2	556.3	557.9
35°	567.5	555.8	546.7	537.8	531.9	533.2	534.2	535.0	537.3	540.0	541.8
37.5°	538.9	528.7	519.4	512.3	509.6	512.0	514.2	516.1	518.8	520.8	522.6
40°	518.3	510.7	501.7	495.3	496.3	497.7	499.5	501.7	503.9	505.3	507.1
42.5°	499.2	491.2	484.4	479.1	480.4	482.2	483.2	484.4	487.0	489.4	490.5
45°	470.1	463.8	457.5	454.3	455.3	456.2	457.0	458.4	460.6	462.4	463.0
47.5°	437.4	433.0	428.8	425.7	427.1	426.8	427.9	430.8	431.5	432.7	435.1
50°	416.5	412.4	407.5	406.6	406.6	406.6	407.0	410.6	410.6	412.4	414.2
52.5°	393.4	390.8	387.6	386.0	385.3	385.3	387.2	389.0	389.7	392.3	394.1
55°	359.2	356.5	353.9	352.5	351.5	352.5	356.1	357.0	359.2	360.6	362.0
57.5°	323.6	321.6	319.4	318.7	318.5	319.7	321.7	324.3	324.9	329.1	331.1
60°	300.2	297.0	295.2	295.2	294.4	298.4	297.5	302.0	302.9	305.6	308.8
62.5°	276.0	271.8	271.0	271.0	272.3	273.5	274.7	276.7	279.1	282.5	285.0
65°	237.1	234.9	238.0	237.5	236.6	239.4	239.4	241.6	244.3	247.5	252.4
67.5°	200.2	199.1	199.3	199.3	200.7	202.2	203.5	205.4	208.7	212.1	215.2
70°	175.3	176.7	174.4	176.2	177.6	178.1	178.9	181.7	185.3	187.5	191.1
72.5°	151.2	151.1	151.4	152.1	153.4	154.2	155.2	158.3	162.2	164.1	166.9
75°	116.3	115.8	117.2	117.2	119.4	120.4	121.2	122.6	126.2	128.9	131.1
77.5°	84.9	85.5	85.2	86.7	86.1	86.3	89.0	90.4	90.7	96.1	97.3
80°	64.0	64.9	65.3	65.8	66.3	65.3	68.5	69.8	69.8	73.0	75.3
82.5°	46.0	46.5	47.7	48.1	48.2	49.2	49.4	50.4	51.5	52.9	55.8
85°	23.0	24.4	24.8	24.4	24.8	23.8	25.2	25.7	26.2	26.2	26.2
87.5°	9.2	10.1	10.2	11.2	11.5	12.4	12.6	12.0	12.2	13.4	12.1
90°	9.9	12.5	15.3	18.3	21.1	24.0	24.9	25.7	26.7	27.6	28.2
92.5°	16.1	16.9	19.1	21.3	23.4	25.6	27.0	28.4	29.9	31.3	32.1
95°	24.5	21.3	23.7	26.1	28.6	31.0	32.5	34.1	35.6	37.2	38.0
97.5°	106.2	96.3	80.2	64.2	48.2	32.2	34.0	35.7	37.5	39.3	40.3
100°	186.8	171.7	137.1	102.4	67.7	33.0	34.8	36.6	38.3	40.1	41.2
102.5°	234.7	217.3	179.4	141.5	103.7	65.8	60.3	54.8	49.2	43.7	41.2
105°	307.9	299.1	279.1	259.1	239.1	219.0	179.7	140.3	101.0	61.6	42.3
107.5°	386.3	388.9	392.1	395.2	398.4	401.6	372.6	343.8	315.0	286.1	256.8
110°	439.3	441.3	443.8	446.3	448.7	451.2	443.8	436.4	429.1	421.8	402.3



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	489.7	491.8	494.2	496.7	499.1	501.5	501.7	501.8	502.0	502.1	498.8
115°	564.5	566.2	568.2	570.2	572.2	574.2	576.4	578.6	580.8	583.1	584.6
117.5°	639.2	640.5	641.5	642.6	643.6	644.6	646.4	648.2	650.0	651.7	652.7
120°	686.2	687.6	688.2	688.9	689.6	690.2	692.0	693.8	695.5	697.3	698.2
122.5°	731.2	732.5	733.3	734.2	734.9	735.8	737.1	738.3	739.6	740.8	741.5
125°	795.4	796.7	797.5	798.5	799.4	800.2	800.7	801.2	801.6	802.0	802.5
127.5°	857.0	858.4	859.5	860.6	861.6	862.6	863.4	864.1	864.8	865.5	865.6
130°	895.4	896.7	897.6	898.5	899.4	900.3	901.2	902.1	902.9	903.9	904.0
132.5°	932.2	933.4	934.2	934.9	935.6	936.3	937.2	938.1	939.0	939.9	940.0
135°	986.6	987.7	988.7	989.5	990.4	991.4	992.0	992.6	993.3	994.0	994.0
137.5°	1036.1	1037.2	1037.7	1038.2	1038.6	1039.1	1040.2	1041.3	1042.3	1043.4	1043.7
140°	1066.7	1067.6	1068.3	1069.0	1069.7	1070.3	1071.3	1072.1	1073.0	1073.9	1074.1
142.5°	1096.3	1097.3	1097.9	1098.6	1099.3	1099.9	1100.7	1101.4	1102.1	1102.8	1102.9
145°	1138.6	1139.6	1140.1	1140.5	1140.9	1141.3	1141.8	1142.3	1142.7	1143.1	1143.3
147.5°	1175.4	1176.2	1176.6	1177.1	1177.5	1177.9	1178.5	1178.9	1179.3	1179.7	1179.5
150°	1198.1	1198.6	1199.0	1199.5	1200.0	1200.4	1200.8	1201.3	1201.7	1202.1	1202.0
152.5°	1218.2	1218.5	1218.7	1219.1	1219.3	1219.6	1220.4	1221.2	1222.0	1222.8	1222.7
155°	1245.6	1245.5	1245.7	1246.0	1246.2	1246.4	1247.5	1248.6	1249.7	1250.9	1250.7
157.5°	1270.8	1270.7	1270.5	1270.2	1270.1	1269.8	1271.2	1272.5	1273.8	1275.1	1275.0
160°	1284.5	1284.3	1284.1	1283.8	1283.7	1283.4	1284.8	1286.1	1287.4	1288.7	1288.7
162.5°	1296.7	1296.3	1296.1	1295.9	1295.6	1295.4	1296.9	1298.5	1299.9	1301.5	1301.5
165°	1312.8	1312.3	1312.1	1311.8	1311.6	1311.4	1313.2	1315.0	1316.7	1318.5	1318.6
167.5°	1324.6	1324.2	1324.2	1324.2	1324.2	1324.2	1326.0	1327.7	1329.6	1331.4	1331.4
170°	1331.9	1331.5	1331.5	1331.5	1331.5	1331.5	1333.2	1335.0	1336.8	1338.5	1338.5
172.5°	1335.9	1335.5	1335.7	1335.8	1336.0	1336.2	1338.0	1339.8	1341.5	1343.3	1343.2
175°	1342.0	1341.5	1341.8	1342.0	1342.2	1342.4	1344.0	1345.6	1347.1	1348.7	1348.5
177.5°	1344.5	1344.1	1344.3	1344.5	1344.6	1344.8	1346.3	1347.6	1349.1	1350.5	1350.3
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	889.6	889.2	891.7	889.9	891.7	889.2	889.6	892.1	892.9	893.2	893.2
5°	828.0	829.4	824.8	824.8	824.8	829.4	828.0	830.7	833.0	834.8	837.5
7.5°	773.2	771.2	771.4	769.0	771.4	771.2	773.2	775.4	778.3	782.2	785.9
10°	739.7	737.0	736.1	736.5	736.1	737.0	739.7	745.1	746.9	750.5	754.6
12.5°	711.9	711.4	705.4	705.5	705.4	711.4	711.9	713.3	717.3	724.9	729.7
15°	679.2	670.7	669.8	672.5	669.8	670.7	679.2	679.2	681.1	686.9	689.7
17.5°	646.5	642.0	642.3	640.9	642.3	642.0	646.5	647.3	648.7	653.5	657.1
20°	629.2	626.5	626.1	622.9	626.1	626.5	629.2	629.2	631.0	633.3	636.9
22.5°	613.4	612.5	612.8	609.2	612.8	612.5	613.4	614.5	616.3	617.8	620.4
25°	593.7	595.9	594.1	594.1	594.1	595.9	593.7	594.1	594.5	596.8	598.6
27.5°	580.3	580.2	579.3	579.3	579.3	580.2	580.3	579.2	578.7	577.9	577.5
30°	570.2	569.7	570.7	570.7	570.7	569.7	570.2	568.4	567.5	567.1	565.2
32.5°	560.1	560.8	560.9	561.3	560.9	560.8	560.1	557.9	556.3	555.2	553.7
35°	544.5	544.9	546.3	545.4	546.3	544.9	544.5	541.8	540.0	537.3	535.0
37.5°	523.4	525.5	525.0	525.7	525.0	525.5	523.4	522.6	520.8	518.8	516.1
40°	507.6	508.9	508.4	508.4	508.4	508.9	507.6	507.1	505.3	503.9	501.7
42.5°	491.3	492.3	491.1	490.4	491.1	492.3	491.3	490.5	489.4	487.0	484.4
45°	464.7	463.8	465.2	463.4	465.2	463.8	464.7	463.0	462.4	460.6	458.4
47.5°	435.0	435.8	436.3	437.6	436.3	435.8	435.0	435.1	432.7	431.5	430.8
50°	415.2	417.8	417.8	417.4	417.8	417.8	415.2	414.2	412.4	410.6	410.6
52.5°	395.6	396.9	398.7	398.6	398.7	396.9	395.6	394.1	392.3	389.7	389.0
55°	365.6	366.4	367.4	367.8	367.4	366.4	365.6	362.0	360.6	359.2	357.0
57.5°	334.3	334.0	336.1	336.8	336.1	334.0	334.3	331.1	329.1	324.9	324.3
60°	312.4	312.4	316.0	317.4	316.0	312.4	312.4	308.8	305.6	302.9	302.0
62.5°	289.0	290.4	293.9	292.1	293.9	290.4	289.0	285.0	282.5	279.1	276.7
65°	254.7	258.3	257.9	259.6	257.9	258.3	254.7	252.4	247.5	244.3	241.6
67.5°	218.9	221.1	224.4	224.6	224.4	221.1	218.9	215.2	212.1	208.7	205.4
70°	194.8	197.0	198.8	200.1	198.8	197.0	194.8	191.1	187.5	185.3	181.7
72.5°	171.3	172.5	176.8	174.9	176.8	172.5	171.3	166.9	164.1	162.2	158.3
75°	134.3	137.5	140.2	138.8	140.2	137.5	134.3	131.1	128.9	126.2	122.6
77.5°	99.4	102.5	103.8	102.6	103.8	102.5	99.4	97.3	96.1	90.7	90.4
80°	78.4	78.0	80.7	80.2	80.7	78.0	78.4	75.3	73.0	69.8	69.8
82.5°	57.5	57.1	58.3	58.6	58.3	57.1	57.5	55.8	52.9	51.5	50.4
85°	28.0	29.3	27.5	27.0	27.5	29.3	28.0	26.2	26.2	26.2	25.7
87.5°	12.2	12.3	12.1	11.8	12.1	12.3	12.2	12.1	13.4	12.2	12.0
90°	28.7	29.1	29.5	30.0	29.5	29.1	28.7	28.2	27.6	26.7	25.7
92.5°	32.4	32.7	33.0	33.2	33.0	32.7	32.4	32.1	31.3	29.9	28.4
95°	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	37.2	35.6	34.1
97.5°	40.6	40.8	41.0	41.2	41.0	40.8	40.6	40.3	39.3	37.5	35.7
100°	41.3	41.6	41.8	42.0	41.8	41.6	41.3	41.2	40.1	38.3	36.6
102.5°	41.6	42.0	42.4	42.8	42.4	42.0	41.6	41.2	43.7	49.2	54.8
105°	42.7	43.1	43.6	44.0	43.6	43.1	42.7	42.3	61.6	101.0	140.3
107.5°	227.2	197.5	167.9	138.3	167.9	197.5	227.2	256.8	286.1	315.0	343.8
110°	370.5	338.6	306.9	275.1	306.9	338.6	370.5	402.3	421.8	429.1	436.4



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	492.1	485.3	478.6	471.9	478.6	485.3	492.1	498.8	502.1	502.0	501.8
115°	585.5	586.4	587.3	588.1	587.3	586.4	585.5	584.6	583.1	580.8	578.6
117.5°	652.9	653.1	653.2	653.4	653.2	653.1	652.9	652.7	651.7	650.0	648.2
120°	698.2	698.2	698.2	698.2	698.2	698.2	698.2	698.2	697.3	695.5	693.8
122.5°	741.7	741.8	742.1	742.3	742.1	741.8	741.7	741.5	740.8	739.6	738.3
125°	802.9	803.4	803.8	804.3	803.8	803.4	802.9	802.5	802.0	801.6	801.2
127.5°	865.2	864.8	864.4	863.8	864.4	864.8	865.2	865.6	865.5	864.8	864.1
130°	903.6	903.2	902.8	902.3	902.8	903.2	903.6	904.0	903.9	902.9	902.1
132.5°	939.4	938.7	938.1	937.5	938.1	938.7	939.4	940.0	939.9	939.0	938.1
135°	993.3	992.6	992.0	991.4	992.0	992.6	993.3	994.0	994.0	993.3	992.6
137.5°	1043.3	1042.8	1042.4	1041.9	1042.4	1042.8	1043.3	1043.7	1043.4	1042.3	1041.3
140°	1073.7	1073.2	1072.8	1072.4	1072.8	1073.2	1073.7	1074.1	1073.9	1073.0	1072.1
142.5°	1102.3	1101.6	1101.0	1100.4	1101.0	1101.6	1102.3	1102.9	1102.8	1102.1	1101.4
145°	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.1	1142.7	1142.3
147.5°	1178.5	1177.4	1176.4	1175.4	1176.4	1177.4	1178.5	1179.5	1179.7	1179.3	1178.9
150°	1201.4	1200.8	1200.1	1199.4	1200.1	1200.8	1201.4	1202.0	1202.1	1201.7	1201.3
152.5°	1221.7	1220.6	1219.6	1218.6	1219.6	1220.6	1221.7	1222.7	1222.8	1222.0	1221.2
155°	1249.4	1248.1	1246.7	1245.4	1246.7	1248.1	1249.4	1250.7	1250.9	1249.7	1248.6
157.5°	1273.2	1271.4	1269.7	1268.0	1269.7	1271.4	1273.2	1275.0	1275.1	1273.8	1272.5
160°	1287.1	1285.6	1283.9	1282.4	1283.9	1285.6	1287.1	1288.7	1288.7	1287.4	1286.1
162.5°	1300.1	1298.7	1297.4	1296.0	1297.4	1298.7	1300.1	1301.5	1301.5	1299.9	1298.5
165°	1317.1	1315.5	1314.0	1312.4	1314.0	1315.5	1317.1	1318.6	1318.5	1316.7	1315.0
167.5°	1329.6	1327.7	1326.0	1324.2	1326.0	1327.7	1329.6	1331.4	1331.4	1329.6	1327.7
170°	1336.8	1335.0	1333.2	1331.5	1333.2	1335.0	1336.8	1338.5	1338.5	1336.8	1335.0
172.5°	1341.3	1339.4	1337.4	1335.4	1337.4	1339.4	1341.3	1343.2	1343.3	1341.5	1339.8
175°	1346.8	1345.0	1343.2	1341.4	1343.2	1345.0	1346.8	1348.5	1348.7	1347.1	1345.6
177.5°	1348.6	1346.8	1345.0	1343.2	1345.0	1346.8	1348.6	1350.3	1350.5	1349.1	1347.6
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	892.1	892.1	899.0	903.3	908.7	912.3	914.8	917.4	921.7	927.5	933.9
5°	841.1	842.9	852.8	862.7	872.2	880.3	887.1	895.2	905.1	917.3	930.8
7.5°	791.7	798.7	808.7	820.7	834.0	845.8	857.8	871.2	885.1	903.0	922.0
10°	760.0	767.7	779.8	795.1	809.1	823.0	837.9	852.4	870.0	891.1	915.5
12.5°	732.2	739.5	752.0	768.8	782.0	797.5	814.5	833.3	853.0	878.5	906.1
15°	693.7	702.2	717.6	725.7	746.0	764.5	780.2	807.3	832.5	858.7	890.7
17.5°	662.1	666.9	679.3	694.4	709.6	730.3	751.0	773.5	798.7	830.6	870.6
20°	640.5	644.5	658.1	673.9	690.1	709.0	727.5	750.0	778.4	812.3	855.5
22.5°	624.3	628.7	637.6	654.4	669.5	685.3	703.7	730.6	760.8	793.8	840.8
25°	600.8	603.6	609.4	622.9	636.5	654.0	670.3	695.5	726.6	765.3	812.3
27.5°	578.6	581.2	586.1	595.8	608.4	622.7	640.3	661.8	693.4	735.5	785.2
30°	565.2	565.7	570.2	579.2	590.0	601.8	617.9	642.3	672.1	714.9	767.2
32.5°	553.7	552.0	555.1	561.9	572.4	584.1	597.4	621.4	650.1	692.2	745.9
35°	534.2	533.2	531.9	537.8	546.7	555.8	567.5	585.6	617.9	657.2	713.5
37.5°	514.2	512.0	509.6	512.3	519.4	528.7	538.9	555.0	582.9	626.1	680.0
40°	499.5	497.7	496.3	495.3	501.7	510.7	518.3	533.6	559.8	600.8	654.0
42.5°	483.2	482.2	480.4	479.1	484.4	491.2	499.2	512.8	538.9	577.4	627.8
45°	457.0	456.2	455.3	454.3	457.5	463.8	470.1	480.0	502.6	540.0	585.6
47.5°	427.9	426.8	427.1	425.7	428.8	433.0	437.4	448.1	469.7	499.9	533.1
50°	407.0	406.6	406.6	406.6	407.5	412.4	416.5	424.6	444.4	474.7	498.5
52.5°	387.2	385.3	385.3	386.0	387.6	390.8	393.4	402.3	419.6	444.4	466.1
55°	356.1	352.5	351.5	352.5	353.9	356.5	359.2	366.4	381.3	399.8	412.4
57.5°	321.7	319.7	318.5	318.7	319.4	321.6	323.6	331.5	343.2	352.8	360.9
60°	297.5	298.4	294.4	295.2	295.2	297.0	300.2	305.1	315.0	321.8	329.9
62.5°	274.7	273.5	272.3	271.0	271.0	271.8	276.0	279.9	288.3	291.9	298.3
65°	239.4	239.4	236.6	237.5	238.0	234.9	237.1	241.6	247.0	248.4	254.3
67.5°	203.5	202.2	200.7	199.3	199.3	199.1	200.2	202.5	206.6	207.0	211.5
70°	178.9	178.1	177.6	176.2	174.4	176.7	175.3	177.6	179.9	180.3	183.0
72.5°	155.2	154.2	153.4	152.1	151.4	151.1	151.2	153.8	155.3	154.7	157.7
75°	121.2	120.4	119.4	117.2	117.2	115.8	116.3	118.1	119.9	118.6	121.2
77.5°	89.0	86.3	86.1	86.7	85.2	85.5	84.9	84.6	85.5	85.6	88.0
80°	68.5	65.3	66.3	65.8	65.3	64.9	64.0	64.5	64.9	65.3	66.7
82.5°	49.4	49.2	48.2	48.1	47.7	46.5	46.0	46.8	47.3	47.0	48.0
85°	25.2	23.8	24.8	24.4	24.8	24.4	23.0	23.0	23.8	23.4	24.4
87.5°	12.6	12.4	11.5	11.2	10.2	10.1	9.2	9.1	9.0	8.6	8.9
90°	24.9	24.0	21.1	18.3	15.3	12.5	9.9	7.7	5.4	3.2	1.0
92.5°	27.0	25.6	23.4	21.3	19.1	16.9	16.1	16.7	17.4	18.0	18.6
95°	32.5	31.0	28.6	26.1	23.7	21.3	24.5	33.7	42.8	51.9	61.0
97.5°	34.0	32.2	48.2	64.2	80.2	96.3	106.2	110.4	114.4	118.6	122.6
100°	34.8	33.0	67.7	102.4	137.1	171.7	186.8	182.4	178.0	173.5	169.0
102.5°	60.3	65.8	103.7	141.5	179.4	217.3	234.7	231.4	228.3	225.1	221.9
105°	179.7	219.0	239.1	259.1	279.1	299.1	307.9	305.4	303.0	300.6	298.1
107.5°	372.6	401.6	398.4	395.2	392.1	388.9	386.3	384.4	382.5	380.5	378.5
110°	443.8	451.2	448.7	446.3	443.8	441.3	439.3	437.5	435.7	433.9	432.1



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	501.7	501.5	499.1	496.7	494.2	491.8	489.7	488.2	486.6	484.9	483.4
115°	576.4	574.2	572.2	570.2	568.2	566.2	564.5	563.2	561.8	560.5	559.2
117.5°	646.4	644.6	643.6	642.6	641.5	640.5	639.2	637.6	635.8	634.2	632.6
120°	692.0	690.2	689.6	688.9	688.2	687.6	686.2	684.2	682.3	680.2	678.2
122.5°	737.1	735.8	734.9	734.2	733.3	732.5	731.2	729.5	727.9	726.3	724.6
125°	800.7	800.2	799.4	798.5	797.5	796.7	795.4	793.6	791.8	790.1	788.2
127.5°	863.4	862.6	861.6	860.6	859.5	858.4	857.0	855.2	853.4	851.6	849.9
130°	901.2	900.3	899.4	898.5	897.6	896.7	895.4	893.6	891.8	890.1	888.3
132.5°	937.2	936.3	935.6	934.9	934.2	933.4	932.2	930.4	928.7	926.9	925.1
135°	992.0	991.4	990.4	989.5	988.7	987.7	986.6	985.3	984.0	982.7	981.3
137.5°	1040.2	1039.1	1038.6	1038.2	1037.7	1037.2	1036.1	1034.4	1032.7	1031.0	1029.3
140°	1071.3	1070.3	1069.7	1069.0	1068.3	1067.6	1066.7	1065.3	1064.0	1062.6	1061.4
142.5°	1100.7	1099.9	1099.3	1098.6	1097.9	1097.3	1096.3	1094.9	1093.6	1092.3	1091.0
145°	1141.8	1141.3	1140.9	1140.5	1140.1	1139.6	1138.6	1137.0	1135.5	1133.9	1132.4
147.5°	1178.5	1177.9	1177.5	1177.1	1176.6	1176.2	1175.4	1174.4	1173.5	1172.4	1171.4
150°	1200.8	1200.4	1200.0	1199.5	1199.0	1198.6	1198.1	1197.4	1196.7	1196.0	1195.4
152.5°	1220.4	1219.6	1219.3	1219.1	1218.7	1218.5	1218.2	1217.9	1217.6	1217.3	1217.0
155°	1247.5	1246.4	1246.2	1246.0	1245.7	1245.5	1245.6	1246.0	1246.5	1247.0	1247.4
157.5°	1271.2	1269.8	1270.1	1270.2	1270.5	1270.7	1270.8	1270.8	1270.9	1270.9	1271.0
160°	1284.8	1283.4	1283.7	1283.8	1284.1	1284.3	1284.5	1284.8	1285.0	1285.2	1285.4
162.5°	1296.9	1295.4	1295.6	1295.9	1296.1	1296.3	1296.7	1297.3	1297.9	1298.5	1299.0
165°	1313.2	1311.4	1311.6	1311.8	1312.1	1312.3	1312.8	1313.5	1314.1	1314.7	1315.4
167.5°	1326.0	1324.2	1324.2	1324.2	1324.2	1324.2	1324.6	1325.6	1326.5	1327.3	1328.3
170°	1333.2	1331.5	1331.5	1331.5	1331.5	1331.5	1331.9	1332.7	1333.7	1334.6	1335.4
172.5°	1338.0	1336.2	1336.0	1335.8	1335.7	1335.5	1335.9	1337.0	1338.1	1339.2	1340.2
175°	1344.0	1342.4	1342.2	1342.0	1341.8	1341.5	1342.0	1343.1	1344.2	1345.3	1346.4
177.5°	1346.3	1344.8	1344.6	1344.5	1344.3	1344.1	1344.5	1345.4	1346.3	1347.1	1348.1
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	936.1	937.9	944.1	948.4	953.4	956.3	959.2	961.4	964.2	964.9	975.4
5°	940.3	949.3	965.1	976.8	991.2	1006.9	1017.8	1022.8	1035.8	1046.6	1068.2
7.5°	939.1	958.3	982.1	1006.8	1033.3	1057.8	1079.1	1104.3	1122.3	1149.3	1175.8
10°	938.0	963.7	994.4	1025.9	1062.9	1097.1	1127.7	1162.0	1190.4	1227.9	1259.8
12.5°	934.8	965.9	1008.4	1045.8	1090.6	1137.9	1183.3	1227.3	1252.4	1314.7	1344.2
15°	926.8	963.7	1016.9	1073.7	1135.4	1191.4	1249.1	1295.0	1369.3	1423.9	1458.6
17.5°	911.5	963.2	1026.2	1094.8	1169.8	1243.5	1308.9	1378.6	1457.5	1523.5	1593.9
20°	904.2	961.0	1031.3	1107.1	1185.0	1268.4	1342.8	1426.6	1512.7	1577.6	1667.8
22.5°	890.9	955.2	1031.0	1115.3	1198.7	1285.0	1372.0	1456.6	1556.0	1645.5	1731.2
25°	869.0	941.2	1019.6	1113.8	1211.6	1298.1	1402.3	1514.5	1618.2	1733.1	1818.8
27.5°	846.1	923.2	1001.8	1089.3	1194.6	1297.3	1428.2	1555.1	1681.9	1781.1	1844.4
30°	828.5	903.3	984.5	1072.8	1176.9	1299.1	1445.5	1583.9	1707.4	1792.6	1828.2
32.5°	809.3	885.3	957.0	1049.7	1160.7	1298.0	1456.4	1600.9	1708.9	1765.6	1758.7
35°	779.4	842.9	912.7	1002.0	1132.7	1290.0	1462.7	1602.4	1668.7	1656.5	1564.5
37.5°	736.1	789.5	858.3	956.1	1100.3	1273.3	1450.1	1554.9	1550.6	1451.5	1318.3
40°	709.0	754.6	820.8	923.6	1075.0	1262.6	1430.2	1498.3	1440.6	1302.2	1142.6
42.5°	673.7	715.6	781.9	887.5	1047.2	1240.5	1392.3	1412.1	1299.2	1140.0	993.7
45°	618.9	655.8	724.4	833.4	1005.6	1192.7	1299.9	1251.7	1099.8	935.3	824.0
47.5°	560.0	598.4	664.3	776.4	945.4	1120.7	1171.7	1069.2	913.2	779.8	677.6
50°	522.9	559.8	624.3	737.4	904.7	1061.5	1082.7	950.2	806.8	689.7	605.8
52.5°	485.3	520.1	583.5	697.1	857.0	993.0	979.9	844.9	713.1	613.2	547.4
55°	429.6	462.4	522.9	629.2	774.8	882.5	835.3	706.4	597.3	519.7	469.7
57.5°	379.6	411.2	463.3	559.4	686.0	760.0	699.7	591.1	504.4	444.7	407.4
60°	345.7	373.7	423.3	512.5	622.5	678.8	619.3	523.3	450.3	402.5	369.2
62.5°	313.7	337.9	383.9	464.9	560.4	607.8	547.6	466.3	404.2	361.8	333.5
65°	265.0	287.1	327.7	390.8	469.2	500.8	448.9	383.1	334.9	303.3	284.4
67.5°	220.7	239.4	274.5	324.2	381.9	404.8	365.4	314.4	278.1	252.8	237.7
70°	191.1	207.3	234.9	277.7	329.9	347.5	310.6	268.6	242.0	221.8	207.8
72.5°	166.3	178.1	203.1	236.2	279.8	293.8	268.0	231.2	206.4	191.1	180.0
75°	126.7	136.6	152.8	179.4	209.6	217.7	198.3	175.3	158.7	147.8	139.3
77.5°	91.4	98.6	110.4	126.7	147.7	155.0	142.7	127.3	115.2	107.9	103.1
80°	69.0	74.8	84.7	98.2	110.9	114.9	107.7	96.0	87.5	83.4	79.3
82.5°	51.0	54.2	60.2	69.4	78.1	82.8	76.7	69.7	65.1	61.4	59.8
85°	25.7	27.5	30.2	33.8	39.2	41.0	38.7	36.9	34.3	32.0	32.0
87.5°	10.0	10.5	12.0	13.2	15.2	16.8	17.0	16.9	17.0	16.9	16.7
90°	3.2	5.4	7.7	9.9	12.5	15.3	18.3	21.1	24.0	24.9	25.7
92.5°	18.0	17.4	16.7	16.1	16.9	19.1	21.3	23.4	25.6	27.0	28.4
95°	51.9	42.8	33.7	24.5	21.3	23.7	26.1	28.6	31.0	32.5	34.1
97.5°	118.6	114.4	110.4	106.2	96.3	80.2	64.2	48.2	32.2	34.0	35.7
100°	173.5	178.0	182.4	186.8	171.7	137.1	102.4	67.7	33.0	34.8	36.6
102.5°	225.1	228.3	231.4	234.7	217.3	179.4	141.5	103.7	65.8	60.3	54.8
105°	300.6	303.0	305.4	307.9	299.1	279.1	259.1	239.1	219.0	179.7	140.3
107.5°	380.5	382.5	384.4	386.3	388.9	392.1	395.2	398.4	401.6	372.6	343.8
110°	433.9	435.7	437.5	439.3	441.3	443.8	446.3	448.7	451.2	443.8	436.4



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	484.9	486.6	488.2	489.7	491.8	494.2	496.7	499.1	501.5	501.7	501.8
115°	560.5	561.8	563.2	564.5	566.2	568.2	570.2	572.2	574.2	576.4	578.6
117.5°	634.2	635.8	637.6	639.2	640.5	641.5	642.6	643.6	644.6	646.4	648.2
120°	680.2	682.3	684.2	686.2	687.6	688.2	688.9	689.6	690.2	692.0	693.8
122.5°	726.3	727.9	729.5	731.2	732.5	733.3	734.2	734.9	735.8	737.1	738.3
125°	790.1	791.8	793.6	795.4	796.7	797.5	798.5	799.4	800.2	800.7	801.2
127.5°	851.6	853.4	855.2	857.0	858.4	859.5	860.6	861.6	862.6	863.4	864.1
130°	890.1	891.8	893.6	895.4	896.7	897.6	898.5	899.4	900.3	901.2	902.1
132.5°	926.9	928.7	930.4	932.2	933.4	934.2	934.9	935.6	936.3	937.2	938.1
135°	982.7	984.0	985.3	986.6	987.7	988.7	989.5	990.4	991.4	992.0	992.6
137.5°	1031.0	1032.7	1034.4	1036.1	1037.2	1037.7	1038.2	1038.6	1039.1	1040.2	1041.3
140°	1062.6	1064.0	1065.3	1066.7	1067.6	1068.3	1069.0	1069.7	1070.3	1071.3	1072.1
142.5°	1092.3	1093.6	1094.9	1096.3	1097.3	1097.9	1098.6	1099.3	1099.9	1100.7	1101.4
145°	1133.9	1135.5	1137.0	1138.6	1139.6	1140.1	1140.5	1140.9	1141.3	1141.8	1142.3
147.5°	1172.4	1173.5	1174.4	1175.4	1176.2	1176.6	1177.1	1177.5	1177.9	1178.5	1178.9
150°	1196.0	1196.7	1197.4	1198.1	1198.6	1199.0	1199.5	1200.0	1200.4	1200.8	1201.3
152.5°	1217.3	1217.6	1217.9	1218.2	1218.5	1218.7	1219.1	1219.3	1219.6	1220.4	1221.2
155°	1247.0	1246.5	1246.0	1245.6	1245.5	1245.7	1246.0	1246.2	1246.4	1247.5	1248.6
157.5°	1270.9	1270.9	1270.8	1270.8	1270.7	1270.5	1270.2	1270.1	1269.8	1271.2	1272.5
160°	1285.2	1285.0	1284.8	1284.5	1284.3	1284.1	1283.8	1283.7	1283.4	1284.8	1286.1
162.5°	1298.5	1297.9	1297.3	1296.7	1296.3	1296.1	1295.9	1295.6	1295.4	1296.9	1298.5
165°	1314.7	1314.1	1313.5	1312.8	1312.3	1312.1	1311.8	1311.6	1311.4	1313.2	1315.0
167.5°	1327.3	1326.5	1325.6	1324.6	1324.2	1324.2	1324.2	1324.2	1324.2	1326.0	1327.7
170°	1334.6	1333.7	1332.7	1331.9	1331.5	1331.5	1331.5	1331.5	1331.5	1333.2	1335.0
172.5°	1339.2	1338.1	1337.0	1335.9	1335.5	1335.7	1335.8	1336.0	1336.2	1338.0	1339.8
175°	1345.3	1344.2	1343.1	1342.0	1341.5	1341.8	1342.0	1342.2	1342.4	1344.0	1345.6
177.5°	1347.1	1346.3	1345.4	1344.5	1344.1	1344.3	1344.5	1344.6	1344.8	1346.3	1347.6
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	979.0	979.4	983.3	986.3	984.8	986.6	987.3
5°	1069.6	1085.9	1094.4	1100.7	1101.2	1101.6	1105.3
7.5°	1198.1	1215.5	1228.2	1247.5	1253.3	1259.8	1257.9
10°	1291.8	1317.5	1339.6	1351.3	1364.0	1382.4	1367.6
12.5°	1379.5	1425.0	1458.6	1476.9	1488.8	1492.5	1485.1
15°	1524.0	1583.5	1615.5	1614.5	1655.2	1672.8	1645.2
17.5°	1656.5	1711.4	1755.4	1778.0	1811.7	1819.2	1815.8
20°	1737.7	1797.6	1831.9	1870.6	1888.2	1903.9	1906.7
22.5°	1807.6	1861.4	1898.2	1930.4	1945.2	1952.7	1957.1
25°	1879.6	1922.0	1944.1	1955.3	1959.4	1958.5	1952.7
27.5°	1874.7	1877.9	1853.6	1829.7	1808.4	1784.3	1776.0
30°	1826.0	1788.1	1720.5	1682.2	1625.8	1581.2	1599.2
32.5°	1698.0	1622.6	1546.7	1462.9	1393.6	1373.9	1354.0
35°	1449.1	1316.6	1239.2	1148.9	1112.9	1076.9	1052.1
37.5°	1172.4	1069.9	977.9	918.9	882.9	860.1	847.7
40°	1013.7	921.4	845.6	797.8	770.3	744.7	741.1
42.5°	887.2	801.2	744.2	706.2	679.8	668.9	661.0
45°	726.6	666.7	628.4	601.3	583.8	577.0	567.9
47.5°	615.0	572.7	543.9	525.5	512.2	507.2	506.4
50°	552.6	517.5	496.3	481.8	471.5	469.7	462.4
52.5°	505.8	475.3	458.7	446.2	438.7	433.6	431.4
55°	439.0	418.7	403.9	396.7	390.8	385.8	385.8
57.5°	384.1	367.2	357.3	351.2	349.4	345.9	343.6
60°	350.3	335.8	328.1	322.7	319.2	319.6	315.6
62.5°	317.0	307.7	300.4	295.0	290.7	290.8	291.0
65°	270.0	262.8	257.4	255.5	252.9	249.7	250.6
67.5°	228.8	222.1	217.8	214.7	213.9	212.2	214.7
70°	199.2	194.2	191.1	188.4	187.5	188.0	190.2
72.5°	172.2	168.7	166.6	165.3	163.3	163.4	165.0
75°	135.3	132.5	130.7	129.3	128.9	128.9	128.9
77.5°	99.4	98.8	97.9	95.9	96.0	96.5	96.6
80°	78.4	77.1	76.6	75.8	74.4	73.4	75.8
82.5°	58.6	57.3	56.8	56.7	54.5	54.3	56.2
85°	31.5	30.2	30.7	30.2	30.2	29.8	29.8
87.5°	16.5	16.4	16.1	16.5	16.3	16.0	16.8
90°	26.7	27.6	28.2	28.7	29.1	29.5	30.0
92.5°	29.9	31.3	32.1	32.4	32.7	33.0	33.2
95°	35.6	37.2	38.0	38.0	38.0	38.0	38.0
97.5°	37.5	39.3	40.3	40.6	40.8	41.0	41.2
100°	38.3	40.1	41.2	41.3	41.6	41.8	42.0
102.5°	49.2	43.7	41.2	41.6	42.0	42.4	42.8
105°	101.0	61.6	42.3	42.7	43.1	43.6	44.0
107.5°	315.0	286.1	256.8	227.2	197.5	167.9	138.3
110°	429.1	421.8	402.3	370.5	338.6	306.9	275.1



TEST NUMBER: P331991-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	502.0	502.1	498.8	492.1	485.3	478.6	471.9
115°	580.8	583.1	584.6	585.5	586.4	587.3	588.1
117.5°	650.0	651.7	652.7	652.9	653.1	653.2	653.4
120°	695.5	697.3	698.2	698.2	698.2	698.2	698.2
122.5°	739.6	740.8	741.5	741.7	741.8	742.1	742.3
125°	801.6	802.0	802.5	802.9	803.4	803.8	804.3
127.5°	864.8	865.5	865.6	865.2	864.8	864.4	863.8
130°	902.9	903.9	904.0	903.6	903.2	902.8	902.3
132.5°	939.0	939.9	940.0	939.4	938.7	938.1	937.5
135°	993.3	994.0	994.0	993.3	992.6	992.0	991.4
137.5°	1042.3	1043.4	1043.7	1043.3	1042.8	1042.4	1041.9
140°	1073.0	1073.9	1074.1	1073.7	1073.2	1072.8	1072.4
142.5°	1102.1	1102.8	1102.9	1102.3	1101.6	1101.0	1100.4
145°	1142.7	1143.1	1143.3	1143.3	1143.3	1143.3	1143.3
147.5°	1179.3	1179.7	1179.5	1178.5	1177.4	1176.4	1175.4
150°	1201.7	1202.1	1202.0	1201.4	1200.8	1200.1	1199.4
152.5°	1222.0	1222.8	1222.7	1221.7	1220.6	1219.6	1218.6
155°	1249.7	1250.9	1250.7	1249.4	1248.1	1246.7	1245.4
157.5°	1273.8	1275.1	1275.0	1273.2	1271.4	1269.7	1268.0
160°	1287.4	1288.7	1288.7	1287.1	1285.6	1283.9	1282.4
162.5°	1299.9	1301.5	1301.5	1300.1	1298.7	1297.4	1296.0
165°	1316.7	1318.5	1318.6	1317.1	1315.5	1314.0	1312.4
167.5°	1329.6	1331.4	1331.4	1329.6	1327.7	1326.0	1324.2
170°	1336.8	1338.5	1338.5	1336.8	1335.0	1333.2	1331.5
172.5°	1341.5	1343.3	1343.2	1341.3	1339.4	1337.4	1335.4
175°	1347.1	1348.7	1348.5	1346.8	1345.0	1343.2	1341.4
177.5°	1349.1	1350.5	1350.3	1348.6	1346.8	1345.0	1343.2
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4

(END OF REPORT)