

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332347-930

Luminaire Tested: **S123RDIP-S1000D805U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332347-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D805U930-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5462.4 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332347-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332347-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	95	92	88	93	89	86	83	77	74	72	66	64	62	56	54	53	48
2	91	84	78	73	84	78	73	68	68	64	60	58	55	53	49	47	45	41
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39	35
4	76	66	58	52	71	62	55	49	54	48	44	46	42	39	40	36	34	31
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	36	32	30	27
6	65	53	45	39	60	50	42	37	44	38	33	38	33	30	33	29	26	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	34	29	36	31	26	32	27	24	27	24	21	19
9	52	40	32	27	48	38	31	26	33	28	24	29	25	22	25	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14727	14727	14727
5°	14783	14579	14664
10°	14700	14397	14348
15°	14542	14060	13912
20°	14325	13639	13321
25°	14101	13166	12744
30°	13806	12621	11931
35°	13502	12073	11184
40°	13222	11428	10260
45°	12855	10794	9426
50°	12450	10071	8492
55°	12037	9246	7621
60°	11657	8361	6665
65°	11163	7404	5708
70°	10546	6216	4611
75°	9649	4891	4338
80°	8598	4333	3986
85°	7262	3841	3569



TEST NUMBER: P332347-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.5	2.4
10°-20°	357.5	6.5
20°-30°	514.7	9.4
30°-40°	579.8	10.6
40°-50°	554.7	10.2
50°-60°	454.2	8.3
60°-70°	306.5	5.6
70°-80°	154.2	2.8
80°-90°	43.2	0.8
90°-100°	175.2	3.2
100°-110°	496.2	9.1
110°-120°	488.1	8.9
120°-130°	389.3	7.1
130°-140°	307.0	5.6
140°-150°	229.1	4.2
150°-160°	159.7	2.9
160°-170°	93.8	1.7
170°-180°	30.5	0.6
0°-30°	1000.7	18.3
0°-40°	1580.5	28.9
0°-60°	2589.5	47.4
0°-90°	3093.3	56.6
90°-120°	1159.6	21.2
90°-150°	2085.0	38.2
90°-180°	2369.0	43.4
0°-180°	5462.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1368	1368	1368	1368	1368	
5°	1368	1362	1349	1359	1357	130
15°	1305	1292	1262	1256	1248	367
25°	1187	1158	1109	1086	1073	546
35°	1028	986	919	873	851	643
45°	844	793	709	648	619	651
55°	641	585	493	431	406	575
65°	438	376	291	239	224	434
75°	232	178	118	107	104	247
85°	59	36	31	29	29	66
90°	1	8	16	18	18	4
95°	22	70	378	110	74	23
105°	74	109	512	896	811	79
115°	131	163	392	860	986	129
125°	182	214	366	663	778	161
135°	213	254	361	546	630	164
145°	243	278	356	448	493	152
155°	276	298	345	392	408	127
165°	302	310	330	350	356	85
175°	314	315	317	321	321	30
180°	315	315	315	315	315	



TEST NUMBER: P332347-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1372.6	1371.8	1371.1	1370.3	1369.5	1367.9	1365.5	1363.2	1360.8	1358.5	1360.6
5°	1368.2	1366.9	1365.7	1364.5	1363.3	1361.1	1358.2	1355.3	1352.3	1349.3	1351.5
7.5°	1355.5	1354.2	1352.9	1351.5	1350.2	1347.6	1343.8	1339.9	1336.1	1332.3	1333.5
10°	1344.9	1343.2	1341.4	1339.7	1338.0	1334.9	1330.5	1326.0	1321.6	1317.2	1317.4
12.5°	1329.8	1327.9	1326.0	1324.0	1322.1	1318.4	1313.0	1307.6	1302.2	1296.7	1296.6
15°	1305.0	1302.3	1299.5	1296.8	1294.1	1289.3	1282.4	1275.5	1268.6	1261.7	1260.5
17.5°	1273.7	1270.5	1267.4	1264.2	1261.0	1255.1	1246.3	1237.5	1228.7	1219.9	1217.3
20°	1250.6	1246.7	1242.7	1238.8	1234.8	1228.2	1218.8	1209.4	1200.0	1190.7	1187.5
22.5°	1224.8	1220.3	1215.8	1211.2	1206.7	1199.5	1189.4	1179.5	1169.5	1159.6	1155.6
25°	1187.3	1181.2	1175.0	1168.8	1162.7	1153.9	1142.6	1131.2	1119.9	1108.6	1103.3
27.5°	1141.8	1135.1	1128.2	1121.4	1114.6	1104.9	1092.3	1079.6	1067.0	1054.4	1047.2
30°	1110.8	1103.3	1096.0	1088.6	1081.2	1070.6	1056.8	1042.9	1029.2	1015.4	1007.0
32.5°	1079.7	1071.3	1062.9	1054.5	1046.2	1034.7	1020.1	1005.5	990.8	976.2	967.1
35°	1027.5	1018.6	1009.7	1000.9	992.1	979.9	964.7	949.3	934.1	918.8	908.2
37.5°	974.7	964.8	955.0	945.1	935.2	922.2	905.9	889.5	873.2	856.9	844.8
40°	941.0	930.2	919.2	908.4	897.6	883.4	865.9	848.4	830.9	813.3	800.5
42.5°	902.8	891.9	881.1	870.3	859.4	845.0	826.9	808.8	790.7	772.6	758.6
45°	844.5	833.3	822.2	811.1	800.1	785.1	766.1	747.1	728.1	709.1	695.0
47.5°	786.1	773.9	761.7	749.5	737.4	721.8	702.8	683.8	664.8	645.8	630.6
50°	743.5	731.9	720.3	708.7	697.1	681.3	661.4	641.4	621.4	601.4	586.1
52.5°	705.3	692.8	680.1	667.6	655.0	638.8	619.1	599.2	579.5	559.7	543.8
55°	641.4	629.3	617.2	605.1	593.0	576.5	555.5	534.6	513.6	492.7	478.4
57.5°	582.4	569.2	556.0	542.8	529.7	512.6	491.5	470.4	449.4	428.4	414.8
60°	541.5	528.0	514.4	500.8	487.2	470.3	449.8	429.3	408.9	388.4	375.0
62.5°	500.7	487.1	473.5	460.0	446.5	429.4	409.0	388.5	368.0	347.6	335.0
65°	438.3	424.8	411.2	397.6	384.1	367.7	348.5	329.2	310.0	290.7	278.7
67.5°	375.9	362.2	348.5	334.8	321.1	305.0	286.6	268.2	249.7	231.2	222.3
70°	335.1	321.8	308.5	295.1	281.8	266.6	249.3	232.0	214.7	197.5	188.9
72.5°	294.2	281.2	268.1	254.9	241.8	227.4	211.7	196.1	180.3	164.7	157.6
75°	232.0	220.0	208.2	196.4	184.6	171.9	158.3	144.7	131.2	117.6	115.1
77.5°	175.1	164.4	153.7	143.0	132.3	122.5	113.8	105.1	96.4	87.6	86.3
80°	138.7	128.6	118.5	108.4	98.2	90.7	85.4	80.2	75.1	69.9	69.1
82.5°	104.1	95.4	86.7	77.9	69.1	63.6	61.1	58.8	56.3	53.9	53.2
85°	58.8	53.4	47.9	42.6	37.1	34.0	33.3	32.5	31.8	31.1	30.6
87.5°	21.5	19.6	17.7	16.0	14.0	13.2	13.6	13.9	14.3	14.8	14.4
90°	1.3	2.5	3.8	5.7	7.0	8.3	10.2	12.1	14.0	15.9	15.3
92.5°	7.9	11.7	17.1	22.1	27.4	36.9	53.6	81.0	107.9	98.0	73.9
95°	21.7	23.6	30.6	41.4	58.0	82.8	137.1	232.0	336.6	378.0	306.6
97.5°	36.9	37.6	43.1	52.5	68.8	95.7	147.5	254.6	428.8	585.8	626.7
100°	47.2	47.8	52.3	61.2	76.5	101.3	145.9	240.3	408.0	603.6	729.2
102.5°	57.9	59.0	62.9	71.4	85.2	107.9	148.0	228.0	377.3	570.5	734.3
105°	73.9	75.8	79.7	87.3	99.5	119.2	153.6	219.2	339.7	512.5	695.5
107.5°	91.0	92.9	96.6	104.1	115.5	133.9	164.0	218.7	315.8	461.2	627.4
110°	103.3	105.2	108.4	115.4	126.2	144.1	172.8	221.2	306.6	432.2	584.5



TEST NUMBER: P332347-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	114.5	116.4	119.6	126.6	137.5	154.7	181.4	226.2	301.5	412.8	547.3
115°	130.7	133.2	137.1	143.4	154.3	171.5	195.7	234.6	299.6	392.0	502.3
117.5°	146.8	149.8	153.0	158.8	171.0	186.9	210.8	245.6	300.8	379.8	475.2
120°	158.1	160.0	163.1	169.6	181.6	197.6	220.5	253.7	302.8	374.1	460.9
122.5°	167.8	169.7	172.8	179.8	191.4	208.3	230.7	261.3	306.3	370.6	449.1
125°	181.6	183.0	186.8	193.8	205.9	223.1	245.4	273.5	311.7	365.9	434.1
127.5°	192.2	194.1	198.9	206.0	219.4	236.6	258.1	283.4	317.8	363.6	420.9
130°	198.9	200.8	206.5	214.2	227.6	244.8	265.8	290.0	321.9	362.1	413.7
132.5°	204.0	206.4	212.6	221.8	235.2	251.9	272.4	296.1	325.0	361.5	407.1
135°	212.9	215.5	222.5	232.0	245.4	262.6	282.3	304.0	329.5	360.8	398.4
137.5°	221.3	224.0	230.9	241.1	254.3	270.3	289.3	309.9	332.6	359.4	390.9
140°	226.9	230.1	236.5	246.7	259.4	275.3	293.8	313.0	334.7	358.9	386.3
142.5°	233.0	235.7	242.6	251.8	264.6	279.4	297.4	316.0	336.1	357.8	382.2
145°	242.9	244.8	250.5	260.1	270.9	285.6	302.1	319.4	337.2	356.3	376.7
147.5°	252.8	254.0	259.6	267.8	278.3	290.8	306.0	321.4	337.2	353.9	371.4
150°	259.4	260.1	265.1	273.5	282.3	293.8	308.5	321.9	337.2	351.9	367.8
152.5°	266.0	266.2	271.3	278.6	286.4	297.4	310.1	322.9	335.7	349.3	363.7
155°	276.0	276.0	279.8	286.2	293.2	302.1	313.0	323.2	334.0	344.9	357.6
157.5°	283.9	284.4	287.5	293.1	299.1	306.0	314.6	323.8	331.8	340.9	350.7
160°	290.0	290.0	292.6	297.7	302.1	308.5	316.2	323.8	330.8	337.9	346.1
162.5°	294.6	294.6	296.7	300.8	304.7	310.1	316.7	323.3	328.8	334.8	341.5
165°	301.5	300.8	302.1	305.3	307.9	312.3	317.4	321.9	325.7	330.2	335.3
167.5°	306.7	306.0	306.6	309.0	310.8	313.6	317.3	320.9	322.7	325.6	329.3
170°	309.8	308.5	309.2	311.0	312.3	313.6	316.8	319.4	320.7	322.5	325.7
172.5°	311.9	311.0	311.2	312.6	313.3	314.1	316.8	318.9	319.1	320.0	322.1
175°	314.2	313.6	313.0	314.2	314.2	314.9	316.2	317.4	316.8	316.8	318.0
177.5°	315.4	314.9	314.4	314.9	314.9	314.9	315.4	316.4	315.4	314.9	315.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P332347-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1362.8	1365.0	1367.1	1368.0	1367.6	1367.3	1366.8	1366.4
5°	1353.8	1356.0	1358.2	1359.1	1358.6	1358.1	1357.6	1357.1
7.5°	1334.7	1335.9	1337.2	1337.4	1336.5	1335.7	1334.9	1334.0
10°	1317.7	1317.9	1318.2	1317.7	1316.4	1315.2	1313.9	1312.7
12.5°	1296.4	1296.3	1296.2	1295.3	1294.0	1292.5	1291.1	1289.6
15°	1259.2	1258.0	1256.8	1255.2	1253.5	1251.8	1250.1	1248.4
17.5°	1214.7	1212.1	1209.5	1206.9	1204.4	1201.8	1199.2	1196.6
20°	1184.2	1181.0	1177.9	1174.8	1171.8	1168.8	1165.9	1162.9
22.5°	1151.6	1147.6	1143.6	1140.2	1137.5	1134.7	1132.0	1129.2
25°	1098.2	1093.0	1087.9	1083.9	1081.2	1078.5	1075.8	1073.0
27.5°	1040.0	1032.8	1025.6	1019.9	1015.8	1011.6	1007.5	1003.4
30°	998.6	990.2	981.8	975.7	971.7	967.8	963.8	959.9
32.5°	957.9	948.8	939.6	932.9	928.8	924.6	920.5	916.3
35°	897.6	887.0	876.4	868.9	864.5	860.0	855.6	851.1
37.5°	832.8	820.8	808.8	800.0	794.5	789.0	783.6	778.1
40°	787.7	774.9	762.1	752.8	747.1	741.5	735.8	730.2
42.5°	744.5	730.5	716.5	706.9	701.9	696.8	691.7	686.6
45°	680.9	666.9	652.8	642.9	636.9	631.0	625.1	619.2
47.5°	615.2	600.0	584.7	574.4	569.1	563.9	558.6	553.3
50°	570.9	555.5	540.3	529.8	524.2	518.4	512.8	507.1
52.5°	528.0	512.1	496.2	485.7	480.6	475.6	470.5	465.4
55°	464.1	449.8	435.5	425.8	420.9	416.0	411.1	406.1
57.5°	401.3	387.8	374.3	365.4	361.3	357.0	352.9	348.6
60°	361.7	348.5	335.1	326.4	322.2	318.0	313.8	309.6
62.5°	322.5	310.0	297.4	288.9	284.6	280.2	275.8	271.4
65°	266.6	254.5	242.4	235.0	232.3	229.6	226.9	224.1
67.5°	213.2	204.2	195.2	189.1	186.3	183.4	180.4	177.6
70°	180.3	171.6	163.0	157.4	154.6	151.9	149.2	146.5
72.5°	150.6	143.5	136.5	132.4	131.3	130.1	129.0	127.8
75°	112.7	110.2	107.8	106.3	105.8	105.3	104.8	104.3
77.5°	85.0	83.6	82.3	81.4	81.0	80.5	80.0	79.5
80°	68.4	67.7	66.9	66.4	65.9	65.4	64.8	64.3
82.5°	52.4	51.7	51.0	50.5	50.5	50.4	50.2	50.1
85°	30.1	29.6	29.1	28.9	28.9	28.9	28.9	28.9
87.5°	14.3	14.3	14.2	14.3	13.9	13.9	13.8	13.5
90°	15.9	16.6	17.2	18.5	17.9	18.5	19.2	18.5
92.5°	53.6	42.6	37.6	34.3	33.2	31.2	31.9	30.7
95°	229.5	155.6	121.7	98.8	86.7	81.0	76.5	73.9
97.5°	572.0	458.2	375.9	299.7	252.7	224.0	206.8	201.3
100°	751.5	699.9	625.3	534.8	470.4	423.9	399.0	399.7
102.5°	811.1	809.5	766.1	708.7	658.6	621.7	601.0	586.3
105°	828.7	892.3	904.5	887.9	858.6	834.4	814.0	810.8
107.5°	778.4	881.9	937.8	960.4	961.0	952.8	945.9	940.0
110°	730.5	847.7	928.1	972.7	990.5	995.6	994.3	993.1



TEST NUMBER: P332347-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	683.1	802.9	892.9	950.2	982.9	998.7	1003.6	1003.8
115°	620.2	731.1	824.8	894.3	942.1	970.1	982.9	986.1
117.5°	574.7	670.4	754.6	825.1	874.9	907.0	925.4	929.8
120°	550.7	636.7	713.3	777.6	828.0	863.7	879.0	882.8
122.5°	531.9	609.8	680.6	740.5	785.1	817.3	834.1	838.9
125°	506.7	576.3	637.4	688.4	729.2	757.2	773.1	777.6
127.5°	484.9	546.7	602.0	648.4	684.7	708.7	723.1	727.2
130°	471.1	528.4	580.1	623.4	657.2	680.1	693.5	698.6
132.5°	458.3	511.1	559.1	600.5	632.2	655.2	667.0	670.6
135°	441.1	486.3	527.7	564.1	595.3	614.5	625.9	630.4
137.5°	425.4	462.5	498.2	529.7	556.0	575.4	585.1	588.0
140°	416.2	448.7	479.3	506.7	531.0	548.8	559.1	558.4
142.5°	407.6	435.5	462.0	485.8	506.5	522.3	531.5	530.8
145°	397.1	418.2	438.5	457.1	473.0	486.3	491.5	492.7
147.5°	388.6	405.3	421.8	434.9	446.9	456.0	460.9	461.4
150°	382.5	397.1	410.5	422.6	432.2	439.2	443.0	443.0
152.5°	376.8	389.5	401.3	411.4	418.9	425.4	427.7	427.7
155°	368.4	378.6	388.2	395.8	401.5	406.7	408.0	408.5
157.5°	359.5	368.0	375.4	381.4	386.4	390.2	391.3	391.1
160°	354.4	361.4	367.8	372.3	376.7	380.5	380.5	379.9
162.5°	348.3	354.2	360.1	364.1	367.0	370.3	370.3	369.7
165°	340.4	344.2	348.7	351.9	354.4	356.9	356.3	356.3
167.5°	333.5	336.4	339.0	341.3	342.4	344.2	343.6	343.6
170°	328.9	330.8	333.4	334.7	335.3	336.6	335.9	335.9
172.5°	324.8	326.2	328.2	329.1	329.1	330.4	329.3	328.8
175°	319.4	320.0	321.2	321.2	321.2	321.9	321.2	320.7
177.5°	315.9	316.4	316.9	316.9	316.4	316.9	315.9	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9

(END OF REPORT)