

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331998-935

Luminaire Tested: **S123DIP-S775D1195U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331998-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1195U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6260.4 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331998-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331998-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	67	65	57	55	53	44	43	42
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36
3	80	71	63	57	73	65	58	53	54	49	45	44	40	38	35	32	30
4	73	62	55	49	67	57	50	45	48	43	39	39	35	32	31	28	26
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	38	33	29	32	28	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11286	11286	11286
5°	11339	11182	11261
10°	11262	11086	11154
15°	11131	10961	10981
20°	10977	10781	10791
25°	10772	10568	10546
30°	10544	10331	10253
35°	10307	10081	9950
40°	10058	9805	9653
45°	9785	9552	9319
50°	9512	9239	8982
55°	9154	8916	8646
60°	8792	8540	8269
65°	8474	8130	7875
70°	8003	7660	7320
75°	7311	7049	6750
80°	6595	6316	6261
85°	5780	5570	5348



TEST NUMBER: P331998-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	1.6
10°-20°	278.9	4.5
20°-30°	411.9	6.6
30°-40°	481.2	7.7
40°-50°	483.8	7.7
50°-60°	425.0	6.8
60°-70°	316.6	5.1
70°-80°	180.4	2.9
80°-90°	55.6	0.9
90°-100°	83.0	1.3
100°-110°	248.3	4.0
110°-120°	422.3	6.7
120°-130°	555.5	8.9
130°-140°	624.4	10.0
140°-150°	613.8	9.8
150°-160°	516.7	8.3
160°-170°	343.9	5.5
170°-180°	120.4	1.9
0°-30°	789.6	12.6
0°-40°	1270.8	20.3
0°-60°	2179.5	34.8
0°-90°	2732.0	43.6
90°-120°	753.6	12.0
90°-150°	2547.3	40.7
90°-180°	3528.0	56.4
0°-180°	6260.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1048	1048	1048	1048	1048	
5°	1049	1045	1035	1043	1042	99
15°	999	995	984	990	985	281
25°	907	901	890	890	888	418
35°	784	779	767	762	757	490
45°	643	639	628	617	612	496
55°	488	486	475	466	461	437
65°	333	328	319	312	309	328
75°	176	172	170	165	162	188
85°	47	45	45	43	43	51
90°	1	11	24	28	30	6
95°	59	66	74	78	78	66
105°	225	228	236	236	238	241
115°	425	428	426	427	426	421
125°	622	625	623	619	615	555
135°	807	813	812	808	806	622
145°	979	981	984	983	979	612
155°	1122	1122	1122	1126	1119	516
165°	1222	1219	1218	1224	1218	344
175°	1270	1267	1266	1272	1266	121
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P331998-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5
2.5°	1052.1	1051.5	1050.9	1050.2	1049.6	1048.4	1046.5	1044.8	1043.0	1041.3	1042.8
5°	1049.4	1048.4	1047.4	1046.4	1045.3	1043.8	1041.6	1039.4	1037.2	1034.9	1037.0
7.5°	1039.1	1038.1	1037.1	1036.1	1035.1	1033.5	1031.1	1028.9	1026.6	1024.3	1026.1
10°	1030.4	1029.4	1028.5	1027.4	1026.5	1024.7	1022.0	1019.4	1016.8	1014.3	1016.1
12.5°	1018.9	1018.0	1017.3	1016.4	1015.5	1013.9	1011.5	1009.0	1006.6	1004.1	1005.5
15°	998.9	998.1	997.3	996.5	995.7	994.0	991.4	988.8	986.2	983.6	985.2
17.5°	975.6	974.6	973.5	972.5	971.5	969.7	967.1	964.4	961.8	959.2	960.4
20°	958.3	957.1	956.0	954.8	953.6	951.6	949.0	946.4	943.8	941.2	942.0
22.5°	938.8	937.6	936.4	935.2	934.0	932.1	929.5	927.0	924.4	921.7	922.4
25°	907.0	905.8	904.6	903.4	902.2	900.3	897.6	895.0	892.4	889.8	890.0
27.5°	872.9	871.7	870.6	869.4	868.2	866.3	863.4	860.7	857.8	855.0	855.1
30°	848.3	847.3	846.4	845.3	844.3	842.4	839.6	836.8	834.1	831.2	831.2
32.5°	823.8	822.5	821.1	819.8	818.6	816.8	814.6	812.4	810.3	808.1	807.0
35°	784.4	783.2	782.0	780.8	779.5	777.7	775.0	772.4	769.8	767.2	766.0
37.5°	743.9	742.4	740.9	739.3	737.9	735.8	733.1	730.5	727.8	725.2	723.8
40°	715.8	714.6	713.4	712.2	711.0	709.0	706.2	703.4	700.6	697.8	696.2
42.5°	687.7	686.3	684.9	683.6	682.3	680.2	677.3	674.5	671.8	668.9	667.4
45°	642.8	642.0	641.2	640.4	639.6	637.9	635.2	632.7	630.1	627.5	625.1
47.5°	598.2	597.1	595.9	594.8	593.6	591.8	589.4	586.9	584.4	582.0	579.6
50°	568.0	567.0	565.9	565.0	564.0	562.1	559.6	557.0	554.3	551.7	549.6
52.5°	536.2	535.5	534.9	534.2	533.5	531.8	529.0	526.2	523.5	520.7	518.8
55°	487.8	487.5	487.3	487.2	486.9	485.5	482.9	480.4	477.7	475.1	472.9
57.5°	441.6	440.9	440.2	439.5	438.9	437.5	435.4	433.3	431.2	429.1	427.1
60°	408.4	408.2	408.0	407.8	407.6	406.3	403.9	401.5	399.1	396.7	394.9
62.5°	378.8	378.3	377.8	377.3	376.8	375.3	372.9	370.5	368.1	365.7	363.9
65°	332.7	331.7	330.6	329.7	328.6	327.2	325.1	323.1	321.2	319.2	317.5
67.5°	283.8	282.9	282.1	281.1	280.3	279.1	277.6	276.0	274.5	273.0	271.6
70°	254.3	253.0	251.8	250.6	249.4	248.2	247.0	245.8	244.6	243.4	242.0
72.5°	223.3	222.3	221.4	220.6	219.7	218.6	217.2	215.9	214.5	213.1	211.9
75°	175.8	175.0	174.2	173.4	172.6	171.9	171.3	170.7	170.0	169.5	168.5
77.5°	133.8	133.4	132.9	132.5	132.0	131.5	130.7	130.0	129.3	128.5	127.9
80°	106.4	105.8	105.2	104.6	104.0	103.5	103.1	102.7	102.3	101.9	101.7
82.5°	79.7	79.6	79.5	79.3	79.2	79.1	79.0	79.0	78.9	78.8	78.4
85°	46.8	46.5	46.1	45.7	45.3	45.1	45.1	45.1	45.1	45.1	44.7
87.5°	18.9	18.9	18.9	18.9	18.8	19.0	19.5	19.8	20.2	20.7	20.7
90°	1.0	3.2	5.4	7.7	9.9	12.5	15.3	18.3	21.1	24.0	24.9
92.5°	24.2	25.7	27.2	28.8	30.2	31.9	33.5	35.1	36.8	38.4	39.1
95°	59.1	60.6	62.2	63.7	65.3	66.9	68.7	70.4	72.2	74.0	74.9
97.5°	104.9	106.0	107.2	108.3	109.4	110.7	112.0	113.3	114.5	115.8	116.8
100°	136.0	137.4	138.7	140.1	141.4	142.6	143.7	144.8	145.9	147.1	147.7
102.5°	172.0	172.9	173.7	174.4	175.3	176.4	177.9	179.3	180.8	182.3	183.0
105°	225.1	225.5	226.0	226.4	226.9	228.1	230.1	232.1	234.1	236.1	236.1
107.5°	286.7	287.0	287.2	287.5	287.7	288.3	289.1	289.9	290.7	291.5	292.2
110°	325.1	325.5	326.0	326.5	326.9	327.4	327.8	328.2	328.6	329.2	330.0



TEST NUMBER: P331998-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	365.2	365.4	365.7	365.9	366.2	366.4	366.4	366.5	366.6	366.7	367.8
115°	425.2	425.9	426.5	427.1	427.8	427.9	427.5	427.1	426.6	426.2	426.4
117.5°	485.6	486.0	486.5	486.9	487.3	487.3	486.7	486.1	485.6	485.0	484.9
120°	523.2	524.5	525.9	527.2	528.6	528.7	527.5	526.4	525.3	524.2	524.0
122.5°	562.4	563.4	564.4	565.3	566.4	566.5	565.9	565.3	564.8	564.2	563.6
125°	622.2	622.9	623.5	624.2	624.9	625.0	624.6	624.1	623.7	623.3	622.3
127.5°	677.4	678.9	680.3	681.7	683.1	683.6	683.1	682.6	682.2	681.7	680.4
130°	714.3	716.0	717.8	719.6	721.3	721.9	721.3	720.6	720.0	719.3	718.4
132.5°	751.1	752.9	754.7	756.4	758.2	758.9	758.4	757.9	757.3	756.9	755.8
135°	807.3	808.7	809.9	811.3	812.6	813.2	813.0	812.8	812.5	812.3	811.4
137.5°	859.4	860.4	861.5	862.6	863.8	864.6	865.2	865.7	866.3	866.9	866.0
140°	895.4	896.5	897.6	898.7	899.7	900.4	900.7	900.9	901.1	901.4	901.1
142.5°	928.2	929.3	930.4	931.5	932.6	933.3	933.8	934.2	934.5	935.0	934.7
145°	979.4	979.8	980.2	980.7	981.1	981.7	982.4	983.0	983.7	984.4	984.1
147.5°	1024.2	1025.0	1025.8	1026.6	1027.4	1028.1	1028.7	1029.3	1029.9	1030.6	1030.6
150°	1055.4	1055.8	1056.3	1056.7	1057.2	1057.7	1058.1	1058.5	1058.9	1059.4	1059.4
152.5°	1081.0	1081.7	1082.3	1082.9	1083.5	1083.9	1084.2	1084.5	1084.8	1085.0	1085.4
155°	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.8	1122.0	1122.2	1122.4	1123.3
157.5°	1155.8	1155.5	1155.3	1155.0	1154.8	1154.7	1154.9	1155.1	1155.3	1155.5	1156.4
160°	1177.4	1177.0	1176.6	1176.1	1175.7	1175.4	1175.4	1175.4	1175.4	1175.4	1176.6
162.5°	1196.6	1196.0	1195.4	1194.8	1194.2	1193.9	1194.1	1194.3	1194.5	1194.6	1195.8
165°	1221.5	1220.8	1220.1	1219.4	1218.8	1218.5	1218.5	1218.5	1218.5	1218.5	1219.8
167.5°	1241.3	1240.4	1239.5	1238.6	1237.7	1237.3	1237.5	1237.7	1237.9	1238.0	1239.4
170°	1252.5	1251.5	1250.7	1249.8	1248.9	1248.4	1248.4	1248.4	1248.4	1248.4	1250.0
172.5°	1261.3	1260.4	1259.5	1258.6	1257.7	1257.3	1257.3	1257.3	1257.3	1257.3	1258.7
175°	1270.5	1269.6	1268.7	1267.8	1267.0	1266.4	1266.4	1266.4	1266.4	1266.4	1267.8
177.5°	1274.3	1273.6	1272.9	1272.1	1271.4	1271.1	1271.1	1271.1	1271.1	1271.1	1272.1
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P331998-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5
2.5°	1044.5	1046.1	1047.7	1048.4	1048.3	1048.1	1047.9	1047.8
5°	1039.0	1040.9	1043.0	1043.8	1043.4	1043.0	1042.6	1042.2
7.5°	1027.9	1029.8	1031.6	1032.3	1032.1	1031.8	1031.6	1031.4
10°	1017.9	1019.6	1021.4	1022.2	1021.7	1021.3	1021.0	1020.5
12.5°	1006.8	1008.1	1009.4	1010.0	1009.7	1009.4	1009.3	1009.0
15°	986.8	988.3	990.0	990.2	988.9	987.7	986.6	985.4
17.5°	961.5	962.6	963.7	964.1	963.6	963.2	962.8	962.3
20°	942.8	943.6	944.4	944.5	943.9	943.3	942.7	942.1
22.5°	923.0	923.7	924.3	924.2	923.5	922.7	922.0	921.2
25°	890.2	890.4	890.6	890.4	889.8	889.2	888.6	888.0
27.5°	855.3	855.5	855.7	855.3	854.6	853.9	853.1	852.3
30°	831.2	831.2	831.2	830.5	829.1	827.7	826.3	824.9
32.5°	805.9	804.8	803.7	802.7	801.9	801.2	800.4	799.7
35°	764.8	763.6	762.4	761.3	760.3	759.3	758.3	757.2
37.5°	722.3	720.8	719.5	718.4	717.7	717.1	716.4	715.8
40°	694.6	693.0	691.4	690.2	689.4	688.5	687.8	687.0
42.5°	665.7	664.1	662.5	661.3	660.6	659.7	658.9	658.1
45°	622.7	620.3	617.9	616.1	615.2	614.2	613.1	612.2
47.5°	577.3	575.0	572.6	570.9	570.1	569.2	568.3	567.4
50°	547.3	545.1	542.9	541.2	540.0	538.8	537.6	536.4
52.5°	516.9	515.1	513.2	511.7	510.5	509.3	508.1	506.9
55°	470.7	468.5	466.3	464.7	463.6	462.7	461.7	460.7
57.5°	425.2	423.3	421.3	419.7	418.5	417.4	416.2	415.1
60°	393.0	391.2	389.4	388.1	387.0	386.1	385.0	384.1
62.5°	362.1	360.2	358.4	357.2	356.5	355.9	355.2	354.5
65°	315.9	314.4	312.7	311.6	311.0	310.4	309.8	309.2
67.5°	270.2	268.8	267.3	266.2	265.4	264.6	263.7	262.9
70°	240.6	239.2	237.8	236.6	235.6	234.6	233.6	232.6
72.5°	210.6	209.4	208.2	207.2	206.7	206.2	205.7	205.2
75°	167.5	166.5	165.5	164.7	164.1	163.5	162.9	162.3
77.5°	127.2	126.5	125.8	125.5	125.5	125.5	125.5	125.5
80°	101.5	101.3	101.1	101.0	101.0	101.0	101.0	101.0
82.5°	78.1	77.7	77.3	77.1	77.0	76.8	76.6	76.5
85°	44.3	43.9	43.5	43.3	43.3	43.3	43.3	43.3
87.5°	20.7	20.8	20.8	20.8	20.9	21.0	21.1	21.2
90°	25.8	26.7	27.6	28.2	28.7	29.1	29.5	30.0
92.5°	39.9	40.6	41.2	41.5	41.2	41.0	40.6	40.4
95°	75.8	76.7	77.6	78.0	78.0	78.0	78.0	78.0
97.5°	117.9	118.9	119.9	120.4	120.3	120.2	120.1	120.0
100°	148.4	149.0	149.7	150.2	150.8	151.2	151.6	152.1
102.5°	183.6	184.3	184.9	185.2	185.1	185.0	184.9	184.9
105°	236.1	236.1	236.1	236.3	236.8	237.2	237.6	238.1
107.5°	292.9	293.7	294.4	294.5	294.3	294.0	293.8	293.5
110°	330.9	331.8	332.7	332.9	332.4	332.0	331.6	331.1



TEST NUMBER: P331998-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	368.9	370.0	371.0	371.5	371.4	371.3	371.3	371.2
115°	426.6	426.8	427.1	427.1	426.8	426.6	426.4	426.2
117.5°	484.9	484.8	484.8	484.5	483.9	483.2	482.6	482.0
120°	523.7	523.6	523.3	523.0	522.5	522.1	521.7	521.2
122.5°	563.1	562.5	561.9	561.3	560.7	560.1	559.4	558.8
125°	621.5	620.6	619.7	618.8	617.9	617.0	616.1	615.3
127.5°	679.2	678.0	676.7	675.5	674.5	673.5	672.4	671.5
130°	717.5	716.6	715.7	714.5	712.9	711.4	709.8	708.3
132.5°	754.8	753.7	752.6	751.5	750.3	749.1	747.9	746.7
135°	810.5	809.6	808.7	808.0	807.6	807.2	806.8	806.3
137.5°	865.0	864.1	863.2	862.3	861.4	860.7	859.8	858.9
140°	900.9	900.7	900.4	899.6	898.0	896.5	894.9	893.4
142.5°	934.5	934.3	934.1	933.3	932.1	930.9	929.8	928.6
145°	984.0	983.7	983.5	982.9	982.1	981.1	980.2	979.4
147.5°	1030.6	1030.6	1030.6	1029.9	1028.6	1027.3	1025.9	1024.6
150°	1059.4	1059.4	1059.4	1058.8	1057.4	1056.1	1054.7	1053.4
152.5°	1085.7	1086.1	1086.4	1086.1	1084.9	1083.7	1082.5	1081.4
155°	1124.2	1125.1	1126.0	1125.7	1124.1	1122.6	1121.0	1119.4
157.5°	1157.3	1158.2	1159.2	1159.0	1157.8	1156.5	1155.3	1154.0
160°	1177.7	1178.8	1179.9	1180.0	1179.1	1178.2	1177.3	1176.5
162.5°	1196.9	1198.0	1199.1	1198.9	1197.5	1196.1	1194.6	1193.3
165°	1221.2	1222.4	1223.8	1223.7	1222.1	1220.6	1219.0	1217.5
167.5°	1240.8	1242.2	1243.5	1243.5	1242.2	1240.8	1239.4	1238.0
170°	1251.5	1253.2	1254.7	1254.7	1253.2	1251.5	1250.0	1248.4
172.5°	1260.1	1261.5	1262.8	1262.7	1261.1	1259.6	1258.0	1256.5
175°	1269.1	1270.5	1271.8	1271.7	1270.1	1268.6	1267.0	1265.5
177.5°	1273.2	1274.3	1275.3	1275.2	1274.0	1272.7	1271.5	1270.3
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5

(END OF REPORT)