

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831890

Luminaire Tested: S123RDIP-S1000D805U930-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831890  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D805U930-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5878.1 lumens  
Efficiency: N/A  
Efficacy: 105.5 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 55.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831890

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P831890

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60		
1	101	97	93	90	94	91	88	85	79	77	75	69	67	66	59	58	57	52		
2	93	86	80	75	87	81	76	71	71	67	64	62	59	56	53	51	49	45		
3	85	76	70	64	80	72	66	61	63	59	55	55	52	49	48	46	43	40		
4	79	68	61	55	73	65	58	53	57	52	48	50	46	43	44	41	38	35		
5	73	62	54	48	68	58	51	46	52	46	42	46	41	38	40	37	34	31		
6	68	56	48	43	63	53	46	41	47	42	38	42	38	34	37	34	31	28		
7	63	51	43	38	59	48	42	37	43	38	34	39	34	31	34	31	28	26		
8	59	47	39	34	55	44	38	33	40	34	31	36	31	28	32	28	26	23		
9	55	43	36	31	52	41	35	30	37	32	28	33	29	26	30	26	24	22		
10	52	40	33	28	49	38	32	27	34	29	26	31	27	24	28	24	22	20		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	28478	28478	28478	28478	28478
5°	33813	32736	28657	23166	21507
10°	30636	33250	28514	18560	15923
15°	21094	28509	28213	15170	12596
20°	14675	21950	27646	12791	11071
25°	11182	16728	26822	11370	10203
30°	9734	13375	25792	10556	9451
35°	8937	11282	24331	9871	8766
40°	8154	10075	22420	9198	8139
45°	7365	9214	20360	8561	7514
50°	6685	8502	17928	7937	6738
55°	6047	7807	15593	7328	5782
60°	5419	7100	13543	6654	5464
65°	5000	6299	11660	5980	5165
70°	4063	5445	10172	5410	4198
75°	3564	4329	8617	4487	3697
80°	3230	3663	7060	3763	3496
85°	2952	3211	5360	3421	3211

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 21482 cd/sqm



TEST NUMBER: P831890

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	241.1	4.1
10°-20°	558.0	9.5
20°-30°	640.2	10.9
30°-40°	631.1	10.7
40°-50°	556.5	9.5
50°-60°	428.1	7.3
60°-70°	281.5	4.8
70°-80°	136.7	2.3
80°-90°	36.2	0.6
90°-100°	170.9	2.9
100°-110°	500.3	8.5
110°-120°	488.5	8.3
120°-130°	389.1	6.6
130°-140°	307.0	5.2
140°-150°	229.0	3.9
150°-160°	159.7	2.7
160°-170°	93.8	1.6
170°-180°	30.5	0.5
0°-30°	1439.4	24.5
0°-40°	2070.5	35.2
0°-60°	3055.1	52.0
0°-90°	3509.5	59.7
90°-120°	1159.6	19.7
90°-150°	2084.6	35.5
90°-180°	2369.0	40.3
0°-180°	5878.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2646	2646	2646	2646	2646	
5°	3129	3030	2652	2144	1990	286
15°	1893	2558	2532	1361	1130	534
25°	942	1408	2258	957	859	445
35°	680	859	1852	751	667	424
45°	484	605	1338	562	494	376
55°	322	416	831	390	308	289
65°	196	247	458	235	203	192
75°	86	104	207	108	89	92
85°	24	26	43	28	26	25
90°	18	16	1	16	18	11
95°	74	378	22	378	74	120
105°	811	512	74	512	811	809
115°	986	392	131	392	986	962
125°	778	366	182	366	778	704
135°	630	361	213	361	630	489
145°	493	356	243	356	493	313
155°	409	345	276	345	409	190
165°	356	330	302	330	356	102
175°	321	317	314	317	321	31
180°	315	315	315	315	315	



TEST NUMBER: P831890

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7
2.5°	2932.0	2922.8	2913.6	2910.9	2908.2	2899.5	2890.8	2871.3	2851.8	2831.7	2811.6
5°	3129.4	3130.5	3131.6	3128.9	3126.2	3114.8	3103.4	3079.6	3055.7	3029.7	3003.6
7.5°	3068.7	3086.1	3103.4	3106.7	3109.9	3118.6	3127.3	3121.9	3116.4	3106.7	3096.9
10°	2802.9	2801.9	2800.8	2820.3	2839.8	2897.9	2955.9	2985.7	3015.6	3042.1	3068.7
12.5°	2369.1	2370.7	2372.3	2436.3	2500.3	2555.1	2609.9	2685.8	2761.7	2843.6	2925.5
15°	1892.9	1919.4	1946.0	2003.0	2059.9	2142.3	2224.8	2326.7	2428.7	2558.3	2688.0
17.5°	1554.4	1565.8	1577.2	1632.0	1686.8	1764.9	1843.0	1958.5	2074.0	2241.1	2408.1
20°	1281.1	1291.4	1301.7	1341.3	1380.9	1455.7	1530.6	1640.7	1750.8	1916.2	2081.6
22.5°	1069.5	1089.6	1109.7	1136.3	1162.8	1217.1	1271.3	1383.6	1495.8	1646.6	1797.4
25°	941.5	950.8	960.0	982.8	1005.5	1057.6	1109.7	1184.0	1258.3	1408.5	1558.8
27.5°	854.8	857.5	860.2	877.0	893.8	927.4	961.1	1030.0	1098.8	1222.5	1346.2
30°	783.2	788.1	792.9	806.0	819.0	843.4	867.8	916.6	965.4	1076.1	1186.7
32.5°	727.9	730.6	733.3	744.1	755.0	772.9	790.8	829.3	867.8	952.4	1037.0
35°	680.1	680.7	681.2	689.3	697.5	714.8	732.2	764.2	796.2	858.6	920.9
37.5°	625.9	629.7	633.5	639.4	645.4	660.6	675.8	701.8	727.9	779.4	830.9
40°	580.3	583.6	586.8	593.9	600.9	612.9	624.8	648.7	672.5	717.0	761.5
42.5°	534.8	536.9	539.1	546.2	553.2	567.9	582.5	601.5	620.5	657.3	694.2
45°	483.8	489.2	494.6	502.2	509.8	522.3	534.8	554.3	573.8	605.3	636.7
47.5°	441.5	444.2	446.9	453.4	459.9	475.1	490.3	507.7	525.0	554.3	583.6
50°	399.2	400.3	401.4	407.3	413.3	426.8	440.4	460.5	480.5	507.7	534.8
52.5°	359.0	361.8	364.5	370.4	376.4	385.6	394.8	415.5	436.1	462.6	489.2
55°	322.2	323.8	325.4	329.8	334.1	344.9	355.8	373.7	391.6	416.0	440.4
57.5°	287.5	289.6	291.8	295.0	298.3	308.1	317.8	333.6	349.3	373.7	398.1
60°	251.7	254.4	257.1	260.9	264.7	272.3	279.9	294.0	308.1	329.8	351.5
62.5°	225.6	226.2	226.7	230.0	233.2	238.6	244.1	255.5	266.8	288.5	310.2
65°	196.3	198.0	199.6	201.2	202.8	207.2	211.5	221.3	231.0	247.3	263.6
67.5°	166.0	167.6	169.2	171.9	174.6	178.4	182.2	188.7	195.3	210.4	225.6
70°	129.1	129.1	129.1	133.4	137.8	144.3	150.8	155.7	160.5	173.0	185.5
72.5°	105.2	105.8	106.3	106.8	107.4	111.2	115.0	123.1	131.3	138.8	146.4
75°	85.7	86.2	86.8	87.3	87.9	88.9	90.0	92.7	95.5	104.1	112.8
77.5°	68.3	68.9	69.4	70.0	70.5	71.6	72.7	73.8	74.8	78.1	81.4
80°	52.1	52.6	53.2	53.7	54.2	54.8	55.3	56.4	57.5	59.1	60.7
82.5°	38.0	38.0	38.0	38.0	38.0	39.1	40.1	40.1	40.1	41.2	42.3
85°	23.9	23.9	23.9	24.4	24.9	24.9	24.9	25.5	26.0	26.0	26.0
87.5°	10.8	10.3	9.8	10.3	10.8	10.8	10.8	11.4	11.9	11.9	11.9
90°	18.5	19.1	18.5	17.8	18.5	17.2	16.6	15.9	15.3	15.9	14.0
92.5°	33.8	35.1	34.4	37.0	38.2	42.7	49.1	63.1	88.6	118.6	131.3
95°	73.9	76.5	81.0	86.7	98.8	121.7	155.5	229.5	306.6	378.0	336.6
97.5°	151.7	158.7	174.0	198.2	240.9	313.6	397.7	527.1	601.1	581.3	434.1
100°	399.7	399.0	423.9	470.4	534.8	625.3	699.9	751.5	729.2	603.6	407.9
102.5°	633.0	651.4	671.2	705.6	752.2	801.2	836.9	826.1	735.6	562.2	369.7
105°	810.8	814.0	834.4	858.6	887.9	904.5	892.4	828.6	695.4	512.5	339.7
107.5°	926.8	933.8	942.1	953.6	957.4	940.2	890.5	790.4	638.1	468.5	318.1
110°	993.1	994.4	995.6	990.5	972.7	928.1	847.8	730.5	584.5	432.2	306.6



TEST NUMBER: P831890

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1006.5	1005.8	999.5	981.0	944.7	884.1	791.7	671.2	538.0	407.9	300.2
115°	986.1	982.9	970.1	942.1	894.3	824.8	731.1	620.2	502.3	392.0	299.6
117.5°	941.5	937.0	917.9	886.6	836.9	764.9	678.8	580.7	478.7	381.2	300.2
120°	882.8	879.0	863.7	828.0	777.6	713.3	636.8	550.7	460.9	374.2	302.8
122.5°	828.0	822.9	805.7	774.5	731.1	672.5	603.0	527.1	446.2	369.7	307.2
125°	777.6	773.2	757.3	729.2	688.4	637.4	576.2	506.7	434.1	365.9	311.7
127.5°	734.3	730.5	715.8	691.6	654.6	607.5	551.4	488.3	422.6	364.0	316.8
130°	698.6	693.5	680.1	657.2	623.4	580.0	528.4	471.1	413.7	362.1	321.9
132.5°	663.6	660.4	648.9	625.9	594.7	553.9	506.7	455.1	405.4	361.4	325.7
135°	630.4	625.9	614.5	595.3	564.1	527.8	486.3	441.1	398.4	360.8	329.5
137.5°	595.3	591.5	582.0	562.2	535.4	502.9	466.0	427.7	392.0	359.5	332.1
140°	558.4	559.0	548.8	531.0	506.7	479.3	448.7	416.2	386.3	358.9	334.6
142.5°	524.0	524.6	515.7	500.4	480.6	457.7	432.2	405.4	381.2	357.6	336.6
145°	492.7	491.4	486.3	473.0	457.0	438.5	418.1	397.1	376.7	356.3	337.2
147.5°	466.0	465.3	460.2	450.7	437.9	424.5	407.3	390.1	372.3	354.4	337.2
150°	443.0	443.0	439.2	432.2	422.6	410.5	397.1	382.4	367.8	351.9	337.2
152.5°	423.9	423.9	422.0	415.6	408.6	399.0	387.5	375.4	362.7	348.7	335.3
155°	408.6	407.9	406.7	401.6	395.8	388.2	378.6	368.4	357.6	344.8	334.0
157.5°	393.9	393.9	392.6	388.8	383.7	377.4	369.7	360.8	351.9	341.7	332.1
160°	379.9	380.5	380.5	376.7	372.3	367.8	361.4	354.4	346.1	337.8	330.8
162.5°	367.2	367.8	367.8	364.6	362.1	358.2	352.5	346.8	340.4	334.0	328.3
165°	356.3	356.3	357.0	354.4	351.9	348.7	344.2	340.4	335.3	330.2	325.7
167.5°	345.5	345.5	346.1	344.2	342.9	340.4	337.8	334.6	330.2	326.4	323.2
170°	335.9	335.9	336.6	335.3	334.6	333.4	330.8	328.9	325.7	322.5	320.6
172.5°	327.0	327.6	328.9	327.6	327.6	327.0	325.1	323.8	321.3	319.3	318.7
175°	320.6	321.3	321.9	321.3	321.3	321.3	320.0	319.3	318.1	316.8	316.8
177.5°	316.2	316.2	317.4	316.8	317.4	317.4	316.8	316.2	315.5	314.9	315.5
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P831890

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7
2.5°	2808.9	2806.2	2780.2	2754.1	2728.6	2703.2	2684.2	2665.2	2633.2	2601.2	2581.1
5°	2983.0	2962.4	2921.2	2880.0	2818.1	2756.3	2704.2	2652.2	2586.0	2519.8	2464.5
7.5°	3080.1	3063.3	3013.4	2963.5	2881.6	2799.7	2718.3	2637.0	2539.4	2441.7	2358.2
10°	3082.8	3096.9	3055.7	3014.5	2922.3	2830.1	2719.4	2608.8	2477.5	2346.3	2238.3
12.5°	2986.3	3047.0	3038.3	3029.7	2935.8	2842.0	2707.5	2573.0	2411.9	2250.8	2115.8
15°	2805.7	2923.4	2958.1	2992.8	2915.2	2837.7	2684.7	2531.8	2342.5	2153.2	1998.1
17.5°	2573.0	2737.9	2829.5	2921.2	2864.8	2808.4	2640.8	2473.2	2260.0	2046.9	1878.2
20°	2297.5	2513.3	2657.0	2800.8	2780.2	2759.6	2586.5	2413.5	2183.6	1953.6	1770.8
22.5°	2025.2	2253.0	2451.5	2650.0	2671.2	2692.3	2517.7	2343.0	2091.4	1839.7	1653.7
25°	1790.3	2021.9	2258.4	2494.9	2542.6	2590.3	2424.4	2258.4	1997.5	1736.7	1551.7
27.5°	1566.4	1786.6	2046.9	2307.2	2394.0	2480.8	2328.9	2177.1	1905.3	1633.6	1449.2
30°	1383.6	1580.5	1846.2	2112.0	2232.9	2353.9	2214.5	2075.1	1805.5	1536.0	1355.4
32.5°	1213.3	1389.5	1656.4	1923.2	2063.7	2204.2	2083.8	1963.4	1704.1	1444.9	1266.4
35°	1078.8	1236.6	1485.5	1734.5	1891.8	2049.1	1950.3	1851.6	1598.4	1345.1	1176.4
37.5°	963.2	1095.6	1329.3	1563.1	1730.1	1897.2	1814.8	1732.3	1494.2	1256.1	1096.7
40°	867.8	974.1	1191.6	1409.1	1572.9	1736.7	1666.1	1595.6	1382.5	1169.3	1020.2
42.5°	785.9	877.5	1072.8	1268.1	1418.3	1568.5	1521.9	1475.2	1282.2	1089.1	950.8
45°	713.8	790.8	962.7	1134.6	1272.9	1411.2	1374.4	1337.5	1171.0	1004.5	877.5
47.5°	649.8	715.9	869.4	1022.9	1147.1	1271.3	1237.1	1203.0	1065.2	927.4	811.9
50°	591.2	647.6	775.6	903.6	1015.3	1127.0	1098.8	1070.6	956.7	842.8	743.0
52.5°	535.9	582.5	697.5	812.5	902.5	992.5	970.8	949.1	861.3	773.4	682.8
55°	483.2	526.1	623.2	720.3	797.3	874.3	852.6	830.9	762.6	694.2	614.5
57.5°	435.5	472.9	551.6	630.2	691.5	752.8	742.5	732.2	675.2	618.3	552.7
60°	385.1	418.7	486.5	554.3	603.7	653.0	641.1	629.1	588.5	547.8	491.4
62.5°	340.1	369.9	424.1	478.4	518.5	558.6	550.0	541.3	510.4	479.5	432.8
65°	292.9	322.2	366.1	410.0	441.5	472.9	465.3	457.8	434.4	411.1	373.7
67.5°	250.0	274.4	312.4	350.4	371.5	392.7	388.3	384.0	366.1	348.2	318.9
70°	206.6	227.8	259.3	290.7	305.4	320.0	321.6	323.2	307.0	290.7	269.0
72.5°	163.3	180.1	209.4	238.6	250.0	261.4	260.9	260.3	250.6	240.8	221.3
75°	125.3	137.8	160.5	183.3	193.1	202.8	205.0	207.2	198.0	188.7	177.9
77.5°	90.0	98.7	116.1	133.4	144.3	155.1	156.2	157.3	152.9	148.6	138.3
80°	63.5	66.2	77.0	87.9	99.3	110.6	112.3	113.9	109.6	105.2	98.7
82.5°	43.9	45.6	49.4	53.2	62.4	71.6	73.8	75.9	73.8	71.6	64.5
85°	26.6	27.1	28.7	30.4	34.7	39.1	41.2	43.4	42.3	41.2	37.4
87.5°	11.9	11.9	12.5	13.0	14.1	15.2	17.9	20.6	19.0	17.4	15.7
90°	12.1	10.2	8.3	7.0	5.7	3.8	2.5	1.3	2.5	3.8	5.7
92.5°	98.2	64.4	44.0	32.5	26.1	20.4	14.0	9.6	14.0	20.4	26.1
95°	232.0	137.0	82.9	58.0	41.4	30.6	23.6	21.7	23.6	30.6	41.4
97.5°	258.2	147.9	94.3	66.9	50.4	40.8	35.1	34.4	35.1	40.8	50.4
100°	240.3	146.0	101.3	76.5	61.2	52.3	47.8	47.2	47.8	52.3	61.2
102.5°	225.0	148.5	109.6	87.3	73.9	65.7	61.8	60.6	61.8	65.7	73.9
105°	219.3	153.6	119.2	99.4	87.3	79.7	75.9	73.9	75.9	79.7	87.3
107.5°	218.0	161.9	131.3	112.8	101.3	93.7	89.9	88.0	89.9	93.7	101.3
110°	221.2	172.7	144.1	126.2	115.4	108.4	105.2	103.3	105.2	108.4	115.4





TEST NUMBER: P831890

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	227.6	183.6	157.4	140.2	129.4	122.4	119.2	117.3	119.2	122.4	129.4
115°	234.6	195.7	171.5	154.3	143.4	137.0	133.2	130.7	133.2	137.0	143.4
117.5°	243.5	208.4	184.2	168.3	156.2	150.4	147.2	144.1	147.2	150.4	156.2
120°	253.7	220.5	197.6	181.7	169.6	163.2	160.0	158.1	160.0	163.2	169.6
122.5°	263.3	233.3	211.0	193.8	182.3	175.3	172.1	170.2	172.1	175.3	182.3
125°	273.5	245.4	223.1	205.9	193.8	186.8	182.9	181.7	182.9	186.8	193.8
127.5°	281.7	256.2	234.6	217.4	204.0	197.0	192.5	190.6	192.5	197.0	204.0
130°	290.0	265.8	244.8	227.6	214.2	206.5	200.8	198.9	200.8	206.5	214.2
132.5°	297.7	274.1	253.7	237.1	223.7	214.2	207.8	205.2	207.8	214.2	223.7
135°	304.0	282.4	262.6	245.4	232.0	222.5	215.4	212.9	215.4	222.5	232.0
137.5°	309.1	288.1	269.0	253.1	239.7	229.5	222.5	219.9	222.5	229.5	239.7
140°	313.0	293.8	275.4	259.4	246.7	236.5	230.1	226.9	230.1	236.5	246.7
142.5°	316.8	298.3	280.5	265.8	253.1	244.1	237.1	234.6	237.1	244.1	253.1
145°	319.3	302.1	285.6	270.9	260.1	250.5	244.8	242.9	244.8	250.5	260.1
147.5°	321.3	305.3	290.0	277.3	266.4	258.2	252.4	251.1	252.4	258.2	266.4
150°	321.9	308.5	293.8	282.4	273.5	265.2	260.1	259.4	260.1	265.2	273.5
152.5°	323.2	310.4	298.3	287.5	279.8	272.8	267.7	267.7	267.7	272.8	279.8
155°	323.2	313.0	302.1	293.2	286.2	279.8	276.0	276.0	276.0	279.8	286.2
157.5°	323.8	314.2	305.3	298.3	291.9	286.2	283.0	282.4	283.0	286.2	291.9
160°	323.8	316.2	308.5	302.1	297.7	292.6	290.0	290.0	290.0	292.6	297.7
162.5°	323.2	316.8	310.4	305.3	301.5	297.7	295.8	295.8	295.8	297.7	301.5
165°	321.9	317.4	312.3	307.9	305.3	302.1	300.9	301.5	300.9	302.1	305.3
167.5°	321.3	317.4	313.6	310.4	308.5	306.0	305.3	306.0	305.3	306.0	308.5
170°	319.3	316.8	313.6	312.3	311.1	309.1	308.5	309.8	308.5	309.1	311.1
172.5°	318.7	316.8	314.2	313.6	313.0	311.7	311.7	312.3	311.7	311.7	313.0
175°	317.4	316.2	314.9	314.2	314.2	313.0	313.6	314.2	313.6	313.0	314.2
177.5°	316.8	315.5	314.9	314.9	314.9	314.2	314.9	315.5	314.9	314.2	314.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P831890

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7	2645.7
2.5°	2561.1	2530.1	2499.2	2477.0	2454.7	2427.1	2399.4	2398.3	2397.3	2376.6	2356.0
5°	2409.2	2355.5	2301.8	2249.2	2196.6	2144.0	2091.4	2079.4	2067.5	2049.6	2031.7
7.5°	2274.7	2189.0	2103.3	2036.0	1968.8	1916.2	1863.6	1827.8	1792.0	1764.3	1736.7
10°	2130.4	2024.1	1917.8	1836.5	1755.1	1698.1	1641.2	1600.0	1558.8	1539.2	1519.7
12.5°	1980.7	1865.2	1749.7	1669.9	1590.2	1521.9	1453.5	1416.1	1378.7	1351.6	1324.5
15°	1843.0	1718.8	1594.6	1509.9	1425.3	1361.3	1297.3	1259.9	1222.5	1195.4	1168.3
17.5°	1709.5	1584.3	1459.0	1373.3	1287.6	1229.5	1171.5	1135.2	1098.8	1082.0	1065.2
20°	1588.0	1461.7	1335.3	1254.5	1173.7	1116.7	1059.8	1040.3	1020.7	1005.0	989.3
22.5°	1467.6	1346.2	1224.7	1147.1	1069.5	1028.3	987.1	971.4	955.6	943.7	931.8
25°	1366.8	1245.8	1124.9	1057.1	989.3	957.3	925.3	915.0	904.7	892.7	880.8
27.5°	1264.8	1149.8	1034.8	980.6	926.4	900.3	874.3	861.3	848.3	838.5	828.7
30°	1174.8	1068.5	962.2	917.1	872.1	849.3	826.6	812.5	798.4	789.1	779.9
32.5°	1088.0	993.6	899.2	860.7	822.2	800.0	777.8	764.2	750.6	739.8	728.9
35°	1007.7	925.8	843.9	808.7	773.4	751.2	728.9	715.4	701.8	691.0	680.1
37.5°	937.2	862.9	788.6	755.5	722.4	702.9	683.4	669.3	655.2	643.8	632.4
40°	871.0	805.4	739.8	707.8	675.8	654.6	633.5	621.0	608.5	598.2	587.9
42.5°	812.5	752.3	692.1	660.6	629.1	609.1	589.0	574.4	559.7	553.8	547.8
45°	750.6	697.5	644.3	614.0	583.6	562.4	541.3	528.8	516.3	510.9	505.5
47.5°	696.4	647.0	597.7	567.9	538.0	519.0	500.1	490.3	480.5	472.9	465.3
50°	643.2	595.5	547.8	519.0	490.3	474.0	457.8	445.8	433.9	428.5	423.0
52.5°	592.3	548.9	505.5	476.2	446.9	431.2	415.5	405.1	394.8	383.5	372.1
55°	534.8	496.8	458.8	432.8	406.8	390.5	374.2	362.3	350.4	338.4	326.5
57.5°	487.0	449.6	412.2	388.9	365.6	349.8	334.1	321.1	308.1	298.3	288.5
60°	435.0	402.4	369.9	347.1	324.3	309.1	294.0	281.5	269.0	264.1	259.3
62.5°	386.2	355.8	325.4	305.4	285.3	270.6	256.0	247.9	239.7	236.5	233.2
65°	336.3	310.2	284.2	265.8	247.3	234.8	222.4	218.6	214.8	212.1	209.4
67.5°	289.6	267.4	245.1	228.9	212.6	203.9	195.3	190.9	186.6	183.3	180.1
70°	247.3	227.8	208.3	194.2	180.1	171.9	163.8	160.0	156.2	150.2	144.3
72.5°	201.8	186.6	171.4	160.5	149.7	142.6	135.6	128.0	120.4	115.0	109.6
75°	167.0	151.9	136.7	126.4	116.1	107.9	99.8	97.1	94.4	92.7	91.1
77.5°	128.0	115.0	102.0	93.8	85.7	81.9	78.1	76.5	74.8	74.3	73.8
80°	92.2	81.4	70.5	66.2	61.8	60.7	59.7	58.6	57.5	56.9	56.4
82.5°	57.5	52.1	46.6	45.6	44.5	43.9	43.4	42.8	42.3	41.8	41.2
85°	33.6	31.5	29.3	28.7	28.2	27.7	27.1	27.1	27.1	27.1	27.1
87.5°	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1	14.1	13.6	13.0
90°	7.0	8.3	10.2	12.1	14.0	15.9	15.3	15.9	16.6	17.2	18.5
92.5°	32.5	44.0	64.4	98.2	131.3	118.6	88.6	63.1	49.1	42.7	38.2
95°	58.0	82.9	137.0	232.0	336.6	378.0	306.6	229.5	155.5	121.7	98.8
97.5°	66.9	94.3	147.9	258.2	434.1	581.3	601.1	527.1	397.7	313.6	240.9
100°	76.5	101.3	146.0	240.3	407.9	603.6	729.2	751.5	699.9	625.3	534.8
102.5°	87.3	109.6	148.5	225.0	369.7	562.2	735.6	826.1	836.9	801.2	752.2
105°	99.4	119.2	153.6	219.3	339.7	512.5	695.4	828.6	892.4	904.5	887.9
107.5°	112.8	131.3	161.9	218.0	318.1	468.5	638.1	790.4	890.5	940.2	957.4
110°	126.2	144.1	172.7	221.2	306.6	432.2	584.5	730.5	847.8	928.1	972.7



TEST NUMBER: P831890

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	140.2	157.4	183.6	227.6	300.2	407.9	538.0	671.2	791.7	884.1	944.7
115°	154.3	171.5	195.7	234.6	299.6	392.0	502.3	620.2	731.1	824.8	894.3
117.5°	168.3	184.2	208.4	243.5	300.2	381.2	478.7	580.7	678.8	764.9	836.9
120°	181.7	197.6	220.5	253.7	302.8	374.2	460.9	550.7	636.8	713.3	777.6
122.5°	193.8	211.0	233.3	263.3	307.2	369.7	446.2	527.1	603.0	672.5	731.1
125°	205.9	223.1	245.4	273.5	311.7	365.9	434.1	506.7	576.2	637.4	688.4
127.5°	217.4	234.6	256.2	281.7	316.8	364.0	422.6	488.3	551.4	607.5	654.6
130°	227.6	244.8	265.8	290.0	321.9	362.1	413.7	471.1	528.4	580.0	623.4
132.5°	237.1	253.7	274.1	297.7	325.7	361.4	405.4	455.1	506.7	553.9	594.7
135°	245.4	262.6	282.4	304.0	329.5	360.8	398.4	441.1	486.3	527.8	564.1
137.5°	253.1	269.0	288.1	309.1	332.1	359.5	392.0	427.7	466.0	502.9	535.4
140°	259.4	275.4	293.8	313.0	334.6	358.9	386.3	416.2	448.7	479.3	506.7
142.5°	265.8	280.5	298.3	316.8	336.6	357.6	381.2	405.4	432.2	457.7	480.6
145°	270.9	285.6	302.1	319.3	337.2	356.3	376.7	397.1	418.1	438.5	457.0
147.5°	277.3	290.0	305.3	321.3	337.2	354.4	372.3	390.1	407.3	424.5	437.9
150°	282.4	293.8	308.5	321.9	337.2	351.9	367.8	382.4	397.1	410.5	422.6
152.5°	287.5	298.3	310.4	323.2	335.3	348.7	362.7	375.4	387.5	399.0	408.6
155°	293.2	302.1	313.0	323.2	334.0	344.8	357.6	368.4	378.6	388.2	395.8
157.5°	298.3	305.3	314.2	323.8	332.1	341.7	351.9	360.8	369.7	377.4	383.7
160°	302.1	308.5	316.2	323.8	330.8	337.8	346.1	354.4	361.4	367.8	372.3
162.5°	305.3	310.4	316.8	323.2	328.3	334.0	340.4	346.8	352.5	358.2	362.1
165°	307.9	312.3	317.4	321.9	325.7	330.2	335.3	340.4	344.2	348.7	351.9
167.5°	310.4	313.6	317.4	321.3	323.2	326.4	330.2	334.6	337.8	340.4	342.9
170°	312.3	313.6	316.8	319.3	320.6	322.5	325.7	328.9	330.8	333.4	334.6
172.5°	313.6	314.2	316.8	318.7	318.7	319.3	321.3	323.8	325.1	327.0	327.6
175°	314.2	314.9	316.2	317.4	316.8	316.8	318.1	319.3	320.0	321.3	321.3
177.5°	314.9	314.9	315.5	316.8	315.5	314.9	315.5	316.2	316.8	317.4	317.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P831890

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2645.7	2645.7	2645.7	2645.7
2.5°	2350.6	2345.2	2343.0	2340.9
5°	2014.9	1998.1	1994.3	1990.5
7.5°	1729.6	1722.6	1699.2	1675.9
10°	1498.0	1476.3	1466.6	1456.8
12.5°	1304.4	1284.3	1281.1	1277.8
15°	1154.2	1140.1	1135.2	1130.3
17.5°	1055.4	1045.7	1039.7	1033.7
20°	982.2	975.2	970.8	966.5
22.5°	926.4	920.9	917.7	914.4
25°	872.7	864.5	861.8	859.1
27.5°	821.7	814.6	811.9	809.2
30°	774.0	768.0	764.2	760.4
32.5°	721.9	714.8	712.7	710.5
35°	675.8	671.4	669.3	667.1
37.5°	627.0	621.6	618.3	615.0
40°	585.2	582.5	580.9	579.2
42.5°	542.9	538.0	537.5	536.9
45°	500.6	495.7	494.6	493.6
47.5°	461.0	456.7	456.1	455.6
50°	417.1	411.1	406.8	402.4
52.5°	366.6	361.2	357.4	353.6
55°	320.5	314.6	311.3	308.1
57.5°	285.8	283.1	281.5	279.9
60°	257.6	256.0	254.9	253.8
62.5°	231.6	230.0	230.0	230.0
65°	207.7	206.1	204.5	202.8
67.5°	176.8	173.6	173.0	172.5
70°	139.4	134.5	134.0	133.4
72.5°	109.0	108.5	107.4	106.3
75°	90.0	88.9	88.9	88.9
77.5°	72.7	71.6	71.6	71.6
80°	55.9	55.3	55.9	56.4
82.5°	41.2	41.2	40.7	40.1
85°	26.6	26.0	26.0	26.0
87.5°	13.0	13.0	13.0	13.0
90°	17.8	18.5	19.1	18.5
92.5°	37.0	34.4	35.1	33.8
95°	86.7	81.0	76.5	73.9
97.5°	198.2	174.0	158.7	151.7
100°	470.4	423.9	399.0	399.7
102.5°	705.6	671.2	651.4	633.0
105°	858.6	834.4	814.0	810.8
107.5°	953.6	942.1	933.8	926.8
110°	990.5	995.6	994.4	993.1



TEST NUMBER: P831890

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	981.0	999.5	1005.8	1006.5
115°	942.1	970.1	982.9	986.1
117.5°	886.6	917.9	937.0	941.5
120°	828.0	863.7	879.0	882.8
122.5°	774.5	805.7	822.9	828.0
125°	729.2	757.3	773.2	777.6
127.5°	691.6	715.8	730.5	734.3
130°	657.2	680.1	693.5	698.6
132.5°	625.9	648.9	660.4	663.6
135°	595.3	614.5	625.9	630.4
137.5°	562.2	582.0	591.5	595.3
140°	531.0	548.8	559.0	558.4
142.5°	500.4	515.7	524.6	524.0
145°	473.0	486.3	491.4	492.7
147.5°	450.7	460.2	465.3	466.0
150°	432.2	439.2	443.0	443.0
152.5°	415.6	422.0	423.9	423.9
155°	401.6	406.7	407.9	408.6
157.5°	388.8	392.6	393.9	393.9
160°	376.7	380.5	380.5	379.9
162.5°	364.6	367.8	367.8	367.2
165°	354.4	357.0	356.3	356.3
167.5°	344.2	346.1	345.5	345.5
170°	335.3	336.6	335.9	335.9
172.5°	327.6	328.9	327.6	327.0
175°	321.3	321.9	321.3	320.6
177.5°	316.8	317.4	316.2	316.2
180°	314.9	314.9	314.9	314.9



TEST NUMBER: P831890

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.25	14.14	14.13	15.03	16.16	17.91	18.80	18.80	19.69	20.83
	3H	14.48	15.27	15.37	16.17	17.33	19.42	20.21	20.31	21.11	22.27
	4H	14.86	15.61	15.77	16.52	17.68	19.91	20.66	20.82	21.57	22.73
	6H	15.14	15.83	16.07	16.75	17.93	20.22	20.91	21.15	21.83	23.01
	8H	15.23	15.89	16.16	16.82	18.00	20.31	20.96	21.23	21.89	23.07
	12H	15.29	15.91	16.22	16.83	18.04	20.34	20.96	21.27	21.89	23.09
4H	2H	13.98	14.73	14.89	15.64	16.80	17.92	18.66	18.83	19.57	20.74
	3H	15.35	15.97	16.28	16.91	18.10	19.58	20.20	20.50	21.14	22.32
	4H	15.81	16.38	16.75	17.31	18.52	20.19	20.75	21.12	21.69	22.89
	6H	16.18	16.67	17.13	17.63	18.83	20.63	21.11	21.58	22.07	23.28
	8H	16.31	16.76	17.26	17.71	18.93	20.76	21.21	21.71	22.17	23.39
	12H	16.39	16.79	17.36	17.77	18.99	20.83	21.23	21.79	22.20	23.43
8H	4H	16.13	16.58	17.08	17.54	18.76	20.16	20.61	21.11	21.56	22.78
	6H	16.60	16.97	17.57	17.96	19.18	20.66	21.03	21.63	22.03	23.24
	8H	16.79	17.12	17.77	18.10	19.34	20.84	21.17	21.83	22.16	23.39
	12H	16.93	17.22	17.92	18.20	19.48	20.96	21.25	21.95	22.23	23.51
12H	4H	16.14	16.55	17.11	17.52	18.75	20.11	20.52	21.08	21.49	22.71
	6H	16.65	16.98	17.64	17.97	19.20	20.63	20.96	21.62	21.95	23.18
	8H	16.87	17.16	17.86	18.14	19.43	20.83	21.12	21.81	22.09	23.38