

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331975-935

Luminaire Tested: **S123DIP-S775D805U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331975-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D805U935-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5312.4 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	46	44	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10014	10014	10014	10014
5°	11943	10057	8912	10057
10°	14948	10006	8050	10006
15°	18333	9926	7494	9926
20°	21841	9800	7135	9800
25°	23192	9647	7056	9647
30°	19877	9536	7093	9536
35°	13825	9376	7167	9376
40°	10413	9190	7144	9190
45°	8645	8914	7054	8914
50°	7743	8348	6990	8348
55°	7240	7739	6902	7739
60°	6794	7102	6833	7102
65°	6383	6477	6612	6477
70°	5986	5759	6297	5759
75°	5361	5041	5772	5041
80°	4699	4135	4971	4135
85°	3680	3013	3335	3013



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.6	1.7
10°-20°	293.9	5.5
20°-30°	493.2	9.3
30°-40°	558.5	10.5
40°-50°	500.8	9.4
50°-60°	404.1	7.6
60°-70°	281.6	5.3
70°-80°	148.0	2.8
80°-90°	38.8	0.7
90°-100°	185.1	3.5
100°-110°	524.0	9.9
110°-120°	515.5	9.7
120°-130°	411.2	7.7
130°-140°	324.2	6.1
140°-150°	242.0	4.6
150°-160°	168.6	3.2
160°-170°	99.1	1.9
170°-180°	32.2	0.6
0°-30°	878.7	16.5
0°-40°	1437.2	27.1
0°-60°	2342.1	44.1
0°-90°	2810.5	52.9
90°-120°	1224.6	23.1
90°-150°	2201.9	41.4
90°-180°	2502.0	47.1
0°-180°	5312.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	1105	931	825	931	1105	115
15°	1645	891	672	891	1645	475
25°	1953	812	594	812	1953	856
35°	1052	714	545	714	1052	684
45°	568	586	463	586	568	449
55°	386	412	368	412	386	346
65°	251	254	260	254	251	250
75°	129	121	139	121	129	138
85°	30	24	27	24	30	36
90°	20	1	20	1	20	12
95°	78	23	78	23	78	141
105°	856	78	856	78	856	845
115°	1041	138	1041	138	1041	1012
125°	821	192	821	192	821	744
135°	666	225	666	225	666	516
145°	520	256	520	256	520	331
155°	431	291	431	291	431	201
165°	376	318	376	318	376	108
175°	339	332	339	332	339	33
180°	332	332	332	332	332	



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	987.3	986.6	984.8	986.3	983.3	979.4	979.0	975.4	964.9	964.2	961.4
5°	1105.3	1101.6	1101.2	1100.7	1094.4	1085.9	1069.6	1068.2	1046.6	1035.8	1022.8
7.5°	1257.9	1259.8	1253.3	1247.5	1228.2	1215.5	1198.1	1175.8	1149.3	1122.3	1104.3
10°	1367.6	1382.4	1364.0	1351.3	1339.6	1317.5	1291.8	1259.8	1227.9	1190.4	1162.0
12.5°	1485.1	1492.5	1488.8	1476.9	1458.6	1425.0	1379.5	1344.2	1314.7	1252.4	1227.3
15°	1645.2	1672.8	1655.2	1614.5	1615.5	1583.5	1524.0	1458.6	1423.9	1369.3	1295.0
17.5°	1815.8	1819.2	1811.7	1778.0	1755.4	1711.4	1656.5	1593.9	1523.5	1457.5	1378.6
20°	1906.7	1903.9	1888.2	1870.6	1831.9	1797.6	1737.7	1667.8	1577.6	1512.7	1426.6
22.5°	1957.1	1952.7	1945.2	1930.4	1898.2	1861.4	1807.6	1731.2	1645.5	1556.0	1456.6
25°	1952.7	1958.5	1959.4	1955.3	1944.1	1922.0	1879.6	1818.8	1733.1	1618.2	1514.5
27.5°	1776.0	1784.3	1808.4	1829.7	1853.6	1877.9	1874.7	1844.4	1781.1	1681.9	1555.1
30°	1599.2	1581.2	1625.8	1682.2	1720.5	1788.1	1826.0	1828.2	1792.6	1707.4	1583.9
32.5°	1354.0	1373.9	1393.6	1462.9	1546.7	1622.6	1698.0	1758.7	1765.6	1708.9	1600.9
35°	1052.1	1076.9	1112.9	1148.9	1239.2	1316.6	1449.1	1564.5	1656.5	1668.7	1602.4
37.5°	847.7	860.1	882.9	918.9	977.9	1069.9	1172.4	1318.3	1451.5	1550.6	1554.9
40°	741.1	744.7	770.3	797.8	845.6	921.4	1013.7	1142.6	1302.2	1440.6	1498.3
42.5°	661.0	668.9	679.8	706.2	744.2	801.2	887.2	993.7	1140.0	1299.2	1412.1
45°	567.9	577.0	583.8	601.3	628.4	666.7	726.6	824.0	935.3	1099.8	1251.7
47.5°	506.4	507.2	512.2	525.5	543.9	572.7	615.0	677.6	779.8	913.2	1069.2
50°	462.4	469.7	471.5	481.8	496.3	517.5	552.6	605.8	689.7	806.8	950.2
52.5°	431.4	433.6	438.7	446.2	458.7	475.3	505.8	547.4	613.2	713.1	844.9
55°	385.8	385.8	390.8	396.7	403.9	418.7	439.0	469.7	519.7	597.3	706.4
57.5°	343.6	345.9	349.4	351.2	357.3	367.2	384.1	407.4	444.7	504.4	591.1
60°	315.6	319.6	319.2	322.7	328.1	335.8	350.3	369.2	402.5	450.3	523.3
62.5°	291.0	290.8	290.7	295.0	300.4	307.7	317.0	333.5	361.8	404.2	466.3
65°	250.6	249.7	252.9	255.5	257.4	262.8	270.0	284.4	303.3	334.9	383.1
67.5°	214.7	212.2	213.9	214.7	217.8	222.1	228.8	237.7	252.8	278.1	314.4
70°	190.2	188.0	187.5	188.4	191.1	194.2	199.2	207.8	221.8	242.0	268.6
72.5°	165.0	163.4	163.3	165.3	166.6	168.7	172.2	180.0	191.1	206.4	231.2
75°	128.9	128.9	128.9	129.3	130.7	132.5	135.3	139.3	147.8	158.7	175.3
77.5°	96.6	96.5	96.0	95.9	97.9	98.8	99.4	103.1	107.9	115.2	127.3
80°	75.8	73.4	74.4	75.8	76.6	77.1	78.4	79.3	83.4	87.5	96.0
82.5°	56.2	54.3	54.5	56.7	56.8	57.3	58.6	59.8	61.4	65.1	69.7
85°	29.8	29.8	30.2	30.2	30.7	30.2	31.5	32.0	32.0	34.3	36.9
87.5°	14.7	14.1	14.4	14.6	14.4	14.5	14.6	14.9	15.2	15.6	15.6
90°	19.5	20.2	19.5	18.9	19.5	18.2	17.5	16.8	16.2	16.8	14.8
92.5°	32.5	33.7	33.0	35.0	36.2	39.7	44.9	56.7	78.1	103.5	113.9
95°	78.1	80.8	85.5	91.5	104.4	128.5	164.3	242.4	323.8	399.2	355.4
97.5°	212.6	218.3	236.5	266.8	316.5	397.0	483.9	604.1	661.9	618.6	452.9
100°	422.1	421.4	447.6	496.8	564.7	660.4	739.1	793.7	770.1	637.5	430.8
102.5°	619.1	634.6	656.6	695.5	748.4	809.0	854.9	856.6	775.5	602.4	398.5
105°	856.3	859.6	881.1	906.7	937.7	955.2	942.4	875.1	734.4	541.2	358.8
107.5°	992.7	998.9	1006.3	1014.9	1014.3	990.3	931.3	822.1	662.5	487.1	333.5
110°	1048.8	1050.1	1051.5	1046.0	1027.3	980.1	895.3	771.5	617.3	456.4	323.8



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1060.1	1059.8	1054.7	1038.0	1003.5	943.0	847.9	721.3	578.0	435.9	318.4
115°	1041.4	1038.0	1024.5	994.9	944.4	871.1	772.1	655.0	530.5	414.0	316.4
117.5°	981.9	977.2	957.9	923.9	871.3	796.9	708.0	606.9	501.8	401.1	317.6
120°	932.3	928.2	912.1	874.4	821.2	753.3	672.4	581.6	486.7	395.1	319.8
122.5°	886.0	880.9	863.1	829.1	782.0	718.8	643.9	561.7	474.3	391.4	323.5
125°	821.2	816.5	799.7	770.1	727.0	673.1	608.6	535.1	458.4	386.4	329.2
127.5°	767.9	763.6	748.4	723.1	684.8	635.8	577.4	512.0	444.4	384.0	335.6
130°	737.8	732.4	718.2	694.1	658.3	612.6	558.0	497.5	436.9	382.4	339.9
132.5°	708.2	704.4	691.9	667.6	634.1	590.5	539.8	484.0	429.9	381.8	343.2
135°	665.7	661.0	648.9	628.7	595.7	557.3	513.6	465.8	420.7	381.0	348.0
137.5°	621.0	617.9	607.6	587.1	559.4	526.2	488.4	449.3	412.8	379.5	351.3
140°	589.7	590.4	579.5	560.8	535.1	506.2	473.9	439.5	407.9	379.0	353.4
142.5°	560.6	561.3	551.6	534.9	513.1	487.9	459.9	430.4	403.6	377.9	355.0
145°	520.3	519.0	513.6	499.5	482.7	463.1	441.6	419.4	397.9	376.3	356.1
147.5°	487.2	486.7	481.6	472.0	459.3	445.4	428.0	410.4	392.2	373.8	356.1
150°	467.9	467.9	463.8	456.4	446.3	433.5	419.4	403.9	388.4	371.6	356.1
152.5°	451.7	451.7	449.3	442.4	434.5	423.8	411.3	398.0	384.1	368.9	354.5
155°	431.4	430.8	429.5	424.0	418.0	409.9	399.8	389.1	377.6	364.2	352.8
157.5°	413.0	413.2	412.1	408.0	402.8	396.5	388.7	379.6	370.4	360.0	350.4
160°	401.2	401.8	401.8	397.9	393.1	388.4	381.7	374.3	365.5	356.8	349.4
162.5°	390.5	391.1	391.1	387.6	384.5	380.3	374.1	367.8	360.7	353.5	347.2
165°	376.3	376.3	376.9	374.3	371.6	368.2	363.5	359.5	354.0	348.7	344.0
167.5°	362.8	362.8	363.5	361.6	360.4	358.0	355.2	352.1	347.8	343.9	340.8
170°	354.7	354.7	355.4	354.0	353.4	352.1	349.4	347.3	344.0	340.6	338.6
172.5°	347.2	347.8	349.0	347.6	347.5	346.6	344.5	343.0	340.2	337.9	337.0
175°	338.6	339.2	339.9	339.2	339.2	339.2	337.9	337.3	335.9	334.6	334.6
177.5°	333.6	333.6	334.7	334.2	334.7	334.7	334.2	333.6	333.0	332.5	333.0
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	959.2	956.3	953.4	948.4	944.1	937.9	936.1	933.9	927.5	921.7	917.4
5°	1017.8	1006.9	991.2	976.8	965.1	949.3	940.3	930.8	917.3	905.1	895.2
7.5°	1079.1	1057.8	1033.3	1006.8	982.1	958.3	939.1	922.0	903.0	885.1	871.2
10°	1127.7	1097.1	1062.9	1025.9	994.4	963.7	938.0	915.5	891.1	870.0	852.4
12.5°	1183.3	1137.9	1090.6	1045.8	1008.4	965.9	934.8	906.1	878.5	853.0	833.3
15°	1249.1	1191.4	1135.4	1073.7	1016.9	963.7	926.8	890.7	858.7	832.5	807.3
17.5°	1308.9	1243.5	1169.8	1094.8	1026.2	963.2	911.5	870.6	830.6	798.7	773.5
20°	1342.8	1268.4	1185.0	1107.1	1031.3	961.0	904.2	855.5	812.3	778.4	750.0
22.5°	1372.0	1285.0	1198.7	1115.3	1031.0	955.2	890.9	840.8	793.8	760.8	730.6
25°	1402.3	1298.1	1211.6	1113.8	1019.6	941.2	869.0	812.3	765.3	726.6	695.5
27.5°	1428.2	1297.3	1194.6	1089.3	1001.8	923.2	846.1	785.2	735.5	693.4	661.8
30°	1445.5	1299.1	1176.9	1072.8	984.5	903.3	828.5	767.2	714.9	672.1	642.3
32.5°	1456.4	1298.0	1160.7	1049.7	957.0	885.3	809.3	745.9	692.2	650.1	621.4
35°	1462.7	1290.0	1132.7	1002.0	912.7	842.9	779.4	713.5	657.2	617.9	585.6
37.5°	1450.1	1273.3	1100.3	956.1	858.3	789.5	736.1	680.0	626.1	582.9	555.0
40°	1430.2	1262.6	1075.0	923.6	820.8	754.6	709.0	654.0	600.8	559.8	533.6
42.5°	1392.3	1240.5	1047.2	887.5	781.9	715.6	673.7	627.8	577.4	538.9	512.8
45°	1299.9	1192.7	1005.6	833.4	724.4	655.8	618.9	585.6	540.0	502.6	480.0
47.5°	1171.7	1120.7	945.4	776.4	664.3	598.4	560.0	533.1	499.9	469.7	448.1
50°	1082.7	1061.5	904.7	737.4	624.3	559.8	522.9	498.5	474.7	444.4	424.6
52.5°	979.9	993.0	857.0	697.1	583.5	520.1	485.3	466.1	444.4	419.6	402.3
55°	835.3	882.5	774.8	629.2	522.9	462.4	429.6	412.4	399.8	381.3	366.4
57.5°	699.7	760.0	686.0	559.4	463.3	411.2	379.6	360.9	352.8	343.2	331.5
60°	619.3	678.8	622.5	512.5	423.3	373.7	345.7	329.9	321.8	315.0	305.1
62.5°	547.6	607.8	560.4	464.9	383.9	337.9	313.7	298.3	291.9	288.3	279.9
65°	448.9	500.8	469.2	390.8	327.7	287.1	265.0	254.3	248.4	247.0	241.6
67.5°	365.4	404.8	381.9	324.2	274.5	239.4	220.7	211.5	207.0	206.6	202.5
70°	310.6	347.5	329.9	277.7	234.9	207.3	191.1	183.0	180.3	179.9	177.6
72.5°	268.0	293.8	279.8	236.2	203.1	178.1	166.3	157.7	154.7	155.3	153.8
75°	198.3	217.7	209.6	179.4	152.8	136.6	126.7	121.2	118.6	119.9	118.1
77.5°	142.7	155.0	147.7	126.7	110.4	98.6	91.4	88.0	85.6	85.5	84.6
80°	107.7	114.9	110.9	98.2	84.7	74.8	69.0	66.7	65.3	64.9	64.5
82.5°	76.7	82.8	78.1	69.4	60.2	54.2	51.0	48.0	47.0	47.3	46.8
85°	38.7	41.0	39.2	33.8	30.2	27.5	25.7	24.4	23.4	23.8	23.0
87.5°	15.9	15.8	14.4	12.7	11.7	10.2	9.9	9.0	8.4	8.8	8.8
90°	12.8	10.8	8.8	7.4	6.0	4.0	2.7	1.4	2.7	4.0	6.0
92.5°	85.5	56.6	38.9	28.9	23.3	18.1	12.4	8.4	12.4	18.1	23.3
95°	245.0	144.7	87.5	61.2	43.7	32.3	24.9	22.9	24.9	32.3	43.7
97.5°	268.9	155.8	101.1	72.7	55.4	45.5	39.7	39.0	39.7	45.5	55.4
100°	253.7	154.1	107.0	80.8	64.7	55.2	50.5	49.9	50.5	55.2	64.7
102.5°	240.8	156.3	114.0	90.0	75.4	66.5	62.3	61.1	62.3	66.5	75.4
105°	231.5	162.2	125.9	105.0	92.2	84.1	80.1	78.1	80.1	84.1	92.2
107.5°	230.9	173.2	141.4	122.0	109.9	102.0	98.2	96.1	98.2	102.0	109.9
110°	233.6	182.4	152.1	133.3	121.8	114.4	111.1	109.1	111.1	114.4	121.8



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	238.9	191.6	163.4	145.2	133.7	126.3	123.0	120.9	123.0	126.3	133.7
115°	247.7	206.6	181.1	162.9	151.4	144.7	140.7	138.0	140.7	144.7	151.4
117.5°	259.3	222.7	197.3	180.6	167.7	161.5	158.2	155.1	158.2	161.5	167.7
120°	267.9	232.9	208.7	191.8	179.1	172.3	168.9	166.9	168.9	172.3	179.1
122.5°	276.0	243.7	220.0	202.1	189.9	182.5	179.2	177.2	179.2	182.5	189.9
125°	288.8	259.2	235.6	217.4	204.7	197.3	193.2	191.8	193.2	197.3	204.7
127.5°	299.3	272.6	249.9	231.7	217.6	210.0	205.0	203.0	205.0	210.0	217.6
130°	306.3	280.7	258.5	240.3	226.2	218.1	212.1	210.0	212.1	218.1	226.2
132.5°	312.7	287.7	266.0	248.4	234.3	224.5	218.0	215.4	218.0	224.5	234.3
135°	321.1	298.2	277.3	259.2	245.0	235.0	227.6	224.8	227.6	235.0	245.0
137.5°	327.3	305.5	285.4	268.5	254.6	243.8	236.5	233.7	236.5	243.8	254.6
140°	330.5	310.3	290.8	274.0	260.5	249.8	243.0	239.6	243.0	249.8	260.5
142.5°	333.7	314.1	295.1	279.4	265.9	256.2	248.9	246.1	248.9	256.2	265.9
145°	337.3	319.1	301.6	286.1	274.7	264.6	258.5	256.5	258.5	264.6	274.7
147.5°	339.4	323.1	307.1	293.9	282.8	274.1	268.2	267.0	268.2	274.1	282.8
150°	339.9	325.8	310.3	298.2	288.8	280.0	274.7	274.0	274.7	280.0	288.8
152.5°	341.0	327.4	314.1	302.5	294.2	286.5	281.1	280.9	281.1	286.5	294.2
155°	341.3	330.5	319.1	309.6	302.2	295.5	291.4	291.4	291.4	295.5	302.2
157.5°	342.0	332.3	323.1	315.8	309.5	303.6	300.3	299.8	300.3	303.6	309.5
160°	342.0	333.9	325.8	319.1	314.4	309.0	306.3	306.3	306.3	309.0	314.4
162.5°	341.4	334.4	327.4	321.8	317.6	313.3	311.2	311.2	311.2	313.3	317.6
165°	339.9	335.2	329.8	325.1	322.4	319.1	317.7	318.4	317.7	319.1	322.4
167.5°	338.9	335.1	331.2	328.2	326.3	323.8	323.1	323.9	323.1	323.8	326.3
170°	337.3	334.6	331.2	329.8	328.5	326.5	325.8	327.2	325.8	326.5	328.5
172.5°	336.7	334.6	331.7	330.9	330.1	328.6	328.5	329.3	328.5	328.6	330.1
175°	335.2	333.9	332.5	331.8	331.8	330.5	331.2	331.8	331.2	330.5	331.8
177.5°	334.2	333.0	332.5	332.5	332.5	332.0	332.5	333.0	332.5	332.0	332.5
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	914.8	912.3	908.7	903.3	899.0	892.1	892.1	893.2	893.2	892.9	892.1
5°	887.1	880.3	872.2	862.7	852.8	842.9	841.1	837.5	834.8	833.0	830.7
7.5°	857.8	845.8	834.0	820.7	808.7	798.7	791.7	785.9	782.2	778.3	775.4
10°	837.9	823.0	809.1	795.1	779.8	767.7	760.0	754.6	750.5	746.9	745.1
12.5°	814.5	797.5	782.0	768.8	752.0	739.5	732.2	729.7	724.9	717.3	713.3
15°	780.2	764.5	746.0	725.7	717.6	702.2	693.7	689.7	686.9	681.1	679.2
17.5°	751.0	730.3	709.6	694.4	679.3	666.9	662.1	657.1	653.5	648.7	647.3
20°	727.5	709.0	690.1	673.9	658.1	644.5	640.5	636.9	633.3	631.0	629.2
22.5°	703.7	685.3	669.5	654.4	637.6	628.7	624.3	620.4	617.8	616.3	614.5
25°	670.3	654.0	636.5	622.9	609.4	603.6	600.8	598.6	596.8	594.5	594.1
27.5°	640.3	622.7	608.4	595.8	586.1	581.2	578.6	577.5	577.9	578.7	579.2
30°	617.9	601.8	590.0	579.2	570.2	565.7	565.2	565.2	567.1	567.5	568.4
32.5°	597.4	584.1	572.4	561.9	555.1	552.0	553.7	553.7	555.2	556.3	557.9
35°	567.5	555.8	546.7	537.8	531.9	533.2	534.2	535.0	537.3	540.0	541.8
37.5°	538.9	528.7	519.4	512.3	509.6	512.0	514.2	516.1	518.8	520.8	522.6
40°	518.3	510.7	501.7	495.3	496.3	497.7	499.5	501.7	503.9	505.3	507.1
42.5°	499.2	491.2	484.4	479.1	480.4	482.2	483.2	484.4	487.0	489.4	490.5
45°	470.1	463.8	457.5	454.3	455.3	456.2	457.0	458.4	460.6	462.4	463.0
47.5°	437.4	433.0	428.8	425.7	427.1	426.8	427.9	430.8	431.5	432.7	435.1
50°	416.5	412.4	407.5	406.6	406.6	406.6	407.0	410.6	410.6	412.4	414.2
52.5°	393.4	390.8	387.6	386.0	385.3	385.3	387.2	389.0	389.7	392.3	394.1
55°	359.2	356.5	353.9	352.5	351.5	352.5	356.1	357.0	359.2	360.6	362.0
57.5°	323.6	321.6	319.4	318.7	318.5	319.7	321.7	324.3	324.9	329.1	331.1
60°	300.2	297.0	295.2	295.2	294.4	298.4	297.5	302.0	302.9	305.6	308.8
62.5°	276.0	271.8	271.0	271.0	272.3	273.5	274.7	276.7	279.1	282.5	285.0
65°	237.1	234.9	238.0	237.5	236.6	239.4	239.4	241.6	244.3	247.5	252.4
67.5°	200.2	199.1	199.3	199.3	200.7	202.2	203.5	205.4	208.7	212.1	215.2
70°	175.3	176.7	174.4	176.2	177.6	178.1	178.9	181.7	185.3	187.5	191.1
72.5°	151.2	151.1	151.4	152.1	153.4	154.2	155.2	158.3	162.2	164.1	166.9
75°	116.3	115.8	117.2	117.2	119.4	120.4	121.2	122.6	126.2	128.9	131.1
77.5°	84.9	85.5	85.2	86.7	86.1	86.3	89.0	90.4	90.7	96.1	97.3
80°	64.0	64.9	65.3	65.8	66.3	65.3	68.5	69.8	69.8	73.0	75.3
82.5°	46.0	46.5	47.7	48.1	48.2	49.2	49.4	50.4	51.5	52.9	55.8
85°	23.0	24.4	24.8	24.4	24.8	23.8	25.2	25.7	26.2	26.2	26.2
87.5°	8.7	9.3	9.4	10.2	10.2	10.9	10.8	10.2	10.3	11.5	10.4
90°	7.4	8.8	10.8	12.8	14.8	16.8	16.2	16.8	17.5	18.2	19.5
92.5°	28.9	38.9	56.6	85.5	113.9	103.5	78.1	56.7	44.9	39.7	36.2
95°	61.2	87.5	144.7	245.0	355.4	399.2	323.8	242.4	164.3	128.5	104.4
97.5°	72.7	101.1	155.8	268.9	452.9	618.6	661.9	604.1	483.9	397.0	316.5
100°	80.8	107.0	154.1	253.7	430.8	637.5	770.1	793.7	739.1	660.4	564.7
102.5°	90.0	114.0	156.3	240.8	398.5	602.4	775.5	856.6	854.9	809.0	748.4
105°	105.0	125.9	162.2	231.5	358.8	541.2	734.4	875.1	942.4	955.2	937.7
107.5°	122.0	141.4	173.2	230.9	333.5	487.1	662.5	822.1	931.3	990.3	1014.3
110°	133.3	152.1	182.4	233.6	323.8	456.4	617.3	771.5	895.3	980.1	1027.3



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	145.2	163.4	191.6	238.9	318.4	435.9	578.0	721.3	847.9	943.0	1003.5
115°	162.9	181.1	206.6	247.7	316.4	414.0	530.5	655.0	772.1	871.1	944.4
117.5°	180.6	197.3	222.7	259.3	317.6	401.1	501.8	606.9	708.0	796.9	871.3
120°	191.8	208.7	232.9	267.9	319.8	395.1	486.7	581.6	672.4	753.3	821.2
122.5°	202.1	220.0	243.7	276.0	323.5	391.4	474.3	561.7	643.9	718.8	782.0
125°	217.4	235.6	259.2	288.8	329.2	386.4	458.4	535.1	608.6	673.1	727.0
127.5°	231.7	249.9	272.6	299.3	335.6	384.0	444.4	512.0	577.4	635.8	684.8
130°	240.3	258.5	280.7	306.3	339.9	382.4	436.9	497.5	558.0	612.6	658.3
132.5°	248.4	266.0	287.7	312.7	343.2	381.8	429.9	484.0	539.8	590.5	634.1
135°	259.2	277.3	298.2	321.1	348.0	381.0	420.7	465.8	513.6	557.3	595.7
137.5°	268.5	285.4	305.5	327.3	351.3	379.5	412.8	449.3	488.4	526.2	559.4
140°	274.0	290.8	310.3	330.5	353.4	379.0	407.9	439.5	473.9	506.2	535.1
142.5°	279.4	295.1	314.1	333.7	355.0	377.9	403.6	430.4	459.9	487.9	513.1
145°	286.1	301.6	319.1	337.3	356.1	376.3	397.9	419.4	441.6	463.1	482.7
147.5°	293.9	307.1	323.1	339.4	356.1	373.8	392.2	410.4	428.0	445.4	459.3
150°	298.2	310.3	325.8	339.9	356.1	371.6	388.4	403.9	419.4	433.5	446.3
152.5°	302.5	314.1	327.4	341.0	354.5	368.9	384.1	398.0	411.3	423.8	434.5
155°	309.6	319.1	330.5	341.3	352.8	364.2	377.6	389.1	399.8	409.9	418.0
157.5°	315.8	323.1	332.3	342.0	350.4	360.0	370.4	379.6	388.7	396.5	402.8
160°	319.1	325.8	333.9	342.0	349.4	356.8	365.5	374.3	381.7	388.4	393.1
162.5°	321.8	327.4	334.4	341.4	347.2	353.5	360.7	367.8	374.1	380.3	384.5
165°	325.1	329.8	335.2	339.9	344.0	348.7	354.0	359.5	363.5	368.2	371.6
167.5°	328.2	331.2	335.1	338.9	340.8	343.9	347.8	352.1	355.2	358.0	360.4
170°	329.8	331.2	334.6	337.3	338.6	340.6	344.0	347.3	349.4	352.1	353.4
172.5°	330.9	331.7	334.6	336.7	337.0	337.9	340.2	343.0	344.5	346.6	347.5
175°	331.8	332.5	333.9	335.2	334.6	334.6	335.9	337.3	337.9	339.2	339.2
177.5°	332.5	332.5	333.0	334.2	333.0	332.5	333.0	333.6	334.2	334.7	334.7
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	889.6	889.2	891.7	889.9	891.7	889.2	889.6	892.1	892.9	893.2	893.2
5°	828.0	829.4	824.8	824.8	824.8	829.4	828.0	830.7	833.0	834.8	837.5
7.5°	773.2	771.2	771.4	769.0	771.4	771.2	773.2	775.4	778.3	782.2	785.9
10°	739.7	737.0	736.1	736.5	736.1	737.0	739.7	745.1	746.9	750.5	754.6
12.5°	711.9	711.4	705.4	705.5	705.4	711.4	711.9	713.3	717.3	724.9	729.7
15°	679.2	670.7	669.8	672.5	669.8	670.7	679.2	679.2	681.1	686.9	689.7
17.5°	646.5	642.0	642.3	640.9	642.3	642.0	646.5	647.3	648.7	653.5	657.1
20°	629.2	626.5	626.1	622.9	626.1	626.5	629.2	629.2	631.0	633.3	636.9
22.5°	613.4	612.5	612.8	609.2	612.8	612.5	613.4	614.5	616.3	617.8	620.4
25°	593.7	595.9	594.1	594.1	594.1	595.9	593.7	594.1	594.5	596.8	598.6
27.5°	580.3	580.2	579.3	579.3	579.3	580.2	580.3	579.2	578.7	577.9	577.5
30°	570.2	569.7	570.7	570.7	570.7	569.7	570.2	568.4	567.5	567.1	565.2
32.5°	560.1	560.8	560.9	561.3	560.9	560.8	560.1	557.9	556.3	555.2	553.7
35°	544.5	544.9	546.3	545.4	546.3	544.9	544.5	541.8	540.0	537.3	535.0
37.5°	523.4	525.5	525.0	525.7	525.0	525.5	523.4	522.6	520.8	518.8	516.1
40°	507.6	508.9	508.4	508.4	508.4	508.9	507.6	507.1	505.3	503.9	501.7
42.5°	491.3	492.3	491.1	490.4	491.1	492.3	491.3	490.5	489.4	487.0	484.4
45°	464.7	463.8	465.2	463.4	465.2	463.8	464.7	463.0	462.4	460.6	458.4
47.5°	435.0	435.8	436.3	437.6	436.3	435.8	435.0	435.1	432.7	431.5	430.8
50°	415.2	417.8	417.8	417.4	417.8	417.8	415.2	414.2	412.4	410.6	410.6
52.5°	395.6	396.9	398.7	398.6	398.7	396.9	395.6	394.1	392.3	389.7	389.0
55°	365.6	366.4	367.4	367.8	367.4	366.4	365.6	362.0	360.6	359.2	357.0
57.5°	334.3	334.0	336.1	336.8	336.1	334.0	334.3	331.1	329.1	324.9	324.3
60°	312.4	312.4	316.0	317.4	316.0	312.4	312.4	308.8	305.6	302.9	302.0
62.5°	289.0	290.4	293.9	292.1	293.9	290.4	289.0	285.0	282.5	279.1	276.7
65°	254.7	258.3	257.9	259.6	257.9	258.3	254.7	252.4	247.5	244.3	241.6
67.5°	218.9	221.1	224.4	224.6	224.4	221.1	218.9	215.2	212.1	208.7	205.4
70°	194.8	197.0	198.8	200.1	198.8	197.0	194.8	191.1	187.5	185.3	181.7
72.5°	171.3	172.5	176.8	174.9	176.8	172.5	171.3	166.9	164.1	162.2	158.3
75°	134.3	137.5	140.2	138.8	140.2	137.5	134.3	131.1	128.9	126.2	122.6
77.5°	99.4	102.5	103.8	102.6	103.8	102.5	99.4	97.3	96.1	90.7	90.4
80°	78.4	78.0	80.7	80.2	80.7	78.0	78.4	75.3	73.0	69.8	69.8
82.5°	57.5	57.1	58.3	58.6	58.3	57.1	57.5	55.8	52.9	51.5	50.4
85°	28.0	29.3	27.5	27.0	27.5	29.3	28.0	26.2	26.2	26.2	25.7
87.5°	10.2	10.4	10.2	9.6	10.2	10.4	10.2	10.4	11.5	10.3	10.2
90°	18.9	19.5	20.2	19.5	20.2	19.5	18.9	19.5	18.2	17.5	16.8
92.5°	35.0	33.0	33.7	32.5	33.7	33.0	35.0	36.2	39.7	44.9	56.7
95°	91.5	85.5	80.8	78.1	80.8	85.5	91.5	104.4	128.5	164.3	242.4
97.5°	266.8	236.5	218.3	212.6	218.3	236.5	266.8	316.5	397.0	483.9	604.1
100°	496.8	447.6	421.4	422.1	421.4	447.6	496.8	564.7	660.4	739.1	793.7
102.5°	695.5	656.6	634.6	619.1	634.6	656.6	695.5	748.4	809.0	854.9	856.6
105°	906.7	881.1	859.6	856.3	859.6	881.1	906.7	937.7	955.2	942.4	875.1
107.5°	1014.9	1006.3	998.9	992.7	998.9	1006.3	1014.9	1014.3	990.3	931.3	822.1
110°	1046.0	1051.5	1050.1	1048.8	1050.1	1051.5	1046.0	1027.3	980.1	895.3	771.5



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1038.0	1054.7	1059.8	1060.1	1059.8	1054.7	1038.0	1003.5	943.0	847.9	721.3
115°	994.9	1024.5	1038.0	1041.4	1038.0	1024.5	994.9	944.4	871.1	772.1	655.0
117.5°	923.9	957.9	977.2	981.9	977.2	957.9	923.9	871.3	796.9	708.0	606.9
120°	874.4	912.1	928.2	932.3	928.2	912.1	874.4	821.2	753.3	672.4	581.6
122.5°	829.1	863.1	880.9	886.0	880.9	863.1	829.1	782.0	718.8	643.9	561.7
125°	770.1	799.7	816.5	821.2	816.5	799.7	770.1	727.0	673.1	608.6	535.1
127.5°	723.1	748.4	763.6	767.9	763.6	748.4	723.1	684.8	635.8	577.4	512.0
130°	694.1	718.2	732.4	737.8	732.4	718.2	694.1	658.3	612.6	558.0	497.5
132.5°	667.6	691.9	704.4	708.2	704.4	691.9	667.6	634.1	590.5	539.8	484.0
135°	628.7	648.9	661.0	665.7	661.0	648.9	628.7	595.7	557.3	513.6	465.8
137.5°	587.1	607.6	617.9	621.0	617.9	607.6	587.1	559.4	526.2	488.4	449.3
140°	560.8	579.5	590.4	589.7	590.4	579.5	560.8	535.1	506.2	473.9	439.5
142.5°	534.9	551.6	561.3	560.6	561.3	551.6	534.9	513.1	487.9	459.9	430.4
145°	499.5	513.6	519.0	520.3	519.0	513.6	499.5	482.7	463.1	441.6	419.4
147.5°	472.0	481.6	486.7	487.2	486.7	481.6	472.0	459.3	445.4	428.0	410.4
150°	456.4	463.8	467.9	467.9	467.9	463.8	456.4	446.3	433.5	419.4	403.9
152.5°	442.4	449.3	451.7	451.7	451.7	449.3	442.4	434.5	423.8	411.3	398.0
155°	424.0	429.5	430.8	431.4	430.8	429.5	424.0	418.0	409.9	399.8	389.1
157.5°	408.0	412.1	413.2	413.0	413.2	412.1	408.0	402.8	396.5	388.7	379.6
160°	397.9	401.8	401.8	401.2	401.8	401.8	397.9	393.1	388.4	381.7	374.3
162.5°	387.6	391.1	391.1	390.5	391.1	391.1	387.6	384.5	380.3	374.1	367.8
165°	374.3	376.9	376.3	376.3	376.3	376.9	374.3	371.6	368.2	363.5	359.5
167.5°	361.6	363.5	362.8	362.8	362.8	363.5	361.6	360.4	358.0	355.2	352.1
170°	354.0	355.4	354.7	354.7	354.7	355.4	354.0	353.4	352.1	349.4	347.3
172.5°	347.6	349.0	347.8	347.2	347.8	349.0	347.6	347.5	346.6	344.5	343.0
175°	339.2	339.9	339.2	338.6	339.2	339.9	339.2	339.2	339.2	337.9	337.3
177.5°	334.2	334.7	333.6	333.6	333.6	334.7	334.2	334.7	334.7	334.2	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	892.1	892.1	899.0	903.3	908.7	912.3	914.8	917.4	921.7	927.5	933.9
5°	841.1	842.9	852.8	862.7	872.2	880.3	887.1	895.2	905.1	917.3	930.8
7.5°	791.7	798.7	808.7	820.7	834.0	845.8	857.8	871.2	885.1	903.0	922.0
10°	760.0	767.7	779.8	795.1	809.1	823.0	837.9	852.4	870.0	891.1	915.5
12.5°	732.2	739.5	752.0	768.8	782.0	797.5	814.5	833.3	853.0	878.5	906.1
15°	693.7	702.2	717.6	725.7	746.0	764.5	780.2	807.3	832.5	858.7	890.7
17.5°	662.1	666.9	679.3	694.4	709.6	730.3	751.0	773.5	798.7	830.6	870.6
20°	640.5	644.5	658.1	673.9	690.1	709.0	727.5	750.0	778.4	812.3	855.5
22.5°	624.3	628.7	637.6	654.4	669.5	685.3	703.7	730.6	760.8	793.8	840.8
25°	600.8	603.6	609.4	622.9	636.5	654.0	670.3	695.5	726.6	765.3	812.3
27.5°	578.6	581.2	586.1	595.8	608.4	622.7	640.3	661.8	693.4	735.5	785.2
30°	565.2	565.7	570.2	579.2	590.0	601.8	617.9	642.3	672.1	714.9	767.2
32.5°	553.7	552.0	555.1	561.9	572.4	584.1	597.4	621.4	650.1	692.2	745.9
35°	534.2	533.2	531.9	537.8	546.7	555.8	567.5	585.6	617.9	657.2	713.5
37.5°	514.2	512.0	509.6	512.3	519.4	528.7	538.9	555.0	582.9	626.1	680.0
40°	499.5	497.7	496.3	495.3	501.7	510.7	518.3	533.6	559.8	600.8	654.0
42.5°	483.2	482.2	480.4	479.1	484.4	491.2	499.2	512.8	538.9	577.4	627.8
45°	457.0	456.2	455.3	454.3	457.5	463.8	470.1	480.0	502.6	540.0	585.6
47.5°	427.9	426.8	427.1	425.7	428.8	433.0	437.4	448.1	469.7	499.9	533.1
50°	407.0	406.6	406.6	406.6	407.5	412.4	416.5	424.6	444.4	474.7	498.5
52.5°	387.2	385.3	385.3	386.0	387.6	390.8	393.4	402.3	419.6	444.4	466.1
55°	356.1	352.5	351.5	352.5	353.9	356.5	359.2	366.4	381.3	399.8	412.4
57.5°	321.7	319.7	318.5	318.7	319.4	321.6	323.6	331.5	343.2	352.8	360.9
60°	297.5	298.4	294.4	295.2	295.2	297.0	300.2	305.1	315.0	321.8	329.9
62.5°	274.7	273.5	272.3	271.0	271.0	271.8	276.0	279.9	288.3	291.9	298.3
65°	239.4	239.4	236.6	237.5	238.0	234.9	237.1	241.6	247.0	248.4	254.3
67.5°	203.5	202.2	200.7	199.3	199.3	199.1	200.2	202.5	206.6	207.0	211.5
70°	178.9	178.1	177.6	176.2	174.4	176.7	175.3	177.6	179.9	180.3	183.0
72.5°	155.2	154.2	153.4	152.1	151.4	151.1	151.2	153.8	155.3	154.7	157.7
75°	121.2	120.4	119.4	117.2	117.2	115.8	116.3	118.1	119.9	118.6	121.2
77.5°	89.0	86.3	86.1	86.7	85.2	85.5	84.9	84.6	85.5	85.6	88.0
80°	68.5	65.3	66.3	65.8	65.3	64.9	64.0	64.5	64.9	65.3	66.7
82.5°	49.4	49.2	48.2	48.1	47.7	46.5	46.0	46.8	47.3	47.0	48.0
85°	25.2	23.8	24.8	24.4	24.8	24.4	23.0	23.0	23.8	23.4	24.4
87.5°	10.8	10.9	10.2	10.2	9.4	9.3	8.7	8.8	8.8	8.4	9.0
90°	16.2	16.8	14.8	12.8	10.8	8.8	7.4	6.0	4.0	2.7	1.4
92.5°	78.1	103.5	113.9	85.5	56.6	38.9	28.9	23.3	18.1	12.4	8.4
95°	323.8	399.2	355.4	245.0	144.7	87.5	61.2	43.7	32.3	24.9	22.9
97.5°	661.9	618.6	452.9	268.9	155.8	101.1	72.7	55.4	45.5	39.7	39.0
100°	770.1	637.5	430.8	253.7	154.1	107.0	80.8	64.7	55.2	50.5	49.9
102.5°	775.5	602.4	398.5	240.8	156.3	114.0	90.0	75.4	66.5	62.3	61.1
105°	734.4	541.2	358.8	231.5	162.2	125.9	105.0	92.2	84.1	80.1	78.1
107.5°	662.5	487.1	333.5	230.9	173.2	141.4	122.0	109.9	102.0	98.2	96.1
110°	617.3	456.4	323.8	233.6	182.4	152.1	133.3	121.8	114.4	111.1	109.1



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	578.0	435.9	318.4	238.9	191.6	163.4	145.2	133.7	126.3	123.0	120.9
115°	530.5	414.0	316.4	247.7	206.6	181.1	162.9	151.4	144.7	140.7	138.0
117.5°	501.8	401.1	317.6	259.3	222.7	197.3	180.6	167.7	161.5	158.2	155.1
120°	486.7	395.1	319.8	267.9	232.9	208.7	191.8	179.1	172.3	168.9	166.9
122.5°	474.3	391.4	323.5	276.0	243.7	220.0	202.1	189.9	182.5	179.2	177.2
125°	458.4	386.4	329.2	288.8	259.2	235.6	217.4	204.7	197.3	193.2	191.8
127.5°	444.4	384.0	335.6	299.3	272.6	249.9	231.7	217.6	210.0	205.0	203.0
130°	436.9	382.4	339.9	306.3	280.7	258.5	240.3	226.2	218.1	212.1	210.0
132.5°	429.9	381.8	343.2	312.7	287.7	266.0	248.4	234.3	224.5	218.0	215.4
135°	420.7	381.0	348.0	321.1	298.2	277.3	259.2	245.0	235.0	227.6	224.8
137.5°	412.8	379.5	351.3	327.3	305.5	285.4	268.5	254.6	243.8	236.5	233.7
140°	407.9	379.0	353.4	330.5	310.3	290.8	274.0	260.5	249.8	243.0	239.6
142.5°	403.6	377.9	355.0	333.7	314.1	295.1	279.4	265.9	256.2	248.9	246.1
145°	397.9	376.3	356.1	337.3	319.1	301.6	286.1	274.7	264.6	258.5	256.5
147.5°	392.2	373.8	356.1	339.4	323.1	307.1	293.9	282.8	274.1	268.2	267.0
150°	388.4	371.6	356.1	339.9	325.8	310.3	298.2	288.8	280.0	274.7	274.0
152.5°	384.1	368.9	354.5	341.0	327.4	314.1	302.5	294.2	286.5	281.1	280.9
155°	377.6	364.2	352.8	341.3	330.5	319.1	309.6	302.2	295.5	291.4	291.4
157.5°	370.4	360.0	350.4	342.0	332.3	323.1	315.8	309.5	303.6	300.3	299.8
160°	365.5	356.8	349.4	342.0	333.9	325.8	319.1	314.4	309.0	306.3	306.3
162.5°	360.7	353.5	347.2	341.4	334.4	327.4	321.8	317.6	313.3	311.2	311.2
165°	354.0	348.7	344.0	339.9	335.2	329.8	325.1	322.4	319.1	317.7	318.4
167.5°	347.8	343.9	340.8	338.9	335.1	331.2	328.2	326.3	323.8	323.1	323.9
170°	344.0	340.6	338.6	337.3	334.6	331.2	329.8	328.5	326.5	325.8	327.2
172.5°	340.2	337.9	337.0	336.7	334.6	331.7	330.9	330.1	328.6	328.5	329.3
175°	335.9	334.6	334.6	335.2	333.9	332.5	331.8	331.8	330.5	331.2	331.8
177.5°	333.0	332.5	333.0	334.2	333.0	332.5	332.5	332.5	332.0	332.5	333.0
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	936.1	937.9	944.1	948.4	953.4	956.3	959.2	961.4	964.2	964.9	975.4
5°	940.3	949.3	965.1	976.8	991.2	1006.9	1017.8	1022.8	1035.8	1046.6	1068.2
7.5°	939.1	958.3	982.1	1006.8	1033.3	1057.8	1079.1	1104.3	1122.3	1149.3	1175.8
10°	938.0	963.7	994.4	1025.9	1062.9	1097.1	1127.7	1162.0	1190.4	1227.9	1259.8
12.5°	934.8	965.9	1008.4	1045.8	1090.6	1137.9	1183.3	1227.3	1252.4	1314.7	1344.2
15°	926.8	963.7	1016.9	1073.7	1135.4	1191.4	1249.1	1295.0	1369.3	1423.9	1458.6
17.5°	911.5	963.2	1026.2	1094.8	1169.8	1243.5	1308.9	1378.6	1457.5	1523.5	1593.9
20°	904.2	961.0	1031.3	1107.1	1185.0	1268.4	1342.8	1426.6	1512.7	1577.6	1667.8
22.5°	890.9	955.2	1031.0	1115.3	1198.7	1285.0	1372.0	1456.6	1556.0	1645.5	1731.2
25°	869.0	941.2	1019.6	1113.8	1211.6	1298.1	1402.3	1514.5	1618.2	1733.1	1818.8
27.5°	846.1	923.2	1001.8	1089.3	1194.6	1297.3	1428.2	1555.1	1681.9	1781.1	1844.4
30°	828.5	903.3	984.5	1072.8	1176.9	1299.1	1445.5	1583.9	1707.4	1792.6	1828.2
32.5°	809.3	885.3	957.0	1049.7	1160.7	1298.0	1456.4	1600.9	1708.9	1765.6	1758.7
35°	779.4	842.9	912.7	1002.0	1132.7	1290.0	1462.7	1602.4	1668.7	1656.5	1564.5
37.5°	736.1	789.5	858.3	956.1	1100.3	1273.3	1450.1	1554.9	1550.6	1451.5	1318.3
40°	709.0	754.6	820.8	923.6	1075.0	1262.6	1430.2	1498.3	1440.6	1302.2	1142.6
42.5°	673.7	715.6	781.9	887.5	1047.2	1240.5	1392.3	1412.1	1299.2	1140.0	993.7
45°	618.9	655.8	724.4	833.4	1005.6	1192.7	1299.9	1251.7	1099.8	935.3	824.0
47.5°	560.0	598.4	664.3	776.4	945.4	1120.7	1171.7	1069.2	913.2	779.8	677.6
50°	522.9	559.8	624.3	737.4	904.7	1061.5	1082.7	950.2	806.8	689.7	605.8
52.5°	485.3	520.1	583.5	697.1	857.0	993.0	979.9	844.9	713.1	613.2	547.4
55°	429.6	462.4	522.9	629.2	774.8	882.5	835.3	706.4	597.3	519.7	469.7
57.5°	379.6	411.2	463.3	559.4	686.0	760.0	699.7	591.1	504.4	444.7	407.4
60°	345.7	373.7	423.3	512.5	622.5	678.8	619.3	523.3	450.3	402.5	369.2
62.5°	313.7	337.9	383.9	464.9	560.4	607.8	547.6	466.3	404.2	361.8	333.5
65°	265.0	287.1	327.7	390.8	469.2	500.8	448.9	383.1	334.9	303.3	284.4
67.5°	220.7	239.4	274.5	324.2	381.9	404.8	365.4	314.4	278.1	252.8	237.7
70°	191.1	207.3	234.9	277.7	329.9	347.5	310.6	268.6	242.0	221.8	207.8
72.5°	166.3	178.1	203.1	236.2	279.8	293.8	268.0	231.2	206.4	191.1	180.0
75°	126.7	136.6	152.8	179.4	209.6	217.7	198.3	175.3	158.7	147.8	139.3
77.5°	91.4	98.6	110.4	126.7	147.7	155.0	142.7	127.3	115.2	107.9	103.1
80°	69.0	74.8	84.7	98.2	110.9	114.9	107.7	96.0	87.5	83.4	79.3
82.5°	51.0	54.2	60.2	69.4	78.1	82.8	76.7	69.7	65.1	61.4	59.8
85°	25.7	27.5	30.2	33.8	39.2	41.0	38.7	36.9	34.3	32.0	32.0
87.5°	9.9	10.2	11.7	12.7	14.4	15.8	15.9	15.6	15.6	15.2	14.9
90°	2.7	4.0	6.0	7.4	8.8	10.8	12.8	14.8	16.8	16.2	16.8
92.5°	12.4	18.1	23.3	28.9	38.9	56.6	85.5	113.9	103.5	78.1	56.7
95°	24.9	32.3	43.7	61.2	87.5	144.7	245.0	355.4	399.2	323.8	242.4
97.5°	39.7	45.5	55.4	72.7	101.1	155.8	268.9	452.9	618.6	661.9	604.1
100°	50.5	55.2	64.7	80.8	107.0	154.1	253.7	430.8	637.5	770.1	793.7
102.5°	62.3	66.5	75.4	90.0	114.0	156.3	240.8	398.5	602.4	775.5	856.6
105°	80.1	84.1	92.2	105.0	125.9	162.2	231.5	358.8	541.2	734.4	875.1
107.5°	98.2	102.0	109.9	122.0	141.4	173.2	230.9	333.5	487.1	662.5	822.1
110°	111.1	114.4	121.8	133.3	152.1	182.4	233.6	323.8	456.4	617.3	771.5



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.0	126.3	133.7	145.2	163.4	191.6	238.9	318.4	435.9	578.0	721.3
115°	140.7	144.7	151.4	162.9	181.1	206.6	247.7	316.4	414.0	530.5	655.0
117.5°	158.2	161.5	167.7	180.6	197.3	222.7	259.3	317.6	401.1	501.8	606.9
120°	168.9	172.3	179.1	191.8	208.7	232.9	267.9	319.8	395.1	486.7	581.6
122.5°	179.2	182.5	189.9	202.1	220.0	243.7	276.0	323.5	391.4	474.3	561.7
125°	193.2	197.3	204.7	217.4	235.6	259.2	288.8	329.2	386.4	458.4	535.1
127.5°	205.0	210.0	217.6	231.7	249.9	272.6	299.3	335.6	384.0	444.4	512.0
130°	212.1	218.1	226.2	240.3	258.5	280.7	306.3	339.9	382.4	436.9	497.5
132.5°	218.0	224.5	234.3	248.4	266.0	287.7	312.7	343.2	381.8	429.9	484.0
135°	227.6	235.0	245.0	259.2	277.3	298.2	321.1	348.0	381.0	420.7	465.8
137.5°	236.5	243.8	254.6	268.5	285.4	305.5	327.3	351.3	379.5	412.8	449.3
140°	243.0	249.8	260.5	274.0	290.8	310.3	330.5	353.4	379.0	407.9	439.5
142.5°	248.9	256.2	265.9	279.4	295.1	314.1	333.7	355.0	377.9	403.6	430.4
145°	258.5	264.6	274.7	286.1	301.6	319.1	337.3	356.1	376.3	397.9	419.4
147.5°	268.2	274.1	282.8	293.9	307.1	323.1	339.4	356.1	373.8	392.2	410.4
150°	274.7	280.0	288.8	298.2	310.3	325.8	339.9	356.1	371.6	388.4	403.9
152.5°	281.1	286.5	294.2	302.5	314.1	327.4	341.0	354.5	368.9	384.1	398.0
155°	291.4	295.5	302.2	309.6	319.1	330.5	341.3	352.8	364.2	377.6	389.1
157.5°	300.3	303.6	309.5	315.8	323.1	332.3	342.0	350.4	360.0	370.4	379.6
160°	306.3	309.0	314.4	319.1	325.8	333.9	342.0	349.4	356.8	365.5	374.3
162.5°	311.2	313.3	317.6	321.8	327.4	334.4	341.4	347.2	353.5	360.7	367.8
165°	317.7	319.1	322.4	325.1	329.8	335.2	339.9	344.0	348.7	354.0	359.5
167.5°	323.1	323.8	326.3	328.2	331.2	335.1	338.9	340.8	343.9	347.8	352.1
170°	325.8	326.5	328.5	329.8	331.2	334.6	337.3	338.6	340.6	344.0	347.3
172.5°	328.5	328.6	330.1	330.9	331.7	334.6	336.7	337.0	337.9	340.2	343.0
175°	331.2	330.5	331.8	331.8	332.5	333.9	335.2	334.6	334.6	335.9	337.3
177.5°	332.5	332.0	332.5	332.5	332.5	333.0	334.2	333.0	332.5	333.0	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	979.0	979.4	983.3	986.3	984.8	986.6	987.3
5°	1069.6	1085.9	1094.4	1100.7	1101.2	1101.6	1105.3
7.5°	1198.1	1215.5	1228.2	1247.5	1253.3	1259.8	1257.9
10°	1291.8	1317.5	1339.6	1351.3	1364.0	1382.4	1367.6
12.5°	1379.5	1425.0	1458.6	1476.9	1488.8	1492.5	1485.1
15°	1524.0	1583.5	1615.5	1614.5	1655.2	1672.8	1645.2
17.5°	1656.5	1711.4	1755.4	1778.0	1811.7	1819.2	1815.8
20°	1737.7	1797.6	1831.9	1870.6	1888.2	1903.9	1906.7
22.5°	1807.6	1861.4	1898.2	1930.4	1945.2	1952.7	1957.1
25°	1879.6	1922.0	1944.1	1955.3	1959.4	1958.5	1952.7
27.5°	1874.7	1877.9	1853.6	1829.7	1808.4	1784.3	1776.0
30°	1826.0	1788.1	1720.5	1682.2	1625.8	1581.2	1599.2
32.5°	1698.0	1622.6	1546.7	1462.9	1393.6	1373.9	1354.0
35°	1449.1	1316.6	1239.2	1148.9	1112.9	1076.9	1052.1
37.5°	1172.4	1069.9	977.9	918.9	882.9	860.1	847.7
40°	1013.7	921.4	845.6	797.8	770.3	744.7	741.1
42.5°	887.2	801.2	744.2	706.2	679.8	668.9	661.0
45°	726.6	666.7	628.4	601.3	583.8	577.0	567.9
47.5°	615.0	572.7	543.9	525.5	512.2	507.2	506.4
50°	552.6	517.5	496.3	481.8	471.5	469.7	462.4
52.5°	505.8	475.3	458.7	446.2	438.7	433.6	431.4
55°	439.0	418.7	403.9	396.7	390.8	385.8	385.8
57.5°	384.1	367.2	357.3	351.2	349.4	345.9	343.6
60°	350.3	335.8	328.1	322.7	319.2	319.6	315.6
62.5°	317.0	307.7	300.4	295.0	290.7	290.8	291.0
65°	270.0	262.8	257.4	255.5	252.9	249.7	250.6
67.5°	228.8	222.1	217.8	214.7	213.9	212.2	214.7
70°	199.2	194.2	191.1	188.4	187.5	188.0	190.2
72.5°	172.2	168.7	166.6	165.3	163.3	163.4	165.0
75°	135.3	132.5	130.7	129.3	128.9	128.9	128.9
77.5°	99.4	98.8	97.9	95.9	96.0	96.5	96.6
80°	78.4	77.1	76.6	75.8	74.4	73.4	75.8
82.5°	58.6	57.3	56.8	56.7	54.5	54.3	56.2
85°	31.5	30.2	30.7	30.2	30.2	29.8	29.8
87.5°	14.6	14.5	14.4	14.6	14.4	14.1	14.7
90°	17.5	18.2	19.5	18.9	19.5	20.2	19.5
92.5°	44.9	39.7	36.2	35.0	33.0	33.7	32.5
95°	164.3	128.5	104.4	91.5	85.5	80.8	78.1
97.5°	483.9	397.0	316.5	266.8	236.5	218.3	212.6
100°	739.1	660.4	564.7	496.8	447.6	421.4	422.1
102.5°	854.9	809.0	748.4	695.5	656.6	634.6	619.1
105°	942.4	955.2	937.7	906.7	881.1	859.6	856.3
107.5°	931.3	990.3	1014.3	1014.9	1006.3	998.9	992.7
110°	895.3	980.1	1027.3	1046.0	1051.5	1050.1	1048.8



TEST NUMBER: P331975-935

CATALOG NUMBER: S123DIP-S775D805U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	847.9	943.0	1003.5	1038.0	1054.7	1059.8	1060.1
115°	772.1	871.1	944.4	994.9	1024.5	1038.0	1041.4
117.5°	708.0	796.9	871.3	923.9	957.9	977.2	981.9
120°	672.4	753.3	821.2	874.4	912.1	928.2	932.3
122.5°	643.9	718.8	782.0	829.1	863.1	880.9	886.0
125°	608.6	673.1	727.0	770.1	799.7	816.5	821.2
127.5°	577.4	635.8	684.8	723.1	748.4	763.6	767.9
130°	558.0	612.6	658.3	694.1	718.2	732.4	737.8
132.5°	539.8	590.5	634.1	667.6	691.9	704.4	708.2
135°	513.6	557.3	595.7	628.7	648.9	661.0	665.7
137.5°	488.4	526.2	559.4	587.1	607.6	617.9	621.0
140°	473.9	506.2	535.1	560.8	579.5	590.4	589.7
142.5°	459.9	487.9	513.1	534.9	551.6	561.3	560.6
145°	441.6	463.1	482.7	499.5	513.6	519.0	520.3
147.5°	428.0	445.4	459.3	472.0	481.6	486.7	487.2
150°	419.4	433.5	446.3	456.4	463.8	467.9	467.9
152.5°	411.3	423.8	434.5	442.4	449.3	451.7	451.7
155°	399.8	409.9	418.0	424.0	429.5	430.8	431.4
157.5°	388.7	396.5	402.8	408.0	412.1	413.2	413.0
160°	381.7	388.4	393.1	397.9	401.8	401.8	401.2
162.5°	374.1	380.3	384.5	387.6	391.1	391.1	390.5
165°	363.5	368.2	371.6	374.3	376.9	376.3	376.3
167.5°	355.2	358.0	360.4	361.6	363.5	362.8	362.8
170°	349.4	352.1	353.4	354.0	355.4	354.7	354.7
172.5°	344.5	346.6	347.5	347.6	349.0	347.8	347.2
175°	337.9	339.2	339.2	339.2	339.9	339.2	338.6
177.5°	334.2	334.7	334.7	334.2	334.7	333.6	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5

(END OF REPORT)