

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332385-930

Luminaire Tested: **S123RDIP-S1165D1195U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332385-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7071.7 lumens  
Efficiency: N/A  
Efficacy: 98.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	34
4	76	66	58	52	71	62	55	50	53	48	44	45	42	38	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	32	29	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	16113	16113	16113	16113
5°	19207	16181	14249	16181
10°	23981	16088	12873	16088
15°	28149	15924	11739	15924
20°	31416	15678	10775	15678
25°	30914	15419	10183	15419
30°	22222	15181	9573	15181
35°	14837	14870	9179	14870
40°	10932	14497	8769	14497
45°	9168	13842	8369	13842
50°	8090	12983	7812	12983
55°	7096	12001	7047	12001
60°	6318	11063	6456	11063
65°	5547	10055	6006	10055
70°	4356	9155	5485	9155
75°	3839	7993	5011	7993
80°	3335	6794	4928	6794
85°	2692	5459	5224	5459



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.2	2.1
10°-20°	459.9	6.5
20°-30°	722.5	10.2
30°-40°	753.8	10.7
40°-50°	645.1	9.1
50°-60°	491.7	7.0
60°-70°	315.1	4.5
70°-80°	151.6	2.1
80°-90°	43.7	0.6
90°-100°	78.6	1.1
100°-110°	235.1	3.3
110°-120°	399.9	5.7
120°-130°	526.0	7.4
130°-140°	591.2	8.4
140°-150°	581.2	8.2
150°-160°	489.3	6.9
160°-170°	325.7	4.6
170°-180°	114.0	1.6
0°-30°	1329.6	18.8
0°-40°	2083.4	29.5
0°-60°	3220.2	45.5
0°-90°	3730.6	52.8
90°-120°	713.6	10.1
90°-150°	2412.1	34.1
90°-180°	3341.0	47.2
0°-180°	7071.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1497	1497	1497	1497	1497	
5°	1778	1498	1319	1498	1778	184
15°	2526	1429	1053	1429	2526	716
25°	2603	1298	857	1298	2603	1119
35°	1129	1132	698	1132	1129	740
45°	602	909	550	909	602	474
55°	378	640	376	640	378	342
65°	218	395	236	395	218	214
75°	92	192	120	192	92	99
85°	22	44	42	44	22	26
90°	28	1	28	1	28	15
95°	74	56	74	56	74	76
105°	225	213	225	213	225	239
115°	404	403	404	403	404	400
125°	583	589	583	589	583	521
135°	764	764	764	764	764	587
145°	927	927	927	927	927	579
155°	1060	1062	1060	1062	1060	488
165°	1153	1157	1153	1157	1153	325
175°	1198	1203	1198	1203	1198	114
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1594.3	1596.4	1589.7	1588.7	1580.9	1578.9	1578.9	1568.1	1561.5	1552.8	1547.7
5°	1777.6	1787.9	1782.7	1771.2	1751.9	1747.4	1735.3	1716.0	1694.3	1667.4	1654.6
7.5°	2006.5	2020.5	2015.1	1997.2	1977.1	1960.9	1926.5	1894.6	1849.8	1810.6	1777.0
10°	2194.1	2179.4	2167.8	2150.5	2131.9	2101.8	2066.0	2016.6	1959.6	1914.7	1864.8
12.5°	2334.5	2332.2	2317.5	2299.7	2273.5	2244.8	2200.7	2140.6	2074.4	2009.5	1952.4
15°	2526.0	2529.9	2520.3	2501.7	2464.5	2413.9	2347.2	2322.3	2227.4	2157.0	2086.4
17.5°	2658.5	2657.8	2656.5	2630.7	2592.8	2556.8	2495.0	2429.3	2343.4	2244.1	2149.1
20°	2742.6	2736.2	2737.5	2708.7	2680.5	2638.8	2578.5	2483.1	2412.6	2297.9	2199.8
22.5°	2740.5	2739.3	2744.1	2734.3	2713.8	2681.8	2634.5	2553.8	2463.9	2348.1	2237.8
25°	2602.9	2597.8	2628.0	2636.3	2669.0	2674.7	2660.6	2616.4	2531.2	2412.0	2275.5
27.5°	2178.5	2175.6	2231.6	2301.5	2390.2	2459.1	2525.8	2557.9	2531.2	2445.8	2309.1
30°	1787.9	1848.0	1876.2	1977.5	2090.3	2224.9	2342.8	2454.9	2482.4	2445.3	2333.1
32.5°	1484.3	1536.9	1560.5	1647.4	1752.5	1910.1	2086.9	2245.7	2357.9	2386.3	2318.8
35°	1129.1	1129.8	1183.6	1222.0	1319.4	1481.6	1653.3	1866.0	2077.5	2237.7	2254.3
37.5°	901.0	904.2	936.7	975.0	1048.1	1133.8	1285.1	1461.9	1706.2	1952.2	2096.3
40°	778.0	783.7	808.0	845.9	898.4	963.1	1081.0	1247.7	1451.4	1725.0	1948.6
42.5°	699.0	708.3	720.9	750.0	782.5	843.2	938.5	1067.2	1252.5	1511.2	1769.3
45°	602.3	607.5	617.1	630.6	660.0	702.3	766.4	852.9	1006.7	1215.0	1473.2
47.5°	531.3	528.6	538.7	549.7	569.3	598.1	641.1	711.7	821.4	988.5	1207.5
50°	483.1	482.5	489.6	497.9	516.5	537.6	572.9	626.1	713.2	851.7	1052.2
52.5°	438.1	440.5	445.5	455.8	469.3	486.4	518.0	556.4	631.2	750.6	917.9
55°	378.1	380.0	387.0	392.8	402.4	419.7	439.6	471.7	522.9	606.2	744.0
57.5°	327.3	326.4	333.2	334.6	345.5	359.6	375.0	399.8	437.0	499.0	591.7
60°	293.5	291.6	297.3	301.8	307.6	319.1	331.9	356.3	385.8	431.3	510.7
62.5°	262.7	261.8	266.0	270.5	275.3	285.8	296.5	315.3	338.6	376.9	439.9
65°	217.8	219.8	221.7	223.6	226.2	232.6	242.9	255.7	271.7	298.6	344.1
67.5°	171.2	173.2	173.8	177.7	183.3	187.3	193.6	205.0	216.1	238.8	264.6
70°	138.4	137.8	138.4	140.3	147.4	154.4	162.7	171.1	178.1	194.1	216.0
72.5°	119.0	117.8	119.4	119.8	123.3	125.2	130.4	138.3	147.4	158.2	173.9
75°	92.3	92.3	92.3	92.3	94.8	96.1	98.1	100.0	103.1	108.3	119.8
77.5°	68.2	68.3	69.2	69.9	70.4	71.1	72.3	74.2	75.3	78.0	83.1
80°	53.8	54.5	53.8	54.5	54.5	55.8	56.4	58.3	58.9	62.1	64.1
82.5°	40.5	40.1	40.5	41.2	41.2	42.4	42.6	43.9	44.1	45.7	47.7
85°	21.8	20.5	21.8	21.1	22.4	21.1	21.8	23.1	23.1	23.7	26.3
87.5°	10.8	11.7	10.7	11.1	11.0	11.3	11.2	11.0	11.9	11.3	11.2
90°	28.5	28.0	27.6	27.1	26.7	26.1	25.3	24.5	23.6	22.7	20.0
92.5°	38.2	38.5	38.8	39.1	39.3	39.1	38.4	37.7	37.0	36.4	34.8
95°	73.9	73.9	73.9	73.9	73.9	73.5	72.6	71.7	70.9	70.1	68.4
97.5°	113.7	113.7	113.8	113.9	114.0	113.6	112.6	111.6	110.6	109.7	108.4
100°	144.0	143.6	143.2	142.8	142.3	141.8	141.1	140.5	139.9	139.3	138.2
102.5°	175.0	175.1	175.2	175.3	175.4	175.1	174.5	173.8	173.3	172.6	171.2
105°	225.4	225.0	224.6	224.2	223.8	223.6	223.6	223.6	223.6	223.6	221.7
107.5°	277.9	278.2	278.4	278.7	278.9	278.8	278.1	277.4	276.7	276.1	275.2
110°	313.6	314.0	314.4	314.8	315.2	315.0	314.2	313.3	312.5	311.7	311.2



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	351.5	351.6	351.6	351.7	351.8	351.3	350.3	349.3	348.3	347.2	347.2
115°	403.6	403.7	404.0	404.1	404.4	404.4	404.1	404.0	403.7	403.6	404.0
117.5°	456.4	457.0	457.5	458.2	458.8	459.1	459.1	459.2	459.2	459.3	459.8
120°	493.5	494.0	494.4	494.8	495.2	495.5	495.8	495.9	496.2	496.4	497.4
122.5°	529.1	529.7	530.4	530.9	531.5	532.1	532.6	533.2	533.7	534.3	534.8
125°	582.6	583.4	584.2	585.1	586.0	586.8	587.7	588.5	589.3	590.2	590.6
127.5°	635.9	636.7	637.7	638.7	639.7	640.7	642.0	643.1	644.3	645.5	646.0
130°	670.7	672.1	673.6	675.1	676.5	677.8	678.6	679.4	680.3	681.1	681.8
132.5°	707.0	708.2	709.3	710.5	711.6	712.7	713.7	714.7	715.7	716.7	717.1
135°	763.5	763.9	764.3	764.8	765.2	765.8	766.6	767.5	768.3	769.2	769.4
137.5°	813.3	814.2	815.0	815.7	816.5	817.3	818.2	819.1	820.0	820.9	820.4
140°	846.0	847.4	848.9	850.4	851.8	852.6	852.9	853.0	853.3	853.5	853.3
142.5°	879.3	880.4	881.5	882.6	883.8	884.5	884.7	884.9	885.1	885.3	884.9
145°	927.4	928.2	929.0	929.9	930.7	931.3	931.5	931.7	931.9	932.1	931.5
147.5°	970.2	971.4	972.7	974.0	975.3	975.9	975.9	975.9	975.9	975.9	975.3
150°	997.5	998.7	1000.0	1001.3	1002.6	1003.1	1003.1	1003.1	1003.1	1003.1	1002.7
152.5°	1024.0	1025.1	1026.2	1027.3	1028.4	1028.7	1028.4	1028.1	1027.8	1027.4	1027.2
155°	1060.0	1061.5	1063.0	1064.5	1065.9	1066.2	1065.4	1064.5	1063.7	1062.8	1062.7
157.5°	1092.7	1094.0	1095.1	1096.3	1097.5	1097.6	1096.7	1095.8	1095.0	1094.1	1094.0
160°	1114.0	1114.8	1115.7	1116.6	1117.4	1117.3	1116.2	1115.2	1114.1	1113.0	1113.0
162.5°	1129.9	1131.2	1132.6	1133.9	1135.3	1135.5	1134.4	1133.3	1132.3	1131.2	1131.1
165°	1152.8	1154.3	1155.8	1157.2	1158.7	1158.9	1157.6	1156.3	1155.0	1153.8	1153.8
167.5°	1172.3	1173.6	1174.9	1176.2	1177.5	1177.5	1176.2	1174.9	1173.6	1172.3	1172.2
170°	1182.2	1183.7	1185.1	1186.7	1188.1	1188.1	1186.7	1185.1	1183.7	1182.2	1182.2
172.5°	1189.8	1191.2	1192.7	1194.2	1195.7	1195.8	1194.5	1193.2	1191.9	1190.6	1190.6
175°	1198.3	1199.8	1201.3	1202.7	1204.2	1204.3	1203.1	1201.8	1200.5	1199.2	1199.2
177.5°	1202.9	1204.0	1205.2	1206.4	1207.5	1207.6	1206.6	1205.7	1204.6	1203.6	1203.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1545.6	1544.1	1536.9	1528.7	1517.9	1510.7	1505.1	1502.0	1492.8	1481.6	1473.8
5°	1641.1	1621.9	1601.3	1576.4	1553.3	1529.6	1514.8	1497.5	1476.4	1452.7	1436.1
7.5°	1743.4	1705.7	1665.1	1623.2	1581.8	1544.6	1511.8	1483.7	1450.0	1416.0	1392.2
10°	1821.8	1766.7	1709.7	1651.3	1598.1	1548.2	1509.7	1471.9	1431.6	1392.4	1363.0
12.5°	1893.0	1820.5	1754.8	1683.1	1615.1	1555.3	1500.0	1455.5	1407.0	1365.3	1331.7
15°	1983.3	1908.9	1829.5	1720.5	1630.2	1554.6	1487.3	1429.0	1370.0	1318.7	1286.1
17.5°	2067.6	1955.7	1848.9	1758.1	1640.7	1546.2	1464.1	1394.4	1329.7	1275.3	1235.1
20°	2102.5	1994.1	1878.2	1762.2	1646.8	1541.2	1445.6	1368.7	1301.5	1239.9	1202.8
22.5°	2123.4	2000.8	1878.7	1754.0	1631.5	1521.7	1427.2	1342.6	1269.7	1211.2	1165.4
25°	2148.0	2001.9	1867.3	1744.3	1619.3	1500.2	1388.0	1298.3	1219.4	1157.3	1108.6
27.5°	2164.1	1992.3	1833.2	1696.5	1569.7	1451.0	1348.3	1253.1	1173.2	1107.4	1055.2
30°	2167.1	1984.5	1807.0	1659.1	1530.2	1421.3	1312.4	1221.4	1136.8	1066.9	1018.2
32.5°	2171.3	1965.6	1771.6	1614.5	1482.5	1374.7	1275.9	1189.0	1102.4	1033.6	983.9
35°	2154.3	1955.1	1718.0	1537.2	1405.2	1300.8	1211.8	1131.6	1046.4	979.7	929.2
37.5°	2081.5	1913.4	1662.4	1450.4	1312.4	1215.6	1143.0	1073.2	995.1	923.2	875.5
40°	2008.2	1872.4	1619.3	1397.6	1253.4	1154.1	1088.8	1031.7	956.1	888.8	837.6
42.5°	1899.1	1816.6	1578.3	1342.2	1186.7	1091.0	1035.9	982.4	916.1	847.7	799.6
45°	1698.8	1709.7	1494.4	1254.0	1094.5	998.3	946.5	909.3	850.4	793.9	744.6
47.5°	1447.6	1549.5	1395.8	1160.1	997.2	907.0	861.6	829.2	789.5	734.1	689.1
50°	1283.5	1429.0	1316.9	1097.1	936.2	846.5	801.6	775.3	740.8	697.2	654.3
52.5°	1132.3	1288.5	1221.5	1026.8	870.1	788.1	744.2	722.6	695.1	654.1	615.3
55°	923.4	1081.7	1066.3	920.8	770.9	697.2	663.9	639.5	620.9	590.2	559.5
57.5°	746.9	897.0	904.9	802.9	683.5	610.7	582.0	563.6	551.5	528.3	499.9
60°	635.7	773.5	800.4	723.5	620.9	556.8	528.6	513.9	504.3	485.8	463.9
62.5°	543.4	660.6	691.1	635.8	560.9	501.0	478.9	464.7	458.2	442.1	422.9
65°	415.9	513.3	542.7	512.0	472.9	424.9	406.9	394.8	389.0	380.0	365.9
67.5°	312.7	383.7	416.0	394.4	380.3	349.8	338.4	331.9	326.8	320.7	308.8
70°	251.2	303.7	337.0	331.3	319.8	303.7	295.4	290.9	285.8	280.7	270.4
72.5°	201.9	238.1	269.4	272.3	262.9	259.7	252.3	250.5	247.4	241.2	235.5
75°	134.0	158.9	180.7	189.1	192.9	196.1	192.9	192.2	191.6	186.5	183.3
77.5°	87.8	101.3	115.0	129.2	135.2	139.6	140.6	142.9	141.2	138.5	137.0
80°	67.3	70.5	80.1	92.3	101.9	105.7	108.3	109.6	108.9	108.3	105.7
82.5°	48.8	51.5	56.0	64.6	72.6	79.1	80.6	80.4	81.8	82.2	80.1
85°	26.3	26.9	28.2	29.5	34.0	41.0	43.0	44.2	45.5	45.5	41.7
87.5°	11.7	10.6	11.1	10.6	11.7	11.8	14.4	16.6	17.5	15.9	16.3
90°	17.3	14.5	11.8	9.4	7.3	5.1	3.0	1.0	3.0	5.1	7.3
92.5°	33.3	31.7	30.2	28.6	27.2	25.8	24.4	22.9	24.4	25.8	27.2
95°	66.7	65.1	63.3	61.8	60.3	58.9	57.4	55.9	57.4	58.9	60.3
97.5°	107.3	106.1	104.8	103.6	102.6	101.5	100.4	99.3	100.4	101.5	102.6
100°	137.1	136.1	135.0	133.9	132.6	131.3	130.1	128.8	130.1	131.3	132.6
102.5°	169.8	168.4	167.1	166.0	165.2	164.4	163.7	162.9	163.7	164.4	165.2
105°	219.8	217.8	216.0	214.8	214.4	214.0	213.5	213.1	213.5	214.0	214.4
107.5°	274.5	273.8	273.0	272.5	272.2	272.0	271.7	271.5	271.7	272.0	272.2
110°	310.8	310.4	310.0	309.6	309.2	308.7	308.3	307.9	308.3	308.7	309.2





TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	347.1	347.0	346.9	346.7	346.5	346.3	346.0	345.8	346.0	346.3	346.5
115°	404.4	404.8	405.2	405.1	404.5	403.8	403.2	402.6	403.2	403.8	404.5
117.5°	460.3	460.9	461.5	461.5	461.1	460.6	460.2	459.8	460.2	460.6	461.1
120°	498.5	499.5	500.6	500.5	499.2	498.0	496.7	495.5	496.7	498.0	499.2
122.5°	535.3	535.9	536.5	536.3	535.3	534.4	533.5	532.6	533.5	534.4	535.3
125°	591.0	591.4	591.8	591.7	591.1	590.4	589.9	589.2	589.9	590.4	591.1
127.5°	646.4	646.9	647.3	646.9	645.6	644.2	642.9	641.5	642.9	644.2	645.6
130°	682.3	683.0	683.6	683.1	681.4	679.7	678.0	676.4	678.0	679.7	681.4
132.5°	717.6	718.1	718.6	718.0	716.2	714.6	712.9	711.2	712.9	714.6	716.2
135°	769.6	769.8	770.1	769.5	768.3	767.0	765.7	764.4	765.7	767.0	768.3
137.5°	819.8	819.3	818.7	817.9	816.8	815.8	814.7	813.8	814.7	815.8	816.8
140°	853.0	852.9	852.6	852.0	851.0	849.9	848.9	847.8	848.9	849.9	851.0
142.5°	884.6	884.2	883.8	883.1	882.1	881.0	880.0	878.9	880.0	881.0	882.1
145°	930.8	930.3	929.6	929.0	928.6	928.2	927.8	927.4	927.8	928.2	928.6
147.5°	974.7	974.1	973.5	972.9	972.1	971.3	970.6	969.8	970.6	971.3	972.1
150°	1002.3	1001.9	1001.5	1001.1	1000.6	1000.2	999.8	999.4	999.8	1000.2	1000.6
152.5°	1027.0	1026.6	1026.4	1026.0	1025.4	1024.8	1024.3	1023.6	1024.3	1024.8	1025.4
155°	1062.4	1062.3	1062.0	1061.9	1061.9	1061.9	1061.9	1061.9	1061.9	1061.9	1061.9
157.5°	1093.8	1093.6	1093.4	1093.5	1093.7	1094.0	1094.2	1094.5	1094.2	1094.0	1093.7
160°	1113.0	1113.0	1113.0	1113.3	1113.7	1114.1	1114.5	1114.9	1114.5	1114.1	1113.7
162.5°	1130.9	1130.7	1130.6	1130.8	1131.4	1132.0	1132.5	1133.1	1132.5	1132.0	1131.4
165°	1153.8	1153.8	1153.8	1154.1	1154.7	1155.4	1156.0	1156.7	1156.0	1155.4	1154.7
167.5°	1172.0	1171.8	1171.7	1172.0	1172.9	1173.7	1174.5	1175.4	1174.5	1173.7	1172.9
170°	1182.2	1182.2	1182.2	1182.6	1183.5	1184.3	1185.1	1186.0	1185.1	1184.3	1183.5
172.5°	1190.6	1190.6	1190.6	1191.0	1191.8	1192.6	1193.5	1194.3	1193.5	1192.6	1191.8
175°	1199.2	1199.2	1199.2	1199.7	1200.5	1201.3	1202.2	1203.1	1202.2	1201.3	1200.5
177.5°	1203.6	1203.6	1203.6	1204.0	1204.6	1205.3	1206.0	1206.6	1206.0	1205.3	1204.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1471.3	1464.6	1460.0	1449.8	1443.1	1435.9	1428.7	1433.4	1432.8	1432.3	1432.3
5°	1422.0	1407.2	1393.8	1376.5	1365.5	1352.1	1341.8	1340.5	1343.1	1334.2	1329.0
7.5°	1373.0	1352.8	1333.7	1314.7	1294.5	1278.3	1268.1	1263.4	1256.9	1251.3	1245.6
10°	1338.6	1314.9	1296.3	1272.6	1250.8	1231.6	1219.4	1211.1	1206.6	1202.2	1193.8
12.5°	1303.3	1280.1	1256.4	1229.6	1208.8	1186.5	1177.4	1168.1	1159.4	1154.5	1143.0
15°	1251.5	1221.4	1196.4	1168.2	1145.1	1123.3	1110.5	1091.9	1089.3	1083.0	1071.4
17.5°	1199.5	1166.9	1132.5	1111.5	1085.5	1062.8	1043.3	1037.1	1018.7	1011.8	1001.8
20°	1158.5	1128.5	1102.2	1074.6	1036.8	1015.7	1000.3	992.0	977.2	968.2	961.8
22.5°	1123.2	1092.6	1062.2	1030.0	998.9	975.2	963.9	951.0	942.9	930.3	923.4
25°	1072.7	1039.3	1002.8	968.2	945.8	927.9	910.0	898.4	886.9	881.1	868.3
27.5°	1014.0	979.2	945.0	918.8	891.2	873.5	857.3	847.0	833.2	823.5	816.4
30°	981.7	940.7	911.2	887.5	852.2	835.6	823.5	810.7	800.4	790.1	783.1
32.5°	944.3	906.9	878.9	849.5	822.6	804.3	788.6	777.3	768.6	758.8	751.8
35°	885.6	854.2	825.3	795.9	776.0	757.4	738.8	729.2	720.9	711.9	705.6
37.5°	832.5	803.2	775.8	747.8	723.2	708.1	693.1	685.7	674.5	668.5	661.9
40°	799.7	770.9	741.4	714.5	688.8	677.4	663.9	653.0	642.7	638.2	631.2
42.5°	763.9	735.0	710.1	681.2	660.1	644.5	632.1	620.2	612.5	605.9	601.9
45°	710.6	685.0	660.6	631.9	612.0	598.5	584.4	573.5	566.5	562.0	554.9
47.5°	659.0	633.4	608.6	583.5	564.3	548.9	534.8	527.3	517.9	512.4	507.6
50°	621.6	598.5	572.3	549.2	529.9	514.5	503.0	493.4	485.1	478.0	474.8
52.5°	587.3	562.6	540.0	518.4	498.1	480.7	470.2	460.1	453.8	445.7	442.1
55°	530.6	506.9	487.6	466.5	446.6	431.9	419.1	410.1	403.7	394.8	389.6
57.5°	477.4	456.2	433.2	414.8	394.4	381.9	371.3	359.1	351.3	344.2	339.2
60°	441.5	417.2	397.3	380.0	362.1	346.0	336.4	326.8	318.5	311.4	307.0
62.5°	404.1	382.8	363.9	345.1	328.7	314.8	303.6	295.5	288.2	283.7	279.2
65°	346.7	330.0	310.8	295.4	280.1	269.8	260.8	253.7	248.7	245.4	241.6
67.5°	293.8	277.7	260.9	245.8	235.5	227.7	221.8	215.8	213.3	209.1	206.6
70°	259.5	242.9	228.1	216.6	206.4	200.6	196.7	192.2	189.6	184.6	182.0
72.5°	222.1	210.0	199.4	190.0	181.7	176.5	171.6	166.1	162.0	156.4	153.8
75°	175.0	164.0	155.7	149.3	144.1	137.1	130.1	124.3	122.4	120.5	119.8
77.5°	129.6	122.6	116.6	111.2	104.8	99.7	98.2	96.9	96.5	95.5	95.5
80°	101.9	95.5	91.0	84.5	80.7	80.7	80.7	79.5	80.1	80.1	80.1
82.5°	75.7	69.9	67.4	65.1	64.3	64.8	64.8	65.1	64.7	65.7	65.2
85°	39.1	39.7	41.0	40.4	41.0	41.0	42.3	41.7	42.3	41.0	42.3
87.5°	16.2	18.3	19.3	20.4	21.4	21.4	22.2	22.3	23.0	23.2	23.3
90°	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.5	25.3	26.1	26.7
92.5°	28.6	30.2	31.7	33.3	34.8	36.4	37.0	37.7	38.4	39.1	39.3
95°	61.8	63.3	65.1	66.7	68.4	70.1	70.9	71.7	72.6	73.5	73.9
97.5°	103.6	104.8	106.1	107.3	108.4	109.7	110.6	111.6	112.6	113.6	114.0
100°	133.9	135.0	136.1	137.1	138.2	139.3	139.9	140.5	141.1	141.8	142.3
102.5°	166.0	167.1	168.4	169.8	171.2	172.6	173.3	173.8	174.5	175.1	175.4
105°	214.8	216.0	217.8	219.8	221.7	223.6	223.6	223.6	223.6	223.6	223.8
107.5°	272.5	273.0	273.8	274.5	275.2	276.1	276.7	277.4	278.1	278.8	278.9
110°	309.6	310.0	310.4	310.8	311.2	311.7	312.5	313.3	314.2	315.0	315.2



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	346.7	346.9	347.0	347.1	347.2	347.2	348.3	349.3	350.3	351.3	351.8
115°	405.1	405.2	404.8	404.4	404.0	403.6	403.7	404.0	404.1	404.4	404.4
117.5°	461.5	461.5	460.9	460.3	459.8	459.3	459.2	459.2	459.1	459.1	458.8
120°	500.5	500.6	499.5	498.5	497.4	496.4	496.2	495.9	495.8	495.5	495.2
122.5°	536.3	536.5	535.9	535.3	534.8	534.3	533.7	533.2	532.6	532.1	531.5
125°	591.7	591.8	591.4	591.0	590.6	590.2	589.3	588.5	587.7	586.8	586.0
127.5°	646.9	647.3	646.9	646.4	646.0	645.5	644.3	643.1	642.0	640.7	639.7
130°	683.1	683.6	683.0	682.3	681.8	681.1	680.3	679.4	678.6	677.8	676.5
132.5°	718.0	718.6	718.1	717.6	717.1	716.7	715.7	714.7	713.7	712.7	711.6
135°	769.5	770.1	769.8	769.6	769.4	769.2	768.3	767.5	766.6	765.8	765.2
137.5°	817.9	818.7	819.3	819.8	820.4	820.9	820.0	819.1	818.2	817.3	816.5
140°	852.0	852.6	852.9	853.0	853.3	853.5	853.3	853.0	852.9	852.6	851.8
142.5°	883.1	883.8	884.2	884.6	884.9	885.3	885.1	884.9	884.7	884.5	883.8
145°	929.0	929.6	930.3	930.8	931.5	932.1	931.9	931.7	931.5	931.3	930.7
147.5°	972.9	973.5	974.1	974.7	975.3	975.9	975.9	975.9	975.9	975.9	975.3
150°	1001.1	1001.5	1001.9	1002.3	1002.7	1003.1	1003.1	1003.1	1003.1	1003.1	1002.6
152.5°	1026.0	1026.4	1026.6	1027.0	1027.2	1027.4	1027.8	1028.1	1028.4	1028.7	1028.4
155°	1061.9	1062.0	1062.3	1062.4	1062.7	1062.8	1063.7	1064.5	1065.4	1066.2	1065.9
157.5°	1093.5	1093.4	1093.6	1093.8	1094.0	1094.1	1095.0	1095.8	1096.7	1097.6	1097.5
160°	1113.3	1113.0	1113.0	1113.0	1113.0	1113.0	1114.1	1115.2	1116.2	1117.3	1117.4
162.5°	1130.8	1130.6	1130.7	1130.9	1131.1	1131.2	1132.3	1133.3	1134.4	1135.5	1135.3
165°	1154.1	1153.8	1153.8	1153.8	1153.8	1153.8	1155.0	1156.3	1157.6	1158.9	1158.7
167.5°	1172.0	1171.7	1171.8	1172.0	1172.2	1172.3	1173.6	1174.9	1176.2	1177.5	1177.5
170°	1182.6	1182.2	1182.2	1182.2	1182.2	1182.2	1183.7	1185.1	1186.7	1188.1	1188.1
172.5°	1191.0	1190.6	1190.6	1190.6	1190.6	1190.6	1191.9	1193.2	1194.5	1195.8	1195.7
175°	1199.7	1199.2	1199.2	1199.2	1199.2	1199.2	1200.5	1201.8	1203.1	1204.3	1204.2
177.5°	1204.0	1203.6	1203.6	1203.6	1203.6	1203.6	1204.6	1205.7	1206.6	1207.6	1207.5
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1426.2	1425.6	1426.2	1424.1	1426.2	1425.6	1426.2	1432.3	1432.3	1432.8	1433.4
5°	1327.1	1326.5	1324.5	1318.7	1324.5	1326.5	1327.1	1329.0	1334.2	1343.1	1340.5
7.5°	1240.6	1239.7	1234.0	1234.2	1234.0	1239.7	1240.6	1245.6	1251.3	1256.9	1263.4
10°	1189.4	1189.9	1182.3	1177.8	1182.3	1189.9	1189.4	1193.8	1202.2	1206.6	1211.1
12.5°	1139.6	1136.7	1130.5	1125.5	1130.5	1136.7	1139.6	1143.0	1154.5	1159.4	1168.1
15°	1074.0	1067.6	1052.2	1053.4	1052.2	1067.6	1074.0	1071.4	1083.0	1089.3	1091.9
17.5°	996.7	992.0	991.7	982.8	991.7	992.0	996.7	1001.8	1011.8	1018.7	1037.1
20°	951.6	948.4	949.7	940.7	949.7	948.4	951.6	961.8	968.2	977.2	992.0
22.5°	916.2	913.0	907.6	904.8	907.6	913.0	916.2	923.4	930.3	942.9	951.0
25°	864.5	859.3	854.2	857.4	854.2	859.3	864.5	868.3	881.1	886.9	898.4
27.5°	812.7	808.9	803.7	803.1	803.7	808.9	812.7	816.4	823.5	833.2	847.0
30°	779.8	776.0	773.5	770.2	773.5	776.0	779.8	783.1	790.1	800.4	810.7
32.5°	746.6	745.8	741.2	740.5	741.2	745.8	746.6	751.8	758.8	768.6	777.3
35°	703.0	699.1	697.8	698.5	697.8	699.1	703.0	705.6	711.9	720.9	729.2
37.5°	661.5	656.4	654.1	651.8	654.1	656.4	661.5	661.9	668.5	674.5	685.7
40°	631.9	626.7	625.4	624.1	625.4	626.7	631.9	631.2	638.2	642.7	653.0
42.5°	598.5	596.5	595.7	593.4	595.7	596.5	598.5	601.9	605.9	612.5	620.2
45°	553.0	552.4	548.5	549.8	548.5	552.4	553.0	554.9	562.0	566.5	573.5
47.5°	505.1	502.2	499.5	501.3	499.5	502.2	505.1	507.6	512.4	517.9	527.3
50°	472.3	471.0	465.2	466.5	465.2	471.0	472.3	474.8	478.0	485.1	493.4
52.5°	439.4	434.6	432.4	431.6	432.4	434.6	439.4	442.1	445.7	453.8	460.1
55°	385.1	379.4	376.7	375.5	376.7	379.4	385.1	389.6	394.8	403.7	410.1
57.5°	331.8	330.3	328.2	329.6	328.2	330.3	331.8	339.2	344.2	351.3	359.1
60°	300.5	300.5	300.5	299.9	300.5	300.5	300.5	307.0	311.4	318.5	326.8
62.5°	276.5	274.9	274.4	275.3	274.4	274.9	276.5	279.2	283.7	288.2	295.5
65°	239.7	239.0	236.4	235.8	236.4	239.0	239.7	241.6	245.4	248.7	253.7
67.5°	205.0	202.6	201.9	201.0	201.9	202.6	205.0	206.6	209.1	213.3	215.8
70°	178.8	177.5	173.7	174.3	173.7	177.5	178.8	182.0	184.6	189.6	192.2
72.5°	150.6	149.3	148.5	147.7	148.5	149.3	150.6	153.8	156.4	162.0	166.1
75°	119.2	118.5	117.9	120.5	117.9	118.5	119.2	119.8	120.5	122.4	124.3
77.5°	95.5	95.5	95.9	94.8	95.9	95.5	95.5	95.5	95.5	96.5	96.9
80°	80.1	80.1	79.5	79.5	79.5	80.1	80.1	80.1	80.1	80.1	79.5
82.5°	64.2	64.7	65.1	64.1	65.1	64.7	64.2	65.2	65.7	64.7	65.1
85°	42.3	41.7	43.0	42.3	43.0	41.7	42.3	42.3	41.0	42.3	41.7
87.5°	24.4	23.5	23.6	24.1	23.6	23.5	24.4	23.3	23.2	23.0	22.3
90°	27.1	27.6	28.0	28.5	28.0	27.6	27.1	26.7	26.1	25.3	24.5
92.5°	39.1	38.8	38.5	38.2	38.5	38.8	39.1	39.3	39.1	38.4	37.7
95°	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.5	72.6	71.7
97.5°	113.9	113.8	113.7	113.7	113.7	113.8	113.9	114.0	113.6	112.6	111.6
100°	142.8	143.2	143.6	144.0	143.6	143.2	142.8	142.3	141.8	141.1	140.5
102.5°	175.3	175.2	175.1	175.0	175.1	175.2	175.3	175.4	175.1	174.5	173.8
105°	224.2	224.6	225.0	225.4	225.0	224.6	224.2	223.8	223.6	223.6	223.6
107.5°	278.7	278.4	278.2	277.9	278.2	278.4	278.7	278.9	278.8	278.1	277.4
110°	314.8	314.4	314.0	313.6	314.0	314.4	314.8	315.2	315.0	314.2	313.3



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	351.7	351.6	351.6	351.5	351.6	351.6	351.7	351.8	351.3	350.3	349.3
115°	404.1	404.0	403.7	403.6	403.7	404.0	404.1	404.4	404.4	404.1	404.0
117.5°	458.2	457.5	457.0	456.4	457.0	457.5	458.2	458.8	459.1	459.1	459.2
120°	494.8	494.4	494.0	493.5	494.0	494.4	494.8	495.2	495.5	495.8	495.9
122.5°	530.9	530.4	529.7	529.1	529.7	530.4	530.9	531.5	532.1	532.6	533.2
125°	585.1	584.2	583.4	582.6	583.4	584.2	585.1	586.0	586.8	587.7	588.5
127.5°	638.7	637.7	636.7	635.9	636.7	637.7	638.7	639.7	640.7	642.0	643.1
130°	675.1	673.6	672.1	670.7	672.1	673.6	675.1	676.5	677.8	678.6	679.4
132.5°	710.5	709.3	708.2	707.0	708.2	709.3	710.5	711.6	712.7	713.7	714.7
135°	764.8	764.3	763.9	763.5	763.9	764.3	764.8	765.2	765.8	766.6	767.5
137.5°	815.7	815.0	814.2	813.3	814.2	815.0	815.7	816.5	817.3	818.2	819.1
140°	850.4	848.9	847.4	846.0	847.4	848.9	850.4	851.8	852.6	852.9	853.0
142.5°	882.6	881.5	880.4	879.3	880.4	881.5	882.6	883.8	884.5	884.7	884.9
145°	929.9	929.0	928.2	927.4	928.2	929.0	929.9	930.7	931.3	931.5	931.7
147.5°	974.0	972.7	971.4	970.2	971.4	972.7	974.0	975.3	975.9	975.9	975.9
150°	1001.3	1000.0	998.7	997.5	998.7	1000.0	1001.3	1002.6	1003.1	1003.1	1003.1
152.5°	1027.3	1026.2	1025.1	1024.0	1025.1	1026.2	1027.3	1028.4	1028.7	1028.4	1028.1
155°	1064.5	1063.0	1061.5	1060.0	1061.5	1063.0	1064.5	1065.9	1066.2	1065.4	1064.5
157.5°	1096.3	1095.1	1094.0	1092.7	1094.0	1095.1	1096.3	1097.5	1097.6	1096.7	1095.8
160°	1116.6	1115.7	1114.8	1114.0	1114.8	1115.7	1116.6	1117.4	1117.3	1116.2	1115.2
162.5°	1133.9	1132.6	1131.2	1129.9	1131.2	1132.6	1133.9	1135.3	1135.5	1134.4	1133.3
165°	1157.2	1155.8	1154.3	1152.8	1154.3	1155.8	1157.2	1158.7	1158.9	1157.6	1156.3
167.5°	1176.2	1174.9	1173.6	1172.3	1173.6	1174.9	1176.2	1177.5	1177.5	1176.2	1174.9
170°	1186.7	1185.1	1183.7	1182.2	1183.7	1185.1	1186.7	1188.1	1188.1	1186.7	1185.1
172.5°	1194.2	1192.7	1191.2	1189.8	1191.2	1192.7	1194.2	1195.7	1195.8	1194.5	1193.2
175°	1202.7	1201.3	1199.8	1198.3	1199.8	1201.3	1202.7	1204.2	1204.3	1203.1	1201.8
177.5°	1206.4	1205.2	1204.0	1202.9	1204.0	1205.2	1206.4	1207.5	1207.6	1206.6	1205.7
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1428.7	1435.9	1443.1	1449.8	1460.0	1464.6	1471.3	1473.8	1481.6	1492.8	1502.0
5°	1341.8	1352.1	1365.5	1376.5	1393.8	1407.2	1422.0	1436.1	1452.7	1476.4	1497.5
7.5°	1268.1	1278.3	1294.5	1314.7	1333.7	1352.8	1373.0	1392.2	1416.0	1450.0	1483.7
10°	1219.4	1231.6	1250.8	1272.6	1296.3	1314.9	1338.6	1363.0	1392.4	1431.6	1471.9
12.5°	1177.4	1186.5	1208.8	1229.6	1256.4	1280.1	1303.3	1331.7	1365.3	1407.0	1455.5
15°	1110.5	1123.3	1145.1	1168.2	1196.4	1221.4	1251.5	1286.1	1318.7	1370.0	1429.0
17.5°	1043.3	1062.8	1085.5	1111.5	1132.5	1166.9	1199.5	1235.1	1275.3	1329.7	1394.4
20°	1000.3	1015.7	1036.8	1074.6	1102.2	1128.5	1158.5	1202.8	1239.9	1301.5	1368.7
22.5°	963.9	975.2	998.9	1030.0	1062.2	1092.6	1123.2	1165.4	1211.2	1269.7	1342.6
25°	910.0	927.9	945.8	968.2	1002.8	1039.3	1072.7	1108.6	1157.3	1219.4	1298.3
27.5°	857.3	873.5	891.2	918.8	945.0	979.2	1014.0	1055.2	1107.4	1173.2	1253.1
30°	823.5	835.6	852.2	887.5	911.2	940.7	981.7	1018.2	1066.9	1136.8	1221.4
32.5°	788.6	804.3	822.6	849.5	878.9	906.9	944.3	983.9	1033.6	1102.4	1189.0
35°	738.8	757.4	776.0	795.9	825.3	854.2	885.6	929.2	979.7	1046.4	1131.6
37.5°	693.1	708.1	723.2	747.8	775.8	803.2	832.5	875.5	923.2	995.1	1073.2
40°	663.9	677.4	688.8	714.5	741.4	770.9	799.7	837.6	888.8	956.1	1031.7
42.5°	632.1	644.5	660.1	681.2	710.1	735.0	763.9	799.6	847.7	916.1	982.4
45°	584.4	598.5	612.0	631.9	660.6	685.0	710.6	744.6	793.9	850.4	909.3
47.5°	534.8	548.9	564.3	583.5	608.6	633.4	659.0	689.1	734.1	789.5	829.2
50°	503.0	514.5	529.9	549.2	572.3	598.5	621.6	654.3	697.2	740.8	775.3
52.5°	470.2	480.7	498.1	518.4	540.0	562.6	587.3	615.3	654.1	695.1	722.6
55°	419.1	431.9	446.6	466.5	487.6	506.9	530.6	559.5	590.2	620.9	639.5
57.5°	371.3	381.9	394.4	414.8	433.2	456.2	477.4	499.9	528.3	551.5	563.6
60°	336.4	346.0	362.1	380.0	397.3	417.2	441.5	463.9	485.8	504.3	513.9
62.5°	303.6	314.8	328.7	345.1	363.9	382.8	404.1	422.9	442.1	458.2	464.7
65°	260.8	269.8	280.1	295.4	310.8	330.0	346.7	365.9	380.0	389.0	394.8
67.5°	221.8	227.7	235.5	245.8	260.9	277.7	293.8	308.8	320.7	326.8	331.9
70°	196.7	200.6	206.4	216.6	228.1	242.9	259.5	270.4	280.7	285.8	290.9
72.5°	171.6	176.5	181.7	190.0	199.4	210.0	222.1	235.5	241.2	247.4	250.5
75°	130.1	137.1	144.1	149.3	155.7	164.0	175.0	183.3	186.5	191.6	192.2
77.5°	98.2	99.7	104.8	111.2	116.6	122.6	129.6	137.0	138.5	141.2	142.9
80°	80.7	80.7	80.7	84.5	91.0	95.5	101.9	105.7	108.3	108.9	109.6
82.5°	64.8	64.8	64.3	65.1	67.4	69.9	75.7	80.1	82.2	81.8	80.4
85°	42.3	41.0	41.0	40.4	41.0	39.7	39.1	41.7	45.5	45.5	44.2
87.5°	22.2	21.4	21.4	20.4	19.3	18.3	16.2	16.3	15.9	17.5	16.6
90°	23.6	22.7	20.0	17.3	14.5	11.8	9.4	7.3	5.1	3.0	1.0
92.5°	37.0	36.4	34.8	33.3	31.7	30.2	28.6	27.2	25.8	24.4	22.9
95°	70.9	70.1	68.4	66.7	65.1	63.3	61.8	60.3	58.9	57.4	55.9
97.5°	110.6	109.7	108.4	107.3	106.1	104.8	103.6	102.6	101.5	100.4	99.3
100°	139.9	139.3	138.2	137.1	136.1	135.0	133.9	132.6	131.3	130.1	128.8
102.5°	173.3	172.6	171.2	169.8	168.4	167.1	166.0	165.2	164.4	163.7	162.9
105°	223.6	223.6	221.7	219.8	217.8	216.0	214.8	214.4	214.0	213.5	213.1
107.5°	276.7	276.1	275.2	274.5	273.8	273.0	272.5	272.2	272.0	271.7	271.5
110°	312.5	311.7	311.2	310.8	310.4	310.0	309.6	309.2	308.7	308.3	307.9



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	348.3	347.2	347.2	347.1	347.0	346.9	346.7	346.5	346.3	346.0	345.8
115°	403.7	403.6	404.0	404.4	404.8	405.2	405.1	404.5	403.8	403.2	402.6
117.5°	459.2	459.3	459.8	460.3	460.9	461.5	461.5	461.1	460.6	460.2	459.8
120°	496.2	496.4	497.4	498.5	499.5	500.6	500.5	499.2	498.0	496.7	495.5
122.5°	533.7	534.3	534.8	535.3	535.9	536.5	536.3	535.3	534.4	533.5	532.6
125°	589.3	590.2	590.6	591.0	591.4	591.8	591.7	591.1	590.4	589.9	589.2
127.5°	644.3	645.5	646.0	646.4	646.9	647.3	646.9	645.6	644.2	642.9	641.5
130°	680.3	681.1	681.8	682.3	683.0	683.6	683.1	681.4	679.7	678.0	676.4
132.5°	715.7	716.7	717.1	717.6	718.1	718.6	718.0	716.2	714.6	712.9	711.2
135°	768.3	769.2	769.4	769.6	769.8	770.1	769.5	768.3	767.0	765.7	764.4
137.5°	820.0	820.9	820.4	819.8	819.3	818.7	817.9	816.8	815.8	814.7	813.8
140°	853.3	853.5	853.3	853.0	852.9	852.6	852.0	851.0	849.9	848.9	847.8
142.5°	885.1	885.3	884.9	884.6	884.2	883.8	883.1	882.1	881.0	880.0	878.9
145°	931.9	932.1	931.5	930.8	930.3	929.6	929.0	928.6	928.2	927.8	927.4
147.5°	975.9	975.9	975.3	974.7	974.1	973.5	972.9	972.1	971.3	970.6	969.8
150°	1003.1	1003.1	1002.7	1002.3	1001.9	1001.5	1001.1	1000.6	1000.2	999.8	999.4
152.5°	1027.8	1027.4	1027.2	1027.0	1026.6	1026.4	1026.0	1025.4	1024.8	1024.3	1023.6
155°	1063.7	1062.8	1062.7	1062.4	1062.3	1062.0	1061.9	1061.9	1061.9	1061.9	1061.9
157.5°	1095.0	1094.1	1094.0	1093.8	1093.6	1093.4	1093.5	1093.7	1094.0	1094.2	1094.5
160°	1114.1	1113.0	1113.0	1113.0	1113.0	1113.0	1113.3	1113.7	1114.1	1114.5	1114.9
162.5°	1132.3	1131.2	1131.1	1130.9	1130.7	1130.6	1130.8	1131.4	1132.0	1132.5	1133.1
165°	1155.0	1153.8	1153.8	1153.8	1153.8	1153.8	1154.1	1154.7	1155.4	1156.0	1156.7
167.5°	1173.6	1172.3	1172.2	1172.0	1171.8	1171.7	1172.0	1172.9	1173.7	1174.5	1175.4
170°	1183.7	1182.2	1182.2	1182.2	1182.2	1182.2	1182.6	1183.5	1184.3	1185.1	1186.0
172.5°	1191.9	1190.6	1190.6	1190.6	1190.6	1190.6	1191.0	1191.8	1192.6	1193.5	1194.3
175°	1200.5	1199.2	1199.2	1199.2	1199.2	1199.2	1199.7	1200.5	1201.3	1202.2	1203.1
177.5°	1204.6	1203.6	1203.6	1203.6	1203.6	1203.6	1204.0	1204.6	1205.3	1206.0	1206.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1505.1	1510.7	1517.9	1528.7	1536.9	1544.1	1545.6	1547.7	1552.8	1561.5	1568.1
5°	1514.8	1529.6	1553.3	1576.4	1601.3	1621.9	1641.1	1654.6	1667.4	1694.3	1716.0
7.5°	1511.8	1544.6	1581.8	1623.2	1665.1	1705.7	1743.4	1777.0	1810.6	1849.8	1894.6
10°	1509.7	1548.2	1598.1	1651.3	1709.7	1766.7	1821.8	1864.8	1914.7	1959.6	2016.6
12.5°	1500.0	1555.3	1615.1	1683.1	1754.8	1820.5	1893.0	1952.4	2009.5	2074.4	2140.6
15°	1487.3	1554.6	1630.2	1720.5	1829.5	1908.9	1983.3	2086.4	2157.0	2227.4	2322.3
17.5°	1464.1	1546.2	1640.7	1758.1	1848.9	1955.7	2067.6	2149.1	2244.1	2343.4	2429.3
20°	1445.6	1541.2	1646.8	1762.2	1878.2	1994.1	2102.5	2199.8	2297.9	2412.6	2483.1
22.5°	1427.2	1521.7	1631.5	1754.0	1878.7	2000.8	2123.4	2237.8	2348.1	2463.9	2553.8
25°	1388.0	1500.2	1619.3	1744.3	1867.3	2001.9	2148.0	2275.5	2412.0	2531.2	2616.4
27.5°	1348.3	1451.0	1569.7	1696.5	1833.2	1992.3	2164.1	2309.1	2445.8	2531.2	2557.9
30°	1312.4	1421.3	1530.2	1659.1	1807.0	1984.5	2167.1	2333.1	2445.3	2482.4	2454.9
32.5°	1275.9	1374.7	1482.5	1614.5	1771.6	1965.6	2171.3	2318.8	2386.3	2357.9	2245.7
35°	1211.8	1300.8	1405.2	1537.2	1718.0	1955.1	2154.3	2254.3	2237.7	2077.5	1866.0
37.5°	1143.0	1215.6	1312.4	1450.4	1662.4	1913.4	2081.5	2096.3	1952.2	1706.2	1461.9
40°	1088.8	1154.1	1253.4	1397.6	1619.3	1872.4	2008.2	1948.6	1725.0	1451.4	1247.7
42.5°	1035.9	1091.0	1186.7	1342.2	1578.3	1816.6	1899.1	1769.3	1511.2	1252.5	1067.2
45°	946.5	998.3	1094.5	1254.0	1494.4	1709.7	1698.8	1473.2	1215.0	1006.7	852.9
47.5°	861.6	907.0	997.2	1160.1	1395.8	1549.5	1447.6	1207.5	988.5	821.4	711.7
50°	801.6	846.5	936.2	1097.1	1316.9	1429.0	1283.5	1052.2	851.7	713.2	626.1
52.5°	744.2	788.1	870.1	1026.8	1221.5	1288.5	1132.3	917.9	750.6	631.2	556.4
55°	663.9	697.2	770.9	920.8	1066.3	1081.7	923.4	744.0	606.2	522.9	471.7
57.5°	582.0	610.7	683.5	802.9	904.9	897.0	746.9	591.7	499.0	437.0	399.8
60°	528.6	556.8	620.9	723.5	800.4	773.5	635.7	510.7	431.3	385.8	356.3
62.5°	478.9	501.0	560.9	635.8	691.1	660.6	543.4	439.9	376.9	338.6	315.3
65°	406.9	424.9	472.9	512.0	542.7	513.3	415.9	344.1	298.6	271.7	255.7
67.5°	338.4	349.8	380.3	394.4	416.0	383.7	312.7	264.6	238.8	216.1	205.0
70°	295.4	303.7	319.8	331.3	337.0	303.7	251.2	216.0	194.1	178.1	171.1
72.5°	252.3	259.7	262.9	272.3	269.4	238.1	201.9	173.9	158.2	147.4	138.3
75°	192.9	196.1	192.9	189.1	180.7	158.9	134.0	119.8	108.3	103.1	100.0
77.5°	140.6	139.6	135.2	129.2	115.0	101.3	87.8	83.1	78.0	75.3	74.2
80°	108.3	105.7	101.9	92.3	80.1	70.5	67.3	64.1	62.1	58.9	58.3
82.5°	80.6	79.1	72.6	64.6	56.0	51.5	48.8	47.7	45.7	44.1	43.9
85°	43.0	41.0	34.0	29.5	28.2	26.9	26.3	26.3	23.7	23.1	23.1
87.5°	14.4	11.8	11.7	10.6	11.1	10.6	11.7	11.2	11.3	11.9	11.0
90°	3.0	5.1	7.3	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.5
92.5°	24.4	25.8	27.2	28.6	30.2	31.7	33.3	34.8	36.4	37.0	37.7
95°	57.4	58.9	60.3	61.8	63.3	65.1	66.7	68.4	70.1	70.9	71.7
97.5°	100.4	101.5	102.6	103.6	104.8	106.1	107.3	108.4	109.7	110.6	111.6
100°	130.1	131.3	132.6	133.9	135.0	136.1	137.1	138.2	139.3	139.9	140.5
102.5°	163.7	164.4	165.2	166.0	167.1	168.4	169.8	171.2	172.6	173.3	173.8
105°	213.5	214.0	214.4	214.8	216.0	217.8	219.8	221.7	223.6	223.6	223.6
107.5°	271.7	272.0	272.2	272.5	273.0	273.8	274.5	275.2	276.1	276.7	277.4
110°	308.3	308.7	309.2	309.6	310.0	310.4	310.8	311.2	311.7	312.5	313.3





TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	346.0	346.3	346.5	346.7	346.9	347.0	347.1	347.2	347.2	348.3	349.3
115°	403.2	403.8	404.5	405.1	405.2	404.8	404.4	404.0	403.6	403.7	404.0
117.5°	460.2	460.6	461.1	461.5	461.5	460.9	460.3	459.8	459.3	459.2	459.2
120°	496.7	498.0	499.2	500.5	500.6	499.5	498.5	497.4	496.4	496.2	495.9
122.5°	533.5	534.4	535.3	536.3	536.5	535.9	535.3	534.8	534.3	533.7	533.2
125°	589.9	590.4	591.1	591.7	591.8	591.4	591.0	590.6	590.2	589.3	588.5
127.5°	642.9	644.2	645.6	646.9	647.3	646.9	646.4	646.0	645.5	644.3	643.1
130°	678.0	679.7	681.4	683.1	683.6	683.0	682.3	681.8	681.1	680.3	679.4
132.5°	712.9	714.6	716.2	718.0	718.6	718.1	717.6	717.1	716.7	715.7	714.7
135°	765.7	767.0	768.3	769.5	770.1	769.8	769.6	769.4	769.2	768.3	767.5
137.5°	814.7	815.8	816.8	817.9	818.7	819.3	819.8	820.4	820.9	820.0	819.1
140°	848.9	849.9	851.0	852.0	852.6	852.9	853.0	853.3	853.5	853.3	853.0
142.5°	880.0	881.0	882.1	883.1	883.8	884.2	884.6	884.9	885.3	885.1	884.9
145°	927.8	928.2	928.6	929.0	929.6	930.3	930.8	931.5	932.1	931.9	931.7
147.5°	970.6	971.3	972.1	972.9	973.5	974.1	974.7	975.3	975.9	975.9	975.9
150°	999.8	1000.2	1000.6	1001.1	1001.5	1001.9	1002.3	1002.7	1003.1	1003.1	1003.1
152.5°	1024.3	1024.8	1025.4	1026.0	1026.4	1026.6	1027.0	1027.2	1027.4	1027.8	1028.1
155°	1061.9	1061.9	1061.9	1061.9	1062.0	1062.3	1062.4	1062.7	1062.8	1063.7	1064.5
157.5°	1094.2	1094.0	1093.7	1093.5	1093.4	1093.6	1093.8	1094.0	1094.1	1095.0	1095.8
160°	1114.5	1114.1	1113.7	1113.3	1113.0	1113.0	1113.0	1113.0	1113.0	1114.1	1115.2
162.5°	1132.5	1132.0	1131.4	1130.8	1130.6	1130.7	1130.9	1131.1	1131.2	1132.3	1133.3
165°	1156.0	1155.4	1154.7	1154.1	1153.8	1153.8	1153.8	1153.8	1153.8	1155.0	1156.3
167.5°	1174.5	1173.7	1172.9	1172.0	1171.7	1171.8	1172.0	1172.2	1172.3	1173.6	1174.9
170°	1185.1	1184.3	1183.5	1182.6	1182.2	1182.2	1182.2	1182.2	1182.2	1183.7	1185.1
172.5°	1193.5	1192.6	1191.8	1191.0	1190.6	1190.6	1190.6	1190.6	1190.6	1191.9	1193.2
175°	1202.2	1201.3	1200.5	1199.7	1199.2	1199.2	1199.2	1199.2	1199.2	1200.5	1201.8
177.5°	1206.0	1205.3	1204.6	1204.0	1203.6	1203.6	1203.6	1203.6	1203.6	1204.6	1205.7
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1578.9	1578.9	1580.9	1588.7	1589.7	1596.4	1594.3
5°	1735.3	1747.4	1751.9	1771.2	1782.7	1787.9	1777.6
7.5°	1926.5	1960.9	1977.1	1997.2	2015.1	2020.5	2006.5
10°	2066.0	2101.8	2131.9	2150.5	2167.8	2179.4	2194.1
12.5°	2200.7	2244.8	2273.5	2299.7	2317.5	2332.2	2334.5
15°	2347.2	2413.9	2464.5	2501.7	2520.3	2529.9	2526.0
17.5°	2495.0	2556.8	2592.8	2630.7	2656.5	2657.8	2658.5
20°	2578.5	2638.8	2680.5	2708.7	2737.5	2736.2	2742.6
22.5°	2634.5	2681.8	2713.8	2734.3	2744.1	2739.3	2740.5
25°	2660.6	2674.7	2669.0	2636.3	2628.0	2597.8	2602.9
27.5°	2525.8	2459.1	2390.2	2301.5	2231.6	2175.6	2178.5
30°	2342.8	2224.9	2090.3	1977.5	1876.2	1848.0	1787.9
32.5°	2086.9	1910.1	1752.5	1647.4	1560.5	1536.9	1484.3
35°	1653.3	1481.6	1319.4	1222.0	1183.6	1129.8	1129.1
37.5°	1285.1	1133.8	1048.1	975.0	936.7	904.2	901.0
40°	1081.0	963.1	898.4	845.9	808.0	783.7	778.0
42.5°	938.5	843.2	782.5	750.0	720.9	708.3	699.0
45°	766.4	702.3	660.0	630.6	617.1	607.5	602.3
47.5°	641.1	598.1	569.3	549.7	538.7	528.6	531.3
50°	572.9	537.6	516.5	497.9	489.6	482.5	483.1
52.5°	518.0	486.4	469.3	455.8	445.5	440.5	438.1
55°	439.6	419.7	402.4	392.8	387.0	380.0	378.1
57.5°	375.0	359.6	345.5	334.6	333.2	326.4	327.3
60°	331.9	319.1	307.6	301.8	297.3	291.6	293.5
62.5°	296.5	285.8	275.3	270.5	266.0	261.8	262.7
65°	242.9	232.6	226.2	223.6	221.7	219.8	217.8
67.5°	193.6	187.3	183.3	177.7	173.8	173.2	171.2
70°	162.7	154.4	147.4	140.3	138.4	137.8	138.4
72.5°	130.4	125.2	123.3	119.8	119.4	117.8	119.0
75°	98.1	96.1	94.8	92.3	92.3	92.3	92.3
77.5°	72.3	71.1	70.4	69.9	69.2	68.3	68.2
80°	56.4	55.8	54.5	54.5	53.8	54.5	53.8
82.5°	42.6	42.4	41.2	41.2	40.5	40.1	40.5
85°	21.8	21.1	22.4	21.1	21.8	20.5	21.8
87.5°	11.2	11.3	11.0	11.1	10.7	11.7	10.8
90°	25.3	26.1	26.7	27.1	27.6	28.0	28.5
92.5°	38.4	39.1	39.3	39.1	38.8	38.5	38.2
95°	72.6	73.5	73.9	73.9	73.9	73.9	73.9
97.5°	112.6	113.6	114.0	113.9	113.8	113.7	113.7
100°	141.1	141.8	142.3	142.8	143.2	143.6	144.0
102.5°	174.5	175.1	175.4	175.3	175.2	175.1	175.0
105°	223.6	223.6	223.8	224.2	224.6	225.0	225.4
107.5°	278.1	278.8	278.9	278.7	278.4	278.2	277.9
110°	314.2	315.0	315.2	314.8	314.4	314.0	313.6



TEST NUMBER: P332385-930

CATALOG NUMBER: S123RDIP-S1165D1195U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	350.3	351.3	351.8	351.7	351.6	351.6	351.5
115°	404.1	404.4	404.4	404.1	404.0	403.7	403.6
117.5°	459.1	459.1	458.8	458.2	457.5	457.0	456.4
120°	495.8	495.5	495.2	494.8	494.4	494.0	493.5
122.5°	532.6	532.1	531.5	530.9	530.4	529.7	529.1
125°	587.7	586.8	586.0	585.1	584.2	583.4	582.6
127.5°	642.0	640.7	639.7	638.7	637.7	636.7	635.9
130°	678.6	677.8	676.5	675.1	673.6	672.1	670.7
132.5°	713.7	712.7	711.6	710.5	709.3	708.2	707.0
135°	766.6	765.8	765.2	764.8	764.3	763.9	763.5
137.5°	818.2	817.3	816.5	815.7	815.0	814.2	813.3
140°	852.9	852.6	851.8	850.4	848.9	847.4	846.0
142.5°	884.7	884.5	883.8	882.6	881.5	880.4	879.3
145°	931.5	931.3	930.7	929.9	929.0	928.2	927.4
147.5°	975.9	975.9	975.3	974.0	972.7	971.4	970.2
150°	1003.1	1003.1	1002.6	1001.3	1000.0	998.7	997.5
152.5°	1028.4	1028.7	1028.4	1027.3	1026.2	1025.1	1024.0
155°	1065.4	1066.2	1065.9	1064.5	1063.0	1061.5	1060.0
157.5°	1096.7	1097.6	1097.5	1096.3	1095.1	1094.0	1092.7
160°	1116.2	1117.3	1117.4	1116.6	1115.7	1114.8	1114.0
162.5°	1134.4	1135.5	1135.3	1133.9	1132.6	1131.2	1129.9
165°	1157.6	1158.9	1158.7	1157.2	1155.8	1154.3	1152.8
167.5°	1176.2	1177.5	1177.5	1176.2	1174.9	1173.6	1172.3
170°	1186.7	1188.1	1188.1	1186.7	1185.1	1183.7	1182.2
172.5°	1194.5	1195.8	1195.7	1194.2	1192.7	1191.2	1189.8
175°	1203.1	1204.3	1204.2	1202.7	1201.3	1199.8	1198.3
177.5°	1206.6	1207.6	1207.5	1206.4	1205.2	1204.0	1202.9
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9

(END OF REPORT)