

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332360-930

Luminaire Tested: **S123RDIP-S1165D365U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020


Test Information

Test Method: LM-79-08
Report Number: P332360-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D365U930-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4910.7 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	98	98	98	88	88	88	80	80	80	76
1	104	100	97	93	99	96	92	90	87	85	82	79	77	76	72	71	69	66
2	96	89	83	78	91	85	79	75	78	73	70	71	67	65	65	62	60	57
3	88	79	72	66	84	75	69	64	69	64	60	63	59	56	58	55	52	49
4	81	70	63	57	77	68	60	55	62	56	52	57	52	49	52	49	45	43
5	75	63	55	49	71	61	53	48	56	50	45	52	47	43	48	43	40	38
6	69	57	49	43	66	55	48	42	51	45	40	47	42	38	44	39	36	33
7	64	52	44	39	61	50	43	38	47	40	36	43	38	34	40	36	32	30
8	60	48	40	35	57	46	39	34	43	37	32	40	34	31	37	32	29	27
9	56	44	36	31	54	42	35	30	39	33	29	37	31	28	34	30	26	24
10	53	40	33	28	50	39	32	28	37	31	26	34	29	25	32	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16113	16113	16113	16113
5°	19207	16181	14249	16181
10°	23981	16088	12873	16088
15°	28149	15924	11739	15924
20°	31416	15678	10775	15678
25°	30914	15419	10183	15419
30°	22222	15181	9573	15181
35°	14837	14870	9179	14870
40°	10932	14497	8769	14497
45°	9168	13842	8369	13842
50°	8090	12983	7812	12983
55°	7096	12001	7047	12001
60°	6318	11063	6456	11063
65°	5547	10055	6006	10055
70°	4356	9155	5485	9155
75°	3839	7993	5011	7993
80°	3335	6794	4928	6794
85°	2692	5459	5224	5459



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.2	3.0
10°-20°	459.9	9.4
20°-30°	722.5	14.7
30°-40°	753.8	15.4
40°-50°	645.1	13.1
50°-60°	491.7	10.0
60°-70°	315.1	6.4
70°-80°	151.6	3.1
80°-90°	41.2	0.8
90°-100°	14.1	0.3
100°-110°	67.2	1.4
110°-120°	161.4	3.3
120°-130°	205.5	4.2
130°-140°	219.6	4.5
140°-150°	205.4	4.2
150°-160°	165.6	3.4
160°-170°	106.9	2.2
170°-180°	36.8	0.8
0°-30°	1329.6	27.1
0°-40°	2083.4	42.4
0°-60°	3220.2	65.6
0°-90°	3728.1	75.9
90°-120°	242.7	4.9
90°-150°	873.2	17.8
90°-180°	1183.0	24.1
0°-180°	4910.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1497	1497	1497	1497	1497	
5°	1778	1498	1319	1498	1778	184
15°	2526	1429	1053	1429	2526	716
25°	2603	1298	857	1298	2603	1119
35°	1129	1132	698	1132	1129	740
45°	602	909	550	909	602	474
55°	378	640	376	640	378	342
65°	218	395	236	395	218	214
75°	92	192	120	192	92	99
85°	22	44	42	44	22	25
90°	9	0	9	0	9	5
95°	11	18	11	18	11	9
105°	13	86	13	86	13	29
115°	169	161	169	161	169	157
125°	232	227	232	227	232	207
135°	286	283	286	283	286	220
145°	329	326	329	326	329	206
155°	359	359	359	359	359	165
165°	378	379	378	379	378	107
175°	386	388	386	388	386	37
180°	388	388	388	388	388	



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1594.3	1596.4	1589.7	1588.7	1580.9	1578.9	1578.9	1568.1	1561.5	1552.8	1547.7
5°	1777.6	1787.9	1782.7	1771.2	1751.9	1747.4	1735.3	1716.0	1694.3	1667.4	1654.6
7.5°	2006.5	2020.5	2015.1	1997.2	1977.1	1960.9	1926.5	1894.6	1849.8	1810.6	1777.0
10°	2194.1	2179.4	2167.8	2150.5	2131.9	2101.8	2066.0	2016.6	1959.6	1914.7	1864.8
12.5°	2334.5	2332.2	2317.5	2299.7	2273.5	2244.8	2200.7	2140.6	2074.4	2009.5	1952.4
15°	2526.0	2529.9	2520.3	2501.7	2464.5	2413.9	2347.2	2322.3	2227.4	2157.0	2086.4
17.5°	2658.5	2657.8	2656.5	2630.7	2592.8	2556.8	2495.0	2429.3	2343.4	2244.1	2149.1
20°	2742.6	2736.2	2737.5	2708.7	2680.5	2638.8	2578.5	2483.1	2412.6	2297.9	2199.8
22.5°	2740.5	2739.3	2744.1	2734.3	2713.8	2681.8	2634.5	2553.8	2463.9	2348.1	2237.8
25°	2602.9	2597.8	2628.0	2636.3	2669.0	2674.7	2660.6	2616.4	2531.2	2412.0	2275.5
27.5°	2178.5	2175.6	2231.6	2301.5	2390.2	2459.1	2525.8	2557.9	2531.2	2445.8	2309.1
30°	1787.9	1848.0	1876.2	1977.5	2090.3	2224.9	2342.8	2454.9	2482.4	2445.3	2333.1
32.5°	1484.3	1536.9	1560.5	1647.4	1752.5	1910.1	2086.9	2245.7	2357.9	2386.3	2318.8
35°	1129.1	1129.8	1183.6	1222.0	1319.4	1481.6	1653.3	1866.0	2077.5	2237.7	2254.3
37.5°	901.0	904.2	936.7	975.0	1048.1	1133.8	1285.1	1461.9	1706.2	1952.2	2096.3
40°	778.0	783.7	808.0	845.9	898.4	963.1	1081.0	1247.7	1451.4	1725.0	1948.6
42.5°	699.0	708.3	720.9	750.0	782.5	843.2	938.5	1067.2	1252.5	1511.2	1769.3
45°	602.3	607.5	617.1	630.6	660.0	702.3	766.4	852.9	1006.7	1215.0	1473.2
47.5°	531.3	528.6	538.7	549.7	569.3	598.1	641.1	711.7	821.4	988.5	1207.5
50°	483.1	482.5	489.6	497.9	516.5	537.6	572.9	626.1	713.2	851.7	1052.2
52.5°	438.1	440.5	445.5	455.8	469.3	486.4	518.0	556.4	631.2	750.6	917.9
55°	378.1	380.0	387.0	392.8	402.4	419.7	439.6	471.7	522.9	606.2	744.0
57.5°	327.3	326.4	333.2	334.6	345.5	359.6	375.0	399.8	437.0	499.0	591.7
60°	293.5	291.6	297.3	301.8	307.6	319.1	331.9	356.3	385.8	431.3	510.7
62.5°	262.7	261.8	266.0	270.5	275.3	285.8	296.5	315.3	338.6	376.9	439.9
65°	217.8	219.8	221.7	223.6	226.2	232.6	242.9	255.7	271.7	298.6	344.1
67.5°	171.2	173.2	173.8	177.7	183.3	187.3	193.6	205.0	216.1	238.8	264.6
70°	138.4	137.8	138.4	140.3	147.4	154.4	162.7	171.1	178.1	194.1	216.0
72.5°	119.0	117.8	119.4	119.8	123.3	125.2	130.4	138.3	147.4	158.2	173.9
75°	92.3	92.3	92.3	92.3	94.8	96.1	98.1	100.0	103.1	108.3	119.8
77.5°	68.2	68.3	69.2	69.9	70.4	71.1	72.3	74.2	75.3	78.0	83.1
80°	53.8	54.5	53.8	54.5	54.5	55.8	56.4	58.3	58.9	62.1	64.1
82.5°	40.5	40.1	40.5	41.2	41.2	42.4	42.6	43.9	44.1	45.7	47.7
85°	21.8	20.5	21.8	21.1	22.4	21.1	21.8	23.1	23.1	23.7	26.3
87.5°	6.8	7.8	6.8	7.3	7.3	7.7	7.7	7.7	8.6	8.1	8.4
90°	8.6	8.5	8.4	8.2	8.2	7.9	7.7	7.4	7.2	6.9	6.1
92.5°	9.5	9.5	9.4	9.3	9.3	9.0	8.6	8.2	7.7	7.3	6.8
95°	10.9	10.9	10.9	10.9	10.9	10.8	10.3	9.9	9.4	9.0	8.2
97.5°	11.9	11.8	11.7	11.7	11.6	11.3	10.8	10.3	9.8	9.3	13.9
100°	12.1	12.1	12.0	11.9	11.8	11.6	11.0	10.5	10.0	9.5	19.5
102.5°	12.3	12.2	12.1	12.0	11.9	12.6	14.2	15.8	17.4	19.0	29.8
105°	12.6	12.6	12.4	12.3	12.1	17.8	29.1	40.4	51.8	63.1	68.9
107.5°	39.8	48.3	56.9	65.5	73.9	82.4	90.7	99.1	107.3	115.6	114.7
110°	79.2	88.4	97.5	106.7	115.9	121.5	123.6	125.7	127.8	130.0	129.2



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	135.9	137.9	139.8	141.7	143.7	144.6	144.6	144.6	144.5	144.5	143.7
115°	169.4	169.2	168.9	168.6	168.4	168.0	167.3	166.6	166.0	165.3	164.8
117.5°	188.2	188.2	188.1	188.0	188.0	187.7	187.2	186.7	186.1	185.6	185.4
120°	201.1	201.1	201.1	201.1	201.1	200.8	200.3	199.8	199.3	198.8	198.6
122.5°	213.8	213.7	213.7	213.6	213.5	213.4	213.0	212.6	212.3	211.9	211.7
125°	231.6	231.5	231.4	231.2	231.1	231.0	230.9	230.7	230.6	230.5	230.2
127.5°	248.8	248.9	249.1	249.2	249.3	249.3	249.1	248.8	248.7	248.4	248.2
130°	259.8	260.0	260.2	260.2	260.4	260.3	260.1	259.8	259.5	259.3	259.0
132.5°	270.0	270.2	270.4	270.5	270.8	270.7	270.4	270.2	269.9	269.7	269.5
135°	285.5	285.7	285.9	286.1	286.3	286.3	286.1	285.9	285.7	285.5	285.3
137.5°	300.1	300.2	300.4	300.4	300.6	300.5	300.2	299.9	299.6	299.3	299.1
140°	308.8	309.0	309.1	309.2	309.3	309.3	309.0	308.8	308.5	308.3	308.1
142.5°	316.9	317.1	317.2	317.5	317.6	317.6	317.4	317.2	317.0	316.8	316.6
145°	329.3	329.3	329.3	329.3	329.3	329.2	329.1	329.0	328.9	328.7	328.6
147.5°	338.5	338.8	339.1	339.4	339.7	339.8	339.7	339.5	339.4	339.2	339.2
150°	345.4	345.6	345.8	346.0	346.2	346.3	346.1	346.0	345.8	345.7	345.6
152.5°	351.0	351.2	351.6	351.9	352.1	352.2	352.0	351.7	351.5	351.2	351.1
155°	358.7	359.1	359.5	359.9	360.2	360.3	360.0	359.6	359.3	359.0	358.9
157.5°	365.2	365.7	366.2	366.7	367.2	367.3	366.9	366.5	366.1	365.7	365.7
160°	369.3	369.8	370.2	370.7	371.1	371.2	370.8	370.4	370.0	369.7	369.7
162.5°	373.2	373.7	374.1	374.5	374.9	374.8	374.4	374.0	373.5	373.1	373.2
165°	378.0	378.5	378.9	379.4	379.8	379.8	379.3	378.7	378.2	377.7	377.7
167.5°	381.4	381.9	382.4	382.9	383.4	383.4	382.9	382.4	381.9	381.4	381.4
170°	383.4	384.0	384.5	385.0	385.5	385.5	385.0	384.5	384.0	383.4	383.4
172.5°	384.6	385.1	385.7	386.3	386.9	386.9	386.4	385.9	385.4	384.8	384.8
175°	386.4	386.9	387.3	387.9	388.4	388.4	388.0	387.5	387.1	386.6	386.5
177.5°	386.9	387.3	387.9	388.4	388.9	389.0	388.6	388.2	387.8	387.3	387.3
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1545.6	1544.1	1536.9	1528.7	1517.9	1510.7	1505.1	1502.0	1492.8	1481.6	1473.8
5°	1641.1	1621.9	1601.3	1576.4	1553.3	1529.6	1514.8	1497.5	1476.4	1452.7	1436.1
7.5°	1743.4	1705.7	1665.1	1623.2	1581.8	1544.6	1511.8	1483.7	1450.0	1416.0	1392.2
10°	1821.8	1766.7	1709.7	1651.3	1598.1	1548.2	1509.7	1471.9	1431.6	1392.4	1363.0
12.5°	1893.0	1820.5	1754.8	1683.1	1615.1	1555.3	1500.0	1455.5	1407.0	1365.3	1331.7
15°	1983.3	1908.9	1829.5	1720.5	1630.2	1554.6	1487.3	1429.0	1370.0	1318.7	1286.1
17.5°	2067.6	1955.7	1848.9	1758.1	1640.7	1546.2	1464.1	1394.4	1329.7	1275.3	1235.1
20°	2102.5	1994.1	1878.2	1762.2	1646.8	1541.2	1445.6	1368.7	1301.5	1239.9	1202.8
22.5°	2123.4	2000.8	1878.7	1754.0	1631.5	1521.7	1427.2	1342.6	1269.7	1211.2	1165.4
25°	2148.0	2001.9	1867.3	1744.3	1619.3	1500.2	1388.0	1298.3	1219.4	1157.3	1108.6
27.5°	2164.1	1992.3	1833.2	1696.5	1569.7	1451.0	1348.3	1253.1	1173.2	1107.4	1055.2
30°	2167.1	1984.5	1807.0	1659.1	1530.2	1421.3	1312.4	1221.4	1136.8	1066.9	1018.2
32.5°	2171.3	1965.6	1771.6	1614.5	1482.5	1374.7	1275.9	1189.0	1102.4	1033.6	983.9
35°	2154.3	1955.1	1718.0	1537.2	1405.2	1300.8	1211.8	1131.6	1046.4	979.7	929.2
37.5°	2081.5	1913.4	1662.4	1450.4	1312.4	1215.6	1143.0	1073.2	995.1	923.2	875.5
40°	2008.2	1872.4	1619.3	1397.6	1253.4	1154.1	1088.8	1031.7	956.1	888.8	837.6
42.5°	1899.1	1816.6	1578.3	1342.2	1186.7	1091.0	1035.9	982.4	916.1	847.7	799.6
45°	1698.8	1709.7	1494.4	1254.0	1094.5	998.3	946.5	909.3	850.4	793.9	744.6
47.5°	1447.6	1549.5	1395.8	1160.1	997.2	907.0	861.6	829.2	789.5	734.1	689.1
50°	1283.5	1429.0	1316.9	1097.1	936.2	846.5	801.6	775.3	740.8	697.2	654.3
52.5°	1132.3	1288.5	1221.5	1026.8	870.1	788.1	744.2	722.6	695.1	654.1	615.3
55°	923.4	1081.7	1066.3	920.8	770.9	697.2	663.9	639.5	620.9	590.2	559.5
57.5°	746.9	897.0	904.9	802.9	683.5	610.7	582.0	563.6	551.5	528.3	499.9
60°	635.7	773.5	800.4	723.5	620.9	556.8	528.6	513.9	504.3	485.8	463.9
62.5°	543.4	660.6	691.1	635.8	560.9	501.0	478.9	464.7	458.2	442.1	422.9
65°	415.9	513.3	542.7	512.0	472.9	424.9	406.9	394.8	389.0	380.0	365.9
67.5°	312.7	383.7	416.0	394.4	380.3	349.8	338.4	331.9	326.8	320.7	308.8
70°	251.2	303.7	337.0	331.3	319.8	303.7	295.4	290.9	285.8	280.7	270.4
72.5°	201.9	238.1	269.4	272.3	262.9	259.7	252.3	250.5	247.4	241.2	235.5
75°	134.0	158.9	180.7	189.1	192.9	196.1	192.9	192.2	191.6	186.5	183.3
77.5°	87.8	101.3	115.0	129.2	135.2	139.6	140.6	142.9	141.2	138.5	137.0
80°	67.3	70.5	80.1	92.3	101.9	105.7	108.3	109.6	108.9	108.3	105.7
82.5°	48.8	51.5	56.0	64.6	72.6	79.1	80.6	80.4	81.8	82.2	80.1
85°	26.3	26.9	28.2	29.5	34.0	41.0	43.0	44.2	45.5	45.5	41.7
87.5°	9.2	8.6	9.5	9.3	10.7	11.1	14.0	16.5	17.1	15.2	15.3
90°	5.2	4.4	3.6	2.9	2.2	1.5	0.9	0.3	0.9	1.5	2.2
92.5°	6.1	5.5	4.9	4.6	4.8	5.0	5.2	5.4	5.2	5.0	4.8
95°	7.5	6.8	6.1	7.1	9.7	12.3	14.9	17.6	14.9	12.3	9.7
97.5°	18.5	23.1	27.7	30.6	31.8	32.9	34.2	35.3	34.2	32.9	31.8
100°	29.5	39.5	49.5	53.8	52.5	51.3	50.0	48.7	50.0	51.3	52.5
102.5°	40.8	51.7	62.6	67.6	66.7	65.7	64.8	63.9	64.8	65.7	66.7
105°	74.6	80.4	86.2	88.7	88.0	87.2	86.6	85.9	86.6	87.2	88.0
107.5°	113.8	112.9	112.0	111.3	110.7	110.1	109.6	109.0	109.6	110.1	110.7
110°	128.5	127.8	127.1	126.5	126.0	125.5	125.0	124.5	125.0	125.5	126.0



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	143.1	142.4	141.6	141.0	140.6	140.1	139.7	139.2	139.7	140.1	140.6
115°	164.2	163.6	163.1	162.6	162.2	161.8	161.4	161.0	161.4	161.8	162.2
117.5°	185.1	184.7	184.5	184.1	183.6	183.1	182.7	182.2	182.7	183.1	183.6
120°	198.4	198.2	198.0	197.6	197.1	196.5	195.9	195.3	195.9	196.5	197.1
122.5°	211.4	211.2	210.9	210.6	210.1	209.6	209.2	208.7	209.2	209.6	210.1
125°	230.0	229.8	229.4	229.1	228.5	228.0	227.6	227.1	227.6	228.0	228.5
127.5°	247.9	247.5	247.2	246.8	246.3	245.8	245.3	244.8	245.3	245.8	246.3
130°	258.8	258.5	258.3	257.9	257.4	256.8	256.3	255.8	256.3	256.8	257.4
132.5°	269.3	269.0	268.8	268.5	268.0	267.5	266.9	266.4	266.9	267.5	268.0
135°	285.0	284.7	284.5	284.1	283.8	283.4	283.0	282.7	283.0	283.4	283.8
137.5°	299.0	298.9	298.7	298.4	297.9	297.4	296.9	296.4	296.9	297.4	297.9
140°	307.9	307.7	307.5	307.2	306.8	306.5	306.1	305.7	306.1	306.5	306.8
142.5°	316.4	316.3	316.0	315.8	315.4	315.0	314.6	314.2	314.6	315.0	315.4
145°	328.5	328.3	328.2	327.9	327.5	327.0	326.6	326.1	326.6	327.0	327.5
147.5°	339.0	338.9	338.8	338.5	338.3	337.9	337.7	337.4	337.7	337.9	338.3
150°	345.4	345.4	345.2	345.0	344.9	344.6	344.5	344.3	344.5	344.6	344.9
152.5°	351.1	351.0	351.0	350.8	350.7	350.7	350.6	350.5	350.6	350.7	350.7
155°	358.8	358.8	358.7	358.7	358.9	359.0	359.1	359.3	359.1	359.0	358.9
157.5°	365.8	365.9	366.0	366.0	366.0	366.1	366.1	366.1	366.1	366.1	366.0
160°	369.7	369.8	369.9	370.0	370.0	370.1	370.1	370.2	370.1	370.1	370.0
162.5°	373.2	373.2	373.3	373.5	373.7	373.8	374.0	374.1	374.0	373.8	373.7
165°	377.8	377.9	378.0	378.1	378.3	378.5	378.6	378.9	378.6	378.5	378.3
167.5°	381.4	381.4	381.4	381.5	381.8	382.0	382.3	382.5	382.3	382.0	381.8
170°	383.4	383.4	383.4	383.6	383.8	384.1	384.3	384.6	384.3	384.1	383.8
172.5°	384.7	384.7	384.7	384.7	385.1	385.4	385.7	386.0	385.7	385.4	385.1
175°	386.5	386.5	386.4	386.5	386.9	387.1	387.4	387.8	387.4	387.1	386.9
177.5°	387.2	387.2	387.1	387.2	387.5	387.8	388.0	388.2	388.0	387.8	387.5
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1471.3	1464.6	1460.0	1449.8	1443.1	1435.9	1428.7	1433.4	1432.8	1432.3	1432.3
5°	1422.0	1407.2	1393.8	1376.5	1365.5	1352.1	1341.8	1340.5	1343.1	1334.2	1329.0
7.5°	1373.0	1352.8	1333.7	1314.7	1294.5	1278.3	1268.1	1263.4	1256.9	1251.3	1245.6
10°	1338.6	1314.9	1296.3	1272.6	1250.8	1231.6	1219.4	1211.1	1206.6	1202.2	1193.8
12.5°	1303.3	1280.1	1256.4	1229.6	1208.8	1186.5	1177.4	1168.1	1159.4	1154.5	1143.0
15°	1251.5	1221.4	1196.4	1168.2	1145.1	1123.3	1110.5	1091.9	1089.3	1083.0	1071.4
17.5°	1199.5	1166.9	1132.5	1111.5	1085.5	1062.8	1043.3	1037.1	1018.7	1011.8	1001.8
20°	1158.5	1128.5	1102.2	1074.6	1036.8	1015.7	1000.3	992.0	977.2	968.2	961.8
22.5°	1123.2	1092.6	1062.2	1030.0	998.9	975.2	963.9	951.0	942.9	930.3	923.4
25°	1072.7	1039.3	1002.8	968.2	945.8	927.9	910.0	898.4	886.9	881.1	868.3
27.5°	1014.0	979.2	945.0	918.8	891.2	873.5	857.3	847.0	833.2	823.5	816.4
30°	981.7	940.7	911.2	887.5	852.2	835.6	823.5	810.7	800.4	790.1	783.1
32.5°	944.3	906.9	878.9	849.5	822.6	804.3	788.6	777.3	768.6	758.8	751.8
35°	885.6	854.2	825.3	795.9	776.0	757.4	738.8	729.2	720.9	711.9	705.6
37.5°	832.5	803.2	775.8	747.8	723.2	708.1	693.1	685.7	674.5	668.5	661.9
40°	799.7	770.9	741.4	714.5	688.8	677.4	663.9	653.0	642.7	638.2	631.2
42.5°	763.9	735.0	710.1	681.2	660.1	644.5	632.1	620.2	612.5	605.9	601.9
45°	710.6	685.0	660.6	631.9	612.0	598.5	584.4	573.5	566.5	562.0	554.9
47.5°	659.0	633.4	608.6	583.5	564.3	548.9	534.8	527.3	517.9	512.4	507.6
50°	621.6	598.5	572.3	549.2	529.9	514.5	503.0	493.4	485.1	478.0	474.8
52.5°	587.3	562.6	540.0	518.4	498.1	480.7	470.2	460.1	453.8	445.7	442.1
55°	530.6	506.9	487.6	466.5	446.6	431.9	419.1	410.1	403.7	394.8	389.6
57.5°	477.4	456.2	433.2	414.8	394.4	381.9	371.3	359.1	351.3	344.2	339.2
60°	441.5	417.2	397.3	380.0	362.1	346.0	336.4	326.8	318.5	311.4	307.0
62.5°	404.1	382.8	363.9	345.1	328.7	314.8	303.6	295.5	288.2	283.7	279.2
65°	346.7	330.0	310.8	295.4	280.1	269.8	260.8	253.7	248.7	245.4	241.6
67.5°	293.8	277.7	260.9	245.8	235.5	227.7	221.8	215.8	213.3	209.1	206.6
70°	259.5	242.9	228.1	216.6	206.4	200.6	196.7	192.2	189.6	184.6	182.0
72.5°	222.1	210.0	199.4	190.0	181.7	176.5	171.6	166.1	162.0	156.4	153.8
75°	175.0	164.0	155.7	149.3	144.1	137.1	130.1	124.3	122.4	120.5	119.8
77.5°	129.6	122.6	116.6	111.2	104.8	99.7	98.2	96.9	96.5	95.5	95.5
80°	101.9	95.5	91.0	84.5	80.7	80.7	80.7	79.5	80.1	80.1	80.1
82.5°	75.7	69.9	67.4	65.1	64.3	64.8	64.8	65.1	64.7	65.7	65.2
85°	39.1	39.7	41.0	40.4	41.0	41.0	42.3	41.7	42.3	41.0	42.3
87.5°	14.9	16.6	17.3	17.9	18.7	18.3	18.8	18.9	19.5	19.6	19.6
90°	2.9	3.6	4.4	5.2	6.1	6.9	7.2	7.4	7.7	7.9	8.2
92.5°	4.6	4.9	5.5	6.1	6.8	7.3	7.7	8.2	8.6	9.0	9.3
95°	7.1	6.1	6.8	7.5	8.2	9.0	9.4	9.9	10.3	10.8	10.9
97.5°	30.6	27.7	23.1	18.5	13.9	9.3	9.8	10.3	10.8	11.3	11.6
100°	53.8	49.5	39.5	29.5	19.5	9.5	10.0	10.5	11.0	11.6	11.8
102.5°	67.6	62.6	51.7	40.8	29.8	19.0	17.4	15.8	14.2	12.6	11.9
105°	88.7	86.2	80.4	74.6	68.9	63.1	51.8	40.4	29.1	17.8	12.1
107.5°	111.3	112.0	112.9	113.8	114.7	115.6	107.3	99.1	90.7	82.4	73.9
110°	126.5	127.1	127.8	128.5	129.2	130.0	127.8	125.7	123.6	121.5	115.9



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	141.0	141.6	142.4	143.1	143.7	144.5	144.5	144.6	144.6	144.6	143.7
115°	162.6	163.1	163.6	164.2	164.8	165.3	166.0	166.6	167.3	168.0	168.4
117.5°	184.1	184.5	184.7	185.1	185.4	185.6	186.1	186.7	187.2	187.7	188.0
120°	197.6	198.0	198.2	198.4	198.6	198.8	199.3	199.8	200.3	200.8	201.1
122.5°	210.6	210.9	211.2	211.4	211.7	211.9	212.3	212.6	213.0	213.4	213.5
125°	229.1	229.4	229.8	230.0	230.2	230.5	230.6	230.7	230.9	231.0	231.1
127.5°	246.8	247.2	247.5	247.9	248.2	248.4	248.7	248.8	249.1	249.3	249.3
130°	257.9	258.3	258.5	258.8	259.0	259.3	259.5	259.8	260.1	260.3	260.4
132.5°	268.5	268.8	269.0	269.3	269.5	269.7	269.9	270.2	270.4	270.7	270.8
135°	284.1	284.5	284.7	285.0	285.3	285.5	285.7	285.9	286.1	286.3	286.3
137.5°	298.4	298.7	298.9	299.0	299.1	299.3	299.6	299.9	300.2	300.5	300.6
140°	307.2	307.5	307.7	307.9	308.1	308.3	308.5	308.8	309.0	309.3	309.3
142.5°	315.8	316.0	316.3	316.4	316.6	316.8	317.0	317.2	317.4	317.6	317.6
145°	327.9	328.2	328.3	328.5	328.6	328.7	328.9	329.0	329.1	329.2	329.3
147.5°	338.5	338.8	338.9	339.0	339.2	339.2	339.4	339.5	339.7	339.8	339.7
150°	345.0	345.2	345.4	345.4	345.6	345.7	345.8	346.0	346.1	346.3	346.2
152.5°	350.8	351.0	351.0	351.1	351.1	351.2	351.5	351.7	352.0	352.2	352.1
155°	358.7	358.7	358.8	358.8	358.9	359.0	359.3	359.6	360.0	360.3	360.2
157.5°	366.0	366.0	365.9	365.8	365.7	365.7	366.1	366.5	366.9	367.3	367.2
160°	370.0	369.9	369.8	369.7	369.7	369.7	370.0	370.4	370.8	371.2	371.1
162.5°	373.5	373.3	373.2	373.2	373.2	373.1	373.5	374.0	374.4	374.8	374.9
165°	378.1	378.0	377.9	377.8	377.7	377.7	378.2	378.7	379.3	379.8	379.8
167.5°	381.5	381.4	381.4	381.4	381.4	381.4	381.9	382.4	382.9	383.4	383.4
170°	383.6	383.4	383.4	383.4	383.4	383.4	384.0	384.5	385.0	385.5	385.5
172.5°	384.7	384.7	384.7	384.7	384.8	384.8	385.4	385.9	386.4	386.9	386.9
175°	386.5	386.4	386.5	386.5	386.5	386.6	387.1	387.5	388.0	388.4	388.4
177.5°	387.2	387.1	387.2	387.2	387.3	387.3	387.8	388.2	388.6	389.0	388.9
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1426.2	1425.6	1426.2	1424.1	1426.2	1425.6	1426.2	1432.3	1432.3	1432.8	1433.4
5°	1327.1	1326.5	1324.5	1318.7	1324.5	1326.5	1327.1	1329.0	1334.2	1343.1	1340.5
7.5°	1240.6	1239.7	1234.0	1234.2	1234.0	1239.7	1240.6	1245.6	1251.3	1256.9	1263.4
10°	1189.4	1189.9	1182.3	1177.8	1182.3	1189.9	1189.4	1193.8	1202.2	1206.6	1211.1
12.5°	1139.6	1136.7	1130.5	1125.5	1130.5	1136.7	1139.6	1143.0	1154.5	1159.4	1168.1
15°	1074.0	1067.6	1052.2	1053.4	1052.2	1067.6	1074.0	1071.4	1083.0	1089.3	1091.9
17.5°	996.7	992.0	991.7	982.8	991.7	992.0	996.7	1001.8	1011.8	1018.7	1037.1
20°	951.6	948.4	949.7	940.7	949.7	948.4	951.6	961.8	968.2	977.2	992.0
22.5°	916.2	913.0	907.6	904.8	907.6	913.0	916.2	923.4	930.3	942.9	951.0
25°	864.5	859.3	854.2	857.4	854.2	859.3	864.5	868.3	881.1	886.9	898.4
27.5°	812.7	808.9	803.7	803.1	803.7	808.9	812.7	816.4	823.5	833.2	847.0
30°	779.8	776.0	773.5	770.2	773.5	776.0	779.8	783.1	790.1	800.4	810.7
32.5°	746.6	745.8	741.2	740.5	741.2	745.8	746.6	751.8	758.8	768.6	777.3
35°	703.0	699.1	697.8	698.5	697.8	699.1	703.0	705.6	711.9	720.9	729.2
37.5°	661.5	656.4	654.1	651.8	654.1	656.4	661.5	661.9	668.5	674.5	685.7
40°	631.9	626.7	625.4	624.1	625.4	626.7	631.9	631.2	638.2	642.7	653.0
42.5°	598.5	596.5	595.7	593.4	595.7	596.5	598.5	601.9	605.9	612.5	620.2
45°	553.0	552.4	548.5	549.8	548.5	552.4	553.0	554.9	562.0	566.5	573.5
47.5°	505.1	502.2	499.5	501.3	499.5	502.2	505.1	507.6	512.4	517.9	527.3
50°	472.3	471.0	465.2	466.5	465.2	471.0	472.3	474.8	478.0	485.1	493.4
52.5°	439.4	434.6	432.4	431.6	432.4	434.6	439.4	442.1	445.7	453.8	460.1
55°	385.1	379.4	376.7	375.5	376.7	379.4	385.1	389.6	394.8	403.7	410.1
57.5°	331.8	330.3	328.2	329.6	328.2	330.3	331.8	339.2	344.2	351.3	359.1
60°	300.5	300.5	300.5	299.9	300.5	300.5	300.5	307.0	311.4	318.5	326.8
62.5°	276.5	274.9	274.4	275.3	274.4	274.9	276.5	279.2	283.7	288.2	295.5
65°	239.7	239.0	236.4	235.8	236.4	239.0	239.7	241.6	245.4	248.7	253.7
67.5°	205.0	202.6	201.9	201.0	201.9	202.6	205.0	206.6	209.1	213.3	215.8
70°	178.8	177.5	173.7	174.3	173.7	177.5	178.8	182.0	184.6	189.6	192.2
72.5°	150.6	149.3	148.5	147.7	148.5	149.3	150.6	153.8	156.4	162.0	166.1
75°	119.2	118.5	117.9	120.5	117.9	118.5	119.2	119.8	120.5	122.4	124.3
77.5°	95.5	95.5	95.9	94.8	95.9	95.5	95.5	95.5	95.5	96.5	96.9
80°	80.1	80.1	79.5	79.5	79.5	80.1	80.1	80.1	80.1	80.1	79.5
82.5°	64.2	64.7	65.1	64.1	65.1	64.7	64.2	65.2	65.7	64.7	65.1
85°	42.3	41.7	43.0	42.3	43.0	41.7	42.3	42.3	41.0	42.3	41.7
87.5°	20.6	19.6	19.6	20.2	19.6	19.6	20.6	19.6	19.6	19.5	18.9
90°	8.2	8.4	8.5	8.6	8.5	8.4	8.2	8.2	7.9	7.7	7.4
92.5°	9.3	9.4	9.5	9.5	9.5	9.4	9.3	9.3	9.0	8.6	8.2
95°	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.8	10.3	9.9
97.5°	11.7	11.7	11.8	11.9	11.8	11.7	11.7	11.6	11.3	10.8	10.3
100°	11.9	12.0	12.1	12.1	12.1	12.0	11.9	11.8	11.6	11.0	10.5
102.5°	12.0	12.1	12.2	12.3	12.2	12.1	12.0	11.9	12.6	14.2	15.8
105°	12.3	12.4	12.6	12.6	12.6	12.4	12.3	12.1	17.8	29.1	40.4
107.5°	65.5	56.9	48.3	39.8	48.3	56.9	65.5	73.9	82.4	90.7	99.1
110°	106.7	97.5	88.4	79.2	88.4	97.5	106.7	115.9	121.5	123.6	125.7



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	141.7	139.8	137.9	135.9	137.9	139.8	141.7	143.7	144.6	144.6	144.6
115°	168.6	168.9	169.2	169.4	169.2	168.9	168.6	168.4	168.0	167.3	166.6
117.5°	188.0	188.1	188.2	188.2	188.2	188.1	188.0	188.0	187.7	187.2	186.7
120°	201.1	201.1	201.1	201.1	201.1	201.1	201.1	201.1	200.8	200.3	199.8
122.5°	213.6	213.7	213.7	213.8	213.7	213.7	213.6	213.5	213.4	213.0	212.6
125°	231.2	231.4	231.5	231.6	231.5	231.4	231.2	231.1	231.0	230.9	230.7
127.5°	249.2	249.1	248.9	248.8	248.9	249.1	249.2	249.3	249.3	249.1	248.8
130°	260.2	260.2	260.0	259.8	260.0	260.2	260.2	260.4	260.3	260.1	259.8
132.5°	270.5	270.4	270.2	270.0	270.2	270.4	270.5	270.8	270.7	270.4	270.2
135°	286.1	285.9	285.7	285.5	285.7	285.9	286.1	286.3	286.3	286.1	285.9
137.5°	300.4	300.4	300.2	300.1	300.2	300.4	300.4	300.6	300.5	300.2	299.9
140°	309.2	309.1	309.0	308.8	309.0	309.1	309.2	309.3	309.3	309.0	308.8
142.5°	317.5	317.2	317.1	316.9	317.1	317.2	317.5	317.6	317.6	317.4	317.2
145°	329.3	329.3	329.3	329.3	329.3	329.3	329.3	329.3	329.2	329.1	329.0
147.5°	339.4	339.1	338.8	338.5	338.8	339.1	339.4	339.7	339.8	339.7	339.5
150°	346.0	345.8	345.6	345.4	345.6	345.8	346.0	346.2	346.3	346.1	346.0
152.5°	351.9	351.6	351.2	351.0	351.2	351.6	351.9	352.1	352.2	352.0	351.7
155°	359.9	359.5	359.1	358.7	359.1	359.5	359.9	360.2	360.3	360.0	359.6
157.5°	366.7	366.2	365.7	365.2	365.7	366.2	366.7	367.2	367.3	366.9	366.5
160°	370.7	370.2	369.8	369.3	369.8	370.2	370.7	371.1	371.2	370.8	370.4
162.5°	374.5	374.1	373.7	373.2	373.7	374.1	374.5	374.9	374.8	374.4	374.0
165°	379.4	378.9	378.5	378.0	378.5	378.9	379.4	379.8	379.8	379.3	378.7
167.5°	382.9	382.4	381.9	381.4	381.9	382.4	382.9	383.4	383.4	382.9	382.4
170°	385.0	384.5	384.0	383.4	384.0	384.5	385.0	385.5	385.5	385.0	384.5
172.5°	386.3	385.7	385.1	384.6	385.1	385.7	386.3	386.9	386.9	386.4	385.9
175°	387.9	387.3	386.9	386.4	386.9	387.3	387.9	388.4	388.4	388.0	387.5
177.5°	388.4	387.9	387.3	386.9	387.3	387.9	388.4	388.9	389.0	388.6	388.2
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1428.7	1435.9	1443.1	1449.8	1460.0	1464.6	1471.3	1473.8	1481.6	1492.8	1502.0
5°	1341.8	1352.1	1365.5	1376.5	1393.8	1407.2	1422.0	1436.1	1452.7	1476.4	1497.5
7.5°	1268.1	1278.3	1294.5	1314.7	1333.7	1352.8	1373.0	1392.2	1416.0	1450.0	1483.7
10°	1219.4	1231.6	1250.8	1272.6	1296.3	1314.9	1338.6	1363.0	1392.4	1431.6	1471.9
12.5°	1177.4	1186.5	1208.8	1229.6	1256.4	1280.1	1303.3	1331.7	1365.3	1407.0	1455.5
15°	1110.5	1123.3	1145.1	1168.2	1196.4	1221.4	1251.5	1286.1	1318.7	1370.0	1429.0
17.5°	1043.3	1062.8	1085.5	1111.5	1132.5	1166.9	1199.5	1235.1	1275.3	1329.7	1394.4
20°	1000.3	1015.7	1036.8	1074.6	1102.2	1128.5	1158.5	1202.8	1239.9	1301.5	1368.7
22.5°	963.9	975.2	998.9	1030.0	1062.2	1092.6	1123.2	1165.4	1211.2	1269.7	1342.6
25°	910.0	927.9	945.8	968.2	1002.8	1039.3	1072.7	1108.6	1157.3	1219.4	1298.3
27.5°	857.3	873.5	891.2	918.8	945.0	979.2	1014.0	1055.2	1107.4	1173.2	1253.1
30°	823.5	835.6	852.2	887.5	911.2	940.7	981.7	1018.2	1066.9	1136.8	1221.4
32.5°	788.6	804.3	822.6	849.5	878.9	906.9	944.3	983.9	1033.6	1102.4	1189.0
35°	738.8	757.4	776.0	795.9	825.3	854.2	885.6	929.2	979.7	1046.4	1131.6
37.5°	693.1	708.1	723.2	747.8	775.8	803.2	832.5	875.5	923.2	995.1	1073.2
40°	663.9	677.4	688.8	714.5	741.4	770.9	799.7	837.6	888.8	956.1	1031.7
42.5°	632.1	644.5	660.1	681.2	710.1	735.0	763.9	799.6	847.7	916.1	982.4
45°	584.4	598.5	612.0	631.9	660.6	685.0	710.6	744.6	793.9	850.4	909.3
47.5°	534.8	548.9	564.3	583.5	608.6	633.4	659.0	689.1	734.1	789.5	829.2
50°	503.0	514.5	529.9	549.2	572.3	598.5	621.6	654.3	697.2	740.8	775.3
52.5°	470.2	480.7	498.1	518.4	540.0	562.6	587.3	615.3	654.1	695.1	722.6
55°	419.1	431.9	446.6	466.5	487.6	506.9	530.6	559.5	590.2	620.9	639.5
57.5°	371.3	381.9	394.4	414.8	433.2	456.2	477.4	499.9	528.3	551.5	563.6
60°	336.4	346.0	362.1	380.0	397.3	417.2	441.5	463.9	485.8	504.3	513.9
62.5°	303.6	314.8	328.7	345.1	363.9	382.8	404.1	422.9	442.1	458.2	464.7
65°	260.8	269.8	280.1	295.4	310.8	330.0	346.7	365.9	380.0	389.0	394.8
67.5°	221.8	227.7	235.5	245.8	260.9	277.7	293.8	308.8	320.7	326.8	331.9
70°	196.7	200.6	206.4	216.6	228.1	242.9	259.5	270.4	280.7	285.8	290.9
72.5°	171.6	176.5	181.7	190.0	199.4	210.0	222.1	235.5	241.2	247.4	250.5
75°	130.1	137.1	144.1	149.3	155.7	164.0	175.0	183.3	186.5	191.6	192.2
77.5°	98.2	99.7	104.8	111.2	116.6	122.6	129.6	137.0	138.5	141.2	142.9
80°	80.7	80.7	80.7	84.5	91.0	95.5	101.9	105.7	108.3	108.9	109.6
82.5°	64.8	64.8	64.3	65.1	67.4	69.9	75.7	80.1	82.2	81.8	80.4
85°	42.3	41.0	41.0	40.4	41.0	39.7	39.1	41.7	45.5	45.5	44.2
87.5°	18.8	18.3	18.7	17.9	17.3	16.6	14.9	15.3	15.2	17.1	16.5
90°	7.2	6.9	6.1	5.2	4.4	3.6	2.9	2.2	1.5	0.9	0.3
92.5°	7.7	7.3	6.8	6.1	5.5	4.9	4.6	4.8	5.0	5.2	5.4
95°	9.4	9.0	8.2	7.5	6.8	6.1	7.1	9.7	12.3	14.9	17.6
97.5°	9.8	9.3	13.9	18.5	23.1	27.7	30.6	31.8	32.9	34.2	35.3
100°	10.0	9.5	19.5	29.5	39.5	49.5	53.8	52.5	51.3	50.0	48.7
102.5°	17.4	19.0	29.8	40.8	51.7	62.6	67.6	66.7	65.7	64.8	63.9
105°	51.8	63.1	68.9	74.6	80.4	86.2	88.7	88.0	87.2	86.6	85.9
107.5°	107.3	115.6	114.7	113.8	112.9	112.0	111.3	110.7	110.1	109.6	109.0
110°	127.8	130.0	129.2	128.5	127.8	127.1	126.5	126.0	125.5	125.0	124.5



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	144.5	144.5	143.7	143.1	142.4	141.6	141.0	140.6	140.1	139.7	139.2
115°	166.0	165.3	164.8	164.2	163.6	163.1	162.6	162.2	161.8	161.4	161.0
117.5°	186.1	185.6	185.4	185.1	184.7	184.5	184.1	183.6	183.1	182.7	182.2
120°	199.3	198.8	198.6	198.4	198.2	198.0	197.6	197.1	196.5	195.9	195.3
122.5°	212.3	211.9	211.7	211.4	211.2	210.9	210.6	210.1	209.6	209.2	208.7
125°	230.6	230.5	230.2	230.0	229.8	229.4	229.1	228.5	228.0	227.6	227.1
127.5°	248.7	248.4	248.2	247.9	247.5	247.2	246.8	246.3	245.8	245.3	244.8
130°	259.5	259.3	259.0	258.8	258.5	258.3	257.9	257.4	256.8	256.3	255.8
132.5°	269.9	269.7	269.5	269.3	269.0	268.8	268.5	268.0	267.5	266.9	266.4
135°	285.7	285.5	285.3	285.0	284.7	284.5	284.1	283.8	283.4	283.0	282.7
137.5°	299.6	299.3	299.1	299.0	298.9	298.7	298.4	297.9	297.4	296.9	296.4
140°	308.5	308.3	308.1	307.9	307.7	307.5	307.2	306.8	306.5	306.1	305.7
142.5°	317.0	316.8	316.6	316.4	316.3	316.0	315.8	315.4	315.0	314.6	314.2
145°	328.9	328.7	328.6	328.5	328.3	328.2	327.9	327.5	327.0	326.6	326.1
147.5°	339.4	339.2	339.2	339.0	338.9	338.8	338.5	338.3	337.9	337.7	337.4
150°	345.8	345.7	345.6	345.4	345.4	345.2	345.0	344.9	344.6	344.5	344.3
152.5°	351.5	351.2	351.1	351.1	351.0	351.0	350.8	350.7	350.7	350.6	350.5
155°	359.3	359.0	358.9	358.8	358.8	358.7	358.7	358.9	359.0	359.1	359.3
157.5°	366.1	365.7	365.7	365.8	365.9	366.0	366.0	366.0	366.1	366.1	366.1
160°	370.0	369.7	369.7	369.7	369.8	369.9	370.0	370.0	370.1	370.1	370.2
162.5°	373.5	373.1	373.2	373.2	373.2	373.3	373.5	373.7	373.8	374.0	374.1
165°	378.2	377.7	377.7	377.8	377.9	378.0	378.1	378.3	378.5	378.6	378.9
167.5°	381.9	381.4	381.4	381.4	381.4	381.4	381.5	381.8	382.0	382.3	382.5
170°	384.0	383.4	383.4	383.4	383.4	383.4	383.6	383.8	384.1	384.3	384.6
172.5°	385.4	384.8	384.8	384.7	384.7	384.7	384.7	385.1	385.4	385.7	386.0
175°	387.1	386.6	386.5	386.5	386.5	386.4	386.5	386.9	387.1	387.4	387.8
177.5°	387.8	387.3	387.3	387.2	387.2	387.1	387.2	387.5	387.8	388.0	388.2
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1505.1	1510.7	1517.9	1528.7	1536.9	1544.1	1545.6	1547.7	1552.8	1561.5	1568.1
5°	1514.8	1529.6	1553.3	1576.4	1601.3	1621.9	1641.1	1654.6	1667.4	1694.3	1716.0
7.5°	1511.8	1544.6	1581.8	1623.2	1665.1	1705.7	1743.4	1777.0	1810.6	1849.8	1894.6
10°	1509.7	1548.2	1598.1	1651.3	1709.7	1766.7	1821.8	1864.8	1914.7	1959.6	2016.6
12.5°	1500.0	1555.3	1615.1	1683.1	1754.8	1820.5	1893.0	1952.4	2009.5	2074.4	2140.6
15°	1487.3	1554.6	1630.2	1720.5	1829.5	1908.9	1983.3	2086.4	2157.0	2227.4	2322.3
17.5°	1464.1	1546.2	1640.7	1758.1	1848.9	1955.7	2067.6	2149.1	2244.1	2343.4	2429.3
20°	1445.6	1541.2	1646.8	1762.2	1878.2	1994.1	2102.5	2199.8	2297.9	2412.6	2483.1
22.5°	1427.2	1521.7	1631.5	1754.0	1878.7	2000.8	2123.4	2237.8	2348.1	2463.9	2553.8
25°	1388.0	1500.2	1619.3	1744.3	1867.3	2001.9	2148.0	2275.5	2412.0	2531.2	2616.4
27.5°	1348.3	1451.0	1569.7	1696.5	1833.2	1992.3	2164.1	2309.1	2445.8	2531.2	2557.9
30°	1312.4	1421.3	1530.2	1659.1	1807.0	1984.5	2167.1	2333.1	2445.3	2482.4	2454.9
32.5°	1275.9	1374.7	1482.5	1614.5	1771.6	1965.6	2171.3	2318.8	2386.3	2357.9	2245.7
35°	1211.8	1300.8	1405.2	1537.2	1718.0	1955.1	2154.3	2254.3	2237.7	2077.5	1866.0
37.5°	1143.0	1215.6	1312.4	1450.4	1662.4	1913.4	2081.5	2096.3	1952.2	1706.2	1461.9
40°	1088.8	1154.1	1253.4	1397.6	1619.3	1872.4	2008.2	1948.6	1725.0	1451.4	1247.7
42.5°	1035.9	1091.0	1186.7	1342.2	1578.3	1816.6	1899.1	1769.3	1511.2	1252.5	1067.2
45°	946.5	998.3	1094.5	1254.0	1494.4	1709.7	1698.8	1473.2	1215.0	1006.7	852.9
47.5°	861.6	907.0	997.2	1160.1	1395.8	1549.5	1447.6	1207.5	988.5	821.4	711.7
50°	801.6	846.5	936.2	1097.1	1316.9	1429.0	1283.5	1052.2	851.7	713.2	626.1
52.5°	744.2	788.1	870.1	1026.8	1221.5	1288.5	1132.3	917.9	750.6	631.2	556.4
55°	663.9	697.2	770.9	920.8	1066.3	1081.7	923.4	744.0	606.2	522.9	471.7
57.5°	582.0	610.7	683.5	802.9	904.9	897.0	746.9	591.7	499.0	437.0	399.8
60°	528.6	556.8	620.9	723.5	800.4	773.5	635.7	510.7	431.3	385.8	356.3
62.5°	478.9	501.0	560.9	635.8	691.1	660.6	543.4	439.9	376.9	338.6	315.3
65°	406.9	424.9	472.9	512.0	542.7	513.3	415.9	344.1	298.6	271.7	255.7
67.5°	338.4	349.8	380.3	394.4	416.0	383.7	312.7	264.6	238.8	216.1	205.0
70°	295.4	303.7	319.8	331.3	337.0	303.7	251.2	216.0	194.1	178.1	171.1
72.5°	252.3	259.7	262.9	272.3	269.4	238.1	201.9	173.9	158.2	147.4	138.3
75°	192.9	196.1	192.9	189.1	180.7	158.9	134.0	119.8	108.3	103.1	100.0
77.5°	140.6	139.6	135.2	129.2	115.0	101.3	87.8	83.1	78.0	75.3	74.2
80°	108.3	105.7	101.9	92.3	80.1	70.5	67.3	64.1	62.1	58.9	58.3
82.5°	80.6	79.1	72.6	64.6	56.0	51.5	48.8	47.7	45.7	44.1	43.9
85°	43.0	41.0	34.0	29.5	28.2	26.9	26.3	26.3	23.7	23.1	23.1
87.5°	14.0	11.1	10.7	9.3	9.5	8.6	9.2	8.4	8.1	8.6	7.7
90°	0.9	1.5	2.2	2.9	3.6	4.4	5.2	6.1	6.9	7.2	7.4
92.5°	5.2	5.0	4.8	4.6	4.9	5.5	6.1	6.8	7.3	7.7	8.2
95°	14.9	12.3	9.7	7.1	6.1	6.8	7.5	8.2	9.0	9.4	9.9
97.5°	34.2	32.9	31.8	30.6	27.7	23.1	18.5	13.9	9.3	9.8	10.3
100°	50.0	51.3	52.5	53.8	49.5	39.5	29.5	19.5	9.5	10.0	10.5
102.5°	64.8	65.7	66.7	67.6	62.6	51.7	40.8	29.8	19.0	17.4	15.8
105°	86.6	87.2	88.0	88.7	86.2	80.4	74.6	68.9	63.1	51.8	40.4
107.5°	109.6	110.1	110.7	111.3	112.0	112.9	113.8	114.7	115.6	107.3	99.1
110°	125.0	125.5	126.0	126.5	127.1	127.8	128.5	129.2	130.0	127.8	125.7



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	139.7	140.1	140.6	141.0	141.6	142.4	143.1	143.7	144.5	144.5	144.6
115°	161.4	161.8	162.2	162.6	163.1	163.6	164.2	164.8	165.3	166.0	166.6
117.5°	182.7	183.1	183.6	184.1	184.5	184.7	185.1	185.4	185.6	186.1	186.7
120°	195.9	196.5	197.1	197.6	198.0	198.2	198.4	198.6	198.8	199.3	199.8
122.5°	209.2	209.6	210.1	210.6	210.9	211.2	211.4	211.7	211.9	212.3	212.6
125°	227.6	228.0	228.5	229.1	229.4	229.8	230.0	230.2	230.5	230.6	230.7
127.5°	245.3	245.8	246.3	246.8	247.2	247.5	247.9	248.2	248.4	248.7	248.8
130°	256.3	256.8	257.4	257.9	258.3	258.5	258.8	259.0	259.3	259.5	259.8
132.5°	266.9	267.5	268.0	268.5	268.8	269.0	269.3	269.5	269.7	269.9	270.2
135°	283.0	283.4	283.8	284.1	284.5	284.7	285.0	285.3	285.5	285.7	285.9
137.5°	296.9	297.4	297.9	298.4	298.7	298.9	299.0	299.1	299.3	299.6	299.9
140°	306.1	306.5	306.8	307.2	307.5	307.7	307.9	308.1	308.3	308.5	308.8
142.5°	314.6	315.0	315.4	315.8	316.0	316.3	316.4	316.6	316.8	317.0	317.2
145°	326.6	327.0	327.5	327.9	328.2	328.3	328.5	328.6	328.7	328.9	329.0
147.5°	337.7	337.9	338.3	338.5	338.8	338.9	339.0	339.2	339.2	339.4	339.5
150°	344.5	344.6	344.9	345.0	345.2	345.4	345.4	345.6	345.7	345.8	346.0
152.5°	350.6	350.7	350.7	350.8	351.0	351.0	351.1	351.1	351.2	351.5	351.7
155°	359.1	359.0	358.9	358.7	358.7	358.8	358.8	358.9	359.0	359.3	359.6
157.5°	366.1	366.1	366.0	366.0	366.0	365.9	365.8	365.7	365.7	366.1	366.5
160°	370.1	370.1	370.0	370.0	369.9	369.8	369.7	369.7	369.7	370.0	370.4
162.5°	374.0	373.8	373.7	373.5	373.3	373.2	373.2	373.2	373.1	373.5	374.0
165°	378.6	378.5	378.3	378.1	378.0	377.9	377.8	377.7	377.7	378.2	378.7
167.5°	382.3	382.0	381.8	381.5	381.4	381.4	381.4	381.4	381.4	381.9	382.4
170°	384.3	384.1	383.8	383.6	383.4	383.4	383.4	383.4	383.4	384.0	384.5
172.5°	385.7	385.4	385.1	384.7	384.7	384.7	384.7	384.8	384.8	385.4	385.9
175°	387.4	387.1	386.9	386.5	386.4	386.5	386.5	386.5	386.6	387.1	387.5
177.5°	388.0	387.8	387.5	387.2	387.1	387.2	387.2	387.3	387.3	387.8	388.2
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1578.9	1578.9	1580.9	1588.7	1589.7	1596.4	1594.3
5°	1735.3	1747.4	1751.9	1771.2	1782.7	1787.9	1777.6
7.5°	1926.5	1960.9	1977.1	1997.2	2015.1	2020.5	2006.5
10°	2066.0	2101.8	2131.9	2150.5	2167.8	2179.4	2194.1
12.5°	2200.7	2244.8	2273.5	2299.7	2317.5	2332.2	2334.5
15°	2347.2	2413.9	2464.5	2501.7	2520.3	2529.9	2526.0
17.5°	2495.0	2556.8	2592.8	2630.7	2656.5	2657.8	2658.5
20°	2578.5	2638.8	2680.5	2708.7	2737.5	2736.2	2742.6
22.5°	2634.5	2681.8	2713.8	2734.3	2744.1	2739.3	2740.5
25°	2660.6	2674.7	2669.0	2636.3	2628.0	2597.8	2602.9
27.5°	2525.8	2459.1	2390.2	2301.5	2231.6	2175.6	2178.5
30°	2342.8	2224.9	2090.3	1977.5	1876.2	1848.0	1787.9
32.5°	2086.9	1910.1	1752.5	1647.4	1560.5	1536.9	1484.3
35°	1653.3	1481.6	1319.4	1222.0	1183.6	1129.8	1129.1
37.5°	1285.1	1133.8	1048.1	975.0	936.7	904.2	901.0
40°	1081.0	963.1	898.4	845.9	808.0	783.7	778.0
42.5°	938.5	843.2	782.5	750.0	720.9	708.3	699.0
45°	766.4	702.3	660.0	630.6	617.1	607.5	602.3
47.5°	641.1	598.1	569.3	549.7	538.7	528.6	531.3
50°	572.9	537.6	516.5	497.9	489.6	482.5	483.1
52.5°	518.0	486.4	469.3	455.8	445.5	440.5	438.1
55°	439.6	419.7	402.4	392.8	387.0	380.0	378.1
57.5°	375.0	359.6	345.5	334.6	333.2	326.4	327.3
60°	331.9	319.1	307.6	301.8	297.3	291.6	293.5
62.5°	296.5	285.8	275.3	270.5	266.0	261.8	262.7
65°	242.9	232.6	226.2	223.6	221.7	219.8	217.8
67.5°	193.6	187.3	183.3	177.7	173.8	173.2	171.2
70°	162.7	154.4	147.4	140.3	138.4	137.8	138.4
72.5°	130.4	125.2	123.3	119.8	119.4	117.8	119.0
75°	98.1	96.1	94.8	92.3	92.3	92.3	92.3
77.5°	72.3	71.1	70.4	69.9	69.2	68.3	68.2
80°	56.4	55.8	54.5	54.5	53.8	54.5	53.8
82.5°	42.6	42.4	41.2	41.2	40.5	40.1	40.5
85°	21.8	21.1	22.4	21.1	21.8	20.5	21.8
87.5°	7.7	7.7	7.3	7.3	6.8	7.8	6.8
90°	7.7	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	8.6	9.0	9.3	9.3	9.4	9.5	9.5
95°	10.3	10.8	10.9	10.9	10.9	10.9	10.9
97.5°	10.8	11.3	11.6	11.7	11.7	11.8	11.9
100°	11.0	11.6	11.8	11.9	12.0	12.1	12.1
102.5°	14.2	12.6	11.9	12.0	12.1	12.2	12.3
105°	29.1	17.8	12.1	12.3	12.4	12.6	12.6
107.5°	90.7	82.4	73.9	65.5	56.9	48.3	39.8
110°	123.6	121.5	115.9	106.7	97.5	88.4	79.2



TEST NUMBER: P332360-930

CATALOG NUMBER: S123RDIP-S1165D365U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	144.6	144.6	143.7	141.7	139.8	137.9	135.9
115°	167.3	168.0	168.4	168.6	168.9	169.2	169.4
117.5°	187.2	187.7	188.0	188.0	188.1	188.2	188.2
120°	200.3	200.8	201.1	201.1	201.1	201.1	201.1
122.5°	213.0	213.4	213.5	213.6	213.7	213.7	213.8
125°	230.9	231.0	231.1	231.2	231.4	231.5	231.6
127.5°	249.1	249.3	249.3	249.2	249.1	248.9	248.8
130°	260.1	260.3	260.4	260.2	260.2	260.0	259.8
132.5°	270.4	270.7	270.8	270.5	270.4	270.2	270.0
135°	286.1	286.3	286.3	286.1	285.9	285.7	285.5
137.5°	300.2	300.5	300.6	300.4	300.4	300.2	300.1
140°	309.0	309.3	309.3	309.2	309.1	309.0	308.8
142.5°	317.4	317.6	317.6	317.5	317.2	317.1	316.9
145°	329.1	329.2	329.3	329.3	329.3	329.3	329.3
147.5°	339.7	339.8	339.7	339.4	339.1	338.8	338.5
150°	346.1	346.3	346.2	346.0	345.8	345.6	345.4
152.5°	352.0	352.2	352.1	351.9	351.6	351.2	351.0
155°	360.0	360.3	360.2	359.9	359.5	359.1	358.7
157.5°	366.9	367.3	367.2	366.7	366.2	365.7	365.2
160°	370.8	371.2	371.1	370.7	370.2	369.8	369.3
162.5°	374.4	374.8	374.9	374.5	374.1	373.7	373.2
165°	379.3	379.8	379.8	379.4	378.9	378.5	378.0
167.5°	382.9	383.4	383.4	382.9	382.4	381.9	381.4
170°	385.0	385.5	385.5	385.0	384.5	384.0	383.4
172.5°	386.4	386.9	386.9	386.3	385.7	385.1	384.6
175°	388.0	388.4	388.4	387.9	387.3	386.9	386.4
177.5°	388.6	389.0	388.9	388.4	387.9	387.3	386.9
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8

(END OF REPORT)