

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831783

Luminaire Tested: S123RDIP-S1000D1025U935-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831783  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D1025U935-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1025 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7233.0 lumens  
Efficiency: N/A  
Efficacy: 118.6 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 61  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831783

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P831783

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				51
1	99	95	91	88	91	88	85	82	75	73	71	63	61	60	52	51	50				45	
2	91	84	78	73	84	78	73	69	67	63	60	56	54	51	47	45	43				39	
3	83	75	68	62	77	69	63	59	60	55	51	51	47	45	42	40	38				34	
4	77	67	59	54	71	62	56	51	54	49	45	46	42	39	38	36	34				30	
5	71	60	52	47	66	56	49	44	49	43	39	42	38	35	35	32	30				27	
6	66	54	47	41	61	51	44	39	44	39	35	38	34	31	32	29	27				24	
7	61	49	42	37	57	46	40	35	41	35	31	35	31	28	30	27	25				22	
8	57	45	38	33	53	42	36	31	37	32	28	32	28	25	28	25	22				20	
9	53	42	34	30	49	39	33	28	34	29	26	30	26	23	26	23	21				19	
10	50	38	32	27	46	36	30	26	32	27	24	28	24	21	24	21	19				17	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	30074	30074	30074	30074	30074
5°	35710	34571	30263	24464	22713
10°	32354	35114	30112	19601	16816
15°	22276	30107	29795	16020	13301
20°	15497	23180	29196	13509	11692
25°	11809	17667	28326	12006	10776
30°	10280	14124	27237	11149	9981
35°	9437	11914	25695	10424	9257
40°	8612	10640	23678	9714	8595
45°	7777	9730	21500	9042	7934
50°	7060	8977	18933	8383	7117
55°	6384	8244	16467	7739	6105
60°	5722	7496	14303	7029	5772
65°	5280	6653	12312	6316	5456
70°	4290	5750	10744	5715	4434
75°	3764	4575	9100	4741	3905
80°	3409	3868	7457	3973	3694
85°	3112	3396	5656	3606	3396

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 22686 cd/sqm

TEST NUMBER: P831783

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	254.7	3.5
10°-20°	589.3	8.1
20°-30°	676.1	9.3
30°-40°	666.4	9.2
40°-50°	587.7	8.1
50°-60°	452.1	6.3
60°-70°	297.3	4.1
70°-80°	144.4	2.0
80°-90°	38.7	0.5
90°-100°	40.8	0.6
100°-110°	197.2	2.7
110°-120°	483.3	6.7
120°-130°	613.5	8.5
130°-140°	655.4	9.1
140°-150°	612.9	8.5
150°-160°	494.3	6.8
160°-170°	319.0	4.4
170°-180°	109.9	1.5
0°-30°	1520.1	21.0
0°-40°	2186.5	30.2
0°-60°	3226.4	44.6
0°-90°	3706.7	51.2
90°-120°	721.2	10.0
90°-150°	2603.0	36.0
90°-180°	3526.0	48.7
0°-180°	7233.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2794	2794	2794	2794	2794	
5°	3305	3200	2801	2264	2102	302
15°	1999	2702	2674	1438	1194	564
25°	994	1488	2385	1011	907	470
35°	718	907	1955	793	704	448
45°	511	639	1412	594	521	397
55°	340	439	878	412	325	305
65°	207	261	483	248	214	203
75°	90	110	219	114	94	97
85°	25	28	46	29	28	27
90°	26	21	1	21	26	13
95°	33	27	52	27	33	27
105°	38	188	256	188	38	79
115°	505	493	480	493	505	475
125°	691	688	677	688	691	617
135°	852	852	843	852	852	657
145°	982	981	973	981	982	613
155°	1070	1071	1072	1071	1070	494
165°	1128	1127	1130	1127	1128	319
175°	1152	1153	1157	1153	1152	110
180°	1157	1157	1157	1157	1157	



TEST NUMBER: P831783

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0
2.5°	3096.4	3086.6	3076.9	3074.0	3071.2	3062.0	3052.8	3032.2	3011.6	2990.4	2969.2
5°	3304.9	3306.0	3307.2	3304.3	3301.4	3289.4	3277.4	3252.2	3227.0	3199.5	3172.0
7.5°	3240.7	3259.0	3277.4	3280.8	3284.2	3293.4	3302.6	3296.8	3291.1	3280.8	3270.5
10°	2960.1	2958.9	2957.8	2978.4	2999.0	3060.3	3121.6	3153.1	3184.6	3212.6	3240.7
12.5°	2501.8	2503.6	2505.3	2572.9	2640.5	2698.3	2756.2	2836.3	2916.5	3003.0	3089.5
15°	1999.0	2027.0	2055.1	2115.2	2175.4	2262.4	2349.5	2457.2	2564.8	2701.7	2838.6
17.5°	1641.5	1653.6	1665.6	1723.5	1781.3	1863.8	1946.3	2068.3	2190.3	2366.7	2543.1
20°	1352.9	1363.8	1374.6	1416.5	1458.3	1537.3	1616.3	1732.6	1848.9	2023.6	2198.3
22.5°	1129.5	1150.7	1171.9	1199.9	1228.0	1285.3	1342.6	1461.1	1579.7	1738.9	1898.1
25°	994.3	1004.1	1013.8	1037.9	1061.9	1116.9	1171.9	1250.3	1328.8	1487.5	1646.1
27.5°	902.7	905.5	908.4	926.2	943.9	979.4	1014.9	1087.7	1160.4	1291.0	1421.6
30°	827.1	832.2	837.4	851.1	864.9	890.7	916.4	968.0	1019.5	1136.4	1253.2
32.5°	768.7	771.5	774.4	785.8	797.3	816.2	835.1	875.8	916.4	1005.8	1095.1
35°	718.2	718.8	719.4	728.0	736.6	754.9	773.2	807.0	840.8	906.7	972.6
37.5°	661.0	665.0	669.0	675.3	681.6	697.6	713.7	741.2	768.7	823.1	877.5
40°	612.9	616.3	619.7	627.2	634.6	647.2	659.8	685.0	710.2	757.2	804.2
42.5°	564.7	567.0	569.3	576.8	584.2	599.7	615.2	635.2	655.2	694.2	733.1
45°	510.9	516.6	522.4	530.4	538.4	551.6	564.7	585.4	606.0	639.2	672.4
47.5°	466.2	469.1	472.0	478.8	485.7	501.7	517.8	536.1	554.4	585.4	616.3
50°	421.6	422.7	423.8	430.1	436.4	450.8	465.1	486.3	507.5	536.1	564.7
52.5°	379.2	382.0	384.9	391.2	397.5	407.2	417.0	438.7	460.5	488.6	516.6
55°	340.2	341.9	343.7	348.2	352.8	364.3	375.7	394.6	413.5	439.3	465.1
57.5°	303.6	305.9	308.1	311.6	315.0	325.3	335.6	352.3	368.9	394.6	420.4
60°	265.8	268.6	271.5	275.5	279.5	287.5	295.5	310.4	325.3	348.2	371.2
62.5°	238.3	238.8	239.4	242.9	246.3	252.0	257.7	269.8	281.8	304.7	327.6
65°	207.3	209.1	210.8	212.5	214.2	218.8	223.4	233.7	244.0	261.2	278.4
67.5°	175.3	177.0	178.7	181.6	184.4	188.4	192.4	199.3	206.2	222.2	238.3
70°	136.3	136.3	136.3	140.9	145.5	152.4	159.2	164.4	169.5	182.7	195.9
72.5°	111.1	111.7	112.3	112.8	113.4	117.4	121.4	130.0	138.6	146.6	154.6
75°	90.5	91.1	91.6	92.2	92.8	93.9	95.1	97.9	100.8	110.0	119.1
77.5°	72.2	72.7	73.3	73.9	74.5	75.6	76.8	77.9	79.0	82.5	85.9
80°	55.0	55.6	56.1	56.7	57.3	57.8	58.4	59.6	60.7	62.4	64.1
82.5°	40.1	40.1	40.1	40.1	40.1	41.2	42.4	42.4	42.4	43.5	44.7
85°	25.2	25.2	25.2	25.8	26.3	26.3	26.3	26.9	27.5	27.5	27.5
87.5°	11.5	10.9	10.3	10.9	11.5	11.5	11.5	12.0	12.6	12.6	12.6
90°	25.8	25.4	25.0	24.6	24.3	23.7	22.9	22.2	21.4	20.6	18.1
92.5°	29.2	29.0	28.8	28.6	28.5	27.7	26.4	25.0	23.7	22.3	20.6
95°	32.7	32.7	32.7	32.7	32.7	32.0	30.7	29.3	28.0	26.6	24.5
97.5°	35.2	35.0	34.9	34.7	34.5	33.6	32.1	30.6	29.0	27.5	37.2
100°	36.1	35.9	35.7	35.5	35.3	34.5	32.9	31.4	29.9	28.4	58.2
102.5°	37.0	36.6	36.2	35.8	35.4	38.4	44.7	51.0	57.3	63.6	96.8
105°	37.8	37.4	37.0	36.7	36.3	53.0	86.8	120.6	154.4	188.2	205.4
107.5°	89.4	114.4	139.4	164.4	189.5	216.7	246.1	275.5	304.9	334.3	331.4
110°	236.3	263.6	291.0	318.3	345.6	362.4	368.7	375.0	381.3	387.6	385.5



TEST NUMBER: P831783

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	447.7	448.1	448.5	448.9	449.3	448.6	446.9	445.2	443.5	441.7	439.6
115°	505.3	504.6	503.8	503.0	502.3	500.9	499.0	497.1	495.2	493.3	491.6
117.5°	551.7	551.5	551.4	551.2	551.0	550.1	548.6	547.1	545.5	544.0	543.0
120°	599.9	599.9	599.9	599.9	599.9	599.1	597.6	596.0	594.5	593.0	592.4
122.5°	647.1	646.9	646.7	646.6	646.4	645.8	644.8	643.9	642.9	642.0	641.2
125°	691.0	690.6	690.2	689.8	689.4	689.0	688.7	688.3	687.9	687.5	686.8
127.5°	733.9	734.3	734.7	735.1	735.5	735.4	734.8	734.2	733.6	733.1	732.1
130°	775.2	775.6	775.9	776.3	776.7	776.5	775.8	775.0	774.2	773.5	772.7
132.5°	813.0	813.6	814.1	814.7	815.3	815.2	814.4	813.7	812.9	812.1	811.6
135°	851.7	852.2	852.8	853.4	854.0	854.0	853.4	852.8	852.2	851.7	850.9
137.5°	888.6	889.0	889.4	889.8	890.1	889.9	888.9	888.0	887.0	886.0	885.7
140°	921.3	921.7	922.0	922.4	922.8	922.6	921.9	921.1	920.3	919.6	919.0
142.5°	951.4	951.9	952.5	953.1	953.6	953.6	953.1	952.5	951.9	951.4	950.8
145°	982.3	982.3	982.3	982.3	982.3	982.1	981.7	981.3	981.0	980.6	980.2
147.5°	1004.6	1005.6	1006.6	1007.5	1008.5	1008.7	1008.4	1008.0	1007.6	1007.2	1006.8
150°	1030.4	1031.0	1031.6	1032.1	1032.7	1032.8	1032.4	1032.0	1031.7	1031.3	1030.9
152.5°	1051.0	1052.0	1053.0	1053.9	1054.9	1055.0	1054.2	1053.4	1052.7	1051.9	1051.7
155°	1070.0	1071.1	1072.2	1073.4	1074.5	1074.6	1073.7	1072.7	1071.8	1070.8	1070.6
157.5°	1086.3	1087.8	1089.3	1090.9	1092.4	1092.6	1091.4	1090.3	1089.1	1088.0	1088.2
160°	1101.8	1103.1	1104.4	1105.8	1107.1	1107.2	1106.1	1104.9	1103.8	1102.6	1102.8
162.5°	1116.4	1117.5	1118.7	1119.8	1120.9	1120.9	1119.5	1118.2	1116.8	1115.5	1115.7
165°	1127.5	1128.9	1130.2	1131.5	1132.9	1132.8	1131.3	1129.7	1128.2	1126.7	1126.9
167.5°	1136.1	1137.7	1139.2	1140.7	1142.2	1142.2	1140.7	1139.2	1137.7	1136.1	1136.1
170°	1143.9	1145.4	1146.9	1148.4	1150.0	1150.0	1148.4	1146.9	1145.4	1143.9	1143.9
172.5°	1148.2	1149.9	1151.6	1153.3	1155.0	1155.1	1153.6	1152.1	1150.5	1149.0	1148.8
175°	1152.5	1154.0	1155.5	1157.0	1158.6	1158.7	1157.3	1156.0	1154.7	1153.3	1153.1
177.5°	1153.3	1155.2	1157.1	1159.0	1161.0	1161.1	1159.6	1158.1	1156.6	1155.0	1154.8
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8



TEST NUMBER: P831783

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0
2.5°	2966.4	2963.5	2936.0	2908.5	2881.6	2854.7	2834.6	2814.6	2780.8	2747.0	2725.8
5°	3150.2	3128.5	3084.9	3041.4	2976.1	2910.8	2855.8	2800.8	2731.0	2661.1	2602.7
7.5°	3252.7	3235.0	3182.3	3129.6	3043.1	2956.6	2870.7	2784.8	2681.7	2578.6	2490.4
10°	3255.6	3270.5	3227.0	3183.4	3086.1	2988.7	2871.9	2755.0	2616.4	2477.8	2363.8
12.5°	3153.7	3217.8	3208.6	3199.5	3100.4	3001.3	2859.3	2717.2	2547.1	2377.0	2234.4
15°	2962.9	3087.2	3123.9	3160.5	3078.6	2996.7	2835.2	2673.7	2473.8	2273.9	2110.1
17.5°	2717.2	2891.3	2988.1	3084.9	3025.4	2965.8	2788.8	2611.8	2386.7	2161.6	1983.5
20°	2426.2	2654.2	2806.0	2957.8	2936.0	2914.2	2731.5	2548.8	2306.0	2063.1	1870.1
22.5°	2138.7	2379.3	2588.9	2798.5	2820.9	2843.2	2658.8	2474.4	2208.6	1942.8	1746.4
25°	1890.7	2135.3	2385.0	2634.7	2685.1	2735.5	2560.3	2385.0	2109.5	1834.0	1638.7
27.5°	1654.2	1886.7	2161.6	2436.5	2528.2	2619.8	2459.5	2299.1	2012.1	1725.2	1530.4
30°	1461.1	1669.0	1949.7	2230.4	2358.1	2485.8	2338.6	2191.4	1906.7	1622.1	1431.3
32.5°	1281.3	1467.4	1749.2	2031.0	2179.4	2327.7	2200.6	2073.4	1799.6	1525.9	1337.4
35°	1139.2	1305.9	1568.8	1831.7	1997.8	2163.9	2059.7	1955.4	1687.9	1420.5	1242.3
37.5°	1017.2	1157.0	1403.9	1650.7	1827.1	2003.5	1916.5	1829.4	1578.0	1326.5	1158.1
40°	916.4	1028.7	1258.4	1488.0	1661.0	1834.0	1759.5	1685.1	1460.0	1234.9	1077.4
42.5°	829.9	926.7	1132.9	1339.1	1497.8	1656.4	1607.2	1557.9	1354.0	1150.1	1004.1
45°	753.8	835.1	1016.7	1198.2	1344.3	1490.3	1451.4	1412.4	1236.6	1060.8	926.7
47.5°	686.2	756.1	918.1	1080.2	1211.4	1342.6	1306.5	1270.4	1124.9	979.4	857.4
50°	624.3	683.9	819.1	954.2	1072.2	1190.2	1160.4	1130.6	1010.4	890.1	784.7
52.5°	565.9	615.2	736.6	858.0	953.1	1048.2	1025.3	1002.3	909.6	816.8	721.1
55°	510.3	555.6	658.1	760.6	842.0	923.3	900.4	877.5	805.3	733.1	648.9
57.5°	459.9	499.5	582.5	665.6	730.3	795.0	784.1	773.2	713.1	653.0	583.6
60°	406.7	442.2	513.8	585.4	637.5	689.6	677.0	664.4	621.5	578.5	518.9
62.5°	359.1	390.6	447.9	505.2	547.6	589.9	580.8	571.6	539.0	506.3	457.1
65°	309.3	340.2	386.6	433.0	466.2	499.5	491.4	483.4	458.8	434.2	394.6
67.5°	264.0	289.8	329.9	370.0	392.3	414.7	410.1	405.5	386.6	367.7	336.8
70°	218.2	240.6	273.8	307.0	322.5	337.9	339.7	341.4	324.2	307.0	284.1
72.5°	172.4	190.2	221.1	252.0	264.0	276.1	275.5	274.9	264.6	254.3	233.7
75°	132.3	145.5	169.5	193.6	203.9	214.2	216.5	218.8	209.1	199.3	187.9
77.5°	95.1	104.2	122.6	140.9	152.4	163.8	165.0	166.1	161.5	156.9	146.1
80°	67.0	69.9	81.3	92.8	104.8	116.8	118.6	120.3	115.7	111.1	104.2
82.5°	46.4	48.1	52.1	56.1	65.9	75.6	77.9	80.2	77.9	75.6	68.2
85°	28.1	28.6	30.4	32.1	36.7	41.2	43.5	45.8	44.7	43.5	39.5
87.5°	12.6	12.6	13.2	13.7	14.9	16.0	18.9	21.8	20.0	18.3	16.6
90°	15.7	13.2	10.7	8.5	6.6	4.7	2.8	0.9	2.8	4.7	6.6
92.5°	18.9	17.2	15.5	15.2	16.3	17.5	18.6	19.8	18.6	17.5	16.3
95°	22.4	20.3	18.2	21.1	28.9	36.8	44.6	52.4	44.6	36.8	28.9
97.5°	47.0	56.7	66.5	74.0	79.4	84.7	90.0	95.4	90.0	84.7	79.4
100°	87.9	117.7	147.5	160.5	156.7	152.9	149.1	145.2	149.1	152.9	156.7
102.5°	130.1	163.3	196.5	211.9	209.4	206.9	204.4	202.0	204.4	206.9	209.4
105°	222.6	239.8	257.0	264.5	262.4	260.3	258.2	256.1	258.2	260.3	262.4
107.5°	328.6	325.7	322.8	320.6	318.8	317.1	315.4	313.7	315.4	317.1	318.8
110°	383.4	381.3	379.2	377.4	375.8	374.3	372.8	371.3	372.8	374.3	375.8





TEST NUMBER: P831783

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	437.5	435.4	433.3	431.6	430.3	428.9	427.6	426.3	427.6	428.9	430.3
115°	489.9	488.1	486.4	485.0	483.8	482.7	481.6	480.4	481.6	482.7	483.8
117.5°	542.1	541.1	540.2	539.0	537.7	536.4	535.0	533.7	535.0	536.4	537.7
120°	591.8	591.3	590.7	589.5	587.8	586.1	584.4	582.7	584.4	586.1	587.8
122.5°	640.4	639.7	638.9	637.9	636.5	635.2	633.9	632.5	633.9	635.2	636.5
125°	686.0	685.2	684.5	683.3	681.8	680.3	678.7	677.2	678.7	680.3	681.8
127.5°	731.2	730.2	729.3	728.0	726.5	725.0	723.4	721.9	723.4	725.0	726.5
130°	771.9	771.2	770.4	769.3	767.7	766.2	764.7	763.1	764.7	766.2	767.7
132.5°	811.0	810.4	809.8	808.8	807.3	805.7	804.2	802.7	804.2	805.7	807.3
135°	850.1	849.4	848.6	847.7	846.5	845.4	844.2	843.1	844.2	845.4	846.5
137.5°	885.3	884.9	884.5	883.6	882.0	880.5	879.0	877.4	879.0	880.5	882.0
140°	918.4	917.8	917.3	916.4	915.3	914.1	913.0	911.8	913.0	914.1	915.3
142.5°	950.2	949.6	949.1	948.2	947.1	945.9	944.8	943.6	944.8	945.9	947.1
145°	979.8	979.4	979.1	978.2	976.9	975.5	974.2	972.8	974.2	975.5	976.9
147.5°	1006.5	1006.1	1005.7	1005.0	1004.1	1003.1	1002.2	1001.2	1002.2	1003.1	1004.1
150°	1030.5	1030.1	1029.8	1029.3	1028.7	1028.1	1027.6	1027.0	1027.6	1028.1	1028.7
152.5°	1051.5	1051.3	1051.1	1051.0	1050.8	1050.6	1050.4	1050.2	1050.4	1050.6	1050.8
155°	1070.4	1070.2	1070.1	1070.1	1070.5	1070.9	1071.3	1071.7	1071.3	1070.9	1070.5
157.5°	1088.4	1088.6	1088.8	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9	1088.9
160°	1103.0	1103.2	1103.4	1103.6	1103.8	1103.9	1104.1	1104.3	1104.1	1103.9	1103.8
162.5°	1115.9	1116.1	1116.3	1116.6	1117.2	1117.8	1118.4	1118.9	1118.4	1117.8	1117.2
165°	1127.1	1127.2	1127.4	1127.8	1128.4	1129.0	1129.5	1130.1	1129.5	1129.0	1128.4
167.5°	1136.1	1136.1	1136.1	1136.5	1137.3	1138.0	1138.8	1139.6	1138.8	1138.0	1137.3
170°	1143.9	1143.9	1143.9	1144.2	1145.0	1145.8	1146.5	1147.3	1146.5	1145.8	1145.0
172.5°	1148.6	1148.4	1148.3	1148.6	1149.6	1150.5	1151.5	1152.5	1151.5	1150.5	1149.6
175°	1152.9	1152.7	1152.6	1152.9	1153.9	1154.8	1155.8	1156.8	1155.8	1154.8	1153.9
177.5°	1154.7	1154.5	1154.3	1154.7	1155.6	1156.6	1157.5	1158.5	1157.5	1156.6	1155.6
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8



TEST NUMBER: P831783

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0
2.5°	2704.6	2672.0	2639.3	2615.8	2592.3	2563.1	2533.9	2532.8	2531.6	2509.9	2488.1
5°	2544.2	2487.5	2430.8	2375.3	2319.7	2264.1	2208.6	2196.0	2183.4	2164.5	2145.6
7.5°	2402.2	2311.7	2221.2	2150.2	2079.1	2023.6	1968.0	1930.2	1892.4	1863.2	1834.0
10°	2249.8	2137.6	2025.3	1939.4	1853.5	1793.3	1733.2	1689.7	1646.1	1625.5	1604.9
12.5°	2091.7	1969.7	1847.7	1763.5	1679.4	1607.2	1535.0	1495.5	1456.0	1427.3	1398.7
15°	1946.3	1815.1	1683.9	1594.6	1505.2	1437.6	1370.1	1330.5	1291.0	1262.4	1233.7
17.5°	1805.4	1673.1	1540.7	1450.2	1359.7	1298.5	1237.2	1198.8	1160.4	1142.7	1124.9
20°	1677.1	1543.6	1410.2	1324.8	1239.5	1179.3	1119.2	1098.6	1077.9	1061.3	1044.7
22.5°	1549.9	1421.6	1293.3	1211.4	1129.5	1086.0	1042.4	1025.8	1009.2	996.6	984.0
25°	1443.4	1315.6	1187.9	1116.3	1044.7	1010.9	977.1	966.3	955.4	942.8	930.2
27.5°	1335.7	1214.3	1092.8	1035.6	978.3	950.8	923.3	909.6	895.8	885.5	875.2
30°	1240.6	1128.4	1016.1	968.5	921.0	897.0	872.9	858.0	843.1	833.4	823.6
32.5°	1149.0	1049.3	949.6	909.0	868.3	844.8	821.3	807.0	792.7	781.3	769.8
35°	1064.2	977.7	891.2	854.0	816.8	793.3	769.8	755.5	741.2	729.7	718.2
37.5°	989.7	911.3	832.8	797.9	762.9	742.3	721.7	706.8	691.9	679.9	667.8
40°	919.9	850.6	781.3	747.5	713.7	691.3	669.0	655.8	642.6	631.8	620.9
42.5°	858.0	794.4	730.9	697.6	664.4	643.2	622.0	606.6	591.1	584.8	578.5
45°	792.7	736.6	680.4	648.4	616.3	594.0	571.6	558.4	545.3	539.5	533.8
47.5°	735.4	683.3	631.2	599.7	568.2	548.1	528.1	517.8	507.5	499.5	491.4
50°	679.3	628.9	578.5	548.1	517.8	500.6	483.4	470.8	458.2	452.5	446.8
52.5°	625.5	579.6	533.8	502.9	472.0	455.3	438.7	427.9	417.0	404.9	392.9
55°	564.7	524.7	484.6	457.1	429.6	412.4	395.2	382.6	370.0	357.4	344.8
57.5°	514.3	474.8	435.3	410.7	386.0	369.4	352.8	339.1	325.3	315.0	304.7
60°	459.4	425.0	390.6	366.6	342.5	326.5	310.4	297.3	284.1	278.9	273.8
62.5°	407.8	375.7	343.7	322.5	301.3	285.8	270.3	261.8	253.2	249.7	246.3
65°	355.1	327.6	300.1	280.7	261.2	248.0	234.8	230.8	226.8	224.0	221.1
67.5°	305.9	282.4	258.9	241.7	224.5	215.4	206.2	201.6	197.0	193.6	190.2
70°	261.2	240.6	219.9	205.1	190.2	181.6	173.0	169.0	165.0	158.7	152.4
72.5°	213.1	197.0	181.0	169.5	158.1	150.6	143.2	135.2	127.2	121.4	115.7
75°	176.4	160.4	144.3	133.5	122.6	114.0	105.4	102.5	99.7	97.9	96.2
77.5°	135.2	121.4	107.7	99.1	90.5	86.5	82.5	80.8	79.0	78.5	77.9
80°	97.4	85.9	74.5	69.9	65.3	64.1	63.0	61.9	60.7	60.1	59.6
82.5°	60.7	55.0	49.3	48.1	47.0	46.4	45.8	45.2	44.7	44.1	43.5
85°	35.5	33.2	30.9	30.4	29.8	29.2	28.6	28.6	28.6	28.6	28.6
87.5°	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.3	13.7
90°	8.5	10.7	13.2	15.7	18.1	20.6	21.4	22.2	22.9	23.7	24.3
92.5°	15.2	15.5	17.2	18.9	20.6	22.3	23.7	25.0	26.4	27.7	28.5
95°	21.1	18.2	20.3	22.4	24.5	26.6	28.0	29.3	30.7	32.0	32.7
97.5°	74.0	66.5	56.7	47.0	37.2	27.5	29.0	30.6	32.1	33.6	34.5
100°	160.5	147.5	117.7	87.9	58.2	28.4	29.9	31.4	32.9	34.5	35.3
102.5°	211.9	196.5	163.3	130.1	96.8	63.6	57.3	51.0	44.7	38.4	35.4
105°	264.5	257.0	239.8	222.6	205.4	188.2	154.4	120.6	86.8	53.0	36.3
107.5°	320.6	322.8	325.7	328.6	331.4	334.3	304.9	275.5	246.1	216.7	189.5
110°	377.4	379.2	381.3	383.4	385.5	387.6	381.3	375.0	368.7	362.4	345.6



TEST NUMBER: P831783

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	431.6	433.3	435.4	437.5	439.6	441.7	443.5	445.2	446.9	448.6	449.3
115°	485.0	486.4	488.1	489.9	491.6	493.3	495.2	497.1	499.0	500.9	502.3
117.5°	539.0	540.2	541.1	542.1	543.0	544.0	545.5	547.1	548.6	550.1	551.0
120°	589.5	590.7	591.3	591.8	592.4	593.0	594.5	596.0	597.6	599.1	599.9
122.5°	637.9	638.9	639.7	640.4	641.2	642.0	642.9	643.9	644.8	645.8	646.4
125°	683.3	684.5	685.2	686.0	686.8	687.5	687.9	688.3	688.7	689.0	689.4
127.5°	728.0	729.3	730.2	731.2	732.1	733.1	733.6	734.2	734.8	735.4	735.5
130°	769.3	770.4	771.2	771.9	772.7	773.5	774.2	775.0	775.8	776.5	776.7
132.5°	808.8	809.8	810.4	811.0	811.6	812.1	812.9	813.7	814.4	815.2	815.3
135°	847.7	848.6	849.4	850.1	850.9	851.7	852.2	852.8	853.4	854.0	854.0
137.5°	883.6	884.5	884.9	885.3	885.7	886.0	887.0	888.0	888.9	889.9	890.1
140°	916.4	917.3	917.8	918.4	919.0	919.6	920.3	921.1	921.9	922.6	922.8
142.5°	948.2	949.1	949.6	950.2	950.8	951.4	951.9	952.5	953.1	953.6	953.6
145°	978.2	979.1	979.4	979.8	980.2	980.6	981.0	981.3	981.7	982.1	982.3
147.5°	1005.0	1005.7	1006.1	1006.5	1006.8	1007.2	1007.6	1008.0	1008.4	1008.7	1008.5
150°	1029.3	1029.8	1030.1	1030.5	1030.9	1031.3	1031.7	1032.0	1032.4	1032.8	1032.7
152.5°	1051.0	1051.1	1051.3	1051.5	1051.7	1051.9	1052.7	1053.4	1054.2	1055.0	1054.9
155°	1070.1	1070.1	1070.2	1070.4	1070.6	1070.8	1071.8	1072.7	1073.7	1074.6	1074.5
157.5°	1088.9	1088.8	1088.6	1088.4	1088.2	1088.0	1089.1	1090.3	1091.4	1092.6	1092.4
160°	1103.6	1103.4	1103.2	1103.0	1102.8	1102.6	1103.8	1104.9	1106.1	1107.2	1107.1
162.5°	1116.6	1116.3	1116.1	1115.9	1115.7	1115.5	1116.8	1118.2	1119.5	1120.9	1120.9
165°	1127.8	1127.4	1127.2	1127.1	1126.9	1126.7	1128.2	1129.7	1131.3	1132.8	1132.9
167.5°	1136.5	1136.1	1136.1	1136.1	1136.1	1136.1	1137.7	1139.2	1140.7	1142.2	1142.2
170°	1144.2	1143.9	1143.9	1143.9	1143.9	1143.9	1145.4	1146.9	1148.4	1150.0	1150.0
172.5°	1148.6	1148.3	1148.4	1148.6	1148.8	1149.0	1150.5	1152.1	1153.6	1155.1	1155.0
175°	1152.9	1152.6	1152.7	1152.9	1153.1	1153.3	1154.7	1156.0	1157.3	1158.7	1158.6
177.5°	1154.7	1154.3	1154.5	1154.7	1154.8	1155.0	1156.6	1158.1	1159.6	1161.1	1161.0
180°	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8



TEST NUMBER: P831783

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2794.0	2794.0	2794.0	2794.0
2.5°	2482.4	2476.6	2474.4	2472.1
5°	2127.8	2110.1	2106.1	2102.1
7.5°	1826.6	1819.1	1794.5	1769.8
10°	1582.0	1559.1	1548.8	1538.5
12.5°	1377.5	1356.3	1352.9	1349.4
15°	1218.8	1204.0	1198.8	1193.6
17.5°	1114.6	1104.3	1098.0	1091.7
20°	1037.3	1029.8	1025.3	1020.7
22.5°	978.3	972.6	969.1	965.7
25°	921.6	913.0	910.1	907.3
27.5°	867.7	860.3	857.4	854.6
30°	817.3	811.0	807.0	803.0
32.5°	762.4	754.9	752.6	750.3
35°	713.7	709.1	706.8	704.5
37.5°	662.1	656.4	653.0	649.5
40°	618.0	615.2	613.4	611.7
42.5°	573.3	568.2	567.6	567.0
45°	528.7	523.5	522.4	521.2
47.5°	486.9	482.3	481.7	481.1
50°	440.5	434.2	429.6	425.0
52.5°	387.2	381.5	377.5	373.4
55°	338.5	332.2	328.8	325.3
57.5°	301.8	299.0	297.3	295.5
60°	272.1	270.3	269.2	268.1
62.5°	244.6	242.9	242.9	242.9
65°	219.4	217.7	215.9	214.2
67.5°	186.7	183.3	182.7	182.1
70°	147.2	142.0	141.5	140.9
72.5°	115.1	114.6	113.4	112.3
75°	95.1	93.9	93.9	93.9
77.5°	76.8	75.6	75.6	75.6
80°	59.0	58.4	59.0	59.6
82.5°	43.5	43.5	43.0	42.4
85°	28.1	27.5	27.5	27.5
87.5°	13.7	13.7	13.7	13.7
90°	24.6	25.0	25.4	25.8
92.5°	28.6	28.8	29.0	29.2
95°	32.7	32.7	32.7	32.7
97.5°	34.7	34.9	35.0	35.2
100°	35.5	35.7	35.9	36.1
102.5°	35.8	36.2	36.6	37.0
105°	36.7	37.0	37.4	37.8
107.5°	164.4	139.4	114.4	89.4
110°	318.3	291.0	263.6	236.3



TEST NUMBER: P831783

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	448.9	448.5	448.1	447.7
115°	503.0	503.8	504.6	505.3
117.5°	551.2	551.4	551.5	551.7
120°	599.9	599.9	599.9	599.9
122.5°	646.6	646.7	646.9	647.1
125°	689.8	690.2	690.6	691.0
127.5°	735.1	734.7	734.3	733.9
130°	776.3	775.9	775.6	775.2
132.5°	814.7	814.1	813.6	813.0
135°	853.4	852.8	852.2	851.7
137.5°	889.8	889.4	889.0	888.6
140°	922.4	922.0	921.7	921.3
142.5°	953.1	952.5	951.9	951.4
145°	982.3	982.3	982.3	982.3
147.5°	1007.5	1006.6	1005.6	1004.6
150°	1032.1	1031.6	1031.0	1030.4
152.5°	1053.9	1053.0	1052.0	1051.0
155°	1073.4	1072.2	1071.1	1070.0
157.5°	1090.9	1089.3	1087.8	1086.3
160°	1105.8	1104.4	1103.1	1101.8
162.5°	1119.8	1118.7	1117.5	1116.4
165°	1131.5	1130.2	1128.9	1127.5
167.5°	1140.7	1139.2	1137.7	1136.1
170°	1148.4	1146.9	1145.4	1143.9
172.5°	1153.3	1151.6	1149.9	1148.2
175°	1157.0	1155.5	1154.0	1152.5
177.5°	1159.0	1157.1	1155.2	1153.3
180°	1156.8	1156.8	1156.8	1156.8



TEST NUMBER: P831783

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.69	13.50	13.65	14.47	15.73	17.35	18.17	18.31	19.13	20.39
	3H	13.91	14.64	14.88	15.61	16.89	18.85	19.58	19.82	20.56	21.84
	4H	14.29	14.98	15.27	15.96	17.25	19.34	20.03	20.32	21.01	22.30
	6H	14.57	15.20	15.56	16.19	17.49	19.65	20.29	20.64	21.27	22.57
	8H	14.66	15.26	15.66	16.26	17.56	19.73	20.33	20.73	21.33	22.63
	12H	14.71	15.28	15.71	16.28	17.60	19.76	20.33	20.77	21.33	22.65
4H	2H	13.41	14.10	14.40	15.08	16.37	17.35	18.04	18.34	19.01	20.30
	3H	14.78	15.35	15.77	16.36	17.66	19.00	19.58	20.00	20.58	21.89
	4H	15.23	15.76	16.24	16.76	18.08	19.61	20.13	20.61	21.13	22.46
	6H	15.60	16.05	16.62	17.07	18.40	20.05	20.50	21.06	21.52	22.84
	8H	15.72	16.14	16.74	17.16	18.50	20.18	20.60	21.19	21.61	22.95
	12H	15.80	16.18	16.84	17.21	18.55	20.24	20.62	21.27	21.65	22.99
8H	4H	15.55	15.96	16.56	16.98	18.32	19.58	19.99	20.59	21.01	22.35
	6H	16.01	16.35	17.05	17.41	18.75	20.07	20.42	21.11	21.48	22.81
	8H	16.20	16.51	17.25	17.55	18.91	20.26	20.56	21.31	21.61	22.96
	12H	16.34	16.61	17.39	17.65	19.05	20.37	20.64	21.42	21.68	23.08
12H	4H	15.56	15.93	16.59	16.97	18.31	19.53	19.90	20.56	20.94	22.28
	6H	16.07	16.37	17.12	17.42	18.77	20.05	20.35	21.10	21.39	22.75
	8H	16.29	16.55	17.34	17.59	18.99	20.24	20.50	21.29	21.54	22.94