

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332372-930

Luminaire Tested: **S123RDIP-S1165D805U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332372-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D805U930-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6345.7 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	93	89	94	90	87	84	78	76	74	68	66	64	58	57	56
2	92	85	79	74	86	80	74	70	70	66	62	60	57	55	52	50	48
3	84	75	68	63	79	71	64	59	62	57	53	54	50	47	46	44	42
4	78	67	59	54	72	63	56	51	56	50	46	48	44	41	42	39	36
5	71	60	52	46	67	57	50	44	50	44	40	44	39	36	38	35	32
6	66	54	46	41	62	51	44	39	45	40	35	40	35	32	35	31	29
7	61	49	41	36	57	46	39	34	41	36	31	36	32	28	32	28	26
8	57	45	37	32	53	42	36	31	38	32	28	34	29	26	29	26	23
9	53	41	34	29	50	39	32	28	35	29	25	31	26	23	27	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16113	16113	16113	16113
5°	19207	16181	14249	16181
10°	23981	16088	12873	16088
15°	28149	15924	11739	15924
20°	31416	15678	10775	15678
25°	30914	15419	10183	15419
30°	22222	15181	9573	15181
35°	14837	14870	9179	14870
40°	10932	14497	8769	14497
45°	9168	13842	8369	13842
50°	8090	12983	7812	12983
55°	7096	12001	7047	12001
60°	6318	11063	6456	11063
65°	5547	10055	6006	10055
70°	4356	9155	5485	9155
75°	3839	7993	5011	7993
80°	3335	6794	4928	6794
85°	2692	5459	5224	5459



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.2	2.3
10°-20°	459.9	7.2
20°-30°	722.5	11.4
30°-40°	753.8	11.9
40°-50°	645.1	10.2
50°-60°	491.7	7.7
60°-70°	315.1	5.0
70°-80°	151.6	2.4
80°-90°	42.5	0.7
90°-100°	31.2	0.5
100°-110°	148.7	2.3
110°-120°	357.1	5.6
120°-130°	454.7	7.2
130°-140°	485.8	7.7
140°-150°	454.3	7.2
150°-160°	366.5	5.8
160°-170°	236.5	3.7
170°-180°	81.5	1.3
0°-30°	1329.6	21.0
0°-40°	2083.4	32.8
0°-60°	3220.2	50.7
0°-90°	3729.5	58.8
90°-120°	536.9	8.5
90°-150°	1931.8	30.4
90°-180°	2616.0	41.2
0°-180°	6345.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1497	1497	1497	1497	1497	
5°	1778	1498	1319	1498	1778	184
15°	2526	1429	1053	1429	2526	716
25°	2603	1298	857	1298	2603	1119
35°	1129	1132	698	1132	1129	740
45°	602	909	550	909	602	474
55°	378	640	376	640	378	342
65°	218	395	236	395	218	214
75°	92	192	120	192	92	99
85°	22	44	42	44	22	25
90°	19	1	19	1	19	9
95°	24	39	24	39	24	20
105°	28	190	28	190	28	64
115°	375	356	375	356	375	346
125°	512	502	512	502	512	458
135°	632	625	632	625	632	487
145°	729	722	729	722	729	455
155°	794	795	794	795	794	366
165°	836	838	836	838	836	236
175°	855	858	855	858	855	81
180°	858	858	858	858	858	



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1594.3	1596.4	1589.7	1588.7	1580.9	1578.9	1578.9	1568.1	1561.5	1552.8	1547.7
5°	1777.6	1787.9	1782.7	1771.2	1751.9	1747.4	1735.3	1716.0	1694.3	1667.4	1654.6
7.5°	2006.5	2020.5	2015.1	1997.2	1977.1	1960.9	1926.5	1894.6	1849.8	1810.6	1777.0
10°	2194.1	2179.4	2167.8	2150.5	2131.9	2101.8	2066.0	2016.6	1959.6	1914.7	1864.8
12.5°	2334.5	2332.2	2317.5	2299.7	2273.5	2244.8	2200.7	2140.6	2074.4	2009.5	1952.4
15°	2526.0	2529.9	2520.3	2501.7	2464.5	2413.9	2347.2	2322.3	2227.4	2157.0	2086.4
17.5°	2658.5	2657.8	2656.5	2630.7	2592.8	2556.8	2495.0	2429.3	2343.4	2244.1	2149.1
20°	2742.6	2736.2	2737.5	2708.7	2680.5	2638.8	2578.5	2483.1	2412.6	2297.9	2199.8
22.5°	2740.5	2739.3	2744.1	2734.3	2713.8	2681.8	2634.5	2553.8	2463.9	2348.1	2237.8
25°	2602.9	2597.8	2628.0	2636.3	2669.0	2674.7	2660.6	2616.4	2531.2	2412.0	2275.5
27.5°	2178.5	2175.6	2231.6	2301.5	2390.2	2459.1	2525.8	2557.9	2531.2	2445.8	2309.1
30°	1787.9	1848.0	1876.2	1977.5	2090.3	2224.9	2342.8	2454.9	2482.4	2445.3	2333.1
32.5°	1484.3	1536.9	1560.5	1647.4	1752.5	1910.1	2086.9	2245.7	2357.9	2386.3	2318.8
35°	1129.1	1129.8	1183.6	1222.0	1319.4	1481.6	1653.3	1866.0	2077.5	2237.7	2254.3
37.5°	901.0	904.2	936.7	975.0	1048.1	1133.8	1285.1	1461.9	1706.2	1952.2	2096.3
40°	778.0	783.7	808.0	845.9	898.4	963.1	1081.0	1247.7	1451.4	1725.0	1948.6
42.5°	699.0	708.3	720.9	750.0	782.5	843.2	938.5	1067.2	1252.5	1511.2	1769.3
45°	602.3	607.5	617.1	630.6	660.0	702.3	766.4	852.9	1006.7	1215.0	1473.2
47.5°	531.3	528.6	538.7	549.7	569.3	598.1	641.1	711.7	821.4	988.5	1207.5
50°	483.1	482.5	489.6	497.9	516.5	537.6	572.9	626.1	713.2	851.7	1052.2
52.5°	438.1	440.5	445.5	455.8	469.3	486.4	518.0	556.4	631.2	750.6	917.9
55°	378.1	380.0	387.0	392.8	402.4	419.7	439.6	471.7	522.9	606.2	744.0
57.5°	327.3	326.4	333.2	334.6	345.5	359.6	375.0	399.8	437.0	499.0	591.7
60°	293.5	291.6	297.3	301.8	307.6	319.1	331.9	356.3	385.8	431.3	510.7
62.5°	262.7	261.8	266.0	270.5	275.3	285.8	296.5	315.3	338.6	376.9	439.9
65°	217.8	219.8	221.7	223.6	226.2	232.6	242.9	255.7	271.7	298.6	344.1
67.5°	171.2	173.2	173.8	177.7	183.3	187.3	193.6	205.0	216.1	238.8	264.6
70°	138.4	137.8	138.4	140.3	147.4	154.4	162.7	171.1	178.1	194.1	216.0
72.5°	119.0	117.8	119.4	119.8	123.3	125.2	130.4	138.3	147.4	158.2	173.9
75°	92.3	92.3	92.3	92.3	94.8	96.1	98.1	100.0	103.1	108.3	119.8
77.5°	68.2	68.3	69.2	69.9	70.4	71.1	72.3	74.2	75.3	78.0	83.1
80°	53.8	54.5	53.8	54.5	54.5	55.8	56.4	58.3	58.9	62.1	64.1
82.5°	40.5	40.1	40.5	41.2	41.2	42.4	42.6	43.9	44.1	45.7	47.7
85°	21.8	20.5	21.8	21.1	22.4	21.1	21.8	23.1	23.1	23.7	26.3
87.5°	9.0	9.9	8.8	9.3	9.2	9.7	9.5	9.5	10.4	9.7	9.9
90°	19.2	18.8	18.6	18.3	18.0	17.5	17.0	16.5	15.9	15.3	13.5
92.5°	21.2	21.0	20.8	20.6	20.5	20.0	19.0	18.1	17.2	16.3	14.9
95°	24.2	24.2	24.2	24.2	24.2	23.7	22.7	21.8	20.8	19.7	18.2
97.5°	26.3	26.1	26.0	25.8	25.7	25.0	23.9	22.8	21.7	20.5	30.7
100°	26.7	26.7	26.5	26.3	26.2	25.6	24.5	23.3	22.2	21.0	43.1
102.5°	27.3	27.0	26.7	26.5	26.3	27.9	31.4	34.9	38.4	41.9	66.0
105°	28.0	27.8	27.5	27.2	26.9	39.3	64.4	89.4	114.5	139.6	152.3
107.5°	88.1	107.0	125.9	144.8	163.6	182.3	200.7	219.1	237.5	255.8	253.8
110°	175.3	195.5	215.8	236.0	256.3	268.8	273.5	278.1	282.8	287.5	285.9



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	300.8	305.0	309.2	313.6	317.8	319.9	319.8	319.8	319.7	319.6	318.0
115°	374.8	374.2	373.7	373.1	372.5	371.5	370.1	368.7	367.3	365.9	364.6
117.5°	416.4	416.2	416.1	416.0	415.9	415.2	414.2	413.0	411.9	410.7	410.1
120°	444.9	444.9	444.9	444.9	444.9	444.3	443.2	442.1	440.9	439.8	439.4
122.5°	473.0	472.9	472.7	472.6	472.5	472.1	471.2	470.4	469.7	468.9	468.3
125°	512.5	512.2	511.9	511.6	511.4	511.0	510.8	510.5	510.2	509.9	509.3
127.5°	550.5	550.7	551.1	551.3	551.5	551.5	551.1	550.6	550.2	549.7	549.0
130°	574.9	575.2	575.5	575.8	576.1	575.9	575.4	574.8	574.2	573.6	573.1
132.5°	597.4	597.8	598.2	598.6	598.9	598.8	598.3	597.7	597.2	596.6	596.1
135°	631.7	632.1	632.5	632.9	633.3	633.3	632.9	632.5	632.1	631.7	631.1
137.5°	663.9	664.2	664.5	664.8	665.0	664.9	664.1	663.5	662.8	662.1	661.8
140°	683.3	683.5	683.9	684.1	684.4	684.3	683.7	683.1	682.6	682.0	681.6
142.5°	701.2	701.6	701.9	702.3	702.7	702.7	702.2	701.8	701.3	700.9	700.4
145°	728.6	728.6	728.6	728.6	728.6	728.4	728.1	727.8	727.6	727.2	727.0
147.5°	748.9	749.6	750.2	750.9	751.5	751.7	751.5	751.1	750.9	750.6	750.3
150°	764.3	764.7	765.1	765.5	766.0	766.0	765.7	765.4	765.2	764.9	764.6
152.5°	776.5	777.1	777.8	778.4	779.1	779.2	778.6	778.1	777.6	777.1	777.0
155°	793.5	794.4	795.2	796.1	797.0	797.0	796.3	795.7	794.9	794.2	794.0
157.5°	808.0	809.1	810.2	811.3	812.4	812.5	811.6	810.8	810.0	809.1	809.3
160°	817.2	818.2	819.1	820.1	821.1	821.2	820.4	819.5	818.6	817.7	817.9
162.5°	825.8	826.7	827.5	828.4	829.3	829.2	828.3	827.4	826.4	825.4	825.6
165°	836.3	837.2	838.2	839.3	840.2	840.2	839.0	837.9	836.7	835.6	835.8
167.5°	843.8	844.9	846.0	847.2	848.3	848.3	847.2	846.0	844.9	843.8	843.8
170°	848.4	849.5	850.6	851.7	852.9	852.9	851.7	850.6	849.5	848.4	848.4
172.5°	850.9	852.2	853.5	854.7	855.9	856.0	854.8	853.7	852.6	851.4	851.3
175°	854.8	855.9	857.0	858.2	859.2	859.3	858.3	857.4	856.4	855.4	855.2
177.5°	855.9	857.0	858.2	859.3	860.5	860.5	859.7	858.8	857.9	856.9	856.8
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1545.6	1544.1	1536.9	1528.7	1517.9	1510.7	1505.1	1502.0	1492.8	1481.6	1473.8
5°	1641.1	1621.9	1601.3	1576.4	1553.3	1529.6	1514.8	1497.5	1476.4	1452.7	1436.1
7.5°	1743.4	1705.7	1665.1	1623.2	1581.8	1544.6	1511.8	1483.7	1450.0	1416.0	1392.2
10°	1821.8	1766.7	1709.7	1651.3	1598.1	1548.2	1509.7	1471.9	1431.6	1392.4	1363.0
12.5°	1893.0	1820.5	1754.8	1683.1	1615.1	1555.3	1500.0	1455.5	1407.0	1365.3	1331.7
15°	1983.3	1908.9	1829.5	1720.5	1630.2	1554.6	1487.3	1429.0	1370.0	1318.7	1286.1
17.5°	2067.6	1955.7	1848.9	1758.1	1640.7	1546.2	1464.1	1394.4	1329.7	1275.3	1235.1
20°	2102.5	1994.1	1878.2	1762.2	1646.8	1541.2	1445.6	1368.7	1301.5	1239.9	1202.8
22.5°	2123.4	2000.8	1878.7	1754.0	1631.5	1521.7	1427.2	1342.6	1269.7	1211.2	1165.4
25°	2148.0	2001.9	1867.3	1744.3	1619.3	1500.2	1388.0	1298.3	1219.4	1157.3	1108.6
27.5°	2164.1	1992.3	1833.2	1696.5	1569.7	1451.0	1348.3	1253.1	1173.2	1107.4	1055.2
30°	2167.1	1984.5	1807.0	1659.1	1530.2	1421.3	1312.4	1221.4	1136.8	1066.9	1018.2
32.5°	2171.3	1965.6	1771.6	1614.5	1482.5	1374.7	1275.9	1189.0	1102.4	1033.6	983.9
35°	2154.3	1955.1	1718.0	1537.2	1405.2	1300.8	1211.8	1131.6	1046.4	979.7	929.2
37.5°	2081.5	1913.4	1662.4	1450.4	1312.4	1215.6	1143.0	1073.2	995.1	923.2	875.5
40°	2008.2	1872.4	1619.3	1397.6	1253.4	1154.1	1088.8	1031.7	956.1	888.8	837.6
42.5°	1899.1	1816.6	1578.3	1342.2	1186.7	1091.0	1035.9	982.4	916.1	847.7	799.6
45°	1698.8	1709.7	1494.4	1254.0	1094.5	998.3	946.5	909.3	850.4	793.9	744.6
47.5°	1447.6	1549.5	1395.8	1160.1	997.2	907.0	861.6	829.2	789.5	734.1	689.1
50°	1283.5	1429.0	1316.9	1097.1	936.2	846.5	801.6	775.3	740.8	697.2	654.3
52.5°	1132.3	1288.5	1221.5	1026.8	870.1	788.1	744.2	722.6	695.1	654.1	615.3
55°	923.4	1081.7	1066.3	920.8	770.9	697.2	663.9	639.5	620.9	590.2	559.5
57.5°	746.9	897.0	904.9	802.9	683.5	610.7	582.0	563.6	551.5	528.3	499.9
60°	635.7	773.5	800.4	723.5	620.9	556.8	528.6	513.9	504.3	485.8	463.9
62.5°	543.4	660.6	691.1	635.8	560.9	501.0	478.9	464.7	458.2	442.1	422.9
65°	415.9	513.3	542.7	512.0	472.9	424.9	406.9	394.8	389.0	380.0	365.9
67.5°	312.7	383.7	416.0	394.4	380.3	349.8	338.4	331.9	326.8	320.7	308.8
70°	251.2	303.7	337.0	331.3	319.8	303.7	295.4	290.9	285.8	280.7	270.4
72.5°	201.9	238.1	269.4	272.3	262.9	259.7	252.3	250.5	247.4	241.2	235.5
75°	134.0	158.9	180.7	189.1	192.9	196.1	192.9	192.2	191.6	186.5	183.3
77.5°	87.8	101.3	115.0	129.2	135.2	139.6	140.6	142.9	141.2	138.5	137.0
80°	67.3	70.5	80.1	92.3	101.9	105.7	108.3	109.6	108.9	108.3	105.7
82.5°	48.8	51.5	56.0	64.6	72.6	79.1	80.6	80.4	81.8	82.2	80.1
85°	26.3	26.9	28.2	29.5	34.0	41.0	43.0	44.2	45.5	45.5	41.7
87.5°	10.5	9.6	10.3	9.9	11.3	11.5	14.3	16.6	17.4	15.6	15.8
90°	11.6	9.8	7.9	6.3	4.9	3.5	2.0	0.7	2.0	3.5	4.9
92.5°	13.5	12.1	10.8	10.3	10.7	11.1	11.5	11.8	11.5	11.1	10.7
95°	16.6	15.1	13.5	15.7	21.4	27.2	33.1	38.9	33.1	27.2	21.4
97.5°	40.9	51.1	61.3	67.8	70.4	73.0	75.6	78.1	75.6	73.0	70.4
100°	65.2	87.3	109.4	119.0	116.2	113.4	110.6	107.7	110.6	113.4	116.2
102.5°	90.2	114.4	138.5	149.5	147.5	145.4	143.4	141.4	143.4	145.4	147.5
105°	165.1	177.8	190.6	196.2	194.6	193.1	191.5	190.0	191.5	193.1	194.6
107.5°	251.8	249.8	247.8	246.1	244.9	243.7	242.5	241.2	242.5	243.7	244.9
110°	284.4	282.8	281.2	279.9	278.8	277.6	276.5	275.3	276.5	277.6	278.8



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	316.5	315.0	313.3	312.1	311.0	310.1	309.0	308.0	309.0	310.1	311.0
115°	363.3	362.1	360.8	359.7	358.9	358.0	357.2	356.3	357.2	358.0	358.9
117.5°	409.4	408.8	408.1	407.2	406.3	405.2	404.1	403.1	404.1	405.2	406.3
120°	439.0	438.5	438.1	437.2	435.9	434.7	433.4	432.2	433.4	434.7	435.9
122.5°	467.8	467.2	466.7	465.9	464.9	463.8	462.8	461.7	462.8	463.8	464.9
125°	508.7	508.3	507.7	506.8	505.6	504.5	503.4	502.3	503.4	504.5	505.6
127.5°	548.4	547.6	547.0	546.1	544.9	543.8	542.7	541.5	542.7	543.8	544.9
130°	572.5	571.9	571.4	570.5	569.4	568.3	567.1	566.0	567.1	568.3	569.4
132.5°	595.7	595.3	594.8	594.0	592.9	591.7	590.6	589.5	590.6	591.7	592.9
135°	630.6	630.0	629.4	628.7	627.9	627.0	626.1	625.3	626.1	627.0	627.9
137.5°	661.5	661.2	660.9	660.1	659.1	658.0	657.0	655.9	657.0	658.0	659.1
140°	681.2	680.8	680.3	679.7	678.8	678.0	677.1	676.3	677.1	678.0	678.8
142.5°	700.0	699.6	699.2	698.5	697.7	696.8	696.0	695.1	696.0	696.8	697.7
145°	726.7	726.4	726.1	725.5	724.5	723.5	722.5	721.5	722.5	723.5	724.5
147.5°	750.0	749.7	749.5	749.0	748.4	747.7	747.1	746.4	747.1	747.7	748.4
150°	764.3	764.0	763.8	763.4	763.0	762.5	762.1	761.7	762.1	762.5	763.0
152.5°	776.7	776.6	776.4	776.2	776.1	775.8	775.7	775.4	775.7	775.8	776.1
155°	793.9	793.8	793.6	793.7	794.0	794.3	794.6	794.8	794.6	794.3	794.0
157.5°	809.4	809.5	809.7	809.8	809.8	809.8	809.8	809.8	809.8	809.8	809.8
160°	818.1	818.2	818.3	818.5	818.6	818.8	818.9	819.0	818.9	818.8	818.6
162.5°	825.7	825.8	826.0	826.2	826.6	827.0	827.4	827.7	827.4	827.0	826.6
165°	835.9	836.1	836.2	836.5	836.9	837.3	837.7	838.2	837.7	837.3	836.9
167.5°	843.8	843.8	843.8	844.1	844.7	845.2	845.8	846.4	845.8	845.2	844.7
170°	848.4	848.4	848.4	848.6	849.2	849.8	850.4	850.9	850.4	849.8	849.2
172.5°	851.2	851.1	851.0	851.3	851.9	852.6	853.3	853.9	853.3	852.6	851.9
175°	855.1	854.9	854.8	855.1	855.8	856.6	857.2	857.9	857.2	856.6	855.8
177.5°	856.7	856.6	856.5	856.7	857.3	857.9	858.4	858.9	858.4	857.9	857.3
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1471.3	1464.6	1460.0	1449.8	1443.1	1435.9	1428.7	1433.4	1432.8	1432.3	1432.3
5°	1422.0	1407.2	1393.8	1376.5	1365.5	1352.1	1341.8	1340.5	1343.1	1334.2	1329.0
7.5°	1373.0	1352.8	1333.7	1314.7	1294.5	1278.3	1268.1	1263.4	1256.9	1251.3	1245.6
10°	1338.6	1314.9	1296.3	1272.6	1250.8	1231.6	1219.4	1211.1	1206.6	1202.2	1193.8
12.5°	1303.3	1280.1	1256.4	1229.6	1208.8	1186.5	1177.4	1168.1	1159.4	1154.5	1143.0
15°	1251.5	1221.4	1196.4	1168.2	1145.1	1123.3	1110.5	1091.9	1089.3	1083.0	1071.4
17.5°	1199.5	1166.9	1132.5	1111.5	1085.5	1062.8	1043.3	1037.1	1018.7	1011.8	1001.8
20°	1158.5	1128.5	1102.2	1074.6	1036.8	1015.7	1000.3	992.0	977.2	968.2	961.8
22.5°	1123.2	1092.6	1062.2	1030.0	998.9	975.2	963.9	951.0	942.9	930.3	923.4
25°	1072.7	1039.3	1002.8	968.2	945.8	927.9	910.0	898.4	886.9	881.1	868.3
27.5°	1014.0	979.2	945.0	918.8	891.2	873.5	857.3	847.0	833.2	823.5	816.4
30°	981.7	940.7	911.2	887.5	852.2	835.6	823.5	810.7	800.4	790.1	783.1
32.5°	944.3	906.9	878.9	849.5	822.6	804.3	788.6	777.3	768.6	758.8	751.8
35°	885.6	854.2	825.3	795.9	776.0	757.4	738.8	729.2	720.9	711.9	705.6
37.5°	832.5	803.2	775.8	747.8	723.2	708.1	693.1	685.7	674.5	668.5	661.9
40°	799.7	770.9	741.4	714.5	688.8	677.4	663.9	653.0	642.7	638.2	631.2
42.5°	763.9	735.0	710.1	681.2	660.1	644.5	632.1	620.2	612.5	605.9	601.9
45°	710.6	685.0	660.6	631.9	612.0	598.5	584.4	573.5	566.5	562.0	554.9
47.5°	659.0	633.4	608.6	583.5	564.3	548.9	534.8	527.3	517.9	512.4	507.6
50°	621.6	598.5	572.3	549.2	529.9	514.5	503.0	493.4	485.1	478.0	474.8
52.5°	587.3	562.6	540.0	518.4	498.1	480.7	470.2	460.1	453.8	445.7	442.1
55°	530.6	506.9	487.6	466.5	446.6	431.9	419.1	410.1	403.7	394.8	389.6
57.5°	477.4	456.2	433.2	414.8	394.4	381.9	371.3	359.1	351.3	344.2	339.2
60°	441.5	417.2	397.3	380.0	362.1	346.0	336.4	326.8	318.5	311.4	307.0
62.5°	404.1	382.8	363.9	345.1	328.7	314.8	303.6	295.5	288.2	283.7	279.2
65°	346.7	330.0	310.8	295.4	280.1	269.8	260.8	253.7	248.7	245.4	241.6
67.5°	293.8	277.7	260.9	245.8	235.5	227.7	221.8	215.8	213.3	209.1	206.6
70°	259.5	242.9	228.1	216.6	206.4	200.6	196.7	192.2	189.6	184.6	182.0
72.5°	222.1	210.0	199.4	190.0	181.7	176.5	171.6	166.1	162.0	156.4	153.8
75°	175.0	164.0	155.7	149.3	144.1	137.1	130.1	124.3	122.4	120.5	119.8
77.5°	129.6	122.6	116.6	111.2	104.8	99.7	98.2	96.9	96.5	95.5	95.5
80°	101.9	95.5	91.0	84.5	80.7	80.7	80.7	79.5	80.1	80.1	80.1
82.5°	75.7	69.9	67.4	65.1	64.3	64.8	64.8	65.1	64.7	65.7	65.2
85°	39.1	39.7	41.0	40.4	41.0	41.0	42.3	41.7	42.3	41.0	42.3
87.5°	15.7	17.4	18.3	19.2	20.1	20.0	20.6	20.7	21.4	21.4	21.5
90°	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.5	17.0	17.5	18.0
92.5°	10.3	10.8	12.1	13.5	14.9	16.3	17.2	18.1	19.0	20.0	20.5
95°	15.7	13.5	15.1	16.6	18.2	19.7	20.8	21.8	22.7	23.7	24.2
97.5°	67.8	61.3	51.1	40.9	30.7	20.5	21.7	22.8	23.9	25.0	25.7
100°	119.0	109.4	87.3	65.2	43.1	21.0	22.2	23.3	24.5	25.6	26.2
102.5°	149.5	138.5	114.4	90.2	66.0	41.9	38.4	34.9	31.4	27.9	26.3
105°	196.2	190.6	177.8	165.1	152.3	139.6	114.5	89.4	64.4	39.3	26.9
107.5°	246.1	247.8	249.8	251.8	253.8	255.8	237.5	219.1	200.7	182.3	163.6
110°	279.9	281.2	282.8	284.4	285.9	287.5	282.8	278.1	273.5	268.8	256.3



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	312.1	313.3	315.0	316.5	318.0	319.6	319.7	319.8	319.8	319.9	317.8
115°	359.7	360.8	362.1	363.3	364.6	365.9	367.3	368.7	370.1	371.5	372.5
117.5°	407.2	408.1	408.8	409.4	410.1	410.7	411.9	413.0	414.2	415.2	415.9
120°	437.2	438.1	438.5	439.0	439.4	439.8	440.9	442.1	443.2	444.3	444.9
122.5°	465.9	466.7	467.2	467.8	468.3	468.9	469.7	470.4	471.2	472.1	472.5
125°	506.8	507.7	508.3	508.7	509.3	509.9	510.2	510.5	510.8	511.0	511.4
127.5°	546.1	547.0	547.6	548.4	549.0	549.7	550.2	550.6	551.1	551.5	551.5
130°	570.5	571.4	571.9	572.5	573.1	573.6	574.2	574.8	575.4	575.9	576.1
132.5°	594.0	594.8	595.3	595.7	596.1	596.6	597.2	597.7	598.3	598.8	598.9
135°	628.7	629.4	630.0	630.6	631.1	631.7	632.1	632.5	632.9	633.3	633.3
137.5°	660.1	660.9	661.2	661.5	661.8	662.1	662.8	663.5	664.1	664.9	665.0
140°	679.7	680.3	680.8	681.2	681.6	682.0	682.6	683.1	683.7	684.3	684.4
142.5°	698.5	699.2	699.6	700.0	700.4	700.9	701.3	701.8	702.2	702.7	702.7
145°	725.5	726.1	726.4	726.7	727.0	727.2	727.6	727.8	728.1	728.4	728.6
147.5°	749.0	749.5	749.7	750.0	750.3	750.6	750.9	751.1	751.5	751.7	751.5
150°	763.4	763.8	764.0	764.3	764.6	764.9	765.2	765.4	765.7	766.0	766.0
152.5°	776.2	776.4	776.6	776.7	777.0	777.1	777.6	778.1	778.6	779.2	779.1
155°	793.7	793.6	793.8	793.9	794.0	794.2	794.9	795.7	796.3	797.0	797.0
157.5°	809.8	809.7	809.5	809.4	809.3	809.1	810.0	810.8	811.6	812.5	812.4
160°	818.5	818.3	818.2	818.1	817.9	817.7	818.6	819.5	820.4	821.2	821.1
162.5°	826.2	826.0	825.8	825.7	825.6	825.4	826.4	827.4	828.3	829.2	829.3
165°	836.5	836.2	836.1	835.9	835.8	835.6	836.7	837.9	839.0	840.2	840.2
167.5°	844.1	843.8	843.8	843.8	843.8	843.8	844.9	846.0	847.2	848.3	848.3
170°	848.6	848.4	848.4	848.4	848.4	848.4	849.5	850.6	851.7	852.9	852.9
172.5°	851.3	851.0	851.1	851.2	851.3	851.4	852.6	853.7	854.8	856.0	855.9
175°	855.1	854.8	854.9	855.1	855.2	855.4	856.4	857.4	858.3	859.3	859.2
177.5°	856.7	856.5	856.6	856.7	856.8	856.9	857.9	858.8	859.7	860.5	860.5
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1426.2	1425.6	1426.2	1424.1	1426.2	1425.6	1426.2	1432.3	1432.3	1432.8	1433.4
5°	1327.1	1326.5	1324.5	1318.7	1324.5	1326.5	1327.1	1329.0	1334.2	1343.1	1340.5
7.5°	1240.6	1239.7	1234.0	1234.2	1234.0	1239.7	1240.6	1245.6	1251.3	1256.9	1263.4
10°	1189.4	1189.9	1182.3	1177.8	1182.3	1189.9	1189.4	1193.8	1202.2	1206.6	1211.1
12.5°	1139.6	1136.7	1130.5	1125.5	1130.5	1136.7	1139.6	1143.0	1154.5	1159.4	1168.1
15°	1074.0	1067.6	1052.2	1053.4	1052.2	1067.6	1074.0	1071.4	1083.0	1089.3	1091.9
17.5°	996.7	992.0	991.7	982.8	991.7	992.0	996.7	1001.8	1011.8	1018.7	1037.1
20°	951.6	948.4	949.7	940.7	949.7	948.4	951.6	961.8	968.2	977.2	992.0
22.5°	916.2	913.0	907.6	904.8	907.6	913.0	916.2	923.4	930.3	942.9	951.0
25°	864.5	859.3	854.2	857.4	854.2	859.3	864.5	868.3	881.1	886.9	898.4
27.5°	812.7	808.9	803.7	803.1	803.7	808.9	812.7	816.4	823.5	833.2	847.0
30°	779.8	776.0	773.5	770.2	773.5	776.0	779.8	783.1	790.1	800.4	810.7
32.5°	746.6	745.8	741.2	740.5	741.2	745.8	746.6	751.8	758.8	768.6	777.3
35°	703.0	699.1	697.8	698.5	697.8	699.1	703.0	705.6	711.9	720.9	729.2
37.5°	661.5	656.4	654.1	651.8	654.1	656.4	661.5	661.9	668.5	674.5	685.7
40°	631.9	626.7	625.4	624.1	625.4	626.7	631.9	631.2	638.2	642.7	653.0
42.5°	598.5	596.5	595.7	593.4	595.7	596.5	598.5	601.9	605.9	612.5	620.2
45°	553.0	552.4	548.5	549.8	548.5	552.4	553.0	554.9	562.0	566.5	573.5
47.5°	505.1	502.2	499.5	501.3	499.5	502.2	505.1	507.6	512.4	517.9	527.3
50°	472.3	471.0	465.2	466.5	465.2	471.0	472.3	474.8	478.0	485.1	493.4
52.5°	439.4	434.6	432.4	431.6	432.4	434.6	439.4	442.1	445.7	453.8	460.1
55°	385.1	379.4	376.7	375.5	376.7	379.4	385.1	389.6	394.8	403.7	410.1
57.5°	331.8	330.3	328.2	329.6	328.2	330.3	331.8	339.2	344.2	351.3	359.1
60°	300.5	300.5	300.5	299.9	300.5	300.5	300.5	307.0	311.4	318.5	326.8
62.5°	276.5	274.9	274.4	275.3	274.4	274.9	276.5	279.2	283.7	288.2	295.5
65°	239.7	239.0	236.4	235.8	236.4	239.0	239.7	241.6	245.4	248.7	253.7
67.5°	205.0	202.6	201.9	201.0	201.9	202.6	205.0	206.6	209.1	213.3	215.8
70°	178.8	177.5	173.7	174.3	173.7	177.5	178.8	182.0	184.6	189.6	192.2
72.5°	150.6	149.3	148.5	147.7	148.5	149.3	150.6	153.8	156.4	162.0	166.1
75°	119.2	118.5	117.9	120.5	117.9	118.5	119.2	119.8	120.5	122.4	124.3
77.5°	95.5	95.5	95.9	94.8	95.9	95.5	95.5	95.5	95.5	96.5	96.9
80°	80.1	80.1	79.5	79.5	79.5	80.1	80.1	80.1	80.1	80.1	79.5
82.5°	64.2	64.7	65.1	64.1	65.1	64.7	64.2	65.2	65.7	64.7	65.1
85°	42.3	41.7	43.0	42.3	43.0	41.7	42.3	42.3	41.0	42.3	41.7
87.5°	22.6	21.7	21.7	22.3	21.7	21.7	22.6	21.5	21.4	21.4	20.7
90°	18.3	18.6	18.8	19.2	18.8	18.6	18.3	18.0	17.5	17.0	16.5
92.5°	20.6	20.8	21.0	21.2	21.0	20.8	20.6	20.5	20.0	19.0	18.1
95°	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	23.7	22.7	21.8
97.5°	25.8	26.0	26.1	26.3	26.1	26.0	25.8	25.7	25.0	23.9	22.8
100°	26.3	26.5	26.7	26.7	26.7	26.5	26.3	26.2	25.6	24.5	23.3
102.5°	26.5	26.7	27.0	27.3	27.0	26.7	26.5	26.3	27.9	31.4	34.9
105°	27.2	27.5	27.8	28.0	27.8	27.5	27.2	26.9	39.3	64.4	89.4
107.5°	144.8	125.9	107.0	88.1	107.0	125.9	144.8	163.6	182.3	200.7	219.1
110°	236.0	215.8	195.5	175.3	195.5	215.8	236.0	256.3	268.8	273.5	278.1



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	313.6	309.2	305.0	300.8	305.0	309.2	313.6	317.8	319.9	319.8	319.8
115°	373.1	373.7	374.2	374.8	374.2	373.7	373.1	372.5	371.5	370.1	368.7
117.5°	416.0	416.1	416.2	416.4	416.2	416.1	416.0	415.9	415.2	414.2	413.0
120°	444.9	444.9	444.9	444.9	444.9	444.9	444.9	444.9	444.3	443.2	442.1
122.5°	472.6	472.7	472.9	473.0	472.9	472.7	472.6	472.5	472.1	471.2	470.4
125°	511.6	511.9	512.2	512.5	512.2	511.9	511.6	511.4	511.0	510.8	510.5
127.5°	551.3	551.1	550.7	550.5	550.7	551.1	551.3	551.5	551.5	551.1	550.6
130°	575.8	575.5	575.2	574.9	575.2	575.5	575.8	576.1	575.9	575.4	574.8
132.5°	598.6	598.2	597.8	597.4	597.8	598.2	598.6	598.9	598.8	598.3	597.7
135°	632.9	632.5	632.1	631.7	632.1	632.5	632.9	633.3	633.3	632.9	632.5
137.5°	664.8	664.5	664.2	663.9	664.2	664.5	664.8	665.0	664.9	664.1	663.5
140°	684.1	683.9	683.5	683.3	683.5	683.9	684.1	684.4	684.3	683.7	683.1
142.5°	702.3	701.9	701.6	701.2	701.6	701.9	702.3	702.7	702.7	702.2	701.8
145°	728.6	728.6	728.6	728.6	728.6	728.6	728.6	728.6	728.4	728.1	727.8
147.5°	750.9	750.2	749.6	748.9	749.6	750.2	750.9	751.5	751.7	751.5	751.1
150°	765.5	765.1	764.7	764.3	764.7	765.1	765.5	766.0	766.0	765.7	765.4
152.5°	778.4	777.8	777.1	776.5	777.1	777.8	778.4	779.1	779.2	778.6	778.1
155°	796.1	795.2	794.4	793.5	794.4	795.2	796.1	797.0	797.0	796.3	795.7
157.5°	811.3	810.2	809.1	808.0	809.1	810.2	811.3	812.4	812.5	811.6	810.8
160°	820.1	819.1	818.2	817.2	818.2	819.1	820.1	821.1	821.2	820.4	819.5
162.5°	828.4	827.5	826.7	825.8	826.7	827.5	828.4	829.3	829.2	828.3	827.4
165°	839.3	838.2	837.2	836.3	837.2	838.2	839.3	840.2	840.2	839.0	837.9
167.5°	847.2	846.0	844.9	843.8	844.9	846.0	847.2	848.3	848.3	847.2	846.0
170°	851.7	850.6	849.5	848.4	849.5	850.6	851.7	852.9	852.9	851.7	850.6
172.5°	854.7	853.5	852.2	850.9	852.2	853.5	854.7	855.9	856.0	854.8	853.7
175°	858.2	857.0	855.9	854.8	855.9	857.0	858.2	859.2	859.3	858.3	857.4
177.5°	859.3	858.2	857.0	855.9	857.0	858.2	859.3	860.5	860.5	859.7	858.8
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1428.7	1435.9	1443.1	1449.8	1460.0	1464.6	1471.3	1473.8	1481.6	1492.8	1502.0
5°	1341.8	1352.1	1365.5	1376.5	1393.8	1407.2	1422.0	1436.1	1452.7	1476.4	1497.5
7.5°	1268.1	1278.3	1294.5	1314.7	1333.7	1352.8	1373.0	1392.2	1416.0	1450.0	1483.7
10°	1219.4	1231.6	1250.8	1272.6	1296.3	1314.9	1338.6	1363.0	1392.4	1431.6	1471.9
12.5°	1177.4	1186.5	1208.8	1229.6	1256.4	1280.1	1303.3	1331.7	1365.3	1407.0	1455.5
15°	1110.5	1123.3	1145.1	1168.2	1196.4	1221.4	1251.5	1286.1	1318.7	1370.0	1429.0
17.5°	1043.3	1062.8	1085.5	1111.5	1132.5	1166.9	1199.5	1235.1	1275.3	1329.7	1394.4
20°	1000.3	1015.7	1036.8	1074.6	1102.2	1128.5	1158.5	1202.8	1239.9	1301.5	1368.7
22.5°	963.9	975.2	998.9	1030.0	1062.2	1092.6	1123.2	1165.4	1211.2	1269.7	1342.6
25°	910.0	927.9	945.8	968.2	1002.8	1039.3	1072.7	1108.6	1157.3	1219.4	1298.3
27.5°	857.3	873.5	891.2	918.8	945.0	979.2	1014.0	1055.2	1107.4	1173.2	1253.1
30°	823.5	835.6	852.2	887.5	911.2	940.7	981.7	1018.2	1066.9	1136.8	1221.4
32.5°	788.6	804.3	822.6	849.5	878.9	906.9	944.3	983.9	1033.6	1102.4	1189.0
35°	738.8	757.4	776.0	795.9	825.3	854.2	885.6	929.2	979.7	1046.4	1131.6
37.5°	693.1	708.1	723.2	747.8	775.8	803.2	832.5	875.5	923.2	995.1	1073.2
40°	663.9	677.4	688.8	714.5	741.4	770.9	799.7	837.6	888.8	956.1	1031.7
42.5°	632.1	644.5	660.1	681.2	710.1	735.0	763.9	799.6	847.7	916.1	982.4
45°	584.4	598.5	612.0	631.9	660.6	685.0	710.6	744.6	793.9	850.4	909.3
47.5°	534.8	548.9	564.3	583.5	608.6	633.4	659.0	689.1	734.1	789.5	829.2
50°	503.0	514.5	529.9	549.2	572.3	598.5	621.6	654.3	697.2	740.8	775.3
52.5°	470.2	480.7	498.1	518.4	540.0	562.6	587.3	615.3	654.1	695.1	722.6
55°	419.1	431.9	446.6	466.5	487.6	506.9	530.6	559.5	590.2	620.9	639.5
57.5°	371.3	381.9	394.4	414.8	433.2	456.2	477.4	499.9	528.3	551.5	563.6
60°	336.4	346.0	362.1	380.0	397.3	417.2	441.5	463.9	485.8	504.3	513.9
62.5°	303.6	314.8	328.7	345.1	363.9	382.8	404.1	422.9	442.1	458.2	464.7
65°	260.8	269.8	280.1	295.4	310.8	330.0	346.7	365.9	380.0	389.0	394.8
67.5°	221.8	227.7	235.5	245.8	260.9	277.7	293.8	308.8	320.7	326.8	331.9
70°	196.7	200.6	206.4	216.6	228.1	242.9	259.5	270.4	280.7	285.8	290.9
72.5°	171.6	176.5	181.7	190.0	199.4	210.0	222.1	235.5	241.2	247.4	250.5
75°	130.1	137.1	144.1	149.3	155.7	164.0	175.0	183.3	186.5	191.6	192.2
77.5°	98.2	99.7	104.8	111.2	116.6	122.6	129.6	137.0	138.5	141.2	142.9
80°	80.7	80.7	80.7	84.5	91.0	95.5	101.9	105.7	108.3	108.9	109.6
82.5°	64.8	64.8	64.3	65.1	67.4	69.9	75.7	80.1	82.2	81.8	80.4
85°	42.3	41.0	41.0	40.4	41.0	39.7	39.1	41.7	45.5	45.5	44.2
87.5°	20.6	20.0	20.1	19.2	18.3	17.4	15.7	15.8	15.6	17.4	16.6
90°	15.9	15.3	13.5	11.6	9.8	7.9	6.3	4.9	3.5	2.0	0.7
92.5°	17.2	16.3	14.9	13.5	12.1	10.8	10.3	10.7	11.1	11.5	11.8
95°	20.8	19.7	18.2	16.6	15.1	13.5	15.7	21.4	27.2	33.1	38.9
97.5°	21.7	20.5	30.7	40.9	51.1	61.3	67.8	70.4	73.0	75.6	78.1
100°	22.2	21.0	43.1	65.2	87.3	109.4	119.0	116.2	113.4	110.6	107.7
102.5°	38.4	41.9	66.0	90.2	114.4	138.5	149.5	147.5	145.4	143.4	141.4
105°	114.5	139.6	152.3	165.1	177.8	190.6	196.2	194.6	193.1	191.5	190.0
107.5°	237.5	255.8	253.8	251.8	249.8	247.8	246.1	244.9	243.7	242.5	241.2
110°	282.8	287.5	285.9	284.4	282.8	281.2	279.9	278.8	277.6	276.5	275.3



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	319.7	319.6	318.0	316.5	315.0	313.3	312.1	311.0	310.1	309.0	308.0
115°	367.3	365.9	364.6	363.3	362.1	360.8	359.7	358.9	358.0	357.2	356.3
117.5°	411.9	410.7	410.1	409.4	408.8	408.1	407.2	406.3	405.2	404.1	403.1
120°	440.9	439.8	439.4	439.0	438.5	438.1	437.2	435.9	434.7	433.4	432.2
122.5°	469.7	468.9	468.3	467.8	467.2	466.7	465.9	464.9	463.8	462.8	461.7
125°	510.2	509.9	509.3	508.7	508.3	507.7	506.8	505.6	504.5	503.4	502.3
127.5°	550.2	549.7	549.0	548.4	547.6	547.0	546.1	544.9	543.8	542.7	541.5
130°	574.2	573.6	573.1	572.5	571.9	571.4	570.5	569.4	568.3	567.1	566.0
132.5°	597.2	596.6	596.1	595.7	595.3	594.8	594.0	592.9	591.7	590.6	589.5
135°	632.1	631.7	631.1	630.6	630.0	629.4	628.7	627.9	627.0	626.1	625.3
137.5°	662.8	662.1	661.8	661.5	661.2	660.9	660.1	659.1	658.0	657.0	655.9
140°	682.6	682.0	681.6	681.2	680.8	680.3	679.7	678.8	678.0	677.1	676.3
142.5°	701.3	700.9	700.4	700.0	699.6	699.2	698.5	697.7	696.8	696.0	695.1
145°	727.6	727.2	727.0	726.7	726.4	726.1	725.5	724.5	723.5	722.5	721.5
147.5°	750.9	750.6	750.3	750.0	749.7	749.5	749.0	748.4	747.7	747.1	746.4
150°	765.2	764.9	764.6	764.3	764.0	763.8	763.4	763.0	762.5	762.1	761.7
152.5°	777.6	777.1	777.0	776.7	776.6	776.4	776.2	776.1	775.8	775.7	775.4
155°	794.9	794.2	794.0	793.9	793.8	793.6	793.7	794.0	794.3	794.6	794.8
157.5°	810.0	809.1	809.3	809.4	809.5	809.7	809.8	809.8	809.8	809.8	809.8
160°	818.6	817.7	817.9	818.1	818.2	818.3	818.5	818.6	818.8	818.9	819.0
162.5°	826.4	825.4	825.6	825.7	825.8	826.0	826.2	826.6	827.0	827.4	827.7
165°	836.7	835.6	835.8	835.9	836.1	836.2	836.5	836.9	837.3	837.7	838.2
167.5°	844.9	843.8	843.8	843.8	843.8	843.8	844.1	844.7	845.2	845.8	846.4
170°	849.5	848.4	848.4	848.4	848.4	848.4	848.6	849.2	849.8	850.4	850.9
172.5°	852.6	851.4	851.3	851.2	851.1	851.0	851.3	851.9	852.6	853.3	853.9
175°	856.4	855.4	855.2	855.1	854.9	854.8	855.1	855.8	856.6	857.2	857.9
177.5°	857.9	856.9	856.8	856.7	856.6	856.5	856.7	857.3	857.9	858.4	858.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1505.1	1510.7	1517.9	1528.7	1536.9	1544.1	1545.6	1547.7	1552.8	1561.5	1568.1
5°	1514.8	1529.6	1553.3	1576.4	1601.3	1621.9	1641.1	1654.6	1667.4	1694.3	1716.0
7.5°	1511.8	1544.6	1581.8	1623.2	1665.1	1705.7	1743.4	1777.0	1810.6	1849.8	1894.6
10°	1509.7	1548.2	1598.1	1651.3	1709.7	1766.7	1821.8	1864.8	1914.7	1959.6	2016.6
12.5°	1500.0	1555.3	1615.1	1683.1	1754.8	1820.5	1893.0	1952.4	2009.5	2074.4	2140.6
15°	1487.3	1554.6	1630.2	1720.5	1829.5	1908.9	1983.3	2086.4	2157.0	2227.4	2322.3
17.5°	1464.1	1546.2	1640.7	1758.1	1848.9	1955.7	2067.6	2149.1	2244.1	2343.4	2429.3
20°	1445.6	1541.2	1646.8	1762.2	1878.2	1994.1	2102.5	2199.8	2297.9	2412.6	2483.1
22.5°	1427.2	1521.7	1631.5	1754.0	1878.7	2000.8	2123.4	2237.8	2348.1	2463.9	2553.8
25°	1388.0	1500.2	1619.3	1744.3	1867.3	2001.9	2148.0	2275.5	2412.0	2531.2	2616.4
27.5°	1348.3	1451.0	1569.7	1696.5	1833.2	1992.3	2164.1	2309.1	2445.8	2531.2	2557.9
30°	1312.4	1421.3	1530.2	1659.1	1807.0	1984.5	2167.1	2333.1	2445.3	2482.4	2454.9
32.5°	1275.9	1374.7	1482.5	1614.5	1771.6	1965.6	2171.3	2318.8	2386.3	2357.9	2245.7
35°	1211.8	1300.8	1405.2	1537.2	1718.0	1955.1	2154.3	2254.3	2237.7	2077.5	1866.0
37.5°	1143.0	1215.6	1312.4	1450.4	1662.4	1913.4	2081.5	2096.3	1952.2	1706.2	1461.9
40°	1088.8	1154.1	1253.4	1397.6	1619.3	1872.4	2008.2	1948.6	1725.0	1451.4	1247.7
42.5°	1035.9	1091.0	1186.7	1342.2	1578.3	1816.6	1899.1	1769.3	1511.2	1252.5	1067.2
45°	946.5	998.3	1094.5	1254.0	1494.4	1709.7	1698.8	1473.2	1215.0	1006.7	852.9
47.5°	861.6	907.0	997.2	1160.1	1395.8	1549.5	1447.6	1207.5	988.5	821.4	711.7
50°	801.6	846.5	936.2	1097.1	1316.9	1429.0	1283.5	1052.2	851.7	713.2	626.1
52.5°	744.2	788.1	870.1	1026.8	1221.5	1288.5	1132.3	917.9	750.6	631.2	556.4
55°	663.9	697.2	770.9	920.8	1066.3	1081.7	923.4	744.0	606.2	522.9	471.7
57.5°	582.0	610.7	683.5	802.9	904.9	897.0	746.9	591.7	499.0	437.0	399.8
60°	528.6	556.8	620.9	723.5	800.4	773.5	635.7	510.7	431.3	385.8	356.3
62.5°	478.9	501.0	560.9	635.8	691.1	660.6	543.4	439.9	376.9	338.6	315.3
65°	406.9	424.9	472.9	512.0	542.7	513.3	415.9	344.1	298.6	271.7	255.7
67.5°	338.4	349.8	380.3	394.4	416.0	383.7	312.7	264.6	238.8	216.1	205.0
70°	295.4	303.7	319.8	331.3	337.0	303.7	251.2	216.0	194.1	178.1	171.1
72.5°	252.3	259.7	262.9	272.3	269.4	238.1	201.9	173.9	158.2	147.4	138.3
75°	192.9	196.1	192.9	189.1	180.7	158.9	134.0	119.8	108.3	103.1	100.0
77.5°	140.6	139.6	135.2	129.2	115.0	101.3	87.8	83.1	78.0	75.3	74.2
80°	108.3	105.7	101.9	92.3	80.1	70.5	67.3	64.1	62.1	58.9	58.3
82.5°	80.6	79.1	72.6	64.6	56.0	51.5	48.8	47.7	45.7	44.1	43.9
85°	43.0	41.0	34.0	29.5	28.2	26.9	26.3	26.3	23.7	23.1	23.1
87.5°	14.3	11.5	11.3	9.9	10.3	9.6	10.5	9.9	9.7	10.4	9.5
90°	2.0	3.5	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.5
92.5°	11.5	11.1	10.7	10.3	10.8	12.1	13.5	14.9	16.3	17.2	18.1
95°	33.1	27.2	21.4	15.7	13.5	15.1	16.6	18.2	19.7	20.8	21.8
97.5°	75.6	73.0	70.4	67.8	61.3	51.1	40.9	30.7	20.5	21.7	22.8
100°	110.6	113.4	116.2	119.0	109.4	87.3	65.2	43.1	21.0	22.2	23.3
102.5°	143.4	145.4	147.5	149.5	138.5	114.4	90.2	66.0	41.9	38.4	34.9
105°	191.5	193.1	194.6	196.2	190.6	177.8	165.1	152.3	139.6	114.5	89.4
107.5°	242.5	243.7	244.9	246.1	247.8	249.8	251.8	253.8	255.8	237.5	219.1
110°	276.5	277.6	278.8	279.9	281.2	282.8	284.4	285.9	287.5	282.8	278.1



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	309.0	310.1	311.0	312.1	313.3	315.0	316.5	318.0	319.6	319.7	319.8
115°	357.2	358.0	358.9	359.7	360.8	362.1	363.3	364.6	365.9	367.3	368.7
117.5°	404.1	405.2	406.3	407.2	408.1	408.8	409.4	410.1	410.7	411.9	413.0
120°	433.4	434.7	435.9	437.2	438.1	438.5	439.0	439.4	439.8	440.9	442.1
122.5°	462.8	463.8	464.9	465.9	466.7	467.2	467.8	468.3	468.9	469.7	470.4
125°	503.4	504.5	505.6	506.8	507.7	508.3	508.7	509.3	509.9	510.2	510.5
127.5°	542.7	543.8	544.9	546.1	547.0	547.6	548.4	549.0	549.7	550.2	550.6
130°	567.1	568.3	569.4	570.5	571.4	571.9	572.5	573.1	573.6	574.2	574.8
132.5°	590.6	591.7	592.9	594.0	594.8	595.3	595.7	596.1	596.6	597.2	597.7
135°	626.1	627.0	627.9	628.7	629.4	630.0	630.6	631.1	631.7	632.1	632.5
137.5°	657.0	658.0	659.1	660.1	660.9	661.2	661.5	661.8	662.1	662.8	663.5
140°	677.1	678.0	678.8	679.7	680.3	680.8	681.2	681.6	682.0	682.6	683.1
142.5°	696.0	696.8	697.7	698.5	699.2	699.6	700.0	700.4	700.9	701.3	701.8
145°	722.5	723.5	724.5	725.5	726.1	726.4	726.7	727.0	727.2	727.6	727.8
147.5°	747.1	747.7	748.4	749.0	749.5	749.7	750.0	750.3	750.6	750.9	751.1
150°	762.1	762.5	763.0	763.4	763.8	764.0	764.3	764.6	764.9	765.2	765.4
152.5°	775.7	775.8	776.1	776.2	776.4	776.6	776.7	777.0	777.1	777.6	778.1
155°	794.6	794.3	794.0	793.7	793.6	793.8	793.9	794.0	794.2	794.9	795.7
157.5°	809.8	809.8	809.8	809.8	809.7	809.5	809.4	809.3	809.1	810.0	810.8
160°	818.9	818.8	818.6	818.5	818.3	818.2	818.1	817.9	817.7	818.6	819.5
162.5°	827.4	827.0	826.6	826.2	826.0	825.8	825.7	825.6	825.4	826.4	827.4
165°	837.7	837.3	836.9	836.5	836.2	836.1	835.9	835.8	835.6	836.7	837.9
167.5°	845.8	845.2	844.7	844.1	843.8	843.8	843.8	843.8	843.8	844.9	846.0
170°	850.4	849.8	849.2	848.6	848.4	848.4	848.4	848.4	848.4	849.5	850.6
172.5°	853.3	852.6	851.9	851.3	851.0	851.1	851.2	851.3	851.4	852.6	853.7
175°	857.2	856.6	855.8	855.1	854.8	854.9	855.1	855.2	855.4	856.4	857.4
177.5°	858.4	857.9	857.3	856.7	856.5	856.6	856.7	856.8	856.9	857.9	858.8
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1578.9	1578.9	1580.9	1588.7	1589.7	1596.4	1594.3
5°	1735.3	1747.4	1751.9	1771.2	1782.7	1787.9	1777.6
7.5°	1926.5	1960.9	1977.1	1997.2	2015.1	2020.5	2006.5
10°	2066.0	2101.8	2131.9	2150.5	2167.8	2179.4	2194.1
12.5°	2200.7	2244.8	2273.5	2299.7	2317.5	2332.2	2334.5
15°	2347.2	2413.9	2464.5	2501.7	2520.3	2529.9	2526.0
17.5°	2495.0	2556.8	2592.8	2630.7	2656.5	2657.8	2658.5
20°	2578.5	2638.8	2680.5	2708.7	2737.5	2736.2	2742.6
22.5°	2634.5	2681.8	2713.8	2734.3	2744.1	2739.3	2740.5
25°	2660.6	2674.7	2669.0	2636.3	2628.0	2597.8	2602.9
27.5°	2525.8	2459.1	2390.2	2301.5	2231.6	2175.6	2178.5
30°	2342.8	2224.9	2090.3	1977.5	1876.2	1848.0	1787.9
32.5°	2086.9	1910.1	1752.5	1647.4	1560.5	1536.9	1484.3
35°	1653.3	1481.6	1319.4	1222.0	1183.6	1129.8	1129.1
37.5°	1285.1	1133.8	1048.1	975.0	936.7	904.2	901.0
40°	1081.0	963.1	898.4	845.9	808.0	783.7	778.0
42.5°	938.5	843.2	782.5	750.0	720.9	708.3	699.0
45°	766.4	702.3	660.0	630.6	617.1	607.5	602.3
47.5°	641.1	598.1	569.3	549.7	538.7	528.6	531.3
50°	572.9	537.6	516.5	497.9	489.6	482.5	483.1
52.5°	518.0	486.4	469.3	455.8	445.5	440.5	438.1
55°	439.6	419.7	402.4	392.8	387.0	380.0	378.1
57.5°	375.0	359.6	345.5	334.6	333.2	326.4	327.3
60°	331.9	319.1	307.6	301.8	297.3	291.6	293.5
62.5°	296.5	285.8	275.3	270.5	266.0	261.8	262.7
65°	242.9	232.6	226.2	223.6	221.7	219.8	217.8
67.5°	193.6	187.3	183.3	177.7	173.8	173.2	171.2
70°	162.7	154.4	147.4	140.3	138.4	137.8	138.4
72.5°	130.4	125.2	123.3	119.8	119.4	117.8	119.0
75°	98.1	96.1	94.8	92.3	92.3	92.3	92.3
77.5°	72.3	71.1	70.4	69.9	69.2	68.3	68.2
80°	56.4	55.8	54.5	54.5	53.8	54.5	53.8
82.5°	42.6	42.4	41.2	41.2	40.5	40.1	40.5
85°	21.8	21.1	22.4	21.1	21.8	20.5	21.8
87.5°	9.5	9.7	9.2	9.3	8.8	9.9	9.0
90°	17.0	17.5	18.0	18.3	18.6	18.8	19.2
92.5°	19.0	20.0	20.5	20.6	20.8	21.0	21.2
95°	22.7	23.7	24.2	24.2	24.2	24.2	24.2
97.5°	23.9	25.0	25.7	25.8	26.0	26.1	26.3
100°	24.5	25.6	26.2	26.3	26.5	26.7	26.7
102.5°	31.4	27.9	26.3	26.5	26.7	27.0	27.3
105°	64.4	39.3	26.9	27.2	27.5	27.8	28.0
107.5°	200.7	182.3	163.6	144.8	125.9	107.0	88.1
110°	273.5	268.8	256.3	236.0	215.8	195.5	175.3



TEST NUMBER: P332372-930

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	319.8	319.9	317.8	313.6	309.2	305.0	300.8
115°	370.1	371.5	372.5	373.1	373.7	374.2	374.8
117.5°	414.2	415.2	415.9	416.0	416.1	416.2	416.4
120°	443.2	444.3	444.9	444.9	444.9	444.9	444.9
122.5°	471.2	472.1	472.5	472.6	472.7	472.9	473.0
125°	510.8	511.0	511.4	511.6	511.9	512.2	512.5
127.5°	551.1	551.5	551.5	551.3	551.1	550.7	550.5
130°	575.4	575.9	576.1	575.8	575.5	575.2	574.9
132.5°	598.3	598.8	598.9	598.6	598.2	597.8	597.4
135°	632.9	633.3	633.3	632.9	632.5	632.1	631.7
137.5°	664.1	664.9	665.0	664.8	664.5	664.2	663.9
140°	683.7	684.3	684.4	684.1	683.9	683.5	683.3
142.5°	702.2	702.7	702.7	702.3	701.9	701.6	701.2
145°	728.1	728.4	728.6	728.6	728.6	728.6	728.6
147.5°	751.5	751.7	751.5	750.9	750.2	749.6	748.9
150°	765.7	766.0	766.0	765.5	765.1	764.7	764.3
152.5°	778.6	779.2	779.1	778.4	777.8	777.1	776.5
155°	796.3	797.0	797.0	796.1	795.2	794.4	793.5
157.5°	811.6	812.5	812.4	811.3	810.2	809.1	808.0
160°	820.4	821.2	821.1	820.1	819.1	818.2	817.2
162.5°	828.3	829.2	829.3	828.4	827.5	826.7	825.8
165°	839.0	840.2	840.2	839.3	838.2	837.2	836.3
167.5°	847.2	848.3	848.3	847.2	846.0	844.9	843.8
170°	851.7	852.9	852.9	851.7	850.6	849.5	848.4
172.5°	854.8	856.0	855.9	854.7	853.5	852.2	850.9
175°	858.3	859.3	859.2	858.2	857.0	855.9	854.8
177.5°	859.7	860.5	860.5	859.3	858.2	857.0	855.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9

(END OF REPORT)