

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332334-935

Luminaire Tested: **S123RDIP-S1000D365U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332334-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D365U935-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4338.5 lumens  
Efficiency: N/A  
Efficacy: 99.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332334-935

CATALOG NUMBER: S123RDIP-S1000D365U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332334-935

CATALOG NUMBER: S123RDIP-S1000D365U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	104	100	96	92	99	95	92	89	86	84	81	78	76	74	71	69	68	64
2	95	88	81	76	90	84	78	73	76	72	68	69	66	63	63	60	58	55
3	87	77	70	64	83	74	67	62	68	62	58	62	57	54	56	53	50	47
4	80	69	61	55	76	66	59	53	61	55	50	55	51	47	51	47	43	41
5	74	62	54	47	70	59	52	46	54	48	43	50	45	41	46	42	38	36
6	68	56	48	42	65	54	46	40	49	43	38	45	40	36	42	37	34	31
7	63	51	43	37	60	49	41	36	45	39	34	42	36	32	38	34	30	28
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	35	31	27	25
9	55	42	35	30	52	41	34	29	38	32	28	35	30	26	33	28	25	23
10	52	39	32	27	49	38	31	26	35	29	25	33	27	24	30	26	23	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15553	15553	15553
5°	15612	15397	15486
10°	15524	15204	15152
15°	15357	14848	14692
20°	15128	14403	14068
25°	14892	13904	13459
30°	14579	13328	12599
35°	14259	12750	11811
40°	13964	12069	10835
45°	13575	11399	9954
50°	13147	10637	8967
55°	12710	9764	8049
60°	12312	8831	7037
65°	11790	7819	6029
70°	11138	6565	4869
75°	10189	5165	4579
80°	9081	4575	4209
85°	7669	4051	3767



TEST NUMBER: P332334-935

CATALOG NUMBER: S123RDIP-S1000D365U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.7	3.1
10°-20°	377.5	8.7
20°-30°	543.6	12.5
30°-40°	612.3	14.1
40°-50°	585.8	13.5
50°-60°	479.7	11.1
60°-70°	323.7	7.5
70°-80°	162.8	3.8
80°-90°	44.2	1.0
90°-100°	25.2	0.6
100°-110°	75.5	1.7
110°-120°	128.5	3.0
120°-130°	169.0	3.9
130°-140°	189.9	4.4
140°-150°	186.7	4.3
150°-160°	157.2	3.6
160°-170°	104.6	2.4
170°-180°	36.6	0.8
0°-30°	1056.8	24.4
0°-40°	1669.1	38.5
0°-60°	2734.6	63.0
0°-90°	3265.3	75.3
90°-120°	229.2	5.3
90°-150°	774.8	17.9
90°-180°	1073.0	24.7
0°-180°	4338.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1439	1425	1435	1433	137
15°	1378	1364	1332	1326	1318	388
25°	1254	1223	1171	1147	1133	576
35°	1085	1041	970	922	899	679
45°	892	837	749	684	654	688
55°	677	618	520	455	429	607
65°	463	397	307	252	237	458
75°	245	188	124	113	110	261
85°	62	38	33	31	30	70
90°	0	3	7	8	9	4
95°	18	20	23	24	24	20
105°	68	69	72	72	72	73
115°	129	130	130	130	130	128
125°	189	190	190	188	187	169
135°	246	247	247	246	245	189
145°	298	298	299	299	298	186
155°	341	341	341	342	340	157
165°	372	371	371	372	370	105
175°	386	385	385	387	385	37
180°	387	387	387	387	387	



TEST NUMBER: P332334-935

CATALOG NUMBER: S123RDIP-S1000D365U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1449.6	1448.7	1447.9	1447.1	1446.2	1444.6	1442.1	1439.6	1437.1	1434.6	1436.8
5°	1444.9	1443.6	1442.3	1441.0	1439.7	1437.4	1434.3	1431.2	1428.1	1425.0	1427.3
7.5°	1431.5	1430.1	1428.7	1427.3	1425.9	1423.1	1419.1	1415.1	1411.0	1407.0	1408.3
10°	1420.3	1418.5	1416.6	1414.8	1413.0	1409.7	1405.1	1400.3	1395.7	1391.0	1391.3
12.5°	1404.4	1402.3	1400.3	1398.3	1396.2	1392.3	1386.6	1380.9	1375.2	1369.4	1369.2
15°	1378.1	1375.3	1372.3	1369.5	1366.7	1361.6	1354.3	1346.9	1339.7	1332.4	1331.1
17.5°	1345.1	1341.7	1338.4	1335.1	1331.7	1325.4	1316.1	1306.9	1297.6	1288.3	1285.6
20°	1320.7	1316.6	1312.3	1308.2	1304.0	1297.0	1287.1	1277.2	1267.3	1257.4	1254.0
22.5°	1293.5	1288.7	1283.9	1279.1	1274.4	1266.7	1256.1	1245.6	1235.1	1224.6	1220.4
25°	1253.9	1247.4	1240.9	1234.3	1227.9	1218.6	1206.6	1194.6	1182.7	1170.7	1165.2
27.5°	1205.8	1198.7	1191.5	1184.3	1177.1	1166.8	1153.5	1140.1	1126.8	1113.5	1105.9
30°	1173.0	1165.2	1157.4	1149.6	1141.8	1130.6	1116.0	1101.4	1086.8	1072.3	1063.4
32.5°	1140.2	1131.4	1122.5	1113.6	1104.8	1092.7	1077.3	1061.9	1046.4	1031.0	1021.3
35°	1085.1	1075.7	1066.3	1057.0	1047.7	1034.8	1018.7	1002.5	986.4	970.3	959.1
37.5°	1029.3	1018.9	1008.5	998.1	987.7	973.9	956.7	939.4	922.1	904.9	892.2
40°	993.8	982.3	970.8	959.3	947.9	932.9	914.5	896.0	877.4	858.9	845.4
42.5°	953.4	941.9	930.5	919.0	907.6	892.3	873.2	854.1	835.0	815.9	801.1
45°	891.8	880.0	868.3	856.6	844.9	829.1	809.0	788.9	768.9	748.8	734.0
47.5°	830.2	817.3	804.4	791.5	778.7	762.2	742.2	722.1	702.1	682.0	665.9
50°	785.1	772.9	760.7	748.5	736.2	719.5	698.4	677.3	656.3	635.2	619.0
52.5°	744.9	731.6	718.2	705.0	691.7	674.6	653.8	632.8	612.0	591.1	574.3
55°	677.3	664.6	651.8	639.0	626.3	608.8	586.7	564.6	542.4	520.3	505.2
57.5°	615.0	601.1	587.2	573.3	559.4	541.3	519.0	496.8	474.6	452.4	438.1
60°	571.9	557.6	543.2	528.9	514.5	496.6	475.0	453.4	431.8	410.2	396.1
62.5°	528.7	514.4	500.1	485.8	471.5	453.5	431.9	410.3	388.7	367.0	353.8
65°	462.9	448.6	434.2	419.9	405.6	388.3	368.0	347.7	327.4	307.0	294.3
67.5°	397.0	382.5	368.1	353.6	339.1	322.1	302.6	283.2	263.7	244.2	234.7
70°	353.9	339.8	325.8	311.7	297.6	281.5	263.3	245.0	226.8	208.6	199.5
72.5°	310.7	297.0	283.1	269.2	255.4	240.1	223.6	207.1	190.5	173.9	166.4
75°	245.0	232.4	219.9	207.4	194.9	181.5	167.2	152.8	138.5	124.2	121.6
77.5°	184.9	173.6	162.3	151.0	139.7	129.4	120.2	111.0	101.8	92.6	91.2
80°	146.5	135.8	125.1	114.4	103.8	95.7	90.2	84.7	79.3	73.8	73.0
82.5°	109.9	100.7	91.5	82.2	73.0	67.2	64.6	62.1	59.5	56.9	56.1
85°	62.1	56.4	50.6	44.9	39.2	35.9	35.1	34.4	33.6	32.8	32.3
87.5°	22.6	20.4	18.3	16.1	13.9	12.9	13.1	13.3	13.4	13.7	13.5
90°	0.3	0.9	1.6	2.3	3.0	3.8	4.6	5.5	6.5	7.3	7.6
92.5°	7.4	7.8	8.3	8.8	9.2	9.6	10.2	10.7	11.2	11.7	11.9
95°	18.0	18.4	18.9	19.4	19.8	20.3	20.9	21.4	22.0	22.6	22.8
97.5°	31.9	32.2	32.6	33.0	33.3	33.7	34.1	34.4	34.9	35.2	35.6
100°	41.4	41.8	42.2	42.6	43.0	43.4	43.7	44.1	44.4	44.7	44.9
102.5°	52.3	52.6	52.8	53.0	53.3	53.6	54.1	54.6	55.0	55.4	55.6
105°	68.4	68.6	68.7	68.9	69.0	69.4	70.0	70.6	71.2	71.8	71.8
107.5°	87.2	87.3	87.4	87.5	87.6	87.6	87.9	88.2	88.4	88.7	88.9
110°	98.9	99.0	99.2	99.3	99.4	99.5	99.7	99.9	100.0	100.1	100.4



TEST NUMBER: P332334-935

CATALOG NUMBER: S123RDIP-S1000D365U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	111.1	111.2	111.2	111.3	111.4	111.4	111.5	111.5	111.5	111.6	111.8
115°	129.3	129.5	129.8	129.9	130.1	130.2	130.0	129.9	129.8	129.6	129.7
117.5°	147.7	147.8	148.0	148.1	148.3	148.2	148.0	147.8	147.7	147.5	147.5
120°	159.1	159.5	160.0	160.3	160.7	160.7	160.5	160.1	159.8	159.5	159.4
122.5°	171.1	171.3	171.7	171.9	172.3	172.3	172.1	171.9	171.8	171.6	171.4
125°	189.2	189.4	189.7	189.9	190.1	190.1	189.9	189.9	189.7	189.6	189.2
127.5°	206.0	206.5	206.9	207.3	207.8	207.9	207.8	207.6	207.5	207.3	207.0
130°	217.2	217.7	218.3	218.9	219.4	219.6	219.4	219.2	219.0	218.8	218.5
132.5°	228.4	229.0	229.5	230.1	230.6	230.8	230.7	230.5	230.3	230.2	229.9
135°	245.6	246.0	246.3	246.8	247.2	247.4	247.3	247.2	247.1	247.1	246.8
137.5°	261.4	261.7	262.0	262.3	262.7	262.9	263.1	263.3	263.5	263.6	263.4
140°	272.3	272.7	273.0	273.4	273.7	273.9	274.0	274.0	274.1	274.1	274.1
142.5°	282.3	282.7	283.0	283.4	283.6	283.9	284.0	284.1	284.2	284.4	284.3
145°	297.9	298.0	298.2	298.3	298.4	298.6	298.8	299.0	299.2	299.4	299.4
147.5°	311.5	311.8	312.0	312.3	312.5	312.7	312.9	313.1	313.2	313.5	313.5
150°	321.0	321.2	321.2	321.4	321.6	321.7	321.8	321.9	322.1	322.2	322.2
152.5°	328.8	329.0	329.2	329.3	329.6	329.7	329.8	329.8	329.9	330.0	330.1
155°	341.1	341.1	341.1	341.1	341.1	341.1	341.2	341.2	341.3	341.4	341.6
157.5°	351.5	351.5	351.4	351.3	351.2	351.2	351.3	351.3	351.4	351.5	351.7
160°	358.1	358.0	357.8	357.7	357.6	357.5	357.5	357.5	357.5	357.5	357.8
162.5°	363.9	363.8	363.6	363.4	363.2	363.2	363.2	363.3	363.3	363.3	363.7
165°	371.5	371.3	371.1	370.9	370.7	370.6	370.6	370.6	370.6	370.6	371.0
167.5°	377.5	377.3	377.0	376.7	376.4	376.3	376.4	376.4	376.5	376.6	376.9
170°	380.9	380.6	380.4	380.1	379.9	379.7	379.7	379.7	379.7	379.7	380.2
172.5°	383.7	383.3	383.1	382.8	382.5	382.4	382.4	382.4	382.4	382.4	382.8
175°	386.4	386.2	385.9	385.6	385.4	385.2	385.2	385.2	385.2	385.2	385.6
177.5°	387.5	387.4	387.1	386.9	386.7	386.6	386.6	386.6	386.6	386.6	386.9
180°	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4



TEST NUMBER: P332334-935

CATALOG NUMBER: S123RDIP-S1000D365U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1439.2	1441.5	1443.7	1444.7	1444.2	1443.9	1443.5	1443.0
5°	1429.7	1432.0	1434.3	1435.3	1434.8	1434.3	1433.7	1433.2
7.5°	1409.5	1410.8	1412.1	1412.4	1411.4	1410.6	1409.7	1408.8
10°	1391.5	1391.8	1392.1	1391.5	1390.2	1388.9	1387.6	1386.3
12.5°	1369.1	1369.0	1368.8	1368.0	1366.5	1364.9	1363.5	1361.9
15°	1329.8	1328.5	1327.2	1325.6	1323.8	1322.0	1320.2	1318.4
17.5°	1282.8	1280.0	1277.3	1274.5	1271.9	1269.1	1266.4	1263.7
20°	1250.6	1247.2	1243.9	1240.6	1237.5	1234.3	1231.2	1228.1
22.5°	1216.2	1211.9	1207.7	1204.1	1201.3	1198.3	1195.4	1192.5
25°	1159.8	1154.3	1148.8	1144.6	1141.8	1138.9	1136.1	1133.2
27.5°	1098.3	1090.7	1083.1	1077.1	1072.7	1068.3	1063.9	1059.6
30°	1054.6	1045.7	1036.8	1030.4	1026.1	1022.0	1017.8	1013.7
32.5°	1011.6	1001.9	992.2	985.2	980.9	976.5	972.1	967.7
35°	947.9	936.7	925.5	917.6	912.9	908.2	903.5	898.8
37.5°	879.5	866.8	854.1	844.8	839.0	833.3	827.5	821.7
40°	831.9	818.4	804.8	795.0	789.0	783.1	777.1	771.1
42.5°	786.3	771.5	756.6	746.6	741.2	735.9	730.5	725.1
45°	719.1	704.3	689.4	678.9	672.6	666.4	660.1	653.9
47.5°	649.7	633.6	617.4	606.6	601.0	595.5	589.9	584.3
50°	602.9	586.7	570.6	559.5	553.5	547.5	541.6	535.5
52.5°	557.6	540.8	524.0	512.9	507.6	502.2	496.9	491.5
55°	490.1	475.0	459.9	449.7	444.5	439.3	434.1	428.9
57.5°	423.8	409.5	395.3	385.9	381.5	377.0	372.6	368.2
60°	382.0	368.0	353.9	344.7	340.3	335.8	331.4	326.9
62.5°	340.5	327.4	314.1	305.1	300.6	295.9	291.3	286.6
65°	281.5	268.7	256.0	248.1	245.3	242.5	239.6	236.7
67.5°	225.2	215.6	206.1	199.8	196.7	193.6	190.5	187.5
70°	190.4	181.2	172.1	166.2	163.2	160.4	157.6	154.7
72.5°	159.0	151.5	144.1	139.8	138.6	137.4	136.2	135.0
75°	119.0	116.4	113.8	112.3	111.8	111.2	110.6	110.1
77.5°	89.8	88.3	87.0	86.0	85.5	85.0	84.5	83.9
80°	72.2	71.5	70.7	70.1	69.6	69.1	68.4	67.9
82.5°	55.4	54.6	53.8	53.4	53.3	53.2	53.0	53.0
85°	31.8	31.3	30.7	30.5	30.5	30.5	30.5	30.5
87.5°	13.3	13.2	13.0	12.8	12.7	12.5	12.3	12.1
90°	7.8	8.1	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	12.1	12.3	12.6	12.7	12.6	12.5	12.4	12.3
95°	23.1	23.3	23.6	23.8	23.8	23.8	23.8	23.8
97.5°	35.8	36.2	36.5	36.6	36.6	36.6	36.5	36.5
100°	45.1	45.4	45.5	45.7	45.8	46.0	46.1	46.2
102.5°	55.9	56.1	56.2	56.3	56.3	56.3	56.2	56.2
105°	71.8	71.8	71.8	71.9	72.0	72.2	72.3	72.4
107.5°	89.1	89.3	89.5	89.6	89.5	89.5	89.4	89.3
110°	100.7	100.9	101.2	101.3	101.1	101.0	100.8	100.7





TEST NUMBER: P332334-935

CATALOG NUMBER: S123RDIP-S1000D365U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	112.2	112.5	112.9	113.0	113.0	113.0	112.9	112.9
115°	129.8	129.8	129.9	129.9	129.8	129.8	129.7	129.6
117.5°	147.5	147.5	147.5	147.3	147.1	147.0	146.8	146.6
120°	159.3	159.2	159.2	159.0	158.9	158.8	158.7	158.5
122.5°	171.3	171.1	170.9	170.7	170.6	170.3	170.1	170.0
125°	189.0	188.7	188.5	188.2	188.0	187.7	187.4	187.1
127.5°	206.6	206.2	205.8	205.4	205.2	204.8	204.6	204.2
130°	218.3	217.9	217.7	217.3	216.9	216.4	215.9	215.4
132.5°	229.5	229.2	228.9	228.6	228.2	227.8	227.5	227.1
135°	246.5	246.2	246.0	245.8	245.6	245.5	245.4	245.2
137.5°	263.1	262.9	262.5	262.3	262.0	261.7	261.5	261.2
140°	274.0	274.0	273.9	273.6	273.1	272.7	272.2	271.7
142.5°	284.2	284.1	284.1	283.9	283.5	283.2	282.8	282.4
145°	299.3	299.2	299.1	298.9	298.7	298.4	298.2	297.9
147.5°	313.5	313.5	313.5	313.2	312.9	312.5	312.0	311.6
150°	322.2	322.2	322.2	322.0	321.6	321.2	320.8	320.4
152.5°	330.2	330.4	330.5	330.3	329.9	329.6	329.2	328.9
155°	341.9	342.2	342.5	342.3	341.9	341.4	341.0	340.4
157.5°	352.0	352.3	352.6	352.5	352.1	351.8	351.4	351.0
160°	358.2	358.5	358.9	358.9	358.6	358.3	358.1	357.8
162.5°	364.0	364.4	364.7	364.6	364.2	363.8	363.3	362.9
165°	371.4	371.8	372.2	372.2	371.7	371.3	370.7	370.3
167.5°	377.4	377.8	378.2	378.2	377.8	377.4	376.9	376.6
170°	380.6	381.2	381.6	381.6	381.2	380.6	380.2	379.7
172.5°	383.2	383.7	384.1	384.1	383.6	383.1	382.6	382.2
175°	386.0	386.4	386.8	386.8	386.3	385.8	385.4	384.9
177.5°	387.3	387.5	387.9	387.9	387.5	387.1	386.8	386.3
180°	387.4	387.4	387.4	387.4	387.4	387.4	387.4	387.4

(END OF REPORT)