

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832024

Luminaire Tested: S123RDIP-S1165D805U930-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832024
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D805U930-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6301.3 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832024

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P832024

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64																												
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61	56																												
2	94	87	81	76	88	82	77	73	73	69	66	64	62	59	57	55	53	49																												
3	86	77	71	65	81	73	67	62	65	61	57	58	54	51	51	49	46	43																												
4	80	69	62	56	75	66	59	54	59	54	49	53	48	45	47	44	41	38																												
5	74	63	55	49	69	60	53	47	54	48	44	48	44	40	43	39	37	34																												
6	68	57	49	44	64	54	47	42	49	43	39	44	39	36	39	36	33	30																												
7	64	52	44	39	60	50	43	38	45	39	35	41	36	32	36	33	30	28																												
8	60	48	40	35	56	46	39	34	41	36	32	38	33	30	34	30	27	25																												
9	56	44	37	32	53	42	36	31	38	33	29	35	30	27	32	28	25	23																												
10	53	41	34	29	50	39	33	28	36	30	27	33	28	25	30	26	23	21																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	32890	32890	32890	32890	32890
5°	39053	37807	33097	26754	24840
10°	35382	38402	32932	21436	18390
15°	24361	32926	32584	17521	14547
20°	16947	25350	31930	14773	12786
25°	12915	19320	30978	13131	11784
30°	11242	15447	29788	12192	10915
35°	10322	13030	28101	11401	10125
40°	9417	11636	25895	10624	9400
45°	8505	10642	23514	9889	8677
50°	7720	9818	20706	9168	7783
55°	6983	9015	18008	8464	6677
60°	6256	8198	15642	7685	6312
65°	5777	7274	13466	6907	5968
70°	4692	6288	11748	6250	4850
75°	4117	5003	9952	5186	4271
80°	3725	4234	8151	4351	4035
85°	3409	3717	6187	3940	3717

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 24811 cd/sqm



TEST NUMBER: P832024

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	278.5	4.4
10°-20°	644.5	10.2
20°-30°	739.4	11.7
30°-40°	728.8	11.6
40°-50°	642.7	10.2
50°-60°	494.5	7.8
60°-70°	325.1	5.2
70°-80°	157.9	2.5
80°-90°	41.5	0.7
90°-100°	52.2	0.8
100°-110°	158.1	2.5
110°-120°	269.1	4.3
120°-130°	354.1	5.6
130°-140°	398.0	6.3
140°-150°	391.3	6.2
150°-160°	329.4	5.2
160°-170°	219.3	3.5
170°-180°	76.8	1.2
0°-30°	1662.4	26.4
0°-40°	2391.2	37.9
0°-60°	3528.4	56.0
0°-90°	4052.9	64.3
90°-120°	479.5	7.6
90°-150°	1622.8	25.8
90°-180°	2248.0	35.7
0°-180°	6301.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3056	3056	3056	3056	3056	
5°	3614	3499	3063	2476	2299	330
15°	2186	2955	2924	1572	1305	617
25°	1087	1627	2608	1106	992	514
35°	786	992	2138	868	770	490
45°	559	699	1545	650	570	434
55°	372	480	960	451	356	334
65°	227	286	529	271	234	222
75°	99	120	239	125	103	107
85°	28	30	50	32	30	29
90°	19	15	1	15	19	11
95°	50	47	38	47	50	50
105°	152	150	143	150	152	161
115°	272	272	271	272	272	269
125°	392	397	396	397	392	351
135°	514	518	514	518	514	395
145°	624	627	624	627	624	390
155°	713	715	715	715	713	329
165°	776	776	778	776	776	219
175°	806	807	810	807	806	77
180°	812	812	812	812	812	



TEST NUMBER: P832024

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6
2.5°	3386.3	3375.6	3365.0	3361.9	3358.7	3348.7	3338.7	3316.1	3293.6	3270.4	3247.2
5°	3614.3	3615.6	3616.8	3613.7	3610.5	3597.4	3584.2	3556.7	3529.1	3499.0	3469.0
7.5°	3544.1	3564.2	3584.2	3588.0	3591.8	3601.8	3611.8	3605.5	3599.3	3588.0	3576.7
10°	3237.2	3236.0	3234.7	3257.3	3279.8	3346.8	3413.9	3448.3	3482.8	3513.5	3544.1
12.5°	2736.1	2738.0	2739.9	2813.8	2887.7	2950.9	3014.2	3101.9	3189.6	3284.2	3378.8
15°	2186.1	2216.8	2247.5	2313.3	2379.1	2474.3	2569.5	2687.2	2805.0	2954.7	3104.4
17.5°	1795.2	1808.4	1821.6	1884.8	1948.1	2038.3	2128.5	2261.9	2395.3	2588.3	2781.2
20°	1479.5	1491.4	1503.3	1549.1	1594.8	1681.2	1767.7	1894.8	2022.0	2213.1	2404.1
22.5°	1235.3	1258.4	1281.6	1312.3	1343.0	1405.6	1468.3	1597.9	1727.6	1901.7	2075.9
25°	1087.4	1098.1	1108.7	1135.0	1161.3	1221.5	1281.6	1367.4	1453.2	1626.7	1800.3
27.5°	987.2	990.3	993.5	1012.9	1032.3	1071.1	1110.0	1189.5	1269.1	1411.9	1554.7
30°	904.5	910.2	915.8	930.8	945.9	974.0	1002.2	1058.6	1115.0	1242.8	1370.6
32.5°	840.6	843.8	846.9	859.4	871.9	892.6	913.3	957.8	1002.2	1100.0	1197.7
35°	785.5	786.1	786.8	796.1	805.5	825.6	845.6	882.6	919.5	991.6	1063.6
37.5°	722.9	727.2	731.6	738.5	745.4	762.9	780.5	810.6	840.6	900.1	959.6
40°	670.2	674.0	677.8	685.9	694.0	707.8	721.6	749.2	776.7	828.1	879.5
42.5°	617.6	620.1	622.6	630.8	638.9	655.8	672.7	694.7	716.6	759.2	801.8
45°	558.7	565.0	571.3	580.0	588.8	603.2	617.6	640.2	662.7	699.1	735.4
47.5°	509.9	513.0	516.1	523.7	531.2	548.7	566.3	586.3	606.4	640.2	674.0
50°	461.0	462.3	463.5	470.4	477.3	493.0	508.6	531.8	555.0	586.3	617.6
52.5°	414.7	417.8	420.9	427.8	434.7	445.4	456.0	479.8	503.6	534.3	565.0
55°	372.1	374.0	375.8	380.8	385.9	398.4	410.9	431.6	452.3	480.4	508.6
57.5°	332.0	334.5	337.0	340.8	344.5	355.8	367.1	385.2	403.4	431.6	459.8
60°	290.6	293.8	296.9	301.3	305.7	314.5	323.2	339.5	355.8	380.8	405.9
62.5°	260.6	261.2	261.8	265.6	269.4	275.6	281.9	295.0	308.2	333.2	358.3
65°	226.8	228.6	230.5	232.4	234.3	239.3	244.3	255.6	266.8	285.6	304.4
67.5°	191.7	193.6	195.4	198.6	201.7	206.1	210.5	218.0	225.5	243.0	260.6
70°	149.1	149.1	149.1	154.1	159.1	166.6	174.1	179.8	185.4	199.8	214.2
72.5°	121.5	122.1	122.8	123.4	124.0	128.4	132.8	142.2	151.6	160.4	169.1
75°	99.0	99.6	100.2	100.8	101.5	102.7	104.0	107.1	110.2	120.3	130.3
77.5°	78.9	79.6	80.2	80.8	81.4	82.7	83.9	85.2	86.4	90.2	94.0
80°	60.1	60.8	61.4	62.0	62.6	63.3	63.9	65.1	66.4	68.3	70.2
82.5°	43.8	43.8	43.8	43.8	43.8	45.1	46.4	46.4	46.4	47.6	48.9
85°	27.6	27.6	27.6	28.2	28.8	28.8	28.8	29.4	30.1	30.1	30.1
87.5°	12.5	11.9	11.3	11.9	12.5	12.5	12.5	13.2	13.8	13.8	13.8
90°	19.1	18.8	18.6	18.3	18.0	17.6	17.0	16.4	15.9	15.3	13.5
92.5°	27.4	27.7	28.0	28.3	28.5	28.5	28.0	27.6	27.2	26.8	25.9
95°	49.7	49.7	49.7	49.7	49.7	49.4	48.9	48.3	47.7	47.2	46.0
97.5°	71.4	71.5	71.7	71.8	72.0	71.7	71.0	70.3	69.6	68.8	68.0
100°	96.9	96.6	96.3	96.0	95.8	95.4	95.0	94.6	94.1	93.7	93.0
102.5°	123.0	123.2	123.3	123.4	123.6	123.4	123.0	122.6	122.2	121.8	120.8
105°	151.7	151.4	151.1	150.9	150.6	150.4	150.4	150.4	150.4	150.4	149.2
107.5°	181.0	181.2	181.3	181.5	181.6	181.5	181.0	180.6	180.2	179.8	179.2
110°	211.0	211.3	211.6	211.8	212.1	212.0	211.4	210.8	210.3	209.7	209.4



TEST NUMBER: P832024

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	242.9	242.9	242.9	242.9	242.9	242.5	241.8	241.1	240.4	239.7	239.7
115°	271.5	271.7	271.8	272.0	272.1	272.1	272.0	271.8	271.7	271.5	271.8
117.5°	300.9	301.3	301.7	302.1	302.6	302.8	302.8	302.8	302.8	302.8	303.1
120°	332.1	332.4	332.7	333.0	333.2	333.4	333.6	333.7	333.9	334.0	334.7
122.5°	362.1	362.5	362.9	363.3	363.8	364.2	364.6	365.0	365.5	365.9	366.2
125°	392.0	392.6	393.2	393.7	394.3	394.9	395.4	396.0	396.6	397.1	397.4
127.5°	422.0	422.5	423.1	423.7	424.2	425.0	425.8	426.7	427.5	428.4	428.6
130°	451.3	452.3	453.3	454.3	455.3	456.0	456.6	457.2	457.7	458.3	458.7
132.5°	481.9	482.6	483.3	484.0	484.7	485.4	486.2	486.9	487.6	488.3	488.6
135°	513.8	514.1	514.3	514.6	514.9	515.3	515.9	516.5	517.0	517.6	517.7
137.5°	541.8	542.2	542.7	543.1	543.5	544.1	544.8	545.5	546.2	546.9	546.5
140°	569.2	570.2	571.2	572.2	573.2	573.8	573.9	574.0	574.2	574.3	574.2
142.5°	597.3	598.0	598.7	599.4	600.1	600.5	600.7	600.8	601.0	601.1	600.8
145°	624.0	624.6	625.2	625.7	626.3	626.7	626.8	627.0	627.1	627.2	626.8
147.5°	648.3	649.1	650.0	650.8	651.7	652.1	652.1	652.1	652.1	652.1	651.7
150°	671.2	672.1	672.9	673.8	674.6	675.0	675.0	675.0	675.0	675.0	674.8
152.5°	693.5	694.2	694.9	695.7	696.4	696.6	696.3	696.0	695.7	695.4	695.3
155°	713.3	714.3	715.3	716.3	717.3	717.5	716.9	716.3	715.8	715.2	715.1
157.5°	731.8	732.6	733.5	734.3	735.2	735.3	734.8	734.2	733.6	733.1	732.9
160°	749.6	750.2	750.8	751.3	751.9	751.8	751.1	750.4	749.7	749.0	749.0
162.5°	763.0	764.0	765.0	766.0	767.0	767.1	766.4	765.7	765.0	764.3	764.1
165°	775.8	776.7	777.7	778.7	779.7	779.8	778.9	778.1	777.2	776.4	776.4
167.5°	787.2	788.1	788.9	789.8	790.6	790.6	789.8	788.9	788.1	787.2	787.1
170°	795.5	796.5	797.5	798.5	799.5	799.5	798.5	797.5	796.5	795.5	795.5
172.5°	801.9	802.9	803.9	804.9	805.9	805.9	805.1	804.2	803.4	802.5	802.5
175°	806.4	807.3	808.3	809.3	810.3	810.4	809.5	808.7	807.8	807.0	807.0
177.5°	808.9	809.9	810.9	811.9	812.9	812.9	812.1	811.2	810.4	809.5	809.5
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P832024

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6
2.5°	3244.1	3241.0	3210.9	3180.8	3151.4	3122.0	3100.0	3078.1	3041.2	3004.2	2981.0
5°	3445.2	3421.4	3373.8	3326.2	3254.8	3183.3	3123.2	3063.1	2986.7	2910.2	2846.3
7.5°	3557.3	3537.9	3480.3	3422.6	3328.0	3233.5	3139.5	3045.5	2932.8	2820.0	2723.6
10°	3560.4	3576.7	3529.1	3481.5	3375.0	3268.5	3140.7	3013.0	2861.4	2709.8	2585.1
12.5°	3448.9	3519.1	3509.1	3499.0	3390.7	3282.3	3127.0	2971.6	2785.6	2599.5	2443.6
15°	3240.3	3376.3	3416.4	3456.5	3366.9	3277.3	3100.7	2924.0	2705.4	2486.8	2307.6
17.5°	2971.6	3162.0	3267.9	3373.8	3308.6	3243.5	3049.9	2856.4	2610.2	2364.0	2169.2
20°	2653.4	2902.7	3068.7	3234.7	3210.9	3187.1	2987.3	2787.5	2521.9	2256.3	2045.2
22.5°	2339.0	2602.0	2831.3	3060.6	3085.0	3109.4	2907.7	2706.0	2415.4	2124.7	1909.9
25°	2067.7	2335.2	2608.3	2881.4	2936.5	2991.7	2800.0	2608.3	2307.0	2005.7	1792.1
27.5°	1809.0	2063.3	2364.0	2664.7	2764.9	2865.1	2689.7	2514.4	2200.5	1886.7	1673.7
30°	1597.9	1825.3	2132.3	2439.2	2578.9	2718.6	2557.6	2396.6	2085.3	1774.0	1565.4
32.5°	1401.2	1604.8	1913.0	2221.2	2383.4	2545.7	2406.6	2267.6	1968.1	1668.7	1462.6
35°	1245.9	1428.2	1715.7	2003.2	2184.9	2366.5	2252.5	2138.5	1846.0	1553.5	1358.7
37.5°	1112.5	1265.3	1535.3	1805.3	1998.2	2191.1	2095.9	2000.7	1725.7	1450.7	1266.6
40°	1002.2	1125.0	1376.2	1627.4	1816.5	2005.7	1924.3	1842.9	1596.7	1350.5	1178.2
42.5°	907.6	1013.5	1239.0	1464.5	1638.0	1811.5	1757.7	1703.8	1480.8	1257.8	1098.1
45°	824.3	913.3	1111.9	1310.4	1470.2	1629.9	1587.3	1544.7	1352.4	1160.1	1013.5
47.5°	750.4	826.8	1004.1	1181.4	1324.8	1468.3	1428.8	1389.3	1230.2	1071.1	937.7
50°	682.8	747.9	895.7	1043.6	1172.6	1301.6	1269.1	1236.5	1105.0	973.4	858.2
52.5°	618.9	672.7	805.5	938.3	1042.3	1146.3	1121.2	1096.2	994.7	893.2	788.6
55°	558.1	607.6	719.7	831.9	920.8	1009.7	984.7	959.6	880.7	801.8	709.7
57.5°	503.0	546.2	637.0	727.9	798.7	869.4	857.5	845.6	779.9	714.1	638.3
60°	444.7	483.6	561.9	640.2	697.2	754.2	740.4	726.6	679.6	632.7	567.5
62.5°	392.7	427.2	489.8	552.5	598.8	645.2	635.2	625.1	589.4	553.7	499.9
65°	338.3	372.1	422.8	473.6	509.9	546.2	537.4	528.7	501.7	474.8	431.6
67.5°	288.8	317.0	360.8	404.7	429.1	453.5	448.5	443.5	422.8	402.1	368.3
70°	238.7	263.1	299.4	335.7	352.7	369.6	371.5	373.3	354.5	335.7	310.7
72.5°	188.5	208.0	241.8	275.6	288.8	301.9	301.3	300.7	289.4	278.1	255.6
75°	144.7	159.1	185.4	211.7	223.0	234.3	236.8	239.3	228.6	218.0	205.5
77.5°	104.0	114.0	134.0	154.1	166.6	179.1	180.4	181.7	176.6	171.6	159.7
80°	73.3	76.4	88.9	101.5	114.6	127.8	129.7	131.5	126.5	121.5	114.0
82.5°	50.7	52.6	57.0	61.4	72.0	82.7	85.2	87.7	85.2	82.7	74.5
85°	30.7	31.3	33.2	35.1	40.1	45.1	47.6	50.1	48.9	47.6	43.2
87.5°	13.8	13.8	14.4	15.0	16.3	17.5	20.7	23.8	21.9	20.0	18.2
90°	11.6	9.8	7.9	6.3	4.9	3.5	2.1	0.6	2.1	3.5	4.9
92.5°	25.1	24.2	23.4	22.5	21.7	20.8	20.0	19.1	20.0	20.8	21.7
95°	44.9	43.8	42.6	41.6	40.6	39.6	38.6	37.6	38.6	39.6	40.6
97.5°	67.1	66.3	65.4	64.7	64.0	63.2	62.5	61.8	62.5	63.2	64.0
100°	92.3	91.6	90.9	90.1	89.2	88.4	87.5	86.7	87.5	88.4	89.2
102.5°	119.8	118.8	117.8	117.1	116.7	116.2	115.8	115.4	115.8	116.2	116.7
105°	147.9	146.6	145.3	144.6	144.3	144.0	143.7	143.4	143.7	144.0	144.3
107.5°	178.6	178.1	177.5	177.1	177.0	176.9	176.7	176.6	176.7	176.9	177.0
110°	209.1	208.9	208.6	208.3	208.0	207.7	207.4	207.2	207.4	207.7	208.0



TEST NUMBER: P832024

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	239.7	239.7	239.7	239.6	239.5	239.3	239.2	239.0	239.2	239.3	239.5
115°	272.1	272.4	272.7	272.6	272.2	271.8	271.3	270.9	271.3	271.8	272.2
117.5°	303.3	303.6	303.9	304.0	303.8	303.7	303.6	303.4	303.6	303.7	303.8
120°	335.4	336.1	336.8	336.8	335.9	335.1	334.2	333.4	334.2	335.1	335.9
122.5°	366.5	366.7	367.0	366.9	366.3	365.7	365.2	364.6	365.2	365.7	366.3
125°	397.7	398.0	398.3	398.2	397.8	397.3	396.9	396.5	396.9	397.3	397.8
127.5°	428.9	429.2	429.5	429.2	428.4	427.5	426.7	425.8	426.7	427.5	428.4
130°	459.2	459.6	460.0	459.7	458.5	457.4	456.3	455.1	456.3	457.4	458.5
132.5°	488.8	489.1	489.4	489.0	487.9	486.7	485.6	484.5	485.6	486.7	487.9
135°	517.9	518.0	518.2	517.8	517.0	516.1	515.3	514.4	515.3	516.1	517.0
137.5°	546.1	545.6	545.2	544.7	543.9	543.2	542.5	541.8	542.5	543.2	543.9
140°	574.0	573.9	573.8	573.3	572.6	571.9	571.2	570.5	571.2	571.9	572.6
142.5°	600.5	600.3	600.0	599.5	598.8	598.1	597.3	596.6	597.3	598.1	598.8
145°	626.4	626.0	625.5	625.2	624.9	624.6	624.3	624.0	624.3	624.6	624.9
147.5°	651.2	650.8	650.4	649.9	649.3	648.8	648.2	647.6	648.2	648.8	649.3
150°	674.5	674.2	673.9	673.6	673.3	673.1	672.8	672.5	672.8	673.1	673.3
152.5°	695.2	695.0	694.9	694.6	694.2	693.7	693.3	692.9	693.3	693.7	694.2
155°	714.9	714.8	714.6	714.6	714.6	714.6	714.6	714.6	714.6	714.6	714.6
157.5°	732.8	732.6	732.5	732.5	732.6	732.8	732.9	733.1	732.9	732.8	732.6
160°	749.0	749.0	749.0	749.1	749.4	749.7	750.0	750.3	750.0	749.7	749.4
162.5°	764.0	763.9	763.7	763.9	764.3	764.7	765.1	765.6	765.1	764.7	764.3
165°	776.4	776.4	776.4	776.6	777.0	777.5	777.9	778.3	777.9	777.5	777.0
167.5°	786.9	786.8	786.7	786.9	787.4	788.0	788.6	789.1	788.6	788.0	787.4
170°	795.5	795.5	795.5	795.8	796.4	796.9	797.5	798.1	797.5	796.9	796.4
172.5°	802.5	802.5	802.5	802.8	803.4	803.9	804.5	805.1	804.5	803.9	803.4
175°	807.0	807.0	807.0	807.3	807.8	808.4	809.0	809.5	809.0	808.4	807.8
177.5°	809.5	809.5	809.5	809.8	810.4	811.0	811.5	812.1	811.5	811.0	810.4
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P832024

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6	3055.6
2.5°	2957.8	2922.1	2886.4	2860.7	2835.1	2803.1	2771.2	2769.9	2768.7	2744.9	2721.1
5°	2782.4	2720.4	2658.4	2597.7	2536.9	2476.1	2415.4	2401.6	2387.8	2367.1	2346.5
7.5°	2627.1	2528.1	2429.2	2351.5	2273.8	2213.1	2152.3	2111.0	2069.6	2037.7	2005.7
10°	2460.5	2337.7	2214.9	2121.0	2027.0	1961.2	1895.5	1847.9	1800.3	1777.7	1755.2
12.5°	2287.6	2154.2	2020.8	1928.7	1836.6	1757.7	1678.7	1635.5	1592.3	1561.0	1529.7
15°	2128.5	1985.0	1841.6	1743.9	1646.2	1572.3	1498.3	1455.1	1411.9	1380.6	1349.3
17.5°	1974.4	1829.7	1685.0	1586.0	1487.1	1420.0	1353.0	1311.0	1269.1	1249.7	1230.2
20°	1834.1	1688.1	1542.2	1448.9	1355.5	1289.7	1224.0	1201.4	1178.9	1160.7	1142.5
22.5°	1695.0	1554.7	1414.4	1324.8	1235.3	1187.6	1140.0	1121.9	1103.7	1089.9	1076.1
25°	1578.5	1438.8	1299.1	1220.8	1142.5	1105.6	1068.6	1056.7	1044.8	1031.0	1017.3
27.5°	1460.8	1328.0	1195.2	1132.5	1069.9	1039.8	1009.7	994.7	979.7	968.4	957.1
30°	1356.8	1234.0	1111.2	1059.2	1007.2	980.9	954.6	938.3	922.1	911.4	900.8
32.5°	1256.5	1147.6	1038.6	994.1	949.6	923.9	898.3	882.6	866.9	854.4	841.9
35°	1163.8	1069.3	974.7	934.0	893.2	867.6	841.9	826.2	810.6	798.0	785.5
37.5°	1082.4	996.6	910.8	872.6	834.4	811.8	789.3	773.0	756.7	743.5	730.4
40°	1006.0	930.2	854.4	817.4	780.5	756.1	731.6	717.2	702.8	690.9	679.0
42.5°	938.3	868.8	799.3	762.9	726.6	703.4	680.3	663.4	646.4	639.5	632.7
45°	866.9	805.5	744.2	709.1	674.0	649.6	625.1	610.7	596.3	590.1	583.8
47.5°	804.3	747.3	690.3	655.8	621.4	599.5	577.5	566.3	555.0	546.2	537.4
50°	742.9	687.8	632.7	599.5	566.3	547.5	528.7	514.9	501.1	494.9	488.6
52.5°	684.0	633.9	583.8	550.0	516.1	498.0	479.8	467.9	456.0	442.9	429.7
55°	617.6	573.8	529.9	499.9	469.8	451.0	432.2	418.4	404.7	390.9	377.1
57.5°	562.5	519.3	476.1	449.1	422.2	404.0	385.9	370.8	355.8	344.5	333.2
60°	502.4	464.8	427.2	400.9	374.6	357.0	339.5	325.1	310.7	305.1	299.4
62.5°	446.0	410.9	375.8	352.7	329.5	312.6	295.7	286.3	276.9	273.1	269.4
65°	388.4	358.3	328.2	306.9	285.6	271.2	256.8	252.4	248.1	244.9	241.8
67.5°	334.5	308.8	283.1	264.3	245.5	235.5	225.5	220.5	215.5	211.7	208.0
70°	285.6	263.1	240.5	224.2	208.0	198.6	189.2	184.8	180.4	173.5	166.6
72.5°	233.0	215.5	197.9	185.4	172.9	164.7	156.6	147.8	139.1	132.8	126.5
75°	192.9	175.4	157.9	146.0	134.0	124.7	115.3	112.1	109.0	107.1	105.2
77.5°	147.8	132.8	117.8	108.4	99.0	94.6	90.2	88.3	86.4	85.8	85.2
80°	106.5	94.0	81.4	76.4	71.4	70.2	68.9	67.7	66.4	65.8	65.1
82.5°	66.4	60.1	53.9	52.6	51.4	50.7	50.1	49.5	48.9	48.2	47.6
85°	38.8	36.3	33.8	33.2	32.6	31.9	31.3	31.3	31.3	31.3	31.3
87.5°	16.3	16.3	16.3	16.3	16.3	16.3	16.3	16.3	16.3	15.7	15.0
90°	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.4	17.0	17.6	18.0
92.5°	22.5	23.4	24.2	25.1	25.9	26.8	27.2	27.6	28.0	28.5	28.5
95°	41.6	42.6	43.8	44.9	46.0	47.2	47.7	48.3	48.9	49.4	49.7
97.5°	64.7	65.4	66.3	67.1	68.0	68.8	69.6	70.3	71.0	71.7	72.0
100°	90.1	90.9	91.6	92.3	93.0	93.7	94.1	94.6	95.0	95.4	95.8
102.5°	117.1	117.8	118.8	119.8	120.8	121.8	122.2	122.6	123.0	123.4	123.6
105°	144.6	145.3	146.6	147.9	149.2	150.4	150.4	150.4	150.4	150.4	150.6
107.5°	177.1	177.5	178.1	178.6	179.2	179.8	180.2	180.6	181.0	181.5	181.6
110°	208.3	208.6	208.9	209.1	209.4	209.7	210.3	210.8	211.4	212.0	212.1



TEST NUMBER: P832024

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	239.6	239.7	239.7	239.7	239.7	239.7	240.4	241.1	241.8	242.5	242.9
115°	272.6	272.7	272.4	272.1	271.8	271.5	271.7	271.8	272.0	272.1	272.1
117.5°	304.0	303.9	303.6	303.3	303.1	302.8	302.8	302.8	302.8	302.8	302.6
120°	336.8	336.8	336.1	335.4	334.7	334.0	333.9	333.7	333.6	333.4	333.2
122.5°	366.9	367.0	366.7	366.5	366.2	365.9	365.5	365.0	364.6	364.2	363.8
125°	398.2	398.3	398.0	397.7	397.4	397.1	396.6	396.0	395.4	394.9	394.3
127.5°	429.2	429.5	429.2	428.9	428.6	428.4	427.5	426.7	425.8	425.0	424.2
130°	459.7	460.0	459.6	459.2	458.7	458.3	457.7	457.2	456.6	456.0	455.3
132.5°	489.0	489.4	489.1	488.8	488.6	488.3	487.6	486.9	486.2	485.4	484.7
135°	517.8	518.2	518.0	517.9	517.7	517.6	517.0	516.5	515.9	515.3	514.9
137.5°	544.7	545.2	545.6	546.1	546.5	546.9	546.2	545.5	544.8	544.1	543.5
140°	573.3	573.8	573.9	574.0	574.2	574.3	574.2	574.0	573.9	573.8	573.2
142.5°	599.5	600.0	600.3	600.5	600.8	601.1	601.0	600.8	600.7	600.5	600.1
145°	625.2	625.5	626.0	626.4	626.8	627.2	627.1	627.0	626.8	626.7	626.3
147.5°	649.9	650.4	650.8	651.2	651.7	652.1	652.1	652.1	652.1	652.1	651.7
150°	673.6	673.9	674.2	674.5	674.8	675.0	675.0	675.0	675.0	675.0	674.6
152.5°	694.6	694.9	695.0	695.2	695.3	695.4	695.7	696.0	696.3	696.6	696.4
155°	714.6	714.6	714.8	714.9	715.1	715.2	715.8	716.3	716.9	717.5	717.3
157.5°	732.5	732.5	732.6	732.8	732.9	733.1	733.6	734.2	734.8	735.3	735.2
160°	749.1	749.0	749.0	749.0	749.0	749.0	749.7	750.4	751.1	751.8	751.9
162.5°	763.9	763.7	763.9	764.0	764.1	764.3	765.0	765.7	766.4	767.1	767.0
165°	776.6	776.4	776.4	776.4	776.4	776.4	777.2	778.1	778.9	779.8	779.7
167.5°	786.9	786.7	786.8	786.9	787.1	787.2	788.1	788.9	789.8	790.6	790.6
170°	795.8	795.5	795.5	795.5	795.5	795.5	796.5	797.5	798.5	799.5	799.5
172.5°	802.8	802.5	802.5	802.5	802.5	802.5	803.4	804.2	805.1	805.9	805.9
175°	807.3	807.0	807.0	807.0	807.0	807.0	807.8	808.7	809.5	810.4	810.3
177.5°	809.8	809.5	809.5	809.5	809.5	809.5	810.4	811.2	812.1	812.9	812.9
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P832024

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3055.6	3055.6	3055.6	3055.6
2.5°	2714.8	2708.5	2706.0	2703.5
5°	2327.1	2307.6	2303.3	2298.9
7.5°	1997.6	1989.4	1962.5	1935.6
10°	1730.1	1705.0	1693.8	1682.5
12.5°	1506.5	1483.3	1479.5	1475.8
15°	1333.0	1316.7	1311.0	1305.4
17.5°	1219.0	1207.7	1200.8	1193.9
20°	1134.4	1126.3	1121.2	1116.2
22.5°	1069.9	1063.6	1059.9	1056.1
25°	1007.9	998.5	995.3	992.2
27.5°	949.0	940.8	937.7	934.6
30°	893.9	887.0	882.6	878.2
32.5°	833.7	825.6	823.1	820.6
35°	780.5	775.5	773.0	770.5
37.5°	724.1	717.8	714.1	710.3
40°	675.9	672.7	670.9	669.0
42.5°	627.0	621.4	620.8	620.1
45°	578.2	572.5	571.3	570.0
47.5°	532.4	527.4	526.8	526.2
50°	481.7	474.8	469.8	464.8
52.5°	423.4	417.2	412.8	408.4
55°	370.2	363.3	359.6	355.8
57.5°	330.1	327.0	325.1	323.2
60°	297.5	295.7	294.4	293.2
62.5°	267.5	265.6	265.6	265.6
65°	239.9	238.0	236.2	234.3
67.5°	204.2	200.4	199.8	199.2
70°	161.0	155.3	154.7	154.1
72.5°	125.9	125.3	124.0	122.8
75°	104.0	102.7	102.7	102.7
77.5°	83.9	82.7	82.7	82.7
80°	64.5	63.9	64.5	65.1
82.5°	47.6	47.6	47.0	46.4
85°	30.7	30.1	30.1	30.1
87.5°	15.0	15.0	15.0	15.0
90°	18.3	18.6	18.8	19.1
92.5°	28.3	28.0	27.7	27.4
95°	49.7	49.7	49.7	49.7
97.5°	71.8	71.7	71.5	71.4
100°	96.0	96.3	96.6	96.9
102.5°	123.4	123.3	123.2	123.0
105°	150.9	151.1	151.4	151.7
107.5°	181.5	181.3	181.2	181.0
110°	211.8	211.6	211.3	211.0



TEST NUMBER: P832024

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	242.9	242.9	242.9	242.9
115°	272.0	271.8	271.7	271.5
117.5°	302.1	301.7	301.3	300.9
120°	333.0	332.7	332.4	332.1
122.5°	363.3	362.9	362.5	362.1
125°	393.7	393.2	392.6	392.0
127.5°	423.7	423.1	422.5	422.0
130°	454.3	453.3	452.3	451.3
132.5°	484.0	483.3	482.6	481.9
135°	514.6	514.3	514.1	513.8
137.5°	543.1	542.7	542.2	541.8
140°	572.2	571.2	570.2	569.2
142.5°	599.4	598.7	598.0	597.3
145°	625.7	625.2	624.6	624.0
147.5°	650.8	650.0	649.1	648.3
150°	673.8	672.9	672.1	671.2
152.5°	695.7	694.9	694.2	693.5
155°	716.3	715.3	714.3	713.3
157.5°	734.3	733.5	732.6	731.8
160°	751.3	750.8	750.2	749.6
162.5°	766.0	765.0	764.0	763.0
165°	778.7	777.7	776.7	775.8
167.5°	789.8	788.9	788.1	787.2
170°	798.5	797.5	796.5	795.5
172.5°	804.9	803.9	802.9	801.9
175°	809.3	808.3	807.3	806.4
177.5°	811.9	810.9	809.9	808.9
180°	811.5	811.5	811.5	811.5



TEST NUMBER: P832024

CATALOG NUMBER: S123RDIP-S1165D805U930-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.13	15.07	14.97	15.91	16.97	18.80	19.73	19.64	20.58	21.64
	3H	15.36	16.20	16.21	17.05	18.14	20.31	21.14	21.16	22.00	23.08
	4H	15.75	16.53	16.62	17.40	18.50	20.80	21.58	21.67	22.45	23.55
	6H	16.04	16.76	16.91	17.63	18.74	21.12	21.84	21.99	22.71	23.82
	8H	16.13	16.81	17.01	17.70	18.81	21.20	21.88	22.08	22.77	23.88
	12H	16.18	16.83	17.07	17.72	18.85	21.23	21.89	22.12	22.77	23.90
4H	2H	14.87	15.65	15.74	16.52	17.61	18.81	19.59	19.68	20.46	21.55
	3H	16.25	16.90	17.13	17.80	18.91	20.47	21.12	21.35	22.02	23.13
	4H	16.71	17.30	17.60	18.19	19.33	21.08	21.67	21.98	22.57	23.71
	6H	17.08	17.59	17.99	18.51	19.65	21.53	22.04	22.43	22.95	24.09
	8H	17.21	17.68	18.12	18.59	19.75	21.66	22.13	22.57	23.05	24.20
	12H	17.29	17.71	18.21	18.65	19.80	21.73	22.15	22.65	23.08	24.24
8H	4H	17.03	17.50	17.94	18.42	19.57	21.06	21.53	21.97	22.45	23.60
	6H	17.50	17.89	18.43	18.84	19.99	21.56	21.95	22.49	22.90	24.05
	8H	17.69	18.03	18.63	18.98	20.15	21.74	22.09	22.69	23.04	24.20
	12H	17.83	18.14	18.78	19.08	20.29	21.86	22.17	22.81	23.11	24.33
12H	4H	17.04	17.47	17.97	18.40	19.56	21.01	21.44	21.94	22.37	23.53
	6H	17.55	17.90	18.50	18.85	20.02	21.53	21.88	22.48	22.82	23.99
	8H	17.78	18.08	18.72	19.02	20.24	21.73	22.03	22.68	22.97	24.19