

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832077

Luminaire Tested: S123RDIP-S340D1195U930-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832077
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1195U930-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5090.1 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 43.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832077

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P832077

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24				24
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21				21
2	84	77	72	67	75	69	64	60	53	50	48	39	37	35	26	25	24	18				18
3	77	68	62	56	68	61	55	51	48	44	40	35	32	30	23	22	21	16				16
4	71	61	53	48	63	54	48	43	42	38	35	31	29	26	21	19	18	14				14
5	65	54	47	41	58	49	42	37	38	34	30	28	25	23	19	17	16	12				12
6	60	49	41	36	53	44	37	33	34	30	26	26	23	20	18	16	14	11				11
7	55	44	37	31	49	40	33	29	31	27	23	23	20	18	16	14	13	10				10
8	51	40	33	28	46	36	30	25	29	24	21	22	19	16	15	13	12	9				9
9	48	36	29	25	43	33	27	23	26	22	19	20	17	15	14	12	11	9				9
10	45	33	27	22	40	30	24	20	24	20	17	18	15	13	13	11	10	8				8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	9749	9749	9749	9749	9749
5°	11577	11207	9811	7931	7363
10°	10488	11384	9762	6355	5451
15°	7221	9760	9658	5194	4313
20°	5024	7514	9465	4379	3790
25°	3828	5727	9183	3892	3493
30°	3332	4579	8830	3614	3235
35°	3059	3862	8330	3380	3001
40°	2792	3450	7676	3149	2786
45°	2521	3154	6970	2930	2573
50°	2289	2910	6137	2718	2308
55°	2070	2672	5339	2509	1980
60°	1856	2430	4637	2278	1871
65°	1712	2157	3991	2048	1768
70°	1391	1863	3484	1854	1438
75°	1219	1485	2949	1535	1268
80°	1103	1252	2417	1289	1196
85°	1013	1099	1840	1173	1099

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 7354 cd/sqm

TEST NUMBER: P832077

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.6	1.6
10°-20°	191.0	3.8
20°-30°	219.2	4.3
30°-40°	216.0	4.2
40°-50°	190.5	3.7
50°-60°	146.6	2.9
60°-70°	96.4	1.9
70°-80°	46.8	0.9
80°-90°	14.3	0.3
90°-100°	44.9	0.9
100°-110°	217.3	4.3
110°-120°	532.6	10.5
120°-130°	676.2	13.3
130°-140°	722.4	14.2
140°-150°	675.5	13.3
150°-160°	544.9	10.7
160°-170°	351.6	6.9
170°-180°	121.2	2.4
0°-30°	492.8	9.7
0°-40°	708.8	13.9
0°-60°	1045.9	20.5
0°-90°	1203.4	23.6
90°-120°	794.9	15.6
90°-150°	2869.0	56.4
90°-180°	3887.0	76.4
0°-180°	5090.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	906	906	906	906	906	
5°	1071	1037	908	734	681	98
15°	648	876	867	466	387	183
25°	322	482	773	328	294	152
35°	233	294	634	257	228	145
45°	166	207	458	192	169	129
55°	110	142	284	134	106	99
65°	67	85	157	80	69	66
75°	29	36	71	37	30	32
85°	8	9	15	10	9	9
90°	28	23	1	23	28	13
95°	36	29	58	29	36	30
105°	42	207	282	207	42	87
115°	557	544	530	544	557	524
125°	762	758	746	758	762	681
135°	939	939	929	939	939	724
145°	1083	1081	1072	1081	1083	676
155°	1179	1180	1181	1180	1179	544
165°	1243	1242	1246	1242	1243	351
175°	1270	1271	1275	1271	1270	121
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P832077

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7
2.5°	1003.8	1000.6	997.5	996.5	995.6	992.6	989.7	983.0	976.3	969.4	962.6
5°	1071.4	1071.7	1072.1	1071.2	1070.2	1066.3	1062.4	1054.3	1046.1	1037.2	1028.3
7.5°	1050.6	1056.5	1062.4	1063.6	1064.7	1067.6	1070.6	1068.8	1066.9	1063.6	1060.2
10°	959.6	959.2	958.8	965.5	972.2	992.1	1011.9	1022.2	1032.4	1041.5	1050.6
12.5°	811.0	811.6	812.2	834.1	856.0	874.7	893.5	919.5	945.5	973.5	1001.5
15°	648.0	657.1	666.2	685.7	705.2	733.4	761.7	796.6	831.5	875.8	920.2
17.5°	532.2	536.1	540.0	558.7	577.5	604.2	630.9	670.5	710.0	767.2	824.4
20°	438.6	442.1	445.6	459.2	472.7	498.4	524.0	561.7	599.4	656.0	712.6
22.5°	366.2	373.0	379.9	389.0	398.1	416.7	435.2	473.7	512.1	563.7	615.3
25°	322.3	325.5	328.7	336.4	344.2	362.1	379.9	405.3	430.8	482.2	533.6
27.5°	292.6	293.6	294.5	300.2	306.0	317.5	329.0	352.6	376.2	418.5	460.9
30°	268.1	269.8	271.5	275.9	280.4	288.7	297.1	313.8	330.5	368.4	406.3
32.5°	249.2	250.1	251.0	254.8	258.5	264.6	270.7	283.9	297.1	326.1	355.0
35°	232.8	233.0	233.2	236.0	238.8	244.7	250.7	261.6	272.6	293.9	315.3
37.5°	214.3	215.6	216.9	218.9	221.0	226.2	231.4	240.3	249.2	266.8	284.5
40°	198.7	199.8	200.9	203.3	205.7	209.8	213.9	222.1	230.2	245.5	260.7
42.5°	183.1	183.8	184.6	187.0	189.4	194.4	199.4	205.9	212.4	225.0	237.7
45°	165.6	167.5	169.3	171.9	174.5	178.8	183.1	189.8	196.4	207.2	218.0
47.5°	151.1	152.1	153.0	155.2	157.5	162.7	167.9	173.8	179.7	189.8	199.8
50°	136.7	137.0	137.4	139.4	141.5	146.1	150.8	157.6	164.5	173.8	183.1
52.5°	122.9	123.8	124.8	126.8	128.9	132.0	135.2	142.2	149.3	158.4	167.5
55°	110.3	110.8	111.4	112.9	114.4	118.1	121.8	127.9	134.1	142.4	150.8
57.5°	98.4	99.2	99.9	101.0	102.1	105.5	108.8	114.2	119.6	127.9	136.3
60°	86.2	87.1	88.0	89.3	90.6	93.2	95.8	100.6	105.5	112.9	120.3
62.5°	77.2	77.4	77.6	78.7	79.8	81.7	83.6	87.5	91.4	98.8	106.2
65°	67.2	67.8	68.3	68.9	69.4	70.9	72.4	75.8	79.1	84.7	90.2
67.5°	56.8	57.4	57.9	58.9	59.8	61.1	62.4	64.6	66.8	72.0	77.2
70°	44.2	44.2	44.2	45.7	47.2	49.4	51.6	53.3	55.0	59.2	63.5
72.5°	36.0	36.2	36.4	36.6	36.8	38.1	39.4	42.1	44.9	47.5	50.1
75°	29.3	29.5	29.7	29.9	30.1	30.5	30.8	31.8	32.7	35.7	38.6
77.5°	23.4	23.6	23.8	24.0	24.1	24.5	24.9	25.3	25.6	26.7	27.9
80°	17.8	18.0	18.2	18.4	18.6	18.8	18.9	19.3	19.7	20.2	20.8
82.5°	13.0	13.0	13.0	13.0	13.0	13.4	13.7	13.7	13.7	14.1	14.5
85°	8.2	8.2	8.2	8.4	8.5	8.5	8.5	8.7	8.9	8.9	8.9
87.5°	3.7	3.5	3.3	3.5	3.7	3.7	3.7	3.9	4.1	4.1	4.1
90°	28.4	28.0	27.6	27.2	26.7	26.1	25.3	24.4	23.6	22.7	20.0
92.5°	32.2	32.0	31.8	31.6	31.4	30.5	29.0	27.6	26.1	24.6	22.7
95°	36.0	36.0	36.0	36.0	36.0	35.3	33.8	32.3	30.8	29.4	27.0
97.5°	38.8	38.6	38.4	38.2	38.0	37.0	35.4	33.7	32.0	30.3	41.0
100°	39.8	39.6	39.4	39.2	38.9	38.0	36.3	34.6	32.9	31.3	64.1
102.5°	40.7	40.3	39.9	39.5	39.0	42.3	49.3	56.2	63.1	70.1	106.7
105°	41.7	41.3	40.8	40.4	40.0	58.4	95.7	132.9	170.2	207.4	226.4
107.5°	98.5	126.1	153.7	181.2	208.8	238.8	271.2	303.6	336.1	368.5	365.3
110°	260.5	290.6	320.7	350.8	380.9	399.4	406.4	413.3	420.3	427.2	424.9



TEST NUMBER: P832077

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	493.5	493.9	494.3	494.8	495.2	494.4	492.6	490.7	488.8	486.9	484.6
115°	557.0	556.1	555.3	554.4	553.6	552.1	550.0	547.9	545.8	543.7	541.8
117.5°	608.1	607.9	607.7	607.5	607.3	606.3	604.6	603.0	601.3	599.6	598.5
120°	661.2	661.2	661.2	661.2	661.2	660.3	658.6	657.0	655.3	653.6	653.0
122.5°	713.3	713.0	712.8	712.6	712.4	711.8	710.7	709.7	708.6	707.6	706.7
125°	761.6	761.1	760.7	760.3	759.9	759.5	759.0	758.6	758.2	757.8	756.9
127.5°	808.9	809.3	809.8	810.2	810.6	810.5	809.9	809.2	808.6	808.0	806.9
130°	854.4	854.8	855.2	855.7	856.1	855.9	855.0	854.2	853.3	852.5	851.7
132.5°	896.1	896.7	897.3	898.0	898.6	898.5	897.7	896.8	896.0	895.1	894.5
135°	938.7	939.3	940.0	940.6	941.2	941.2	940.6	940.0	939.3	938.7	937.9
137.5°	979.4	979.8	980.3	980.7	981.1	980.8	979.7	978.7	977.6	976.6	976.2
140°	1015.4	1015.8	1016.3	1016.7	1017.1	1016.9	1016.1	1015.2	1014.4	1013.5	1012.9
142.5°	1048.6	1049.2	1049.8	1050.5	1051.1	1051.1	1050.5	1049.8	1049.2	1048.6	1047.9
145°	1082.7	1082.7	1082.7	1082.7	1082.7	1082.5	1082.0	1081.6	1081.2	1080.8	1080.4
147.5°	1107.3	1108.4	1109.4	1110.5	1111.5	1111.8	1111.4	1111.0	1110.6	1110.1	1109.7
150°	1135.7	1136.4	1137.0	1137.6	1138.2	1138.3	1137.9	1137.5	1137.1	1136.7	1136.2
152.5°	1158.5	1159.5	1160.6	1161.6	1162.7	1162.8	1161.9	1161.1	1160.2	1159.4	1159.2
155°	1179.3	1180.6	1181.8	1183.1	1184.3	1184.4	1183.4	1182.3	1181.3	1180.2	1180.0
157.5°	1197.3	1199.0	1200.7	1202.3	1204.0	1204.2	1203.0	1201.7	1200.4	1199.2	1199.4
160°	1214.3	1215.8	1217.3	1218.8	1220.2	1220.3	1219.1	1217.8	1216.5	1215.3	1215.5
162.5°	1230.4	1231.7	1233.0	1234.2	1235.5	1235.4	1233.9	1232.4	1231.0	1229.5	1229.7
165°	1242.8	1244.2	1245.7	1247.2	1248.6	1248.5	1246.9	1245.2	1243.5	1241.8	1242.0
167.5°	1252.2	1253.9	1255.6	1257.3	1259.0	1259.0	1257.3	1255.6	1253.9	1252.2	1252.2
170°	1260.8	1262.4	1264.1	1265.8	1267.5	1267.5	1265.8	1264.1	1262.4	1260.8	1260.8
172.5°	1265.5	1267.4	1269.3	1271.2	1273.1	1273.2	1271.5	1269.8	1268.1	1266.4	1266.2
175°	1270.2	1271.9	1273.6	1275.3	1277.0	1277.1	1275.6	1274.1	1272.6	1271.2	1271.0
177.5°	1271.2	1273.3	1275.4	1277.5	1279.6	1279.8	1278.1	1276.4	1274.7	1273.1	1272.9
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P832077

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7
2.5°	961.6	960.7	951.8	942.9	934.1	925.4	918.9	912.4	901.5	890.5	883.6
5°	1021.2	1014.2	1000.1	986.0	964.8	943.6	925.8	908.0	885.3	862.7	843.7
7.5°	1054.5	1048.7	1031.6	1014.5	986.5	958.5	930.6	902.8	869.3	835.9	807.3
10°	1055.4	1060.2	1046.1	1032.0	1000.4	968.9	931.0	893.1	848.2	803.2	766.3
12.5°	1022.3	1043.1	1040.2	1037.2	1005.1	973.0	926.9	880.9	825.7	770.6	724.3
15°	960.5	1000.8	1012.7	1024.6	998.0	971.5	919.1	866.7	801.9	737.1	684.0
17.5°	880.9	937.3	968.7	1000.1	980.8	961.4	904.1	846.7	773.7	700.7	643.0
20°	786.5	860.4	909.6	958.8	951.8	944.7	885.5	826.3	747.5	668.8	606.2
22.5°	693.3	771.3	839.3	907.2	914.5	921.7	861.9	802.1	716.0	629.8	566.1
25°	612.9	692.2	773.2	854.1	870.5	886.8	830.0	773.2	683.9	594.5	531.2
27.5°	536.2	611.6	700.7	789.9	819.6	849.3	797.3	745.3	652.3	559.3	496.1
30°	473.7	541.1	632.0	723.0	764.4	805.8	758.1	710.4	618.1	525.8	464.0
32.5°	415.4	475.7	567.1	658.4	706.5	754.6	713.4	672.2	583.4	494.6	433.6
35°	369.3	423.3	508.6	593.8	647.6	701.5	667.7	633.9	547.2	460.5	402.7
37.5°	329.8	375.1	455.1	535.1	592.3	649.5	621.3	593.1	511.5	430.0	375.4
40°	297.1	333.5	407.9	482.4	538.5	594.5	570.4	546.3	473.3	400.3	349.3
42.5°	269.0	300.4	367.3	434.1	485.5	537.0	521.0	505.0	438.9	372.8	325.5
45°	244.4	270.7	329.6	388.4	435.8	483.1	470.5	457.9	400.9	343.9	300.4
47.5°	222.4	245.1	297.6	350.2	392.7	435.2	423.5	411.8	364.7	317.5	278.0
50°	202.4	221.7	265.5	309.3	347.6	385.8	376.2	366.5	327.5	288.5	254.4
52.5°	183.4	199.4	238.8	278.1	309.0	339.8	332.4	324.9	294.9	264.8	233.8
55°	165.4	180.1	213.3	246.6	272.9	299.3	291.9	284.5	261.1	237.7	210.4
57.5°	149.1	161.9	188.8	215.8	236.7	257.7	254.2	250.7	231.2	211.7	189.2
60°	131.8	143.3	166.6	189.8	206.7	223.6	219.5	215.4	201.5	187.5	168.2
62.5°	116.4	126.6	145.2	163.8	177.5	191.2	188.3	185.3	174.7	164.1	148.2
65°	100.3	110.3	125.3	140.4	151.1	161.9	159.3	156.7	148.7	140.7	127.9
67.5°	85.6	94.0	107.0	119.9	127.2	134.4	132.9	131.5	125.3	119.2	109.2
70°	70.7	78.0	88.8	99.5	104.5	109.6	110.1	110.7	105.1	99.5	92.1
72.5°	55.9	61.6	71.7	81.7	85.6	89.5	89.3	89.1	85.8	82.4	75.8
75°	42.9	47.2	55.0	62.8	66.1	69.4	70.2	70.9	67.8	64.6	60.9
77.5°	30.8	33.8	39.7	45.7	49.4	53.1	53.5	53.8	52.4	50.9	47.3
80°	21.7	22.7	26.4	30.1	34.0	37.9	38.4	39.0	37.5	36.0	33.8
82.5°	15.0	15.6	16.9	18.2	21.4	24.5	25.3	26.0	25.3	24.5	22.1
85°	9.1	9.3	9.8	10.4	11.9	13.4	14.1	14.9	14.5	14.1	12.8
87.5°	4.1	4.1	4.3	4.5	4.8	5.2	6.1	7.1	6.5	5.9	5.4
90°	17.3	14.5	11.8	9.4	7.3	5.2	3.1	0.9	3.1	5.2	7.3
92.5°	20.8	18.9	17.0	16.7	18.0	19.3	20.5	21.8	20.5	19.3	18.0
95°	24.7	22.4	20.1	23.3	31.9	40.5	49.2	57.8	49.2	40.5	31.9
97.5°	51.8	62.5	73.3	81.6	87.5	93.4	99.2	105.1	99.2	93.4	87.5
100°	96.9	129.8	162.6	176.9	172.7	168.5	164.3	160.1	164.3	168.5	172.7
102.5°	143.3	180.0	216.6	233.5	230.8	228.1	225.3	222.6	225.3	228.1	230.8
105°	245.3	264.3	283.2	291.5	289.2	286.9	284.6	282.3	284.6	286.9	289.2
107.5°	362.2	359.0	355.8	353.3	351.4	349.5	347.6	345.7	347.6	349.5	351.4
110°	422.6	420.3	417.9	415.9	414.3	412.6	410.9	409.2	410.9	412.6	414.3



TEST NUMBER: P832077

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	482.2	479.9	477.6	475.7	474.2	472.8	471.3	469.8	471.3	472.8	474.2
115°	539.9	538.0	536.1	534.5	533.3	532.0	530.8	529.5	530.8	532.0	533.3
117.5°	597.5	596.4	595.4	594.1	592.6	591.2	589.7	588.2	589.7	591.2	592.6
120°	652.3	651.7	651.1	649.8	647.9	646.0	644.1	642.2	644.1	646.0	647.9
122.5°	705.9	705.0	704.2	703.0	701.6	700.1	698.6	697.2	698.6	700.1	701.6
125°	756.1	755.3	754.4	753.1	751.5	749.8	748.1	746.4	748.1	749.8	751.5
127.5°	805.9	804.8	803.8	802.4	800.7	799.0	797.4	795.7	797.4	799.0	800.7
130°	850.8	850.0	849.1	847.9	846.2	844.5	842.8	841.1	842.8	844.5	846.2
132.5°	893.9	893.2	892.6	891.4	889.8	888.1	886.4	884.7	886.4	888.1	889.8
135°	937.0	936.2	935.3	934.3	933.0	931.8	930.5	929.2	930.5	931.8	933.0
137.5°	975.7	975.3	974.9	973.8	972.2	970.5	968.8	967.1	968.8	970.5	972.2
140°	1012.3	1011.6	1011.0	1010.1	1008.8	1007.5	1006.3	1005.0	1006.3	1007.5	1008.8
142.5°	1047.3	1046.7	1046.0	1045.1	1043.8	1042.6	1041.3	1040.0	1041.3	1042.6	1043.8
145°	1079.9	1079.5	1079.1	1078.1	1076.7	1075.2	1073.7	1072.3	1073.7	1075.2	1076.7
147.5°	1109.3	1108.9	1108.5	1107.7	1106.7	1105.6	1104.6	1103.5	1104.6	1105.6	1106.7
150°	1135.8	1135.4	1135.0	1134.5	1133.8	1133.2	1132.6	1131.9	1132.6	1133.2	1133.8
152.5°	1159.0	1158.8	1158.6	1158.3	1158.1	1157.9	1157.7	1157.5	1157.7	1157.9	1158.1
155°	1179.8	1179.6	1179.4	1179.5	1179.9	1180.3	1180.8	1181.2	1180.8	1180.3	1179.9
157.5°	1199.6	1199.8	1200.0	1200.1	1200.1	1200.1	1200.1	1200.1	1200.1	1200.1	1200.1
160°	1215.7	1215.9	1216.1	1216.3	1216.5	1216.8	1217.0	1217.2	1217.0	1216.8	1216.5
162.5°	1229.9	1230.1	1230.3	1230.8	1231.4	1232.0	1232.7	1233.3	1232.7	1232.0	1231.4
165°	1242.2	1242.4	1242.6	1243.1	1243.7	1244.3	1245.0	1245.6	1245.0	1244.3	1243.7
167.5°	1252.2	1252.2	1252.2	1252.6	1253.5	1254.3	1255.2	1256.0	1255.2	1254.3	1253.5
170°	1260.8	1260.8	1260.8	1261.2	1262.0	1262.9	1263.7	1264.5	1263.7	1262.9	1262.0
172.5°	1266.0	1265.8	1265.6	1266.0	1267.1	1268.1	1269.2	1270.2	1269.2	1268.1	1267.1
175°	1270.8	1270.5	1270.3	1270.8	1271.8	1272.9	1273.9	1275.0	1273.9	1272.9	1271.8
177.5°	1272.6	1272.4	1272.2	1272.6	1273.7	1274.7	1275.8	1276.9	1275.8	1274.7	1273.7
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P832077

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7	905.7
2.5°	876.8	866.2	855.6	848.0	840.4	830.9	821.4	821.1	820.7	813.6	806.6
5°	824.8	806.4	788.0	770.0	752.0	734.0	716.0	711.9	707.8	701.7	695.6
7.5°	778.7	749.4	720.1	697.0	674.0	656.0	638.0	625.7	613.5	604.0	594.5
10°	729.3	693.0	656.6	628.7	600.9	581.4	561.9	547.8	533.6	527.0	520.3
12.5°	678.1	638.5	599.0	571.7	544.4	521.0	497.6	484.8	472.0	462.7	453.4
15°	630.9	588.4	545.9	516.9	488.0	466.1	444.1	431.3	418.5	409.2	400.0
17.5°	585.3	542.4	499.5	470.1	440.8	420.9	401.1	388.6	376.2	370.4	364.7
20°	543.7	500.4	457.1	429.5	401.8	382.3	362.8	356.1	349.4	344.1	338.7
22.5°	502.4	460.9	419.3	392.7	366.2	352.0	337.9	332.5	327.2	323.1	319.0
25°	467.9	426.5	385.1	361.9	338.7	327.7	316.8	313.2	309.7	305.6	301.5
27.5°	433.0	393.6	354.3	335.7	317.1	308.2	299.3	294.9	290.4	287.1	283.7
30°	402.2	365.8	329.4	314.0	298.6	290.8	283.0	278.1	273.3	270.2	267.0
32.5°	372.5	340.2	307.9	294.7	281.5	273.9	266.3	261.6	257.0	253.3	249.6
35°	345.0	317.0	288.9	276.8	264.8	257.2	249.6	244.9	240.3	236.6	232.8
37.5°	320.9	295.4	270.0	258.6	247.3	240.6	234.0	229.1	224.3	220.4	216.5
40°	298.2	275.7	253.3	242.3	231.4	224.1	216.9	212.6	208.3	204.8	201.3
42.5°	278.1	257.5	236.9	226.2	215.4	208.5	201.6	196.6	191.6	189.6	187.5
45°	257.0	238.8	220.6	210.2	199.8	192.5	185.3	181.0	176.8	174.9	173.1
47.5°	238.4	221.5	204.6	194.4	184.2	177.7	171.2	167.9	164.5	161.9	159.3
50°	220.2	203.9	187.5	177.7	167.9	162.3	156.7	152.6	148.5	146.7	144.8
52.5°	202.8	187.9	173.1	163.0	153.0	147.6	142.2	138.7	135.2	131.3	127.4
55°	183.1	170.1	157.1	148.2	139.3	133.7	128.1	124.0	119.9	115.9	111.8
57.5°	166.7	153.9	141.1	133.1	125.1	119.8	114.4	109.9	105.5	102.1	98.8
60°	148.9	137.8	126.6	118.8	111.0	105.8	100.6	96.4	92.1	90.4	88.8
62.5°	132.2	121.8	111.4	104.5	97.7	92.7	87.6	84.9	82.1	81.0	79.8
65°	115.1	106.2	97.3	91.0	84.7	80.4	76.1	74.8	73.5	72.6	71.7
67.5°	99.2	91.5	83.9	78.4	72.8	69.8	66.8	65.4	63.9	62.8	61.6
70°	84.7	78.0	71.3	66.5	61.6	58.9	56.1	54.8	53.5	51.4	49.4
72.5°	69.1	63.9	58.7	55.0	51.2	48.8	46.4	43.8	41.2	39.4	37.5
75°	57.2	52.0	46.8	43.3	39.7	36.9	34.2	33.2	32.3	31.8	31.2
77.5°	43.8	39.4	34.9	32.1	29.3	28.0	26.7	26.2	25.6	25.4	25.3
80°	31.6	27.9	24.1	22.7	21.2	20.8	20.4	20.1	19.7	19.5	19.3
82.5°	19.7	17.8	16.0	15.6	15.2	15.0	14.9	14.7	14.5	14.3	14.1
85°	11.5	10.8	10.0	9.8	9.7	9.5	9.3	9.3	9.3	9.3	9.3
87.5°	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.6	4.5
90°	9.4	11.8	14.5	17.3	20.0	22.7	23.6	24.4	25.3	26.1	26.7
92.5°	16.7	17.0	18.9	20.8	22.7	24.6	26.1	27.6	29.0	30.5	31.4
95°	23.3	20.1	22.4	24.7	27.0	29.4	30.8	32.3	33.8	35.3	36.0
97.5°	81.6	73.3	62.5	51.8	41.0	30.3	32.0	33.7	35.4	37.0	38.0
100°	176.9	162.6	129.8	96.9	64.1	31.3	32.9	34.6	36.3	38.0	38.9
102.5°	233.5	216.6	180.0	143.3	106.7	70.1	63.1	56.2	49.3	42.3	39.0
105°	291.5	283.2	264.3	245.3	226.4	207.4	170.2	132.9	95.7	58.4	40.0
107.5°	353.3	355.8	359.0	362.2	365.3	368.5	336.1	303.6	271.2	238.8	208.8
110°	415.9	417.9	420.3	422.6	424.9	427.2	420.3	413.3	406.4	399.4	380.9



TEST NUMBER: P832077

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	475.7	477.6	479.9	482.2	484.6	486.9	488.8	490.7	492.6	494.4	495.2
115°	534.5	536.1	538.0	539.9	541.8	543.7	545.8	547.9	550.0	552.1	553.6
117.5°	594.1	595.4	596.4	597.5	598.5	599.6	601.3	603.0	604.6	606.3	607.3
120°	649.8	651.1	651.7	652.3	653.0	653.6	655.3	657.0	658.6	660.3	661.2
122.5°	703.0	704.2	705.0	705.9	706.7	707.6	708.6	709.7	710.7	711.8	712.4
125°	753.1	754.4	755.3	756.1	756.9	757.8	758.2	758.6	759.0	759.5	759.9
127.5°	802.4	803.8	804.8	805.9	806.9	808.0	808.6	809.2	809.9	810.5	810.6
130°	847.9	849.1	850.0	850.8	851.7	852.5	853.3	854.2	855.0	855.9	856.1
132.5°	891.4	892.6	893.2	893.9	894.5	895.1	896.0	896.8	897.7	898.5	898.6
135°	934.3	935.3	936.2	937.0	937.9	938.7	939.3	940.0	940.6	941.2	941.2
137.5°	973.8	974.9	975.3	975.7	976.2	976.6	977.6	978.7	979.7	980.8	981.1
140°	1010.1	1011.0	1011.6	1012.3	1012.9	1013.5	1014.4	1015.2	1016.1	1016.9	1017.1
142.5°	1045.1	1046.0	1046.7	1047.3	1047.9	1048.6	1049.2	1049.8	1050.5	1051.1	1051.1
145°	1078.1	1079.1	1079.5	1079.9	1080.4	1080.8	1081.2	1081.6	1082.0	1082.5	1082.7
147.5°	1107.7	1108.5	1108.9	1109.3	1109.7	1110.1	1110.6	1111.0	1111.4	1111.8	1111.5
150°	1134.5	1135.0	1135.4	1135.8	1136.2	1136.7	1137.1	1137.5	1137.9	1138.3	1138.2
152.5°	1158.3	1158.6	1158.8	1159.0	1159.2	1159.4	1160.2	1161.1	1161.9	1162.8	1162.7
155°	1179.5	1179.4	1179.6	1179.8	1180.0	1180.2	1181.3	1182.3	1183.4	1184.4	1184.3
157.5°	1200.1	1200.0	1199.8	1199.6	1199.4	1199.2	1200.4	1201.7	1203.0	1204.2	1204.0
160°	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3	1216.5	1217.8	1219.1	1220.3	1220.2
162.5°	1230.8	1230.3	1230.1	1229.9	1229.7	1229.5	1231.0	1232.4	1233.9	1235.4	1235.5
165°	1243.1	1242.6	1242.4	1242.2	1242.0	1241.8	1243.5	1245.2	1246.9	1248.5	1248.6
167.5°	1252.6	1252.2	1252.2	1252.2	1252.2	1252.2	1253.9	1255.6	1257.3	1259.0	1259.0
170°	1261.2	1260.8	1260.8	1260.8	1260.8	1260.8	1262.4	1264.1	1265.8	1267.5	1267.5
172.5°	1266.0	1265.6	1265.8	1266.0	1266.2	1266.4	1268.1	1269.8	1271.5	1273.2	1273.1
175°	1270.8	1270.3	1270.5	1270.8	1271.0	1271.2	1272.6	1274.1	1275.6	1277.1	1277.0
177.5°	1272.6	1272.2	1272.4	1272.6	1272.9	1273.1	1274.7	1276.4	1278.1	1279.8	1279.6
180°	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0	1275.0



TEST NUMBER: P832077

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	905.7	905.7	905.7	905.7
2.5°	804.7	802.9	802.1	801.4
5°	689.8	684.0	682.7	681.4
7.5°	592.1	589.7	581.7	573.7
10°	512.8	505.4	502.1	498.7
12.5°	446.6	439.7	438.6	437.5
15°	395.1	390.3	388.6	387.0
17.5°	361.3	358.0	355.9	353.9
20°	336.3	333.8	332.4	330.9
22.5°	317.1	315.3	314.2	313.1
25°	298.8	296.0	295.0	294.1
27.5°	281.3	278.9	278.0	277.0
30°	265.0	262.9	261.6	260.3
32.5°	247.1	244.7	244.0	243.2
35°	231.4	229.9	229.1	228.4
37.5°	214.6	212.8	211.7	210.6
40°	200.3	199.4	198.9	198.3
42.5°	185.9	184.2	184.0	183.8
45°	171.4	169.7	169.3	169.0
47.5°	157.8	156.3	156.2	156.0
50°	142.8	140.7	139.3	137.8
52.5°	125.5	123.7	122.4	121.1
55°	109.7	107.7	106.6	105.5
57.5°	97.9	96.9	96.4	95.8
60°	88.2	87.6	87.3	86.9
62.5°	79.3	78.7	78.7	78.7
65°	71.1	70.6	70.0	69.4
67.5°	60.5	59.4	59.2	59.0
70°	47.7	46.0	45.9	45.7
72.5°	37.3	37.1	36.8	36.4
75°	30.8	30.5	30.5	30.5
77.5°	24.9	24.5	24.5	24.5
80°	19.1	18.9	19.1	19.3
82.5°	14.1	14.1	13.9	13.7
85°	9.1	8.9	8.9	8.9
87.5°	4.5	4.5	4.5	4.5
90°	27.2	27.6	28.0	28.4
92.5°	31.6	31.8	32.0	32.2
95°	36.0	36.0	36.0	36.0
97.5°	38.2	38.4	38.6	38.8
100°	39.2	39.4	39.6	39.8
102.5°	39.5	39.9	40.3	40.7
105°	40.4	40.8	41.3	41.7
107.5°	181.2	153.7	126.1	98.5
110°	350.8	320.7	290.6	260.5



TEST NUMBER: P832077

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	494.8	494.3	493.9	493.5
115°	554.4	555.3	556.1	557.0
117.5°	607.5	607.7	607.9	608.1
120°	661.2	661.2	661.2	661.2
122.5°	712.6	712.8	713.0	713.3
125°	760.3	760.7	761.1	761.6
127.5°	810.2	809.8	809.3	808.9
130°	855.7	855.2	854.8	854.4
132.5°	898.0	897.3	896.7	896.1
135°	940.6	940.0	939.3	938.7
137.5°	980.7	980.3	979.8	979.4
140°	1016.7	1016.3	1015.8	1015.4
142.5°	1050.5	1049.8	1049.2	1048.6
145°	1082.7	1082.7	1082.7	1082.7
147.5°	1110.5	1109.4	1108.4	1107.3
150°	1137.6	1137.0	1136.4	1135.7
152.5°	1161.6	1160.6	1159.5	1158.5
155°	1183.1	1181.8	1180.6	1179.3
157.5°	1202.3	1200.7	1199.0	1197.3
160°	1218.8	1217.3	1215.8	1214.3
162.5°	1234.2	1233.0	1231.7	1230.4
165°	1247.2	1245.7	1244.2	1242.8
167.5°	1257.3	1255.6	1253.9	1252.2
170°	1265.8	1264.1	1262.4	1260.8
172.5°	1271.2	1269.3	1267.4	1265.5
175°	1275.3	1273.6	1271.9	1270.2
177.5°	1277.5	1275.4	1273.3	1271.2
180°	1275.0	1275.0	1275.0	1275.0

TEST NUMBER: P832077

CATALOG NUMBER: S123RDIP-S340D1195U930-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.45	6.09	6.61	7.23	8.84	10.11	10.75	11.27	11.90	13.50
	3H	6.65	7.23	7.82	8.38	10.00	11.60	12.17	12.76	13.32	14.94
	4H	7.03	7.57	8.20	8.73	10.35	12.08	12.62	13.25	13.77	15.40
	6H	7.30	7.80	8.48	8.96	10.59	12.38	12.88	13.56	14.04	15.67
	8H	7.38	7.86	8.57	9.03	10.66	12.45	12.93	13.64	14.10	15.73
	12H	7.43	7.88	8.62	9.04	10.69	12.48	12.93	13.67	14.09	15.74
4H	2H	6.15	6.69	7.33	7.85	9.47	10.08	10.63	11.27	11.78	13.41
	3H	7.50	7.96	8.69	9.13	10.77	11.72	12.18	12.91	13.36	14.99
	4H	7.95	8.37	9.14	9.53	11.19	12.32	12.74	13.51	13.91	15.56
	6H	8.31	8.66	9.50	9.85	11.50	12.75	13.11	13.95	14.30	15.94
	8H	8.43	8.76	9.62	9.94	11.60	12.88	13.22	14.07	14.39	16.06
	12H	8.50	8.80	9.71	9.99	11.66	12.94	13.24	14.14	14.43	16.09
8H	4H	8.25	8.58	9.44	9.76	11.42	12.28	12.61	13.47	13.79	15.45
	6H	8.71	8.98	9.92	10.20	11.86	12.77	13.04	13.98	14.27	15.92
	8H	8.90	9.14	10.12	10.34	12.02	12.96	13.19	14.17	14.39	16.07
	12H	9.04	9.25	10.26	10.44	12.15	13.06	13.27	14.28	14.47	16.18
12H	4H	8.25	8.56	9.46	9.75	11.41	12.22	12.52	13.43	13.71	15.38
	6H	8.77	9.00	9.98	10.20	11.88	12.74	12.98	13.96	14.18	15.86
	8H	8.98	9.19	10.20	10.38	12.09	12.93	13.14	14.15	14.33	16.04