

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332255-930

Luminaire Tested: **S123RDIP-S340D805U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332255-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3676.9 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332255-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332255-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16
5	65	54	46	41	58	49	42	37	39	34	30	30	26	24	21	19	17	14
6	60	48	41	35	54	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5042	5042	5042
5°	5061	4991	5020
10°	5032	4928	4912
15°	4979	4813	4763
20°	4904	4669	4560
25°	4828	4507	4363
30°	4727	4320	4084
35°	4623	4133	3829
40°	4526	3912	3513
45°	4401	3694	3227
50°	4262	3448	2907
55°	4121	3166	2609
60°	3991	2863	2282
65°	3823	2534	1954
70°	3610	2127	1577
75°	3302	1676	1485
80°	2944	1488	1364
85°	2482	1309	1223



TEST NUMBER: P332255-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.2
10°-20°	122.4	3.3
20°-30°	176.2	4.8
30°-40°	198.5	5.4
40°-50°	189.9	5.2
50°-60°	155.5	4.2
60°-70°	104.9	2.9
70°-80°	52.8	1.4
80°-90°	16.4	0.4
90°-100°	31.2	0.8
100°-110°	148.7	4.0
110°-120°	357.1	9.7
120°-130°	454.7	12.4
130°-140°	485.8	13.2
140°-150°	454.3	12.4
150°-160°	366.5	10.0
160°-170°	236.5	6.4
170°-180°	81.5	2.2
0°-30°	342.6	9.3
0°-40°	541.1	14.7
0°-60°	886.5	24.1
0°-90°	1060.6	28.8
90°-120°	536.9	14.6
90°-150°	1931.8	52.5
90°-180°	2616.0	71.1
0°-180°	3676.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	465	465	44
15°	447	442	432	430	427	126
25°	406	396	380	372	367	187
35°	352	338	314	299	291	220
45°	289	271	243	222	212	223
55°	220	200	169	147	139	197
65°	150	129	100	82	77	148
75°	79	61	40	37	36	85
85°	20	12	11	10	10	23
90°	1	7	15	18	19	3
95°	39	15	20	24	24	48
105°	190	193	140	33	28	201
115°	356	360	366	372	375	352
125°	502	507	510	511	512	448
135°	625	629	632	633	632	481
145°	722	726	727	728	729	451
155°	795	794	794	797	794	366
165°	838	836	836	840	836	237
175°	858	855	855	859	855	82
180°	858	858	858	858	858	



TEST NUMBER: P332255-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	469.9	469.6	469.4	469.1	468.9	468.3	467.5	466.7	465.9	465.0	465.8
5°	468.4	468.0	467.6	467.2	466.7	466.0	465.0	464.0	462.9	461.9	462.7
7.5°	464.1	463.6	463.2	462.7	462.3	461.4	460.1	458.8	457.4	456.1	456.5
10°	460.4	459.8	459.3	458.7	458.0	457.0	455.5	454.0	452.4	450.9	451.0
12.5°	455.3	454.6	454.0	453.3	452.7	451.3	449.5	447.7	445.8	443.9	443.8
15°	446.8	445.8	444.9	443.9	443.0	441.4	439.0	436.7	434.3	431.9	431.5
17.5°	436.0	435.0	433.9	432.8	431.7	429.7	426.6	423.6	420.7	417.7	416.8
20°	428.1	426.8	425.4	424.1	422.7	420.4	417.3	414.0	410.8	407.6	406.5
22.5°	419.3	417.8	416.2	414.7	413.1	410.7	407.2	403.8	400.4	397.0	395.6
25°	406.5	404.4	402.3	400.1	398.0	395.0	391.2	387.3	383.4	379.5	377.7
27.5°	390.9	388.6	386.2	383.9	381.6	378.3	374.0	369.6	365.3	360.9	358.5
30°	380.3	377.7	375.2	372.7	370.1	366.5	361.7	357.0	352.3	347.6	344.7
32.5°	369.7	366.7	363.9	361.0	358.2	354.2	349.2	344.2	339.2	334.2	331.1
35°	351.8	348.7	345.7	342.7	339.7	335.5	330.3	325.0	319.8	314.5	311.0
37.5°	333.7	330.3	326.9	323.6	320.2	315.7	310.1	304.5	299.0	293.3	289.3
40°	322.1	318.5	314.7	311.0	307.3	302.4	296.4	290.4	284.5	278.4	274.1
42.5°	309.1	305.3	301.7	297.9	294.2	289.3	283.1	276.9	270.7	264.5	259.7
45°	289.1	285.3	281.5	277.7	273.9	268.7	262.3	255.8	249.2	242.7	237.9
47.5°	269.1	265.0	260.7	256.6	252.4	247.1	240.6	234.1	227.6	221.1	215.9
50°	254.5	250.5	246.6	242.6	238.6	233.3	226.4	219.6	212.7	205.9	200.6
52.5°	241.5	237.2	232.8	228.5	224.2	218.7	211.9	205.1	198.4	191.6	186.2
55°	219.6	215.4	211.3	207.2	203.0	197.4	190.2	183.0	175.9	168.7	163.8
57.5°	199.3	194.9	190.4	185.8	181.3	175.5	168.3	161.0	153.8	146.7	142.0
60°	185.4	180.8	176.1	171.5	166.8	161.0	154.0	147.0	140.0	133.0	128.4
62.5°	171.4	166.7	162.1	157.5	152.9	147.0	140.0	133.0	126.0	119.0	114.7
65°	150.1	145.4	140.8	136.2	131.5	125.9	119.3	112.7	106.2	99.5	95.4
67.5°	128.7	124.0	119.3	114.6	109.9	104.4	98.1	91.8	85.4	79.2	76.1
70°	114.7	110.1	105.6	101.0	96.5	91.2	85.4	79.4	73.5	67.6	64.7
72.5°	100.8	96.3	91.8	87.2	82.8	77.9	72.5	67.1	61.7	56.3	54.0
75°	79.4	75.3	71.3	67.3	63.2	58.9	54.2	49.6	44.9	40.3	39.5
77.5°	59.9	56.3	52.6	48.9	45.3	42.0	39.0	36.0	33.0	30.0	29.6
80°	47.5	44.0	40.6	37.1	33.7	31.1	29.3	27.5	25.7	24.0	23.6
82.5°	35.6	32.6	29.7	26.7	23.6	21.8	21.0	20.1	19.3	18.4	18.2
85°	20.1	18.3	16.4	14.6	12.7	11.7	11.4	11.2	10.9	10.6	10.4
87.5°	7.4	6.9	6.5	6.0	5.5	5.5	5.9	6.3	6.6	7.0	7.1
90°	0.7	2.0	3.5	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9
92.5°	11.8	11.5	11.1	10.7	10.3	10.8	12.1	13.5	14.9	16.3	17.2
95°	38.9	33.1	27.2	21.4	15.7	13.5	15.1	16.6	18.2	19.7	20.8
97.5°	78.1	75.6	73.0	70.4	67.8	61.3	51.1	40.9	30.7	20.5	21.7
100°	107.7	110.6	113.4	116.2	119.0	109.4	87.3	65.2	43.1	21.0	22.2
102.5°	141.4	143.4	145.4	147.5	149.5	138.5	114.4	90.2	66.0	41.9	38.4
105°	190.0	191.5	193.1	194.6	196.2	190.6	177.8	165.1	152.3	139.6	114.5
107.5°	241.2	242.5	243.7	244.9	246.1	247.8	249.8	251.8	253.8	255.8	237.5
110°	275.3	276.5	277.6	278.8	279.9	281.2	282.8	284.4	285.9	287.5	282.8



TEST NUMBER: P332255-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.0	309.0	310.1	311.0	312.1	313.3	315.0	316.5	318.0	319.6	319.7
115°	356.3	357.2	358.0	358.9	359.7	360.8	362.1	363.3	364.6	365.9	367.3
117.5°	403.1	404.1	405.2	406.3	407.2	408.1	408.8	409.4	410.1	410.7	411.9
120°	432.2	433.4	434.7	435.9	437.2	438.1	438.5	439.0	439.4	439.8	440.9
122.5°	461.7	462.8	463.8	464.9	465.9	466.7	467.2	467.8	468.3	468.9	469.7
125°	502.3	503.4	504.5	505.6	506.8	507.7	508.3	508.7	509.3	509.9	510.2
127.5°	541.5	542.7	543.8	544.9	546.1	547.0	547.6	548.4	549.0	549.7	550.2
130°	566.0	567.1	568.3	569.4	570.5	571.4	571.9	572.5	573.1	573.6	574.2
132.5°	589.5	590.6	591.7	592.9	594.0	594.8	595.3	595.7	596.1	596.6	597.2
135°	625.3	626.1	627.0	627.9	628.7	629.4	630.0	630.6	631.1	631.7	632.1
137.5°	655.9	657.0	658.0	659.1	660.1	660.9	661.2	661.5	661.8	662.1	662.8
140°	676.3	677.1	678.0	678.8	679.7	680.3	680.8	681.2	681.6	682.0	682.6
142.5°	695.1	696.0	696.8	697.7	698.5	699.2	699.6	700.0	700.4	700.9	701.3
145°	721.5	722.5	723.5	724.5	725.5	726.1	726.4	726.7	727.0	727.2	727.6
147.5°	746.4	747.1	747.7	748.4	749.0	749.5	749.7	750.0	750.3	750.6	750.9
150°	761.7	762.1	762.5	763.0	763.4	763.8	764.0	764.3	764.6	764.9	765.2
152.5°	775.4	775.7	775.8	776.1	776.2	776.4	776.6	776.7	777.0	777.1	777.6
155°	794.8	794.6	794.3	794.0	793.7	793.6	793.8	793.9	794.0	794.2	794.9
157.5°	809.8	809.8	809.8	809.8	809.8	809.7	809.5	809.4	809.3	809.1	810.0
160°	819.0	818.9	818.8	818.6	818.5	818.3	818.2	818.1	817.9	817.7	818.6
162.5°	827.7	827.4	827.0	826.6	826.2	826.0	825.8	825.7	825.6	825.4	826.4
165°	838.2	837.7	837.3	836.9	836.5	836.2	836.1	835.9	835.8	835.6	836.7
167.5°	846.4	845.8	845.2	844.7	844.1	843.8	843.8	843.8	843.8	843.8	844.9
170°	850.9	850.4	849.8	849.2	848.6	848.4	848.4	848.4	848.4	848.4	849.5
172.5°	853.9	853.3	852.6	851.9	851.3	851.0	851.1	851.2	851.3	851.4	852.6
175°	857.9	857.2	856.6	855.8	855.1	854.8	854.9	855.1	855.2	855.4	856.4
177.5°	858.9	858.4	857.9	857.3	856.7	856.5	856.6	856.7	856.8	856.9	857.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P332255-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	466.5	467.2	468.1	468.3	468.2	468.1	467.9	467.8
5°	463.5	464.2	465.0	465.3	465.1	465.0	464.8	464.6
7.5°	457.0	457.4	457.8	457.9	457.5	457.3	457.0	456.7
10°	451.1	451.2	451.3	451.1	450.7	450.3	449.8	449.4
12.5°	443.8	443.8	443.8	443.4	443.0	442.5	442.0	441.5
15°	431.0	430.6	430.2	429.7	429.2	428.5	428.0	427.4
17.5°	415.9	415.0	414.1	413.2	412.3	411.4	410.6	409.7
20°	405.4	404.3	403.2	402.2	401.1	400.1	399.2	398.1
22.5°	394.3	392.9	391.5	390.4	389.4	388.5	387.5	386.6
25°	375.9	374.2	372.4	371.0	370.1	369.2	368.3	367.4
27.5°	356.0	353.6	351.1	349.2	347.7	346.3	345.0	343.5
30°	341.9	339.0	336.1	334.0	332.6	331.3	330.0	328.6
32.5°	327.9	324.8	321.6	319.4	318.0	316.6	315.1	313.7
35°	307.3	303.6	300.0	297.4	296.0	294.4	292.9	291.4
37.5°	285.1	281.0	276.9	273.9	272.0	270.1	268.2	266.4
40°	269.7	265.3	260.9	257.7	255.8	253.9	251.9	250.0
42.5°	254.9	250.1	245.3	242.1	240.3	238.6	236.8	235.1
45°	233.1	228.3	223.5	220.0	218.1	216.1	214.0	212.0
47.5°	210.6	205.4	200.2	196.7	194.9	193.1	191.2	189.4
50°	195.4	190.2	185.0	181.4	179.4	177.5	175.5	173.6
52.5°	180.8	175.3	169.9	166.3	164.5	162.8	161.1	159.3
55°	158.9	154.0	149.1	145.8	144.1	142.4	140.7	139.0
57.5°	137.4	132.7	128.2	125.1	123.7	122.2	120.8	119.4
60°	123.8	119.3	114.7	111.7	110.3	108.8	107.5	106.0
62.5°	110.4	106.2	101.8	98.9	97.4	96.0	94.4	92.9
65°	91.2	87.2	83.0	80.5	79.5	78.6	77.7	76.7
67.5°	73.0	69.9	66.8	64.7	63.8	62.8	61.8	60.8
70°	61.7	58.8	55.8	53.9	52.9	52.0	51.0	50.1
72.5°	51.5	49.2	46.7	45.3	44.9	44.5	44.2	43.8
75°	38.6	37.7	36.9	36.4	36.2	36.0	35.9	35.7
77.5°	29.1	28.6	28.2	27.9	27.7	27.6	27.4	27.2
80°	23.4	23.2	22.9	22.7	22.5	22.3	22.2	22.0
82.5°	17.9	17.7	17.4	17.3	17.3	17.2	17.2	17.2
85°	10.3	10.1	9.9	9.9	9.9	9.9	9.9	9.9
87.5°	7.1	7.2	7.2	7.2	7.2	7.2	7.2	7.2
90°	16.5	17.0	17.5	18.0	18.3	18.6	18.8	19.2
92.5°	18.1	19.0	20.0	20.5	20.6	20.8	21.0	21.2
95°	21.8	22.7	23.7	24.2	24.2	24.2	24.2	24.2
97.5°	22.8	23.9	25.0	25.7	25.8	26.0	26.1	26.3
100°	23.3	24.5	25.6	26.2	26.3	26.5	26.7	26.7
102.5°	34.9	31.4	27.9	26.3	26.5	26.7	27.0	27.3
105°	89.4	64.4	39.3	26.9	27.2	27.5	27.8	28.0
107.5°	219.1	200.7	182.3	163.6	144.8	125.9	107.0	88.1
110°	278.1	273.5	268.8	256.3	236.0	215.8	195.5	175.3



TEST NUMBER: P332255-930

CATALOG NUMBER: S123RDIP-S340D805U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	319.8	319.8	319.9	317.8	313.6	309.2	305.0	300.8
115°	368.7	370.1	371.5	372.5	373.1	373.7	374.2	374.8
117.5°	413.0	414.2	415.2	415.9	416.0	416.1	416.2	416.4
120°	442.1	443.2	444.3	444.9	444.9	444.9	444.9	444.9
122.5°	470.4	471.2	472.1	472.5	472.6	472.7	472.9	473.0
125°	510.5	510.8	511.0	511.4	511.6	511.9	512.2	512.5
127.5°	550.6	551.1	551.5	551.5	551.3	551.1	550.7	550.5
130°	574.8	575.4	575.9	576.1	575.8	575.5	575.2	574.9
132.5°	597.7	598.3	598.8	598.9	598.6	598.2	597.8	597.4
135°	632.5	632.9	633.3	633.3	632.9	632.5	632.1	631.7
137.5°	663.5	664.1	664.9	665.0	664.8	664.5	664.2	663.9
140°	683.1	683.7	684.3	684.4	684.1	683.9	683.5	683.3
142.5°	701.8	702.2	702.7	702.7	702.3	701.9	701.6	701.2
145°	727.8	728.1	728.4	728.6	728.6	728.6	728.6	728.6
147.5°	751.1	751.5	751.7	751.5	750.9	750.2	749.6	748.9
150°	765.4	765.7	766.0	766.0	765.5	765.1	764.7	764.3
152.5°	778.1	778.6	779.2	779.1	778.4	777.8	777.1	776.5
155°	795.7	796.3	797.0	797.0	796.1	795.2	794.4	793.5
157.5°	810.8	811.6	812.5	812.4	811.3	810.2	809.1	808.0
160°	819.5	820.4	821.2	821.1	820.1	819.1	818.2	817.2
162.5°	827.4	828.3	829.2	829.3	828.4	827.5	826.7	825.8
165°	837.9	839.0	840.2	840.2	839.3	838.2	837.2	836.3
167.5°	846.0	847.2	848.3	848.3	847.2	846.0	844.9	843.8
170°	850.6	851.7	852.9	852.9	851.7	850.6	849.5	848.4
172.5°	853.7	854.8	856.0	855.9	854.7	853.5	852.2	850.9
175°	857.4	858.3	859.3	859.2	858.2	857.0	855.9	854.8
177.5°	858.8	859.7	860.5	860.5	859.3	858.2	857.0	855.9
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9

(END OF REPORT)