

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332380-935

Luminaire Tested: **S123RDIP-S1165D1025U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332380-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7133.5 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	100	95	92	88	92	89	86	83	77	74	72	65	64	62	55	54	53	48
2	91	84	78	73	85	78	73	69	68	64	61	58	55	53	49	47	45	41
3	84	75	67	62	78	70	63	58	60	56	52	52	48	46	44	42	39	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	34	31
5	71	59	52	46	66	56	49	44	49	43	39	42	38	35	36	33	30	27
6	65	54	46	40	61	50	43	38	44	39	34	38	34	31	33	30	27	24
7	61	49	41	35	56	46	39	34	40	35	31	35	31	27	30	27	24	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	24	22	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	22	20	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17016	17016	17016	17016
5°	20283	17088	15048	17088
10°	25326	16990	13595	16990
15°	29727	16817	12397	16817
20°	33176	16557	11379	16557
25°	32647	16284	10753	16284
30°	23467	16032	10110	16032
35°	15669	15704	9692	15704
40°	11545	15309	9261	15309
45°	9683	14618	8840	14618
50°	8544	13711	8251	13711
55°	7492	12675	7443	12675
60°	6674	11683	6818	11683
65°	5861	10618	6342	10618
70°	4601	9668	5794	9668
75°	4055	8442	5294	8442
80°	3521	7172	5201	7172
85°	2841	5768	5521	5768



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	2.2
10°-20°	485.7	6.8
20°-30°	763.0	10.7
30°-40°	796.1	11.2
40°-50°	681.2	9.6
50°-60°	519.2	7.3
60°-70°	332.8	4.7
70°-80°	160.1	2.2
80°-90°	45.7	0.6
90°-100°	236.3	3.3
100°-110°	669.0	9.4
110°-120°	658.1	9.2
120°-130°	525.0	7.4
130°-140°	413.9	5.8
140°-150°	308.9	4.3
150°-160°	215.3	3.0
160°-170°	126.5	1.8
170°-180°	41.2	0.6
0°-30°	1404.1	19.7
0°-40°	2200.2	30.8
0°-60°	3400.7	47.7
0°-90°	3939.3	55.2
90°-120°	1563.5	21.9
90°-150°	2811.2	39.4
90°-180°	3194.0	44.8
0°-180°	7133.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1581	1581	1581	1581	1581	
5°	1877	1582	1393	1582	1877	194
15°	2668	1509	1112	1509	2668	756
25°	2749	1371	905	1371	2749	1181
35°	1192	1195	738	1195	1192	782
45°	636	960	581	960	636	500
55°	399	675	397	675	399	361
65°	230	417	249	417	230	226
75°	98	203	127	203	98	105
85°	23	47	45	47	23	27
90°	25	2	25	2	25	14
95°	100	29	100	29	100	180
105°	1093	100	1093	100	1093	1078
115°	1330	176	1330	176	1330	1292
125°	1048	245	1048	245	1048	950
135°	850	287	850	287	850	659
145°	664	327	664	327	664	423
155°	551	372	551	372	551	257
165°	480	406	480	406	480	137
175°	432	424	432	424	432	42
180°	425	425	425	425	425	



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1683.7	1685.8	1678.8	1677.7	1669.6	1667.4	1667.4	1656.0	1649.0	1639.9	1634.4
5°	1877.2	1888.1	1882.7	1870.4	1850.1	1845.4	1832.6	1812.2	1789.2	1760.8	1747.3
7.5°	2118.9	2133.7	2128.0	2109.2	2087.9	2070.8	2034.5	2000.8	1953.5	1912.1	1876.6
10°	2317.1	2301.5	2289.3	2271.1	2251.4	2219.7	2181.8	2129.6	2069.4	2022.1	1969.3
12.5°	2465.4	2462.9	2447.4	2428.6	2400.9	2370.7	2324.1	2260.6	2190.6	2122.2	2061.8
15°	2667.6	2671.7	2661.5	2641.9	2602.6	2549.2	2478.8	2452.5	2352.3	2277.9	2203.4
17.5°	2807.5	2806.8	2805.4	2778.2	2738.2	2700.1	2634.8	2565.4	2474.8	2369.9	2269.6
20°	2896.3	2889.6	2891.0	2860.5	2830.7	2786.7	2723.1	2622.3	2547.9	2426.7	2323.2
22.5°	2894.2	2892.9	2898.0	2887.5	2865.9	2832.2	2782.1	2697.0	2602.0	2479.8	2363.3
25°	2748.8	2743.4	2775.3	2784.0	2818.6	2824.6	2809.7	2763.0	2673.1	2547.2	2403.1
27.5°	2300.6	2297.6	2356.6	2430.5	2524.2	2596.9	2667.4	2701.3	2673.1	2582.9	2438.5
30°	1888.1	1951.6	1981.4	2088.4	2207.4	2349.6	2474.1	2592.5	2621.6	2582.4	2463.9
32.5°	1567.5	1623.1	1648.0	1739.7	1850.7	2017.2	2203.9	2371.6	2490.1	2520.1	2448.8
35°	1192.4	1193.1	1249.9	1290.5	1393.4	1564.6	1745.9	1970.6	2193.9	2363.1	2380.7
37.5°	951.5	954.8	989.2	1029.7	1106.8	1197.4	1357.1	1543.9	1801.8	2061.6	2213.8
40°	821.6	827.6	853.3	893.3	948.7	1017.1	1141.6	1317.6	1532.8	1821.7	2057.9
42.5°	738.1	748.0	761.3	792.0	826.4	890.4	991.1	1127.0	1322.8	1595.9	1868.5
45°	636.1	641.5	651.7	665.9	697.0	741.7	809.3	900.7	1063.2	1283.1	1555.7
47.5°	561.1	558.3	568.9	580.5	601.2	631.6	677.0	751.6	867.5	1043.9	1275.2
50°	510.2	509.5	517.0	525.8	545.4	567.7	605.0	661.2	753.2	899.4	1111.2
52.5°	462.6	465.2	470.5	481.4	495.6	513.7	547.1	587.5	666.6	792.7	969.3
55°	399.2	401.3	408.7	414.8	425.0	443.2	464.3	498.1	552.2	640.2	785.7
57.5°	345.7	344.7	351.9	353.4	364.9	379.8	396.0	422.2	461.5	526.9	624.9
60°	310.0	307.9	314.0	318.7	324.9	337.0	350.5	376.3	407.4	455.5	539.3
62.5°	277.4	276.5	280.9	285.7	290.8	301.8	313.1	332.9	357.6	398.0	464.6
65°	230.1	232.1	234.1	236.2	238.8	245.6	256.5	270.0	287.0	315.4	363.4
67.5°	180.8	182.9	183.6	187.7	193.6	197.8	204.4	216.5	228.2	252.2	279.5
70°	146.2	145.5	146.2	148.2	155.7	163.1	171.9	180.7	188.1	205.0	228.1
72.5°	125.6	124.4	126.1	126.6	130.2	132.2	137.8	146.0	155.7	167.1	183.7
75°	97.5	97.5	97.5	97.5	100.1	101.5	103.6	105.6	108.9	114.3	126.6
77.5°	72.0	72.2	73.1	73.8	74.3	75.1	76.4	78.4	79.6	82.4	87.7
80°	56.8	57.5	56.8	57.5	57.5	58.9	59.6	61.6	62.3	65.6	67.7
82.5°	42.8	42.4	42.8	43.5	43.5	44.8	44.9	46.4	46.6	48.3	50.4
85°	23.0	21.7	23.0	22.3	23.7	22.3	23.0	24.4	24.4	25.1	27.7
87.5°	10.4	11.6	10.4	10.8	10.9	11.1	10.9	10.8	11.7	11.4	11.4
90°	24.9	25.7	24.9	24.0	24.9	23.2	22.4	21.5	20.7	21.5	18.9
92.5°	41.4	43.0	42.1	44.7	46.2	50.7	57.4	72.3	99.7	132.2	145.4
95°	99.7	103.1	109.2	116.9	133.2	164.2	209.7	309.4	413.4	509.6	453.7
97.5°	271.4	278.8	302.0	340.7	404.1	506.9	617.8	771.3	845.0	789.8	578.2
100°	538.9	538.0	571.5	634.3	721.1	843.1	943.7	1013.3	983.2	813.9	550.0
102.5°	790.5	810.3	838.3	887.9	955.5	1032.9	1091.5	1093.7	990.1	769.2	508.8
105°	1093.2	1097.5	1125.0	1157.6	1197.2	1219.5	1203.2	1117.2	937.6	691.0	458.1
107.5°	1267.5	1275.4	1284.7	1295.7	1295.0	1264.4	1189.1	1049.6	845.8	621.9	425.8
110°	1339.0	1340.7	1342.5	1335.6	1311.5	1251.3	1143.1	984.9	788.1	582.7	413.4



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1353.4	1353.1	1346.5	1325.3	1281.3	1203.9	1082.5	920.9	737.9	556.6	406.5
115°	1329.6	1325.3	1308.0	1270.2	1205.7	1112.1	985.8	836.2	677.3	528.6	403.9
117.5°	1253.5	1247.8	1223.0	1179.7	1112.4	1017.4	904.0	774.9	640.6	512.0	405.4
120°	1190.3	1185.2	1164.5	1116.4	1048.5	961.7	858.6	742.5	621.4	504.5	408.2
122.5°	1131.2	1124.6	1102.0	1058.7	998.3	917.7	822.2	717.1	605.5	499.6	413.0
125°	1048.5	1042.5	1021.0	983.2	928.2	859.5	777.0	683.3	585.3	493.4	420.3
127.5°	980.4	974.9	955.5	923.2	874.2	811.7	737.2	653.7	567.4	490.3	428.5
130°	941.9	935.0	917.1	886.1	840.5	782.0	712.5	635.2	557.8	488.2	434.0
132.5°	904.1	899.3	883.3	852.4	809.6	753.9	689.1	617.9	548.8	487.5	438.2
135°	850.0	844.0	828.5	802.7	760.6	711.6	655.7	594.7	537.2	486.5	444.4
137.5°	792.7	788.8	775.8	749.6	714.2	671.8	623.6	573.6	527.0	484.6	448.4
140°	752.9	753.7	739.9	715.9	683.3	646.3	605.0	561.2	520.8	483.9	451.2
142.5°	715.7	716.6	704.2	682.9	655.0	622.9	587.2	549.5	515.3	482.5	453.2
145°	664.3	662.6	655.7	637.7	616.2	591.2	563.8	535.5	507.9	480.4	454.6
147.5°	622.1	621.4	614.8	602.6	586.3	568.6	546.4	523.9	500.7	477.2	454.6
150°	597.3	597.3	592.1	582.7	569.8	553.5	535.5	515.7	495.8	474.4	454.6
152.5°	576.7	576.7	573.6	564.8	554.7	541.1	525.1	508.1	490.4	471.0	452.5
155°	550.9	550.0	548.3	541.5	533.7	523.4	510.5	496.7	482.2	464.9	450.3
157.5°	527.4	527.5	526.2	521.0	514.3	506.2	496.2	484.7	472.9	459.6	447.5
160°	512.2	513.1	513.1	507.9	501.9	495.8	487.3	477.9	466.7	455.5	446.1
162.5°	498.4	499.3	499.3	494.9	490.9	485.6	477.7	469.6	460.5	451.3	443.3
165°	480.4	480.4	481.3	477.9	474.4	470.1	464.1	458.9	452.0	445.2	439.2
167.5°	463.2	463.2	464.1	461.7	460.1	457.0	453.6	449.6	444.0	439.0	435.1
170°	452.9	452.9	453.7	452.0	451.2	449.4	446.1	443.5	439.2	434.9	432.3
172.5°	443.3	444.0	445.6	443.8	443.7	442.6	439.9	438.0	434.4	431.4	430.2
175°	432.3	433.2	434.0	433.2	433.2	433.2	431.4	430.6	428.9	427.1	427.1
177.5°	425.9	425.9	427.3	426.6	427.3	427.3	426.6	425.9	425.2	424.6	425.2
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1632.3	1630.6	1623.1	1614.4	1603.0	1595.4	1589.5	1586.2	1576.5	1564.6	1556.4
5°	1733.1	1712.8	1691.1	1664.7	1640.4	1615.3	1599.7	1581.5	1559.2	1534.1	1516.6
7.5°	1841.1	1801.3	1758.4	1714.2	1670.4	1631.2	1596.6	1566.8	1531.3	1495.4	1470.2
10°	1923.9	1865.7	1805.5	1743.9	1687.7	1635.0	1594.3	1554.4	1511.8	1470.5	1439.4
12.5°	1999.2	1922.5	1853.1	1777.4	1705.6	1642.5	1584.1	1537.1	1485.8	1441.8	1406.4
15°	2094.5	2015.9	1932.0	1817.0	1721.6	1641.8	1570.6	1509.1	1446.8	1392.7	1358.1
17.5°	2183.5	2065.4	1952.6	1856.7	1732.7	1632.9	1546.2	1472.6	1404.2	1346.8	1304.3
20°	2220.3	2105.9	1983.5	1861.0	1739.1	1627.5	1526.6	1445.4	1374.4	1309.4	1270.2
22.5°	2242.5	2113.0	1984.0	1852.4	1722.9	1607.0	1507.2	1417.9	1340.8	1279.1	1230.7
25°	2268.4	2114.1	1971.9	1842.0	1710.0	1584.2	1465.8	1371.1	1287.8	1222.2	1170.7
27.5°	2285.4	2103.9	1936.0	1791.6	1657.7	1532.3	1423.8	1323.4	1239.0	1169.5	1114.3
30°	2288.6	2095.8	1908.3	1752.0	1616.0	1501.0	1386.0	1289.9	1200.5	1126.7	1075.3
32.5°	2293.0	2075.8	1871.0	1705.0	1565.6	1451.7	1347.5	1255.7	1164.2	1091.6	1039.1
35°	2275.1	2064.7	1814.3	1623.4	1484.0	1373.7	1279.7	1195.1	1105.1	1034.7	981.3
37.5°	2198.2	2020.7	1755.6	1531.7	1386.0	1283.8	1207.1	1133.3	1050.9	974.9	924.5
40°	2120.8	1977.4	1710.0	1475.9	1323.7	1218.7	1149.8	1089.5	1009.7	938.6	884.5
42.5°	2005.5	1918.4	1666.7	1417.5	1253.3	1152.2	1094.0	1037.5	967.4	895.3	844.4
45°	1794.0	1805.5	1578.1	1324.3	1155.8	1054.3	999.5	960.3	898.0	838.4	786.4
47.5°	1528.7	1636.3	1474.0	1225.1	1053.1	957.9	909.9	875.6	833.7	775.2	727.7
50°	1355.5	1509.1	1390.7	1158.6	988.7	894.0	846.5	818.8	782.3	736.2	691.0
52.5°	1195.8	1360.7	1290.0	1084.3	918.9	832.2	785.9	763.1	734.1	690.8	649.8
55°	975.2	1142.3	1126.1	972.4	814.1	736.2	701.1	675.4	655.7	623.3	590.8
57.5°	788.8	947.3	955.6	847.9	721.8	644.9	614.6	595.2	582.4	557.9	527.9
60°	671.3	816.8	845.2	764.1	655.7	588.1	558.3	542.7	532.6	513.0	489.9
62.5°	573.9	697.7	729.9	671.4	592.4	529.1	505.8	490.8	483.9	466.9	446.6
65°	439.2	542.1	573.2	540.7	499.4	448.7	429.7	416.9	410.8	401.3	386.4
67.5°	330.3	405.2	439.4	416.5	401.6	369.5	357.4	350.5	345.1	338.6	326.1
70°	265.3	320.7	355.9	349.8	337.7	320.7	311.9	307.2	301.8	296.4	285.6
72.5°	213.3	251.5	284.5	287.6	277.6	274.2	266.5	264.5	261.2	254.7	248.7
75°	141.5	167.8	190.8	199.7	203.7	207.1	203.7	203.0	202.3	196.9	193.6
77.5°	92.7	106.9	121.4	136.5	142.8	147.4	148.4	150.9	149.1	146.3	144.6
80°	71.0	74.5	84.6	97.5	107.6	111.7	114.3	115.7	115.0	114.3	111.7
82.5°	51.6	54.4	59.2	68.2	76.7	83.5	85.2	84.9	86.4	86.8	84.6
85°	27.7	28.4	29.8	31.2	35.9	43.3	45.4	46.7	48.0	48.0	44.0
87.5°	12.0	10.8	11.5	11.1	12.4	12.4	15.3	17.7	18.5	16.7	17.2
90°	16.4	13.8	11.2	9.5	7.7	5.2	3.4	1.7	3.4	5.2	7.7
92.5°	109.2	72.2	49.7	36.9	29.7	23.1	15.8	10.7	15.8	23.1	29.7
95°	312.8	184.8	111.8	78.2	55.9	41.2	31.8	29.2	31.8	41.2	55.9
97.5°	343.3	198.9	129.1	92.8	70.8	58.1	50.7	49.9	50.7	58.1	70.8
100°	324.0	196.8	136.6	103.1	82.5	70.5	64.5	63.6	64.5	70.5	82.5
102.5°	307.5	199.6	145.6	114.9	96.3	84.9	79.6	78.0	79.6	84.9	96.3
105°	295.7	207.2	160.7	134.1	117.8	107.5	102.3	99.7	102.3	107.5	117.8
107.5°	294.8	221.2	180.5	155.8	140.4	130.3	125.3	122.7	125.3	130.3	140.4
110°	298.3	232.9	194.2	170.1	155.6	146.1	141.8	139.2	141.8	146.1	155.6



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	305.1	244.6	208.7	185.3	170.7	161.3	157.0	154.4	157.0	161.3	170.7
115°	316.2	263.8	231.2	208.0	193.4	184.8	179.6	176.2	179.6	184.8	193.4
117.5°	331.1	284.3	252.0	230.5	214.1	206.3	202.0	198.0	202.0	206.3	214.1
120°	342.1	297.4	266.4	245.0	228.6	220.0	215.7	213.1	215.7	220.0	228.6
122.5°	352.4	311.1	280.9	258.0	242.4	233.1	228.8	226.2	228.8	233.1	242.4
125°	368.7	330.9	300.8	277.6	261.2	251.8	246.7	245.0	246.7	251.8	261.2
127.5°	382.1	348.1	319.0	295.8	277.8	268.1	261.7	259.2	261.7	268.1	277.8
130°	391.1	358.3	330.0	306.8	288.8	278.4	270.7	268.1	270.7	278.4	288.8
132.5°	399.3	367.3	339.7	317.1	299.1	286.7	278.3	275.0	278.3	286.7	299.1
135°	409.9	380.7	354.0	330.9	312.8	300.0	290.5	287.1	290.5	300.0	312.8
137.5°	417.8	390.0	364.4	342.9	325.0	311.3	302.0	298.4	302.0	311.3	325.0
140°	422.0	396.2	371.3	349.8	332.6	318.8	310.2	306.0	310.2	318.8	332.6
142.5°	426.1	401.1	376.8	356.6	339.5	327.1	317.8	314.2	317.8	327.1	339.5
145°	430.6	407.3	385.0	365.2	350.7	337.8	330.0	327.4	330.0	337.8	350.7
147.5°	433.3	412.5	392.1	375.2	361.1	350.0	342.4	340.9	342.4	350.0	361.1
150°	434.0	415.9	396.2	380.7	368.7	357.5	350.7	349.8	350.7	357.5	368.7
152.5°	435.4	418.0	401.1	386.2	375.6	365.8	358.9	358.7	358.9	365.8	375.6
155°	435.8	422.0	407.3	395.4	385.9	377.3	372.1	372.1	372.1	377.3	385.9
157.5°	436.6	424.2	412.5	403.2	395.2	387.6	383.5	382.8	383.5	387.6	395.2
160°	436.6	426.3	415.9	407.3	401.3	394.5	391.1	391.1	391.1	394.5	401.3
162.5°	435.9	427.0	418.0	410.8	405.4	400.0	397.3	397.3	397.3	400.0	405.4
165°	434.0	428.0	421.1	415.1	411.6	407.3	405.6	406.5	405.6	407.3	411.6
167.5°	432.7	427.8	422.8	419.0	416.6	413.4	412.5	413.5	412.5	413.4	416.6
170°	430.6	427.1	422.8	421.1	419.4	416.8	415.9	417.7	415.9	416.8	419.4
172.5°	429.9	427.1	423.5	422.5	421.5	419.6	419.4	420.4	419.4	419.6	421.5
175°	428.0	426.3	424.6	423.7	423.7	422.0	422.8	423.7	422.8	422.0	423.7
177.5°	426.6	425.2	424.6	424.6	424.6	423.9	424.6	425.2	424.6	423.9	424.6
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1553.8	1546.7	1541.9	1531.0	1524.0	1516.4	1508.8	1513.7	1513.1	1512.6	1512.6
5°	1501.7	1486.1	1471.9	1453.6	1442.1	1427.9	1417.0	1415.7	1418.4	1408.9	1403.5
7.5°	1449.9	1428.7	1408.5	1388.4	1367.0	1350.0	1339.2	1334.2	1327.3	1321.5	1315.4
10°	1413.7	1388.6	1369.0	1343.9	1320.9	1300.6	1287.8	1279.0	1274.3	1269.5	1260.8
12.5°	1376.3	1351.9	1326.8	1298.5	1276.6	1253.0	1243.4	1233.6	1224.4	1219.2	1207.1
15°	1321.6	1289.9	1263.4	1233.6	1209.3	1186.3	1172.8	1153.1	1150.4	1143.7	1131.4
17.5°	1266.8	1232.3	1195.9	1173.8	1146.3	1122.4	1101.8	1095.2	1075.8	1068.5	1058.0
20°	1223.5	1191.7	1164.0	1134.9	1094.9	1072.6	1056.4	1047.6	1032.0	1022.5	1015.7
22.5°	1186.1	1153.8	1121.7	1087.8	1054.9	1029.8	1018.0	1004.3	995.7	982.5	975.2
25°	1132.8	1097.6	1059.0	1022.5	998.8	979.9	961.0	948.7	936.6	930.5	917.0
27.5°	1070.8	1034.1	998.0	970.3	941.2	922.5	905.3	894.5	879.9	869.6	862.1
30°	1036.7	993.4	962.3	937.3	900.0	882.4	869.6	856.1	845.2	834.4	827.0
32.5°	997.2	957.7	928.2	897.2	868.7	849.4	832.8	820.9	811.7	801.3	793.9
35°	935.2	902.1	871.6	840.5	819.5	799.9	780.2	770.1	761.3	751.8	745.1
37.5°	879.2	848.2	819.2	789.7	763.7	747.8	731.9	724.2	712.3	705.9	699.0
40°	844.6	814.1	783.0	754.6	727.5	715.3	701.1	689.6	678.7	674.0	666.6
42.5°	806.7	776.2	749.9	719.4	697.2	680.6	667.5	655.0	646.8	639.9	635.7
45°	750.4	723.4	697.7	667.3	646.3	632.1	617.2	605.6	598.2	593.5	586.0
47.5°	695.9	668.9	642.7	616.2	595.9	579.7	564.8	556.8	546.9	541.1	536.1
50°	656.4	632.1	604.3	580.0	559.6	543.4	531.2	521.1	512.3	504.8	501.4
52.5°	620.2	594.2	570.2	547.4	526.1	507.6	496.5	485.9	479.2	470.7	466.8
55°	560.3	535.3	515.0	492.7	471.7	456.1	442.6	433.1	426.4	416.9	411.5
57.5°	504.1	481.7	457.4	438.1	416.5	403.3	392.1	379.3	371.0	363.5	358.3
60°	466.2	440.6	419.6	401.3	382.4	365.4	355.2	345.1	336.3	328.9	324.2
62.5°	426.7	404.2	384.4	364.5	347.2	332.4	320.6	312.1	304.4	299.6	294.9
65°	366.1	348.5	328.2	311.9	295.8	284.9	275.4	267.9	262.6	259.2	255.1
67.5°	310.3	293.3	275.5	259.6	248.7	240.5	234.3	227.9	225.2	220.8	218.2
70°	274.1	256.5	240.9	228.8	217.9	211.8	207.8	203.0	200.3	194.9	192.2
72.5°	234.5	221.8	210.6	200.6	191.9	186.4	181.2	175.4	171.1	165.1	162.4
75°	184.8	173.2	164.5	157.6	152.2	144.8	137.4	131.3	129.2	127.3	126.6
77.5°	136.8	129.5	123.1	117.4	110.7	105.3	103.7	102.3	101.9	100.8	100.8
80°	107.6	100.8	96.1	89.3	85.2	85.2	85.2	83.9	84.6	84.6	84.6
82.5°	80.0	73.8	71.2	68.8	67.9	68.4	68.4	68.8	68.4	69.4	68.9
85°	41.2	41.9	43.3	42.6	43.3	43.3	44.7	44.0	44.7	43.3	44.7
87.5°	17.0	19.0	20.1	21.1	22.2	22.1	22.6	22.7	23.4	23.6	23.9
90°	9.5	11.2	13.8	16.4	18.9	21.5	20.7	21.5	22.4	23.2	24.9
92.5°	36.9	49.7	72.2	109.2	145.4	132.2	99.7	72.3	57.4	50.7	46.2
95°	78.2	111.8	184.8	312.8	453.7	509.6	413.4	309.4	209.7	164.2	133.2
97.5°	92.8	129.1	198.9	343.3	578.2	789.8	845.0	771.3	617.8	506.9	404.1
100°	103.1	136.6	196.8	324.0	550.0	813.9	983.2	1013.3	943.7	843.1	721.1
102.5°	114.9	145.6	199.6	307.5	508.8	769.2	990.1	1093.7	1091.5	1032.9	955.5
105°	134.1	160.7	207.2	295.7	458.1	691.0	937.6	1117.2	1203.2	1219.5	1197.2
107.5°	155.8	180.5	221.2	294.8	425.8	621.9	845.8	1049.6	1189.1	1264.4	1295.0
110°	170.1	194.2	232.9	298.3	413.4	582.7	788.1	984.9	1143.1	1251.3	1311.5



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	185.3	208.7	244.6	305.1	406.5	556.6	737.9	920.9	1082.5	1203.9	1281.3
115°	208.0	231.2	263.8	316.2	403.9	528.6	677.3	836.2	985.8	1112.1	1205.7
117.5°	230.5	252.0	284.3	331.1	405.4	512.0	640.6	774.9	904.0	1017.4	1112.4
120°	245.0	266.4	297.4	342.1	408.2	504.5	621.4	742.5	858.6	961.7	1048.5
122.5°	258.0	280.9	311.1	352.4	413.0	499.6	605.5	717.1	822.2	917.7	998.3
125°	277.6	300.8	330.9	368.7	420.3	493.4	585.3	683.3	777.0	859.5	928.2
127.5°	295.8	319.0	348.1	382.1	428.5	490.3	567.4	653.7	737.2	811.7	874.2
130°	306.8	330.0	358.3	391.1	434.0	488.2	557.8	635.2	712.5	782.0	840.5
132.5°	317.1	339.7	367.3	399.3	438.2	487.5	548.8	617.9	689.1	753.9	809.6
135°	330.9	354.0	380.7	409.9	444.4	486.5	537.2	594.7	655.7	711.6	760.6
137.5°	342.9	364.4	390.0	417.8	448.4	484.6	527.0	573.6	623.6	671.8	714.2
140°	349.8	371.3	396.2	422.0	451.2	483.9	520.8	561.2	605.0	646.3	683.3
142.5°	356.6	376.8	401.1	426.1	453.2	482.5	515.3	549.5	587.2	622.9	655.0
145°	365.2	385.0	407.3	430.6	454.6	480.4	507.9	535.5	563.8	591.2	616.2
147.5°	375.2	392.1	412.5	433.3	454.6	477.2	500.7	523.9	546.4	568.6	586.3
150°	380.7	396.2	415.9	434.0	454.6	474.4	495.8	515.7	535.5	553.5	569.8
152.5°	386.2	401.1	418.0	435.4	452.5	471.0	490.4	508.1	525.1	541.1	554.7
155°	395.4	407.3	422.0	435.8	450.3	464.9	482.2	496.7	510.5	523.4	533.7
157.5°	403.2	412.5	424.2	436.6	447.5	459.6	472.9	484.7	496.2	506.2	514.3
160°	407.3	415.9	426.3	436.6	446.1	455.5	466.7	477.9	487.3	495.8	501.9
162.5°	410.8	418.0	427.0	435.9	443.3	451.3	460.5	469.6	477.7	485.6	490.9
165°	415.1	421.1	428.0	434.0	439.2	445.2	452.0	458.9	464.1	470.1	474.4
167.5°	419.0	422.8	427.8	432.7	435.1	439.0	444.0	449.6	453.6	457.0	460.1
170°	421.1	422.8	427.1	430.6	432.3	434.9	439.2	443.5	446.1	449.4	451.2
172.5°	422.5	423.5	427.1	429.9	430.2	431.4	434.4	438.0	439.9	442.6	443.7
175°	423.7	424.6	426.3	428.0	427.1	427.1	428.9	430.6	431.4	433.2	433.2
177.5°	424.6	424.6	425.2	426.6	425.2	424.6	425.2	425.9	426.6	427.3	427.3
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1506.1	1505.5	1506.1	1503.9	1506.1	1505.5	1506.1	1512.6	1512.6	1513.1	1513.7
5°	1401.4	1400.8	1398.8	1392.7	1398.8	1400.8	1401.4	1403.5	1408.9	1418.4	1415.7
7.5°	1310.1	1309.2	1303.2	1303.4	1303.2	1309.2	1310.1	1315.4	1321.5	1327.3	1334.2
10°	1256.0	1256.6	1248.5	1243.8	1248.5	1256.6	1256.0	1260.8	1269.5	1274.3	1279.0
12.5°	1203.5	1200.4	1193.9	1188.6	1193.9	1200.4	1203.5	1207.1	1219.2	1224.4	1233.6
15°	1134.2	1127.4	1111.2	1112.5	1111.2	1127.4	1134.2	1131.4	1143.7	1150.4	1153.1
17.5°	1052.6	1047.6	1047.3	1037.8	1047.3	1047.6	1052.6	1058.0	1068.5	1075.8	1095.2
20°	1005.0	1001.5	1002.9	993.4	1002.9	1001.5	1005.0	1015.7	1022.5	1032.0	1047.6
22.5°	967.6	964.1	958.5	955.5	958.5	964.1	967.6	975.2	982.5	995.7	1004.3
25°	912.9	907.5	902.1	905.4	902.1	907.5	912.9	917.0	930.5	936.6	948.7
27.5°	858.2	854.2	848.8	848.1	848.8	854.2	858.2	862.1	869.6	879.9	894.5
30°	823.5	819.5	816.8	813.4	816.8	819.5	823.5	827.0	834.4	845.2	856.1
32.5°	788.4	787.6	782.7	782.0	782.7	787.6	788.4	793.9	801.3	811.7	820.9
35°	742.4	738.3	736.9	737.6	736.9	738.3	742.4	745.1	751.8	761.3	770.1
37.5°	698.6	693.2	690.8	688.4	690.8	693.2	698.6	699.0	705.9	712.3	724.2
40°	667.3	661.9	660.5	659.1	660.5	661.9	667.3	666.6	674.0	678.7	689.6
42.5°	632.1	629.9	629.0	626.6	629.0	629.9	632.1	635.7	639.9	646.8	655.0
45°	584.0	583.3	579.3	580.7	579.3	583.3	584.0	586.0	593.5	598.2	605.6
47.5°	533.4	530.4	527.5	529.4	527.5	530.4	533.4	536.1	541.1	546.9	556.8
50°	498.8	497.4	491.3	492.7	491.3	497.4	498.8	501.4	504.8	512.3	521.1
52.5°	464.1	458.9	456.7	455.8	456.7	458.9	464.1	466.8	470.7	479.2	485.9
55°	406.7	400.6	397.9	396.6	397.9	400.6	406.7	411.5	416.9	426.4	433.1
57.5°	350.4	348.8	346.6	348.1	346.6	348.8	350.4	358.3	363.5	371.0	379.3
60°	317.4	317.4	317.4	316.7	317.4	317.4	317.4	324.2	328.9	336.3	345.1
62.5°	292.0	290.3	289.8	290.8	289.8	290.3	292.0	294.9	299.6	304.4	312.1
65°	253.1	252.4	249.7	249.0	249.7	252.4	253.1	255.1	259.2	262.6	267.9
67.5°	216.5	214.0	213.2	212.2	213.2	214.0	216.5	218.2	220.8	225.2	227.9
70°	188.8	187.4	183.4	184.1	183.4	187.4	188.8	192.2	194.9	200.3	203.0
72.5°	159.0	157.6	156.9	155.9	156.9	157.6	159.0	162.4	165.1	171.1	175.4
75°	125.9	125.2	124.5	127.3	124.5	125.2	125.9	126.6	127.3	129.2	131.3
77.5°	100.8	100.8	101.3	100.1	101.3	100.8	100.8	100.8	100.8	101.9	102.3
80°	84.6	84.6	83.9	83.9	83.9	84.6	84.6	84.6	84.6	84.6	83.9
82.5°	67.8	68.4	68.8	67.7	68.8	68.4	67.8	68.9	69.4	68.4	68.8
85°	44.7	44.0	45.4	44.7	45.4	44.0	44.7	44.7	43.3	44.7	44.0
87.5°	24.9	23.9	24.1	24.5	24.1	23.9	24.9	23.9	23.6	23.4	22.7
90°	24.0	24.9	25.7	24.9	25.7	24.9	24.0	24.9	23.2	22.4	21.5
92.5°	44.7	42.1	43.0	41.4	43.0	42.1	44.7	46.2	50.7	57.4	72.3
95°	116.9	109.2	103.1	99.7	103.1	109.2	116.9	133.2	164.2	209.7	309.4
97.5°	340.7	302.0	278.8	271.4	278.8	302.0	340.7	404.1	506.9	617.8	771.3
100°	634.3	571.5	538.0	538.9	538.0	571.5	634.3	721.1	843.1	943.7	1013.3
102.5°	887.9	838.3	810.3	790.5	810.3	838.3	887.9	955.5	1032.9	1091.5	1093.7
105°	1157.6	1125.0	1097.5	1093.2	1097.5	1125.0	1157.6	1197.2	1219.5	1203.2	1117.2
107.5°	1295.7	1284.7	1275.4	1267.5	1275.4	1284.7	1295.7	1295.0	1264.4	1189.1	1049.6
110°	1335.6	1342.5	1340.7	1339.0	1340.7	1342.5	1335.6	1311.5	1251.3	1143.1	984.9



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1325.3	1346.5	1353.1	1353.4	1353.1	1346.5	1325.3	1281.3	1203.9	1082.5	920.9
115°	1270.2	1308.0	1325.3	1329.6	1325.3	1308.0	1270.2	1205.7	1112.1	985.8	836.2
117.5°	1179.7	1223.0	1247.8	1253.5	1247.8	1223.0	1179.7	1112.4	1017.4	904.0	774.9
120°	1116.4	1164.5	1185.2	1190.3	1185.2	1164.5	1116.4	1048.5	961.7	858.6	742.5
122.5°	1058.7	1102.0	1124.6	1131.2	1124.6	1102.0	1058.7	998.3	917.7	822.2	717.1
125°	983.2	1021.0	1042.5	1048.5	1042.5	1021.0	983.2	928.2	859.5	777.0	683.3
127.5°	923.2	955.5	974.9	980.4	974.9	955.5	923.2	874.2	811.7	737.2	653.7
130°	886.1	917.1	935.0	941.9	935.0	917.1	886.1	840.5	782.0	712.5	635.2
132.5°	852.4	883.3	899.3	904.1	899.3	883.3	852.4	809.6	753.9	689.1	617.9
135°	802.7	828.5	844.0	850.0	844.0	828.5	802.7	760.6	711.6	655.7	594.7
137.5°	749.6	775.8	788.8	792.7	788.8	775.8	749.6	714.2	671.8	623.6	573.6
140°	715.9	739.9	753.7	752.9	753.7	739.9	715.9	683.3	646.3	605.0	561.2
142.5°	682.9	704.2	716.6	715.7	716.6	704.2	682.9	655.0	622.9	587.2	549.5
145°	637.7	655.7	662.6	664.3	662.6	655.7	637.7	616.2	591.2	563.8	535.5
147.5°	602.6	614.8	621.4	622.1	621.4	614.8	602.6	586.3	568.6	546.4	523.9
150°	582.7	592.1	597.3	597.3	597.3	592.1	582.7	569.8	553.5	535.5	515.7
152.5°	564.8	573.6	576.7	576.7	576.7	573.6	564.8	554.7	541.1	525.1	508.1
155°	541.5	548.3	550.0	550.9	550.0	548.3	541.5	533.7	523.4	510.5	496.7
157.5°	521.0	526.2	527.5	527.4	527.5	526.2	521.0	514.3	506.2	496.2	484.7
160°	507.9	513.1	513.1	512.2	513.1	513.1	507.9	501.9	495.8	487.3	477.9
162.5°	494.9	499.3	499.3	498.4	499.3	499.3	494.9	490.9	485.6	477.7	469.6
165°	477.9	481.3	480.4	480.4	480.4	481.3	477.9	474.4	470.1	464.1	458.9
167.5°	461.7	464.1	463.2	463.2	463.2	464.1	461.7	460.1	457.0	453.6	449.6
170°	452.0	453.7	452.9	452.9	452.9	453.7	452.0	451.2	449.4	446.1	443.5
172.5°	443.8	445.6	444.0	443.3	444.0	445.6	443.8	443.7	442.6	439.9	438.0
175°	433.2	434.0	433.2	432.3	433.2	434.0	433.2	433.2	433.2	431.4	430.6
177.5°	426.6	427.3	425.9	425.9	425.9	427.3	426.6	427.3	427.3	426.6	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1508.8	1516.4	1524.0	1531.0	1541.9	1546.7	1553.8	1556.4	1564.6	1576.5	1586.2
5°	1417.0	1427.9	1442.1	1453.6	1471.9	1486.1	1501.7	1516.6	1534.1	1559.2	1581.5
7.5°	1339.2	1350.0	1367.0	1388.4	1408.5	1428.7	1449.9	1470.2	1495.4	1531.3	1566.8
10°	1287.8	1300.6	1320.9	1343.9	1369.0	1388.6	1413.7	1439.4	1470.5	1511.8	1554.4
12.5°	1243.4	1253.0	1276.6	1298.5	1326.8	1351.9	1376.3	1406.4	1441.8	1485.8	1537.1
15°	1172.8	1186.3	1209.3	1233.6	1263.4	1289.9	1321.6	1358.1	1392.7	1446.8	1509.1
17.5°	1101.8	1122.4	1146.3	1173.8	1195.9	1232.3	1266.8	1304.3	1346.8	1404.2	1472.6
20°	1056.4	1072.6	1094.9	1134.9	1164.0	1191.7	1223.5	1270.2	1309.4	1374.4	1445.4
22.5°	1018.0	1029.8	1054.9	1087.8	1121.7	1153.8	1186.1	1230.7	1279.1	1340.8	1417.9
25°	961.0	979.9	998.8	1022.5	1059.0	1097.6	1132.8	1170.7	1222.2	1287.8	1371.1
27.5°	905.3	922.5	941.2	970.3	998.0	1034.1	1070.8	1114.3	1169.5	1239.0	1323.4
30°	869.6	882.4	900.0	937.3	962.3	993.4	1036.7	1075.3	1126.7	1200.5	1289.9
32.5°	832.8	849.4	868.7	897.2	928.2	957.7	997.2	1039.1	1091.6	1164.2	1255.7
35°	780.2	799.9	819.5	840.5	871.6	902.1	935.2	981.3	1034.7	1105.1	1195.1
37.5°	731.9	747.8	763.7	789.7	819.2	848.2	879.2	924.5	974.9	1050.9	1133.3
40°	701.1	715.3	727.5	754.6	783.0	814.1	844.6	884.5	938.6	1009.7	1089.5
42.5°	667.5	680.6	697.2	719.4	749.9	776.2	806.7	844.4	895.3	967.4	1037.5
45°	617.2	632.1	646.3	667.3	697.7	723.4	750.4	786.4	838.4	898.0	960.3
47.5°	564.8	579.7	595.9	616.2	642.7	668.9	695.9	727.7	775.2	833.7	875.6
50°	531.2	543.4	559.6	580.0	604.3	632.1	656.4	691.0	736.2	782.3	818.8
52.5°	496.5	507.6	526.1	547.4	570.2	594.2	620.2	649.8	690.8	734.1	763.1
55°	442.6	456.1	471.7	492.7	515.0	535.3	560.3	590.8	623.3	655.7	675.4
57.5°	392.1	403.3	416.5	438.1	457.4	481.7	504.1	527.9	557.9	582.4	595.2
60°	355.2	365.4	382.4	401.3	419.6	440.6	466.2	489.9	513.0	532.6	542.7
62.5°	320.6	332.4	347.2	364.5	384.4	404.2	426.7	446.6	466.9	483.9	490.8
65°	275.4	284.9	295.8	311.9	328.2	348.5	366.1	386.4	401.3	410.8	416.9
67.5°	234.3	240.5	248.7	259.6	275.5	293.3	310.3	326.1	338.6	345.1	350.5
70°	207.8	211.8	217.9	228.8	240.9	256.5	274.1	285.6	296.4	301.8	307.2
72.5°	181.2	186.4	191.9	200.6	210.6	221.8	234.5	248.7	254.7	261.2	264.5
75°	137.4	144.8	152.2	157.6	164.5	173.2	184.8	193.6	196.9	202.3	203.0
77.5°	103.7	105.3	110.7	117.4	123.1	129.5	136.8	144.6	146.3	149.1	150.9
80°	85.2	85.2	85.2	89.3	96.1	100.8	107.6	111.7	114.3	115.0	115.7
82.5°	68.4	68.4	67.9	68.8	71.2	73.8	80.0	84.6	86.8	86.4	84.9
85°	44.7	43.3	43.3	42.6	43.3	41.9	41.2	44.0	48.0	48.0	46.7
87.5°	22.6	22.1	22.2	21.1	20.1	19.0	17.0	17.2	16.7	18.5	17.7
90°	20.7	21.5	18.9	16.4	13.8	11.2	9.5	7.7	5.2	3.4	1.7
92.5°	99.7	132.2	145.4	109.2	72.2	49.7	36.9	29.7	23.1	15.8	10.7
95°	413.4	509.6	453.7	312.8	184.8	111.8	78.2	55.9	41.2	31.8	29.2
97.5°	845.0	789.8	578.2	343.3	198.9	129.1	92.8	70.8	58.1	50.7	49.9
100°	983.2	813.9	550.0	324.0	196.8	136.6	103.1	82.5	70.5	64.5	63.6
102.5°	990.1	769.2	508.8	307.5	199.6	145.6	114.9	96.3	84.9	79.6	78.0
105°	937.6	691.0	458.1	295.7	207.2	160.7	134.1	117.8	107.5	102.3	99.7
107.5°	845.8	621.9	425.8	294.8	221.2	180.5	155.8	140.4	130.3	125.3	122.7
110°	788.1	582.7	413.4	298.3	232.9	194.2	170.1	155.6	146.1	141.8	139.2



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	737.9	556.6	406.5	305.1	244.6	208.7	185.3	170.7	161.3	157.0	154.4
115°	677.3	528.6	403.9	316.2	263.8	231.2	208.0	193.4	184.8	179.6	176.2
117.5°	640.6	512.0	405.4	331.1	284.3	252.0	230.5	214.1	206.3	202.0	198.0
120°	621.4	504.5	408.2	342.1	297.4	266.4	245.0	228.6	220.0	215.7	213.1
122.5°	605.5	499.6	413.0	352.4	311.1	280.9	258.0	242.4	233.1	228.8	226.2
125°	585.3	493.4	420.3	368.7	330.9	300.8	277.6	261.2	251.8	246.7	245.0
127.5°	567.4	490.3	428.5	382.1	348.1	319.0	295.8	277.8	268.1	261.7	259.2
130°	557.8	488.2	434.0	391.1	358.3	330.0	306.8	288.8	278.4	270.7	268.1
132.5°	548.8	487.5	438.2	399.3	367.3	339.7	317.1	299.1	286.7	278.3	275.0
135°	537.2	486.5	444.4	409.9	380.7	354.0	330.9	312.8	300.0	290.5	287.1
137.5°	527.0	484.6	448.4	417.8	390.0	364.4	342.9	325.0	311.3	302.0	298.4
140°	520.8	483.9	451.2	422.0	396.2	371.3	349.8	332.6	318.8	310.2	306.0
142.5°	515.3	482.5	453.2	426.1	401.1	376.8	356.6	339.5	327.1	317.8	314.2
145°	507.9	480.4	454.6	430.6	407.3	385.0	365.2	350.7	337.8	330.0	327.4
147.5°	500.7	477.2	454.6	433.3	412.5	392.1	375.2	361.1	350.0	342.4	340.9
150°	495.8	474.4	454.6	434.0	415.9	396.2	380.7	368.7	357.5	350.7	349.8
152.5°	490.4	471.0	452.5	435.4	418.0	401.1	386.2	375.6	365.8	358.9	358.7
155°	482.2	464.9	450.3	435.8	422.0	407.3	395.4	385.9	377.3	372.1	372.1
157.5°	472.9	459.6	447.5	436.6	424.2	412.5	403.2	395.2	387.6	383.5	382.8
160°	466.7	455.5	446.1	436.6	426.3	415.9	407.3	401.3	394.5	391.1	391.1
162.5°	460.5	451.3	443.3	435.9	427.0	418.0	410.8	405.4	400.0	397.3	397.3
165°	452.0	445.2	439.2	434.0	428.0	421.1	415.1	411.6	407.3	405.6	406.5
167.5°	444.0	439.0	435.1	432.7	427.8	422.8	419.0	416.6	413.4	412.5	413.5
170°	439.2	434.9	432.3	430.6	427.1	422.8	421.1	419.4	416.8	415.9	417.7
172.5°	434.4	431.4	430.2	429.9	427.1	423.5	422.5	421.5	419.6	419.4	420.4
175°	428.9	427.1	427.1	428.0	426.3	424.6	423.7	423.7	422.0	422.8	423.7
177.5°	425.2	424.6	425.2	426.6	425.2	424.6	424.6	424.6	423.9	424.6	425.2
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1589.5	1595.4	1603.0	1614.4	1623.1	1630.6	1632.3	1634.4	1639.9	1649.0	1656.0
5°	1599.7	1615.3	1640.4	1664.7	1691.1	1712.8	1733.1	1747.3	1760.8	1789.2	1812.2
7.5°	1596.6	1631.2	1670.4	1714.2	1758.4	1801.3	1841.1	1876.6	1912.1	1953.5	2000.8
10°	1594.3	1635.0	1687.7	1743.9	1805.5	1865.7	1923.9	1969.3	2022.1	2069.4	2129.6
12.5°	1584.1	1642.5	1705.6	1777.4	1853.1	1922.5	1999.2	2061.8	2122.2	2190.6	2260.6
15°	1570.6	1641.8	1721.6	1817.0	1932.0	2015.9	2094.5	2203.4	2277.9	2352.3	2452.5
17.5°	1546.2	1632.9	1732.7	1856.7	1952.6	2065.4	2183.5	2269.6	2369.9	2474.8	2565.4
20°	1526.6	1627.5	1739.1	1861.0	1983.5	2105.9	2220.3	2323.2	2426.7	2547.9	2622.3
22.5°	1507.2	1607.0	1722.9	1852.4	1984.0	2113.0	2242.5	2363.3	2479.8	2602.0	2697.0
25°	1465.8	1584.2	1710.0	1842.0	1971.9	2114.1	2268.4	2403.1	2547.2	2673.1	2763.0
27.5°	1423.8	1532.3	1657.7	1791.6	1936.0	2103.9	2285.4	2438.5	2582.9	2673.1	2701.3
30°	1386.0	1501.0	1616.0	1752.0	1908.3	2095.8	2288.6	2463.9	2582.4	2621.6	2592.5
32.5°	1347.5	1451.7	1565.6	1705.0	1871.0	2075.8	2293.0	2448.8	2520.1	2490.1	2371.6
35°	1279.7	1373.7	1484.0	1623.4	1814.3	2064.7	2275.1	2380.7	2363.1	2193.9	1970.6
37.5°	1207.1	1283.8	1386.0	1531.7	1755.6	2020.7	2198.2	2213.8	2061.6	1801.8	1543.9
40°	1149.8	1218.7	1323.7	1475.9	1710.0	1977.4	2120.8	2057.9	1821.7	1532.8	1317.6
42.5°	1094.0	1152.2	1253.3	1417.5	1666.7	1918.4	2005.5	1868.5	1595.9	1322.8	1127.0
45°	999.5	1054.3	1155.8	1324.3	1578.1	1805.5	1794.0	1555.7	1283.1	1063.2	900.7
47.5°	909.9	957.9	1053.1	1225.1	1474.0	1636.3	1528.7	1275.2	1043.9	867.5	751.6
50°	846.5	894.0	988.7	1158.6	1390.7	1509.1	1355.5	1111.2	899.4	753.2	661.2
52.5°	785.9	832.2	918.9	1084.3	1290.0	1360.7	1195.8	969.3	792.7	666.6	587.5
55°	701.1	736.2	814.1	972.4	1126.1	1142.3	975.2	785.7	640.2	552.2	498.1
57.5°	614.6	644.9	721.8	847.9	955.6	947.3	788.8	624.9	526.9	461.5	422.2
60°	558.3	588.1	655.7	764.1	845.2	816.8	671.3	539.3	455.5	407.4	376.3
62.5°	505.8	529.1	592.4	671.4	729.9	697.7	573.9	464.6	398.0	357.6	332.9
65°	429.7	448.7	499.4	540.7	573.2	542.1	439.2	363.4	315.4	287.0	270.0
67.5°	357.4	369.5	401.6	416.5	439.4	405.2	330.3	279.5	252.2	228.2	216.5
70°	311.9	320.7	337.7	349.8	355.9	320.7	265.3	228.1	205.0	188.1	180.7
72.5°	266.5	274.2	277.6	287.6	284.5	251.5	213.3	183.7	167.1	155.7	146.0
75°	203.7	207.1	203.7	199.7	190.8	167.8	141.5	126.6	114.3	108.9	105.6
77.5°	148.4	147.4	142.8	136.5	121.4	106.9	92.7	87.7	82.4	79.6	78.4
80°	114.3	111.7	107.6	97.5	84.6	74.5	71.0	67.7	65.6	62.3	61.6
82.5°	85.2	83.5	76.7	68.2	59.2	54.4	51.6	50.4	48.3	46.6	46.4
85°	45.4	43.3	35.9	31.2	29.8	28.4	27.7	27.7	25.1	24.4	24.4
87.5°	15.3	12.4	12.4	11.1	11.5	10.8	12.0	11.4	11.4	11.7	10.8
90°	3.4	5.2	7.7	9.5	11.2	13.8	16.4	18.9	21.5	20.7	21.5
92.5°	15.8	23.1	29.7	36.9	49.7	72.2	109.2	145.4	132.2	99.7	72.3
95°	31.8	41.2	55.9	78.2	111.8	184.8	312.8	453.7	509.6	413.4	309.4
97.5°	50.7	58.1	70.8	92.8	129.1	198.9	343.3	578.2	789.8	845.0	771.3
100°	64.5	70.5	82.5	103.1	136.6	196.8	324.0	550.0	813.9	983.2	1013.3
102.5°	79.6	84.9	96.3	114.9	145.6	199.6	307.5	508.8	769.2	990.1	1093.7
105°	102.3	107.5	117.8	134.1	160.7	207.2	295.7	458.1	691.0	937.6	1117.2
107.5°	125.3	130.3	140.4	155.8	180.5	221.2	294.8	425.8	621.9	845.8	1049.6
110°	141.8	146.1	155.6	170.1	194.2	232.9	298.3	413.4	582.7	788.1	984.9



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.0	161.3	170.7	185.3	208.7	244.6	305.1	406.5	556.6	737.9	920.9
115°	179.6	184.8	193.4	208.0	231.2	263.8	316.2	403.9	528.6	677.3	836.2
117.5°	202.0	206.3	214.1	230.5	252.0	284.3	331.1	405.4	512.0	640.6	774.9
120°	215.7	220.0	228.6	245.0	266.4	297.4	342.1	408.2	504.5	621.4	742.5
122.5°	228.8	233.1	242.4	258.0	280.9	311.1	352.4	413.0	499.6	605.5	717.1
125°	246.7	251.8	261.2	277.6	300.8	330.9	368.7	420.3	493.4	585.3	683.3
127.5°	261.7	268.1	277.8	295.8	319.0	348.1	382.1	428.5	490.3	567.4	653.7
130°	270.7	278.4	288.8	306.8	330.0	358.3	391.1	434.0	488.2	557.8	635.2
132.5°	278.3	286.7	299.1	317.1	339.7	367.3	399.3	438.2	487.5	548.8	617.9
135°	290.5	300.0	312.8	330.9	354.0	380.7	409.9	444.4	486.5	537.2	594.7
137.5°	302.0	311.3	325.0	342.9	364.4	390.0	417.8	448.4	484.6	527.0	573.6
140°	310.2	318.8	332.6	349.8	371.3	396.2	422.0	451.2	483.9	520.8	561.2
142.5°	317.8	327.1	339.5	356.6	376.8	401.1	426.1	453.2	482.5	515.3	549.5
145°	330.0	337.8	350.7	365.2	385.0	407.3	430.6	454.6	480.4	507.9	535.5
147.5°	342.4	350.0	361.1	375.2	392.1	412.5	433.3	454.6	477.2	500.7	523.9
150°	350.7	357.5	368.7	380.7	396.2	415.9	434.0	454.6	474.4	495.8	515.7
152.5°	358.9	365.8	375.6	386.2	401.1	418.0	435.4	452.5	471.0	490.4	508.1
155°	372.1	377.3	385.9	395.4	407.3	422.0	435.8	450.3	464.9	482.2	496.7
157.5°	383.5	387.6	395.2	403.2	412.5	424.2	436.6	447.5	459.6	472.9	484.7
160°	391.1	394.5	401.3	407.3	415.9	426.3	436.6	446.1	455.5	466.7	477.9
162.5°	397.3	400.0	405.4	410.8	418.0	427.0	435.9	443.3	451.3	460.5	469.6
165°	405.6	407.3	411.6	415.1	421.1	428.0	434.0	439.2	445.2	452.0	458.9
167.5°	412.5	413.4	416.6	419.0	422.8	427.8	432.7	435.1	439.0	444.0	449.6
170°	415.9	416.8	419.4	421.1	422.8	427.1	430.6	432.3	434.9	439.2	443.5
172.5°	419.4	419.6	421.5	422.5	423.5	427.1	429.9	430.2	431.4	434.4	438.0
175°	422.8	422.0	423.7	423.7	424.6	426.3	428.0	427.1	427.1	428.9	430.6
177.5°	424.6	423.9	424.6	424.6	424.6	425.2	426.6	425.2	424.6	425.2	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1667.4	1667.4	1669.6	1677.7	1678.8	1685.8	1683.7
5°	1832.6	1845.4	1850.1	1870.4	1882.7	1888.1	1877.2
7.5°	2034.5	2070.8	2087.9	2109.2	2128.0	2133.7	2118.9
10°	2181.8	2219.7	2251.4	2271.1	2289.3	2301.5	2317.1
12.5°	2324.1	2370.7	2400.9	2428.6	2447.4	2462.9	2465.4
15°	2478.8	2549.2	2602.6	2641.9	2661.5	2671.7	2667.6
17.5°	2634.8	2700.1	2738.2	2778.2	2805.4	2806.8	2807.5
20°	2723.1	2786.7	2830.7	2860.5	2891.0	2889.6	2896.3
22.5°	2782.1	2832.2	2865.9	2887.5	2898.0	2892.9	2894.2
25°	2809.7	2824.6	2818.6	2784.0	2775.3	2743.4	2748.8
27.5°	2667.4	2596.9	2524.2	2430.5	2356.6	2297.6	2300.6
30°	2474.1	2349.6	2207.4	2088.4	1981.4	1951.6	1888.1
32.5°	2203.9	2017.2	1850.7	1739.7	1648.0	1623.1	1567.5
35°	1745.9	1564.6	1393.4	1290.5	1249.9	1193.1	1192.4
37.5°	1357.1	1197.4	1106.8	1029.7	989.2	954.8	951.5
40°	1141.6	1017.1	948.7	893.3	853.3	827.6	821.6
42.5°	991.1	890.4	826.4	792.0	761.3	748.0	738.1
45°	809.3	741.7	697.0	665.9	651.7	641.5	636.1
47.5°	677.0	631.6	601.2	580.5	568.9	558.3	561.1
50°	605.0	567.7	545.4	525.8	517.0	509.5	510.2
52.5°	547.1	513.7	495.6	481.4	470.5	465.2	462.6
55°	464.3	443.2	425.0	414.8	408.7	401.3	399.2
57.5°	396.0	379.8	364.9	353.4	351.9	344.7	345.7
60°	350.5	337.0	324.9	318.7	314.0	307.9	310.0
62.5°	313.1	301.8	290.8	285.7	280.9	276.5	277.4
65°	256.5	245.6	238.8	236.2	234.1	232.1	230.1
67.5°	204.4	197.8	193.6	187.7	183.6	182.9	180.8
70°	171.9	163.1	155.7	148.2	146.2	145.5	146.2
72.5°	137.8	132.2	130.2	126.6	126.1	124.4	125.6
75°	103.6	101.5	100.1	97.5	97.5	97.5	97.5
77.5°	76.4	75.1	74.3	73.8	73.1	72.2	72.0
80°	59.6	58.9	57.5	57.5	56.8	57.5	56.8
82.5°	44.9	44.8	43.5	43.5	42.8	42.4	42.8
85°	23.0	22.3	23.7	22.3	23.0	21.7	23.0
87.5°	10.9	11.1	10.9	10.8	10.4	11.6	10.4
90°	22.4	23.2	24.9	24.0	24.9	25.7	24.9
92.5°	57.4	50.7	46.2	44.7	42.1	43.0	41.4
95°	209.7	164.2	133.2	116.9	109.2	103.1	99.7
97.5°	617.8	506.9	404.1	340.7	302.0	278.8	271.4
100°	943.7	843.1	721.1	634.3	571.5	538.0	538.9
102.5°	1091.5	1032.9	955.5	887.9	838.3	810.3	790.5
105°	1203.2	1219.5	1197.2	1157.6	1125.0	1097.5	1093.2
107.5°	1189.1	1264.4	1295.0	1295.7	1284.7	1275.4	1267.5
110°	1143.1	1251.3	1311.5	1335.6	1342.5	1340.7	1339.0



TEST NUMBER: P332380-935

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1082.5	1203.9	1281.3	1325.3	1346.5	1353.1	1353.4
115°	985.8	1112.1	1205.7	1270.2	1308.0	1325.3	1329.6
117.5°	904.0	1017.4	1112.4	1179.7	1223.0	1247.8	1253.5
120°	858.6	961.7	1048.5	1116.4	1164.5	1185.2	1190.3
122.5°	822.2	917.7	998.3	1058.7	1102.0	1124.6	1131.2
125°	777.0	859.5	928.2	983.2	1021.0	1042.5	1048.5
127.5°	737.2	811.7	874.2	923.2	955.5	974.9	980.4
130°	712.5	782.0	840.5	886.1	917.1	935.0	941.9
132.5°	689.1	753.9	809.6	852.4	883.3	899.3	904.1
135°	655.7	711.6	760.6	802.7	828.5	844.0	850.0
137.5°	623.6	671.8	714.2	749.6	775.8	788.8	792.7
140°	605.0	646.3	683.3	715.9	739.9	753.7	752.9
142.5°	587.2	622.9	655.0	682.9	704.2	716.6	715.7
145°	563.8	591.2	616.2	637.7	655.7	662.6	664.3
147.5°	546.4	568.6	586.3	602.6	614.8	621.4	622.1
150°	535.5	553.5	569.8	582.7	592.1	597.3	597.3
152.5°	525.1	541.1	554.7	564.8	573.6	576.7	576.7
155°	510.5	523.4	533.7	541.5	548.3	550.0	550.9
157.5°	496.2	506.2	514.3	521.0	526.2	527.5	527.4
160°	487.3	495.8	501.9	507.9	513.1	513.1	512.2
162.5°	477.7	485.6	490.9	494.9	499.3	499.3	498.4
165°	464.1	470.1	474.4	477.9	481.3	480.4	480.4
167.5°	453.6	457.0	460.1	461.7	464.1	463.2	463.2
170°	446.1	449.4	451.2	452.0	453.7	452.9	452.9
172.5°	439.9	442.6	443.7	443.8	445.6	444.0	443.3
175°	431.4	433.2	433.2	433.2	434.0	433.2	432.3
177.5°	426.6	427.3	427.3	426.6	427.3	425.9	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6

(END OF REPORT)