

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831920

Luminaire Tested: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831920  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7474.2 lumens  
Efficiency: N/A  
Efficacy: 109.8 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831920

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P831920

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57	57	57	57	
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55	50	50	50	50	
2	92	85	79	75	86	80	75	71	69	66	63	60	57	55	51	49	48	43	43	43	43	
3	85	76	69	63	79	71	65	60	62	58	54	54	51	48	46	44	42	38	38	38	38	
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37	34	34	34	34	
5	72	61	54	48	67	58	51	46	51	45	41	45	40	37	39	36	33	30	30	30	30	
6	67	55	48	42	62	52	45	40	46	41	37	41	37	33	36	32	30	27	27	27	27	
7	62	51	43	38	58	48	41	36	43	37	33	38	33	30	33	30	27	25	25	25	25	
8	58	46	39	34	54	44	37	33	39	34	30	35	30	27	31	27	25	22	22	22	22	
9	54	43	36	31	51	41	34	30	36	31	27	32	28	25	29	25	23	21	21	21	21	
10	51	40	33	28	48	38	31	27	34	29	25	30	26	23	27	23	21	19	19	19	19	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	34733	34733	34733	34733	34733
5°	41242	39927	34952	28254	26231
10°	37366	40555	34777	22638	19420
15°	25727	34771	34410	18503	15363
20°	17898	26771	33719	15601	13503
25°	13639	20403	32714	13867	12444
30°	11872	16312	31457	12875	11527
35°	10900	13761	29676	12039	10692
40°	9946	12288	27347	11219	9927
45°	8983	11237	24832	10443	9164
50°	8153	10369	21867	9682	8219
55°	7373	9522	19018	8938	7051
60°	6607	8658	16518	8118	6665
65°	6100	7682	14220	7294	6301
70°	4954	6641	12409	6600	5120
75°	4346	5282	10509	5473	4512
80°	3936	4469	8610	4593	4265
85°	3594	3927	6533	4162	3927

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 26201 cd/sqm



TEST NUMBER: P831920

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	294.1	3.9
10°-20°	680.6	9.1
20°-30°	780.9	10.4
30°-40°	769.7	10.3
40°-50°	678.8	9.1
50°-60°	522.2	7.0
60°-70°	343.3	4.6
70°-80°	166.7	2.2
80°-90°	44.4	0.6
90°-100°	230.4	3.1
100°-110°	674.5	9.0
110°-120°	658.7	8.8
120°-130°	524.6	7.0
130°-140°	413.9	5.5
140°-150°	308.7	4.1
150°-160°	215.3	2.9
160°-170°	126.5	1.7
170°-180°	41.1	0.6
0°-30°	1755.6	23.5
0°-40°	2525.3	33.8
0°-60°	3726.2	49.9
0°-90°	4280.6	57.3
90°-120°	1563.5	20.9
90°-150°	2810.7	37.6
90°-180°	3194.0	42.7
0°-180°	7474.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3227	3227	3227	3227	3227	
5°	3817	3695	3235	2615	2428	349
15°	2309	3120	3088	1660	1379	652
25°	1148	1718	2754	1168	1048	542
35°	830	1047	2258	916	814	517
45°	590	738	1631	686	602	458
55°	393	507	1013	476	376	352
65°	240	302	558	286	247	235
75°	104	127	253	132	108	112
85°	29	32	53	34	32	31
90°	25	22	2	22	25	15
95°	100	510	29	510	100	162
105°	1093	691	100	691	1093	1091
115°	1330	528	176	528	1330	1297
125°	1048	493	245	493	1048	949
135°	850	486	287	486	850	659
145°	664	480	327	480	664	422
155°	551	465	372	465	551	257
165°	480	445	406	445	480	137
175°	432	427	424	427	432	42
180°	425	425	425	425	425	



TEST NUMBER: P831920

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8
2.5°	3576.1	3564.9	3553.6	3550.3	3547.0	3536.4	3525.8	3502.0	3478.2	3453.7	3429.3
5°	3816.9	3818.2	3819.5	3816.2	3812.9	3799.0	3785.1	3756.0	3726.9	3695.2	3663.4
7.5°	3742.8	3764.0	3785.1	3789.1	3793.1	3803.7	3814.2	3807.6	3801.0	3789.1	3777.2
10°	3418.7	3417.3	3416.0	3439.8	3463.6	3534.4	3605.2	3641.6	3678.0	3710.4	3742.8
12.5°	2889.5	2891.4	2893.4	2971.5	3049.5	3116.4	3183.2	3275.8	3368.4	3468.3	3568.2
15°	2308.7	2341.1	2373.5	2442.9	2512.4	2613.0	2713.5	2837.9	2962.2	3120.3	3278.4
17.5°	1895.9	1909.8	1923.7	1990.5	2057.3	2152.5	2247.8	2388.7	2529.6	2733.3	2937.1
20°	1562.5	1575.0	1587.6	1635.9	1684.2	1775.5	1866.8	2001.1	2135.3	2337.1	2538.9
22.5°	1304.5	1329.0	1353.4	1385.9	1418.3	1484.4	1550.6	1687.5	1824.4	2008.3	2192.2
25°	1148.4	1159.6	1170.9	1198.6	1226.4	1289.9	1353.4	1444.1	1534.7	1717.9	1901.2
27.5°	1042.5	1045.8	1049.1	1069.7	1090.2	1131.2	1172.2	1256.2	1340.2	1491.0	1641.9
30°	955.2	961.2	967.1	983.0	998.9	1028.6	1058.4	1117.9	1177.5	1312.4	1447.4
32.5°	887.7	891.0	894.4	907.6	920.8	942.6	964.5	1011.4	1058.4	1161.6	1264.8
35°	829.5	830.2	830.9	840.8	850.7	871.9	893.0	932.1	971.1	1047.2	1123.2
37.5°	763.4	768.0	772.6	779.9	787.2	805.7	824.2	856.0	887.7	950.6	1013.4
40°	707.8	711.8	715.8	724.3	732.9	747.5	762.1	791.2	820.3	874.5	928.8
42.5°	652.2	654.9	657.5	666.1	674.7	692.6	710.5	733.6	756.8	801.7	846.7
45°	590.1	596.7	603.3	612.6	621.8	637.0	652.2	676.1	699.9	738.2	776.6
47.5°	538.5	541.8	545.1	553.0	561.0	579.5	598.0	619.2	640.3	676.1	711.8
50°	486.9	488.2	489.5	496.8	504.1	520.6	537.1	561.6	586.1	619.2	652.2
52.5°	437.9	441.2	444.5	451.8	459.1	470.3	481.6	506.7	531.9	564.3	596.7
55°	392.9	394.9	396.9	402.2	407.5	420.7	433.9	455.8	477.6	507.4	537.1
57.5°	350.6	353.2	355.9	359.9	363.8	375.7	387.6	406.8	426.0	455.8	485.5
60°	306.9	310.2	313.6	318.2	322.8	332.1	341.3	358.5	375.7	402.2	428.7
62.5°	275.2	275.8	276.5	280.5	284.4	291.1	297.7	311.6	325.5	351.9	378.4
65°	239.5	241.4	243.4	245.4	247.4	252.7	258.0	269.9	281.8	301.6	321.5
67.5°	202.4	204.4	206.4	209.7	213.0	217.6	222.3	230.2	238.1	256.7	275.2
70°	157.4	157.4	157.4	162.7	168.0	176.0	183.9	189.9	195.8	211.0	226.2
72.5°	128.3	129.0	129.7	130.3	131.0	135.6	140.2	150.2	160.1	169.3	178.6
75°	104.5	105.2	105.8	106.5	107.2	108.5	109.8	113.1	116.4	127.0	137.6
77.5°	83.3	84.0	84.7	85.3	86.0	87.3	88.6	90.0	91.3	95.3	99.2
80°	63.5	64.2	64.8	65.5	66.2	66.8	67.5	68.8	70.1	72.1	74.1
82.5°	46.3	46.3	46.3	46.3	46.3	47.6	49.0	49.0	49.0	50.3	51.6
85°	29.1	29.1	29.1	29.8	30.4	30.4	30.4	31.1	31.8	31.8	31.8
87.5°	13.2	12.6	11.9	12.6	13.2	13.2	13.2	13.9	14.6	14.6	14.6
90°	24.9	25.8	24.9	24.1	24.9	23.2	22.3	21.5	20.6	21.5	18.9
92.5°	45.5	47.3	46.4	49.8	51.6	57.6	66.2	85.1	119.5	159.9	177.0
95°	99.7	103.1	109.1	116.9	133.2	164.2	209.7	309.4	413.4	509.6	453.8
97.5°	204.5	214.0	234.6	267.3	324.9	422.8	536.3	710.7	810.4	783.8	585.3
100°	538.9	538.0	571.5	634.3	721.1	843.1	943.7	1013.3	983.2	813.9	550.0
102.5°	853.4	878.3	905.0	951.4	1014.1	1080.3	1128.4	1113.8	991.8	758.0	498.5
105°	1093.2	1097.5	1125.0	1157.7	1197.2	1219.5	1203.2	1117.3	937.6	691.0	458.1
107.5°	1249.6	1259.1	1270.2	1285.7	1290.9	1267.7	1200.6	1065.7	860.3	631.7	428.9
110°	1339.0	1340.7	1342.4	1335.6	1311.5	1251.3	1143.0	984.9	788.1	582.7	413.4



TEST NUMBER: P831920

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1357.0	1356.2	1347.6	1322.7	1273.7	1192.0	1067.4	905.0	725.4	550.0	404.8
115°	1329.5	1325.2	1308.1	1270.2	1205.8	1112.1	985.8	836.2	677.2	528.5	403.9
117.5°	1269.4	1263.4	1237.6	1195.5	1128.4	1031.3	915.3	782.9	645.4	513.9	404.8
120°	1190.3	1185.2	1164.5	1116.4	1048.5	961.7	858.6	742.5	621.4	504.5	408.2
122.5°	1116.4	1109.5	1086.3	1044.2	985.8	906.7	813.0	710.7	601.6	498.5	414.2
125°	1048.5	1042.5	1021.0	983.2	928.2	859.4	776.9	683.2	585.3	493.3	420.3
127.5°	990.1	984.9	965.1	932.5	882.6	819.0	743.4	658.3	569.8	490.7	427.1
130°	941.9	935.1	917.0	886.1	840.5	782.1	712.5	635.1	557.8	488.2	434.0
132.5°	894.7	890.4	874.9	844.0	801.8	746.8	683.2	613.6	546.6	487.3	439.2
135°	850.0	844.0	828.5	802.7	760.6	711.6	655.7	594.7	537.1	486.4	444.3
137.5°	802.7	797.6	784.7	758.0	721.9	678.1	628.2	576.7	528.5	484.7	447.8
140°	752.9	753.7	740.0	715.9	683.2	646.3	605.0	561.2	520.8	483.9	451.2
142.5°	706.5	707.3	695.3	674.7	648.0	617.1	582.7	546.6	513.9	482.1	453.8
145°	664.3	662.6	655.7	637.7	616.2	591.3	563.8	535.4	507.9	480.4	454.6
147.5°	628.2	627.4	620.5	607.6	590.4	572.4	549.2	526.0	501.9	477.8	454.6
150°	597.3	597.3	592.1	582.7	569.8	553.5	535.4	515.7	495.9	474.4	454.6
152.5°	571.5	571.5	568.9	560.3	550.9	538.0	522.5	506.2	489.0	470.1	452.1
155°	550.9	550.0	548.3	541.4	533.7	523.4	510.5	496.8	482.1	465.0	450.3
157.5°	531.1	531.1	529.4	524.3	517.4	508.8	498.5	486.4	474.4	460.7	447.8
160°	512.2	513.1	513.1	507.9	501.9	495.9	487.3	477.8	466.7	455.5	446.0
162.5°	495.0	495.9	495.9	491.6	488.2	483.0	475.3	467.5	458.9	450.3	442.6
165°	480.4	480.4	481.3	477.8	474.4	470.1	464.1	458.9	452.1	445.2	439.2
167.5°	465.8	465.8	466.7	464.1	462.4	458.9	455.5	451.2	445.2	440.0	435.7
170°	452.9	452.9	453.8	452.1	451.2	449.5	446.0	443.5	439.2	434.9	432.3
172.5°	440.9	441.7	443.5	441.7	441.7	440.9	438.3	436.6	433.2	430.6	429.7
175°	432.3	433.2	434.0	433.2	433.2	433.2	431.4	430.6	428.9	427.1	427.1
177.5°	426.3	426.3	428.0	427.1	428.0	428.0	427.1	426.3	425.4	424.6	425.4
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P831920

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8
2.5°	3425.9	3422.6	3390.9	3359.1	3328.0	3296.9	3273.8	3250.6	3211.6	3172.6	3148.1
5°	3638.3	3613.1	3562.9	3512.6	3437.2	3361.8	3298.3	3234.8	3154.1	3073.4	3005.9
7.5°	3756.7	3736.2	3675.3	3614.5	3514.6	3414.7	3315.5	3216.2	3097.2	2978.1	2876.2
10°	3760.0	3777.2	3726.9	3676.7	3564.2	3451.7	3316.8	3181.8	3021.8	2861.7	2730.0
12.5°	3642.3	3716.3	3705.8	3695.2	3580.7	3466.3	3302.2	3138.2	2941.7	2745.3	2580.5
15°	3422.0	3565.5	3607.9	3650.2	3555.6	3461.0	3274.5	3087.9	2857.0	2626.2	2437.0
17.5°	3138.2	3339.3	3451.1	3562.9	3494.1	3425.3	3220.9	3016.5	2756.5	2496.5	2290.8
20°	2802.1	3065.4	3240.7	3416.0	3390.9	3365.7	3154.7	2943.7	2663.2	2382.7	2159.8
22.5°	2470.1	2747.9	2990.0	3232.1	3257.9	3283.7	3070.7	2857.7	2550.8	2243.8	2016.9
25°	2183.6	2466.1	2754.5	3042.9	3101.1	3159.4	2956.9	2754.5	2436.3	2118.1	1892.6
27.5°	1910.4	2179.0	2496.5	2814.0	2919.9	3025.7	2840.5	2655.3	2323.9	1992.5	1767.5
30°	1687.5	1927.6	2251.8	2575.9	2723.4	2870.9	2700.9	2530.9	2202.2	1873.4	1653.1
32.5°	1479.8	1694.8	2020.2	2345.7	2517.0	2688.4	2541.5	2394.7	2078.5	1762.3	1544.6
35°	1315.7	1508.2	1811.9	2115.5	2307.3	2499.2	2378.8	2258.4	1949.5	1640.5	1434.8
37.5°	1174.8	1336.2	1621.4	1906.5	2110.2	2314.0	2213.4	2112.9	1822.5	1532.0	1337.6
40°	1058.4	1188.1	1453.3	1718.6	1918.4	2118.1	2032.1	1946.2	1686.2	1426.2	1244.3
42.5°	958.5	1070.3	1308.5	1546.6	1729.8	1913.1	1856.2	1799.3	1563.8	1328.3	1159.6
45°	870.5	964.5	1174.2	1383.9	1552.6	1721.2	1676.3	1631.3	1428.2	1225.1	1070.3
47.5°	792.5	873.2	1060.4	1247.6	1399.1	1550.6	1508.9	1467.2	1299.2	1131.2	990.3
50°	721.0	789.8	946.0	1102.1	1238.3	1374.6	1340.2	1305.8	1166.9	1028.0	906.3
52.5°	653.6	710.5	850.7	990.9	1100.7	1210.6	1184.1	1157.6	1050.5	943.3	832.8
55°	589.4	641.7	760.1	878.5	972.4	1066.3	1039.9	1013.4	930.1	846.7	749.5
57.5°	531.2	576.8	672.8	768.7	843.4	918.2	905.6	893.0	823.6	754.1	674.1
60°	469.7	510.7	593.4	676.1	736.3	796.5	781.9	767.3	717.7	668.1	599.3
62.5°	414.8	451.1	517.3	583.4	632.4	681.4	670.8	660.2	622.5	584.8	527.9
65°	357.2	392.9	446.5	500.1	538.5	576.8	567.6	558.3	529.9	501.4	455.8
67.5°	305.0	334.7	381.0	427.3	453.1	478.9	473.6	468.3	446.5	424.7	389.0
70°	252.0	277.8	316.2	354.6	372.4	390.3	392.3	394.3	374.4	354.6	328.1
72.5°	199.1	219.6	255.3	291.1	305.0	318.8	318.2	317.5	305.6	293.7	269.9
75°	152.8	168.0	195.8	223.6	235.5	247.4	250.0	252.7	241.4	230.2	217.0
77.5°	109.8	120.4	141.6	162.7	176.0	189.2	190.5	191.8	186.5	181.3	168.7
80°	77.4	80.7	93.9	107.2	121.1	134.9	136.9	138.9	133.6	128.3	120.4
82.5°	53.6	55.6	60.2	64.8	76.1	87.3	90.0	92.6	90.0	87.3	78.7
85°	32.4	33.1	35.1	37.0	42.3	47.6	50.3	52.9	51.6	50.3	45.6
87.5°	14.6	14.6	15.2	15.9	17.2	18.5	21.8	25.1	23.2	21.2	19.2
90°	16.3	13.8	11.2	9.5	7.7	5.2	3.4	1.7	3.4	5.2	7.7
92.5°	132.4	86.8	59.3	43.8	35.2	27.5	18.9	12.9	18.9	27.5	35.2
95°	312.8	184.8	111.7	78.2	55.9	41.3	31.8	29.2	31.8	41.3	55.9
97.5°	348.1	199.4	127.2	90.2	67.9	55.0	47.3	46.4	47.3	55.0	67.9
100°	324.0	196.8	136.6	103.1	82.5	70.5	64.5	63.6	64.5	70.5	82.5
102.5°	303.4	200.2	147.8	117.7	99.7	88.5	83.4	81.6	83.4	88.5	99.7
105°	295.6	207.1	160.7	134.1	117.7	107.4	102.3	99.7	102.3	107.4	117.7
107.5°	293.9	218.3	177.0	152.1	136.6	126.3	121.2	118.6	121.2	126.3	136.6
110°	298.2	232.9	194.2	170.2	155.6	146.1	141.8	139.2	141.8	146.1	155.6





TEST NUMBER: P831920

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	306.8	247.5	212.3	189.1	174.5	165.0	160.7	158.1	160.7	165.0	174.5
115°	316.3	263.8	231.2	208.0	193.4	184.8	179.6	176.2	179.6	184.8	193.4
117.5°	328.3	281.0	248.4	226.9	210.6	202.8	198.5	194.2	198.5	202.8	210.6
120°	342.1	297.4	266.4	244.9	228.6	220.0	215.7	213.1	215.7	220.0	228.6
122.5°	354.9	314.6	284.5	261.3	245.8	236.3	232.0	229.5	232.0	236.3	245.8
125°	368.7	330.9	300.8	277.6	261.3	251.8	246.7	244.9	246.7	251.8	261.3
127.5°	379.9	345.5	316.3	293.1	275.0	265.6	259.5	257.0	259.5	265.6	275.0
130°	391.0	358.4	330.0	306.8	288.8	278.5	270.7	268.1	270.7	278.5	288.8
132.5°	401.4	369.6	342.1	319.7	301.7	288.8	280.2	276.7	280.2	288.8	301.7
135°	409.9	380.7	354.1	330.9	312.8	299.9	290.5	287.0	290.5	299.9	312.8
137.5°	416.8	388.5	362.7	341.2	323.1	309.4	299.9	296.5	299.9	309.4	323.1
140°	422.0	396.2	371.3	349.8	332.6	318.8	310.3	306.0	310.3	318.8	332.6
142.5°	427.1	402.2	378.1	358.4	341.2	329.2	319.7	316.3	319.7	329.2	341.2
145°	430.6	407.4	385.0	365.3	350.6	337.8	330.0	327.4	330.0	337.8	350.6
147.5°	433.2	411.7	391.0	373.9	359.2	348.1	340.3	338.6	340.3	348.1	359.2
150°	434.0	416.0	396.2	380.7	368.7	357.5	350.6	349.8	350.6	357.5	368.7
152.5°	435.7	418.5	402.2	387.6	377.3	367.8	361.0	361.0	361.0	367.8	377.3
155°	435.7	422.0	407.4	395.3	385.9	377.3	372.1	372.1	372.1	377.3	385.9
157.5°	436.6	423.7	411.7	402.2	393.6	385.9	381.6	380.7	381.6	385.9	393.6
160°	436.6	426.3	416.0	407.4	401.4	394.5	391.0	391.0	391.0	394.5	401.4
162.5°	435.7	427.1	418.5	411.7	406.5	401.4	398.8	398.8	398.8	401.4	406.5
165°	434.0	428.0	421.1	415.1	411.7	407.4	405.7	406.5	405.7	407.4	411.7
167.5°	433.2	428.0	422.8	418.5	416.0	412.5	411.7	412.5	411.7	412.5	416.0
170°	430.6	427.1	422.8	421.1	419.4	416.8	416.0	417.7	416.0	416.8	419.4
172.5°	429.7	427.1	423.7	422.8	422.0	420.3	420.3	421.1	420.3	420.3	422.0
175°	428.0	426.3	424.6	423.7	423.7	422.0	422.8	423.7	422.8	422.0	423.7
177.5°	427.1	425.4	424.6	424.6	424.6	423.7	424.6	425.4	424.6	423.7	424.6
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P831920

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8
2.5°	3123.6	3085.9	3048.2	3021.1	2994.0	2960.2	2926.5	2925.2	2923.9	2898.7	2873.6
5°	2938.4	2872.9	2807.4	2743.3	2679.1	2614.9	2550.8	2536.2	2521.7	2499.8	2478.0
7.5°	2774.4	2669.8	2565.3	2483.3	2401.3	2337.1	2272.9	2229.3	2185.6	2151.9	2118.1
10°	2598.4	2468.7	2339.1	2239.9	2140.6	2071.2	2001.7	1951.4	1901.2	1877.4	1853.5
12.5°	2415.8	2274.9	2134.0	2036.8	1939.5	1856.2	1772.8	1727.2	1681.5	1648.5	1615.4
15°	2247.8	2096.3	1944.8	1841.6	1738.4	1660.4	1582.3	1536.7	1491.0	1458.0	1424.9
17.5°	2085.1	1932.3	1779.5	1674.9	1570.4	1499.6	1428.9	1384.5	1340.2	1319.7	1299.2
20°	1936.9	1782.8	1628.6	1530.1	1431.5	1362.0	1292.6	1268.8	1245.0	1225.8	1206.6
22.5°	1790.0	1641.9	1493.7	1399.1	1304.5	1254.2	1203.9	1184.8	1165.6	1151.0	1136.5
25°	1667.0	1519.5	1372.0	1289.3	1206.6	1167.6	1128.5	1116.0	1103.4	1088.8	1074.3
27.5°	1542.6	1402.4	1262.2	1196.0	1129.9	1098.1	1066.3	1050.5	1034.6	1022.7	1010.8
30°	1432.8	1303.2	1173.5	1118.6	1063.7	1035.9	1008.1	990.9	973.7	962.5	951.2
32.5°	1327.0	1211.9	1096.8	1049.8	1002.8	975.7	948.6	932.1	915.5	902.3	889.1
35°	1229.1	1129.2	1029.3	986.3	943.3	916.2	889.1	872.5	856.0	842.8	829.5
37.5°	1143.1	1052.5	961.8	921.5	881.1	857.3	833.5	816.3	799.1	785.2	771.3
40°	1062.4	982.3	902.3	863.3	824.2	798.4	772.6	757.4	742.2	729.6	717.1
42.5°	990.9	917.5	844.1	805.7	767.3	742.9	718.4	700.5	682.7	675.4	668.1
45°	915.5	850.7	785.9	748.8	711.8	686.0	660.2	645.0	629.8	623.1	616.5
47.5°	849.4	789.2	729.0	692.6	656.2	633.1	609.9	598.0	586.1	576.8	567.6
50°	784.5	726.3	668.1	633.1	598.0	578.2	558.3	543.8	529.2	522.6	516.0
52.5°	722.4	669.4	616.5	580.8	545.1	525.9	506.7	494.1	481.6	467.7	453.8
55°	652.2	605.9	559.6	527.9	496.1	476.3	456.4	441.9	427.3	412.8	398.2
57.5°	594.0	548.4	502.7	474.3	445.9	426.7	407.5	391.6	375.7	363.8	351.9
60°	530.5	490.8	451.1	423.4	395.6	377.1	358.5	343.3	328.1	322.2	316.2
62.5°	471.0	433.9	396.9	372.4	348.0	330.1	312.2	302.3	292.4	288.4	284.4
65°	410.1	378.4	346.6	324.1	301.6	286.4	271.2	266.6	262.0	258.6	255.3
67.5°	353.2	326.1	299.0	279.2	259.3	248.7	238.1	232.9	227.6	223.6	219.6
70°	301.6	277.8	254.0	236.8	219.6	209.7	199.8	195.1	190.5	183.2	176.0
72.5°	246.1	227.6	209.0	195.8	182.6	174.0	165.4	156.1	146.9	140.2	133.6
75°	203.7	185.2	166.7	154.1	141.6	131.6	121.7	118.4	115.1	113.1	111.1
77.5°	156.1	140.2	124.4	114.4	104.5	99.9	95.3	93.3	91.3	90.6	90.0
80°	112.5	99.2	86.0	80.7	75.4	74.1	72.8	71.4	70.1	69.5	68.8
82.5°	70.1	63.5	56.9	55.6	54.2	53.6	52.9	52.3	51.6	50.9	50.3
85°	41.0	38.4	35.7	35.1	34.4	33.7	33.1	33.1	33.1	33.1	33.1
87.5°	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	16.5	15.9
90°	9.5	11.2	13.8	16.3	18.9	21.5	20.6	21.5	22.3	23.2	24.9
92.5°	43.8	59.3	86.8	132.4	177.0	159.9	119.5	85.1	66.2	57.6	51.6
95°	78.2	111.7	184.8	312.8	453.8	509.6	413.4	309.4	209.7	164.2	133.2
97.5°	90.2	127.2	199.4	348.1	585.3	783.8	810.4	710.7	536.3	422.8	324.9
100°	103.1	136.6	196.8	324.0	550.0	813.9	983.2	1013.3	943.7	843.1	721.1
102.5°	117.7	147.8	200.2	303.4	498.5	758.0	991.8	1113.8	1128.4	1080.3	1014.1
105°	134.1	160.7	207.1	295.6	458.1	691.0	937.6	1117.3	1203.2	1219.5	1197.2
107.5°	152.1	177.0	218.3	293.9	428.9	631.7	860.3	1065.7	1200.6	1267.7	1290.9
110°	170.2	194.2	232.9	298.2	413.4	582.7	788.1	984.9	1143.0	1251.3	1311.5



TEST NUMBER: P831920

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	189.1	212.3	247.5	306.8	404.8	550.0	725.4	905.0	1067.4	1192.0	1273.7
115°	208.0	231.2	263.8	316.3	403.9	528.5	677.2	836.2	985.8	1112.1	1205.8
117.5°	226.9	248.4	281.0	328.3	404.8	513.9	645.4	782.9	915.3	1031.3	1128.4
120°	244.9	266.4	297.4	342.1	408.2	504.5	621.4	742.5	858.6	961.7	1048.5
122.5°	261.3	284.5	314.6	354.9	414.2	498.5	601.6	710.7	813.0	906.7	985.8
125°	277.6	300.8	330.9	368.7	420.3	493.3	585.3	683.2	776.9	859.4	928.2
127.5°	293.1	316.3	345.5	379.9	427.1	490.7	569.8	658.3	743.4	819.0	882.6
130°	306.8	330.0	358.4	391.0	434.0	488.2	557.8	635.1	712.5	782.1	840.5
132.5°	319.7	342.1	369.6	401.4	439.2	487.3	546.6	613.6	683.2	746.8	801.8
135°	330.9	354.1	380.7	409.9	444.3	486.4	537.1	594.7	655.7	711.6	760.6
137.5°	341.2	362.7	388.5	416.8	447.8	484.7	528.5	576.7	628.2	678.1	721.9
140°	349.8	371.3	396.2	422.0	451.2	483.9	520.8	561.2	605.0	646.3	683.2
142.5°	358.4	378.1	402.2	427.1	453.8	482.1	513.9	546.6	582.7	617.1	648.0
145°	365.3	385.0	407.4	430.6	454.6	480.4	507.9	535.4	563.8	591.3	616.2
147.5°	373.9	391.0	411.7	433.2	454.6	477.8	501.9	526.0	549.2	572.4	590.4
150°	380.7	396.2	416.0	434.0	454.6	474.4	495.9	515.7	535.4	553.5	569.8
152.5°	387.6	402.2	418.5	435.7	452.1	470.1	489.0	506.2	522.5	538.0	550.9
155°	395.3	407.4	422.0	435.7	450.3	465.0	482.1	496.8	510.5	523.4	533.7
157.5°	402.2	411.7	423.7	436.6	447.8	460.7	474.4	486.4	498.5	508.8	517.4
160°	407.4	416.0	426.3	436.6	446.0	455.5	466.7	477.8	487.3	495.9	501.9
162.5°	411.7	418.5	427.1	435.7	442.6	450.3	458.9	467.5	475.3	483.0	488.2
165°	415.1	421.1	428.0	434.0	439.2	445.2	452.1	458.9	464.1	470.1	474.4
167.5°	418.5	422.8	428.0	433.2	435.7	440.0	445.2	451.2	455.5	458.9	462.4
170°	421.1	422.8	427.1	430.6	432.3	434.9	439.2	443.5	446.0	449.5	451.2
172.5°	422.8	423.7	427.1	429.7	429.7	430.6	433.2	436.6	438.3	440.9	441.7
175°	423.7	424.6	426.3	428.0	427.1	427.1	428.9	430.6	431.4	433.2	433.2
177.5°	424.6	424.6	425.4	427.1	425.4	424.6	425.4	426.3	427.1	428.0	428.0
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P831920

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	3226.8	3226.8	3226.8	3226.8
2.5°	2867.0	2860.4	2857.7	2855.1
5°	2457.5	2437.0	2432.4	2427.7
7.5°	2109.5	2100.9	2072.5	2044.1
10°	1827.1	1800.6	1788.7	1776.8
12.5°	1590.9	1566.4	1562.5	1558.5
15°	1407.7	1390.5	1384.5	1378.6
17.5°	1287.3	1275.4	1268.1	1260.8
20°	1198.0	1189.4	1184.1	1178.8
22.5°	1129.9	1123.2	1119.3	1115.3
25°	1064.4	1054.4	1051.1	1047.8
27.5°	1002.2	993.6	990.3	987.0
30°	944.0	936.7	932.1	927.4
32.5°	880.5	871.9	869.2	866.6
35°	824.2	818.9	816.3	813.7
37.5°	764.7	758.1	754.1	750.1
40°	713.8	710.5	708.5	706.5
42.5°	662.2	656.2	655.6	654.9
45°	610.6	604.6	603.3	602.0
47.5°	562.3	557.0	556.3	555.7
50°	508.7	501.4	496.1	490.8
52.5°	447.2	440.6	435.9	431.3
55°	391.0	383.7	379.7	375.7
57.5°	348.6	345.3	343.3	341.3
60°	314.2	312.2	310.9	309.6
62.5°	282.5	280.5	280.5	280.5
65°	253.4	251.4	249.4	247.4
67.5°	215.7	211.7	211.0	210.4
70°	170.0	164.1	163.4	162.7
72.5°	133.0	132.3	131.0	129.7
75°	109.8	108.5	108.5	108.5
77.5°	88.6	87.3	87.3	87.3
80°	68.1	67.5	68.1	68.8
82.5°	50.3	50.3	49.6	49.0
85°	32.4	31.8	31.8	31.8
87.5°	15.9	15.9	15.9	15.9
90°	24.1	24.9	25.8	24.9
92.5°	49.8	46.4	47.3	45.5
95°	116.9	109.1	103.1	99.7
97.5°	267.3	234.6	214.0	204.5
100°	634.3	571.5	538.0	538.9
102.5°	951.4	905.0	878.3	853.4
105°	1157.7	1125.0	1097.5	1093.2
107.5°	1285.7	1270.2	1259.1	1249.6
110°	1335.6	1342.4	1340.7	1339.0



TEST NUMBER: P831920

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	1322.7	1347.6	1356.2	1357.0
115°	1270.2	1308.1	1325.2	1329.5
117.5°	1195.5	1237.6	1263.4	1269.4
120°	1116.4	1164.5	1185.2	1190.3
122.5°	1044.2	1086.3	1109.5	1116.4
125°	983.2	1021.0	1042.5	1048.5
127.5°	932.5	965.1	984.9	990.1
130°	886.1	917.0	935.1	941.9
132.5°	844.0	874.9	890.4	894.7
135°	802.7	828.5	844.0	850.0
137.5°	758.0	784.7	797.6	802.7
140°	715.9	740.0	753.7	752.9
142.5°	674.7	695.3	707.3	706.5
145°	637.7	655.7	662.6	664.3
147.5°	607.6	620.5	627.4	628.2
150°	582.7	592.1	597.3	597.3
152.5°	560.3	568.9	571.5	571.5
155°	541.4	548.3	550.0	550.9
157.5°	524.3	529.4	531.1	531.1
160°	507.9	513.1	513.1	512.2
162.5°	491.6	495.9	495.9	495.0
165°	477.8	481.3	480.4	480.4
167.5°	464.1	466.7	465.8	465.8
170°	452.1	453.8	452.9	452.9
172.5°	441.7	443.5	441.7	440.9
175°	433.2	434.0	433.2	432.3
177.5°	427.1	428.0	426.3	426.3
180°	424.6	424.6	424.6	424.6



TEST NUMBER: P831920

CATALOG NUMBER: S123RDIP-S1165D1025U935-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.73	14.60	14.64	15.51	16.68	18.39	19.26	19.30	20.18	21.34
	3H	14.95	15.73	15.87	16.65	17.85	19.90	20.67	20.81	21.60	22.79
	4H	15.34	16.07	16.27	17.00	18.20	20.39	21.12	21.32	22.05	23.25
	6H	15.62	16.29	16.56	17.23	18.44	20.70	21.37	21.64	22.31	23.52
	8H	15.71	16.35	16.66	17.30	18.51	20.78	21.42	21.73	22.37	23.59
	12H	15.76	16.37	16.72	17.32	18.55	20.81	21.42	21.77	22.37	23.61
4H	2H	14.46	15.19	15.39	16.12	17.32	18.39	19.12	19.33	20.05	21.26
	3H	15.83	16.44	16.78	17.40	18.61	20.06	20.66	21.00	21.62	22.84
	4H	16.29	16.84	17.24	17.79	19.04	20.66	21.22	21.62	22.17	23.41
	6H	16.66	17.13	17.62	18.11	19.35	21.10	21.58	22.07	22.56	23.80
	8H	16.78	17.23	17.75	18.20	19.45	21.23	21.68	22.20	22.65	23.90
	12H	16.86	17.26	17.85	18.25	19.51	21.30	21.70	22.29	22.69	23.95
8H	4H	16.60	17.05	17.57	18.02	19.27	20.63	21.08	21.60	22.05	23.30
	6H	17.07	17.43	18.06	18.45	19.70	21.13	21.50	22.13	22.51	23.76
	8H	17.26	17.58	18.27	18.59	19.86	21.32	21.64	22.32	22.64	23.91
	12H	17.40	17.69	18.41	18.68	20.00	21.43	21.72	22.44	22.71	24.03
12H	4H	16.62	17.01	17.60	18.00	19.26	20.58	20.98	21.57	21.97	23.23
	6H	17.13	17.45	18.13	18.45	19.72	21.10	21.43	22.11	22.43	23.70
	8H	17.35	17.63	18.35	18.63	19.94	21.30	21.58	22.31	22.58	23.90