

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332389-935

Luminaire Tested: **S123RDIP-S1165D1195U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332389-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1195U935-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7491.6 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332389-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332389-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50
1	98	94	90	87	91	87	84	81	74	71	69	62	60	58	50	49	48	43
2	90	82	76	71	83	76	71	67	65	61	58	54	52	49	45	43	41	37
3	82	73	66	60	75	67	61	56	58	53	49	48	45	42	40	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17963	17963	17963
5°	18031	17782	17884
10°	17930	17559	17500
15°	17736	17149	16967
20°	17472	16635	16247
25°	17199	16057	15543
30°	16839	15392	14551
35°	16469	14725	13641
40°	16127	13939	12513
45°	15678	13164	11496
50°	15185	12285	10357
55°	14681	11277	9295
60°	14219	10198	8129
65°	13616	9032	6963
70°	12862	7582	5624
75°	11761	5964	5294
80°	10488	5281	4866
85°	8855	4681	4347



TEST NUMBER: P332389-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.7	2.1
10°-20°	436.0	5.8
20°-30°	627.8	8.4
30°-40°	707.2	9.4
40°-50°	676.5	9.0
50°-60°	554.0	7.4
60°-70°	373.8	5.0
70°-80°	188.1	2.5
80°-90°	53.6	0.7
90°-100°	275.0	3.7
100°-110°	778.7	10.4
110°-120°	766.1	10.2
120°-130°	611.0	8.2
130°-140°	481.8	6.4
140°-150°	359.6	4.8
150°-160°	250.6	3.3
160°-170°	147.2	2.0
170°-180°	47.9	0.6
0°-30°	1220.5	16.3
0°-40°	1927.7	25.7
0°-60°	3158.3	42.2
0°-90°	3773.7	50.4
90°-120°	1819.8	24.3
90°-150°	3272.2	43.7
90°-180°	3718.0	49.6
0°-180°	7491.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1669	1669	1669	1669	1669	
5°	1669	1662	1646	1657	1655	158
15°	1592	1575	1539	1532	1523	448
25°	1448	1413	1352	1324	1309	666
35°	1253	1203	1121	1064	1038	784
45°	1030	967	865	790	755	794
55°	782	713	601	525	495	701
65°	535	458	355	291	273	529
75°	283	217	143	131	127	302
85°	72	43	38	35	35	81
90°	2	12	25	28	29	6
95°	34	110	593	173	116	37
105°	116	172	804	1406	1272	123
115°	205	256	615	1349	1548	203
125°	285	337	574	1040	1220	253
135°	334	399	566	857	989	258
145°	381	437	559	703	773	239
155°	433	467	541	615	641	199
165°	473	487	518	550	559	133
175°	493	494	497	504	503	47
180°	494	494	494	494	494	



TEST NUMBER: P332389-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1674.2	1673.2	1672.2	1671.3	1670.3	1668.4	1665.5	1662.6	1659.7	1656.8	1659.5
5°	1668.8	1667.2	1665.8	1664.2	1662.8	1660.2	1656.6	1652.9	1649.3	1645.7	1648.5
7.5°	1653.3	1651.7	1650.1	1648.5	1646.8	1643.6	1639.0	1634.3	1629.6	1624.9	1626.4
10°	1640.4	1638.2	1636.2	1634.0	1631.9	1628.2	1622.7	1617.3	1611.9	1606.5	1606.8
12.5°	1622.0	1619.6	1617.2	1614.9	1612.6	1608.1	1601.5	1594.8	1588.2	1581.6	1581.4
15°	1591.6	1588.3	1585.0	1581.7	1578.4	1572.5	1564.1	1555.7	1547.2	1538.9	1537.3
17.5°	1553.4	1549.6	1545.8	1541.9	1538.1	1530.8	1520.1	1509.3	1498.7	1488.0	1484.8
20°	1525.3	1520.5	1515.7	1510.9	1506.1	1498.0	1486.5	1475.1	1463.6	1452.2	1448.3
22.5°	1493.9	1488.3	1482.8	1477.3	1471.8	1462.9	1450.8	1438.6	1426.5	1414.3	1409.5
25°	1448.1	1440.6	1433.1	1425.6	1418.1	1407.4	1393.5	1379.8	1365.9	1352.0	1345.7
27.5°	1392.7	1384.4	1376.1	1367.8	1359.4	1347.6	1332.2	1316.8	1301.4	1286.0	1277.2
30°	1354.8	1345.7	1336.7	1327.7	1318.7	1305.7	1288.9	1272.0	1255.3	1238.4	1228.1
32.5°	1316.9	1306.7	1296.4	1286.2	1276.0	1262.0	1244.1	1226.3	1208.5	1190.8	1179.6
35°	1253.3	1242.4	1231.6	1220.8	1210.0	1195.2	1176.6	1158.0	1139.3	1120.6	1107.7
37.5°	1188.9	1176.8	1164.8	1152.7	1140.7	1124.7	1104.8	1084.9	1065.1	1045.1	1030.4
40°	1147.7	1134.5	1121.2	1108.0	1094.8	1077.5	1056.1	1034.7	1013.4	992.0	976.4
42.5°	1101.1	1087.9	1074.7	1061.4	1048.2	1030.5	1008.5	986.4	964.3	942.3	925.1
45°	1029.9	1016.4	1002.9	989.4	975.8	957.4	934.3	911.1	887.9	864.8	847.7
47.5°	958.7	943.9	929.0	914.2	899.3	880.3	857.1	834.0	810.8	787.7	769.0
50°	906.8	892.7	878.5	864.4	850.2	831.0	806.7	782.3	757.9	733.6	714.9
52.5°	860.2	844.9	829.6	814.2	798.8	779.1	755.0	730.9	706.8	682.7	663.3
55°	782.3	767.5	752.8	738.0	723.3	703.2	677.6	652.0	626.5	600.9	583.5
57.5°	710.2	694.2	678.1	662.1	646.0	625.2	599.5	573.8	548.1	522.5	505.9
60°	660.5	643.9	627.4	610.9	594.3	573.5	548.5	523.7	498.7	473.7	457.4
62.5°	610.6	594.1	577.6	561.0	544.5	523.7	498.8	473.8	448.8	423.9	408.6
65°	534.6	518.1	501.5	485.0	468.5	448.4	425.0	401.5	378.1	354.6	339.8
67.5°	458.6	441.8	425.1	408.4	391.7	372.0	349.6	327.0	304.5	282.1	271.0
70°	408.7	392.5	376.3	360.0	343.8	325.1	304.1	283.0	262.0	240.9	230.4
72.5°	359.0	342.9	326.9	310.9	294.9	277.3	258.2	239.1	220.0	200.9	192.3
75°	282.8	268.5	254.0	239.5	225.2	209.7	193.1	176.5	160.0	143.4	140.4
77.5°	213.5	200.5	187.4	174.4	161.4	149.5	138.9	128.2	117.5	106.9	105.3
80°	169.2	156.9	144.5	132.2	119.9	110.6	104.2	97.9	91.6	85.2	84.4
82.5°	126.9	116.3	105.6	95.0	84.4	77.6	74.6	71.6	68.7	65.8	64.8
85°	71.7	65.1	58.5	51.9	45.3	41.5	40.6	39.7	38.8	37.9	37.3
87.5°	26.3	24.1	21.9	19.9	17.6	16.7	17.3	17.9	18.5	19.1	18.6
90°	2.0	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0
92.5°	12.4	18.4	26.8	34.6	43.0	57.9	84.0	127.1	169.3	153.9	116.1
95°	34.0	37.0	48.0	65.0	91.0	130.0	215.1	364.1	528.2	593.2	481.1
97.5°	58.0	59.0	67.6	82.4	108.1	150.2	231.5	399.5	673.0	919.3	983.5
100°	74.0	75.0	82.1	96.0	120.0	159.0	229.1	377.1	640.2	947.4	1144.4
102.5°	90.8	92.6	98.8	112.0	133.6	169.4	232.3	357.9	592.2	895.4	1152.4
105°	116.1	119.1	125.0	137.1	156.0	187.1	241.1	344.1	533.2	804.3	1091.4
107.5°	142.8	145.9	151.6	163.4	181.2	210.1	257.5	343.1	495.6	723.8	984.6
110°	162.0	165.1	170.0	181.1	198.0	226.1	271.1	347.2	481.1	678.2	917.3



TEST NUMBER: P332389-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	179.7	182.7	187.7	198.6	215.7	242.9	284.7	355.2	473.2	647.8	858.9
115°	205.1	209.1	215.1	225.1	242.1	269.1	307.1	368.2	470.2	615.2	788.2
117.5°	230.5	235.1	240.0	249.3	268.3	293.3	330.9	385.3	472.0	596.0	745.6
120°	248.1	251.1	256.1	266.1	285.1	310.1	346.1	398.1	475.2	587.2	723.2
122.5°	263.3	266.3	271.3	282.1	300.3	326.9	362.1	410.2	480.8	581.6	704.8
125°	285.1	287.1	293.1	304.1	323.1	350.1	385.1	429.1	489.1	574.2	681.2
127.5°	301.7	304.7	312.1	323.3	344.3	371.3	405.1	444.8	498.8	570.6	660.5
130°	312.1	315.1	324.1	336.1	357.1	384.1	417.2	455.1	505.1	568.2	649.2
132.5°	320.1	323.9	333.7	348.1	369.1	395.4	427.6	464.8	510.0	567.4	638.9
135°	334.2	338.1	349.1	364.1	385.1	412.2	443.2	477.2	517.2	566.2	625.3
137.5°	347.3	351.5	362.3	378.3	399.2	424.1	453.9	486.4	522.0	564.0	613.4
140°	356.1	361.1	371.1	387.1	407.2	432.1	461.2	491.2	525.2	563.2	606.2
142.5°	365.8	370.0	380.7	395.1	415.2	438.6	466.7	495.9	527.6	561.6	599.8
145°	381.2	384.1	393.1	408.1	425.2	448.2	474.2	501.2	529.2	559.2	591.2
147.5°	396.7	398.6	407.3	420.3	436.8	456.3	480.2	504.4	529.2	555.4	582.8
150°	407.2	408.1	416.1	429.1	443.2	461.2	484.1	505.1	529.2	552.2	577.2
152.5°	417.6	417.8	425.8	437.1	449.5	466.7	486.6	506.8	526.8	548.2	570.8
155°	433.2	433.2	439.2	449.2	460.1	474.2	491.2	507.2	524.2	541.2	561.2
157.5°	445.6	446.3	451.2	459.9	469.3	480.2	493.8	508.2	520.8	535.0	550.4
160°	455.1	455.1	459.2	467.2	474.2	484.1	496.2	508.2	519.2	530.2	543.2
162.5°	462.4	462.4	465.5	472.0	478.2	486.6	497.0	507.4	516.0	525.4	536.0
165°	473.2	472.2	474.2	479.1	483.2	490.2	498.2	505.1	511.2	518.1	526.2
167.5°	481.4	480.2	481.1	485.0	487.8	492.1	498.0	503.6	506.4	511.0	516.8
170°	486.2	484.1	485.2	488.2	490.2	492.1	497.1	501.2	503.2	506.2	511.2
172.5°	489.4	488.2	488.4	490.6	491.8	493.0	497.1	500.4	500.8	502.1	505.6
175°	493.2	492.1	491.2	493.2	493.2	494.2	496.2	498.2	497.1	497.1	499.2
177.5°	495.0	494.2	493.4	494.2	494.2	494.2	495.0	496.5	495.0	494.2	495.0
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P332389-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1662.2	1664.8	1667.4	1668.5	1668.0	1667.6	1667.1	1666.6
5°	1651.1	1653.9	1656.6	1657.6	1657.0	1656.4	1655.8	1655.2
7.5°	1627.9	1629.4	1630.9	1631.2	1630.1	1629.1	1628.1	1627.0
10°	1607.1	1607.4	1607.7	1607.1	1605.6	1604.1	1602.6	1601.1
12.5°	1581.2	1581.1	1580.9	1579.9	1578.2	1576.4	1574.7	1573.0
15°	1535.9	1534.3	1532.8	1531.0	1528.9	1526.8	1524.7	1522.6
17.5°	1481.6	1478.3	1475.2	1472.1	1468.9	1465.8	1462.7	1459.5
20°	1444.4	1440.5	1436.6	1432.8	1429.2	1425.6	1422.0	1418.4
22.5°	1404.5	1399.7	1394.8	1390.7	1387.3	1384.0	1380.6	1377.3
25°	1339.5	1333.1	1326.8	1322.0	1318.7	1315.3	1312.1	1308.7
27.5°	1268.4	1259.6	1250.9	1244.0	1238.9	1233.9	1228.8	1223.7
30°	1217.9	1207.7	1197.5	1190.0	1185.2	1180.3	1175.5	1170.7
32.5°	1168.4	1157.2	1146.0	1137.9	1132.8	1127.7	1122.7	1117.7
35°	1094.8	1081.8	1068.9	1059.7	1054.3	1048.9	1043.4	1038.1
37.5°	1015.7	1001.1	986.4	975.7	969.1	962.3	955.7	949.0
40°	960.8	945.1	929.5	918.3	911.3	904.4	897.5	890.5
42.5°	908.1	891.0	873.9	862.3	856.1	849.9	843.7	837.5
45°	830.5	813.4	796.3	784.1	776.9	769.6	762.4	755.2
47.5°	750.4	731.8	713.1	700.6	694.1	687.7	681.2	674.9
50°	696.3	677.6	658.9	646.2	639.3	632.3	625.4	618.5
52.5°	643.9	624.6	605.2	592.4	586.2	580.1	573.9	567.7
55°	566.0	548.5	531.2	519.4	513.4	507.4	501.4	495.3
57.5°	489.5	472.9	456.5	445.7	440.6	435.5	430.3	425.2
60°	441.2	425.0	408.7	398.0	393.0	387.8	382.7	377.6
62.5°	393.3	378.1	362.7	352.5	347.1	341.7	336.4	331.1
65°	325.1	310.4	295.7	286.6	283.4	280.0	276.7	273.4
67.5°	260.0	249.0	238.0	230.7	227.2	223.6	220.1	216.5
70°	219.8	209.3	198.8	191.9	188.6	185.3	181.9	178.7
72.5°	183.7	175.0	166.4	161.4	160.1	158.7	157.3	155.9
75°	137.4	134.4	131.4	129.7	129.1	128.5	127.9	127.3
77.5°	103.7	102.0	100.4	99.3	98.7	98.1	97.5	96.9
80°	83.4	82.6	81.6	80.9	80.3	79.7	79.1	78.5
82.5°	64.0	63.1	62.2	61.6	61.6	61.4	61.3	61.2
85°	36.7	36.1	35.5	35.2	35.2	35.2	35.2	35.2
87.5°	18.6	18.6	18.5	18.7	18.3	18.2	18.2	17.7
90°	25.0	26.0	27.0	29.0	28.0	29.0	30.0	29.0
92.5°	84.2	66.8	59.0	53.8	52.0	49.0	50.0	48.2
95°	360.2	244.1	191.1	155.1	136.0	127.1	120.0	116.1
97.5°	897.7	719.0	590.0	470.4	396.6	351.5	324.5	315.9
100°	1179.4	1098.4	981.4	839.3	738.2	665.2	626.2	627.2
102.5°	1273.1	1270.4	1202.2	1112.2	1033.5	975.8	943.1	920.2
105°	1300.5	1400.5	1419.5	1393.5	1347.5	1309.5	1277.5	1272.5
107.5°	1221.6	1384.1	1471.7	1507.4	1508.1	1495.3	1484.5	1475.3
110°	1146.4	1330.5	1456.6	1526.6	1554.5	1562.5	1560.6	1558.6



TEST NUMBER: P332389-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1071.9	1260.1	1401.3	1491.3	1542.6	1567.4	1574.9	1575.4
115°	973.4	1147.4	1294.4	1403.5	1478.5	1522.5	1542.6	1547.6
117.5°	901.9	1052.1	1184.2	1294.9	1373.1	1423.5	1452.3	1459.1
120°	864.3	999.4	1119.4	1220.5	1299.4	1355.5	1379.5	1385.5
122.5°	834.7	956.9	1068.2	1162.0	1232.3	1282.6	1309.1	1316.6
125°	795.3	904.3	1000.3	1080.4	1144.4	1188.4	1213.4	1220.5
127.5°	760.9	858.1	944.7	1017.5	1074.6	1112.2	1134.8	1141.2
130°	739.3	829.3	910.3	978.4	1031.4	1067.4	1088.4	1096.4
132.5°	719.3	802.1	877.5	942.4	992.1	1028.1	1046.8	1052.4
135°	692.2	763.3	828.3	885.3	934.4	964.3	982.3	989.4
137.5°	667.6	725.8	781.9	831.3	872.5	902.9	918.1	922.7
140°	653.2	704.2	752.3	795.3	833.3	861.3	877.3	876.3
142.5°	639.6	683.5	725.0	762.5	794.9	819.7	834.1	833.1
145°	623.2	656.3	688.3	717.2	742.3	763.3	771.3	773.3
147.5°	609.8	636.0	661.9	682.4	701.5	715.7	723.2	724.0
150°	600.2	623.2	644.2	663.2	678.2	689.2	695.3	695.3
152.5°	591.4	611.2	629.8	645.7	657.5	667.6	671.2	671.2
155°	578.2	594.2	609.2	621.2	630.3	638.3	640.2	641.2
157.5°	564.2	577.6	589.2	598.6	606.4	612.4	614.0	613.8
160°	556.2	567.2	577.2	584.2	591.2	597.2	597.2	596.2
162.5°	546.6	556.0	565.2	571.4	576.0	581.2	581.2	580.2
165°	534.2	540.2	547.2	552.2	556.2	560.2	559.2	559.2
167.5°	523.4	528.0	532.0	535.6	537.4	540.2	539.2	539.2
170°	516.2	519.2	523.1	525.2	526.2	528.2	527.2	527.2
172.5°	509.8	512.0	515.2	516.3	516.6	518.6	516.8	516.0
175°	501.2	502.1	504.2	504.2	504.2	505.1	504.2	503.2
177.5°	495.8	496.5	497.4	497.4	496.5	497.4	495.8	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2

(END OF REPORT)