

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332298-930

Luminaire Tested: **S123RDIP-S560D1195U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332298-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1195U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5084.3 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332298-930

CATALOG NUMBER: S123RDIP-S560D1195U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332298-930

CATALOG NUMBER: S123RDIP-S560D1195U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34
1	94	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	36	29
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	33	32	30	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	28	26	21
4	72	62	54	48	65	56	50	44	45	41	37	36	32	30	26	24	23	18
5	66	55	47	41	60	50	43	38	41	36	32	32	28	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	17	14
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	17	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11
9	48	37	29	25	44	34	27	23	28	23	19	22	19	16	17	14	13	10
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8289	8289	8289
5°	8321	8206	8253
10°	8273	8103	8075
15°	8184	7913	7830
20°	8062	7676	7497
25°	7936	7410	7172
30°	7771	7102	6714
35°	7599	6795	6294
40°	7442	6433	5774
45°	7234	6075	5305
50°	7006	5668	4779
55°	6775	5204	4290
60°	6562	4706	3750
65°	6283	4167	3212
70°	5936	3500	2593
75°	5427	2753	2441
80°	4841	2442	2244
85°	4088	2149	2001



TEST NUMBER: P332298-930

CATALOG NUMBER: S123RDIP-S560D1195U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	1.4
10°-20°	201.2	4.0
20°-30°	289.7	5.7
30°-40°	326.3	6.4
40°-50°	312.2	6.1
50°-60°	255.7	5.0
60°-70°	172.5	3.4
70°-80°	86.8	1.7
80°-90°	26.5	0.5
90°-100°	78.6	1.5
100°-110°	235.1	4.6
110°-120°	399.9	7.9
120°-130°	526.0	10.3
130°-140°	591.2	11.6
140°-150°	581.2	11.4
150°-160°	489.3	9.6
160°-170°	325.7	6.4
170°-180°	114.0	2.2
0°-30°	563.2	11.1
0°-40°	889.5	17.5
0°-60°	1457.4	28.7
0°-90°	1743.2	34.3
90°-120°	713.6	14.0
90°-150°	2412.1	47.4
90°-180°	3341.0	65.7
0°-180°	5084.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	770	770	770	770	770	
5°	770	767	760	765	764	73
15°	734	727	710	707	703	207
25°	668	652	624	611	604	307
35°	578	555	517	491	479	362
45°	475	446	399	365	348	367
55°	361	329	277	242	229	324
65°	247	212	164	134	126	244
75°	130	100	66	60	59	139
85°	33	20	17	16	16	37
90°	1	11	23	26	28	5
95°	56	63	70	74	74	63
105°	213	215	224	224	225	228
115°	403	405	404	404	404	398
125°	589	592	590	586	583	525
135°	764	770	769	766	764	589
145°	927	929	932	931	927	579
155°	1062	1062	1063	1066	1060	489
165°	1157	1154	1154	1159	1153	326
175°	1203	1199	1199	1204	1198	114
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P332298-930

CATALOG NUMBER: S123RDIP-S560D1195U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	772.6	772.1	771.7	771.2	770.8	769.9	768.6	767.2	765.9	764.6	765.8
5°	770.1	769.4	768.7	768.0	767.3	766.1	764.4	762.8	761.1	759.5	760.7
7.5°	763.0	762.2	761.4	760.7	759.9	758.5	756.4	754.2	752.0	749.8	750.5
10°	756.9	755.9	755.0	754.0	753.1	751.3	748.9	746.3	743.8	741.4	741.4
12.5°	748.4	747.4	746.2	745.2	744.1	742.1	739.0	736.0	732.9	729.9	729.8
15°	734.4	733.0	731.4	729.9	728.4	725.6	721.8	717.9	714.0	710.1	709.4
17.5°	716.8	715.1	713.3	711.5	709.7	706.4	701.4	696.5	691.5	686.6	685.2
20°	703.8	701.6	699.4	697.2	695.0	691.2	685.9	680.7	675.4	670.1	668.3
22.5°	689.3	686.8	684.3	681.7	679.1	675.1	669.4	663.8	658.3	652.6	650.4
25°	668.2	664.8	661.3	657.9	654.4	649.5	643.0	636.7	630.3	623.9	621.0
27.5°	642.6	638.8	635.0	631.1	627.3	621.8	614.7	607.6	600.5	593.5	589.4
30°	625.2	621.0	616.9	612.7	608.5	602.5	594.8	587.0	579.2	571.4	566.7
32.5°	607.6	603.0	598.3	593.5	588.8	582.4	574.1	565.9	557.7	549.4	544.3
35°	578.3	573.3	568.3	563.4	558.3	551.5	542.9	534.3	525.7	517.1	511.1
37.5°	548.6	543.1	537.5	531.9	526.4	519.0	509.8	500.7	491.5	482.2	475.5
40°	529.6	523.5	517.4	511.3	505.2	497.2	487.4	477.5	467.7	457.8	450.5
42.5°	508.1	502.0	495.9	489.8	483.7	475.6	465.4	455.2	445.0	434.8	426.9
45°	475.2	469.0	462.8	456.6	450.3	441.8	431.1	420.4	409.8	399.1	391.2
47.5°	442.4	435.5	428.7	421.8	415.0	406.3	395.5	384.8	374.1	363.5	354.9
50°	418.4	411.9	405.4	398.8	392.3	383.4	372.2	361.0	349.8	338.5	329.9
52.5°	397.0	389.9	382.8	375.7	368.7	359.5	348.4	337.3	326.1	315.0	306.1
55°	361.0	354.2	347.4	340.6	333.8	324.5	312.7	300.9	289.1	277.3	269.2
57.5°	327.8	320.3	312.9	305.5	298.1	288.5	276.6	264.8	252.9	241.1	233.5
60°	304.8	297.2	289.5	281.8	274.3	264.6	253.2	241.7	230.1	218.6	211.1
62.5°	281.8	274.2	266.5	258.9	251.3	241.7	230.2	218.7	207.1	195.6	188.6
65°	246.7	239.0	231.5	223.8	216.1	206.9	196.1	185.3	174.5	163.6	156.9
67.5°	211.6	203.9	196.2	188.4	180.8	171.7	161.3	150.9	140.6	130.1	125.1
70°	188.6	181.1	173.7	166.2	158.7	150.0	140.3	130.6	120.9	111.2	106.3
72.5°	165.6	158.2	150.8	143.5	136.1	128.0	119.2	110.3	101.5	92.7	88.7
75°	130.5	123.8	117.2	110.6	103.9	96.7	89.1	81.4	73.9	66.2	64.8
77.5°	98.6	92.5	86.5	80.5	74.4	69.0	64.1	59.2	54.2	49.3	48.6
80°	78.1	72.4	66.7	61.0	55.3	51.0	48.1	45.2	42.2	39.4	38.9
82.5°	58.6	53.6	48.8	43.9	38.9	35.8	34.4	33.1	31.7	30.3	29.9
85°	33.1	30.1	27.0	24.0	20.9	19.2	18.8	18.3	17.9	17.4	17.2
87.5°	12.1	11.4	10.6	9.8	9.0	8.9	9.4	9.9	10.5	11.0	11.1
90°	1.0	3.0	5.1	7.3	9.4	11.8	14.5	17.3	20.0	22.7	23.6
92.5°	22.9	24.4	25.8	27.2	28.6	30.2	31.7	33.3	34.8	36.4	37.0
95°	55.9	57.4	58.9	60.3	61.8	63.3	65.1	66.7	68.4	70.1	70.9
97.5°	99.3	100.4	101.5	102.6	103.6	104.8	106.1	107.3	108.4	109.7	110.6
100°	128.8	130.1	131.3	132.6	133.9	135.0	136.1	137.1	138.2	139.3	139.9
102.5°	162.9	163.7	164.4	165.2	166.0	167.1	168.4	169.8	171.2	172.6	173.3
105°	213.1	213.5	214.0	214.4	214.8	216.0	217.8	219.8	221.7	223.6	223.6
107.5°	271.5	271.7	272.0	272.2	272.5	273.0	273.8	274.5	275.2	276.1	276.7
110°	307.9	308.3	308.7	309.2	309.6	310.0	310.4	310.8	311.2	311.7	312.5



TEST NUMBER: P332298-930

CATALOG NUMBER: S123RDIP-S560D1195U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	345.8	346.0	346.3	346.5	346.7	346.9	347.0	347.1	347.2	347.2	348.3
115°	402.6	403.2	403.8	404.5	405.1	405.2	404.8	404.4	404.0	403.6	403.7
117.5°	459.8	460.2	460.6	461.1	461.5	461.5	460.9	460.3	459.8	459.3	459.2
120°	495.5	496.7	498.0	499.2	500.5	500.6	499.5	498.5	497.4	496.4	496.2
122.5°	532.6	533.5	534.4	535.3	536.3	536.5	535.9	535.3	534.8	534.3	533.7
125°	589.2	589.9	590.4	591.1	591.7	591.8	591.4	591.0	590.6	590.2	589.3
127.5°	641.5	642.9	644.2	645.6	646.9	647.3	646.9	646.4	646.0	645.5	644.3
130°	676.4	678.0	679.7	681.4	683.1	683.6	683.0	682.3	681.8	681.1	680.3
132.5°	711.2	712.9	714.6	716.2	718.0	718.6	718.1	717.6	717.1	716.7	715.7
135°	764.4	765.7	767.0	768.3	769.5	770.1	769.8	769.6	769.4	769.2	768.3
137.5°	813.8	814.7	815.8	816.8	817.9	818.7	819.3	819.8	820.4	820.9	820.0
140°	847.8	848.9	849.9	851.0	852.0	852.6	852.9	853.0	853.3	853.5	853.3
142.5°	878.9	880.0	881.0	882.1	883.1	883.8	884.2	884.6	884.9	885.3	885.1
145°	927.4	927.8	928.2	928.6	929.0	929.6	930.3	930.8	931.5	932.1	931.9
147.5°	969.8	970.6	971.3	972.1	972.9	973.5	974.1	974.7	975.3	975.9	975.9
150°	999.4	999.8	1000.2	1000.6	1001.1	1001.5	1001.9	1002.3	1002.7	1003.1	1003.1
152.5°	1023.6	1024.3	1024.8	1025.4	1026.0	1026.4	1026.6	1027.0	1027.2	1027.4	1027.8
155°	1061.9	1061.9	1061.9	1061.9	1061.9	1062.0	1062.3	1062.4	1062.7	1062.8	1063.7
157.5°	1094.5	1094.2	1094.0	1093.7	1093.5	1093.4	1093.6	1093.8	1094.0	1094.1	1095.0
160°	1114.9	1114.5	1114.1	1113.7	1113.3	1113.0	1113.0	1113.0	1113.0	1113.0	1114.1
162.5°	1133.1	1132.5	1132.0	1131.4	1130.8	1130.6	1130.7	1130.9	1131.1	1131.2	1132.3
165°	1156.7	1156.0	1155.4	1154.7	1154.1	1153.8	1153.8	1153.8	1153.8	1153.8	1155.0
167.5°	1175.4	1174.5	1173.7	1172.9	1172.0	1171.7	1171.8	1172.0	1172.2	1172.3	1173.6
170°	1186.0	1185.1	1184.3	1183.5	1182.6	1182.2	1182.2	1182.2	1182.2	1182.2	1183.7
172.5°	1194.3	1193.5	1192.6	1191.8	1191.0	1190.6	1190.6	1190.6	1190.6	1190.6	1191.9
175°	1203.1	1202.2	1201.3	1200.5	1199.7	1199.2	1199.2	1199.2	1199.2	1199.2	1200.5
177.5°	1206.6	1206.0	1205.3	1204.6	1204.0	1203.6	1203.6	1203.6	1203.6	1203.6	1204.6
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9



TEST NUMBER: P332298-930

CATALOG NUMBER: S123RDIP-S560D1195U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	767.0	768.3	769.5	770.0	769.7	769.5	769.3	769.1
5°	761.9	763.2	764.4	764.9	764.7	764.3	764.1	763.8
7.5°	751.2	751.9	752.6	752.7	752.2	751.8	751.3	750.8
10°	741.6	741.8	741.8	741.6	740.9	740.2	739.6	738.8
12.5°	729.7	729.6	729.5	729.0	728.2	727.4	726.7	725.9
15°	708.7	708.0	707.4	706.5	705.5	704.6	703.6	702.6
17.5°	683.7	682.2	680.7	679.3	677.8	676.4	674.9	673.5
20°	666.5	664.7	662.9	661.2	659.5	657.9	656.2	654.5
22.5°	648.2	645.9	643.7	641.7	640.2	638.6	637.1	635.5
25°	618.1	615.1	612.3	610.0	608.5	607.0	605.4	603.9
27.5°	585.3	581.3	577.2	574.1	571.7	569.4	567.0	564.7
30°	562.0	557.3	552.6	549.1	546.9	544.7	542.4	540.2
32.5°	539.2	533.9	528.8	525.1	522.8	520.4	518.0	515.8
35°	505.2	499.2	493.3	489.0	486.5	484.0	481.5	479.0
37.5°	468.7	461.9	455.2	450.3	447.2	444.1	441.0	437.9
40°	443.4	436.1	428.9	423.7	420.5	417.4	414.2	410.9
42.5°	419.1	411.2	403.2	397.9	395.0	392.2	389.3	386.5
45°	383.3	375.4	367.5	361.8	358.5	355.1	351.8	348.5
47.5°	346.3	337.7	329.1	323.3	320.3	317.3	314.4	311.4
50°	321.3	312.7	304.1	298.2	295.0	291.8	288.6	285.4
52.5°	297.2	288.2	279.2	273.4	270.5	267.7	264.8	262.0
55°	261.2	253.2	245.1	239.7	236.9	234.2	231.4	228.6
57.5°	225.8	218.3	210.7	205.7	203.3	201.0	198.6	196.2
60°	203.6	196.1	188.6	183.7	181.3	179.0	176.6	174.2
62.5°	181.5	174.5	167.4	162.7	160.2	157.7	155.2	152.8
65°	150.0	143.2	136.4	132.2	130.8	129.2	127.7	126.1
67.5°	120.0	114.9	109.8	106.5	104.8	103.2	101.6	100.0
70°	101.4	96.6	91.7	88.5	87.0	85.5	84.0	82.4
72.5°	84.7	80.8	76.8	74.5	73.9	73.2	72.6	71.9
75°	63.4	62.0	60.7	59.8	59.5	59.3	58.9	58.7
77.5°	47.9	47.1	46.3	45.8	45.6	45.2	45.0	44.7
80°	38.5	38.1	37.7	37.3	37.1	36.8	36.5	36.2
82.5°	29.5	29.1	28.7	28.5	28.4	28.4	28.3	28.2
85°	17.0	16.6	16.4	16.2	16.2	16.2	16.2	16.2
87.5°	11.2	11.3	11.3	11.3	11.3	11.3	11.2	11.2
90°	24.5	25.3	26.1	26.7	27.1	27.6	28.0	28.5
92.5°	37.7	38.4	39.1	39.3	39.1	38.8	38.5	38.2
95°	71.7	72.6	73.5	73.9	73.9	73.9	73.9	73.9
97.5°	111.6	112.6	113.6	114.0	113.9	113.8	113.7	113.7
100°	140.5	141.1	141.8	142.3	142.8	143.2	143.6	144.0
102.5°	173.8	174.5	175.1	175.4	175.3	175.2	175.1	175.0
105°	223.6	223.6	223.6	223.8	224.2	224.6	225.0	225.4
107.5°	277.4	278.1	278.8	278.9	278.7	278.4	278.2	277.9
110°	313.3	314.2	315.0	315.2	314.8	314.4	314.0	313.6



TEST NUMBER: P332298-930

CATALOG NUMBER: S123RDIP-S560D1195U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	349.3	350.3	351.3	351.8	351.7	351.6	351.6	351.5
115°	404.0	404.1	404.4	404.4	404.1	404.0	403.7	403.6
117.5°	459.2	459.1	459.1	458.8	458.2	457.5	457.0	456.4
120°	495.9	495.8	495.5	495.2	494.8	494.4	494.0	493.5
122.5°	533.2	532.6	532.1	531.5	530.9	530.4	529.7	529.1
125°	588.5	587.7	586.8	586.0	585.1	584.2	583.4	582.6
127.5°	643.1	642.0	640.7	639.7	638.7	637.7	636.7	635.9
130°	679.4	678.6	677.8	676.5	675.1	673.6	672.1	670.7
132.5°	714.7	713.7	712.7	711.6	710.5	709.3	708.2	707.0
135°	767.5	766.6	765.8	765.2	764.8	764.3	763.9	763.5
137.5°	819.1	818.2	817.3	816.5	815.7	815.0	814.2	813.3
140°	853.0	852.9	852.6	851.8	850.4	848.9	847.4	846.0
142.5°	884.9	884.7	884.5	883.8	882.6	881.5	880.4	879.3
145°	931.7	931.5	931.3	930.7	929.9	929.0	928.2	927.4
147.5°	975.9	975.9	975.9	975.3	974.0	972.7	971.4	970.2
150°	1003.1	1003.1	1003.1	1002.6	1001.3	1000.0	998.7	997.5
152.5°	1028.1	1028.4	1028.7	1028.4	1027.3	1026.2	1025.1	1024.0
155°	1064.5	1065.4	1066.2	1065.9	1064.5	1063.0	1061.5	1060.0
157.5°	1095.8	1096.7	1097.6	1097.5	1096.3	1095.1	1094.0	1092.7
160°	1115.2	1116.2	1117.3	1117.4	1116.6	1115.7	1114.8	1114.0
162.5°	1133.3	1134.4	1135.5	1135.3	1133.9	1132.6	1131.2	1129.9
165°	1156.3	1157.6	1158.9	1158.7	1157.2	1155.8	1154.3	1152.8
167.5°	1174.9	1176.2	1177.5	1177.5	1176.2	1174.9	1173.6	1172.3
170°	1185.1	1186.7	1188.1	1188.1	1186.7	1185.1	1183.7	1182.2
172.5°	1193.2	1194.5	1195.8	1195.7	1194.2	1192.7	1191.2	1189.8
175°	1201.8	1203.1	1204.3	1204.2	1202.7	1201.3	1199.8	1198.3
177.5°	1205.7	1206.6	1207.6	1207.5	1206.4	1205.2	1204.0	1202.9
180°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9

(END OF REPORT)