

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332376-935

Luminaire Tested: **S123RDIP-S1165D805U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332376-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D805U935-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6146.7 lumens  
Efficiency: N/A  
Efficacy: 101.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332376-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332376-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61
1	101	96	93	89	94	90	87	84	79	77	75	69	67	66	59	58	57	53
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	68	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	67	59	53	72	63	56	50	55	50	45	49	44	41	42	39	36	33
5	71	60	51	45	66	56	49	43	50	44	40	44	39	36	38	35	32	29
6	66	54	45	40	61	51	43	38	45	39	35	40	35	31	35	31	28	26
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25	23
8	57	44	36	31	53	42	35	30	38	32	28	33	29	25	29	26	23	21
9	53	41	33	28	49	38	32	27	35	29	25	31	26	23	27	23	21	19
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	25	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17963	17963	17963
5°	18031	17782	17884
10°	17930	17559	17500
15°	17736	17149	16967
20°	17472	16635	16247
25°	17199	16057	15543
30°	16839	15392	14551
35°	16469	14725	13641
40°	16127	13939	12513
45°	15678	13164	11496
50°	15185	12285	10357
55°	14681	11277	9295
60°	14219	10198	8129
65°	13616	9032	6963
70°	12862	7582	5624
75°	11761	5964	5294
80°	10488	5281	4866
85°	8855	4681	4347



TEST NUMBER: P332376-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.7	2.5
10°-20°	436.0	7.1
20°-30°	627.8	10.2
30°-40°	707.2	11.5
40°-50°	676.5	11.0
50°-60°	554.0	9.0
60°-70°	373.8	6.1
70°-80°	188.1	3.1
80°-90°	52.3	0.9
90°-100°	55.8	0.9
100°-110°	167.1	2.7
110°-120°	284.2	4.6
120°-130°	373.8	6.1
130°-140°	420.2	6.8
140°-150°	413.0	6.7
150°-160°	347.7	5.7
160°-170°	231.4	3.8
170°-180°	81.0	1.3
0°-30°	1220.5	19.9
0°-40°	1927.7	31.4
0°-60°	3158.3	51.4
0°-90°	3772.4	61.4
90°-120°	507.1	8.3
90°-150°	1714.1	27.9
90°-180°	2374.0	38.6
0°-180°	6146.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1669	1669	1669	1669	1669	
5°	1669	1662	1646	1657	1655	158
15°	1592	1575	1539	1532	1523	448
25°	1448	1413	1352	1324	1309	666
35°	1253	1203	1121	1064	1038	784
45°	1030	967	865	790	755	794
55°	782	713	601	525	495	701
65°	535	458	355	291	273	529
75°	283	217	143	131	127	302
85°	72	43	38	35	35	81
90°	1	8	16	19	20	6
95°	40	44	50	52	52	45
105°	151	153	159	159	160	162
115°	286	288	287	287	287	283
125°	419	421	419	417	414	373
135°	543	547	547	544	543	418
145°	659	660	662	662	659	411
155°	755	755	755	758	753	347
165°	822	820	820	824	819	232
175°	855	852	852	856	852	81
180°	857	857	857	857	857	



TEST NUMBER: P332376-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1674.2	1673.2	1672.2	1671.3	1670.3	1668.4	1665.5	1662.6	1659.7	1656.8	1659.5
5°	1668.8	1667.2	1665.8	1664.2	1662.8	1660.2	1656.6	1652.9	1649.3	1645.7	1648.5
7.5°	1653.3	1651.7	1650.1	1648.5	1646.8	1643.6	1639.0	1634.3	1629.6	1624.9	1626.4
10°	1640.4	1638.2	1636.2	1634.0	1631.9	1628.2	1622.7	1617.3	1611.9	1606.5	1606.8
12.5°	1622.0	1619.6	1617.2	1614.9	1612.6	1608.1	1601.5	1594.8	1588.2	1581.6	1581.4
15°	1591.6	1588.3	1585.0	1581.7	1578.4	1572.5	1564.1	1555.7	1547.2	1538.9	1537.3
17.5°	1553.4	1549.6	1545.8	1541.9	1538.1	1530.8	1520.1	1509.3	1498.7	1488.0	1484.8
20°	1525.3	1520.5	1515.7	1510.9	1506.1	1498.0	1486.5	1475.1	1463.6	1452.2	1448.3
22.5°	1493.9	1488.3	1482.8	1477.3	1471.8	1462.9	1450.8	1438.6	1426.5	1414.3	1409.5
25°	1448.1	1440.6	1433.1	1425.6	1418.1	1407.4	1393.5	1379.8	1365.9	1352.0	1345.7
27.5°	1392.7	1384.4	1376.1	1367.8	1359.4	1347.6	1332.2	1316.8	1301.4	1286.0	1277.2
30°	1354.8	1345.7	1336.7	1327.7	1318.7	1305.7	1288.9	1272.0	1255.3	1238.4	1228.1
32.5°	1316.9	1306.7	1296.4	1286.2	1276.0	1262.0	1244.1	1226.3	1208.5	1190.8	1179.6
35°	1253.3	1242.4	1231.6	1220.8	1210.0	1195.2	1176.6	1158.0	1139.3	1120.6	1107.7
37.5°	1188.9	1176.8	1164.8	1152.7	1140.7	1124.7	1104.8	1084.9	1065.1	1045.1	1030.4
40°	1147.7	1134.5	1121.2	1108.0	1094.8	1077.5	1056.1	1034.7	1013.4	992.0	976.4
42.5°	1101.1	1087.9	1074.7	1061.4	1048.2	1030.5	1008.5	986.4	964.3	942.3	925.1
45°	1029.9	1016.4	1002.9	989.4	975.8	957.4	934.3	911.1	887.9	864.8	847.7
47.5°	958.7	943.9	929.0	914.2	899.3	880.3	857.1	834.0	810.8	787.7	769.0
50°	906.8	892.7	878.5	864.4	850.2	831.0	806.7	782.3	757.9	733.6	714.9
52.5°	860.2	844.9	829.6	814.2	798.8	779.1	755.0	730.9	706.8	682.7	663.3
55°	782.3	767.5	752.8	738.0	723.3	703.2	677.6	652.0	626.5	600.9	583.5
57.5°	710.2	694.2	678.1	662.1	646.0	625.2	599.5	573.8	548.1	522.5	505.9
60°	660.5	643.9	627.4	610.9	594.3	573.5	548.5	523.7	498.7	473.7	457.4
62.5°	610.6	594.1	577.6	561.0	544.5	523.7	498.8	473.8	448.8	423.9	408.6
65°	534.6	518.1	501.5	485.0	468.5	448.4	425.0	401.5	378.1	354.6	339.8
67.5°	458.6	441.8	425.1	408.4	391.7	372.0	349.6	327.0	304.5	282.1	271.0
70°	408.7	392.5	376.3	360.0	343.8	325.1	304.1	283.0	262.0	240.9	230.4
72.5°	359.0	342.9	326.9	310.9	294.9	277.3	258.2	239.1	220.0	200.9	192.3
75°	282.8	268.5	254.0	239.5	225.2	209.7	193.1	176.5	160.0	143.4	140.4
77.5°	213.5	200.5	187.4	174.4	161.4	149.5	138.9	128.2	117.5	106.9	105.3
80°	169.2	156.9	144.5	132.2	119.9	110.6	104.2	97.9	91.6	85.2	84.4
82.5°	126.9	116.3	105.6	95.0	84.4	77.6	74.6	71.6	68.7	65.8	64.8
85°	71.7	65.1	58.5	51.9	45.3	41.5	40.6	39.7	38.8	37.9	37.3
87.5°	26.1	23.8	21.4	19.1	16.7	15.8	16.1	16.5	16.9	17.3	17.2
90°	0.7	2.2	3.7	5.2	6.6	8.4	10.3	12.2	14.2	16.2	16.8
92.5°	16.3	17.3	18.3	19.4	20.3	21.4	22.6	23.7	24.7	25.8	26.3
95°	39.7	40.7	41.8	42.9	43.9	45.0	46.2	47.4	48.6	49.9	50.5
97.5°	70.5	71.3	72.1	72.8	73.7	74.5	75.3	76.2	77.1	77.9	78.6
100°	91.5	92.5	93.3	94.3	95.1	96.0	96.7	97.5	98.2	98.9	99.4
102.5°	115.8	116.3	116.8	117.4	118.0	118.7	119.7	120.7	121.7	122.7	123.1
105°	151.4	151.8	152.1	152.4	152.7	153.5	154.8	156.2	157.6	158.9	158.9
107.5°	193.0	193.1	193.3	193.5	193.6	194.0	194.6	195.1	195.6	196.1	196.7
110°	218.8	219.0	219.4	219.6	220.0	220.2	220.6	220.8	221.2	221.4	222.1



TEST NUMBER: P332376-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	245.7	245.9	246.1	246.2	246.4	246.5	246.6	246.7	246.8	246.8	247.5
115°	286.1	286.5	287.0	287.4	287.9	288.0	287.7	287.4	287.1	286.8	286.9
117.5°	326.7	327.1	327.4	327.6	328.0	327.9	327.5	327.1	326.7	326.3	326.3
120°	352.1	352.9	353.9	354.7	355.7	355.8	355.0	354.2	353.5	352.8	352.6
122.5°	378.5	379.1	379.8	380.4	381.1	381.3	380.8	380.5	380.0	379.7	379.3
125°	418.7	419.1	419.6	420.1	420.5	420.6	420.3	420.0	419.7	419.4	418.8
127.5°	455.9	456.8	457.8	458.7	459.7	460.0	459.7	459.3	459.0	458.7	457.9
130°	480.6	481.8	483.0	484.2	485.4	485.8	485.3	484.9	484.5	484.0	483.4
132.5°	505.4	506.6	507.8	509.0	510.2	510.7	510.3	510.0	509.6	509.3	508.6
135°	543.2	544.2	545.0	546.0	546.8	547.3	547.1	546.9	546.7	546.6	546.0
137.5°	578.2	579.0	579.7	580.5	581.3	581.8	582.2	582.6	583.0	583.3	582.7
140°	602.4	603.2	604.0	604.8	605.5	605.9	606.1	606.2	606.4	606.5	606.4
142.5°	624.6	625.3	626.0	626.8	627.6	628.1	628.4	628.6	628.9	629.1	629.0
145°	659.0	659.4	659.6	660.0	660.2	660.6	661.1	661.5	661.9	662.4	662.3
147.5°	689.2	689.7	690.3	690.8	691.4	691.8	692.2	692.7	693.1	693.5	693.5
150°	710.2	710.5	710.8	711.1	711.4	711.7	712.0	712.3	712.6	712.9	712.9
152.5°	727.5	727.8	728.2	728.7	729.1	729.4	729.6	729.8	730.0	730.1	730.4
155°	754.6	754.6	754.6	754.6	754.6	754.7	754.8	755.0	755.2	755.3	755.9
157.5°	777.7	777.6	777.4	777.2	777.1	777.1	777.1	777.3	777.4	777.5	778.2
160°	792.3	792.0	791.7	791.4	791.1	791.0	791.0	791.0	791.0	791.0	791.7
162.5°	805.2	804.9	804.4	804.0	803.6	803.4	803.6	803.7	803.7	803.9	804.6
165°	821.9	821.5	821.0	820.6	820.1	819.9	819.9	819.9	819.9	819.9	820.8
167.5°	835.3	834.7	834.1	833.4	832.8	832.7	832.8	832.8	833.0	833.1	834.1
170°	842.8	842.2	841.6	841.0	840.4	840.1	840.1	840.1	840.1	840.1	841.2
172.5°	848.7	848.2	847.6	847.0	846.4	846.0	846.0	846.0	846.0	846.0	847.0
175°	854.9	854.3	853.8	853.2	852.6	852.2	852.2	852.2	852.2	852.2	853.2
177.5°	857.5	857.0	856.5	856.0	855.6	855.3	855.3	855.3	855.3	855.3	856.0
180°	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0



TEST NUMBER: P332376-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1662.2	1664.8	1667.4	1668.5	1668.0	1667.6	1667.1	1666.6
5°	1651.1	1653.9	1656.6	1657.6	1657.0	1656.4	1655.8	1655.2
7.5°	1627.9	1629.4	1630.9	1631.2	1630.1	1629.1	1628.1	1627.0
10°	1607.1	1607.4	1607.7	1607.1	1605.6	1604.1	1602.6	1601.1
12.5°	1581.2	1581.1	1580.9	1579.9	1578.2	1576.4	1574.7	1573.0
15°	1535.9	1534.3	1532.8	1531.0	1528.9	1526.8	1524.7	1522.6
17.5°	1481.6	1478.3	1475.2	1472.1	1468.9	1465.8	1462.7	1459.5
20°	1444.4	1440.5	1436.6	1432.8	1429.2	1425.6	1422.0	1418.4
22.5°	1404.5	1399.7	1394.8	1390.7	1387.3	1384.0	1380.6	1377.3
25°	1339.5	1333.1	1326.8	1322.0	1318.7	1315.3	1312.1	1308.7
27.5°	1268.4	1259.6	1250.9	1244.0	1238.9	1233.9	1228.8	1223.7
30°	1217.9	1207.7	1197.5	1190.0	1185.2	1180.3	1175.5	1170.7
32.5°	1168.4	1157.2	1146.0	1137.9	1132.8	1127.7	1122.7	1117.7
35°	1094.8	1081.8	1068.9	1059.7	1054.3	1048.9	1043.4	1038.1
37.5°	1015.7	1001.1	986.4	975.7	969.1	962.3	955.7	949.0
40°	960.8	945.1	929.5	918.3	911.3	904.4	897.5	890.5
42.5°	908.1	891.0	873.9	862.3	856.1	849.9	843.7	837.5
45°	830.5	813.4	796.3	784.1	776.9	769.6	762.4	755.2
47.5°	750.4	731.8	713.1	700.6	694.1	687.7	681.2	674.9
50°	696.3	677.6	658.9	646.2	639.3	632.3	625.4	618.5
52.5°	643.9	624.6	605.2	592.4	586.2	580.1	573.9	567.7
55°	566.0	548.5	531.2	519.4	513.4	507.4	501.4	495.3
57.5°	489.5	472.9	456.5	445.7	440.6	435.5	430.3	425.2
60°	441.2	425.0	408.7	398.0	393.0	387.8	382.7	377.6
62.5°	393.3	378.1	362.7	352.5	347.1	341.7	336.4	331.1
65°	325.1	310.4	295.7	286.6	283.4	280.0	276.7	273.4
67.5°	260.0	249.0	238.0	230.7	227.2	223.6	220.1	216.5
70°	219.8	209.3	198.8	191.9	188.6	185.3	181.9	178.7
72.5°	183.7	175.0	166.4	161.4	160.1	158.7	157.3	155.9
75°	137.4	134.4	131.4	129.7	129.1	128.5	127.9	127.3
77.5°	103.7	102.0	100.4	99.3	98.7	98.1	97.5	96.9
80°	83.4	82.6	81.6	80.9	80.3	79.7	79.1	78.5
82.5°	64.0	63.1	62.2	61.6	61.6	61.4	61.3	61.2
85°	36.7	36.1	35.5	35.2	35.2	35.2	35.2	35.2
87.5°	17.0	17.0	16.8	16.7	16.5	16.3	16.1	15.9
90°	17.4	17.9	18.5	19.0	19.3	19.6	19.9	20.2
92.5°	26.8	27.3	27.7	27.9	27.7	27.6	27.4	27.2
95°	51.0	51.6	52.2	52.5	52.5	52.5	52.5	52.5
97.5°	79.3	80.0	80.7	81.0	80.9	80.9	80.8	80.8
100°	99.9	100.3	100.7	101.2	101.4	101.7	102.0	102.3
102.5°	123.6	124.0	124.4	124.7	124.6	124.5	124.5	124.4
105°	158.9	158.9	158.9	159.0	159.3	159.6	159.9	160.2
107.5°	197.1	197.6	198.1	198.2	198.0	197.9	197.7	197.5
110°	222.7	223.3	223.9	224.0	223.7	223.4	223.1	222.8





TEST NUMBER: P332376-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	248.2	248.9	249.7	249.9	249.9	249.9	249.8	249.8
115°	287.1	287.2	287.4	287.4	287.2	287.1	286.9	286.8
117.5°	326.3	326.2	326.2	326.0	325.6	325.2	324.8	324.3
120°	352.4	352.3	352.1	351.9	351.6	351.3	351.0	350.7
122.5°	378.9	378.5	378.2	377.7	377.3	376.9	376.4	376.0
125°	418.2	417.6	417.0	416.4	415.8	415.2	414.6	414.0
127.5°	457.0	456.2	455.4	454.6	453.9	453.2	452.5	451.9
130°	482.8	482.2	481.6	480.8	479.7	478.7	477.7	476.6
132.5°	507.9	507.1	506.4	505.7	504.9	504.0	503.3	502.5
135°	545.4	544.8	544.2	543.8	543.5	543.2	542.9	542.6
137.5°	582.1	581.5	580.8	580.2	579.7	579.1	578.6	578.0
140°	606.2	606.1	605.9	605.4	604.2	603.2	602.2	601.2
142.5°	628.9	628.7	628.5	628.1	627.2	626.5	625.6	624.8
145°	662.1	661.9	661.8	661.4	660.8	660.2	659.6	659.0
147.5°	693.5	693.5	693.5	693.0	692.2	691.2	690.3	689.5
150°	712.9	712.9	712.9	712.5	711.5	710.7	709.7	708.9
152.5°	730.6	730.8	731.1	730.8	730.0	729.3	728.5	727.7
155°	756.5	757.1	757.7	757.4	756.4	755.4	754.3	753.3
157.5°	778.8	779.4	780.0	779.9	779.1	778.3	777.4	776.5
160°	792.5	793.2	793.9	794.0	793.4	792.8	792.2	791.6
162.5°	805.4	806.2	806.9	806.8	805.8	804.9	803.9	803.0
165°	821.7	822.6	823.5	823.5	822.4	821.3	820.3	819.2
167.5°	835.0	835.9	836.8	836.8	835.9	835.0	834.1	833.1
170°	842.2	843.3	844.3	844.3	843.3	842.2	841.2	840.1
172.5°	847.9	848.9	849.7	849.7	848.6	847.6	846.5	845.5
175°	854.0	854.9	855.8	855.7	854.7	853.7	852.6	851.5
177.5°	856.8	857.5	858.2	858.2	857.3	856.4	855.7	854.8
180°	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0

(END OF REPORT)