

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332286-930

Luminaire Tested: **S123RDIP-S560D805U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332286-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D805U930-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3990.3 lumens  
Efficiency: N/A  
Efficacy: 103.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332286-930

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332286-930

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37	32
3	81	71	64	59	74	66	60	55	55	50	47	45	42	39	36	33	31	27
4	74	63	56	50	67	58	52	46	49	44	40	40	36	34	32	29	27	24
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	26	23	21	18
7	58	46	38	33	53	42	36	31	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	18	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8289	8289	8289
5°	8321	8206	8253
10°	8273	8103	8075
15°	8184	7913	7830
20°	8062	7676	7497
25°	7936	7410	7172
30°	7771	7102	6714
35°	7599	6795	6294
40°	7442	6433	5774
45°	7234	6075	5305
50°	7006	5668	4779
55°	6775	5204	4290
60°	6562	4706	3750
65°	6283	4167	3212
70°	5936	3500	2593
75°	5427	2753	2441
80°	4841	2442	2244
85°	4088	2149	2001



TEST NUMBER: P332286-930

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.3	1.8
10°-20°	201.2	5.0
20°-30°	289.7	7.3
30°-40°	326.3	8.2
40°-50°	312.2	7.8
50°-60°	255.7	6.4
60°-70°	172.5	4.3
70°-80°	86.8	2.2
80°-90°	25.4	0.6
90°-100°	52.9	1.3
100°-110°	158.2	4.0
110°-120°	269.1	6.7
120°-130°	354.0	8.9
130°-140°	397.9	10.0
140°-150°	391.1	9.8
150°-160°	329.2	8.3
160°-170°	219.2	5.5
170°-180°	76.7	1.9
0°-30°	563.2	14.1
0°-40°	889.5	22.3
0°-60°	1457.4	36.5
0°-90°	1742.0	43.7
90°-120°	480.2	12.0
90°-150°	1623.1	40.7
90°-180°	2248.0	56.3
0°-180°	3990.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	770	770	770	770	770	
5°	770	767	760	765	764	73
15°	734	727	710	707	703	207
25°	668	652	624	611	604	307
35°	578	555	517	491	479	362
45°	475	446	399	365	348	367
55°	361	329	277	242	229	324
65°	247	212	164	134	126	244
75°	130	100	66	60	59	139
85°	33	20	17	16	16	37
90°	1	7	15	18	19	4
95°	38	42	47	50	50	42
105°	143	145	150	150	152	154
115°	271	273	272	272	272	268
125°	396	398	397	395	392	353
135°	514	518	518	515	514	396
145°	624	625	627	626	624	390
155°	714	715	715	717	713	329
165°	778	776	776	780	776	219
175°	810	807	807	810	806	77
180°	812	812	812	812	812	



TEST NUMBER: P332286-930

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	772.6	772.1	771.7	771.2	770.8	769.9	768.6	767.2	765.9	764.6	765.8
5°	770.1	769.4	768.7	768.0	767.3	766.1	764.4	762.8	761.1	759.5	760.7
7.5°	763.0	762.2	761.4	760.7	759.9	758.5	756.4	754.2	752.0	749.8	750.5
10°	756.9	755.9	755.0	754.0	753.1	751.3	748.9	746.3	743.8	741.4	741.4
12.5°	748.4	747.4	746.2	745.2	744.1	742.1	739.0	736.0	732.9	729.9	729.8
15°	734.4	733.0	731.4	729.9	728.4	725.6	721.8	717.9	714.0	710.1	709.4
17.5°	716.8	715.1	713.3	711.5	709.7	706.4	701.4	696.5	691.5	686.6	685.2
20°	703.8	701.6	699.4	697.2	695.0	691.2	685.9	680.7	675.4	670.1	668.3
22.5°	689.3	686.8	684.3	681.7	679.1	675.1	669.4	663.8	658.3	652.6	650.4
25°	668.2	664.8	661.3	657.9	654.4	649.5	643.0	636.7	630.3	623.9	621.0
27.5°	642.6	638.8	635.0	631.1	627.3	621.8	614.7	607.6	600.5	593.5	589.4
30°	625.2	621.0	616.9	612.7	608.5	602.5	594.8	587.0	579.2	571.4	566.7
32.5°	607.6	603.0	598.3	593.5	588.8	582.4	574.1	565.9	557.7	549.4	544.3
35°	578.3	573.3	568.3	563.4	558.3	551.5	542.9	534.3	525.7	517.1	511.1
37.5°	548.6	543.1	537.5	531.9	526.4	519.0	509.8	500.7	491.5	482.2	475.5
40°	529.6	523.5	517.4	511.3	505.2	497.2	487.4	477.5	467.7	457.8	450.5
42.5°	508.1	502.0	495.9	489.8	483.7	475.6	465.4	455.2	445.0	434.8	426.9
45°	475.2	469.0	462.8	456.6	450.3	441.8	431.1	420.4	409.8	399.1	391.2
47.5°	442.4	435.5	428.7	421.8	415.0	406.3	395.5	384.8	374.1	363.5	354.9
50°	418.4	411.9	405.4	398.8	392.3	383.4	372.2	361.0	349.8	338.5	329.9
52.5°	397.0	389.9	382.8	375.7	368.7	359.5	348.4	337.3	326.1	315.0	306.1
55°	361.0	354.2	347.4	340.6	333.8	324.5	312.7	300.9	289.1	277.3	269.2
57.5°	327.8	320.3	312.9	305.5	298.1	288.5	276.6	264.8	252.9	241.1	233.5
60°	304.8	297.2	289.5	281.8	274.3	264.6	253.2	241.7	230.1	218.6	211.1
62.5°	281.8	274.2	266.5	258.9	251.3	241.7	230.2	218.7	207.1	195.6	188.6
65°	246.7	239.0	231.5	223.8	216.1	206.9	196.1	185.3	174.5	163.6	156.9
67.5°	211.6	203.9	196.2	188.4	180.8	171.7	161.3	150.9	140.6	130.1	125.1
70°	188.6	181.1	173.7	166.2	158.7	150.0	140.3	130.6	120.9	111.2	106.3
72.5°	165.6	158.2	150.8	143.5	136.1	128.0	119.2	110.3	101.5	92.7	88.7
75°	130.5	123.8	117.2	110.6	103.9	96.7	89.1	81.4	73.9	66.2	64.8
77.5°	98.6	92.5	86.5	80.5	74.4	69.0	64.1	59.2	54.2	49.3	48.6
80°	78.1	72.4	66.7	61.0	55.3	51.0	48.1	45.2	42.2	39.4	38.9
82.5°	58.6	53.6	48.8	43.9	38.9	35.8	34.4	33.1	31.7	30.3	29.9
85°	33.1	30.1	27.0	24.0	20.9	19.2	18.8	18.3	17.9	17.4	17.2
87.5°	12.1	11.2	10.3	9.3	8.4	8.1	8.5	8.8	9.2	9.5	9.5
90°	0.7	2.0	3.5	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9
92.5°	15.4	16.4	17.4	18.3	19.2	20.3	21.4	22.4	23.4	24.5	24.9
95°	37.6	38.6	39.6	40.6	41.6	42.6	43.8	44.9	46.1	47.2	47.8
97.5°	66.8	67.5	68.2	69.0	69.8	70.5	71.3	72.2	73.0	73.8	74.4
100°	86.7	87.6	88.4	89.3	90.1	90.9	91.6	92.3	93.0	93.7	94.2
102.5°	109.7	110.1	110.6	111.2	111.7	112.4	113.3	114.3	115.2	116.2	116.6
105°	143.4	143.7	144.0	144.3	144.6	145.4	146.6	147.9	149.2	150.4	150.4
107.5°	182.7	182.9	183.0	183.2	183.4	183.7	184.3	184.7	185.2	185.7	186.2
110°	207.2	207.4	207.7	208.0	208.3	208.6	208.9	209.1	209.5	209.7	210.3



TEST NUMBER: P332286-930

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	232.7	232.8	233.0	233.2	233.3	233.4	233.5	233.6	233.7	233.7	234.4
115°	270.9	271.3	271.7	272.1	272.6	272.7	272.4	272.1	271.8	271.6	271.7
117.5°	309.4	309.7	310.0	310.2	310.5	310.5	310.1	309.7	309.4	309.0	309.0
120°	333.4	334.2	335.1	335.9	336.8	336.9	336.1	335.4	334.8	334.0	333.9
122.5°	358.4	359.0	359.6	360.2	360.9	361.0	360.6	360.3	359.9	359.5	359.1
125°	396.5	396.9	397.3	397.8	398.2	398.3	397.9	397.7	397.4	397.1	396.6
127.5°	431.7	432.6	433.5	434.4	435.3	435.6	435.3	435.0	434.6	434.3	433.6
130°	455.1	456.2	457.4	458.5	459.7	460.0	459.6	459.2	458.8	458.3	457.7
132.5°	478.6	479.7	480.9	482.0	483.1	483.6	483.2	482.9	482.6	482.2	481.6
135°	514.4	515.3	516.1	517.0	517.8	518.2	518.0	517.9	517.7	517.6	517.1
137.5°	547.6	548.3	548.9	549.7	550.4	550.9	551.3	551.6	552.0	552.4	551.8
140°	570.5	571.2	571.9	572.7	573.3	573.7	573.9	574.1	574.2	574.3	574.2
142.5°	591.4	592.2	592.8	593.5	594.3	594.8	595.0	595.3	595.5	595.7	595.6
145°	624.0	624.4	624.6	624.9	625.2	625.5	626.0	626.4	626.8	627.2	627.1
147.5°	652.6	653.1	653.6	654.1	654.7	655.1	655.5	655.9	656.3	656.7	656.7
150°	672.5	672.8	673.0	673.4	673.6	673.9	674.2	674.5	674.7	675.1	675.1
152.5°	688.8	689.2	689.6	690.0	690.4	690.7	690.9	691.0	691.2	691.4	691.6
155°	714.5	714.5	714.5	714.5	714.5	714.6	714.8	714.9	715.1	715.2	715.8
157.5°	736.5	736.3	736.1	736.0	735.8	735.8	735.9	736.1	736.1	736.2	736.9
160°	750.2	750.0	749.7	749.4	749.1	749.0	749.0	749.0	749.0	749.0	749.7
162.5°	762.5	762.1	761.7	761.3	760.9	760.8	760.9	761.0	761.1	761.2	761.9
165°	778.3	777.9	777.5	777.1	776.6	776.4	776.4	776.4	776.4	776.4	777.2
167.5°	790.9	790.4	789.8	789.2	788.6	788.5	788.6	788.6	788.8	788.9	789.8
170°	798.1	797.5	797.0	796.4	795.8	795.5	795.5	795.5	795.5	795.5	796.5
172.5°	803.6	803.2	802.6	802.0	801.4	801.1	801.1	801.1	801.1	801.1	802.0
175°	809.5	808.9	808.5	807.9	807.3	807.0	807.0	807.0	807.0	807.0	807.9
177.5°	812.0	811.5	811.1	810.6	810.2	809.9	809.9	809.9	809.9	809.9	810.6
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332286-930

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	767.0	768.3	769.5	770.0	769.7	769.5	769.3	769.1
5°	761.9	763.2	764.4	764.9	764.7	764.3	764.1	763.8
7.5°	751.2	751.9	752.6	752.7	752.2	751.8	751.3	750.8
10°	741.6	741.8	741.8	741.6	740.9	740.2	739.6	738.8
12.5°	729.7	729.6	729.5	729.0	728.2	727.4	726.7	725.9
15°	708.7	708.0	707.4	706.5	705.5	704.6	703.6	702.6
17.5°	683.7	682.2	680.7	679.3	677.8	676.4	674.9	673.5
20°	666.5	664.7	662.9	661.2	659.5	657.9	656.2	654.5
22.5°	648.2	645.9	643.7	641.7	640.2	638.6	637.1	635.5
25°	618.1	615.1	612.3	610.0	608.5	607.0	605.4	603.9
27.5°	585.3	581.3	577.2	574.1	571.7	569.4	567.0	564.7
30°	562.0	557.3	552.6	549.1	546.9	544.7	542.4	540.2
32.5°	539.2	533.9	528.8	525.1	522.8	520.4	518.0	515.8
35°	505.2	499.2	493.3	489.0	486.5	484.0	481.5	479.0
37.5°	468.7	461.9	455.2	450.3	447.2	444.1	441.0	437.9
40°	443.4	436.1	428.9	423.7	420.5	417.4	414.2	410.9
42.5°	419.1	411.2	403.2	397.9	395.0	392.2	389.3	386.5
45°	383.3	375.4	367.5	361.8	358.5	355.1	351.8	348.5
47.5°	346.3	337.7	329.1	323.3	320.3	317.3	314.4	311.4
50°	321.3	312.7	304.1	298.2	295.0	291.8	288.6	285.4
52.5°	297.2	288.2	279.2	273.4	270.5	267.7	264.8	262.0
55°	261.2	253.2	245.1	239.7	236.9	234.2	231.4	228.6
57.5°	225.8	218.3	210.7	205.7	203.3	201.0	198.6	196.2
60°	203.6	196.1	188.6	183.7	181.3	179.0	176.6	174.2
62.5°	181.5	174.5	167.4	162.7	160.2	157.7	155.2	152.8
65°	150.0	143.2	136.4	132.2	130.8	129.2	127.7	126.1
67.5°	120.0	114.9	109.8	106.5	104.8	103.2	101.6	100.0
70°	101.4	96.6	91.7	88.5	87.0	85.5	84.0	82.4
72.5°	84.7	80.8	76.8	74.5	73.9	73.2	72.6	71.9
75°	63.4	62.0	60.7	59.8	59.5	59.3	58.9	58.7
77.5°	47.9	47.1	46.3	45.8	45.6	45.2	45.0	44.7
80°	38.5	38.1	37.7	37.3	37.1	36.8	36.5	36.2
82.5°	29.5	29.1	28.7	28.5	28.4	28.4	28.3	28.2
85°	17.0	16.6	16.4	16.2	16.2	16.2	16.2	16.2
87.5°	9.5	9.5	9.5	9.5	9.5	9.5	9.4	9.3
90°	16.5	17.0	17.5	18.0	18.3	18.6	18.8	19.2
92.5°	25.4	25.8	26.3	26.4	26.3	26.1	25.9	25.8
95°	48.3	48.8	49.4	49.7	49.7	49.7	49.7	49.7
97.5°	75.1	75.7	76.4	76.7	76.6	76.6	76.6	76.5
100°	94.6	95.0	95.4	95.8	96.0	96.3	96.6	96.9
102.5°	117.0	117.4	117.8	118.1	118.0	117.9	117.9	117.8
105°	150.4	150.4	150.4	150.6	150.8	151.2	151.4	151.7
107.5°	186.6	187.1	187.6	187.7	187.5	187.4	187.2	187.0
110°	210.8	211.4	212.0	212.1	211.8	211.6	211.2	211.0





TEST NUMBER: P332286-930

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.1	235.7	236.4	236.7	236.7	236.6	236.5	236.5
115°	271.8	272.0	272.1	272.1	272.0	271.8	271.7	271.6
117.5°	309.0	308.9	308.9	308.7	308.3	307.9	307.5	307.1
120°	333.7	333.6	333.5	333.2	333.0	332.6	332.4	332.1
122.5°	358.8	358.4	358.1	357.7	357.3	356.9	356.4	356.0
125°	396.0	395.4	394.8	394.3	393.7	393.1	392.6	392.0
127.5°	432.8	431.9	431.2	430.5	429.8	429.2	428.5	427.9
130°	457.2	456.6	456.1	455.3	454.3	453.3	452.3	451.3
132.5°	480.9	480.2	479.6	478.8	478.1	477.3	476.5	475.8
135°	516.5	515.9	515.4	514.9	514.6	514.4	514.0	513.8
137.5°	551.2	550.7	550.0	549.4	548.9	548.4	547.9	547.3
140°	574.1	573.9	573.7	573.2	572.2	571.2	570.2	569.2
142.5°	595.5	595.3	595.2	594.8	593.9	593.2	592.4	591.7
145°	627.0	626.8	626.6	626.3	625.7	625.2	624.6	624.0
147.5°	656.7	656.7	656.7	656.2	655.4	654.5	653.7	652.9
150°	675.1	675.1	675.1	674.7	673.8	672.9	672.1	671.2
152.5°	691.8	692.0	692.3	692.0	691.3	690.6	689.8	689.1
155°	716.3	716.9	717.5	717.2	716.2	715.3	714.3	713.3
157.5°	737.4	738.0	738.6	738.5	737.8	736.9	736.1	735.3
160°	750.4	751.1	751.8	751.9	751.3	750.7	750.2	749.6
162.5°	762.6	763.4	764.1	763.9	763.0	762.1	761.2	760.3
165°	778.1	778.9	779.8	779.8	778.8	777.7	776.7	775.8
167.5°	790.7	791.5	792.4	792.4	791.5	790.7	789.8	788.9
170°	797.5	798.5	799.5	799.5	798.5	797.5	796.5	795.5
172.5°	802.9	803.8	804.6	804.6	803.6	802.6	801.6	800.6
175°	808.7	809.5	810.4	810.3	809.3	808.4	807.3	806.3
177.5°	811.3	812.0	812.6	812.6	811.8	811.0	810.2	809.4
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5

(END OF REPORT)