

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832293

Luminaire Tested: S123RDIP-S560D805U930-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832293
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D805U930-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4591.3 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 40.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832293

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P832293

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43				
1	97	93	89	86	88	85	82	79	71	68	67	57	56	55	45	44	43	38				
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	40	39	38	33				
3	82	73	66	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29				
4	75	65	57	52	68	60	53	48	50	46	42	41	38	35	33	31	29	25				
5	69	58	51	45	63	54	47	42	45	40	37	38	34	31	30	28	26	23				
6	64	53	45	39	59	49	42	37	41	36	32	34	31	28	28	25	23	20				
7	59	48	40	35	54	44	38	33	38	33	29	32	28	25	26	23	21	18				
8	55	44	36	31	51	41	34	30	35	30	26	29	25	23	24	21	19	17				
9	52	40	33	28	47	37	31	27	32	27	24	27	23	21	22	20	18	16				
10	48	37	30	25	44	34	28	24	30	25	22	25	22	19	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	16027	16027	16027	16027	16027
5°	19031	18425	16129	13038	12105
10°	17243	18714	16048	10447	8961
15°	11871	16046	15879	8538	7090
20°	8259	12354	15560	7199	6231
25°	6293	9415	15096	6399	5742
30°	5479	7527	14516	5941	5320
35°	5030	6349	13694	5556	4934
40°	4589	5670	12619	5176	4581
45°	4145	5186	11459	4818	4229
50°	3763	4784	10091	4468	3793
55°	3402	4393	8777	4125	3254
60°	3048	3996	7623	3746	3076
65°	2814	3545	6561	3367	2909
70°	2288	3065	5725	3046	2364
75°	2005	2437	4849	2524	2084
80°	1816	2064	3973	2120	1965
85°	1655	1815	3013	1927	1815

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 12091 cd/sqm



TEST NUMBER: P832293

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.7	3.0
10°-20°	314.1	6.8
20°-30°	360.3	7.8
30°-40°	355.2	7.7
40°-50°	313.2	6.8
50°-60°	241.0	5.2
60°-70°	158.4	3.5
70°-80°	76.9	1.7
80°-90°	21.1	0.5
90°-100°	30.2	0.7
100°-110°	146.2	3.2
110°-120°	358.4	7.8
120°-130°	455.0	9.9
130°-140°	486.1	10.6
140°-150°	454.6	9.9
150°-160°	366.6	8.0
160°-170°	236.6	5.2
170°-180°	81.5	1.8
0°-30°	810.1	17.6
0°-40°	1165.3	25.4
0°-60°	1719.5	37.5
0°-90°	1975.9	43.0
90°-120°	534.9	11.6
90°-150°	1930.6	42.0
90°-180°	2615.0	57.0
0°-180°	4591.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1489	1489	1489	1489	1489	
5°	1761	1705	1493	1207	1120	161
15°	1065	1440	1425	766	636	301
25°	530	793	1271	539	484	250
35°	383	483	1042	423	376	239
45°	272	341	753	316	278	211
55°	181	234	468	220	173	163
65°	110	139	258	132	114	108
75°	48	59	117	61	50	52
85°	13	15	24	16	15	14
90°	19	15	1	15	19	9
95°	24	20	39	20	24	20
105°	28	140	190	140	28	58
115°	375	366	356	366	375	353
125°	512	510	502	510	512	458
135°	632	632	625	632	632	487
145°	728	727	722	727	728	455
155°	794	794	795	794	794	366
165°	836	836	838	836	836	236
175°	855	855	858	855	855	81
180°	858	858	858	858	858	



TEST NUMBER: P832293

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0
2.5°	1650.2	1645.0	1639.8	1638.3	1636.8	1631.9	1627.0	1616.0	1605.0	1593.7	1582.4
5°	1761.3	1761.9	1762.5	1761.0	1759.5	1753.1	1746.7	1733.2	1719.8	1705.2	1690.5
7.5°	1727.1	1736.9	1746.7	1748.5	1750.3	1755.2	1760.1	1757.0	1754.0	1748.5	1743.0
10°	1577.6	1576.9	1576.3	1587.3	1598.3	1631.0	1663.6	1680.4	1697.2	1712.2	1727.1
12.5°	1333.4	1334.3	1335.2	1371.2	1407.2	1438.1	1468.9	1511.6	1554.4	1600.5	1646.5
15°	1065.3	1080.3	1095.3	1127.3	1159.4	1205.8	1252.2	1309.5	1366.9	1439.9	1512.8
17.5°	874.9	881.3	887.7	918.5	949.3	993.3	1037.3	1102.3	1167.3	1261.3	1355.3
20°	721.0	726.8	732.6	754.9	777.2	819.3	861.4	923.4	985.4	1078.5	1171.6
22.5°	602.0	613.3	624.6	639.5	654.5	685.0	715.5	778.7	841.9	926.8	1011.6
25°	529.9	535.1	540.3	553.1	565.9	595.2	624.6	666.4	708.2	792.7	877.3
27.5°	481.1	482.6	484.1	493.6	503.1	522.0	540.9	579.7	618.4	688.0	757.6
30°	440.8	443.5	446.3	453.6	460.9	474.7	488.4	515.9	543.4	605.6	667.9
32.5°	409.7	411.2	412.7	418.8	424.9	435.0	445.1	466.7	488.4	536.0	583.6
35°	382.8	383.1	383.4	388.0	392.6	402.3	412.1	430.1	448.1	483.2	518.3
37.5°	352.3	354.4	356.5	359.9	363.3	371.8	380.3	395.0	409.7	438.7	467.7
40°	326.6	328.5	330.3	334.3	338.2	344.9	351.7	365.1	378.5	403.5	428.6
42.5°	301.0	302.2	303.4	307.4	311.4	319.6	327.8	338.5	349.2	370.0	390.7
45°	272.3	275.3	278.4	282.7	286.9	294.0	301.0	312.0	323.0	340.7	358.4
47.5°	248.5	250.0	251.5	255.2	258.9	267.4	276.0	285.7	295.5	312.0	328.5
50°	224.7	225.3	225.9	229.2	232.6	240.2	247.9	259.2	270.5	285.7	301.0
52.5°	202.1	203.6	205.1	208.5	211.8	217.0	222.2	233.8	245.4	260.4	275.3
55°	181.3	182.2	183.2	185.6	188.0	194.1	200.2	210.3	220.4	234.1	247.9
57.5°	161.8	163.0	164.2	166.1	167.9	173.4	178.9	187.7	196.6	210.3	224.1
60°	141.6	143.2	144.7	146.8	149.0	153.2	157.5	165.4	173.4	185.6	197.8
62.5°	127.0	127.3	127.6	129.4	131.3	134.3	137.4	143.8	150.2	162.4	174.6
65°	110.5	111.4	112.3	113.2	114.2	116.6	119.0	124.5	130.0	139.2	148.4
67.5°	93.4	94.3	95.2	96.8	98.3	100.4	102.6	106.2	109.9	118.4	127.0
70°	72.7	72.7	72.7	75.1	77.5	81.2	84.9	87.6	90.4	97.4	104.4
72.5°	59.2	59.5	59.8	60.1	60.4	62.6	64.7	69.3	73.9	78.1	82.4
75°	48.2	48.5	48.8	49.1	49.5	50.1	50.7	52.2	53.7	58.6	63.5
77.5°	38.5	38.8	39.1	39.4	39.7	40.3	40.9	41.5	42.1	44.0	45.8
80°	29.3	29.6	29.9	30.2	30.5	30.8	31.1	31.7	32.4	33.3	34.2
82.5°	21.4	21.4	21.4	21.4	21.4	22.0	22.6	22.6	22.6	23.2	23.8
85°	13.4	13.4	13.4	13.7	14.0	14.0	14.0	14.3	14.7	14.7	14.7
87.5°	6.1	5.8	5.5	5.8	6.1	6.1	6.1	6.4	6.7	6.7	6.7
90°	19.1	18.8	18.6	18.3	18.0	17.6	17.0	16.4	15.9	15.3	13.5
92.5°	21.7	21.5	21.4	21.2	21.1	20.5	19.5	18.6	17.6	16.6	15.3
95°	24.2	24.2	24.2	24.2	24.2	23.7	22.7	21.7	20.8	19.8	18.2
97.5°	26.1	26.0	25.8	25.7	25.6	24.9	23.8	22.7	21.5	20.4	27.6
100°	26.8	26.6	26.5	26.3	26.2	25.6	24.4	23.3	22.2	21.0	43.1
102.5°	27.4	27.1	26.8	26.6	26.3	28.5	33.1	37.8	42.5	47.2	71.8
105°	28.0	27.8	27.5	27.2	26.9	39.3	64.4	89.4	114.5	139.6	152.3
107.5°	66.3	84.8	103.4	122.0	140.5	160.7	182.5	204.3	226.1	247.9	245.8
110°	175.3	195.5	215.8	236.0	256.3	268.8	273.4	278.1	282.8	287.5	285.9



TEST NUMBER: P832293

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	332.1	332.4	332.6	332.9	333.2	332.7	331.4	330.2	328.9	327.6	326.1
115°	374.8	374.2	373.7	373.1	372.5	371.5	370.1	368.7	367.3	365.9	364.6
117.5°	409.2	409.1	408.9	408.8	408.6	408.0	406.9	405.7	404.6	403.5	402.8
120°	444.9	444.9	444.9	444.9	444.9	444.3	443.2	442.1	440.9	439.8	439.4
122.5°	480.0	479.8	479.7	479.5	479.4	479.0	478.3	477.6	476.8	476.1	475.6
125°	512.5	512.2	511.9	511.6	511.3	511.0	510.8	510.5	510.2	509.9	509.3
127.5°	544.3	544.6	544.9	545.2	545.5	545.4	545.0	544.5	544.1	543.7	543.0
130°	574.9	575.2	575.5	575.8	576.1	575.9	575.4	574.8	574.2	573.7	573.1
132.5°	603.0	603.4	603.8	604.3	604.7	604.6	604.0	603.5	602.9	602.3	601.9
135°	631.7	632.1	632.5	632.9	633.4	633.4	632.9	632.5	632.1	631.7	631.1
137.5°	659.1	659.4	659.6	659.9	660.2	660.0	659.3	658.6	657.9	657.2	656.9
140°	683.3	683.6	683.9	684.1	684.4	684.3	683.7	683.1	682.6	682.0	681.6
142.5°	705.6	706.0	706.4	706.9	707.3	707.3	706.9	706.4	706.0	705.6	705.2
145°	728.5	728.5	728.5	728.5	728.5	728.4	728.1	727.8	727.6	727.3	727.0
147.5°	745.1	745.8	746.5	747.2	747.9	748.2	747.9	747.6	747.3	747.0	746.7
150°	764.2	764.7	765.1	765.5	765.9	766.0	765.7	765.4	765.2	764.9	764.6
152.5°	779.5	780.2	781.0	781.7	782.4	782.4	781.9	781.3	780.7	780.2	780.0
155°	793.6	794.4	795.3	796.1	797.0	797.0	796.3	795.6	794.9	794.2	794.1
157.5°	805.7	806.8	807.9	809.1	810.2	810.3	809.5	808.6	807.8	806.9	807.1
160°	817.1	818.1	819.1	820.1	821.1	821.2	820.3	819.5	818.6	817.8	817.9
162.5°	828.0	828.8	829.7	830.5	831.4	831.3	830.3	829.3	828.3	827.3	827.5
165°	836.3	837.3	838.2	839.2	840.2	840.2	839.0	837.9	836.8	835.6	835.8
167.5°	842.6	843.8	844.9	846.0	847.2	847.2	846.0	844.9	843.8	842.6	842.6
170°	848.4	849.5	850.6	851.8	852.9	852.9	851.8	850.6	849.5	848.4	848.4
172.5°	851.6	852.8	854.1	855.4	856.7	856.7	855.6	854.5	853.3	852.2	852.1
175°	854.7	855.9	857.0	858.1	859.3	859.4	858.4	857.4	856.4	855.4	855.2
177.5°	855.4	856.8	858.2	859.6	861.1	861.2	860.1	858.9	857.8	856.7	856.5
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P832293

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0
2.5°	1580.9	1579.4	1564.7	1550.1	1535.7	1521.4	1510.7	1500.0	1482.0	1464.0	1452.7
5°	1678.9	1667.3	1644.1	1620.9	1586.1	1551.3	1522.0	1492.7	1455.5	1418.2	1387.1
7.5°	1733.5	1724.1	1696.0	1667.9	1621.8	1575.7	1529.9	1484.1	1429.2	1374.3	1327.2
10°	1735.1	1743.0	1719.8	1696.6	1644.7	1592.8	1530.5	1468.3	1394.4	1320.5	1259.8
12.5°	1680.7	1714.9	1710.0	1705.2	1652.3	1599.5	1523.8	1448.1	1357.5	1266.8	1190.8
15°	1579.1	1645.3	1664.9	1684.4	1640.7	1597.1	1511.0	1424.9	1318.4	1211.9	1124.6
17.5°	1448.1	1540.9	1592.5	1644.1	1612.4	1580.6	1486.3	1392.0	1272.0	1152.0	1057.1
20°	1293.1	1414.6	1495.4	1576.3	1564.7	1553.1	1455.8	1358.4	1229.0	1099.5	996.7
22.5°	1139.8	1268.0	1379.8	1491.5	1503.4	1515.3	1417.0	1318.7	1177.1	1035.4	930.7
25°	1007.6	1138.0	1271.1	1404.2	1431.0	1457.9	1364.5	1271.1	1124.3	977.4	873.3
27.5°	881.6	1005.5	1152.0	1298.6	1347.4	1396.2	1310.8	1225.3	1072.4	919.4	815.6
30°	778.7	889.5	1039.1	1188.7	1256.7	1324.8	1246.4	1167.9	1016.2	864.5	762.8
32.5°	682.9	782.1	932.2	1082.4	1161.5	1240.6	1172.8	1105.0	959.1	813.2	712.8
35°	607.2	696.0	836.1	976.2	1064.7	1153.3	1097.7	1042.1	899.6	757.0	662.1
37.5°	542.1	616.6	748.2	879.7	973.8	1067.8	1021.4	975.0	841.0	707.0	617.2
40°	488.4	548.2	670.6	793.1	885.2	977.4	937.7	898.1	778.1	658.1	574.2
42.5°	442.3	493.9	603.8	713.7	798.2	882.8	856.5	830.3	721.6	613.0	535.1
45°	401.7	445.1	541.8	638.6	716.4	794.3	773.5	752.8	659.0	565.3	493.9
47.5°	365.7	402.9	489.3	575.7	645.6	715.5	696.3	677.1	599.5	522.0	457.0
50°	332.7	364.5	436.5	508.6	571.4	634.3	618.4	602.6	538.5	474.4	418.2
52.5°	301.6	327.8	392.6	457.3	507.9	558.6	546.4	534.2	484.7	435.3	384.3
55°	272.0	296.1	350.7	405.4	448.7	492.1	479.9	467.7	429.2	390.7	345.9
57.5°	245.1	266.2	310.4	354.7	389.2	423.7	417.9	412.1	380.0	348.0	311.1
60°	216.7	235.7	273.8	312.0	339.7	367.5	360.8	354.1	331.2	308.3	276.6
62.5°	191.4	208.2	238.7	269.2	291.8	314.4	309.5	304.6	287.2	269.8	243.6
65°	164.8	181.3	206.0	230.8	248.5	266.2	261.9	257.6	244.5	231.4	210.3
67.5°	140.7	154.5	175.8	197.2	209.1	221.0	218.6	216.1	206.0	196.0	179.5
70°	116.3	128.2	145.9	163.6	171.9	180.1	181.0	181.9	172.8	163.6	151.4
72.5°	91.9	101.3	117.8	134.3	140.7	147.1	146.8	146.5	141.0	135.5	124.5
75°	70.5	77.5	90.4	103.2	108.7	114.2	115.4	116.6	111.4	106.2	100.1
77.5°	50.7	55.6	65.3	75.1	81.2	87.3	87.9	88.5	86.1	83.6	77.8
80°	35.7	37.2	43.3	49.5	55.9	62.3	63.2	64.1	61.7	59.2	55.6
82.5°	24.7	25.6	27.8	29.9	35.1	40.3	41.5	42.7	41.5	40.3	36.3
85°	15.0	15.3	16.2	17.1	19.5	22.0	23.2	24.4	23.8	23.2	21.1
87.5°	6.7	6.7	7.0	7.3	7.9	8.5	10.1	11.6	10.7	9.8	8.9
90°	11.6	9.8	7.9	6.3	4.9	3.5	2.1	0.6	2.1	3.5	4.9
92.5°	14.0	12.7	11.5	11.3	12.1	13.0	13.8	14.7	13.8	13.0	12.1
95°	16.6	15.1	13.5	15.7	21.5	27.3	33.1	38.9	33.1	27.3	21.5
97.5°	34.8	42.1	49.3	54.9	58.9	62.8	66.8	70.8	66.8	62.8	58.9
100°	65.2	87.3	109.4	119.1	116.2	113.4	110.6	107.7	110.6	113.4	116.2
102.5°	96.5	121.1	145.8	157.2	155.3	153.5	151.6	149.8	151.6	153.5	155.3
105°	165.1	177.8	190.6	196.2	194.6	193.1	191.5	189.9	191.5	193.1	194.6
107.5°	243.7	241.6	239.4	237.7	236.5	235.2	233.9	232.6	233.9	235.2	236.5
110°	284.3	282.8	281.2	279.9	278.8	277.6	276.5	275.4	276.5	277.6	278.8



TEST NUMBER: P832293

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	324.5	322.9	321.4	320.1	319.1	318.1	317.1	316.1	317.1	318.1	319.1
115°	363.3	362.0	360.8	359.7	358.9	358.0	357.2	356.3	357.2	358.0	358.9
117.5°	402.1	401.3	400.6	399.8	398.8	397.8	396.8	395.8	396.8	397.8	398.8
120°	439.0	438.5	438.1	437.3	436.0	434.7	433.4	432.2	433.4	434.7	436.0
122.5°	475.0	474.4	473.9	473.1	472.1	471.1	470.1	469.1	470.1	471.1	472.1
125°	508.8	508.2	507.7	506.8	505.7	504.5	503.4	502.3	503.4	504.5	505.7
127.5°	542.3	541.6	540.9	539.9	538.8	537.7	536.5	535.4	536.5	537.7	538.8
130°	572.5	572.0	571.4	570.5	569.4	568.3	567.1	566.0	567.1	568.3	569.4
132.5°	601.5	601.1	600.6	599.9	598.7	597.6	596.5	595.3	596.5	597.6	598.7
135°	630.5	630.0	629.4	628.7	627.8	627.0	626.1	625.3	626.1	627.0	627.8
137.5°	656.6	656.3	656.0	655.3	654.2	653.0	651.9	650.8	651.9	653.0	654.2
140°	681.2	680.7	680.3	679.7	678.8	678.0	677.1	676.3	677.1	678.0	678.8
142.5°	704.7	704.3	703.9	703.3	702.4	701.6	700.7	699.9	700.7	701.6	702.4
145°	726.7	726.4	726.1	725.5	724.5	723.5	722.5	721.5	722.5	723.5	724.5
147.5°	746.5	746.2	745.9	745.4	744.7	744.0	743.3	742.6	743.3	744.0	744.7
150°	764.3	764.0	763.7	763.4	763.0	762.5	762.1	761.7	762.1	762.5	763.0
152.5°	779.9	779.7	779.6	779.5	779.3	779.2	779.0	778.9	779.0	779.2	779.3
155°	793.9	793.8	793.6	793.7	794.0	794.3	794.5	794.8	794.5	794.3	794.0
157.5°	807.2	807.4	807.5	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6
160°	818.1	818.2	818.3	818.5	818.6	818.8	818.9	819.1	818.9	818.8	818.6
162.5°	827.6	827.8	827.9	828.2	828.6	829.0	829.5	829.9	829.5	829.0	828.6
165°	835.9	836.1	836.2	836.5	836.9	837.3	837.8	838.2	837.8	837.3	836.9
167.5°	842.6	842.6	842.6	842.9	843.5	844.1	844.6	845.2	844.6	844.1	843.5
170°	848.4	848.4	848.4	848.7	849.2	849.8	850.4	850.9	850.4	849.8	849.2
172.5°	851.9	851.8	851.6	851.9	852.6	853.3	854.0	854.7	854.0	853.3	852.6
175°	855.1	855.0	854.8	855.1	855.8	856.5	857.2	857.9	857.2	856.5	855.8
177.5°	856.4	856.2	856.1	856.4	857.1	857.8	858.5	859.2	858.5	857.8	857.1
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P832293

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0	1489.0
2.5°	1441.4	1424.0	1406.6	1394.1	1381.6	1366.0	1350.4	1349.8	1349.2	1337.6	1326.0
5°	1355.9	1325.7	1295.5	1265.9	1236.3	1206.7	1177.1	1170.3	1163.6	1153.6	1143.5
7.5°	1280.2	1232.0	1183.8	1145.9	1108.1	1078.5	1048.9	1028.7	1008.6	993.0	977.4
10°	1199.0	1139.2	1079.4	1033.6	987.8	955.8	923.7	900.5	877.3	866.3	855.3
12.5°	1114.8	1049.8	984.8	939.9	895.0	856.5	818.1	797.0	776.0	760.7	745.4
15°	1037.3	967.4	897.4	849.8	802.2	766.2	730.2	709.1	688.0	672.8	657.5
17.5°	962.2	891.6	821.1	772.9	724.7	692.0	659.4	638.9	618.4	609.0	599.5
20°	893.8	822.7	751.5	706.1	660.6	628.5	596.5	585.5	574.5	565.6	556.8
22.5°	826.0	757.6	689.3	645.6	602.0	578.8	555.6	546.7	537.9	531.1	524.4
25°	769.2	701.2	633.1	594.9	556.8	538.8	520.8	515.0	509.2	502.4	495.7
27.5°	711.9	647.1	582.4	551.9	521.4	506.7	492.1	484.7	477.4	471.9	466.4
30°	661.2	601.4	541.5	516.2	490.8	478.0	465.2	457.3	449.3	444.1	439.0
32.5°	612.3	559.2	506.1	484.4	462.8	450.3	437.7	430.1	422.5	416.4	410.3
35°	567.2	521.1	475.0	455.1	435.3	422.8	410.3	402.6	395.0	388.9	382.8
37.5°	527.5	485.7	443.8	425.2	406.6	395.6	384.6	376.7	368.7	362.3	355.9
40°	490.2	453.3	416.4	398.4	380.3	368.4	356.5	349.5	342.5	336.7	330.9
42.5°	457.3	423.4	389.5	371.8	354.1	342.8	331.5	323.3	315.0	311.7	308.3
45°	422.5	392.6	362.6	345.5	328.5	316.5	304.6	297.6	290.6	287.5	284.5
47.5°	391.9	364.2	336.4	319.6	302.8	292.1	281.4	276.0	270.5	266.2	261.9
50°	362.0	335.2	308.3	292.1	276.0	266.8	257.6	250.9	244.2	241.2	238.1
52.5°	333.3	308.9	284.5	268.0	251.5	242.7	233.8	228.0	222.2	215.8	209.4
55°	301.0	279.6	258.2	243.6	228.9	219.8	210.6	203.9	197.2	190.5	183.8
57.5°	274.1	253.1	232.0	218.9	205.7	196.9	188.0	180.7	173.4	167.9	162.4
60°	244.8	226.5	208.2	195.4	182.5	174.0	165.4	158.4	151.4	148.7	145.9
62.5°	217.3	200.2	183.2	171.9	160.6	152.3	144.1	139.5	134.9	133.1	131.3
65°	189.3	174.6	160.0	149.6	139.2	132.2	125.2	123.0	120.9	119.4	117.8
67.5°	163.0	150.5	138.0	128.8	119.7	114.8	109.9	107.4	105.0	103.2	101.3
70°	139.2	128.2	117.2	109.3	101.3	96.8	92.2	90.1	87.9	84.6	81.2
72.5°	113.6	105.0	96.5	90.4	84.3	80.3	76.3	72.0	67.8	64.7	61.7
75°	94.0	85.5	76.9	71.1	65.3	60.7	56.2	54.6	53.1	52.2	51.3
77.5°	72.0	64.7	57.4	52.8	48.2	46.1	44.0	43.0	42.1	41.8	41.5
80°	51.9	45.8	39.7	37.2	34.8	34.2	33.6	33.0	32.4	32.1	31.7
82.5°	32.4	29.3	26.3	25.6	25.0	24.7	24.4	24.1	23.8	23.5	23.2
85°	18.9	17.7	16.5	16.2	15.9	15.6	15.3	15.3	15.3	15.3	15.3
87.5°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.6	7.3
90°	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.4	17.0	17.6	18.0
92.5°	11.3	11.5	12.7	14.0	15.3	16.6	17.6	18.6	19.5	20.5	21.1
95°	15.7	13.5	15.1	16.6	18.2	19.8	20.8	21.7	22.7	23.7	24.2
97.5°	54.9	49.3	42.1	34.8	27.6	20.4	21.5	22.7	23.8	24.9	25.6
100°	119.1	109.4	87.3	65.2	43.1	21.0	22.2	23.3	24.4	25.6	26.2
102.5°	157.2	145.8	121.1	96.5	71.8	47.2	42.5	37.8	33.1	28.5	26.3
105°	196.2	190.6	177.8	165.1	152.3	139.6	114.5	89.4	64.4	39.3	26.9
107.5°	237.7	239.4	241.6	243.7	245.8	247.9	226.1	204.3	182.5	160.7	140.5
110°	279.9	281.2	282.8	284.3	285.9	287.5	282.8	278.1	273.4	268.8	256.3



TEST NUMBER: P832293

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	320.1	321.4	322.9	324.5	326.1	327.6	328.9	330.2	331.4	332.7	333.2
115°	359.7	360.8	362.0	363.3	364.6	365.9	367.3	368.7	370.1	371.5	372.5
117.5°	399.8	400.6	401.3	402.1	402.8	403.5	404.6	405.7	406.9	408.0	408.6
120°	437.3	438.1	438.5	439.0	439.4	439.8	440.9	442.1	443.2	444.3	444.9
122.5°	473.1	473.9	474.4	475.0	475.6	476.1	476.8	477.6	478.3	479.0	479.4
125°	506.8	507.7	508.2	508.8	509.3	509.9	510.2	510.5	510.8	511.0	511.3
127.5°	539.9	540.9	541.6	542.3	543.0	543.7	544.1	544.5	545.0	545.4	545.5
130°	570.5	571.4	572.0	572.5	573.1	573.7	574.2	574.8	575.4	575.9	576.1
132.5°	599.9	600.6	601.1	601.5	601.9	602.3	602.9	603.5	604.0	604.6	604.7
135°	628.7	629.4	630.0	630.5	631.1	631.7	632.1	632.5	632.9	633.4	633.4
137.5°	655.3	656.0	656.3	656.6	656.9	657.2	657.9	658.6	659.3	660.0	660.2
140°	679.7	680.3	680.7	681.2	681.6	682.0	682.6	683.1	683.7	684.3	684.4
142.5°	703.3	703.9	704.3	704.7	705.2	705.6	706.0	706.4	706.9	707.3	707.3
145°	725.5	726.1	726.4	726.7	727.0	727.3	727.6	727.8	728.1	728.4	728.5
147.5°	745.4	745.9	746.2	746.5	746.7	747.0	747.3	747.6	747.9	748.2	747.9
150°	763.4	763.7	764.0	764.3	764.6	764.9	765.2	765.4	765.7	766.0	765.9
152.5°	779.5	779.6	779.7	779.9	780.0	780.2	780.7	781.3	781.9	782.4	782.4
155°	793.7	793.6	793.8	793.9	794.1	794.2	794.9	795.6	796.3	797.0	797.0
157.5°	807.6	807.5	807.4	807.2	807.1	806.9	807.8	808.6	809.5	810.3	810.2
160°	818.5	818.3	818.2	818.1	817.9	817.8	818.6	819.5	820.3	821.2	821.1
162.5°	828.2	827.9	827.8	827.6	827.5	827.3	828.3	829.3	830.3	831.3	831.4
165°	836.5	836.2	836.1	835.9	835.8	835.6	836.8	837.9	839.0	840.2	840.2
167.5°	842.9	842.6	842.6	842.6	842.6	842.6	843.8	844.9	846.0	847.2	847.2
170°	848.7	848.4	848.4	848.4	848.4	848.4	849.5	850.6	851.8	852.9	852.9
172.5°	851.9	851.6	851.8	851.9	852.1	852.2	853.3	854.5	855.6	856.7	856.7
175°	855.1	854.8	855.0	855.1	855.2	855.4	856.4	857.4	858.4	859.4	859.3
177.5°	856.4	856.1	856.2	856.4	856.5	856.7	857.8	858.9	860.1	861.2	861.1
180°	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9	857.9



TEST NUMBER: P832293

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1489.0	1489.0	1489.0	1489.0
2.5°	1323.0	1319.9	1318.7	1317.5
5°	1134.0	1124.6	1122.4	1120.3
7.5°	973.5	969.5	956.4	943.2
10°	843.1	830.9	825.4	819.9
12.5°	734.1	722.8	721.0	719.2
15°	649.6	641.6	638.9	636.2
17.5°	594.0	588.5	585.2	581.8
20°	552.8	548.8	546.4	544.0
22.5°	521.4	518.3	516.5	514.7
25°	491.2	486.6	485.0	483.5
27.5°	462.5	458.5	457.0	455.4
30°	435.6	432.2	430.1	428.0
32.5°	406.3	402.3	401.1	399.9
35°	380.3	377.9	376.7	375.5
37.5°	352.9	349.8	348.0	346.2
40°	329.4	327.8	326.9	326.0
42.5°	305.6	302.8	302.5	302.2
45°	281.8	279.0	278.4	277.8
47.5°	259.5	257.0	256.7	256.4
50°	234.7	231.4	228.9	226.5
52.5°	206.4	203.3	201.2	199.0
55°	180.4	177.0	175.2	173.4
57.5°	160.9	159.3	158.4	157.5
60°	145.0	144.1	143.5	142.9
62.5°	130.3	129.4	129.4	129.4
65°	116.9	116.0	115.1	114.2
67.5°	99.5	97.7	97.4	97.1
70°	78.5	75.7	75.4	75.1
72.5°	61.4	61.1	60.4	59.8
75°	50.7	50.1	50.1	50.1
77.5°	40.9	40.3	40.3	40.3
80°	31.4	31.1	31.4	31.7
82.5°	23.2	23.2	22.9	22.6
85°	15.0	14.7	14.7	14.7
87.5°	7.3	7.3	7.3	7.3
90°	18.3	18.6	18.8	19.1
92.5°	21.2	21.4	21.5	21.7
95°	24.2	24.2	24.2	24.2
97.5°	25.7	25.8	26.0	26.1
100°	26.3	26.5	26.6	26.8
102.5°	26.6	26.8	27.1	27.4
105°	27.2	27.5	27.8	28.0
107.5°	122.0	103.4	84.8	66.3
110°	236.0	215.8	195.5	175.3



TEST NUMBER: P832293

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	332.9	332.6	332.4	332.1
115°	373.1	373.7	374.2	374.8
117.5°	408.8	408.9	409.1	409.2
120°	444.9	444.9	444.9	444.9
122.5°	479.5	479.7	479.8	480.0
125°	511.6	511.9	512.2	512.5
127.5°	545.2	544.9	544.6	544.3
130°	575.8	575.5	575.2	574.9
132.5°	604.3	603.8	603.4	603.0
135°	632.9	632.5	632.1	631.7
137.5°	659.9	659.6	659.4	659.1
140°	684.1	683.9	683.6	683.3
142.5°	706.9	706.4	706.0	705.6
145°	728.5	728.5	728.5	728.5
147.5°	747.2	746.5	745.8	745.1
150°	765.5	765.1	764.7	764.2
152.5°	781.7	781.0	780.2	779.5
155°	796.1	795.3	794.4	793.6
157.5°	809.1	807.9	806.8	805.7
160°	820.1	819.1	818.1	817.1
162.5°	830.5	829.7	828.8	828.0
165°	839.2	838.2	837.3	836.3
167.5°	846.0	844.9	843.8	842.6
170°	851.8	850.6	849.5	848.4
172.5°	855.4	854.1	852.8	851.6
175°	858.1	857.0	855.9	854.7
177.5°	859.6	858.2	856.8	855.4
180°	857.9	857.9	857.9	857.9



TEST NUMBER: P832293

CATALOG NUMBER: S123RDIP-S560D805U930-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.69	10.45	10.72	11.48	12.85	14.36	15.11	15.38	16.14	17.51
	3H	10.91	11.59	11.94	12.62	14.01	15.85	16.53	16.89	17.56	18.95
	4H	11.29	11.93	12.33	12.97	14.36	16.34	16.98	17.39	18.02	19.41
	6H	11.56	12.15	12.62	13.20	14.61	16.65	17.24	17.70	18.28	19.69
	8H	11.65	12.21	12.71	13.27	14.67	16.72	17.28	17.78	18.34	19.75
	12H	11.70	12.23	12.76	13.28	14.71	16.75	17.28	17.82	18.34	19.76
4H	2H	10.41	11.05	11.46	12.09	13.48	14.34	14.98	15.40	16.02	17.42
	3H	11.77	12.30	12.83	13.37	14.78	16.00	16.53	17.06	17.59	19.00
	4H	12.22	12.71	13.29	13.77	15.20	16.60	17.09	17.67	18.14	19.58
	6H	12.59	13.00	13.66	14.08	15.51	17.03	17.45	18.11	18.53	19.96
	8H	12.71	13.10	13.79	14.17	15.62	17.16	17.55	18.24	18.63	20.07
	12H	12.78	13.13	13.88	14.22	15.67	17.22	17.57	18.32	18.66	20.11
8H	4H	12.53	12.92	13.61	13.99	15.44	16.56	16.95	17.64	18.02	19.47
	6H	12.99	13.31	14.09	14.43	15.87	17.06	17.38	18.15	18.49	19.93
	8H	13.19	13.47	14.29	14.56	16.02	17.24	17.52	18.35	18.62	20.08
	12H	13.32	13.57	14.43	14.66	16.16	17.35	17.60	18.46	18.69	20.19
12H	4H	12.54	12.89	13.63	13.98	15.43	16.51	16.86	17.60	17.95	19.39
	6H	13.05	13.33	14.16	14.43	15.89	17.03	17.31	18.14	18.41	19.87
	8H	13.27	13.51	14.37	14.61	16.11	17.22	17.47	18.33	18.56	20.06