

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332262-935

Luminaire Tested: **S123RDIP-S340D1025U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332262-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1025U935-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4152.1 lumens  
Efficiency: N/A  
Efficacy: 111.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332262-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332262-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27				
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23				
2	85	78	72	67	75	70	65	61	54	51	48	40	38	37	28	26	25	20				
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15				
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13				
6	60	48	40	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11				
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	14	13	10				
8	51	39	32	27	45	35	29	25	28	24	20	22	18	16	15	13	12	9				
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	10	8				
10	44	33	26	21	39	30	24	19	24	19	16	18	15	13	13	11	10	7				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5324	5324	5324
5°	5344	5271	5302
10°	5314	5205	5187
15°	5258	5084	5029
20°	5179	4931	4816
25°	5099	4760	4608
30°	4992	4561	4313
35°	4882	4365	4043
40°	4780	4131	3710
45°	4647	3902	3408
50°	4501	3641	3069
55°	4352	3342	2755
60°	4215	3023	2409
65°	4037	2677	2063
70°	3811	2247	1668
75°	3489	1768	1568
80°	3106	1568	1438
85°	2631	1383	1284



TEST NUMBER: P332262-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.5	1.1
10°-20°	129.2	3.1
20°-30°	186.1	4.5
30°-40°	209.6	5.0
40°-50°	200.5	4.8
50°-60°	164.2	4.0
60°-70°	110.8	2.7
70°-80°	55.7	1.3
80°-90°	18.0	0.4
90°-100°	71.3	1.7
100°-110°	213.3	5.1
110°-120°	362.8	8.7
120°-130°	477.3	11.5
130°-140°	536.4	12.9
140°-150°	527.3	12.7
150°-160°	443.9	10.7
160°-170°	295.5	7.1
170°-180°	103.5	2.5
0°-30°	361.8	8.7
0°-40°	571.4	13.8
0°-60°	936.2	22.5
0°-90°	1120.7	27.0
90°-120°	647.5	15.6
90°-150°	2188.5	52.7
90°-180°	3031.0	73.0
0°-180°	4152.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	495	495	495	495	495	
5°	495	492	488	491	491	47
15°	472	467	456	454	451	133
25°	429	419	401	393	388	197
35°	372	356	332	315	308	232
45°	305	286	256	234	224	235
55°	232	211	178	156	147	208
65°	158	136	105	86	81	157
75°	84	64	42	39	38	89
85°	21	13	11	10	10	24
90°	1	10	21	24	26	4
95°	51	57	64	67	67	57
105°	193	195	203	203	205	207
115°	365	368	366	367	366	361
125°	535	537	536	532	529	477
135°	694	698	698	694	693	534
145°	841	843	846	845	841	525
155°	964	964	964	967	962	443
165°	1049	1047	1047	1051	1046	296
175°	1092	1088	1088	1093	1087	104
180°	1094	1094	1094	1094	1094	



TEST NUMBER: P332262-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	496.3	495.9	495.7	495.4	495.2	494.6	493.7	492.8	492.0	491.1	491.9
5°	494.6	494.2	493.8	493.4	492.8	492.1	491.0	490.0	488.9	487.8	488.6
7.5°	490.1	489.6	489.1	488.6	488.2	487.2	485.9	484.5	483.0	481.6	482.1
10°	486.2	485.6	485.0	484.4	483.7	482.6	481.0	479.4	477.8	476.2	476.3
12.5°	480.8	480.1	479.4	478.7	478.0	476.6	474.7	472.8	470.8	468.8	468.7
15°	471.8	470.8	469.8	468.8	467.9	466.1	463.6	461.2	458.7	456.2	455.7
17.5°	460.5	459.3	458.2	457.0	455.9	453.7	450.6	447.4	444.3	441.1	440.1
20°	452.1	450.7	449.3	447.9	446.4	444.0	440.7	437.2	433.9	430.5	429.3
22.5°	442.8	441.2	439.5	437.9	436.3	433.7	430.1	426.5	422.8	419.2	417.8
25°	429.3	427.1	424.8	422.6	420.3	417.2	413.1	409.0	404.8	400.8	398.9
27.5°	412.8	410.4	407.9	405.4	402.9	399.5	394.9	390.3	385.7	381.2	378.6
30°	401.6	398.9	396.2	393.6	390.9	387.0	382.0	377.0	372.0	367.0	364.0
32.5°	390.4	387.3	384.3	381.3	378.2	374.1	368.8	363.5	358.3	352.9	349.7
35°	371.5	368.2	365.1	361.9	358.7	354.3	348.8	343.2	337.7	332.2	328.4
37.5°	352.4	348.8	345.3	341.7	338.1	333.4	327.5	321.6	315.7	309.8	305.5
40°	340.2	336.3	332.3	328.5	324.5	319.3	313.1	306.7	300.4	294.0	289.5
42.5°	326.4	322.4	318.6	314.6	310.7	305.5	298.9	292.4	285.9	279.3	274.2
45°	305.3	301.3	297.3	293.3	289.2	283.8	277.0	270.1	263.2	256.3	251.2
47.5°	284.2	279.8	275.3	271.0	266.6	261.0	254.1	247.2	240.4	233.5	228.0
50°	268.8	264.6	260.5	256.2	252.0	246.3	239.1	231.9	224.6	217.4	211.9
52.5°	255.0	250.5	245.9	241.3	236.8	230.9	223.8	216.6	209.5	202.3	196.7
55°	231.9	227.5	223.2	218.8	214.4	208.4	200.9	193.3	185.7	178.1	173.0
57.5°	210.5	205.8	201.0	196.2	191.5	185.3	177.7	170.0	162.5	154.9	150.0
60°	195.8	190.9	186.0	181.1	176.2	170.0	162.6	155.2	147.8	140.4	135.6
62.5°	181.0	176.1	171.2	166.3	161.4	155.2	147.8	140.4	133.0	125.6	121.1
65°	158.5	153.6	148.7	143.8	138.9	132.9	126.0	119.0	112.1	105.1	100.7
67.5°	136.0	131.0	126.0	121.1	116.1	110.3	103.6	96.9	90.2	83.6	80.3
70°	121.1	116.3	111.5	106.7	101.9	96.3	90.1	83.9	77.7	71.4	68.3
72.5°	106.4	101.7	96.9	92.1	87.4	82.2	76.5	70.9	65.2	59.5	57.0
75°	83.9	79.6	75.3	71.0	66.7	62.2	57.3	52.3	47.4	42.5	41.7
77.5°	63.3	59.4	55.5	51.7	47.9	44.3	41.2	38.0	34.9	31.7	31.3
80°	50.1	46.5	42.9	39.2	35.6	32.8	30.9	29.0	27.1	25.3	25.0
82.5°	37.6	34.4	31.3	28.2	25.0	23.0	22.1	21.3	20.4	19.5	19.2
85°	21.3	19.3	17.3	15.4	13.4	12.3	12.1	11.8	11.5	11.2	11.0
87.5°	7.8	7.5	7.1	6.6	6.3	6.3	6.8	7.3	7.8	8.3	8.4
90°	0.9	2.8	4.6	6.6	8.5	10.7	13.2	15.7	18.2	20.7	21.4
92.5°	20.8	22.1	23.4	24.7	26.0	27.4	28.8	30.1	31.6	33.0	33.6
95°	50.7	52.0	53.4	54.8	56.1	57.5	59.0	60.5	62.1	63.6	64.4
97.5°	90.1	91.1	92.0	93.1	94.0	95.1	96.2	97.3	98.4	99.5	100.4
100°	116.9	118.0	119.2	120.3	121.5	122.5	123.5	124.4	125.4	126.3	126.9
102.5°	147.8	148.5	149.2	149.9	150.6	151.5	152.8	154.0	155.3	156.6	157.1
105°	193.4	193.7	194.2	194.5	194.9	196.0	197.7	199.4	201.1	202.9	202.9
107.5°	246.3	246.6	246.8	247.0	247.3	247.7	248.4	249.1	249.8	250.5	251.1
110°	279.3	279.7	280.1	280.4	280.9	281.2	281.6	282.0	282.4	282.8	283.5



TEST NUMBER: P332262-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	313.7	313.9	314.2	314.4	314.6	314.8	314.9	315.0	315.0	315.0	316.0
115°	365.2	365.8	366.4	367.0	367.6	367.6	367.3	366.9	366.5	366.1	366.4
117.5°	417.2	417.6	417.9	418.4	418.7	418.6	418.2	417.7	417.2	416.6	416.6
120°	449.5	450.6	451.8	453.0	454.1	454.2	453.2	452.3	451.3	450.4	450.1
122.5°	483.2	484.1	484.8	485.7	486.6	486.7	486.2	485.7	485.3	484.7	484.2
125°	534.6	535.2	535.7	536.3	536.8	537.0	536.6	536.2	535.8	535.5	534.7
127.5°	582.0	583.2	584.4	585.7	586.9	587.3	586.9	586.5	586.1	585.7	584.5
130°	613.6	615.2	616.7	618.2	619.7	620.3	619.7	619.1	618.5	617.9	617.2
132.5°	645.3	646.8	648.3	649.9	651.4	651.9	651.5	651.1	650.7	650.2	649.4
135°	693.6	694.7	695.9	697.0	698.2	698.6	698.4	698.3	698.1	697.8	697.2
137.5°	738.3	739.3	740.2	741.1	742.1	742.8	743.3	743.8	744.3	744.8	744.0
140°	769.2	770.2	771.1	772.1	773.0	773.6	773.8	774.0	774.2	774.4	774.2
142.5°	797.4	798.3	799.4	800.3	801.2	801.8	802.2	802.5	802.9	803.2	803.1
145°	841.4	841.8	842.1	842.6	842.9	843.4	844.0	844.6	845.2	845.7	845.5
147.5°	879.9	880.6	881.3	882.0	882.7	883.3	883.8	884.3	884.8	885.5	885.5
150°	906.7	907.1	907.5	907.8	908.3	908.6	909.0	909.4	909.8	910.2	910.2
152.5°	928.8	929.3	929.8	930.3	930.8	931.3	931.5	931.7	931.9	932.2	932.5
155°	963.5	963.5	963.5	963.5	963.5	963.5	963.7	963.9	964.1	964.3	965.1
157.5°	993.0	992.8	992.6	992.3	992.1	992.0	992.2	992.4	992.6	992.6	993.5
160°	1011.6	1011.2	1010.8	1010.5	1010.0	1009.9	1009.9	1009.9	1009.9	1009.9	1010.8
162.5°	1028.1	1027.5	1027.0	1026.5	1026.0	1025.8	1025.9	1026.1	1026.2	1026.4	1027.3
165°	1049.4	1048.8	1048.3	1047.7	1047.1	1046.8	1046.8	1046.8	1046.8	1046.8	1047.9
167.5°	1066.4	1065.7	1064.9	1064.1	1063.3	1063.1	1063.2	1063.3	1063.5	1063.7	1064.9
170°	1076.1	1075.3	1074.5	1073.8	1073.0	1072.6	1072.6	1072.6	1072.6	1072.6	1073.9
172.5°	1083.6	1082.9	1082.1	1081.3	1080.6	1080.1	1080.1	1080.1	1080.1	1080.1	1081.3
175°	1091.5	1090.7	1089.9	1089.3	1088.5	1088.0	1088.0	1088.0	1088.0	1088.0	1089.3
177.5°	1094.8	1094.2	1093.6	1093.0	1092.4	1092.0	1092.0	1092.0	1092.0	1092.0	1093.0
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P332262-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	492.7	493.4	494.3	494.6	494.5	494.3	494.1	494.0
5°	489.5	490.3	491.0	491.4	491.2	491.0	490.9	490.7
7.5°	482.6	483.0	483.5	483.5	483.2	482.9	482.6	482.3
10°	476.4	476.5	476.6	476.4	476.0	475.5	475.0	474.6
12.5°	468.7	468.6	468.6	468.3	467.8	467.3	466.7	466.2
15°	455.2	454.8	454.3	453.8	453.2	452.5	451.9	451.3
17.5°	439.2	438.2	437.3	436.4	435.4	434.5	433.6	432.7
20°	428.2	427.0	425.9	424.7	423.6	422.6	421.5	420.4
22.5°	416.4	414.9	413.5	412.2	411.2	410.3	409.2	408.3
25°	397.0	395.2	393.3	391.8	390.9	389.9	388.9	388.0
27.5°	376.0	373.4	370.8	368.8	367.2	365.8	364.3	362.7
30°	361.0	358.0	355.0	352.8	351.3	349.9	348.4	347.0
32.5°	346.3	343.0	339.7	337.3	335.8	334.3	332.8	331.3
35°	324.5	320.6	316.8	314.1	312.5	310.9	309.3	307.7
37.5°	301.1	296.7	292.4	289.2	287.2	285.2	283.3	281.3
40°	284.8	280.2	275.5	272.2	270.1	268.1	266.0	264.0
42.5°	269.1	264.2	259.1	255.6	253.7	251.9	250.1	248.2
45°	246.2	241.1	236.0	232.4	230.3	228.2	226.0	223.9
47.5°	222.4	216.9	211.4	207.7	205.8	203.9	201.9	200.0
50°	206.4	200.9	195.4	191.6	189.5	187.4	185.4	183.3
52.5°	190.9	185.1	179.4	175.6	173.7	171.9	170.1	168.2
55°	167.8	162.6	157.5	153.9	152.2	150.4	148.6	146.8
57.5°	145.1	140.2	135.3	132.1	130.6	129.1	127.6	126.1
60°	130.8	126.0	121.1	118.0	116.5	114.9	113.5	111.9
62.5°	116.6	112.1	107.5	104.4	102.9	101.3	99.7	98.2
65°	96.3	92.0	87.6	85.0	83.9	83.0	82.1	81.0
67.5°	77.1	73.8	70.5	68.4	67.3	66.3	65.3	64.2
70°	65.2	62.1	58.9	56.9	55.9	54.9	53.9	53.0
72.5°	54.4	51.9	49.3	47.9	47.4	47.0	46.7	46.2
75°	40.7	39.9	38.9	38.4	38.2	38.1	37.9	37.7
77.5°	30.7	30.2	29.8	29.4	29.3	29.1	28.9	28.8
80°	24.7	24.5	24.2	24.0	23.8	23.6	23.4	23.2
82.5°	18.9	18.7	18.4	18.3	18.3	18.2	18.2	18.2
85°	10.8	10.7	10.5	10.4	10.4	10.4	10.4	10.4
87.5°	8.4	8.5	8.6	8.7	8.7	8.7	8.7	8.7
90°	22.1	22.9	23.7	24.3	24.6	25.1	25.4	25.7
92.5°	34.3	34.9	35.5	35.6	35.4	35.2	35.0	34.7
95°	65.1	65.9	66.6	67.1	67.1	67.1	67.1	67.1
97.5°	101.3	102.2	103.1	103.4	103.4	103.3	103.2	103.1
100°	127.5	128.0	128.6	129.2	129.5	129.8	130.3	130.6
102.5°	157.7	158.3	158.9	159.1	159.0	158.9	158.9	158.9
105°	202.9	202.9	202.9	203.0	203.4	203.8	204.1	204.6
107.5°	251.7	252.3	252.9	253.0	252.9	252.6	252.4	252.2
110°	284.3	285.1	285.9	286.0	285.6	285.2	284.9	284.5





TEST NUMBER: P332262-935

CATALOG NUMBER: S123RDIP-S340D1025U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	316.9	317.8	318.7	319.2	319.1	319.0	318.9	318.8
115°	366.5	366.7	366.9	366.9	366.7	366.5	366.4	366.1
117.5°	416.6	416.6	416.6	416.2	415.7	415.2	414.7	414.1
120°	450.0	449.8	449.6	449.3	448.9	448.6	448.2	447.8
122.5°	483.7	483.3	482.8	482.2	481.7	481.1	480.6	480.1
125°	533.9	533.1	532.4	531.6	530.9	530.1	529.3	528.6
127.5°	583.5	582.5	581.3	580.4	579.5	578.6	577.7	576.9
130°	616.4	615.6	614.9	613.8	612.5	611.1	609.8	608.5
132.5°	648.4	647.6	646.6	645.7	644.6	643.6	642.6	641.5
135°	696.4	695.6	694.8	694.2	693.9	693.4	693.1	692.8
137.5°	743.2	742.4	741.6	740.8	740.1	739.3	738.7	738.0
140°	774.0	773.8	773.6	772.8	771.5	770.2	768.9	767.5
142.5°	802.9	802.7	802.5	801.8	800.8	799.8	798.7	797.7
145°	845.3	845.2	844.9	844.5	843.7	842.9	842.1	841.4
147.5°	885.5	885.5	885.5	884.8	883.7	882.5	881.4	880.3
150°	910.2	910.2	910.2	909.6	908.4	907.3	906.1	905.0
152.5°	932.8	933.1	933.4	933.1	932.0	931.1	930.1	929.1
155°	965.9	966.6	967.3	967.1	965.8	964.4	963.0	961.7
157.5°	994.3	995.1	995.9	995.7	994.7	993.6	992.6	991.4
160°	1011.8	1012.7	1013.7	1013.7	1013.1	1012.3	1011.5	1010.7
162.5°	1028.3	1029.2	1030.2	1030.0	1028.8	1027.6	1026.4	1025.2
165°	1049.1	1050.2	1051.4	1051.3	1050.0	1048.6	1047.3	1045.9
167.5°	1066.0	1067.2	1068.4	1068.4	1067.2	1066.0	1064.9	1063.7
170°	1075.3	1076.6	1078.0	1078.0	1076.6	1075.3	1073.9	1072.6
172.5°	1082.5	1083.7	1084.9	1084.9	1083.5	1082.2	1080.8	1079.4
175°	1090.4	1091.5	1092.7	1092.5	1091.2	1089.9	1088.6	1087.2
177.5°	1093.9	1094.8	1095.7	1095.6	1094.6	1093.5	1092.4	1091.3
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1

(END OF REPORT)