

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332321-930

Luminaire Tested: **S123RDIP-S775D1025U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332321-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1025U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5721.3 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332321-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332321-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	38	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	36	33	31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20
6	62	50	43	37	57	46	40	34	39	34	30	32	28	25	25	23	20	17
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	21	18	16	14
9	50	38	30	26	45	35	28	24	30	24	21	24	21	18	20	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11330	11330	11330
5°	11373	11217	11282
10°	11309	11075	11038
15°	11188	10816	10702
20°	11021	10493	10247
25°	10849	10128	9804
30°	10621	9708	9178
35°	10387	9289	8604
40°	10172	8792	7893
45°	9889	8304	7252
50°	9577	7748	6532
55°	9259	7112	5863
60°	8968	6433	5126
65°	8588	5695	4391
70°	8113	4784	3547
75°	7419	3764	3335
80°	6614	3335	3068
85°	5582	2952	2742



TEST NUMBER: P332321-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	1.7
10°-20°	275.0	4.8
20°-30°	396.0	6.9
30°-40°	446.1	7.8
40°-50°	426.7	7.5
50°-60°	349.5	6.1
60°-70°	235.8	4.1
70°-80°	118.6	2.1
80°-90°	34.4	0.6
90°-100°	39.8	0.7
100°-110°	189.8	3.3
110°-120°	455.9	8.0
120°-130°	580.5	10.1
130°-140°	620.3	10.8
140°-150°	580.0	10.1
150°-160°	467.9	8.2
160°-170°	302.0	5.3
170°-180°	104.1	1.8
0°-30°	769.9	13.5
0°-40°	1215.9	21.3
0°-60°	1992.1	34.8
0°-90°	2381.0	41.6
90°-120°	685.5	12.0
90°-150°	2466.4	43.1
90°-180°	3340.0	58.4
0°-180°	5721.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1053	1053	1053	1053	1053	
5°	1053	1048	1038	1045	1044	100
15°	1004	994	971	966	960	283
25°	914	891	853	835	826	420
35°	790	759	707	671	655	495
45°	650	610	546	498	476	501
55°	493	450	379	331	312	442
65°	337	289	224	184	172	334
75°	178	137	90	82	80	190
85°	45	27	24	22	22	51
90°	1	9	20	23	24	5
95°	50	19	25	31	31	61
105°	242	247	178	42	36	257
115°	455	460	467	475	478	449
125°	641	648	651	653	654	572
135°	798	803	806	809	806	614
145°	921	927	928	930	930	576
155°	1015	1013	1014	1018	1013	467
165°	1070	1068	1067	1073	1068	302
175°	1095	1092	1092	1097	1091	104
180°	1095	1095	1095	1095	1095	



TEST NUMBER: P332321-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1056.0	1055.4	1054.8	1054.2	1053.6	1052.4	1050.5	1048.7	1046.9	1045.1	1046.8
5°	1052.6	1051.7	1050.7	1049.8	1048.8	1047.2	1044.9	1042.6	1040.3	1038.1	1039.8
7.5°	1042.8	1041.9	1040.8	1039.8	1038.8	1036.7	1033.8	1030.9	1027.9	1024.9	1025.9
10°	1034.7	1033.3	1032.0	1030.7	1029.3	1027.0	1023.5	1020.2	1016.8	1013.3	1013.5
12.5°	1023.0	1021.6	1020.1	1018.6	1017.2	1014.3	1010.2	1006.0	1001.8	997.6	997.5
15°	1004.0	1001.8	999.7	997.7	995.6	991.9	986.6	981.3	975.9	970.6	969.7
17.5°	979.8	977.5	975.0	972.6	970.1	965.6	958.8	952.0	945.3	938.6	936.5
20°	962.1	959.0	956.0	953.0	950.0	944.9	937.6	930.4	923.2	916.0	913.5
22.5°	942.3	938.8	935.3	931.8	928.3	922.8	915.1	907.4	899.8	892.1	889.0
25°	913.5	908.7	903.9	899.2	894.5	887.7	879.0	870.3	861.5	852.8	848.8
27.5°	878.4	873.2	868.0	862.7	857.5	850.0	840.3	830.6	820.8	811.1	805.6
30°	854.5	848.8	843.2	837.5	831.8	823.6	813.0	802.3	791.7	781.1	774.7
32.5°	830.6	824.2	817.7	811.3	804.9	796.0	784.7	773.6	762.3	751.1	744.0
35°	790.5	783.7	776.8	770.1	763.2	753.9	742.2	730.3	718.6	706.9	698.7
37.5°	749.9	742.2	734.7	727.1	719.5	709.5	696.9	684.4	671.8	659.3	650.0
40°	723.9	715.6	707.2	698.9	690.6	679.6	666.2	652.7	639.2	625.7	615.9
42.5°	694.6	686.2	677.8	669.5	661.2	650.0	636.1	622.2	608.3	594.4	583.6
45°	649.6	641.2	632.6	624.0	615.5	604.0	589.3	574.7	560.1	545.5	534.7
47.5°	604.8	595.4	586.0	576.7	567.3	555.3	540.7	526.0	511.4	496.8	485.1
50°	571.9	563.0	554.2	545.2	536.3	524.2	508.8	493.4	478.1	462.7	450.9
52.5°	542.6	533.0	523.3	513.6	503.9	491.5	476.2	461.1	445.8	430.6	418.4
55°	493.4	484.1	474.8	465.5	456.2	443.5	427.4	411.3	395.2	379.0	368.0
57.5°	448.0	437.9	427.8	417.6	407.5	394.4	378.1	361.9	345.7	329.5	319.1
60°	416.6	406.2	395.7	385.3	374.9	361.7	346.0	330.3	314.5	298.8	288.5
62.5°	385.1	374.7	364.3	353.8	343.5	330.4	314.6	298.9	283.2	267.3	257.7
65°	337.2	326.8	316.3	305.9	295.5	282.8	268.1	253.2	238.5	223.6	214.3
67.5°	289.3	278.7	268.2	257.6	247.0	234.6	220.5	206.3	192.1	177.9	171.0
70°	257.8	247.6	237.3	227.1	216.9	205.0	191.8	178.6	165.3	152.0	145.3
72.5°	226.4	216.3	206.2	196.1	186.1	175.0	162.9	150.8	138.8	126.7	121.2
75°	178.4	169.3	160.2	151.1	142.0	132.2	121.8	111.4	100.9	90.5	88.6
77.5°	134.7	126.5	118.2	110.0	101.7	94.3	87.6	80.9	74.2	67.4	66.4
80°	106.7	98.9	91.2	83.4	75.6	69.7	65.7	61.7	57.8	53.8	53.2
82.5°	80.1	73.4	66.6	59.9	53.2	48.9	47.0	45.2	43.4	41.5	40.9
85°	45.2	41.1	36.9	32.7	28.5	26.2	25.6	25.0	24.5	23.9	23.6
87.5°	16.6	15.2	13.9	12.6	11.3	10.9	11.4	11.8	12.3	12.8	12.8
90°	0.8	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2
92.5°	15.2	14.6	14.1	13.6	13.1	13.8	15.5	17.3	19.1	20.9	22.0
95°	49.7	42.2	34.8	27.4	20.0	17.3	19.2	21.3	23.2	25.2	26.5
97.5°	99.8	96.4	93.1	89.8	86.4	78.3	65.3	52.3	39.2	26.2	27.6
100°	137.5	141.1	144.8	148.4	152.0	139.7	111.5	83.2	55.0	26.8	28.3
102.5°	180.5	183.1	185.7	188.3	190.9	176.8	146.0	115.2	84.4	53.6	49.1
105°	242.5	244.5	246.5	248.5	250.5	243.3	227.1	210.8	194.5	178.2	146.2
107.5°	307.9	309.6	311.1	312.7	314.3	316.4	318.9	321.6	324.1	326.7	303.2
110°	351.6	353.0	354.4	355.9	357.3	359.1	361.0	363.1	365.0	367.0	361.0



TEST NUMBER: P332321-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.2	394.5	395.8	397.1	398.4	400.1	402.1	404.1	406.0	408.1	408.1
115°	454.9	456.0	457.1	458.2	459.3	460.6	462.2	463.8	465.5	467.1	469.0
117.5°	514.6	516.0	517.3	518.7	520.0	521.1	521.9	522.8	523.6	524.4	525.9
120°	551.7	553.3	555.0	556.6	558.2	559.4	559.9	560.4	561.0	561.5	563.0
122.5°	589.5	590.8	592.2	593.5	594.8	595.9	596.6	597.3	597.9	598.6	599.7
125°	641.2	642.7	644.2	645.6	647.0	648.2	648.9	649.5	650.3	651.0	651.4
127.5°	691.4	692.8	694.3	695.7	697.2	698.3	699.2	700.1	700.9	701.8	702.4
130°	722.7	724.1	725.5	727.0	728.5	729.5	730.3	731.0	731.6	732.4	733.1
132.5°	752.6	754.1	755.5	756.9	758.4	759.4	759.9	760.5	761.2	761.7	762.5
135°	798.3	799.4	800.5	801.6	802.7	803.6	804.3	805.0	805.8	806.5	807.0
137.5°	837.4	838.8	840.2	841.6	842.9	843.8	844.2	844.6	845.0	845.4	846.2
140°	863.4	864.5	865.6	866.7	867.8	868.6	869.1	869.7	870.3	870.7	871.5
142.5°	887.5	888.6	889.7	890.8	891.9	892.7	893.2	893.7	894.3	894.9	895.4
145°	921.2	922.5	923.7	925.0	926.3	927.1	927.5	927.8	928.1	928.5	928.9
147.5°	952.9	953.8	954.6	955.4	956.3	956.8	957.2	957.6	958.0	958.3	958.7
150°	972.5	973.1	973.5	974.1	974.6	975.1	975.4	975.8	976.2	976.6	976.9
152.5°	990.0	990.3	990.6	990.8	991.1	991.3	991.5	991.7	992.0	992.1	992.8
155°	1014.8	1014.4	1014.1	1013.7	1013.3	1013.3	1013.4	1013.6	1013.8	1014.0	1014.9
157.5°	1034.0	1034.0	1034.0	1033.9	1033.9	1033.7	1033.6	1033.4	1033.2	1033.0	1034.1
160°	1045.7	1045.5	1045.4	1045.2	1045.0	1044.8	1044.6	1044.5	1044.2	1044.1	1045.2
162.5°	1056.8	1056.3	1055.8	1055.4	1054.9	1054.6	1054.4	1054.2	1054.0	1053.9	1055.1
165°	1070.2	1069.6	1069.0	1068.5	1068.0	1067.6	1067.4	1067.2	1067.1	1066.9	1068.3
167.5°	1080.5	1079.9	1079.1	1078.4	1077.7	1077.3	1077.3	1077.3	1077.3	1077.3	1078.7
170°	1086.4	1085.7	1085.0	1084.3	1083.5	1083.1	1083.1	1083.1	1083.1	1083.1	1084.6
172.5°	1090.3	1089.5	1088.6	1087.7	1086.9	1086.5	1086.6	1086.8	1086.9	1087.0	1088.5
175°	1095.4	1094.5	1093.6	1092.7	1091.8	1091.4	1091.5	1091.8	1091.9	1092.1	1093.4
177.5°	1096.7	1095.9	1095.2	1094.5	1093.8	1093.5	1093.6	1093.8	1093.9	1094.1	1095.2
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332321-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1048.4	1050.1	1051.7	1052.5	1052.1	1051.8	1051.5	1051.2
5°	1041.5	1043.2	1044.9	1045.5	1045.2	1044.8	1044.4	1044.1
7.5°	1026.9	1027.8	1028.7	1028.9	1028.3	1027.6	1027.0	1026.3
10°	1013.7	1013.9	1014.1	1013.7	1012.8	1011.8	1010.9	1009.9
12.5°	997.4	997.3	997.2	996.5	995.5	994.3	993.3	992.1
15°	968.7	967.8	966.9	965.7	964.4	963.0	961.7	960.4
17.5°	934.5	932.5	930.5	928.5	926.5	924.5	922.6	920.6
20°	911.1	908.6	906.1	903.8	901.5	899.2	896.9	894.6
22.5°	886.0	882.9	879.8	877.2	875.1	872.9	870.8	868.7
25°	844.9	840.9	836.9	833.9	831.8	829.6	827.6	825.5
27.5°	800.1	794.6	789.0	784.6	781.5	778.3	775.1	771.9
30°	768.3	761.7	755.3	750.6	747.5	744.5	741.4	738.4
32.5°	736.9	729.9	722.8	717.7	714.5	711.3	708.2	705.0
35°	690.6	682.4	674.3	668.5	665.0	661.6	658.2	654.8
37.5°	640.7	631.4	622.2	615.5	611.2	607.0	602.8	598.6
40°	606.0	596.1	586.3	579.2	574.8	570.5	566.1	561.7
42.5°	572.7	562.0	551.2	543.9	540.0	536.1	532.1	528.2
45°	523.9	513.1	502.2	494.6	490.0	485.4	480.9	476.4
47.5°	473.3	461.5	449.8	441.9	437.8	433.7	429.7	425.7
50°	439.2	427.4	415.6	407.6	403.2	398.8	394.5	390.1
52.5°	406.2	394.0	381.7	373.7	369.7	365.8	361.9	358.0
55°	357.0	346.0	335.0	327.6	323.8	320.0	316.3	312.4
57.5°	308.8	298.3	288.0	281.1	277.9	274.7	271.4	268.2
60°	278.3	268.1	257.8	251.1	247.9	244.6	241.4	238.1
62.5°	248.1	238.5	228.9	222.3	218.9	215.6	212.2	208.8
65°	205.0	195.8	186.5	180.8	178.7	176.6	174.6	172.4
67.5°	164.0	157.1	150.1	145.5	143.3	141.0	138.8	136.6
70°	138.7	132.0	125.4	121.1	119.0	116.8	114.8	112.7
72.5°	115.9	110.4	105.0	101.8	100.9	100.1	99.2	98.3
75°	86.7	84.8	82.9	81.8	81.4	81.0	80.6	80.2
77.5°	65.4	64.3	63.3	62.6	62.3	61.9	61.5	61.1
80°	52.7	52.1	51.5	51.0	50.6	50.3	49.9	49.5
82.5°	40.4	39.8	39.2	38.9	38.8	38.7	38.6	38.6
85°	23.2	22.7	22.4	22.2	22.2	22.2	22.2	22.2
87.5°	12.8	12.8	12.7	12.7	12.6	12.6	12.5	12.4
90°	21.0	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	23.2	24.3	25.4	26.2	26.3	26.6	26.8	27.0
95°	27.7	29.0	30.3	30.9	30.9	30.9	30.9	30.9
97.5°	29.1	30.6	32.0	32.8	33.0	33.2	33.3	33.5
100°	29.8	31.2	32.6	33.4	33.7	33.8	34.0	34.2
102.5°	44.6	40.1	35.6	33.5	33.8	34.2	34.5	34.8
105°	114.2	82.2	50.2	34.3	34.7	35.1	35.5	35.8
107.5°	279.7	256.2	232.8	209.0	184.8	160.7	136.6	112.4
110°	355.1	349.1	343.2	327.3	301.3	275.5	249.6	223.8



TEST NUMBER: P332321-930

CATALOG NUMBER: S123RDIP-S775D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	408.2	408.4	408.5	405.8	400.3	394.8	389.4	383.9
115°	470.8	472.5	474.3	475.6	476.3	477.0	477.8	478.5
117.5°	527.3	528.7	530.2	531.0	531.2	531.2	531.4	531.6
120°	564.4	565.8	567.3	568.0	568.0	568.0	568.0	568.0
122.5°	600.6	601.7	602.7	603.2	603.4	603.6	603.6	603.8
125°	651.8	652.1	652.5	652.8	653.2	653.5	654.0	654.3
127.5°	703.0	703.5	704.1	704.3	703.8	703.5	703.1	702.8
130°	733.9	734.6	735.3	735.5	735.2	734.7	734.4	734.0
132.5°	763.1	763.9	764.6	764.7	764.2	763.7	763.2	762.7
135°	807.6	808.1	808.6	808.6	808.1	807.6	807.0	806.5
137.5°	847.1	848.0	848.8	849.1	848.7	848.4	848.0	847.7
140°	872.2	872.9	873.7	873.8	873.4	873.1	872.8	872.4
142.5°	896.0	896.6	897.2	897.2	896.7	896.2	895.7	895.2
145°	929.3	929.6	930.0	930.2	930.2	930.2	930.2	930.2
147.5°	959.0	959.4	959.8	959.5	958.7	957.9	957.0	956.2
150°	977.3	977.6	978.0	977.9	977.4	976.8	976.2	975.8
152.5°	993.4	994.1	994.7	994.7	993.8	993.0	992.2	991.3
155°	1015.8	1016.7	1017.6	1017.5	1016.4	1015.4	1014.2	1013.2
157.5°	1035.2	1036.2	1037.4	1037.2	1035.8	1034.4	1033.0	1031.6
160°	1046.3	1047.3	1048.4	1048.3	1047.1	1045.8	1044.6	1043.3
162.5°	1056.3	1057.5	1058.7	1058.8	1057.7	1056.5	1055.5	1054.3
165°	1069.8	1071.2	1072.7	1072.8	1071.5	1070.2	1068.9	1067.7
167.5°	1080.2	1081.7	1083.0	1083.0	1081.7	1080.2	1078.7	1077.3
170°	1086.1	1087.5	1088.9	1088.9	1087.5	1086.1	1084.6	1083.1
172.5°	1090.0	1091.4	1092.8	1092.7	1091.2	1089.6	1088.0	1086.4
175°	1094.6	1095.9	1097.1	1097.1	1095.6	1094.2	1092.7	1091.3
177.5°	1096.3	1097.6	1098.7	1098.5	1097.1	1095.7	1094.2	1092.7
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4

(END OF REPORT)