

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332303-930

Luminaire Tested: **S123RDIP-S775D365U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332303-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D365U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3561.5 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332303-930

CATALOG NUMBER: S123RDIP-S775D365U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332303-930

CATALOG NUMBER: S123RDIP-S775D365U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67								
1	102	98	94	90	96	92	89	86	82	79	77	73	71	69	64	63	61	57								
2	93	86	80	75	88	81	76	71	72	68	65	64	61	58	57	54	52	49								
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	51	48	45	42								
4	78	67	60	53	74	64	57	51	57	52	47	51	47	43	46	42	39	36								
5	72	60	52	46	68	57	50	44	52	46	41	46	41	38	41	37	34	32								
6	67	54	46	40	63	52	44	39	47	41	36	42	37	33	38	34	30	28								
7	62	49	41	36	58	47	40	34	43	36	32	38	33	30	34	30	27	25								
8	57	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22								
9	54	41	34	29	51	39	32	28	36	30	26	33	28	24	29	25	22	20								
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20	18								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11330	11330	11330
5°	11373	11217	11282
10°	11309	11075	11038
15°	11188	10816	10702
20°	11021	10493	10247
25°	10849	10128	9804
30°	10621	9708	9178
35°	10387	9289	8604
40°	10172	8792	7893
45°	9889	8304	7252
50°	9577	7748	6532
55°	9259	7112	5863
60°	8968	6433	5126
65°	8588	5695	4391
70°	8113	4784	3547
75°	7419	3764	3335
80°	6614	3335	3068
85°	5582	2952	2742



TEST NUMBER: P332303-930

CATALOG NUMBER: S123RDIP-S775D365U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	2.8
10°-20°	275.0	7.7
20°-30°	396.0	11.1
30°-40°	446.1	12.5
40°-50°	426.7	12.0
50°-60°	349.5	9.8
60°-70°	235.8	6.6
70°-80°	118.6	3.3
80°-90°	32.5	0.9
90°-100°	14.1	0.4
100°-110°	67.2	1.9
110°-120°	161.4	4.5
120°-130°	205.5	5.8
130°-140°	219.6	6.2
140°-150°	205.4	5.8
150°-160°	165.6	4.7
160°-170°	106.9	3.0
170°-180°	36.8	1.0
0°-30°	769.9	21.6
0°-40°	1215.9	34.1
0°-60°	1992.1	55.9
0°-90°	2379.0	66.8
90°-120°	242.7	6.8
90°-150°	873.2	24.5
90°-180°	1183.0	33.2
0°-180°	3561.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1053	1053	1053	1053	1053	
5°	1053	1048	1038	1045	1044	100
15°	1004	994	971	966	960	283
25°	914	891	853	835	826	420
35°	790	759	707	671	655	495
45°	650	610	546	498	476	501
55°	493	450	379	331	312	442
65°	337	289	224	184	172	334
75°	178	137	90	82	80	190
85°	45	27	24	22	22	51
90°	0	3	7	8	9	3
95°	18	7	9	11	11	22
105°	86	87	63	15	13	91
115°	161	163	165	168	169	159
125°	227	229	230	231	232	203
135°	283	284	286	286	286	217
145°	326	328	329	329	329	204
155°	359	359	359	360	359	165
165°	379	378	378	380	378	107
175°	388	386	387	388	386	37
180°	388	388	388	388	388	



TEST NUMBER: P332303-930

CATALOG NUMBER: S123RDIP-S775D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1056.0	1055.4	1054.8	1054.2	1053.6	1052.4	1050.5	1048.7	1046.9	1045.1	1046.8
5°	1052.6	1051.7	1050.7	1049.8	1048.8	1047.2	1044.9	1042.6	1040.3	1038.1	1039.8
7.5°	1042.8	1041.9	1040.8	1039.8	1038.8	1036.7	1033.8	1030.9	1027.9	1024.9	1025.9
10°	1034.7	1033.3	1032.0	1030.7	1029.3	1027.0	1023.5	1020.2	1016.8	1013.3	1013.5
12.5°	1023.0	1021.6	1020.1	1018.6	1017.2	1014.3	1010.2	1006.0	1001.8	997.6	997.5
15°	1004.0	1001.8	999.7	997.7	995.6	991.9	986.6	981.3	975.9	970.6	969.7
17.5°	979.8	977.5	975.0	972.6	970.1	965.6	958.8	952.0	945.3	938.6	936.5
20°	962.1	959.0	956.0	953.0	950.0	944.9	937.6	930.4	923.2	916.0	913.5
22.5°	942.3	938.8	935.3	931.8	928.3	922.8	915.1	907.4	899.8	892.1	889.0
25°	913.5	908.7	903.9	899.2	894.5	887.7	879.0	870.3	861.5	852.8	848.8
27.5°	878.4	873.2	868.0	862.7	857.5	850.0	840.3	830.6	820.8	811.1	805.6
30°	854.5	848.8	843.2	837.5	831.8	823.6	813.0	802.3	791.7	781.1	774.7
32.5°	830.6	824.2	817.7	811.3	804.9	796.0	784.7	773.6	762.3	751.1	744.0
35°	790.5	783.7	776.8	770.1	763.2	753.9	742.2	730.3	718.6	706.9	698.7
37.5°	749.9	742.2	734.7	727.1	719.5	709.5	696.9	684.4	671.8	659.3	650.0
40°	723.9	715.6	707.2	698.9	690.6	679.6	666.2	652.7	639.2	625.7	615.9
42.5°	694.6	686.2	677.8	669.5	661.2	650.0	636.1	622.2	608.3	594.4	583.6
45°	649.6	641.2	632.6	624.0	615.5	604.0	589.3	574.7	560.1	545.5	534.7
47.5°	604.8	595.4	586.0	576.7	567.3	555.3	540.7	526.0	511.4	496.8	485.1
50°	571.9	563.0	554.2	545.2	536.3	524.2	508.8	493.4	478.1	462.7	450.9
52.5°	542.6	533.0	523.3	513.6	503.9	491.5	476.2	461.1	445.8	430.6	418.4
55°	493.4	484.1	474.8	465.5	456.2	443.5	427.4	411.3	395.2	379.0	368.0
57.5°	448.0	437.9	427.8	417.6	407.5	394.4	378.1	361.9	345.7	329.5	319.1
60°	416.6	406.2	395.7	385.3	374.9	361.7	346.0	330.3	314.5	298.8	288.5
62.5°	385.1	374.7	364.3	353.8	343.5	330.4	314.6	298.9	283.2	267.3	257.7
65°	337.2	326.8	316.3	305.9	295.5	282.8	268.1	253.2	238.5	223.6	214.3
67.5°	289.3	278.7	268.2	257.6	247.0	234.6	220.5	206.3	192.1	177.9	171.0
70°	257.8	247.6	237.3	227.1	216.9	205.0	191.8	178.6	165.3	152.0	145.3
72.5°	226.4	216.3	206.2	196.1	186.1	175.0	162.9	150.8	138.8	126.7	121.2
75°	178.4	169.3	160.2	151.1	142.0	132.2	121.8	111.4	100.9	90.5	88.6
77.5°	134.7	126.5	118.2	110.0	101.7	94.3	87.6	80.9	74.2	67.4	66.4
80°	106.7	98.9	91.2	83.4	75.6	69.7	65.7	61.7	57.8	53.8	53.2
82.5°	80.1	73.4	66.6	59.9	53.2	48.9	47.0	45.2	43.4	41.5	40.9
85°	45.2	41.1	36.9	32.7	28.5	26.2	25.6	25.0	24.5	23.9	23.6
87.5°	16.5	14.9	13.4	11.8	10.3	9.6	9.8	9.9	10.1	10.3	10.2
90°	0.3	0.9	1.5	2.2	2.9	3.6	4.4	5.2	6.1	6.9	7.2
92.5°	5.4	5.2	5.0	4.8	4.6	4.9	5.5	6.1	6.8	7.3	7.7
95°	17.6	14.9	12.3	9.7	7.1	6.1	6.8	7.5	8.2	9.0	9.4
97.5°	35.3	34.2	32.9	31.8	30.6	27.7	23.1	18.5	13.9	9.3	9.8
100°	48.7	50.0	51.3	52.5	53.8	49.5	39.5	29.5	19.5	9.5	10.0
102.5°	63.9	64.8	65.7	66.7	67.6	62.6	51.7	40.8	29.8	19.0	17.4
105°	85.9	86.6	87.2	88.0	88.7	86.2	80.4	74.6	68.9	63.1	51.8
107.5°	109.0	109.6	110.1	110.7	111.3	112.0	112.9	113.8	114.7	115.6	107.3
110°	124.5	125.0	125.5	126.0	126.5	127.1	127.8	128.5	129.2	130.0	127.8



TEST NUMBER: P332303-930

CATALOG NUMBER: S123RDIP-S775D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	139.2	139.7	140.1	140.6	141.0	141.6	142.4	143.1	143.7	144.5	144.5
115°	161.0	161.4	161.8	162.2	162.6	163.1	163.6	164.2	164.8	165.3	166.0
117.5°	182.2	182.7	183.1	183.6	184.1	184.5	184.7	185.1	185.4	185.6	186.1
120°	195.3	195.9	196.5	197.1	197.6	198.0	198.2	198.4	198.6	198.8	199.3
122.5°	208.7	209.2	209.6	210.1	210.6	210.9	211.2	211.4	211.7	211.9	212.3
125°	227.1	227.6	228.0	228.5	229.1	229.4	229.8	230.0	230.2	230.5	230.6
127.5°	244.8	245.3	245.8	246.3	246.8	247.2	247.5	247.9	248.2	248.4	248.7
130°	255.8	256.3	256.8	257.4	257.9	258.3	258.5	258.8	259.0	259.3	259.5
132.5°	266.4	266.9	267.5	268.0	268.5	268.8	269.0	269.3	269.5	269.7	269.9
135°	282.7	283.0	283.4	283.8	284.1	284.5	284.7	285.0	285.3	285.5	285.7
137.5°	296.4	296.9	297.4	297.9	298.4	298.7	298.9	299.0	299.1	299.3	299.6
140°	305.7	306.1	306.5	306.8	307.2	307.5	307.7	307.9	308.1	308.3	308.5
142.5°	314.2	314.6	315.0	315.4	315.8	316.0	316.3	316.4	316.6	316.8	317.0
145°	326.1	326.6	327.0	327.5	327.9	328.2	328.3	328.5	328.6	328.7	328.9
147.5°	337.4	337.7	337.9	338.3	338.5	338.8	338.9	339.0	339.2	339.2	339.4
150°	344.3	344.5	344.6	344.9	345.0	345.2	345.4	345.4	345.6	345.7	345.8
152.5°	350.5	350.6	350.7	350.7	350.8	351.0	351.0	351.1	351.1	351.2	351.5
155°	359.3	359.1	359.0	358.9	358.7	358.7	358.8	358.8	358.9	359.0	359.3
157.5°	366.1	366.1	366.1	366.0	366.0	366.0	365.9	365.8	365.7	365.7	366.1
160°	370.2	370.1	370.1	370.0	370.0	369.9	369.8	369.7	369.7	369.7	370.0
162.5°	374.1	374.0	373.8	373.7	373.5	373.3	373.2	373.2	373.2	373.1	373.5
165°	378.9	378.6	378.5	378.3	378.1	378.0	377.9	377.8	377.7	377.7	378.2
167.5°	382.5	382.3	382.0	381.8	381.5	381.4	381.4	381.4	381.4	381.4	381.9
170°	384.6	384.3	384.1	383.8	383.6	383.4	383.4	383.4	383.4	383.4	384.0
172.5°	386.0	385.7	385.4	385.1	384.7	384.7	384.7	384.7	384.8	384.8	385.4
175°	387.8	387.4	387.1	386.9	386.5	386.4	386.5	386.5	386.5	386.6	387.1
177.5°	388.2	388.0	387.8	387.5	387.2	387.1	387.2	387.2	387.3	387.3	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P332303-930

CATALOG NUMBER: S123RDIP-S775D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1048.4	1050.1	1051.7	1052.5	1052.1	1051.8	1051.5	1051.2
5°	1041.5	1043.2	1044.9	1045.5	1045.2	1044.8	1044.4	1044.1
7.5°	1026.9	1027.8	1028.7	1028.9	1028.3	1027.6	1027.0	1026.3
10°	1013.7	1013.9	1014.1	1013.7	1012.8	1011.8	1010.9	1009.9
12.5°	997.4	997.3	997.2	996.5	995.5	994.3	993.3	992.1
15°	968.7	967.8	966.9	965.7	964.4	963.0	961.7	960.4
17.5°	934.5	932.5	930.5	928.5	926.5	924.5	922.6	920.6
20°	911.1	908.6	906.1	903.8	901.5	899.2	896.9	894.6
22.5°	886.0	882.9	879.8	877.2	875.1	872.9	870.8	868.7
25°	844.9	840.9	836.9	833.9	831.8	829.6	827.6	825.5
27.5°	800.1	794.6	789.0	784.6	781.5	778.3	775.1	771.9
30°	768.3	761.7	755.3	750.6	747.5	744.5	741.4	738.4
32.5°	736.9	729.9	722.8	717.7	714.5	711.3	708.2	705.0
35°	690.6	682.4	674.3	668.5	665.0	661.6	658.2	654.8
37.5°	640.7	631.4	622.2	615.5	611.2	607.0	602.8	598.6
40°	606.0	596.1	586.3	579.2	574.8	570.5	566.1	561.7
42.5°	572.7	562.0	551.2	543.9	540.0	536.1	532.1	528.2
45°	523.9	513.1	502.2	494.6	490.0	485.4	480.9	476.4
47.5°	473.3	461.5	449.8	441.9	437.8	433.7	429.7	425.7
50°	439.2	427.4	415.6	407.6	403.2	398.8	394.5	390.1
52.5°	406.2	394.0	381.7	373.7	369.7	365.8	361.9	358.0
55°	357.0	346.0	335.0	327.6	323.8	320.0	316.3	312.4
57.5°	308.8	298.3	288.0	281.1	277.9	274.7	271.4	268.2
60°	278.3	268.1	257.8	251.1	247.9	244.6	241.4	238.1
62.5°	248.1	238.5	228.9	222.3	218.9	215.6	212.2	208.8
65°	205.0	195.8	186.5	180.8	178.7	176.6	174.6	172.4
67.5°	164.0	157.1	150.1	145.5	143.3	141.0	138.8	136.6
70°	138.7	132.0	125.4	121.1	119.0	116.8	114.8	112.7
72.5°	115.9	110.4	105.0	101.8	100.9	100.1	99.2	98.3
75°	86.7	84.8	82.9	81.8	81.4	81.0	80.6	80.2
77.5°	65.4	64.3	63.3	62.6	62.3	61.9	61.5	61.1
80°	52.7	52.1	51.5	51.0	50.6	50.3	49.9	49.5
82.5°	40.4	39.8	39.2	38.9	38.8	38.7	38.6	38.6
85°	23.2	22.7	22.4	22.2	22.2	22.2	22.2	22.2
87.5°	10.0	9.9	9.9	9.8	9.6	9.5	9.4	9.2
90°	7.4	7.7	7.9	8.2	8.2	8.4	8.5	8.6
92.5°	8.2	8.6	9.0	9.3	9.3	9.4	9.5	9.5
95°	9.9	10.3	10.8	10.9	10.9	10.9	10.9	10.9
97.5°	10.3	10.8	11.3	11.6	11.7	11.7	11.8	11.9
100°	10.5	11.0	11.6	11.8	11.9	12.0	12.1	12.1
102.5°	15.8	14.2	12.6	11.9	12.0	12.1	12.2	12.3
105°	40.4	29.1	17.8	12.1	12.3	12.4	12.6	12.6
107.5°	99.1	90.7	82.4	73.9	65.5	56.9	48.3	39.8
110°	125.7	123.6	121.5	115.9	106.7	97.5	88.4	79.2



TEST NUMBER: P332303-930

CATALOG NUMBER: S123RDIP-S775D365U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	144.6	144.6	144.6	143.7	141.7	139.8	137.9	135.9
115°	166.6	167.3	168.0	168.4	168.6	168.9	169.2	169.4
117.5°	186.7	187.2	187.7	188.0	188.0	188.1	188.2	188.2
120°	199.8	200.3	200.8	201.1	201.1	201.1	201.1	201.1
122.5°	212.6	213.0	213.4	213.5	213.6	213.7	213.7	213.8
125°	230.7	230.9	231.0	231.1	231.2	231.4	231.5	231.6
127.5°	248.8	249.1	249.3	249.3	249.2	249.1	248.9	248.8
130°	259.8	260.1	260.3	260.4	260.2	260.2	260.0	259.8
132.5°	270.2	270.4	270.7	270.8	270.5	270.4	270.2	270.0
135°	285.9	286.1	286.3	286.3	286.1	285.9	285.7	285.5
137.5°	299.9	300.2	300.5	300.6	300.4	300.4	300.2	300.1
140°	308.8	309.0	309.3	309.3	309.2	309.1	309.0	308.8
142.5°	317.2	317.4	317.6	317.6	317.5	317.2	317.1	316.9
145°	329.0	329.1	329.2	329.3	329.3	329.3	329.3	329.3
147.5°	339.5	339.7	339.8	339.7	339.4	339.1	338.8	338.5
150°	346.0	346.1	346.3	346.2	346.0	345.8	345.6	345.4
152.5°	351.7	352.0	352.2	352.1	351.9	351.6	351.2	351.0
155°	359.6	360.0	360.3	360.2	359.9	359.5	359.1	358.7
157.5°	366.5	366.9	367.3	367.2	366.7	366.2	365.7	365.2
160°	370.4	370.8	371.2	371.1	370.7	370.2	369.8	369.3
162.5°	374.0	374.4	374.8	374.9	374.5	374.1	373.7	373.2
165°	378.7	379.3	379.8	379.8	379.4	378.9	378.5	378.0
167.5°	382.4	382.9	383.4	383.4	382.9	382.4	381.9	381.4
170°	384.5	385.0	385.5	385.5	385.0	384.5	384.0	383.4
172.5°	385.9	386.4	386.9	386.9	386.3	385.7	385.1	384.6
175°	387.5	388.0	388.4	388.4	387.9	387.3	386.9	386.4
177.5°	388.2	388.6	389.0	388.9	388.4	387.9	387.3	386.9
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8

(END OF REPORT)