

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332257-935

Luminaire Tested: **S123RDIP-S340D805U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332257-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U935-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3621.9 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332257-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332257-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31						31														
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	26						26														
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	22						22														
3	78	69	62	56	70	62	56	52	50	46	42	38	35	33	27	25	24	19						19														
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17						17														
5	65	54	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	15						15														
6	60	49	41	35	54	44	37	33	36	31	27	28	24	21	20	18	16	13						13														
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	18	16	14	11						11														
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	10						10														
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	9						9														
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	9						9														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5324	5324	5324
5°	5344	5271	5302
10°	5314	5205	5187
15°	5258	5084	5029
20°	5179	4931	4816
25°	5099	4760	4608
30°	4992	4561	4313
35°	4882	4365	4043
40°	4780	4131	3710
45°	4647	3902	3408
50°	4501	3641	3069
55°	4352	3342	2755
60°	4215	3023	2409
65°	4037	2677	2063
70°	3811	2247	1668
75°	3489	1768	1568
80°	3106	1568	1438
85°	2631	1383	1284



TEST NUMBER: P332257-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	1.3
10°-20°	129.2	3.6
20°-30°	186.1	5.1
30°-40°	209.6	5.8
40°-50°	200.5	5.5
50°-60°	164.2	4.5
60°-70°	110.8	3.1
70°-80°	55.7	1.5
80°-90°	17.3	0.5
90°-100°	185.1	5.1
100°-110°	524.0	14.5
110°-120°	515.5	14.2
120°-130°	411.2	11.4
130°-140°	324.2	9.0
140°-150°	242.0	6.7
150°-160°	168.6	4.7
160°-170°	99.1	2.7
170°-180°	32.2	0.9
0°-30°	361.8	10.0
0°-40°	571.4	15.8
0°-60°	936.2	25.8
0°-90°	1120.0	30.9
90°-120°	1224.6	33.8
90°-150°	2201.9	60.8
90°-180°	2502.0	69.1
0°-180°	3621.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	495	495	495	495	495	
5°	495	492	488	491	491	47
15°	472	467	456	454	451	133
25°	429	419	401	393	388	197
35°	372	356	332	315	308	232
45°	305	286	256	234	224	235
55°	232	211	178	156	147	208
65°	158	136	105	86	81	157
75°	84	64	42	39	38	89
85°	21	13	11	10	10	24
90°	1	8	17	19	20	3
95°	23	74	399	116	78	25
105°	78	115	541	946	856	83
115°	138	172	414	908	1041	137
125°	192	226	386	700	821	170
135°	225	268	381	576	666	174
145°	256	294	376	473	520	161
155°	291	314	364	414	431	134
165°	318	327	349	370	376	90
175°	332	332	335	339	339	32
180°	332	332	332	332	332	



TEST NUMBER: P332257-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	496.3	495.9	495.7	495.4	495.2	494.6	493.7	492.8	492.0	491.1	491.9
5°	494.6	494.2	493.8	493.4	492.8	492.1	491.0	490.0	488.9	487.8	488.6
7.5°	490.1	489.6	489.1	488.6	488.2	487.2	485.9	484.5	483.0	481.6	482.1
10°	486.2	485.6	485.0	484.4	483.7	482.6	481.0	479.4	477.8	476.2	476.3
12.5°	480.8	480.1	479.4	478.7	478.0	476.6	474.7	472.8	470.8	468.8	468.7
15°	471.8	470.8	469.8	468.8	467.9	466.1	463.6	461.2	458.7	456.2	455.7
17.5°	460.5	459.3	458.2	457.0	455.9	453.7	450.6	447.4	444.3	441.1	440.1
20°	452.1	450.7	449.3	447.9	446.4	444.0	440.7	437.2	433.9	430.5	429.3
22.5°	442.8	441.2	439.5	437.9	436.3	433.7	430.1	426.5	422.8	419.2	417.8
25°	429.3	427.1	424.8	422.6	420.3	417.2	413.1	409.0	404.8	400.8	398.9
27.5°	412.8	410.4	407.9	405.4	402.9	399.5	394.9	390.3	385.7	381.2	378.6
30°	401.6	398.9	396.2	393.6	390.9	387.0	382.0	377.0	372.0	367.0	364.0
32.5°	390.4	387.3	384.3	381.3	378.2	374.1	368.8	363.5	358.3	352.9	349.7
35°	371.5	368.2	365.1	361.9	358.7	354.3	348.8	343.2	337.7	332.2	328.4
37.5°	352.4	348.8	345.3	341.7	338.1	333.4	327.5	321.6	315.7	309.8	305.5
40°	340.2	336.3	332.3	328.5	324.5	319.3	313.1	306.7	300.4	294.0	289.5
42.5°	326.4	322.4	318.6	314.6	310.7	305.5	298.9	292.4	285.9	279.3	274.2
45°	305.3	301.3	297.3	293.3	289.2	283.8	277.0	270.1	263.2	256.3	251.2
47.5°	284.2	279.8	275.3	271.0	266.6	261.0	254.1	247.2	240.4	233.5	228.0
50°	268.8	264.6	260.5	256.2	252.0	246.3	239.1	231.9	224.6	217.4	211.9
52.5°	255.0	250.5	245.9	241.3	236.8	230.9	223.8	216.6	209.5	202.3	196.7
55°	231.9	227.5	223.2	218.8	214.4	208.4	200.9	193.3	185.7	178.1	173.0
57.5°	210.5	205.8	201.0	196.2	191.5	185.3	177.7	170.0	162.5	154.9	150.0
60°	195.8	190.9	186.0	181.1	176.2	170.0	162.6	155.2	147.8	140.4	135.6
62.5°	181.0	176.1	171.2	166.3	161.4	155.2	147.8	140.4	133.0	125.6	121.1
65°	158.5	153.6	148.7	143.8	138.9	132.9	126.0	119.0	112.1	105.1	100.7
67.5°	136.0	131.0	126.0	121.1	116.1	110.3	103.6	96.9	90.2	83.6	80.3
70°	121.1	116.3	111.5	106.7	101.9	96.3	90.1	83.9	77.7	71.4	68.3
72.5°	106.4	101.7	96.9	92.1	87.4	82.2	76.5	70.9	65.2	59.5	57.0
75°	83.9	79.6	75.3	71.0	66.7	62.2	57.3	52.3	47.4	42.5	41.7
77.5°	63.3	59.4	55.5	51.7	47.9	44.3	41.2	38.0	34.9	31.7	31.3
80°	50.1	46.5	42.9	39.2	35.6	32.8	30.9	29.0	27.1	25.3	25.0
82.5°	37.6	34.4	31.3	28.2	25.0	23.0	22.1	21.3	20.4	19.5	19.2
85°	21.3	19.3	17.3	15.4	13.4	12.3	12.1	11.8	11.5	11.2	11.0
87.5°	8.0	7.5	7.0	6.5	6.0	5.9	6.3	6.7	7.1	7.6	7.3
90°	1.4	2.7	4.0	6.0	7.4	8.8	10.8	12.8	14.8	16.8	16.2
92.5°	8.4	12.4	18.1	23.3	28.9	38.9	56.6	85.5	113.9	103.5	78.1
95°	22.9	24.9	32.3	43.7	61.2	87.5	144.7	245.0	355.4	399.2	323.8
97.5°	39.0	39.7	45.5	55.4	72.7	101.1	155.8	268.9	452.9	618.6	661.9
100°	49.9	50.5	55.2	64.7	80.8	107.0	154.1	253.7	430.8	637.5	770.1
102.5°	61.1	62.3	66.5	75.4	90.0	114.0	156.3	240.8	398.5	602.4	775.5
105°	78.1	80.1	84.1	92.2	105.0	125.9	162.2	231.5	358.8	541.2	734.4
107.5°	96.1	98.2	102.0	109.9	122.0	141.4	173.2	230.9	333.5	487.1	662.5
110°	109.1	111.1	114.4	121.8	133.3	152.1	182.4	233.6	323.8	456.4	617.3



TEST NUMBER: P332257-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	120.9	123.0	126.3	133.7	145.2	163.4	191.6	238.9	318.4	435.9	578.0
115°	138.0	140.7	144.7	151.4	162.9	181.1	206.6	247.7	316.4	414.0	530.5
117.5°	155.1	158.2	161.5	167.7	180.6	197.3	222.7	259.3	317.6	401.1	501.8
120°	166.9	168.9	172.3	179.1	191.8	208.7	232.9	267.9	319.8	395.1	486.7
122.5°	177.2	179.2	182.5	189.9	202.1	220.0	243.7	276.0	323.5	391.4	474.3
125°	191.8	193.2	197.3	204.7	217.4	235.6	259.2	288.8	329.2	386.4	458.4
127.5°	203.0	205.0	210.0	217.6	231.7	249.9	272.6	299.3	335.6	384.0	444.4
130°	210.0	212.1	218.1	226.2	240.3	258.5	280.7	306.3	339.9	382.4	436.9
132.5°	215.4	218.0	224.5	234.3	248.4	266.0	287.7	312.7	343.2	381.8	429.9
135°	224.8	227.6	235.0	245.0	259.2	277.3	298.2	321.1	348.0	381.0	420.7
137.5°	233.7	236.5	243.8	254.6	268.5	285.4	305.5	327.3	351.3	379.5	412.8
140°	239.6	243.0	249.8	260.5	274.0	290.8	310.3	330.5	353.4	379.0	407.9
142.5°	246.1	248.9	256.2	265.9	279.4	295.1	314.1	333.7	355.0	377.9	403.6
145°	256.5	258.5	264.6	274.7	286.1	301.6	319.1	337.3	356.1	376.3	397.9
147.5°	267.0	268.2	274.1	282.8	293.9	307.1	323.1	339.4	356.1	373.8	392.2
150°	274.0	274.7	280.0	288.8	298.2	310.3	325.8	339.9	356.1	371.6	388.4
152.5°	280.9	281.1	286.5	294.2	302.5	314.1	327.4	341.0	354.5	368.9	384.1
155°	291.4	291.4	295.5	302.2	309.6	319.1	330.5	341.3	352.8	364.2	377.6
157.5°	299.8	300.3	303.6	309.5	315.8	323.1	332.3	342.0	350.4	360.0	370.4
160°	306.3	306.3	309.0	314.4	319.1	325.8	333.9	342.0	349.4	356.8	365.5
162.5°	311.2	311.2	313.3	317.6	321.8	327.4	334.4	341.4	347.2	353.5	360.7
165°	318.4	317.7	319.1	322.4	325.1	329.8	335.2	339.9	344.0	348.7	354.0
167.5°	323.9	323.1	323.8	326.3	328.2	331.2	335.1	338.9	340.8	343.9	347.8
170°	327.2	325.8	326.5	328.5	329.8	331.2	334.6	337.3	338.6	340.6	344.0
172.5°	329.3	328.5	328.6	330.1	330.9	331.7	334.6	336.7	337.0	337.9	340.2
175°	331.8	331.2	330.5	331.8	331.8	332.5	333.9	335.2	334.6	334.6	335.9
177.5°	333.0	332.5	332.0	332.5	332.5	332.5	333.0	334.2	333.0	332.5	333.0
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332257-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	492.7	493.4	494.3	494.6	494.5	494.3	494.1	494.0
5°	489.5	490.3	491.0	491.4	491.2	491.0	490.9	490.7
7.5°	482.6	483.0	483.5	483.5	483.2	482.9	482.6	482.3
10°	476.4	476.5	476.6	476.4	476.0	475.5	475.0	474.6
12.5°	468.7	468.6	468.6	468.3	467.8	467.3	466.7	466.2
15°	455.2	454.8	454.3	453.8	453.2	452.5	451.9	451.3
17.5°	439.2	438.2	437.3	436.4	435.4	434.5	433.6	432.7
20°	428.2	427.0	425.9	424.7	423.6	422.6	421.5	420.4
22.5°	416.4	414.9	413.5	412.2	411.2	410.3	409.2	408.3
25°	397.0	395.2	393.3	391.8	390.9	389.9	388.9	388.0
27.5°	376.0	373.4	370.8	368.8	367.2	365.8	364.3	362.7
30°	361.0	358.0	355.0	352.8	351.3	349.9	348.4	347.0
32.5°	346.3	343.0	339.7	337.3	335.8	334.3	332.8	331.3
35°	324.5	320.6	316.8	314.1	312.5	310.9	309.3	307.7
37.5°	301.1	296.7	292.4	289.2	287.2	285.2	283.3	281.3
40°	284.8	280.2	275.5	272.2	270.1	268.1	266.0	264.0
42.5°	269.1	264.2	259.1	255.6	253.7	251.9	250.1	248.2
45°	246.2	241.1	236.0	232.4	230.3	228.2	226.0	223.9
47.5°	222.4	216.9	211.4	207.7	205.8	203.9	201.9	200.0
50°	206.4	200.9	195.4	191.6	189.5	187.4	185.4	183.3
52.5°	190.9	185.1	179.4	175.6	173.7	171.9	170.1	168.2
55°	167.8	162.6	157.5	153.9	152.2	150.4	148.6	146.8
57.5°	145.1	140.2	135.3	132.1	130.6	129.1	127.6	126.1
60°	130.8	126.0	121.1	118.0	116.5	114.9	113.5	111.9
62.5°	116.6	112.1	107.5	104.4	102.9	101.3	99.7	98.2
65°	96.3	92.0	87.6	85.0	83.9	83.0	82.1	81.0
67.5°	77.1	73.8	70.5	68.4	67.3	66.3	65.3	64.2
70°	65.2	62.1	58.9	56.9	55.9	54.9	53.9	53.0
72.5°	54.4	51.9	49.3	47.9	47.4	47.0	46.7	46.2
75°	40.7	39.9	38.9	38.4	38.2	38.1	37.9	37.7
77.5°	30.7	30.2	29.8	29.4	29.3	29.1	28.9	28.8
80°	24.7	24.5	24.2	24.0	23.8	23.6	23.4	23.2
82.5°	18.9	18.7	18.4	18.3	18.3	18.2	18.2	18.2
85°	10.8	10.7	10.5	10.4	10.4	10.4	10.4	10.4
87.5°	7.4	7.5	7.5	7.7	7.5	7.6	7.7	7.4
90°	16.8	17.5	18.2	19.5	18.9	19.5	20.2	19.5
92.5°	56.7	44.9	39.7	36.2	35.0	33.0	33.7	32.5
95°	242.4	164.3	128.5	104.4	91.5	85.5	80.8	78.1
97.5°	604.1	483.9	397.0	316.5	266.8	236.5	218.3	212.6
100°	793.7	739.1	660.4	564.7	496.8	447.6	421.4	422.1
102.5°	856.6	854.9	809.0	748.4	695.5	656.6	634.6	619.1
105°	875.1	942.4	955.2	937.7	906.7	881.1	859.6	856.3
107.5°	822.1	931.3	990.3	1014.3	1014.9	1006.3	998.9	992.7
110°	771.5	895.3	980.1	1027.3	1046.0	1051.5	1050.1	1048.8



TEST NUMBER: P332257-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	721.3	847.9	943.0	1003.5	1038.0	1054.7	1059.8	1060.1
115°	655.0	772.1	871.1	944.4	994.9	1024.5	1038.0	1041.4
117.5°	606.9	708.0	796.9	871.3	923.9	957.9	977.2	981.9
120°	581.6	672.4	753.3	821.2	874.4	912.1	928.2	932.3
122.5°	561.7	643.9	718.8	782.0	829.1	863.1	880.9	886.0
125°	535.1	608.6	673.1	727.0	770.1	799.7	816.5	821.2
127.5°	512.0	577.4	635.8	684.8	723.1	748.4	763.6	767.9
130°	497.5	558.0	612.6	658.3	694.1	718.2	732.4	737.8
132.5°	484.0	539.8	590.5	634.1	667.6	691.9	704.4	708.2
135°	465.8	513.6	557.3	595.7	628.7	648.9	661.0	665.7
137.5°	449.3	488.4	526.2	559.4	587.1	607.6	617.9	621.0
140°	439.5	473.9	506.2	535.1	560.8	579.5	590.4	589.7
142.5°	430.4	459.9	487.9	513.1	534.9	551.6	561.3	560.6
145°	419.4	441.6	463.1	482.7	499.5	513.6	519.0	520.3
147.5°	410.4	428.0	445.4	459.3	472.0	481.6	486.7	487.2
150°	403.9	419.4	433.5	446.3	456.4	463.8	467.9	467.9
152.5°	398.0	411.3	423.8	434.5	442.4	449.3	451.7	451.7
155°	389.1	399.8	409.9	418.0	424.0	429.5	430.8	431.4
157.5°	379.6	388.7	396.5	402.8	408.0	412.1	413.2	413.0
160°	374.3	381.7	388.4	393.1	397.9	401.8	401.8	401.2
162.5°	367.8	374.1	380.3	384.5	387.6	391.1	391.1	390.5
165°	359.5	363.5	368.2	371.6	374.3	376.9	376.3	376.3
167.5°	352.1	355.2	358.0	360.4	361.6	363.5	362.8	362.8
170°	347.3	349.4	352.1	353.4	354.0	355.4	354.7	354.7
172.5°	343.0	344.5	346.6	347.5	347.6	349.0	347.8	347.2
175°	337.3	337.9	339.2	339.2	339.2	339.9	339.2	338.6
177.5°	333.6	334.2	334.7	334.7	334.2	334.7	333.6	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5

(END OF REPORT)