

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832163

Luminaire Tested: S123RDIP-S340D805U935-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P832163  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D805U935-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3771.4 lumens  
Efficiency: N/A  
Efficacy: 114.3 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 33  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P832163

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P832163

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	36	36	29				
2	87	80	74	69	78	72	68	63	58	55	52	45	43	41	33	32	31	26				
3	79	71	64	58	71	64	58	54	52	48	44	41	38	36	30	28	27	22				
4	73	63	56	50	66	57	51	46	46	42	38	37	34	31	27	25	24	20				
5	67	56	49	43	60	51	45	40	42	37	34	33	30	27	25	23	21	18				
6	62	51	43	38	56	46	40	35	38	33	30	30	27	24	23	21	19	16				
7	57	46	38	33	52	42	36	31	35	30	26	28	24	22	21	19	17	14				
8	53	42	35	30	48	38	32	28	32	27	24	25	22	20	20	17	16	13				
9	50	38	31	26	45	35	29	25	29	25	21	24	20	18	18	16	14	12				
10	47	35	28	24	42	32	26	22	27	22	19	22	19	16	17	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	10296	10296	10296	10296	10296
5°	12225	11835	10361	8375	7775
10°	11076	12021	10309	6710	5757
15°	7626	10307	10200	5485	4553
20°	5306	7936	9995	4624	4002
25°	4043	6048	9697	4111	3689
30°	3519	4835	9324	3817	3417
35°	3231	4079	8796	3569	3169
40°	2948	3642	8106	3326	2942
45°	2662	3331	7360	3095	2716
50°	2416	3073	6482	2870	2436
55°	2186	2822	5637	2650	2091
60°	1959	2566	4898	2407	1976
65°	1808	2277	4215	2162	1867
70°	1470	1970	3679	1958	1517
75°	1289	1564	3115	1622	1339
80°	1165	1327	2554	1364	1265
85°	1062	1161	1939	1235	1161

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 7767 cd/sqm



TEST NUMBER: P832163

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.2	2.3
10°-20°	201.7	5.3
20°-30°	231.5	6.1
30°-40°	228.2	6.0
40°-50°	201.2	5.3
50°-60°	154.8	4.1
60°-70°	101.8	2.7
70°-80°	49.4	1.3
80°-90°	14.3	0.4
90°-100°	180.4	4.8
100°-110°	528.3	14.0
110°-120°	515.9	13.7
120°-130°	410.9	10.9
130°-140°	324.2	8.6
140°-150°	241.8	6.4
150°-160°	168.6	4.5
160°-170°	99.0	2.6
170°-180°	32.2	0.9
0°-30°	520.4	13.8
0°-40°	748.5	19.8
0°-60°	1104.5	29.3
0°-90°	1270.0	33.7
90°-120°	1224.6	32.5
90°-150°	2201.5	58.4
90°-180°	2501.0	66.3
0°-180°	3771.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	956	956	956	956	956	
5°	1131	1095	959	775	720	103
15°	684	925	915	492	409	193
25°	340	509	816	346	311	161
35°	246	310	669	272	241	153
45°	175	219	484	203	178	136
55°	116	150	300	141	111	104
65°	71	89	166	85	73	70
75°	31	38	75	39	32	33
85°	9	9	16	10	9	9
90°	20	17	1	17	20	11
95°	78	399	23	399	78	127
105°	856	541	78	541	856	854
115°	1041	414	138	414	1041	1016
125°	821	386	192	386	821	743
135°	666	381	225	381	666	516
145°	520	376	256	376	520	330
155°	432	364	292	364	432	201
165°	376	349	318	349	376	107
175°	339	335	332	335	339	33
180°	332	332	332	332	332	



TEST NUMBER: P832163

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5
2.5°	1060.0	1056.7	1053.4	1052.4	1051.4	1048.3	1045.1	1038.1	1031.0	1023.8	1016.5
5°	1131.4	1131.8	1132.2	1131.2	1130.2	1126.1	1122.0	1113.4	1104.7	1095.3	1085.9
7.5°	1109.5	1115.7	1122.0	1123.2	1124.4	1127.5	1130.6	1128.7	1126.7	1123.2	1119.6
10°	1013.4	1013.0	1012.6	1019.6	1026.7	1047.7	1068.7	1079.5	1090.2	1099.8	1109.5
12.5°	856.5	857.1	857.7	880.8	904.0	923.8	943.6	971.0	998.5	1028.1	1057.7
15°	684.3	693.9	703.6	724.1	744.7	774.5	804.3	841.2	878.1	924.9	971.8
17.5°	562.0	566.1	570.2	590.0	609.8	638.1	666.3	708.1	749.8	810.2	870.6
20°	463.2	466.9	470.6	484.9	499.2	526.3	553.4	593.2	633.0	692.8	752.6
22.5°	386.7	393.9	401.2	410.8	420.4	440.0	459.6	500.2	540.8	595.3	649.8
25°	340.4	343.7	347.1	355.3	363.5	382.4	401.2	428.1	454.9	509.2	563.6
27.5°	309.0	310.0	311.0	317.1	323.1	335.3	347.5	372.4	397.3	442.0	486.7
30°	283.1	284.9	286.7	291.4	296.1	304.9	313.7	331.4	349.0	389.0	429.0
32.5°	263.1	264.1	265.1	269.0	273.0	279.4	285.9	299.8	313.7	344.3	374.9
35°	245.9	246.1	246.3	249.2	252.2	258.4	264.7	276.3	287.9	310.4	333.0
37.5°	226.3	227.7	229.0	231.2	233.3	238.8	244.3	253.7	263.1	281.8	300.4
40°	209.8	211.0	212.2	214.7	217.3	221.6	225.9	234.5	243.1	259.2	275.3
42.5°	193.3	194.1	194.9	197.5	200.0	205.3	210.6	217.5	224.3	237.7	251.0
45°	174.9	176.9	178.8	181.6	184.3	188.8	193.3	200.4	207.5	218.8	230.2
47.5°	159.6	160.6	161.6	163.9	166.3	171.8	177.3	183.5	189.8	200.4	211.0
50°	144.3	144.7	145.1	147.3	149.4	154.3	159.2	166.5	173.7	183.5	193.3
52.5°	129.8	130.8	131.8	133.9	136.1	139.4	142.8	150.2	157.7	167.3	176.9
55°	116.5	117.1	117.7	119.2	120.8	124.7	128.6	135.1	141.6	150.4	159.2
57.5°	103.9	104.7	105.5	106.7	107.8	111.4	114.9	120.6	126.3	135.1	143.9
60°	91.0	92.0	92.9	94.3	95.7	98.4	101.2	106.3	111.4	119.2	127.1
62.5°	81.6	81.8	82.0	83.1	84.3	86.3	88.2	92.4	96.5	104.3	112.2
65°	71.0	71.6	72.2	72.7	73.3	74.9	76.5	80.0	83.5	89.4	95.3
67.5°	60.0	60.6	61.2	62.2	63.1	64.5	65.9	68.2	70.6	76.1	81.6
70°	46.7	46.7	46.7	48.2	49.8	52.2	54.5	56.3	58.0	62.6	67.1
72.5°	38.0	38.2	38.4	38.6	38.8	40.2	41.6	44.5	47.5	50.2	52.9
75°	31.0	31.2	31.4	31.6	31.8	32.2	32.6	33.5	34.5	37.6	40.8
77.5°	24.7	24.9	25.1	25.3	25.5	25.9	26.3	26.7	27.1	28.2	29.4
80°	18.8	19.0	19.2	19.4	19.6	19.8	20.0	20.4	20.8	21.4	22.0
82.5°	13.7	13.7	13.7	13.7	13.7	14.1	14.5	14.5	14.5	14.9	15.3
85°	8.6	8.6	8.6	8.8	9.0	9.0	9.0	9.2	9.4	9.4	9.4
87.5°	3.9	3.7	3.5	3.7	3.9	3.9	3.9	4.1	4.3	4.3	4.3
90°	19.5	20.2	19.5	18.8	19.5	18.2	17.5	16.8	16.2	16.8	14.8
92.5°	35.7	37.0	36.3	39.0	40.4	45.1	51.8	66.6	93.6	125.2	138.7
95°	78.1	80.8	85.5	91.5	104.3	128.6	164.2	242.3	323.8	399.2	355.4
97.5°	160.2	167.6	183.8	209.3	254.4	331.2	420.0	556.7	634.8	613.9	458.4
100°	422.1	421.4	447.6	496.8	564.8	660.4	739.1	793.6	770.1	637.5	430.8
102.5°	668.4	688.0	708.8	745.2	794.3	846.1	883.8	872.4	776.8	593.7	390.4
105°	856.2	859.6	881.1	906.7	937.7	955.2	942.4	875.1	734.4	541.2	358.8
107.5°	978.8	986.2	994.9	1007.0	1011.1	992.9	940.4	834.7	673.8	494.8	335.9
110°	1048.8	1050.1	1051.5	1046.1	1027.2	980.1	895.3	771.4	617.3	456.4	323.8



TEST NUMBER: P832163

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1062.9	1062.2	1055.5	1036.0	997.6	933.7	836.0	708.8	568.1	430.8	317.1
115°	1041.4	1038.0	1024.5	994.9	944.4	871.0	772.1	655.0	530.4	414.0	316.4
117.5°	994.2	989.5	969.3	936.3	883.8	807.8	716.9	613.2	505.5	402.5	317.1
120°	932.3	928.3	912.1	874.4	821.2	753.2	672.5	581.6	486.7	395.1	319.7
122.5°	874.4	869.0	850.9	817.9	772.1	710.2	636.8	556.7	471.2	390.4	324.5
125°	821.2	816.5	799.7	770.1	727.0	673.1	608.5	535.2	458.4	386.4	329.2
127.5°	775.5	771.4	755.9	730.4	691.3	641.5	582.3	515.6	446.3	384.4	334.6
130°	737.8	732.4	718.2	694.0	658.3	612.6	558.0	497.5	436.9	382.3	339.9
132.5°	700.7	697.4	685.3	661.0	628.0	585.0	535.2	480.6	428.1	381.7	344.0
135°	665.7	661.0	648.9	628.7	595.7	557.4	513.6	465.8	420.7	381.0	348.0
137.5°	628.7	624.7	614.6	593.7	565.4	531.1	492.1	451.7	414.0	379.7	350.7
140°	589.7	590.3	579.6	560.7	535.2	506.2	473.9	439.6	407.9	379.0	353.4
142.5°	553.3	554.0	544.6	528.4	507.6	483.3	456.4	428.1	402.5	377.6	355.4
145°	520.3	519.0	513.6	499.5	482.6	463.1	441.6	419.4	397.8	376.3	356.1
147.5°	492.1	491.4	486.0	475.9	462.5	448.3	430.1	412.0	393.1	374.3	356.1
150°	467.8	467.8	463.8	456.4	446.3	433.5	419.4	403.9	388.4	371.6	356.1
152.5°	447.6	447.6	445.6	438.9	431.5	421.4	409.3	396.5	383.0	368.2	354.1
155°	431.5	430.8	429.5	424.1	418.0	409.9	399.8	389.1	377.6	364.2	352.7
157.5°	416.0	416.0	414.7	410.6	405.2	398.5	390.4	381.0	371.6	360.8	350.7
160°	401.2	401.9	401.9	397.8	393.1	388.4	381.7	374.3	365.5	356.8	349.4
162.5°	387.7	388.4	388.4	385.0	382.3	378.3	372.2	366.2	359.5	352.7	346.7
165°	376.3	376.3	377.0	374.3	371.6	368.2	363.5	359.5	354.1	348.7	344.0
167.5°	364.8	364.8	365.5	363.5	362.2	359.5	356.8	353.4	348.7	344.7	341.3
170°	354.7	354.7	355.4	354.1	353.4	352.1	349.4	347.3	344.0	340.6	338.6
172.5°	345.3	346.0	347.3	346.0	346.0	345.3	343.3	342.0	339.3	337.2	336.6
175°	338.6	339.3	339.9	339.3	339.3	339.3	337.9	337.2	335.9	334.6	334.6
177.5°	333.9	333.9	335.2	334.6	335.2	335.2	334.6	333.9	333.2	332.5	333.2
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P832163

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5
2.5°	1015.5	1014.5	1005.1	995.7	986.5	977.3	970.4	963.6	952.0	940.4	933.2
5°	1078.5	1071.0	1056.1	1041.2	1018.9	996.5	977.7	958.9	934.9	911.0	891.0
7.5°	1113.6	1107.5	1089.5	1071.4	1041.8	1012.2	982.8	953.4	918.1	882.8	852.6
10°	1114.6	1119.6	1104.7	1089.8	1056.5	1023.2	983.2	943.2	895.7	848.3	809.2
12.5°	1079.6	1101.6	1098.5	1095.3	1061.4	1027.5	978.9	930.2	872.0	813.8	764.9
15°	1014.4	1056.9	1069.5	1082.0	1054.0	1025.9	970.6	915.3	846.9	778.5	722.4
17.5°	930.2	989.8	1023.0	1056.1	1035.7	1015.3	954.7	894.2	817.1	740.0	679.0
20°	830.6	908.7	960.6	1012.6	1005.1	997.7	935.1	872.6	789.4	706.3	640.2
22.5°	732.2	814.5	886.3	958.1	965.7	973.4	910.2	847.1	756.1	665.1	597.9
25°	647.3	731.0	816.5	902.0	919.3	936.5	876.5	816.5	722.2	627.9	561.0
27.5°	566.3	645.9	740.0	834.1	865.5	896.9	842.0	787.1	688.8	590.6	523.9
30°	500.2	571.4	667.5	763.6	807.3	851.0	800.6	750.2	652.8	555.3	490.0
32.5°	438.6	502.4	598.8	695.3	746.1	796.9	753.4	709.8	616.1	522.4	457.9
35°	390.0	447.1	537.1	627.1	683.9	740.8	705.1	669.4	577.9	486.3	425.3
37.5°	348.2	396.1	480.6	565.1	625.5	685.9	656.1	626.3	540.2	454.1	396.5
40°	313.7	352.2	430.8	509.4	568.6	627.9	602.4	576.9	499.8	422.8	368.8
42.5°	284.1	317.3	387.9	458.4	512.8	567.1	550.2	533.4	463.5	393.7	343.7
45°	258.0	285.9	348.1	410.2	460.2	510.2	496.9	483.5	423.3	363.2	317.3
47.5°	234.9	258.8	314.3	369.8	414.7	459.6	447.3	434.9	385.1	335.3	293.5
50°	213.7	234.1	280.4	326.7	367.1	407.5	397.3	387.1	345.9	304.7	268.6
52.5°	193.7	210.6	252.2	293.7	326.3	358.8	351.0	343.2	311.4	279.6	246.9
55°	174.7	190.2	225.3	260.4	288.2	316.1	308.2	300.4	275.7	251.0	222.2
57.5°	157.5	171.0	199.4	227.9	250.0	272.2	268.4	264.7	244.1	223.5	199.8
60°	139.2	151.4	175.9	200.4	218.2	236.1	231.8	227.5	212.8	198.0	177.7
62.5°	122.9	133.7	153.3	172.9	187.5	202.0	198.8	195.7	184.5	173.3	156.5
65°	105.9	116.5	132.4	148.2	159.6	171.0	168.2	165.5	157.1	148.6	135.1
67.5°	90.4	99.2	112.9	126.7	134.3	142.0	140.4	138.8	132.4	125.9	115.3
70°	74.7	82.4	93.7	105.1	110.4	115.7	116.3	116.9	111.0	105.1	97.3
72.5°	59.0	65.1	75.7	86.3	90.4	94.5	94.3	94.1	90.6	87.1	80.0
75°	45.3	49.8	58.0	66.3	69.8	73.3	74.1	74.9	71.6	68.2	64.3
77.5°	32.6	35.7	42.0	48.2	52.2	56.1	56.5	56.9	55.3	53.7	50.0
80°	22.9	23.9	27.8	31.8	35.9	40.0	40.6	41.2	39.6	38.0	35.7
82.5°	15.9	16.5	17.8	19.2	22.5	25.9	26.7	27.5	26.7	25.9	23.3
85°	9.6	9.8	10.4	11.0	12.5	14.1	14.9	15.7	15.3	14.9	13.5
87.5°	4.3	4.3	4.5	4.7	5.1	5.5	6.5	7.5	6.9	6.3	5.7
90°	12.8	10.8	8.8	7.4	6.1	4.0	2.7	1.3	2.7	4.0	6.1
92.5°	103.7	68.0	46.4	34.3	27.6	21.5	14.8	10.1	14.8	21.5	27.6
95°	245.0	144.7	87.5	61.3	43.8	32.3	24.9	22.9	24.9	32.3	43.8
97.5°	272.6	156.2	99.6	70.7	53.2	43.1	37.0	36.3	37.0	43.1	53.2
100°	253.8	154.2	107.0	80.8	64.6	55.2	50.5	49.8	50.5	55.2	64.6
102.5°	237.6	156.8	115.8	92.2	78.1	69.3	65.3	63.9	65.3	69.3	78.1
105°	231.6	162.2	125.9	105.0	92.2	84.1	80.1	78.1	80.1	84.1	92.2
107.5°	230.2	171.0	138.7	119.1	107.0	99.0	94.9	92.9	94.9	99.0	107.0
110°	233.6	182.4	152.1	133.3	121.8	114.4	111.1	109.0	111.1	114.4	121.8





TEST NUMBER: P832163

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	240.3	193.9	166.3	148.1	136.6	129.2	125.9	123.9	125.9	129.2	136.6
115°	247.7	206.7	181.1	162.9	151.5	144.7	140.7	138.0	140.7	144.7	151.5
117.5°	257.1	220.1	194.5	177.7	164.9	158.9	155.5	152.1	155.5	158.9	164.9
120°	267.9	232.9	208.7	191.8	179.1	172.3	169.0	166.9	169.0	172.3	179.1
122.5°	278.0	246.4	222.8	204.6	192.5	185.1	181.7	179.7	181.7	185.1	192.5
125°	288.8	259.2	235.6	217.4	204.6	197.2	193.2	191.8	193.2	197.2	204.6
127.5°	297.5	270.6	247.7	229.5	215.4	208.0	203.3	201.3	203.3	208.0	215.4
130°	306.3	280.7	258.5	240.3	226.2	218.1	212.0	210.0	212.0	218.1	226.2
132.5°	314.4	289.5	267.9	250.4	236.3	226.2	219.4	216.8	219.4	226.2	236.3
135°	321.1	298.2	277.3	259.2	245.0	234.9	227.5	224.8	227.5	234.9	245.0
137.5°	326.5	304.3	284.1	267.2	253.1	242.3	234.9	232.2	234.9	242.3	253.1
140°	330.5	310.3	290.8	274.0	260.5	249.7	243.0	239.6	243.0	249.7	260.5
142.5°	334.6	315.0	296.2	280.7	267.2	257.8	250.4	247.7	250.4	257.8	267.2
145°	337.2	319.1	301.6	286.1	274.6	264.5	258.5	256.5	258.5	264.5	274.6
147.5°	339.3	322.4	306.3	292.8	281.4	272.6	266.6	265.2	266.6	272.6	281.4
150°	339.9	325.8	310.3	298.2	288.8	280.0	274.6	274.0	274.6	280.0	288.8
152.5°	341.3	327.8	315.0	303.6	295.5	288.1	282.7	282.7	282.7	288.1	295.5
155°	341.3	330.5	319.1	309.6	302.2	295.5	291.5	291.5	291.5	295.5	302.2
157.5°	342.0	331.9	322.4	315.0	308.3	302.2	298.9	298.2	298.9	302.2	308.3
160°	342.0	333.9	325.8	319.1	314.4	309.0	306.3	306.3	306.3	309.0	314.4
162.5°	341.3	334.6	327.8	322.4	318.4	314.4	312.3	312.3	312.3	314.4	318.4
165°	339.9	335.2	329.8	325.1	322.4	319.1	317.7	318.4	317.7	319.1	322.4
167.5°	339.3	335.2	331.2	327.8	325.8	323.1	322.4	323.1	322.4	323.1	325.8
170°	337.2	334.6	331.2	329.8	328.5	326.5	325.8	327.1	325.8	326.5	328.5
172.5°	336.6	334.6	331.9	331.2	330.5	329.2	329.2	329.8	329.2	329.2	330.5
175°	335.2	333.9	332.5	331.9	331.9	330.5	331.2	331.9	331.2	330.5	331.9
177.5°	334.6	333.2	332.5	332.5	332.5	331.9	332.5	333.2	332.5	331.9	332.5
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P832163

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5	956.5
2.5°	925.9	914.7	903.6	895.5	887.5	877.5	867.5	867.1	866.7	859.2	851.8
5°	871.0	851.6	832.2	813.2	794.1	775.1	756.1	751.8	747.5	741.0	734.5
7.5°	822.4	791.4	760.4	736.1	711.8	692.8	673.8	660.8	647.9	637.9	627.9
10°	770.2	731.8	693.4	663.9	634.5	613.9	593.4	578.5	563.6	556.5	549.4
12.5°	716.1	674.3	632.6	603.7	574.9	550.2	525.5	512.0	498.5	488.6	478.8
15°	666.3	621.4	576.5	545.9	515.3	492.2	469.0	455.5	442.0	432.2	422.4
17.5°	618.1	572.8	527.5	496.5	465.5	444.5	423.5	410.4	397.3	391.2	385.1
20°	574.1	528.5	482.8	453.5	424.3	403.7	383.2	376.1	369.0	363.3	357.7
22.5°	530.6	486.7	442.8	414.7	386.7	371.8	356.9	351.2	345.5	341.2	336.9
25°	494.1	450.4	406.7	382.2	357.7	346.1	334.5	330.8	327.1	322.8	318.4
27.5°	457.3	415.7	374.1	354.5	334.9	325.5	316.1	311.4	306.7	303.1	299.6
30°	424.7	386.3	347.9	331.6	315.3	307.1	298.8	293.7	288.6	285.3	282.0
32.5°	393.3	359.2	325.1	311.2	297.3	289.2	281.2	276.3	271.4	267.5	263.5
35°	364.3	334.7	305.1	292.4	279.6	271.6	263.5	258.6	253.7	249.8	245.9
37.5°	338.8	312.0	285.1	273.1	261.2	254.1	247.1	242.0	236.9	232.8	228.6
40°	314.9	291.2	267.5	255.9	244.3	236.7	229.0	224.5	220.0	216.3	212.6
42.5°	293.7	272.0	250.2	238.8	227.5	220.2	212.9	207.7	202.4	200.2	198.0
45°	271.4	252.2	232.9	222.0	211.0	203.3	195.7	191.2	186.7	184.7	182.8
47.5°	251.8	233.9	216.1	205.3	194.5	187.7	180.8	177.3	173.7	171.0	168.2
50°	232.6	215.3	198.0	187.7	177.3	171.4	165.5	161.2	156.9	154.9	152.9
52.5°	214.1	198.4	182.8	172.2	161.6	155.9	150.2	146.5	142.8	138.6	134.5
55°	193.3	179.6	165.9	156.5	147.1	141.2	135.3	131.0	126.7	122.4	118.0
57.5°	176.1	162.6	149.0	140.6	132.2	126.5	120.8	116.1	111.4	107.8	104.3
60°	157.3	145.5	133.7	125.5	117.3	111.8	106.3	101.8	97.3	95.5	93.7
62.5°	139.6	128.6	117.7	110.4	103.1	97.8	92.6	89.6	86.7	85.5	84.3
65°	121.6	112.2	102.7	96.1	89.4	84.9	80.4	79.0	77.6	76.7	75.7
67.5°	104.7	96.7	88.6	82.7	76.9	73.7	70.6	69.0	67.5	66.3	65.1
70°	89.4	82.4	75.3	70.2	65.1	62.2	59.2	57.8	56.5	54.3	52.2
72.5°	72.9	67.5	62.0	58.0	54.1	51.6	49.0	46.3	43.5	41.6	39.6
75°	60.4	54.9	49.4	45.7	42.0	39.0	36.1	35.1	34.1	33.5	32.9
77.5°	46.3	41.6	36.9	33.9	31.0	29.6	28.2	27.6	27.1	26.9	26.7
80°	33.3	29.4	25.5	23.9	22.4	22.0	21.6	21.2	20.8	20.6	20.4
82.5°	20.8	18.8	16.9	16.5	16.1	15.9	15.7	15.5	15.3	15.1	14.9
85°	12.2	11.4	10.6	10.4	10.2	10.0	9.8	9.8	9.8	9.8	9.8
87.5°	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	5.1	4.9	4.7
90°	7.4	8.8	10.8	12.8	14.8	16.8	16.2	16.8	17.5	18.2	19.5
92.5°	34.3	46.4	68.0	103.7	138.7	125.2	93.6	66.6	51.8	45.1	40.4
95°	61.3	87.5	144.7	245.0	355.4	399.2	323.8	242.3	164.2	128.6	104.3
97.5°	70.7	99.6	156.2	272.6	458.4	613.9	634.8	556.7	420.0	331.2	254.4
100°	80.8	107.0	154.2	253.8	430.8	637.5	770.1	793.6	739.1	660.4	564.8
102.5°	92.2	115.8	156.8	237.6	390.4	593.7	776.8	872.4	883.8	846.1	794.3
105°	105.0	125.9	162.2	231.6	358.8	541.2	734.4	875.1	942.4	955.2	937.7
107.5°	119.1	138.7	171.0	230.2	335.9	494.8	673.8	834.7	940.4	992.9	1011.1
110°	133.3	152.1	182.4	233.6	323.8	456.4	617.3	771.4	895.3	980.1	1027.2



TEST NUMBER: P832163

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	148.1	166.3	193.9	240.3	317.1	430.8	568.1	708.8	836.0	933.7	997.6
115°	162.9	181.1	206.7	247.7	316.4	414.0	530.4	655.0	772.1	871.0	944.4
117.5°	177.7	194.5	220.1	257.1	317.1	402.5	505.5	613.2	716.9	807.8	883.8
120°	191.8	208.7	232.9	267.9	319.7	395.1	486.7	581.6	672.5	753.2	821.2
122.5°	204.6	222.8	246.4	278.0	324.5	390.4	471.2	556.7	636.8	710.2	772.1
125°	217.4	235.6	259.2	288.8	329.2	386.4	458.4	535.2	608.5	673.1	727.0
127.5°	229.5	247.7	270.6	297.5	334.6	384.4	446.3	515.6	582.3	641.5	691.3
130°	240.3	258.5	280.7	306.3	339.9	382.3	436.9	497.5	558.0	612.6	658.3
132.5°	250.4	267.9	289.5	314.4	344.0	381.7	428.1	480.6	535.2	585.0	628.0
135°	259.2	277.3	298.2	321.1	348.0	381.0	420.7	465.8	513.6	557.4	595.7
137.5°	267.2	284.1	304.3	326.5	350.7	379.7	414.0	451.7	492.1	531.1	565.4
140°	274.0	290.8	310.3	330.5	353.4	379.0	407.9	439.6	473.9	506.2	535.2
142.5°	280.7	296.2	315.0	334.6	355.4	377.6	402.5	428.1	456.4	483.3	507.6
145°	286.1	301.6	319.1	337.2	356.1	376.3	397.8	419.4	441.6	463.1	482.6
147.5°	292.8	306.3	322.4	339.3	356.1	374.3	393.1	412.0	430.1	448.3	462.5
150°	298.2	310.3	325.8	339.9	356.1	371.6	388.4	403.9	419.4	433.5	446.3
152.5°	303.6	315.0	327.8	341.3	354.1	368.2	383.0	396.5	409.3	421.4	431.5
155°	309.6	319.1	330.5	341.3	352.7	364.2	377.6	389.1	399.8	409.9	418.0
157.5°	315.0	322.4	331.9	342.0	350.7	360.8	371.6	381.0	390.4	398.5	405.2
160°	319.1	325.8	333.9	342.0	349.4	356.8	365.5	374.3	381.7	388.4	393.1
162.5°	322.4	327.8	334.6	341.3	346.7	352.7	359.5	366.2	372.2	378.3	382.3
165°	325.1	329.8	335.2	339.9	344.0	348.7	354.1	359.5	363.5	368.2	371.6
167.5°	327.8	331.2	335.2	339.3	341.3	344.7	348.7	353.4	356.8	359.5	362.2
170°	329.8	331.2	334.6	337.2	338.6	340.6	344.0	347.3	349.4	352.1	353.4
172.5°	331.2	331.9	334.6	336.6	336.6	337.2	339.3	342.0	343.3	345.3	346.0
175°	331.9	332.5	333.9	335.2	334.6	334.6	335.9	337.2	337.9	339.3	339.3
177.5°	332.5	332.5	333.2	334.6	333.2	332.5	333.2	333.9	334.6	335.2	335.2
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5

TEST NUMBER: P832163

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	956.5	956.5	956.5	956.5
2.5°	849.8	847.9	847.1	846.3
5°	728.5	722.4	721.0	719.6
7.5°	625.3	622.8	614.3	605.9
10°	541.6	533.7	530.2	526.7
12.5°	471.6	464.3	463.2	462.0
15°	417.3	412.2	410.4	408.6
17.5°	381.6	378.1	375.9	373.7
20°	355.1	352.6	351.0	349.4
22.5°	334.9	333.0	331.8	330.6
25°	315.5	312.6	311.6	310.6
27.5°	297.1	294.5	293.5	292.6
30°	279.8	277.7	276.3	274.9
32.5°	261.0	258.4	257.7	256.9
35°	244.3	242.8	242.0	241.2
37.5°	226.7	224.7	223.5	222.4
40°	211.6	210.6	210.0	209.4
42.5°	196.3	194.5	194.3	194.1
45°	181.0	179.2	178.8	178.4
47.5°	166.7	165.1	164.9	164.7
50°	150.8	148.6	147.1	145.5
52.5°	132.6	130.6	129.2	127.8
55°	115.9	113.7	112.6	111.4
57.5°	103.3	102.4	101.8	101.2
60°	93.1	92.6	92.2	91.8
62.5°	83.7	83.1	83.1	83.1
65°	75.1	74.5	73.9	73.3
67.5°	63.9	62.7	62.6	62.4
70°	50.4	48.6	48.4	48.2
72.5°	39.4	39.2	38.8	38.4
75°	32.6	32.2	32.2	32.2
77.5°	26.3	25.9	25.9	25.9
80°	20.2	20.0	20.2	20.4
82.5°	14.9	14.9	14.7	14.5
85°	9.6	9.4	9.4	9.4
87.5°	4.7	4.7	4.7	4.7
90°	18.8	19.5	20.2	19.5
92.5°	39.0	36.3	37.0	35.7
95°	91.5	85.5	80.8	78.1
97.5°	209.3	183.8	167.6	160.2
100°	496.8	447.6	421.4	422.1
102.5°	745.2	708.8	688.0	668.4
105°	906.7	881.1	859.6	856.2
107.5°	1007.0	994.9	986.2	978.8
110°	1046.1	1051.5	1050.1	1048.8



TEST NUMBER: P832163

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	1036.0	1055.5	1062.2	1062.9
115°	994.9	1024.5	1038.0	1041.4
117.5°	936.3	969.3	989.5	994.2
120°	874.4	912.1	928.3	932.3
122.5°	817.9	850.9	869.0	874.4
125°	770.1	799.7	816.5	821.2
127.5°	730.4	755.9	771.4	775.5
130°	694.0	718.2	732.4	737.8
132.5°	661.0	685.3	697.4	700.7
135°	628.7	648.9	661.0	665.7
137.5°	593.7	614.6	624.7	628.7
140°	560.7	579.6	590.3	589.7
142.5°	528.4	544.6	554.0	553.3
145°	499.5	513.6	519.0	520.3
147.5°	475.9	486.0	491.4	492.1
150°	456.4	463.8	467.8	467.8
152.5°	438.9	445.6	447.6	447.6
155°	424.1	429.5	430.8	431.5
157.5°	410.6	414.7	416.0	416.0
160°	397.8	401.9	401.9	401.2
162.5°	385.0	388.4	388.4	387.7
165°	374.3	377.0	376.3	376.3
167.5°	363.5	365.5	364.8	364.8
170°	354.1	355.4	354.7	354.7
172.5°	346.0	347.3	346.0	345.3
175°	339.3	339.9	339.3	338.6
177.5°	334.6	335.2	333.9	333.9
180°	332.5	332.5	332.5	332.5

TEST NUMBER: P832163

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.08	7.78	8.18	8.87	10.36	11.75	12.45	12.84	13.53	15.02
	3H	8.29	8.92	9.40	10.01	11.52	13.24	13.86	14.34	14.96	16.47
	4H	8.67	9.26	9.79	10.36	11.87	13.72	14.31	14.84	15.41	16.92
	6H	8.95	9.49	10.07	10.59	12.11	14.03	14.57	15.15	15.67	17.20
	8H	9.03	9.55	10.15	10.66	12.18	14.10	14.62	15.23	15.74	17.25
	12H	9.08	9.57	10.21	10.68	12.22	14.13	14.62	15.26	15.73	17.27
4H	2H	7.79	8.38	8.91	9.48	10.99	11.73	12.32	12.85	13.42	14.93
	3H	9.15	9.64	10.27	10.76	12.29	13.38	13.87	14.50	14.99	16.52
	4H	9.60	10.05	10.73	11.17	12.71	13.98	14.43	15.11	15.54	17.09
	6H	9.96	10.35	11.10	11.48	13.02	14.41	14.80	15.54	15.93	17.47
	8H	10.08	10.44	11.22	11.57	13.13	14.54	14.90	15.67	16.02	17.58
	12H	10.15	10.48	11.31	11.62	13.18	14.59	14.92	15.74	16.06	17.62
8H	4H	9.91	10.27	11.04	11.39	12.95	13.94	14.30	15.07	15.42	16.98
	6H	10.36	10.66	11.52	11.83	13.38	14.43	14.72	15.58	15.89	17.44
	8H	10.56	10.82	11.72	11.97	13.54	14.61	14.87	15.77	16.02	17.59
	12H	10.69	10.92	11.86	12.07	13.67	14.72	14.95	15.89	16.10	17.70
12H	4H	9.91	10.24	11.06	11.38	12.93	13.88	14.21	15.03	15.35	16.90
	6H	10.42	10.68	11.59	11.83	13.40	14.40	14.66	15.56	15.81	17.38
	8H	10.64	10.86	11.80	12.01	13.61	14.59	14.82	15.75	15.96	17.57