

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332316-930

Luminaire Tested: **S123RDIP-S775D805U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332316-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4628.5 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332316-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332316-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				51
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49				44	
2	90	83	77	72	83	77	71	67	65	62	58	55	52	50	46	44	42				37	
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36				32	
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	34	31				28	
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27				24	
6	64	52	44	38	59	49	41	36	42	36	32	36	31	28	30	27	24				21	
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22				19	
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20				17	
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	23	20	18				16	
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16				14	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11330	11330	11330
5°	11373	11217	11282
10°	11309	11075	11038
15°	11188	10816	10702
20°	11021	10493	10247
25°	10849	10128	9804
30°	10621	9708	9178
35°	10387	9289	8604
40°	10172	8792	7893
45°	9889	8304	7252
50°	9577	7748	6532
55°	9259	7112	5863
60°	8968	6433	5126
65°	8588	5695	4391
70°	8113	4784	3547
75°	7419	3764	3335
80°	6614	3335	3068
85°	5582	2952	2742



TEST NUMBER: P332316-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	2.1
10°-20°	275.0	5.9
20°-30°	396.0	8.6
30°-40°	446.1	9.6
40°-50°	426.7	9.2
50°-60°	349.5	7.6
60°-70°	235.8	5.1
70°-80°	118.6	2.6
80°-90°	33.8	0.7
90°-100°	52.9	1.1
100°-110°	158.2	3.4
110°-120°	269.1	5.8
120°-130°	354.0	7.6
130°-140°	397.9	8.6
140°-150°	391.1	8.4
150°-160°	329.2	7.1
160°-170°	219.2	4.7
170°-180°	76.7	1.7
0°-30°	769.9	16.6
0°-40°	1215.9	26.3
0°-60°	1992.1	43.0
0°-90°	2380.3	51.4
90°-120°	480.2	10.4
90°-150°	1623.1	35.1
90°-180°	2248.0	48.6
0°-180°	4628.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1053	1053	1053	1053	1053	
5°	1053	1048	1038	1045	1044	100
15°	1004	994	971	966	960	283
25°	914	891	853	835	826	420
35°	790	759	707	671	655	495
45°	650	610	546	498	476	501
55°	493	450	379	331	312	442
65°	337	289	224	184	172	334
75°	178	137	90	82	80	190
85°	45	27	24	22	22	51
90°	1	7	15	18	19	5
95°	38	42	47	50	50	42
105°	143	145	150	150	152	154
115°	271	273	272	272	272	268
125°	396	398	397	395	392	353
135°	514	518	518	515	514	396
145°	624	625	627	626	624	390
155°	714	715	715	717	713	329
165°	778	776	776	780	776	219
175°	810	807	807	810	806	77
180°	812	812	812	812	812	



TEST NUMBER: P332316-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1056.0	1055.4	1054.8	1054.2	1053.6	1052.4	1050.5	1048.7	1046.9	1045.1	1046.8
5°	1052.6	1051.7	1050.7	1049.8	1048.8	1047.2	1044.9	1042.6	1040.3	1038.1	1039.8
7.5°	1042.8	1041.9	1040.8	1039.8	1038.8	1036.7	1033.8	1030.9	1027.9	1024.9	1025.9
10°	1034.7	1033.3	1032.0	1030.7	1029.3	1027.0	1023.5	1020.2	1016.8	1013.3	1013.5
12.5°	1023.0	1021.6	1020.1	1018.6	1017.2	1014.3	1010.2	1006.0	1001.8	997.6	997.5
15°	1004.0	1001.8	999.7	997.7	995.6	991.9	986.6	981.3	975.9	970.6	969.7
17.5°	979.8	977.5	975.0	972.6	970.1	965.6	958.8	952.0	945.3	938.6	936.5
20°	962.1	959.0	956.0	953.0	950.0	944.9	937.6	930.4	923.2	916.0	913.5
22.5°	942.3	938.8	935.3	931.8	928.3	922.8	915.1	907.4	899.8	892.1	889.0
25°	913.5	908.7	903.9	899.2	894.5	887.7	879.0	870.3	861.5	852.8	848.8
27.5°	878.4	873.2	868.0	862.7	857.5	850.0	840.3	830.6	820.8	811.1	805.6
30°	854.5	848.8	843.2	837.5	831.8	823.6	813.0	802.3	791.7	781.1	774.7
32.5°	830.6	824.2	817.7	811.3	804.9	796.0	784.7	773.6	762.3	751.1	744.0
35°	790.5	783.7	776.8	770.1	763.2	753.9	742.2	730.3	718.6	706.9	698.7
37.5°	749.9	742.2	734.7	727.1	719.5	709.5	696.9	684.4	671.8	659.3	650.0
40°	723.9	715.6	707.2	698.9	690.6	679.6	666.2	652.7	639.2	625.7	615.9
42.5°	694.6	686.2	677.8	669.5	661.2	650.0	636.1	622.2	608.3	594.4	583.6
45°	649.6	641.2	632.6	624.0	615.5	604.0	589.3	574.7	560.1	545.5	534.7
47.5°	604.8	595.4	586.0	576.7	567.3	555.3	540.7	526.0	511.4	496.8	485.1
50°	571.9	563.0	554.2	545.2	536.3	524.2	508.8	493.4	478.1	462.7	450.9
52.5°	542.6	533.0	523.3	513.6	503.9	491.5	476.2	461.1	445.8	430.6	418.4
55°	493.4	484.1	474.8	465.5	456.2	443.5	427.4	411.3	395.2	379.0	368.0
57.5°	448.0	437.9	427.8	417.6	407.5	394.4	378.1	361.9	345.7	329.5	319.1
60°	416.6	406.2	395.7	385.3	374.9	361.7	346.0	330.3	314.5	298.8	288.5
62.5°	385.1	374.7	364.3	353.8	343.5	330.4	314.6	298.9	283.2	267.3	257.7
65°	337.2	326.8	316.3	305.9	295.5	282.8	268.1	253.2	238.5	223.6	214.3
67.5°	289.3	278.7	268.2	257.6	247.0	234.6	220.5	206.3	192.1	177.9	171.0
70°	257.8	247.6	237.3	227.1	216.9	205.0	191.8	178.6	165.3	152.0	145.3
72.5°	226.4	216.3	206.2	196.1	186.1	175.0	162.9	150.8	138.8	126.7	121.2
75°	178.4	169.3	160.2	151.1	142.0	132.2	121.8	111.4	100.9	90.5	88.6
77.5°	134.7	126.5	118.2	110.0	101.7	94.3	87.6	80.9	74.2	67.4	66.4
80°	106.7	98.9	91.2	83.4	75.6	69.7	65.7	61.7	57.8	53.8	53.2
82.5°	80.1	73.4	66.6	59.9	53.2	48.9	47.0	45.2	43.4	41.5	40.9
85°	45.2	41.1	36.9	32.7	28.5	26.2	25.6	25.0	24.5	23.9	23.6
87.5°	16.6	15.2	13.8	12.4	11.0	10.4	10.8	11.2	11.6	11.9	11.9
90°	0.7	2.0	3.5	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9
92.5°	15.4	16.4	17.4	18.3	19.2	20.3	21.4	22.4	23.4	24.5	24.9
95°	37.6	38.6	39.6	40.6	41.6	42.6	43.8	44.9	46.1	47.2	47.8
97.5°	66.8	67.5	68.2	69.0	69.8	70.5	71.3	72.2	73.0	73.8	74.4
100°	86.7	87.6	88.4	89.3	90.1	90.9	91.6	92.3	93.0	93.7	94.2
102.5°	109.7	110.1	110.6	111.2	111.7	112.4	113.3	114.3	115.2	116.2	116.6
105°	143.4	143.7	144.0	144.3	144.6	145.4	146.6	147.9	149.2	150.4	150.4
107.5°	182.7	182.9	183.0	183.2	183.4	183.7	184.3	184.7	185.2	185.7	186.2
110°	207.2	207.4	207.7	208.0	208.3	208.6	208.9	209.1	209.5	209.7	210.3



TEST NUMBER: P332316-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	232.7	232.8	233.0	233.2	233.3	233.4	233.5	233.6	233.7	233.7	234.4
115°	270.9	271.3	271.7	272.1	272.6	272.7	272.4	272.1	271.8	271.6	271.7
117.5°	309.4	309.7	310.0	310.2	310.5	310.5	310.1	309.7	309.4	309.0	309.0
120°	333.4	334.2	335.1	335.9	336.8	336.9	336.1	335.4	334.8	334.0	333.9
122.5°	358.4	359.0	359.6	360.2	360.9	361.0	360.6	360.3	359.9	359.5	359.1
125°	396.5	396.9	397.3	397.8	398.2	398.3	397.9	397.7	397.4	397.1	396.6
127.5°	431.7	432.6	433.5	434.4	435.3	435.6	435.3	435.0	434.6	434.3	433.6
130°	455.1	456.2	457.4	458.5	459.7	460.0	459.6	459.2	458.8	458.3	457.7
132.5°	478.6	479.7	480.9	482.0	483.1	483.6	483.2	482.9	482.6	482.2	481.6
135°	514.4	515.3	516.1	517.0	517.8	518.2	518.0	517.9	517.7	517.6	517.1
137.5°	547.6	548.3	548.9	549.7	550.4	550.9	551.3	551.6	552.0	552.4	551.8
140°	570.5	571.2	571.9	572.7	573.3	573.7	573.9	574.1	574.2	574.3	574.2
142.5°	591.4	592.2	592.8	593.5	594.3	594.8	595.0	595.3	595.5	595.7	595.6
145°	624.0	624.4	624.6	624.9	625.2	625.5	626.0	626.4	626.8	627.2	627.1
147.5°	652.6	653.1	653.6	654.1	654.7	655.1	655.5	655.9	656.3	656.7	656.7
150°	672.5	672.8	673.0	673.4	673.6	673.9	674.2	674.5	674.7	675.1	675.1
152.5°	688.8	689.2	689.6	690.0	690.4	690.7	690.9	691.0	691.2	691.4	691.6
155°	714.5	714.5	714.5	714.5	714.5	714.6	714.8	714.9	715.1	715.2	715.8
157.5°	736.5	736.3	736.1	736.0	735.8	735.8	735.9	736.1	736.1	736.2	736.9
160°	750.2	750.0	749.7	749.4	749.1	749.0	749.0	749.0	749.0	749.0	749.7
162.5°	762.5	762.1	761.7	761.3	760.9	760.8	760.9	761.0	761.1	761.2	761.9
165°	778.3	777.9	777.5	777.1	776.6	776.4	776.4	776.4	776.4	776.4	777.2
167.5°	790.9	790.4	789.8	789.2	788.6	788.5	788.6	788.6	788.8	788.9	789.8
170°	798.1	797.5	797.0	796.4	795.8	795.5	795.5	795.5	795.5	795.5	796.5
172.5°	803.6	803.2	802.6	802.0	801.4	801.1	801.1	801.1	801.1	801.1	802.0
175°	809.5	808.9	808.5	807.9	807.3	807.0	807.0	807.0	807.0	807.0	807.9
177.5°	812.0	811.5	811.1	810.6	810.2	809.9	809.9	809.9	809.9	809.9	810.6
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332316-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6	1052.6
2.5°	1048.4	1050.1	1051.7	1052.5	1052.1	1051.8	1051.5	1051.2
5°	1041.5	1043.2	1044.9	1045.5	1045.2	1044.8	1044.4	1044.1
7.5°	1026.9	1027.8	1028.7	1028.9	1028.3	1027.6	1027.0	1026.3
10°	1013.7	1013.9	1014.1	1013.7	1012.8	1011.8	1010.9	1009.9
12.5°	997.4	997.3	997.2	996.5	995.5	994.3	993.3	992.1
15°	968.7	967.8	966.9	965.7	964.4	963.0	961.7	960.4
17.5°	934.5	932.5	930.5	928.5	926.5	924.5	922.6	920.6
20°	911.1	908.6	906.1	903.8	901.5	899.2	896.9	894.6
22.5°	886.0	882.9	879.8	877.2	875.1	872.9	870.8	868.7
25°	844.9	840.9	836.9	833.9	831.8	829.6	827.6	825.5
27.5°	800.1	794.6	789.0	784.6	781.5	778.3	775.1	771.9
30°	768.3	761.7	755.3	750.6	747.5	744.5	741.4	738.4
32.5°	736.9	729.9	722.8	717.7	714.5	711.3	708.2	705.0
35°	690.6	682.4	674.3	668.5	665.0	661.6	658.2	654.8
37.5°	640.7	631.4	622.2	615.5	611.2	607.0	602.8	598.6
40°	606.0	596.1	586.3	579.2	574.8	570.5	566.1	561.7
42.5°	572.7	562.0	551.2	543.9	540.0	536.1	532.1	528.2
45°	523.9	513.1	502.2	494.6	490.0	485.4	480.9	476.4
47.5°	473.3	461.5	449.8	441.9	437.8	433.7	429.7	425.7
50°	439.2	427.4	415.6	407.6	403.2	398.8	394.5	390.1
52.5°	406.2	394.0	381.7	373.7	369.7	365.8	361.9	358.0
55°	357.0	346.0	335.0	327.6	323.8	320.0	316.3	312.4
57.5°	308.8	298.3	288.0	281.1	277.9	274.7	271.4	268.2
60°	278.3	268.1	257.8	251.1	247.9	244.6	241.4	238.1
62.5°	248.1	238.5	228.9	222.3	218.9	215.6	212.2	208.8
65°	205.0	195.8	186.5	180.8	178.7	176.6	174.6	172.4
67.5°	164.0	157.1	150.1	145.5	143.3	141.0	138.8	136.6
70°	138.7	132.0	125.4	121.1	119.0	116.8	114.8	112.7
72.5°	115.9	110.4	105.0	101.8	100.9	100.1	99.2	98.3
75°	86.7	84.8	82.9	81.8	81.4	81.0	80.6	80.2
77.5°	65.4	64.3	63.3	62.6	62.3	61.9	61.5	61.1
80°	52.7	52.1	51.5	51.0	50.6	50.3	49.9	49.5
82.5°	40.4	39.8	39.2	38.9	38.8	38.7	38.6	38.6
85°	23.2	22.7	22.4	22.2	22.2	22.2	22.2	22.2
87.5°	11.8	11.8	11.8	11.7	11.7	11.5	11.4	11.3
90°	16.5	17.0	17.5	18.0	18.3	18.6	18.8	19.2
92.5°	25.4	25.8	26.3	26.4	26.3	26.1	25.9	25.8
95°	48.3	48.8	49.4	49.7	49.7	49.7	49.7	49.7
97.5°	75.1	75.7	76.4	76.7	76.6	76.6	76.6	76.5
100°	94.6	95.0	95.4	95.8	96.0	96.3	96.6	96.9
102.5°	117.0	117.4	117.8	118.1	118.0	117.9	117.9	117.8
105°	150.4	150.4	150.4	150.6	150.8	151.2	151.4	151.7
107.5°	186.6	187.1	187.6	187.7	187.5	187.4	187.2	187.0
110°	210.8	211.4	212.0	212.1	211.8	211.6	211.2	211.0



TEST NUMBER: P332316-930

CATALOG NUMBER: S123RDIP-S775D805U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.1	235.7	236.4	236.7	236.7	236.6	236.5	236.5
115°	271.8	272.0	272.1	272.1	272.0	271.8	271.7	271.6
117.5°	309.0	308.9	308.9	308.7	308.3	307.9	307.5	307.1
120°	333.7	333.6	333.5	333.2	333.0	332.6	332.4	332.1
122.5°	358.8	358.4	358.1	357.7	357.3	356.9	356.4	356.0
125°	396.0	395.4	394.8	394.3	393.7	393.1	392.6	392.0
127.5°	432.8	431.9	431.2	430.5	429.8	429.2	428.5	427.9
130°	457.2	456.6	456.1	455.3	454.3	453.3	452.3	451.3
132.5°	480.9	480.2	479.6	478.8	478.1	477.3	476.5	475.8
135°	516.5	515.9	515.4	514.9	514.6	514.4	514.0	513.8
137.5°	551.2	550.7	550.0	549.4	548.9	548.4	547.9	547.3
140°	574.1	573.9	573.7	573.2	572.2	571.2	570.2	569.2
142.5°	595.5	595.3	595.2	594.8	593.9	593.2	592.4	591.7
145°	627.0	626.8	626.6	626.3	625.7	625.2	624.6	624.0
147.5°	656.7	656.7	656.7	656.2	655.4	654.5	653.7	652.9
150°	675.1	675.1	675.1	674.7	673.8	672.9	672.1	671.2
152.5°	691.8	692.0	692.3	692.0	691.3	690.6	689.8	689.1
155°	716.3	716.9	717.5	717.2	716.2	715.3	714.3	713.3
157.5°	737.4	738.0	738.6	738.5	737.8	736.9	736.1	735.3
160°	750.4	751.1	751.8	751.9	751.3	750.7	750.2	749.6
162.5°	762.6	763.4	764.1	763.9	763.0	762.1	761.2	760.3
165°	778.1	778.9	779.8	779.8	778.8	777.7	776.7	775.8
167.5°	790.7	791.5	792.4	792.4	791.5	790.7	789.8	788.9
170°	797.5	798.5	799.5	799.5	798.5	797.5	796.5	795.5
172.5°	802.9	803.8	804.6	804.6	803.6	802.6	801.6	800.6
175°	808.7	809.5	810.4	810.3	809.3	808.4	807.3	806.3
177.5°	811.3	812.0	812.6	812.6	811.8	811.0	810.2	809.4
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5

(END OF REPORT)