

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332027

Luminaire Tested: **S123DIP-S1000D1025U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332027
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1025U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8340.0 lumens
Efficiency: N/A
Efficacy: 137.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	51	51	51		
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	51	50	49	43	43	43	43	43	43	43		
2	90	82	76	71	83	76	71	67	65	61	58	55	52	49	45	43	41	37	37	37	37	37	37	37		
3	82	73	65	60	75	67	61	56	58	53	49	48	45	42	40	38	35	31	31	31	31	31	31	31		
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27	27	27	27	27	27	27		
5	69	57	49	44	64	54	46	41	46	40	36	39	35	31	32	29	27	24	24	24	24	24	24	24		
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21	21	21	21	21	21	21		
7	59	47	39	33	54	44	36	31	38	32	28	32	28	25	27	24	21	19	19	19	19	19	19	19		
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17	17	17	17	17	17	17		
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17	15	15	15	15	15	15	15		
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	16	14	14	14	14	14	14	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15118	15118	15118	15118
5°	18029	15183	13456	15183
10°	22566	15106	12153	15106
15°	27679	14985	11314	14985
20°	32972	14795	10772	14795
25°	35011	14563	10652	14563
30°	30009	14395	10708	14395
35°	20871	14155	10820	14155
40°	15719	13874	10786	13874
45°	13052	13457	10648	13457
50°	11692	12603	10551	12603
55°	10931	11684	10421	11684
60°	10254	10723	10314	10723
65°	9638	9775	9984	9775
70°	9039	8696	9508	8696
75°	8093	7615	8717	7615
80°	7085	6242	7507	6242
85°	5545	4533	5039	4533



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.4	1.7
10°-20°	443.6	5.3
20°-30°	744.6	8.9
30°-40°	843.1	10.1
40°-50°	756.1	9.1
50°-60°	610.1	7.3
60°-70°	425.2	5.1
70°-80°	223.5	2.7
80°-90°	58.4	0.7
90°-100°	48.8	0.6
100°-110°	232.8	2.8
110°-120°	559.2	6.7
120°-130°	712.1	8.5
130°-140°	760.8	9.1
140°-150°	711.5	8.5
150°-160°	573.9	6.9
160°-170°	370.4	4.4
170°-180°	127.6	1.5
0°-30°	1326.6	15.9
0°-40°	2169.7	26.0
0°-60°	3535.9	42.4
0°-90°	4242.9	50.9
90°-120°	840.8	10.1
90°-150°	3025.2	36.3
90°-180°	4097.0	49.1
0°-180°	8340.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1404	1404	1404	1404	1404	
5°	1669	1405	1245	1405	1669	173
15°	2484	1345	1015	1345	2484	717
25°	2948	1226	897	1226	2948	1293
35°	1588	1077	823	1077	1588	1032
45°	857	884	700	884	857	678
55°	582	623	555	623	582	523
65°	378	384	392	384	378	377
75°	195	183	210	183	195	208
85°	45	37	41	37	45	54
90°	30	1	30	1	30	16
95°	38	61	38	61	38	32
105°	44	297	44	297	44	100
115°	587	558	587	558	587	542
125°	802	786	802	786	802	717
135°	989	979	989	979	989	763
145°	1141	1130	1141	1130	1141	712
155°	1243	1245	1243	1245	1243	573
165°	1310	1313	1310	1313	1310	370
175°	1338	1344	1338	1344	1338	127
180°	1344	1344	1344	1344	1344	



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1490.5	1489.5	1486.7	1488.9	1484.6	1478.6	1478.0	1472.6	1456.8	1455.7	1451.4
5°	1668.6	1663.1	1662.4	1661.8	1652.2	1639.3	1614.8	1612.8	1580.1	1563.8	1544.0
7.5°	1899.1	1902.0	1892.0	1883.3	1854.2	1835.0	1808.7	1775.1	1735.0	1694.3	1667.2
10°	2064.6	2087.1	2059.2	2040.1	2022.4	1989.1	1950.3	1902.0	1853.7	1797.2	1754.3
12.5°	2242.1	2253.1	2247.5	2229.6	2202.1	2151.3	2082.6	2029.4	1984.9	1890.8	1852.8
15°	2483.8	2525.3	2498.8	2437.5	2438.9	2390.6	2300.7	2202.1	2149.7	2067.3	1955.1
17.5°	2741.3	2746.5	2735.2	2684.1	2650.1	2583.7	2500.8	2406.2	2300.1	2200.4	2081.4
20°	2878.5	2874.4	2850.6	2824.0	2765.5	2713.8	2623.3	2517.8	2381.7	2283.7	2153.8
22.5°	2954.7	2947.9	2936.6	2914.4	2865.7	2810.2	2728.9	2613.6	2484.1	2349.1	2198.9
25°	2947.9	2956.7	2958.1	2952.0	2935.0	2901.6	2837.6	2745.8	2616.5	2443.0	2286.5
27.5°	2681.1	2693.7	2730.0	2762.3	2798.3	2835.1	2830.2	2784.6	2688.9	2539.0	2347.7
30°	2414.4	2387.2	2454.5	2539.6	2597.4	2699.5	2756.7	2760.1	2706.3	2577.7	2391.2
32.5°	2044.2	2074.1	2103.9	2208.6	2335.0	2449.6	2563.4	2655.0	2665.5	2579.9	2416.8
35°	1588.3	1625.7	1680.1	1734.6	1870.7	1987.7	2187.8	2362.0	2500.8	2519.2	2419.1
37.5°	1279.9	1298.4	1332.8	1387.4	1476.4	1615.2	1770.0	1990.2	2191.3	2340.9	2347.4
40°	1118.7	1124.2	1163.0	1204.5	1276.6	1390.9	1530.4	1725.0	1965.9	2174.9	2262.0
42.5°	997.9	1009.8	1026.3	1066.2	1123.6	1209.6	1339.3	1500.2	1721.0	1961.4	2131.8
45°	857.4	871.0	881.2	907.8	948.6	1006.4	1097.0	1243.9	1412.0	1660.4	1889.7
47.5°	764.6	765.7	773.3	793.3	821.1	864.5	928.5	1022.9	1177.2	1378.7	1614.1
50°	698.2	709.1	711.8	727.4	749.2	781.2	834.3	914.6	1041.2	1218.1	1434.5
52.5°	651.4	654.6	662.3	673.6	692.6	717.5	763.5	826.4	925.7	1076.5	1275.5
55°	582.5	582.5	590.0	598.8	609.7	632.2	662.8	709.1	784.6	901.7	1066.3
57.5°	518.8	522.2	527.5	530.2	539.5	554.3	579.9	615.0	671.4	761.5	892.4
60°	476.3	482.5	481.8	487.2	495.4	507.0	528.7	557.3	607.7	679.8	790.1
62.5°	439.3	438.9	438.8	445.3	453.5	464.5	478.7	503.4	546.2	610.1	704.0
65°	378.4	377.0	381.8	385.8	388.6	396.7	407.6	429.4	458.0	505.6	578.4
67.5°	324.2	320.2	322.8	324.2	328.8	335.2	345.4	358.9	381.6	419.9	474.7
70°	287.2	283.8	283.1	284.4	288.5	293.3	300.8	313.7	334.8	365.4	405.6
72.5°	249.1	246.7	246.6	249.6	251.5	254.6	259.9	271.8	288.5	311.5	349.0
75°	194.6	194.6	194.6	195.3	197.3	200.1	204.1	210.3	223.2	239.5	264.7
77.5°	145.9	145.8	144.9	144.8	147.8	149.0	150.0	155.7	162.9	173.9	192.3
80°	114.3	110.9	112.3	114.3	115.7	116.4	118.4	119.8	125.9	132.0	144.9
82.5°	84.9	82.1	82.3	85.5	85.7	86.4	88.5	90.4	92.7	98.3	105.2
85°	44.9	44.9	45.6	45.6	46.3	45.6	47.6	48.3	48.3	51.7	55.8
87.5°	22.3	21.1	21.6	22.1	21.4	21.8	22.2	22.6	22.9	23.3	23.3
90°	29.9	29.5	29.1	28.6	28.2	27.5	26.6	25.7	24.8	24.0	21.1
92.5°	33.1	32.9	32.6	32.3	32.1	31.2	29.8	28.4	27.0	25.6	23.4
95°	37.9	37.9	37.9	37.9	37.9	37.2	35.6	34.0	32.5	30.9	28.5
97.5°	41.1	40.9	40.7	40.5	40.2	39.2	37.5	35.7	33.9	32.1	48.1
100°	41.9	41.7	41.5	41.3	41.0	40.0	38.3	36.5	34.7	32.9	67.5
102.5°	42.7	42.3	41.9	41.5	41.1	43.7	49.2	54.7	60.2	65.7	103.5
105°	43.9	43.5	43.0	42.6	42.1	61.6	100.8	140.1	179.3	218.6	238.6
107.5°	137.9	167.5	197.1	226.7	256.3	285.5	314.3	343.1	371.9	400.7	397.5
110°	274.5	306.2	337.9	369.6	401.4	420.9	428.2	435.5	442.8	450.2	447.7



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	470.9	477.6	484.3	491.0	497.7	501.0	500.9	500.7	500.6	500.5	498.0
115°	586.9	586.0	585.1	584.2	583.4	581.8	579.6	577.4	575.2	572.9	570.9
117.5°	652.0	651.8	651.6	651.5	651.3	650.3	648.5	646.8	645.0	643.2	642.2
120°	696.7	696.7	696.7	696.7	696.7	695.8	694.0	692.3	690.5	688.7	688.1
122.5°	740.6	740.4	740.3	740.1	739.9	739.2	738.0	736.7	735.5	734.2	733.4
125°	802.5	802.1	801.6	801.2	800.7	800.3	799.8	799.4	799.0	798.5	797.6
127.5°	862.0	862.4	862.9	863.3	863.8	863.6	862.9	862.2	861.5	860.8	859.7
130°	900.3	900.8	901.2	901.7	902.1	901.9	901.0	900.1	899.2	898.3	897.4
132.5°	935.5	936.1	936.7	937.3	937.9	937.8	936.9	936.0	935.2	934.3	933.6
135°	989.2	989.8	990.5	991.2	991.8	991.8	991.2	990.5	989.8	989.2	988.3
137.5°	1039.7	1040.1	1040.6	1041.0	1041.4	1041.1	1040.1	1039.0	1037.9	1036.9	1036.4
140°	1070.0	1070.5	1070.9	1071.3	1071.8	1071.6	1070.7	1069.8	1068.9	1068.0	1067.4
142.5°	1098.0	1098.6	1099.2	1099.8	1100.4	1100.4	1099.7	1099.0	1098.3	1097.6	1096.9
145°	1140.9	1140.9	1140.9	1140.9	1140.9	1140.7	1140.2	1139.8	1139.3	1138.9	1138.4
147.5°	1172.8	1173.8	1174.9	1175.9	1176.9	1177.2	1176.7	1176.3	1175.9	1175.4	1175.0
150°	1196.8	1197.4	1198.1	1198.8	1199.4	1199.6	1199.1	1198.7	1198.2	1197.8	1197.3
152.5°	1215.9	1217.0	1218.0	1219.0	1220.0	1220.1	1219.3	1218.5	1217.7	1216.9	1216.7
155°	1242.7	1244.0	1245.4	1246.7	1248.0	1248.1	1247.0	1245.9	1244.8	1243.7	1243.5
157.5°	1265.3	1267.0	1268.7	1270.4	1272.2	1272.4	1271.0	1269.7	1268.4	1267.0	1267.3
160°	1279.6	1281.2	1282.7	1284.3	1285.8	1285.9	1284.6	1283.3	1282.0	1280.6	1280.8
162.5°	1293.2	1294.6	1295.9	1297.3	1298.7	1298.6	1297.1	1295.6	1294.1	1292.6	1292.8
165°	1309.6	1311.1	1312.7	1314.2	1315.8	1315.7	1313.9	1312.1	1310.3	1308.6	1308.8
167.5°	1321.3	1323.1	1324.9	1326.7	1328.4	1328.4	1326.7	1324.9	1323.1	1321.3	1321.3
170°	1328.5	1330.3	1332.1	1333.9	1335.6	1335.6	1333.9	1332.1	1330.3	1328.5	1328.5
172.5°	1332.5	1334.5	1336.4	1338.4	1340.3	1340.4	1338.6	1336.9	1335.1	1333.3	1333.1
175°	1338.5	1340.3	1342.1	1343.8	1345.6	1345.7	1344.2	1342.6	1341.1	1339.5	1339.3
177.5°	1340.3	1342.1	1343.9	1345.6	1347.4	1347.6	1346.2	1344.7	1343.3	1341.9	1341.7
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1448.1	1443.7	1439.4	1431.8	1425.2	1416.0	1413.2	1410.0	1400.2	1391.5	1384.9
5°	1536.5	1520.2	1496.4	1474.6	1456.9	1433.1	1419.5	1405.2	1384.8	1366.4	1351.5
7.5°	1629.1	1597.0	1560.0	1519.9	1482.7	1446.7	1417.7	1391.9	1363.3	1336.2	1315.1
10°	1702.6	1656.3	1604.6	1548.8	1501.2	1454.9	1416.1	1382.1	1345.3	1313.3	1286.8
12.5°	1786.4	1717.8	1646.5	1578.7	1522.4	1458.2	1411.2	1367.9	1326.3	1287.8	1258.0
15°	1885.6	1798.5	1714.2	1620.9	1535.2	1454.9	1399.1	1344.7	1296.3	1256.9	1218.8
17.5°	1976.0	1877.3	1766.1	1652.8	1549.3	1454.1	1376.0	1314.4	1254.0	1205.7	1167.7
20°	2027.2	1914.9	1789.0	1671.3	1557.0	1450.8	1365.1	1291.6	1226.2	1175.2	1132.3
22.5°	2071.3	1939.9	1809.7	1683.8	1556.4	1442.1	1344.9	1269.3	1198.5	1148.5	1102.9
25°	2117.0	1959.8	1829.2	1681.5	1539.3	1420.9	1312.0	1226.2	1155.5	1097.0	1050.0
27.5°	2156.2	1958.5	1803.4	1644.6	1512.3	1393.6	1277.4	1185.4	1110.3	1046.7	999.1
30°	2182.3	1961.2	1776.8	1619.6	1486.2	1363.7	1250.7	1158.2	1079.3	1014.6	969.7
32.5°	2198.7	1959.5	1752.3	1584.7	1444.8	1336.5	1221.9	1126.1	1045.0	981.4	938.1
35°	2208.2	1947.6	1710.1	1512.7	1378.0	1272.5	1176.6	1077.2	992.2	933.0	884.0
37.5°	2189.1	1922.4	1661.1	1443.3	1295.8	1191.9	1111.2	1026.6	945.2	880.0	837.8
40°	2159.2	1906.1	1623.0	1394.3	1239.2	1139.1	1070.4	987.4	907.1	845.2	805.7
42.5°	2102.0	1872.8	1581.1	1339.9	1180.4	1080.3	1017.1	947.7	871.7	813.6	774.1
45°	1962.5	1800.6	1518.2	1258.2	1093.5	990.1	934.3	884.0	815.2	758.7	724.7
47.5°	1769.0	1691.8	1427.3	1172.1	1002.9	903.4	845.4	804.9	754.7	709.1	676.4
50°	1634.5	1602.6	1365.7	1113.3	942.5	845.2	789.4	752.6	716.6	671.0	641.0
52.5°	1479.4	1499.1	1293.9	1052.3	881.0	785.3	732.8	703.6	670.8	633.4	607.3
55°	1261.0	1332.4	1169.8	950.0	789.4	698.2	648.5	622.6	603.6	575.7	553.2
57.5°	1056.4	1147.3	1035.6	844.5	699.4	620.7	573.1	544.9	532.7	518.1	500.4
60°	935.0	1024.8	939.8	773.7	639.0	564.1	521.9	498.1	485.9	475.7	460.7
62.5°	826.7	917.6	846.1	701.9	579.6	510.2	473.5	450.2	440.7	435.4	422.6
65°	677.8	756.0	708.4	590.0	494.7	433.5	400.1	383.8	375.0	372.9	364.7
67.5°	551.6	611.2	576.5	489.4	414.4	361.5	333.2	319.3	312.5	311.8	305.7
70°	468.9	524.7	498.1	419.2	354.5	313.0	288.5	276.3	272.2	271.5	268.1
72.5°	404.6	443.5	422.4	356.6	306.6	268.9	251.0	238.2	233.5	234.5	232.2
75°	299.4	328.7	316.4	270.8	230.7	206.2	191.2	183.1	179.0	181.0	178.3
77.5°	215.4	234.0	222.9	191.4	166.6	148.9	137.9	132.8	129.2	129.0	127.8
80°	162.6	173.5	167.4	148.3	127.9	113.0	104.1	100.7	98.7	98.0	97.3
82.5°	115.8	125.1	117.9	104.8	90.9	81.9	76.9	72.4	70.9	71.3	70.6
85°	58.5	61.9	59.2	51.0	45.6	41.5	38.8	36.7	35.4	36.1	34.7
87.5°	23.8	23.7	21.5	18.9	17.3	15.2	14.8	13.3	12.6	13.1	13.0
90°	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	21.2	19.0	16.9	16.1	16.7	17.3	17.9	18.6	17.9	17.3	16.7
95°	26.1	23.6	21.2	24.5	33.6	42.7	51.8	60.9	51.8	42.7	33.6
97.5°	64.1	80.1	96.0	106.0	110.1	114.2	118.3	122.4	118.3	114.2	110.1
100°	102.1	136.7	171.3	186.4	182.0	177.6	173.1	168.7	173.1	177.6	182.0
102.5°	141.3	179.1	216.9	234.2	231.0	227.8	224.6	221.4	224.6	227.8	231.0
105°	258.5	278.5	298.4	307.2	304.8	302.3	299.9	297.4	299.9	302.3	304.8
107.5°	394.4	391.2	388.1	385.5	383.6	381.6	379.7	377.7	379.7	381.6	383.6
110°	445.3	442.8	440.4	438.3	436.5	434.7	433.0	431.2	433.0	434.7	436.5



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	495.6	493.2	490.7	488.7	487.1	485.5	483.9	482.3	483.9	485.5	487.1
115°	568.9	566.9	565.0	563.3	562.0	560.6	559.3	558.0	559.3	560.6	562.0
117.5°	641.2	640.1	639.1	637.8	636.2	634.5	632.9	631.2	632.9	634.5	636.2
120°	687.4	686.7	686.1	684.7	682.7	680.7	678.7	676.7	678.7	680.7	682.7
122.5°	732.6	731.7	730.9	729.6	728.0	726.3	724.7	723.1	724.7	726.3	728.0
125°	796.7	795.9	795.0	793.6	791.9	790.1	788.3	786.5	788.3	790.1	791.9
127.5°	858.7	857.6	856.5	855.1	853.3	851.6	849.8	848.0	849.8	851.6	853.3
130°	896.6	895.7	894.8	893.5	891.7	889.9	888.1	886.4	888.1	889.9	891.7
132.5°	932.8	932.1	931.4	930.2	928.4	926.6	924.9	923.1	924.9	926.6	928.4
135°	987.4	986.5	985.6	984.5	983.2	981.8	980.5	979.2	980.5	981.8	983.2
137.5°	1035.9	1035.4	1034.9	1033.8	1032.2	1030.5	1028.8	1027.1	1028.8	1030.5	1032.2
140°	1066.7	1066.0	1065.4	1064.4	1063.0	1061.7	1060.4	1059.0	1060.4	1061.7	1063.0
142.5°	1096.2	1095.6	1094.9	1093.9	1092.6	1091.2	1089.9	1088.6	1089.9	1091.2	1092.6
145°	1138.0	1137.6	1137.1	1136.1	1134.6	1133.0	1131.5	1129.9	1131.5	1133.0	1134.6
147.5°	1174.5	1174.1	1173.6	1172.9	1171.9	1170.9	1169.9	1168.8	1169.9	1170.9	1171.9
150°	1196.9	1196.4	1196.0	1195.4	1194.8	1194.1	1193.5	1192.8	1193.5	1194.1	1194.8
152.5°	1216.4	1216.1	1215.9	1215.6	1215.3	1215.0	1214.7	1214.3	1214.7	1215.0	1215.3
155°	1243.2	1243.0	1242.8	1242.9	1243.4	1243.8	1244.2	1244.7	1244.2	1243.8	1243.4
157.5°	1267.5	1267.7	1267.9	1268.1	1268.1	1268.2	1268.2	1268.2	1268.2	1268.2	1268.1
160°	1281.1	1281.3	1281.5	1281.7	1282.0	1282.2	1282.4	1282.6	1282.4	1282.2	1282.0
162.5°	1293.0	1293.3	1293.5	1293.9	1294.5	1295.0	1295.6	1296.2	1295.6	1295.0	1294.5
165°	1309.0	1309.2	1309.5	1309.9	1310.6	1311.2	1311.9	1312.6	1311.9	1311.2	1310.6
167.5°	1321.3	1321.3	1321.3	1321.8	1322.7	1323.6	1324.5	1325.3	1324.5	1323.6	1322.7
170°	1328.5	1328.5	1328.5	1329.0	1329.9	1330.8	1331.6	1332.5	1331.6	1330.8	1329.9
172.5°	1333.0	1332.8	1332.6	1333.1	1334.1	1335.2	1336.3	1337.3	1336.3	1335.2	1334.1
175°	1339.1	1338.8	1338.6	1339.1	1340.2	1341.3	1342.4	1343.5	1342.4	1341.3	1340.2
177.5°	1341.6	1341.4	1341.2	1341.6	1342.4	1343.3	1344.2	1345.1	1344.2	1343.3	1342.4
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1381.1	1377.3	1371.9	1363.7	1357.2	1346.8	1346.8	1348.5	1348.5	1347.9	1346.8
5°	1339.2	1329.0	1316.8	1302.5	1287.5	1272.5	1269.8	1264.4	1260.3	1257.5	1254.1
7.5°	1295.0	1276.9	1259.0	1239.0	1220.8	1205.7	1195.2	1186.5	1180.9	1174.9	1170.6
10°	1265.0	1242.6	1221.5	1200.4	1177.2	1158.9	1147.3	1139.1	1133.0	1127.6	1124.9
12.5°	1229.6	1203.9	1180.7	1160.6	1135.3	1116.4	1105.4	1101.6	1094.4	1082.9	1076.9
15°	1177.9	1154.1	1126.2	1095.6	1083.3	1060.2	1047.3	1041.2	1037.1	1028.2	1025.5
17.5°	1133.7	1102.5	1071.2	1048.4	1025.6	1006.9	999.6	992.0	986.6	979.4	977.2
20°	1098.3	1070.4	1041.8	1017.3	993.5	973.1	967.0	961.5	956.1	952.7	950.0
22.5°	1062.4	1034.5	1010.8	987.9	962.5	949.1	942.5	936.5	932.7	930.4	927.6
25°	1011.9	987.4	960.9	940.4	920.0	911.2	907.1	903.7	901.0	897.6	896.9
27.5°	966.7	940.0	918.5	899.5	884.8	877.4	873.5	871.8	872.4	873.6	874.4
30°	933.0	908.5	890.8	874.4	860.8	854.0	853.3	853.3	856.1	856.7	858.1
32.5°	901.9	881.8	864.1	848.3	838.0	833.3	835.9	835.9	838.1	839.9	842.3
35°	856.7	839.0	825.4	811.8	803.0	805.0	806.4	807.7	811.1	815.2	818.0
37.5°	813.6	798.2	784.1	773.4	769.4	773.0	776.3	779.2	783.1	786.2	789.0
40°	782.6	771.0	757.4	747.9	749.2	751.3	754.0	757.4	760.8	762.8	765.6
42.5°	753.7	741.6	731.3	723.4	725.3	727.9	729.5	731.3	735.2	738.9	740.5
45°	709.8	700.2	690.7	685.9	687.3	688.7	690.0	692.1	695.5	698.2	698.9
47.5°	660.3	653.7	647.3	642.7	644.8	644.3	646.1	650.4	651.5	653.1	656.9
50°	628.8	622.6	615.2	613.8	613.8	613.8	614.5	619.9	619.9	622.6	625.4
52.5°	593.9	590.0	585.2	582.8	581.7	581.7	584.5	587.3	588.4	592.2	594.9
55°	542.4	538.3	534.2	532.1	530.8	532.1	537.6	538.9	542.4	544.4	546.4
57.5°	488.6	485.5	482.2	481.1	480.8	482.6	485.6	489.7	490.5	496.8	499.9
60°	453.2	448.4	445.7	445.7	444.4	450.5	449.1	455.9	457.3	461.4	466.1
62.5°	416.7	410.3	409.2	409.2	411.2	412.9	414.8	417.8	421.4	426.5	430.2
65°	357.9	354.5	359.3	358.6	357.3	361.3	361.3	364.7	368.8	373.6	381.1
67.5°	302.3	300.5	300.9	300.9	303.0	305.3	307.2	310.2	315.1	320.1	325.0
70°	264.7	266.8	263.4	266.1	268.1	268.8	270.2	274.2	279.7	283.1	288.5
72.5°	228.2	228.1	228.5	229.6	231.6	232.9	234.2	238.9	244.8	247.7	252.1
75°	175.6	174.9	176.9	176.9	180.3	181.7	183.1	185.1	190.5	194.6	198.0
77.5°	128.2	129.0	128.6	130.9	130.0	130.2	134.5	136.5	137.1	145.1	146.9
80°	96.6	98.0	98.7	99.4	100.0	98.7	103.4	105.5	105.5	110.2	113.6
82.5°	69.4	70.2	72.0	72.7	72.8	74.2	74.6	76.1	77.7	79.8	84.2
85°	34.7	36.7	37.4	36.7	37.4	36.1	38.1	38.8	39.5	39.5	39.5
87.5°	12.9	13.9	13.9	15.1	15.1	16.2	16.4	15.5	15.7	17.5	15.4
90°	9.9	12.4	15.3	18.2	21.1	24.0	24.8	25.7	26.6	27.5	28.2
92.5°	16.1	16.9	19.0	21.2	23.4	25.6	27.0	28.4	29.8	31.2	32.1
95°	24.5	21.2	23.6	26.1	28.5	30.9	32.5	34.0	35.6	37.2	37.9
97.5°	106.0	96.0	80.1	64.1	48.1	32.1	33.9	35.7	37.5	39.2	40.2
100°	186.4	171.3	136.7	102.1	67.5	32.9	34.7	36.5	38.3	40.0	41.0
102.5°	234.2	216.9	179.1	141.3	103.5	65.7	60.2	54.7	49.2	43.7	41.1
105°	307.2	298.4	278.5	258.5	238.6	218.6	179.3	140.1	100.8	61.6	42.1
107.5°	385.5	388.1	391.2	394.4	397.5	400.7	371.9	343.1	314.3	285.5	256.3
110°	438.3	440.4	442.8	445.3	447.7	450.2	442.8	435.5	428.2	420.9	401.4



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	488.7	490.7	493.2	495.6	498.0	500.5	500.6	500.7	500.9	501.0	497.7
115°	563.3	565.0	566.9	568.9	570.9	572.9	575.2	577.4	579.6	581.8	583.4
117.5°	637.8	639.1	640.1	641.2	642.2	643.2	645.0	646.8	648.5	650.3	651.3
120°	684.7	686.1	686.7	687.4	688.1	688.7	690.5	692.3	694.0	695.8	696.7
122.5°	729.6	730.9	731.7	732.6	733.4	734.2	735.5	736.7	738.0	739.2	739.9
125°	793.6	795.0	795.9	796.7	797.6	798.5	799.0	799.4	799.8	800.3	800.7
127.5°	855.1	856.5	857.6	858.7	859.7	860.8	861.5	862.2	862.9	863.6	863.8
130°	893.5	894.8	895.7	896.6	897.4	898.3	899.2	900.1	901.0	901.9	902.1
132.5°	930.2	931.4	932.1	932.8	933.6	934.3	935.2	936.0	936.9	937.8	937.9
135°	984.5	985.6	986.5	987.4	988.3	989.2	989.8	990.5	991.2	991.8	991.8
137.5°	1033.8	1034.9	1035.4	1035.9	1036.4	1036.9	1037.9	1039.0	1040.1	1041.1	1041.4
140°	1064.4	1065.4	1066.0	1066.7	1067.4	1068.0	1068.9	1069.8	1070.7	1071.6	1071.8
142.5°	1093.9	1094.9	1095.6	1096.2	1096.9	1097.6	1098.3	1099.0	1099.7	1100.4	1100.4
145°	1136.1	1137.1	1137.6	1138.0	1138.4	1138.9	1139.3	1139.8	1140.2	1140.7	1140.9
147.5°	1172.9	1173.6	1174.1	1174.5	1175.0	1175.4	1175.9	1176.3	1176.7	1177.2	1176.9
150°	1195.4	1196.0	1196.4	1196.9	1197.3	1197.8	1198.2	1198.7	1199.1	1199.6	1199.4
152.5°	1215.6	1215.9	1216.1	1216.4	1216.7	1216.9	1217.7	1218.5	1219.3	1220.1	1220.0
155°	1242.9	1242.8	1243.0	1243.2	1243.5	1243.7	1244.8	1245.9	1247.0	1248.1	1248.0
157.5°	1268.1	1267.9	1267.7	1267.5	1267.3	1267.0	1268.4	1269.7	1271.0	1272.4	1272.2
160°	1281.7	1281.5	1281.3	1281.1	1280.8	1280.6	1282.0	1283.3	1284.6	1285.9	1285.8
162.5°	1293.9	1293.5	1293.3	1293.0	1292.8	1292.6	1294.1	1295.6	1297.1	1298.6	1298.7
165°	1309.9	1309.5	1309.2	1309.0	1308.8	1308.6	1310.3	1312.1	1313.9	1315.7	1315.8
167.5°	1321.8	1321.3	1321.3	1321.3	1321.3	1321.3	1323.1	1324.9	1326.7	1328.4	1328.4
170°	1329.0	1328.5	1328.5	1328.5	1328.5	1328.5	1330.3	1332.1	1333.9	1335.6	1335.6
172.5°	1333.1	1332.6	1332.8	1333.0	1333.1	1333.3	1335.1	1336.9	1338.6	1340.4	1340.3
175°	1339.1	1338.6	1338.8	1339.1	1339.3	1339.5	1341.1	1342.6	1344.2	1345.7	1345.6
177.5°	1341.6	1341.2	1341.4	1341.6	1341.7	1341.9	1343.3	1344.7	1346.2	1347.6	1347.4
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1343.0	1342.5	1346.3	1343.6	1346.3	1342.5	1343.0	1346.8	1347.9	1348.5	1348.5
5°	1250.1	1252.1	1245.3	1245.3	1245.3	1252.1	1250.1	1254.1	1257.5	1260.3	1264.4
7.5°	1167.3	1164.3	1164.6	1160.9	1164.6	1164.3	1167.3	1170.6	1174.9	1180.9	1186.5
10°	1116.7	1112.6	1111.2	1111.9	1111.2	1112.6	1116.7	1124.9	1127.6	1133.0	1139.1
12.5°	1074.8	1074.0	1065.0	1065.1	1065.0	1074.0	1074.8	1076.9	1082.9	1094.4	1101.6
15°	1025.5	1012.6	1011.2	1015.3	1011.2	1012.6	1025.5	1025.5	1028.2	1037.1	1041.2
17.5°	976.1	969.3	969.7	967.7	969.7	969.3	976.1	977.2	979.4	986.6	992.0
20°	950.0	945.9	945.2	940.4	945.2	945.9	950.0	950.0	952.7	956.1	961.5
22.5°	926.0	924.7	925.1	919.8	925.1	924.7	926.0	927.6	930.4	932.7	936.5
25°	896.2	899.6	896.9	896.9	896.9	899.6	896.2	896.9	897.6	901.0	903.7
27.5°	876.1	875.9	874.6	874.6	874.6	875.9	876.1	874.4	873.6	872.4	871.8
30°	860.8	860.1	861.5	861.5	861.5	860.1	860.8	858.1	856.7	856.1	853.3
32.5°	845.6	846.5	846.8	847.3	846.8	846.5	845.6	842.3	839.9	838.1	835.9
35°	822.0	822.7	824.8	823.4	824.8	822.7	822.0	818.0	815.2	811.1	807.7
37.5°	790.2	793.3	792.6	793.7	792.6	793.3	790.2	789.0	786.2	783.1	779.2
40°	766.2	768.3	767.6	767.6	767.6	768.3	766.2	765.6	762.8	760.8	757.4
42.5°	741.7	743.2	741.5	740.4	741.5	743.2	741.7	740.5	738.9	735.2	731.3
45°	701.6	700.2	702.3	699.5	702.3	700.2	701.6	698.9	698.2	695.5	692.1
47.5°	656.7	658.0	658.6	660.6	658.6	658.0	656.7	656.9	653.1	651.5	650.4
50°	626.7	630.8	630.8	630.1	630.8	630.8	626.7	625.4	622.6	619.9	619.9
52.5°	597.3	599.2	602.0	601.8	602.0	599.2	597.3	594.9	592.2	588.4	587.3
55°	551.9	553.2	554.6	555.3	554.6	553.2	551.9	546.4	544.4	542.4	538.9
57.5°	504.8	504.2	507.5	508.5	507.5	504.2	504.8	499.9	496.8	490.5	489.7
60°	471.6	471.6	477.0	479.1	477.0	471.6	471.6	466.1	461.4	457.3	455.9
62.5°	436.2	438.4	443.8	441.0	443.8	438.4	436.2	430.2	426.5	421.4	417.8
65°	384.5	389.9	389.2	392.0	389.2	389.9	384.5	381.1	373.6	368.8	364.7
67.5°	330.4	333.8	338.7	339.2	338.7	333.8	330.4	325.0	320.1	315.1	310.2
70°	294.0	297.4	300.1	302.1	300.1	297.4	294.0	288.5	283.1	279.7	274.2
72.5°	258.6	260.4	266.9	264.0	266.9	260.4	258.6	252.1	247.7	244.8	238.9
75°	202.8	207.5	211.6	209.6	211.6	207.5	202.8	198.0	194.6	190.5	185.1
77.5°	150.0	154.7	156.6	154.9	156.6	154.7	150.0	146.9	145.1	137.1	136.5
80°	118.4	117.7	121.8	121.1	121.8	117.7	118.4	113.6	110.2	105.5	105.5
82.5°	86.8	86.2	88.1	88.5	88.1	86.2	86.8	84.2	79.8	77.7	76.1
85°	42.2	44.2	41.5	40.8	41.5	44.2	42.2	39.5	39.5	39.5	38.8
87.5°	15.5	15.6	15.2	14.7	15.2	15.6	15.5	15.4	17.5	15.7	15.5
90°	28.6	29.1	29.5	29.9	29.5	29.1	28.6	28.2	27.5	26.6	25.7
92.5°	32.3	32.6	32.9	33.1	32.9	32.6	32.3	32.1	31.2	29.8	28.4
95°	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.9	37.2	35.6	34.0
97.5°	40.5	40.7	40.9	41.1	40.9	40.7	40.5	40.2	39.2	37.5	35.7
100°	41.3	41.5	41.7	41.9	41.7	41.5	41.3	41.0	40.0	38.3	36.5
102.5°	41.5	41.9	42.3	42.7	42.3	41.9	41.5	41.1	43.7	49.2	54.7
105°	42.6	43.0	43.5	43.9	43.5	43.0	42.6	42.1	61.6	100.8	140.1
107.5°	226.7	197.1	167.5	137.9	167.5	197.1	226.7	256.3	285.5	314.3	343.1
110°	369.6	337.9	306.2	274.5	306.2	337.9	369.6	401.4	420.9	428.2	435.5



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	491.0	484.3	477.6	470.9	477.6	484.3	491.0	497.7	501.0	500.9	500.7
115°	584.2	585.1	586.0	586.9	586.0	585.1	584.2	583.4	581.8	579.6	577.4
117.5°	651.5	651.6	651.8	652.0	651.8	651.6	651.5	651.3	650.3	648.5	646.8
120°	696.7	696.7	696.7	696.7	696.7	696.7	696.7	696.7	695.8	694.0	692.3
122.5°	740.1	740.3	740.4	740.6	740.4	740.3	740.1	739.9	739.2	738.0	736.7
125°	801.2	801.6	802.1	802.5	802.1	801.6	801.2	800.7	800.3	799.8	799.4
127.5°	863.3	862.9	862.4	862.0	862.4	862.9	863.3	863.8	863.6	862.9	862.2
130°	901.7	901.2	900.8	900.3	900.8	901.2	901.7	902.1	901.9	901.0	900.1
132.5°	937.3	936.7	936.1	935.5	936.1	936.7	937.3	937.9	937.8	936.9	936.0
135°	991.2	990.5	989.8	989.2	989.8	990.5	991.2	991.8	991.8	991.2	990.5
137.5°	1041.0	1040.6	1040.1	1039.7	1040.1	1040.6	1041.0	1041.4	1041.1	1040.1	1039.0
140°	1071.3	1070.9	1070.5	1070.0	1070.5	1070.9	1071.3	1071.8	1071.6	1070.7	1069.8
142.5°	1099.8	1099.2	1098.6	1098.0	1098.6	1099.2	1099.8	1100.4	1100.4	1099.7	1099.0
145°	1140.9	1140.9	1140.9	1140.9	1140.9	1140.9	1140.9	1140.9	1140.7	1140.2	1139.8
147.5°	1175.9	1174.9	1173.8	1172.8	1173.8	1174.9	1175.9	1176.9	1177.2	1176.7	1176.3
150°	1198.8	1198.1	1197.4	1196.8	1197.4	1198.1	1198.8	1199.4	1199.6	1199.1	1198.7
152.5°	1219.0	1218.0	1217.0	1215.9	1217.0	1218.0	1219.0	1220.0	1220.1	1219.3	1218.5
155°	1246.7	1245.4	1244.0	1242.7	1244.0	1245.4	1246.7	1248.0	1248.1	1247.0	1245.9
157.5°	1270.4	1268.7	1267.0	1265.3	1267.0	1268.7	1270.4	1272.2	1272.4	1271.0	1269.7
160°	1284.3	1282.7	1281.2	1279.6	1281.2	1282.7	1284.3	1285.8	1285.9	1284.6	1283.3
162.5°	1297.3	1295.9	1294.6	1293.2	1294.6	1295.9	1297.3	1298.7	1298.6	1297.1	1295.6
165°	1314.2	1312.7	1311.1	1309.6	1311.1	1312.7	1314.2	1315.8	1315.7	1313.9	1312.1
167.5°	1326.7	1324.9	1323.1	1321.3	1323.1	1324.9	1326.7	1328.4	1328.4	1326.7	1324.9
170°	1333.9	1332.1	1330.3	1328.5	1330.3	1332.1	1333.9	1335.6	1335.6	1333.9	1332.1
172.5°	1338.4	1336.4	1334.5	1332.5	1334.5	1336.4	1338.4	1340.3	1340.4	1338.6	1336.9
175°	1343.8	1342.1	1340.3	1338.5	1340.3	1342.1	1343.8	1345.6	1345.7	1344.2	1342.6
177.5°	1345.6	1343.9	1342.1	1340.3	1342.1	1343.9	1345.6	1347.4	1347.6	1346.2	1344.7
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1346.8	1346.8	1357.2	1363.7	1371.9	1377.3	1381.1	1384.9	1391.5	1400.2	1410.0
5°	1269.8	1272.5	1287.5	1302.5	1316.8	1329.0	1339.2	1351.5	1366.4	1384.8	1405.2
7.5°	1195.2	1205.7	1220.8	1239.0	1259.0	1276.9	1295.0	1315.1	1336.2	1363.3	1391.9
10°	1147.3	1158.9	1177.2	1200.4	1221.5	1242.6	1265.0	1286.8	1313.3	1345.3	1382.1
12.5°	1105.4	1116.4	1135.3	1160.6	1180.7	1203.9	1229.6	1258.0	1287.8	1326.3	1367.9
15°	1047.3	1060.2	1083.3	1095.6	1126.2	1154.1	1177.9	1218.8	1256.9	1296.3	1344.7
17.5°	999.6	1006.9	1025.6	1048.4	1071.2	1102.5	1133.7	1167.7	1205.7	1254.0	1314.4
20°	967.0	973.1	993.5	1017.3	1041.8	1070.4	1098.3	1132.3	1175.2	1226.2	1291.6
22.5°	942.5	949.1	962.5	987.9	1010.8	1034.5	1062.4	1102.9	1148.5	1198.5	1269.3
25°	907.1	911.2	920.0	940.4	960.9	987.4	1011.9	1050.0	1097.0	1155.5	1226.2
27.5°	873.5	877.4	884.8	899.5	918.5	940.0	966.7	999.1	1046.7	1110.3	1185.4
30°	853.3	854.0	860.8	874.4	890.8	908.5	933.0	969.7	1014.6	1079.3	1158.2
32.5°	835.9	833.3	838.0	848.3	864.1	881.8	901.9	938.1	981.4	1045.0	1126.1
35°	806.4	805.0	803.0	811.8	825.4	839.0	856.7	884.0	933.0	992.2	1077.2
37.5°	776.3	773.0	769.4	773.4	784.1	798.2	813.6	837.8	880.0	945.2	1026.6
40°	754.0	751.3	749.2	747.9	757.4	771.0	782.6	805.7	845.2	907.1	987.4
42.5°	729.5	727.9	725.3	723.4	731.3	741.6	753.7	774.1	813.6	871.7	947.7
45°	690.0	688.7	687.3	685.9	690.7	700.2	709.8	724.7	758.7	815.2	884.0
47.5°	646.1	644.3	644.8	642.7	647.3	653.7	660.3	676.4	709.1	754.7	804.9
50°	614.5	613.8	613.8	613.8	615.2	622.6	628.8	641.0	671.0	716.6	752.6
52.5°	584.5	581.7	581.7	582.8	585.2	590.0	593.9	607.3	633.4	670.8	703.6
55°	537.6	532.1	530.8	532.1	534.2	538.3	542.4	553.2	575.7	603.6	622.6
57.5°	485.6	482.6	480.8	481.1	482.2	485.5	488.6	500.4	518.1	532.7	544.9
60°	449.1	450.5	444.4	445.7	445.7	448.4	453.2	460.7	475.7	485.9	498.1
62.5°	414.8	412.9	411.2	409.2	409.2	410.3	416.7	422.6	435.4	440.7	450.2
65°	361.3	361.3	357.3	358.6	359.3	354.5	357.9	364.7	372.9	375.0	383.8
67.5°	307.2	305.3	303.0	300.9	300.9	300.5	302.3	305.7	311.8	312.5	319.3
70°	270.2	268.8	268.1	266.1	263.4	266.8	264.7	268.1	271.5	272.2	276.3
72.5°	234.2	232.9	231.6	229.6	228.5	228.1	228.2	232.2	234.5	233.5	238.2
75°	183.1	181.7	180.3	176.9	176.9	174.9	175.6	178.3	181.0	179.0	183.1
77.5°	134.5	130.2	130.0	130.9	128.6	129.0	128.2	127.8	129.0	129.2	132.8
80°	103.4	98.7	100.0	99.4	98.7	98.0	96.6	97.3	98.0	98.7	100.7
82.5°	74.6	74.2	72.8	72.7	72.0	70.2	69.4	70.6	71.3	70.9	72.4
85°	38.1	36.1	37.4	36.7	37.4	36.7	34.7	34.7	36.1	35.4	36.7
87.5°	16.4	16.2	15.1	15.1	13.9	13.9	12.9	13.0	13.1	12.6	13.3
90°	24.8	24.0	21.1	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0
92.5°	27.0	25.6	23.4	21.2	19.0	16.9	16.1	16.7	17.3	17.9	18.6
95°	32.5	30.9	28.5	26.1	23.6	21.2	24.5	33.6	42.7	51.8	60.9
97.5°	33.9	32.1	48.1	64.1	80.1	96.0	106.0	110.1	114.2	118.3	122.4
100°	34.7	32.9	67.5	102.1	136.7	171.3	186.4	182.0	177.6	173.1	168.7
102.5°	60.2	65.7	103.5	141.3	179.1	216.9	234.2	231.0	227.8	224.6	221.4
105°	179.3	218.6	238.6	258.5	278.5	298.4	307.2	304.8	302.3	299.9	297.4
107.5°	371.9	400.7	397.5	394.4	391.2	388.1	385.5	383.6	381.6	379.7	377.7
110°	442.8	450.2	447.7	445.3	442.8	440.4	438.3	436.5	434.7	433.0	431.2



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	500.6	500.5	498.0	495.6	493.2	490.7	488.7	487.1	485.5	483.9	482.3
115°	575.2	572.9	570.9	568.9	566.9	565.0	563.3	562.0	560.6	559.3	558.0
117.5°	645.0	643.2	642.2	641.2	640.1	639.1	637.8	636.2	634.5	632.9	631.2
120°	690.5	688.7	688.1	687.4	686.7	686.1	684.7	682.7	680.7	678.7	676.7
122.5°	735.5	734.2	733.4	732.6	731.7	730.9	729.6	728.0	726.3	724.7	723.1
125°	799.0	798.5	797.6	796.7	795.9	795.0	793.6	791.9	790.1	788.3	786.5
127.5°	861.5	860.8	859.7	858.7	857.6	856.5	855.1	853.3	851.6	849.8	848.0
130°	899.2	898.3	897.4	896.6	895.7	894.8	893.5	891.7	889.9	888.1	886.4
132.5°	935.2	934.3	933.6	932.8	932.1	931.4	930.2	928.4	926.6	924.9	923.1
135°	989.8	989.2	988.3	987.4	986.5	985.6	984.5	983.2	981.8	980.5	979.2
137.5°	1037.9	1036.9	1036.4	1035.9	1035.4	1034.9	1033.8	1032.2	1030.5	1028.8	1027.1
140°	1068.9	1068.0	1067.4	1066.7	1066.0	1065.4	1064.4	1063.0	1061.7	1060.4	1059.0
142.5°	1098.3	1097.6	1096.9	1096.2	1095.6	1094.9	1093.9	1092.6	1091.2	1089.9	1088.6
145°	1139.3	1138.9	1138.4	1138.0	1137.6	1137.1	1136.1	1134.6	1133.0	1131.5	1129.9
147.5°	1175.9	1175.4	1175.0	1174.5	1174.1	1173.6	1172.9	1171.9	1170.9	1169.9	1168.8
150°	1198.2	1197.8	1197.3	1196.9	1196.4	1196.0	1195.4	1194.8	1194.1	1193.5	1192.8
152.5°	1217.7	1216.9	1216.7	1216.4	1216.1	1215.9	1215.6	1215.3	1215.0	1214.7	1214.3
155°	1244.8	1243.7	1243.5	1243.2	1243.0	1242.8	1242.9	1243.4	1243.8	1244.2	1244.7
157.5°	1268.4	1267.0	1267.3	1267.5	1267.7	1267.9	1268.1	1268.1	1268.2	1268.2	1268.2
160°	1282.0	1280.6	1280.8	1281.1	1281.3	1281.5	1281.7	1282.0	1282.2	1282.4	1282.6
162.5°	1294.1	1292.6	1292.8	1293.0	1293.3	1293.5	1293.9	1294.5	1295.0	1295.6	1296.2
165°	1310.3	1308.6	1308.8	1309.0	1309.2	1309.5	1309.9	1310.6	1311.2	1311.9	1312.6
167.5°	1323.1	1321.3	1321.3	1321.3	1321.3	1321.3	1321.8	1322.7	1323.6	1324.5	1325.3
170°	1330.3	1328.5	1328.5	1328.5	1328.5	1328.5	1329.0	1329.9	1330.8	1331.6	1332.5
172.5°	1335.1	1333.3	1333.1	1333.0	1332.8	1332.6	1333.1	1334.1	1335.2	1336.3	1337.3
175°	1341.1	1339.5	1339.3	1339.1	1338.8	1338.6	1339.1	1340.2	1341.3	1342.4	1343.5
177.5°	1343.3	1341.9	1341.7	1341.6	1341.4	1341.2	1341.6	1342.4	1343.3	1344.2	1345.1
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1413.2	1416.0	1425.2	1431.8	1439.4	1443.7	1448.1	1451.4	1455.7	1456.8	1472.6
5°	1419.5	1433.1	1456.9	1474.6	1496.4	1520.2	1536.5	1544.0	1563.8	1580.1	1612.8
7.5°	1417.7	1446.7	1482.7	1519.9	1560.0	1597.0	1629.1	1667.2	1694.3	1735.0	1775.1
10°	1416.1	1454.9	1501.2	1548.8	1604.6	1656.3	1702.6	1754.3	1797.2	1853.7	1902.0
12.5°	1411.2	1458.2	1522.4	1578.7	1646.5	1717.8	1786.4	1852.8	1890.8	1984.9	2029.4
15°	1399.1	1454.9	1535.2	1620.9	1714.2	1798.5	1885.6	1955.1	2067.3	2149.7	2202.1
17.5°	1376.0	1454.1	1549.3	1652.8	1766.1	1877.3	1976.0	2081.4	2200.4	2300.1	2406.2
20°	1365.1	1450.8	1557.0	1671.3	1789.0	1914.9	2027.2	2153.8	2283.7	2381.7	2517.8
22.5°	1344.9	1442.1	1556.4	1683.8	1809.7	1939.9	2071.3	2198.9	2349.1	2484.1	2613.6
25°	1312.0	1420.9	1539.3	1681.5	1829.2	1959.8	2117.0	2286.5	2443.0	2616.5	2745.8
27.5°	1277.4	1393.6	1512.3	1644.6	1803.4	1958.5	2156.2	2347.7	2539.0	2688.9	2784.6
30°	1250.7	1363.7	1486.2	1619.6	1776.8	1961.2	2182.3	2391.2	2577.7	2706.3	2760.1
32.5°	1221.9	1336.5	1444.8	1584.7	1752.3	1959.5	2198.7	2416.8	2579.9	2665.5	2655.0
35°	1176.6	1272.5	1378.0	1512.7	1710.1	1947.6	2208.2	2419.1	2519.2	2500.8	2362.0
37.5°	1111.2	1191.9	1295.8	1443.3	1661.1	1922.4	2189.1	2347.4	2340.9	2191.3	1990.2
40°	1070.4	1139.1	1239.2	1394.3	1623.0	1906.1	2159.2	2262.0	2174.9	1965.9	1725.0
42.5°	1017.1	1080.3	1180.4	1339.9	1581.1	1872.8	2102.0	2131.8	1961.4	1721.0	1500.2
45°	934.3	990.1	1093.5	1258.2	1518.2	1800.6	1962.5	1889.7	1660.4	1412.0	1243.9
47.5°	845.4	903.4	1002.9	1172.1	1427.3	1691.8	1769.0	1614.1	1378.7	1177.2	1022.9
50°	789.4	845.2	942.5	1113.3	1365.7	1602.6	1634.5	1434.5	1218.1	1041.2	914.6
52.5°	732.8	785.3	881.0	1052.3	1293.9	1499.1	1479.4	1275.5	1076.5	925.7	826.4
55°	648.5	698.2	789.4	950.0	1169.8	1332.4	1261.0	1066.3	901.7	784.6	709.1
57.5°	573.1	620.7	699.4	844.5	1035.6	1147.3	1056.4	892.4	761.5	671.4	615.0
60°	521.9	564.1	639.0	773.7	939.8	1024.8	935.0	790.1	679.8	607.7	557.3
62.5°	473.5	510.2	579.6	701.9	846.1	917.6	826.7	704.0	610.1	546.2	503.4
65°	400.1	433.5	494.7	590.0	708.4	756.0	677.8	578.4	505.6	458.0	429.4
67.5°	333.2	361.5	414.4	489.4	576.5	611.2	551.6	474.7	419.9	381.6	358.9
70°	288.5	313.0	354.5	419.2	498.1	524.7	468.9	405.6	365.4	334.8	313.7
72.5°	251.0	268.9	306.6	356.6	422.4	443.5	404.6	349.0	311.5	288.5	271.8
75°	191.2	206.2	230.7	270.8	316.4	328.7	299.4	264.7	239.5	223.2	210.3
77.5°	137.9	148.9	166.6	191.4	222.9	234.0	215.4	192.3	173.9	162.9	155.7
80°	104.1	113.0	127.9	148.3	167.4	173.5	162.6	144.9	132.0	125.9	119.8
82.5°	76.9	81.9	90.9	104.8	117.9	125.1	115.8	105.2	98.3	92.7	90.4
85°	38.8	41.5	45.6	51.0	59.2	61.9	58.5	55.8	51.7	48.3	48.3
87.5°	14.8	15.2	17.3	18.9	21.5	23.7	23.8	23.3	23.3	22.9	22.6
90°	3.2	5.4	7.7	9.9	12.4	15.3	18.2	21.1	24.0	24.8	25.7
92.5°	17.9	17.3	16.7	16.1	16.9	19.0	21.2	23.4	25.6	27.0	28.4
95°	51.8	42.7	33.6	24.5	21.2	23.6	26.1	28.5	30.9	32.5	34.0
97.5°	118.3	114.2	110.1	106.0	96.0	80.1	64.1	48.1	32.1	33.9	35.7
100°	173.1	177.6	182.0	186.4	171.3	136.7	102.1	67.5	32.9	34.7	36.5
102.5°	224.6	227.8	231.0	234.2	216.9	179.1	141.3	103.5	65.7	60.2	54.7
105°	299.9	302.3	304.8	307.2	298.4	278.5	258.5	238.6	218.6	179.3	140.1
107.5°	379.7	381.6	383.6	385.5	388.1	391.2	394.4	397.5	400.7	371.9	343.1
110°	433.0	434.7	436.5	438.3	440.4	442.8	445.3	447.7	450.2	442.8	435.5



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	483.9	485.5	487.1	488.7	490.7	493.2	495.6	498.0	500.5	500.6	500.7
115°	559.3	560.6	562.0	563.3	565.0	566.9	568.9	570.9	572.9	575.2	577.4
117.5°	632.9	634.5	636.2	637.8	639.1	640.1	641.2	642.2	643.2	645.0	646.8
120°	678.7	680.7	682.7	684.7	686.1	686.7	687.4	688.1	688.7	690.5	692.3
122.5°	724.7	726.3	728.0	729.6	730.9	731.7	732.6	733.4	734.2	735.5	736.7
125°	788.3	790.1	791.9	793.6	795.0	795.9	796.7	797.6	798.5	799.0	799.4
127.5°	849.8	851.6	853.3	855.1	856.5	857.6	858.7	859.7	860.8	861.5	862.2
130°	888.1	889.9	891.7	893.5	894.8	895.7	896.6	897.4	898.3	899.2	900.1
132.5°	924.9	926.6	928.4	930.2	931.4	932.1	932.8	933.6	934.3	935.2	936.0
135°	980.5	981.8	983.2	984.5	985.6	986.5	987.4	988.3	989.2	989.8	990.5
137.5°	1028.8	1030.5	1032.2	1033.8	1034.9	1035.4	1035.9	1036.4	1036.9	1037.9	1039.0
140°	1060.4	1061.7	1063.0	1064.4	1065.4	1066.0	1066.7	1067.4	1068.0	1068.9	1069.8
142.5°	1089.9	1091.2	1092.6	1093.9	1094.9	1095.6	1096.2	1096.9	1097.6	1098.3	1099.0
145°	1131.5	1133.0	1134.6	1136.1	1137.1	1137.6	1138.0	1138.4	1138.9	1139.3	1139.8
147.5°	1169.9	1170.9	1171.9	1172.9	1173.6	1174.1	1174.5	1175.0	1175.4	1175.9	1176.3
150°	1193.5	1194.1	1194.8	1195.4	1196.0	1196.4	1196.9	1197.3	1197.8	1198.2	1198.7
152.5°	1214.7	1215.0	1215.3	1215.6	1215.9	1216.1	1216.4	1216.7	1216.9	1217.7	1218.5
155°	1244.2	1243.8	1243.4	1242.9	1242.8	1243.0	1243.2	1243.5	1243.7	1244.8	1245.9
157.5°	1268.2	1268.2	1268.1	1268.1	1267.9	1267.7	1267.5	1267.3	1267.0	1268.4	1269.7
160°	1282.4	1282.2	1282.0	1281.7	1281.5	1281.3	1281.1	1280.8	1280.6	1282.0	1283.3
162.5°	1295.6	1295.0	1294.5	1293.9	1293.5	1293.3	1293.0	1292.8	1292.6	1294.1	1295.6
165°	1311.9	1311.2	1310.6	1309.9	1309.5	1309.2	1309.0	1308.8	1308.6	1310.3	1312.1
167.5°	1324.5	1323.6	1322.7	1321.8	1321.3	1321.3	1321.3	1321.3	1321.3	1323.1	1324.9
170°	1331.6	1330.8	1329.9	1329.0	1328.5	1328.5	1328.5	1328.5	1328.5	1330.3	1332.1
172.5°	1336.3	1335.2	1334.1	1333.1	1332.6	1332.8	1333.0	1333.1	1333.3	1335.1	1336.9
175°	1342.4	1341.3	1340.2	1339.1	1338.6	1338.8	1339.1	1339.3	1339.5	1341.1	1342.6
177.5°	1344.2	1343.3	1342.4	1341.6	1341.2	1341.4	1341.6	1341.7	1341.9	1343.3	1344.7
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1478.0	1478.6	1484.6	1488.9	1486.7	1489.5	1490.5
5°	1614.8	1639.3	1652.2	1661.8	1662.4	1663.1	1668.6
7.5°	1808.7	1835.0	1854.2	1883.3	1892.0	1902.0	1899.1
10°	1950.3	1989.1	2022.4	2040.1	2059.2	2087.1	2064.6
12.5°	2082.6	2151.3	2202.1	2229.6	2247.5	2253.1	2242.1
15°	2300.7	2390.6	2438.9	2437.5	2498.8	2525.3	2483.8
17.5°	2500.8	2583.7	2650.1	2684.1	2735.2	2746.5	2741.3
20°	2623.3	2713.8	2765.5	2824.0	2850.6	2874.4	2878.5
22.5°	2728.9	2810.2	2865.7	2914.4	2936.6	2947.9	2954.7
25°	2837.6	2901.6	2935.0	2952.0	2958.1	2956.7	2947.9
27.5°	2830.2	2835.1	2798.3	2762.3	2730.0	2693.7	2681.1
30°	2756.7	2699.5	2597.4	2539.6	2454.5	2387.2	2414.4
32.5°	2563.4	2449.6	2335.0	2208.6	2103.9	2074.1	2044.2
35°	2187.8	1987.7	1870.7	1734.6	1680.1	1625.7	1588.3
37.5°	1770.0	1615.2	1476.4	1387.4	1332.8	1298.4	1279.9
40°	1530.4	1390.9	1276.6	1204.5	1163.0	1124.2	1118.7
42.5°	1339.3	1209.6	1123.6	1066.2	1026.3	1009.8	997.9
45°	1097.0	1006.4	948.6	907.8	881.2	871.0	857.4
47.5°	928.5	864.5	821.1	793.3	773.3	765.7	764.6
50°	834.3	781.2	749.2	727.4	711.8	709.1	698.2
52.5°	763.5	717.5	692.6	673.6	662.3	654.6	651.4
55°	662.8	632.2	609.7	598.8	590.0	582.5	582.5
57.5°	579.9	554.3	539.5	530.2	527.5	522.2	518.8
60°	528.7	507.0	495.4	487.2	481.8	482.5	476.3
62.5°	478.7	464.5	453.5	445.3	438.8	438.9	439.3
65°	407.6	396.7	388.6	385.8	381.8	377.0	378.4
67.5°	345.4	335.2	328.8	324.2	322.8	320.2	324.2
70°	300.8	293.3	288.5	284.4	283.1	283.8	287.2
72.5°	259.9	254.6	251.5	249.6	246.6	246.7	249.1
75°	204.1	200.1	197.3	195.3	194.6	194.6	194.6
77.5°	150.0	149.0	147.8	144.8	144.9	145.8	145.9
80°	118.4	116.4	115.7	114.3	112.3	110.9	114.3
82.5°	88.5	86.4	85.7	85.5	82.3	82.1	84.9
85°	47.6	45.6	46.3	45.6	45.6	44.9	44.9
87.5°	22.2	21.8	21.4	22.1	21.6	21.1	22.3
90°	26.6	27.5	28.2	28.6	29.1	29.5	29.9
92.5°	29.8	31.2	32.1	32.3	32.6	32.9	33.1
95°	35.6	37.2	37.9	37.9	37.9	37.9	37.9
97.5°	37.5	39.2	40.2	40.5	40.7	40.9	41.1
100°	38.3	40.0	41.0	41.3	41.5	41.7	41.9
102.5°	49.2	43.7	41.1	41.5	41.9	42.3	42.7
105°	100.8	61.6	42.1	42.6	43.0	43.5	43.9
107.5°	314.3	285.5	256.3	226.7	197.1	167.5	137.9
110°	428.2	420.9	401.4	369.6	337.9	306.2	274.5



TEST NUMBER: P332027

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	500.9	501.0	497.7	491.0	484.3	477.6	470.9
115°	579.6	581.8	583.4	584.2	585.1	586.0	586.9
117.5°	648.5	650.3	651.3	651.5	651.6	651.8	652.0
120°	694.0	695.8	696.7	696.7	696.7	696.7	696.7
122.5°	738.0	739.2	739.9	740.1	740.3	740.4	740.6
125°	799.8	800.3	800.7	801.2	801.6	802.1	802.5
127.5°	862.9	863.6	863.8	863.3	862.9	862.4	862.0
130°	901.0	901.9	902.1	901.7	901.2	900.8	900.3
132.5°	936.9	937.8	937.9	937.3	936.7	936.1	935.5
135°	991.2	991.8	991.8	991.2	990.5	989.8	989.2
137.5°	1040.1	1041.1	1041.4	1041.0	1040.6	1040.1	1039.7
140°	1070.7	1071.6	1071.8	1071.3	1070.9	1070.5	1070.0
142.5°	1099.7	1100.4	1100.4	1099.8	1099.2	1098.6	1098.0
145°	1140.2	1140.7	1140.9	1140.9	1140.9	1140.9	1140.9
147.5°	1176.7	1177.2	1176.9	1175.9	1174.9	1173.8	1172.8
150°	1199.1	1199.6	1199.4	1198.8	1198.1	1197.4	1196.8
152.5°	1219.3	1220.1	1220.0	1219.0	1218.0	1217.0	1215.9
155°	1247.0	1248.1	1248.0	1246.7	1245.4	1244.0	1242.7
157.5°	1271.0	1272.4	1272.2	1270.4	1268.7	1267.0	1265.3
160°	1284.6	1285.9	1285.8	1284.3	1282.7	1281.2	1279.6
162.5°	1297.1	1298.6	1298.7	1297.3	1295.9	1294.6	1293.2
165°	1313.9	1315.7	1315.8	1314.2	1312.7	1311.1	1309.6
167.5°	1326.7	1328.4	1328.4	1326.7	1324.9	1323.1	1321.3
170°	1333.9	1335.6	1335.6	1333.9	1332.1	1330.3	1328.5
172.5°	1338.6	1340.4	1340.3	1338.4	1336.4	1334.5	1332.5
175°	1344.2	1345.7	1345.6	1343.8	1342.1	1340.3	1338.5
177.5°	1346.2	1347.6	1347.4	1345.6	1343.9	1342.1	1340.3
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5

(END OF REPORT)