

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332273-935

Luminaire Tested: **S123RDIP-S560D365U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332273-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D365U935-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3087.1 lumens  
Efficiency: N/A  
Efficacy: 112.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.23  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332273-935

CATALOG NUMBER: S123RDIP-S560D365U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332273-935

CATALOG NUMBER: S123RDIP-S560D365U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	51	49	47	43
3	84	74	67	61	78	70	64	58	61	56	52	53	50	46	46	43	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	41	38	35	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	37	34	31	28
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	28	25
7	61	48	40	35	56	46	38	33	40	35	30	36	31	27	31	27	25	22
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	53	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8753	8753	8753
5°	8787	8666	8715
10°	8737	8557	8528
15°	8643	8357	8269
20°	8514	8107	7918
25°	8381	7826	7574
30°	8206	7501	7091
35°	8025	7176	6646
40°	7859	6794	6097
45°	7640	6416	5602
50°	7400	5987	5047
55°	7156	5495	4530
60°	6928	4969	3961
65°	6635	4401	3393
70°	6266	3695	2738
75°	5731	2907	2578
80°	5114	2579	2368
85°	4323	2272	2112



TEST NUMBER: P332273-935

CATALOG NUMBER: S123RDIP-S560D365U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.4	2.5
10°-20°	212.5	6.9
20°-30°	305.9	9.9
30°-40°	344.6	11.2
40°-50°	329.7	10.7
50°-60°	270.0	8.7
60°-70°	182.2	5.9
70°-80°	91.6	3.0
80°-90°	25.4	0.8
90°-100°	14.9	0.5
100°-110°	71.0	2.3
110°-120°	170.4	5.5
120°-130°	217.0	7.0
130°-140°	231.9	7.5
140°-150°	216.9	7.0
150°-160°	174.9	5.7
160°-170°	112.9	3.7
170°-180°	38.9	1.3
0°-30°	594.8	19.3
0°-40°	939.4	30.4
0°-60°	1539.1	49.9
0°-90°	1838.3	59.5
90°-120°	256.3	8.3
90°-150°	922.1	29.9
90°-180°	1249.0	40.5
0°-180°	3087.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	813	813	813	813	813	
5°	813	810	802	808	807	77
15°	776	768	750	747	742	218
25°	706	688	659	645	638	324
35°	611	586	546	519	506	382
45°	502	471	422	385	368	387
55°	381	348	293	256	241	342
65°	260	223	173	142	133	258
75°	138	106	70	64	62	147
85°	35	21	18	17	17	39
90°	0	3	7	8	9	3
95°	19	7	10	11	12	23
105°	91	92	67	16	13	96
115°	170	172	175	178	179	168
125°	240	242	243	244	245	214
135°	298	300	302	302	302	230
145°	344	346	347	348	348	216
155°	379	379	379	380	379	175
165°	400	399	399	401	399	113
175°	410	408	408	410	408	39
180°	410	410	410	410	410	



TEST NUMBER: P332273-935

CATALOG NUMBER: S123RDIP-S560D365U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	815.9	815.4	814.9	814.4	814.0	813.0	811.7	810.2	808.8	807.4	808.7
5°	813.2	812.5	811.8	811.1	810.3	809.1	807.3	805.6	803.7	802.0	803.3
7.5°	805.7	804.9	804.1	803.3	802.5	801.0	798.7	796.4	794.1	791.9	792.6
10°	799.4	798.3	797.3	796.3	795.3	793.4	790.8	788.2	785.5	782.9	783.0
12.5°	790.4	789.3	788.1	787.0	785.8	783.7	780.4	777.2	774.0	770.8	770.7
15°	775.6	774.0	772.4	770.8	769.2	766.3	762.2	758.1	754.0	749.9	749.2
17.5°	757.0	755.2	753.3	751.4	749.5	746.0	740.7	735.6	730.3	725.1	723.6
20°	743.3	741.0	738.7	736.2	733.9	730.0	724.4	718.8	713.3	707.7	705.8
22.5°	728.0	725.3	722.6	719.9	717.2	712.9	707.0	701.0	695.2	689.2	686.8
25°	705.7	702.1	698.4	694.7	691.0	685.9	679.1	672.4	665.6	658.9	655.8
27.5°	678.6	674.6	670.5	666.5	662.5	656.7	649.2	641.7	634.2	626.7	622.4
30°	660.2	655.8	651.4	647.0	642.7	636.3	628.1	619.9	611.7	603.5	598.5
32.5°	641.7	636.8	631.8	626.8	621.8	615.0	606.3	597.6	588.9	580.2	574.8
35°	610.7	605.5	600.2	595.0	589.6	582.5	573.3	564.3	555.2	546.1	539.8
37.5°	579.4	573.5	567.7	561.7	555.9	548.1	538.4	528.7	519.0	509.3	502.1
40°	559.3	552.8	546.4	539.9	533.5	525.0	514.7	504.3	493.9	483.5	475.8
42.5°	536.6	530.1	523.7	517.3	510.8	502.2	491.5	480.7	469.9	459.2	450.8
45°	501.9	495.3	488.7	482.2	475.5	466.6	455.3	444.0	432.7	421.5	413.1
47.5°	467.2	459.9	452.7	445.5	438.2	429.0	417.7	406.4	395.1	383.8	374.8
50°	441.9	435.0	428.1	421.2	414.3	404.9	393.0	381.3	369.4	357.5	348.4
52.5°	419.2	411.7	404.2	396.7	389.3	379.7	367.9	356.2	344.4	332.7	323.2
55°	381.3	374.0	366.9	359.6	352.5	342.7	330.2	317.8	305.3	292.8	284.3
57.5°	346.1	338.3	330.5	322.6	314.8	304.6	292.1	279.7	267.1	254.6	246.6
60°	321.8	313.8	305.7	297.6	289.6	279.5	267.3	255.2	243.0	230.8	222.9
62.5°	297.6	289.6	281.5	273.4	265.4	255.2	243.1	230.9	218.7	206.6	199.1
65°	260.5	252.4	244.4	236.3	228.3	218.5	207.1	195.7	184.3	172.8	165.7
67.5°	223.4	215.3	207.2	199.0	190.9	181.3	170.3	159.4	148.4	137.4	132.1
70°	199.1	191.2	183.4	175.5	167.6	158.4	148.2	137.9	127.7	117.4	112.3
72.5°	174.9	167.1	159.3	151.5	143.7	135.2	125.9	116.5	107.2	97.9	93.7
75°	137.8	130.8	123.8	116.8	109.7	102.1	94.1	86.0	78.0	69.9	68.4
77.5°	104.1	97.7	91.4	85.0	78.6	72.8	67.7	62.5	57.3	52.1	51.3
80°	82.5	76.5	70.4	64.4	58.4	53.9	50.8	47.7	44.6	41.6	41.1
82.5°	61.9	56.7	51.5	46.3	41.1	37.8	36.3	35.0	33.5	32.0	31.6
85°	35.0	31.8	28.5	25.3	22.0	20.2	19.8	19.4	18.9	18.4	18.2
87.5°	12.7	11.5	10.4	9.3	8.1	7.6	7.8	8.0	8.2	8.4	8.3
90°	0.3	0.9	1.6	2.3	3.0	3.8	4.6	5.5	6.5	7.3	7.6
92.5°	5.7	5.5	5.3	5.1	4.9	5.2	5.8	6.5	7.1	7.7	8.2
95°	18.6	15.8	13.0	10.2	7.5	6.5	7.2	7.9	8.7	9.5	9.9
97.5°	37.3	36.1	34.8	33.6	32.3	29.3	24.4	19.5	14.6	9.8	10.3
100°	51.4	52.8	54.2	55.4	56.8	52.3	41.7	31.2	20.6	10.1	10.6
102.5°	67.5	68.4	69.4	70.4	71.4	66.1	54.6	43.0	31.5	20.1	18.3
105°	90.7	91.4	92.1	92.9	93.7	91.0	84.9	78.8	72.8	66.6	54.7
107.5°	115.1	115.7	116.3	116.9	117.5	118.3	119.2	120.2	121.1	122.1	113.3
110°	131.5	132.0	132.5	133.0	133.6	134.2	135.0	135.7	136.5	137.2	135.0



TEST NUMBER: P332273-935

CATALOG NUMBER: S123RDIP-S560D365U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.0	147.5	148.0	148.4	149.0	149.6	150.3	151.1	151.8	152.6	152.6
115°	170.0	170.5	170.9	171.3	171.7	172.2	172.8	173.4	174.0	174.6	175.3
117.5°	192.4	193.0	193.4	193.9	194.4	194.8	195.1	195.4	195.8	196.0	196.6
120°	206.3	206.9	207.5	208.1	208.7	209.1	209.3	209.6	209.7	209.9	210.5
122.5°	220.4	220.9	221.4	221.9	222.4	222.7	223.0	223.3	223.5	223.8	224.2
125°	239.8	240.3	240.8	241.3	241.9	242.3	242.6	242.9	243.1	243.4	243.6
127.5°	258.5	259.1	259.6	260.1	260.6	261.1	261.4	261.7	262.1	262.3	262.6
130°	270.2	270.7	271.2	271.8	272.3	272.8	273.0	273.3	273.5	273.8	274.1
132.5°	281.4	281.9	282.5	283.0	283.5	283.9	284.1	284.4	284.6	284.8	285.1
135°	298.5	298.9	299.3	299.7	300.1	300.4	300.7	301.0	301.3	301.5	301.7
137.5°	313.1	313.6	314.1	314.6	315.1	315.5	315.6	315.7	315.9	316.1	316.4
140°	322.8	323.2	323.6	324.0	324.4	324.8	324.9	325.1	325.4	325.5	325.8
142.5°	331.8	332.3	332.6	333.0	333.5	333.7	334.0	334.2	334.3	334.6	334.8
145°	344.4	344.9	345.3	345.9	346.3	346.6	346.7	346.9	347.0	347.2	347.3
147.5°	356.3	356.6	356.9	357.2	357.5	357.7	357.9	358.0	358.2	358.3	358.4
150°	363.6	363.8	363.9	364.2	364.4	364.5	364.7	364.8	365.0	365.1	365.2
152.5°	370.1	370.2	370.3	370.4	370.5	370.7	370.7	370.7	370.8	370.9	371.2
155°	379.4	379.3	379.1	379.0	378.8	378.8	378.9	378.9	379.0	379.1	379.4
157.5°	386.6	386.6	386.6	386.5	386.5	386.5	386.4	386.3	386.2	386.2	386.6
160°	391.0	390.9	390.8	390.7	390.7	390.6	390.5	390.5	390.5	390.4	390.7
162.5°	395.1	394.9	394.8	394.6	394.4	394.3	394.2	394.2	394.1	394.0	394.4
165°	400.1	399.8	399.7	399.5	399.2	399.2	399.1	399.0	398.9	398.9	399.4
167.5°	404.0	403.7	403.5	403.2	402.9	402.8	402.8	402.8	402.8	402.8	403.3
170°	406.1	405.9	405.6	405.4	405.1	404.9	404.9	404.9	404.9	404.9	405.5
172.5°	407.6	407.3	407.0	406.7	406.3	406.2	406.2	406.3	406.4	406.4	407.0
175°	409.5	409.1	408.8	408.5	408.2	408.0	408.1	408.2	408.2	408.3	408.8
177.5°	410.0	409.7	409.5	409.2	408.9	408.8	408.9	408.9	409.0	409.1	409.5
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5



TEST NUMBER: P332273-935

CATALOG NUMBER: S123RDIP-S560D365U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	813.2	813.2	813.2	813.2	813.2	813.2	813.2	813.2
2.5°	810.0	811.3	812.6	813.1	812.9	812.6	812.4	812.2
5°	804.6	806.0	807.3	807.8	807.5	807.2	806.9	806.6
7.5°	793.3	794.0	794.8	794.9	794.4	793.9	793.4	792.9
10°	783.2	783.3	783.4	783.2	782.5	781.7	781.0	780.2
12.5°	770.6	770.5	770.4	769.9	769.0	768.2	767.4	766.5
15°	748.5	747.7	747.0	746.1	745.0	744.1	743.0	742.0
17.5°	722.0	720.5	718.8	717.4	715.8	714.3	712.7	711.3
20°	703.9	702.0	700.1	698.3	696.5	694.7	692.9	691.2
22.5°	684.5	682.1	679.8	677.7	676.1	674.4	672.8	671.1
25°	652.7	649.6	646.6	644.2	642.7	641.0	639.4	637.7
27.5°	618.1	613.9	609.6	606.2	603.7	601.3	598.8	596.3
30°	593.5	588.5	583.6	579.9	577.6	575.2	572.8	570.5
32.5°	569.4	563.9	558.4	554.5	552.1	549.6	547.1	544.7
35°	533.5	527.2	520.9	516.4	513.8	511.2	508.5	505.8
37.5°	495.0	487.8	480.7	475.5	472.3	469.0	465.7	462.4
40°	468.2	460.5	453.0	447.5	444.1	440.7	437.4	433.9
42.5°	442.6	434.2	425.9	420.2	417.2	414.1	411.1	408.1
45°	404.8	396.4	388.1	382.1	378.6	375.1	371.5	368.0
47.5°	365.7	356.6	347.5	341.4	338.3	335.1	332.0	328.8
50°	339.3	330.2	321.2	314.9	311.5	308.2	304.8	301.4
52.5°	313.8	304.4	294.9	288.7	285.7	282.7	279.7	276.6
55°	275.9	267.3	258.8	253.1	250.2	247.3	244.4	241.4
57.5°	238.5	230.5	222.5	217.2	214.7	212.2	209.7	207.2
60°	215.0	207.1	199.1	194.0	191.5	189.0	186.5	184.0
62.5°	191.7	184.3	176.8	171.8	169.2	166.5	163.9	161.4
65°	158.4	151.3	144.0	139.7	138.1	136.5	134.8	133.2
67.5°	126.7	121.3	116.0	112.4	110.7	109.0	107.3	105.6
70°	107.1	102.0	96.9	93.5	91.9	90.3	88.7	87.0
72.5°	89.5	85.3	81.1	78.7	78.0	77.3	76.6	75.9
75°	67.0	65.5	64.1	63.2	62.9	62.6	62.3	62.0
77.5°	50.5	49.8	48.9	48.4	48.1	47.8	47.5	47.2
80°	40.6	40.2	39.8	39.4	39.2	38.8	38.6	38.2
82.5°	31.2	30.7	30.3	30.0	30.0	30.0	29.9	29.8
85°	17.9	17.6	17.3	17.1	17.1	17.1	17.1	17.1
87.5°	8.2	8.1	8.1	8.0	7.9	7.8	7.7	7.7
90°	7.8	8.1	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	8.7	9.1	9.6	9.8	9.8	9.9	10.0	10.1
95°	10.4	10.8	11.4	11.5	11.5	11.5	11.5	11.5
97.5°	10.8	11.5	12.0	12.2	12.3	12.4	12.5	12.6
100°	11.1	11.6	12.2	12.5	12.6	12.7	12.7	12.7
102.5°	16.7	15.0	13.3	12.6	12.7	12.7	12.9	13.0
105°	42.7	30.7	18.8	12.8	13.0	13.1	13.3	13.3
107.5°	104.6	95.8	87.0	78.1	69.1	60.1	51.1	42.0
110°	132.8	130.5	128.3	122.3	112.7	103.0	93.3	83.7





TEST NUMBER: P332273-935

CATALOG NUMBER: S123RDIP-S560D365U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	152.7	152.7	152.7	151.7	149.6	147.7	145.6	143.5
115°	176.0	176.7	177.4	177.8	178.1	178.4	178.7	178.9
117.5°	197.2	197.7	198.2	198.5	198.5	198.6	198.7	198.7
120°	211.0	211.5	212.1	212.4	212.4	212.4	212.4	212.4
122.5°	224.5	225.0	225.3	225.5	225.6	225.7	225.7	225.8
125°	243.7	243.8	243.9	244.1	244.2	244.4	244.5	244.6
127.5°	262.8	263.0	263.3	263.3	263.1	263.0	262.9	262.8
130°	274.4	274.7	274.9	275.0	274.8	274.7	274.6	274.4
132.5°	285.3	285.6	285.9	285.9	285.7	285.5	285.3	285.2
135°	302.0	302.1	302.3	302.3	302.1	302.0	301.7	301.5
137.5°	316.7	317.0	317.4	317.5	317.3	317.2	317.0	316.9
140°	326.1	326.3	326.7	326.7	326.6	326.4	326.3	326.1
142.5°	335.0	335.2	335.4	335.4	335.3	335.0	334.8	334.7
145°	347.4	347.6	347.7	347.8	347.8	347.8	347.8	347.8
147.5°	358.5	358.7	358.9	358.8	358.4	358.1	357.8	357.5
150°	365.4	365.5	365.7	365.6	365.4	365.2	365.0	364.8
152.5°	371.4	371.7	372.0	371.9	371.6	371.3	370.9	370.7
155°	379.8	380.1	380.5	380.4	380.0	379.6	379.2	378.8
157.5°	387.0	387.4	387.9	387.8	387.3	386.8	386.2	385.6
160°	391.2	391.6	392.0	391.9	391.5	391.0	390.5	390.0
162.5°	394.9	395.4	395.8	395.9	395.5	395.0	394.6	394.2
165°	399.9	400.5	401.1	401.1	400.6	400.1	399.7	399.2
167.5°	403.8	404.4	404.9	404.9	404.4	403.8	403.3	402.8
170°	406.0	406.6	407.1	407.1	406.6	406.0	405.5	404.9
172.5°	407.5	408.0	408.5	408.5	407.9	407.3	406.7	406.1
175°	409.2	409.7	410.2	410.2	409.7	409.1	408.5	408.0
177.5°	409.9	410.4	410.8	410.7	410.2	409.7	409.1	408.5
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5

(END OF REPORT)