

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332033

Luminaire Tested: **S123DIP-S1000D1025U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332033
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1025U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8219.6 lumens
Efficiency: N/A
Efficacy: 135.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332033

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332033

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	71	68	61	59	58	50	48	47	42
2	89	82	75	70	82	75	70	66	64	60	57	53	51	48	44	42	40	35
3	81	72	64	58	75	66	60	55	56	52	48	47	44	41	39	36	34	30
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	35	32	29	26
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	17
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17038	17038	17038
5°	17117	16883	17001
10°	17004	16736	16840
15°	16805	16547	16577
20°	16573	16276	16292
25°	16262	15954	15922
30°	15918	15597	15478
35°	15559	15219	15023
40°	15185	14802	14573
45°	14772	14420	14067
50°	14359	13949	13561
55°	13818	13461	13052
60°	13272	12893	12482
65°	12791	12271	11889
70°	12079	11566	11050
75°	11038	10643	10189
80°	9955	9534	9447
85°	8744	8410	8065



TEST NUMBER: P332033

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.1	1.8
10°-20°	421.0	5.1
20°-30°	621.9	7.6
30°-40°	726.5	8.8
40°-50°	730.4	8.9
50°-60°	641.5	7.8
60°-70°	478.0	5.8
70°-80°	272.3	3.3
80°-90°	81.9	1.0
90°-100°	48.8	0.6
100°-110°	232.8	2.8
110°-120°	559.2	6.8
120°-130°	712.1	8.7
130°-140°	760.8	9.3
140°-150°	711.5	8.7
150°-160°	573.9	7.0
160°-170°	370.4	4.5
170°-180°	127.6	1.6
0°-30°	1192.0	14.5
0°-40°	1918.5	23.3
0°-60°	3290.4	40.0
0°-90°	4122.6	50.2
90°-120°	840.8	10.2
90°-150°	3025.2	36.8
90°-180°	4097.0	49.8
0°-180°	8219.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1583	1583	1583	1583	1583	
5°	1584	1577	1562	1575	1573	150
15°	1508	1502	1485	1495	1488	425
25°	1369	1360	1343	1344	1341	630
35°	1184	1175	1158	1150	1143	740
45°	970	964	947	932	924	749
55°	736	734	717	703	696	659
65°	502	495	482	471	467	495
75°	265	260	256	249	245	284
85°	71	68	68	65	65	78
90°	1	11	24	28	30	7
95°	61	23	31	38	38	75
105°	297	303	219	52	44	315
115°	558	564	573	583	587	551
125°	786	794	798	800	802	702
135°	979	985	989	992	989	754
145°	1130	1137	1139	1141	1141	707
155°	1245	1243	1244	1248	1243	573
165°	1313	1310	1309	1316	1310	371
175°	1344	1339	1340	1346	1338	128
180°	1344	1344	1344	1344	1344	



TEST NUMBER: P332033

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1588.3	1587.4	1586.4	1585.4	1584.5	1582.6	1580.0	1577.3	1574.7	1572.0	1574.4
5°	1584.2	1582.7	1581.2	1579.7	1578.2	1575.8	1572.5	1569.1	1565.8	1562.5	1565.5
7.5°	1568.7	1567.2	1565.7	1564.2	1562.7	1560.2	1556.8	1553.3	1549.9	1546.4	1549.1
10°	1555.7	1554.2	1552.6	1551.1	1549.6	1546.9	1543.0	1539.0	1535.1	1531.2	1533.9
12.5°	1538.2	1537.0	1535.7	1534.4	1533.2	1530.7	1527.0	1523.3	1519.6	1515.9	1517.9
15°	1508.0	1506.8	1505.6	1504.4	1503.2	1500.6	1496.7	1492.8	1488.8	1484.9	1487.3
17.5°	1472.9	1471.3	1469.8	1468.2	1466.6	1463.9	1459.9	1456.0	1452.1	1448.1	1449.8
20°	1446.8	1445.0	1443.2	1441.3	1439.5	1436.6	1432.7	1428.8	1424.9	1420.9	1422.1
22.5°	1417.4	1415.6	1413.8	1411.9	1410.1	1407.3	1403.3	1399.4	1395.5	1391.5	1392.5
25°	1369.2	1367.4	1365.6	1363.8	1361.9	1359.1	1355.1	1351.2	1347.3	1343.3	1343.6
27.5°	1317.8	1316.0	1314.2	1312.5	1310.7	1307.7	1303.5	1299.3	1295.0	1290.8	1291.0
30°	1280.7	1279.2	1277.7	1276.2	1274.7	1271.8	1267.6	1263.3	1259.1	1254.9	1254.9
32.5°	1243.7	1241.7	1239.7	1237.7	1235.7	1233.1	1229.8	1226.6	1223.3	1220.0	1218.3
35°	1184.1	1182.3	1180.5	1178.7	1176.8	1174.0	1170.0	1166.1	1162.2	1158.2	1156.4
37.5°	1123.1	1120.8	1118.5	1116.2	1113.9	1110.8	1106.8	1102.8	1098.8	1094.8	1092.6
40°	1080.7	1078.8	1077.0	1075.2	1073.4	1070.4	1066.1	1061.9	1057.7	1053.4	1051.0
42.5°	1038.2	1036.1	1034.1	1032.0	1030.0	1026.8	1022.6	1018.4	1014.1	1009.9	1007.5
45°	970.4	969.2	968.0	966.8	965.6	963.0	959.1	955.1	951.2	947.3	943.7
47.5°	903.2	901.4	899.7	897.9	896.2	893.4	889.8	886.1	882.4	878.7	875.1
50°	857.5	855.9	854.4	852.9	851.4	848.7	844.7	840.8	836.9	833.0	829.6
52.5°	809.5	808.5	807.5	806.5	805.4	802.8	798.7	794.5	790.3	786.1	783.3
55°	736.3	736.0	735.7	735.4	735.1	733.0	729.1	725.1	721.2	717.3	713.9
57.5°	666.6	665.6	664.6	663.6	662.5	660.4	657.3	654.1	651.0	647.9	644.9
60°	616.5	616.2	615.9	615.6	615.3	613.4	609.7	606.1	602.5	598.9	596.1
62.5°	571.9	571.1	570.3	569.5	568.8	566.6	562.9	559.3	555.7	552.0	549.3
65°	502.2	500.7	499.2	497.7	496.2	493.9	490.9	487.9	484.8	481.8	479.4
67.5°	428.5	427.1	425.8	424.5	423.1	421.3	419.0	416.7	414.4	412.1	410.0
70°	383.8	382.0	380.2	378.4	376.6	374.7	372.9	371.1	369.3	367.5	365.4
72.5°	337.0	335.7	334.3	333.0	331.7	330.0	327.9	325.9	323.8	321.7	319.9
75°	265.4	264.2	263.0	261.8	260.6	259.5	258.6	257.7	256.8	255.9	254.4
77.5°	202.0	201.3	200.6	200.0	199.3	198.4	197.4	196.3	195.2	194.1	193.1
80°	160.6	159.7	158.8	157.9	157.0	156.2	155.6	155.0	154.4	153.8	153.5
82.5°	120.3	120.1	120.0	119.8	119.6	119.4	119.3	119.2	119.1	119.0	118.4
85°	70.8	70.2	69.6	69.0	68.4	68.1	68.1	68.1	68.1	68.1	67.4
87.5°	28.5	28.2	27.9	27.7	27.4	27.4	27.7	28.1	28.4	28.7	28.7
90°	1.0	3.2	5.4	7.7	9.9	12.4	15.3	18.2	21.1	24.0	24.8
92.5°	18.6	17.9	17.3	16.7	16.1	16.9	19.0	21.2	23.4	25.6	27.0
95°	60.9	51.8	42.7	33.6	24.5	21.2	23.6	26.1	28.5	30.9	32.5
97.5°	122.4	118.3	114.2	110.1	106.0	96.0	80.1	64.1	48.1	32.1	33.9
100°	168.7	173.1	177.6	182.0	186.4	171.3	136.7	102.1	67.5	32.9	34.7
102.5°	221.4	224.6	227.8	231.0	234.2	216.9	179.1	141.3	103.5	65.7	60.2
105°	297.4	299.9	302.3	304.8	307.2	298.4	278.5	258.5	238.6	218.6	179.3
107.5°	377.7	379.7	381.6	383.6	385.5	388.1	391.2	394.4	397.5	400.7	371.9
110°	431.2	433.0	434.7	436.5	438.3	440.4	442.8	445.3	447.7	450.2	442.8



TEST NUMBER: P332033

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	482.3	483.9	485.5	487.1	488.7	490.7	493.2	495.6	498.0	500.5	500.6
115°	558.0	559.3	560.6	562.0	563.3	565.0	566.9	568.9	570.9	572.9	575.2
117.5°	631.2	632.9	634.5	636.2	637.8	639.1	640.1	641.2	642.2	643.2	645.0
120°	676.7	678.7	680.7	682.7	684.7	686.1	686.7	687.4	688.1	688.7	690.5
122.5°	723.1	724.7	726.3	728.0	729.6	730.9	731.7	732.6	733.4	734.2	735.5
125°	786.5	788.3	790.1	791.9	793.6	795.0	795.9	796.7	797.6	798.5	799.0
127.5°	848.0	849.8	851.6	853.3	855.1	856.5	857.6	858.7	859.7	860.8	861.5
130°	886.4	888.1	889.9	891.7	893.5	894.8	895.7	896.6	897.4	898.3	899.2
132.5°	923.1	924.9	926.6	928.4	930.2	931.4	932.1	932.8	933.6	934.3	935.2
135°	979.2	980.5	981.8	983.2	984.5	985.6	986.5	987.4	988.3	989.2	989.8
137.5°	1027.1	1028.8	1030.5	1032.2	1033.8	1034.9	1035.4	1035.9	1036.4	1036.9	1037.9
140°	1059.0	1060.4	1061.7	1063.0	1064.4	1065.4	1066.0	1066.7	1067.4	1068.0	1068.9
142.5°	1088.6	1089.9	1091.2	1092.6	1093.9	1094.9	1095.6	1096.2	1096.9	1097.6	1098.3
145°	1129.9	1131.5	1133.0	1134.6	1136.1	1137.1	1137.6	1138.0	1138.4	1138.9	1139.3
147.5°	1168.8	1169.9	1170.9	1171.9	1172.9	1173.6	1174.1	1174.5	1175.0	1175.4	1175.9
150°	1192.8	1193.5	1194.1	1194.8	1195.4	1196.0	1196.4	1196.9	1197.3	1197.8	1198.2
152.5°	1214.3	1214.7	1215.0	1215.3	1215.6	1215.9	1216.1	1216.4	1216.7	1216.9	1217.7
155°	1244.7	1244.2	1243.8	1243.4	1242.9	1242.8	1243.0	1243.2	1243.5	1243.7	1244.8
157.5°	1268.2	1268.2	1268.2	1268.1	1268.1	1267.9	1267.7	1267.5	1267.3	1267.0	1268.4
160°	1282.6	1282.4	1282.2	1282.0	1281.7	1281.5	1281.3	1281.1	1280.8	1280.6	1282.0
162.5°	1296.2	1295.6	1295.0	1294.5	1293.9	1293.5	1293.3	1293.0	1292.8	1292.6	1294.1
165°	1312.6	1311.9	1311.2	1310.6	1309.9	1309.5	1309.2	1309.0	1308.8	1308.6	1310.3
167.5°	1325.3	1324.5	1323.6	1322.7	1321.8	1321.3	1321.3	1321.3	1321.3	1321.3	1323.1
170°	1332.5	1331.6	1330.8	1329.9	1329.0	1328.5	1328.5	1328.5	1328.5	1328.5	1330.3
172.5°	1337.3	1336.3	1335.2	1334.1	1333.1	1332.6	1332.8	1333.0	1333.1	1333.3	1335.1
175°	1343.5	1342.4	1341.3	1340.2	1339.1	1338.6	1338.8	1339.1	1339.3	1339.5	1341.1
177.5°	1345.1	1344.2	1343.3	1342.4	1341.6	1341.2	1341.4	1341.6	1341.7	1341.9	1343.3
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P332033

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1576.8	1579.3	1581.7	1582.8	1582.5	1582.3	1582.0	1581.8
5°	1568.5	1571.5	1574.6	1575.8	1575.2	1574.6	1574.0	1573.4
7.5°	1551.9	1554.6	1557.3	1558.5	1558.1	1557.8	1557.4	1557.0
10°	1536.6	1539.3	1542.1	1543.1	1542.5	1541.9	1541.3	1540.7
12.5°	1519.9	1521.9	1523.9	1524.7	1524.4	1524.0	1523.6	1523.3
15°	1489.7	1492.1	1494.6	1494.9	1493.1	1491.2	1489.4	1487.6
17.5°	1451.5	1453.2	1454.9	1455.4	1454.8	1454.1	1453.4	1452.8
20°	1423.3	1424.6	1425.8	1425.9	1425.0	1424.1	1423.2	1422.3
22.5°	1393.5	1394.4	1395.4	1395.3	1394.2	1393.0	1391.9	1390.7
25°	1343.9	1344.3	1344.6	1344.3	1343.3	1342.4	1341.5	1340.6
27.5°	1291.3	1291.5	1291.8	1291.3	1290.2	1289.0	1287.9	1286.7
30°	1254.9	1254.9	1254.9	1253.8	1251.7	1249.6	1247.5	1245.3
32.5°	1216.6	1215.0	1213.3	1211.8	1210.7	1209.5	1208.4	1207.2
35°	1154.6	1152.8	1151.0	1149.3	1147.8	1146.3	1144.8	1143.3
37.5°	1090.5	1088.3	1086.1	1084.5	1083.6	1082.6	1081.6	1080.7
40°	1048.6	1046.2	1043.8	1041.9	1040.7	1039.5	1038.3	1037.1
42.5°	1005.0	1002.6	1000.2	998.4	997.2	996.0	994.8	993.6
45°	940.0	936.4	932.8	930.2	928.7	927.2	925.7	924.1
47.5°	871.5	868.0	864.4	862.0	860.6	859.3	858.0	856.6
50°	826.3	823.0	819.6	817.1	815.3	813.4	811.6	809.8
52.5°	780.4	777.6	774.8	772.4	770.6	768.8	767.0	765.2
55°	710.6	707.3	704.0	701.5	700.0	698.5	697.0	695.5
57.5°	641.9	639.0	636.0	633.6	631.9	630.1	628.4	626.6
60°	593.4	590.7	588.0	585.9	584.3	582.8	581.3	579.8
62.5°	546.6	543.9	541.1	539.3	538.2	537.2	536.2	535.2
65°	477.0	474.5	472.1	470.5	469.6	468.7	467.7	466.8
67.5°	407.9	405.8	403.7	402.0	400.7	399.4	398.1	396.9
70°	363.2	361.1	359.0	357.2	355.7	354.2	352.7	351.1
72.5°	318.0	316.1	314.2	312.9	312.1	311.3	310.6	309.8
75°	252.9	251.3	249.8	248.6	247.7	246.8	245.9	245.0
77.5°	192.0	191.0	190.0	189.5	189.5	189.5	189.5	189.5
80°	153.2	152.9	152.6	152.4	152.4	152.4	152.4	152.4
82.5°	117.9	117.3	116.8	116.4	116.1	115.9	115.7	115.4
85°	66.8	66.2	65.6	65.3	65.3	65.3	65.3	65.3
87.5°	28.6	28.6	28.5	28.5	28.6	28.7	28.8	28.9
90°	25.7	26.6	27.5	28.2	28.6	29.1	29.5	29.9
92.5°	28.4	29.8	31.2	32.1	32.3	32.6	32.9	33.1
95°	34.0	35.6	37.2	37.9	37.9	37.9	37.9	37.9
97.5°	35.7	37.5	39.2	40.2	40.5	40.7	40.9	41.1
100°	36.5	38.3	40.0	41.0	41.3	41.5	41.7	41.9
102.5°	54.7	49.2	43.7	41.1	41.5	41.9	42.3	42.7
105°	140.1	100.8	61.6	42.1	42.6	43.0	43.5	43.9
107.5°	343.1	314.3	285.5	256.3	226.7	197.1	167.5	137.9
110°	435.5	428.2	420.9	401.4	369.6	337.9	306.2	274.5



TEST NUMBER: P332033

CATALOG NUMBER: S123DIP-S1000D1025U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	500.7	500.9	501.0	497.7	491.0	484.3	477.6	470.9
115°	577.4	579.6	581.8	583.4	584.2	585.1	586.0	586.9
117.5°	646.8	648.5	650.3	651.3	651.5	651.6	651.8	652.0
120°	692.3	694.0	695.8	696.7	696.7	696.7	696.7	696.7
122.5°	736.7	738.0	739.2	739.9	740.1	740.3	740.4	740.6
125°	799.4	799.8	800.3	800.7	801.2	801.6	802.1	802.5
127.5°	862.2	862.9	863.6	863.8	863.3	862.9	862.4	862.0
130°	900.1	901.0	901.9	902.1	901.7	901.2	900.8	900.3
132.5°	936.0	936.9	937.8	937.9	937.3	936.7	936.1	935.5
135°	990.5	991.2	991.8	991.8	991.2	990.5	989.8	989.2
137.5°	1039.0	1040.1	1041.1	1041.4	1041.0	1040.6	1040.1	1039.7
140°	1069.8	1070.7	1071.6	1071.8	1071.3	1070.9	1070.5	1070.0
142.5°	1099.0	1099.7	1100.4	1100.4	1099.8	1099.2	1098.6	1098.0
145°	1139.8	1140.2	1140.7	1140.9	1140.9	1140.9	1140.9	1140.9
147.5°	1176.3	1176.7	1177.2	1176.9	1175.9	1174.9	1173.8	1172.8
150°	1198.7	1199.1	1199.6	1199.4	1198.8	1198.1	1197.4	1196.8
152.5°	1218.5	1219.3	1220.1	1220.0	1219.0	1218.0	1217.0	1215.9
155°	1245.9	1247.0	1248.1	1248.0	1246.7	1245.4	1244.0	1242.7
157.5°	1269.7	1271.0	1272.4	1272.2	1270.4	1268.7	1267.0	1265.3
160°	1283.3	1284.6	1285.9	1285.8	1284.3	1282.7	1281.2	1279.6
162.5°	1295.6	1297.1	1298.6	1298.7	1297.3	1295.9	1294.6	1293.2
165°	1312.1	1313.9	1315.7	1315.8	1314.2	1312.7	1311.1	1309.6
167.5°	1324.9	1326.7	1328.4	1328.4	1326.7	1324.9	1323.1	1321.3
170°	1332.1	1333.9	1335.6	1335.6	1333.9	1332.1	1330.3	1328.5
172.5°	1336.9	1338.6	1340.4	1340.3	1338.4	1336.4	1334.5	1332.5
175°	1342.6	1344.2	1345.7	1345.6	1343.8	1342.1	1340.3	1338.5
177.5°	1344.7	1346.2	1347.6	1347.4	1345.6	1343.9	1342.1	1340.3
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5

(END OF REPORT)