

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332328-935

Luminaire Tested: **S123RDIP-S775D1195U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332328-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6043.3 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332328-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332328-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	105	105	105	105	96	96	96	96	79	79	79		63	63	63		48	48	48	42
1	96	92	88	85	88	84	81	78	69	67	65		56	54	53		43	42	41	36
2	88	81	75	70	80	74	69	64	61	57	54		49	47	45		38	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46		44	41	38		34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39		39	36	33		31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34		35	31	28		28	25	23	20
6	62	50	43	37	57	46	40	34	39	34	30		32	28	25		25	23	20	17
7	57	46	38	32	52	42	35	30	35	30	26		29	25	22		23	20	18	15
8	53	41	34	29	49	38	31	27	32	27	23		27	23	20		21	18	16	14
9	50	38	30	26	45	35	28	24	30	24	21		24	21	18		20	17	15	13
10	46	35	28	23	42	32	26	21	27	22	19		23	19	16		18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11965	11965	11965
5°	12011	11846	11914
10°	11943	11696	11657
15°	11814	11422	11303
20°	11639	11080	10822
25°	11457	10696	10354
30°	11216	10253	9692
35°	10970	9809	9087
40°	10742	9285	8335
45°	10443	8770	7658
50°	10114	8182	6899
55°	9779	7512	6191
60°	9472	6794	5414
65°	9070	6016	4638
70°	8567	5051	3745
75°	7835	3976	3523
80°	6986	3521	3242
85°	5903	3112	2890



TEST NUMBER: P332328-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	1.7
10°-20°	290.4	4.8
20°-30°	418.2	6.9
30°-40°	471.1	7.8
40°-50°	450.7	7.5
50°-60°	369.0	6.1
60°-70°	249.0	4.1
70°-80°	125.3	2.1
80°-90°	36.9	0.6
90°-100°	83.0	1.4
100°-110°	248.3	4.1
110°-120°	422.3	7.0
120°-130°	555.5	9.2
130°-140°	624.4	10.3
140°-150°	613.8	10.2
150°-160°	516.7	8.5
160°-170°	343.9	5.7
170°-180°	120.4	2.0
0°-30°	813.0	13.5
0°-40°	1284.1	21.2
0°-60°	2103.8	34.8
0°-90°	2514.9	41.6
90°-120°	753.6	12.5
90°-150°	2547.3	42.2
90°-180°	3528.0	58.4
0°-180°	6043.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1112	1112	1112	1112	1112	
5°	1112	1107	1096	1104	1103	105
15°	1060	1049	1025	1020	1014	299
25°	965	941	901	882	872	443
35°	835	801	746	709	692	522
45°	686	644	576	526	503	529
55°	521	475	400	350	330	467
65°	356	305	236	194	182	352
75°	188	145	96	87	85	201
85°	48	29	25	24	23	54
90°	1	11	24	28	30	6
95°	59	66	74	78	78	66
105°	225	228	236	236	238	241
115°	425	428	426	427	426	421
125°	622	625	623	619	615	555
135°	807	813	812	808	806	622
145°	979	981	984	983	979	612
155°	1122	1122	1122	1126	1119	516
165°	1222	1219	1218	1224	1218	344
175°	1270	1267	1266	1272	1266	121
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P332328-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1115.2	1114.6	1113.9	1113.3	1112.7	1111.4	1109.4	1107.5	1105.6	1103.6	1105.4
5°	1111.6	1110.6	1109.6	1108.6	1107.6	1105.9	1103.5	1101.0	1098.6	1096.3	1098.0
7.5°	1101.3	1100.3	1099.2	1098.0	1097.0	1094.8	1091.7	1088.6	1085.5	1082.4	1083.4
10°	1092.7	1091.2	1089.9	1088.5	1087.0	1084.5	1080.9	1077.4	1073.8	1070.1	1070.3
12.5°	1080.4	1078.8	1077.3	1075.7	1074.2	1071.2	1066.8	1062.4	1057.9	1053.5	1053.4
15°	1060.2	1058.0	1055.8	1053.6	1051.4	1047.5	1041.9	1036.3	1030.6	1025.0	1024.1
17.5°	1034.7	1032.3	1029.7	1027.1	1024.5	1019.7	1012.5	1005.4	998.2	991.2	989.0
20°	1016.1	1012.8	1009.6	1006.4	1003.2	997.8	990.2	982.6	975.0	967.3	964.8
22.5°	995.1	991.4	987.7	984.0	980.3	974.5	966.4	958.3	950.2	942.1	938.8
25°	964.7	959.7	954.6	949.6	944.6	937.5	928.2	919.0	909.8	900.6	896.4
27.5°	927.6	922.1	916.6	911.1	905.6	897.7	887.4	877.2	866.9	856.6	850.8
30°	902.4	896.4	890.4	884.4	878.4	869.8	858.6	847.3	836.1	824.9	818.1
32.5°	877.2	870.4	863.6	856.8	850.0	840.6	828.7	816.9	805.0	793.2	785.7
35°	834.8	827.6	820.4	813.2	806.0	796.2	783.8	771.3	758.9	746.5	737.9
37.5°	791.9	783.9	775.8	767.8	759.8	749.2	736.0	722.7	709.5	696.2	686.4
40°	764.5	755.7	746.8	738.0	729.3	717.7	703.5	689.3	675.0	660.8	650.4
42.5°	733.5	724.7	715.8	707.1	698.3	686.5	671.8	657.0	642.4	627.7	616.3
45°	686.0	677.1	668.0	659.0	650.0	637.8	622.3	606.9	591.5	576.1	564.6
47.5°	638.7	628.8	618.9	609.0	599.1	586.4	571.0	555.5	540.1	524.7	512.3
50°	604.0	594.6	585.2	575.8	566.4	553.5	537.4	521.1	504.9	488.6	476.2
52.5°	573.0	562.8	552.6	542.3	532.2	519.0	502.9	486.9	470.8	454.7	441.9
55°	521.1	511.3	501.4	491.6	481.8	468.4	451.3	434.4	417.3	400.3	388.7
57.5°	473.1	462.4	451.8	441.0	430.3	416.5	399.3	382.2	365.1	348.0	337.0
60°	440.0	429.0	417.9	406.9	395.9	382.0	365.4	348.8	332.2	315.6	304.7
62.5°	406.7	395.7	384.7	373.7	362.7	348.9	332.3	315.6	299.0	282.3	272.2
65°	356.1	345.1	334.1	323.0	312.0	298.7	283.1	267.4	251.8	236.2	226.4
67.5°	305.5	294.3	283.2	272.0	260.9	247.8	232.8	217.8	202.9	187.9	180.6
70°	272.2	261.5	250.6	239.8	229.0	216.5	202.5	188.6	174.5	160.5	153.4
72.5°	239.1	228.4	217.7	207.1	196.5	184.8	172.0	159.3	146.5	133.8	128.0
75°	188.4	178.8	169.2	159.5	150.0	139.7	128.6	117.6	106.6	95.6	93.6
77.5°	142.2	133.5	124.8	116.1	107.5	99.6	92.5	85.4	78.4	71.2	70.2
80°	112.7	104.4	96.3	88.1	79.8	73.6	69.4	65.2	61.0	56.8	56.2
82.5°	84.6	77.5	70.3	63.3	56.2	51.7	49.7	47.7	45.8	43.8	43.2
85°	47.8	43.4	39.0	34.5	30.1	27.6	27.0	26.4	25.8	25.2	24.9
87.5°	17.5	16.2	14.9	13.5	12.2	11.9	12.5	13.0	13.6	14.2	14.2
90°	1.0	3.2	5.4	7.7	9.9	12.5	15.3	18.3	21.1	24.0	24.9
92.5°	24.2	25.7	27.2	28.8	30.2	31.9	33.5	35.1	36.8	38.4	39.1
95°	59.1	60.6	62.2	63.7	65.3	66.9	68.7	70.4	72.2	74.0	74.9
97.5°	104.9	106.0	107.2	108.3	109.4	110.7	112.0	113.3	114.5	115.8	116.8
100°	136.0	137.4	138.7	140.1	141.4	142.6	143.7	144.8	145.9	147.1	147.7
102.5°	172.0	172.9	173.7	174.4	175.3	176.4	177.9	179.3	180.8	182.3	183.0
105°	225.1	225.5	226.0	226.4	226.9	228.1	230.1	232.1	234.1	236.1	236.1
107.5°	286.7	287.0	287.2	287.5	287.7	288.3	289.1	289.9	290.7	291.5	292.2
110°	325.1	325.5	326.0	326.5	326.9	327.4	327.8	328.2	328.6	329.2	330.0



TEST NUMBER: P332328-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	365.2	365.4	365.7	365.9	366.2	366.4	366.4	366.5	366.6	366.7	367.8
115°	425.2	425.9	426.5	427.1	427.8	427.9	427.5	427.1	426.6	426.2	426.4
117.5°	485.6	486.0	486.5	486.9	487.3	487.3	486.7	486.1	485.6	485.0	484.9
120°	523.2	524.5	525.9	527.2	528.6	528.7	527.5	526.4	525.3	524.2	524.0
122.5°	562.4	563.4	564.4	565.3	566.4	566.5	565.9	565.3	564.8	564.2	563.6
125°	622.2	622.9	623.5	624.2	624.9	625.0	624.6	624.1	623.7	623.3	622.3
127.5°	677.4	678.9	680.3	681.7	683.1	683.6	683.1	682.6	682.2	681.7	680.4
130°	714.3	716.0	717.8	719.6	721.3	721.9	721.3	720.6	720.0	719.3	718.4
132.5°	751.1	752.9	754.7	756.4	758.2	758.9	758.4	757.9	757.3	756.9	755.8
135°	807.3	808.7	809.9	811.3	812.6	813.2	813.0	812.8	812.5	812.3	811.4
137.5°	859.4	860.4	861.5	862.6	863.8	864.6	865.2	865.7	866.3	866.9	866.0
140°	895.4	896.5	897.6	898.7	899.7	900.4	900.7	900.9	901.1	901.4	901.1
142.5°	928.2	929.3	930.4	931.5	932.6	933.3	933.8	934.2	934.5	935.0	934.7
145°	979.4	979.8	980.2	980.7	981.1	981.7	982.4	983.0	983.7	984.4	984.1
147.5°	1024.2	1025.0	1025.8	1026.6	1027.4	1028.1	1028.7	1029.3	1029.9	1030.6	1030.6
150°	1055.4	1055.8	1056.3	1056.7	1057.2	1057.7	1058.1	1058.5	1058.9	1059.4	1059.4
152.5°	1081.0	1081.7	1082.3	1082.9	1083.5	1083.9	1084.2	1084.5	1084.8	1085.0	1085.4
155°	1121.5	1121.5	1121.5	1121.5	1121.5	1121.5	1121.8	1122.0	1122.2	1122.4	1123.3
157.5°	1155.8	1155.5	1155.3	1155.0	1154.8	1154.7	1154.9	1155.1	1155.3	1155.5	1156.4
160°	1177.4	1177.0	1176.6	1176.1	1175.7	1175.4	1175.4	1175.4	1175.4	1175.4	1176.6
162.5°	1196.6	1196.0	1195.4	1194.8	1194.2	1193.9	1194.1	1194.3	1194.5	1194.6	1195.8
165°	1221.5	1220.8	1220.1	1219.4	1218.8	1218.5	1218.5	1218.5	1218.5	1218.5	1219.8
167.5°	1241.3	1240.4	1239.5	1238.6	1237.7	1237.3	1237.5	1237.7	1237.9	1238.0	1239.4
170°	1252.5	1251.5	1250.7	1249.8	1248.9	1248.4	1248.4	1248.4	1248.4	1248.4	1250.0
172.5°	1261.3	1260.4	1259.5	1258.6	1257.7	1257.3	1257.3	1257.3	1257.3	1257.3	1258.7
175°	1270.5	1269.6	1268.7	1267.8	1267.0	1266.4	1266.4	1266.4	1266.4	1266.4	1267.8
177.5°	1274.3	1273.6	1272.9	1272.1	1271.4	1271.1	1271.1	1271.1	1271.1	1271.1	1272.1
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P332328-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1107.2	1109.0	1110.7	1111.5	1111.1	1110.8	1110.4	1110.2
5°	1099.8	1101.6	1103.5	1104.1	1103.8	1103.4	1102.9	1102.6
7.5°	1084.4	1085.4	1086.4	1086.6	1085.9	1085.2	1084.5	1083.8
10°	1070.6	1070.7	1070.9	1070.6	1069.5	1068.5	1067.6	1066.5
12.5°	1053.3	1053.2	1053.1	1052.4	1051.3	1050.1	1049.0	1047.8
15°	1023.0	1022.0	1021.1	1019.9	1018.5	1017.0	1015.6	1014.3
17.5°	986.9	984.8	982.7	980.6	978.4	976.4	974.3	972.2
20°	962.2	959.5	956.9	954.4	952.0	949.6	947.2	944.8
22.5°	935.6	932.4	929.1	926.3	924.1	921.9	919.6	917.4
25°	892.3	888.0	883.8	880.6	878.4	876.2	874.0	871.8
27.5°	844.9	839.1	833.3	828.6	825.3	821.9	818.6	815.2
30°	811.3	804.4	797.6	792.6	789.5	786.3	783.0	779.8
32.5°	778.3	770.9	763.4	757.9	754.6	751.2	747.9	744.5
35°	729.3	720.7	712.0	705.9	702.3	698.7	695.1	691.5
37.5°	676.6	666.8	657.0	650.0	645.5	641.0	636.6	632.1
40°	640.0	629.6	619.1	611.7	607.0	602.4	597.8	593.2
42.5°	604.9	593.5	582.1	574.4	570.2	566.1	562.0	557.8
45°	553.3	541.8	530.4	522.3	517.5	512.6	507.9	503.1
47.5°	499.8	487.4	475.0	466.7	462.4	458.1	453.8	449.5
50°	463.8	451.3	438.9	430.4	425.9	421.2	416.6	412.0
52.5°	429.0	416.0	403.1	394.6	390.5	386.3	382.2	378.1
55°	377.0	365.4	353.8	345.9	342.0	337.9	334.0	329.9
57.5°	326.1	315.0	304.1	296.9	293.5	290.1	286.6	283.3
60°	293.9	283.1	272.2	265.2	261.7	258.3	254.9	251.5
62.5°	262.0	251.8	241.7	234.8	231.2	227.6	224.1	220.5
65°	216.5	206.7	196.9	190.9	188.7	186.5	184.3	182.1
67.5°	173.2	165.9	158.5	153.7	151.4	149.0	146.6	144.2
70°	146.5	139.4	132.4	127.9	125.6	123.4	121.2	119.0
72.5°	122.3	116.6	110.9	107.5	106.6	105.7	104.8	103.8
75°	91.5	89.5	87.6	86.4	85.9	85.6	85.2	84.7
77.5°	69.1	67.9	66.9	66.1	65.8	65.3	64.9	64.6
80°	55.6	55.0	54.4	53.9	53.5	53.1	52.7	52.3
82.5°	42.6	42.0	41.4	41.1	41.0	40.9	40.8	40.7
85°	24.5	24.0	23.7	23.4	23.4	23.4	23.4	23.4
87.5°	14.2	14.2	14.2	14.2	14.1	14.1	14.0	13.9
90°	25.8	26.7	27.6	28.2	28.7	29.1	29.5	30.0
92.5°	39.9	40.6	41.2	41.5	41.2	41.0	40.6	40.4
95°	75.8	76.7	77.6	78.0	78.0	78.0	78.0	78.0
97.5°	117.9	118.9	119.9	120.4	120.3	120.2	120.1	120.0
100°	148.4	149.0	149.7	150.2	150.8	151.2	151.6	152.1
102.5°	183.6	184.3	184.9	185.2	185.1	185.0	184.9	184.9
105°	236.1	236.1	236.1	236.3	236.8	237.2	237.6	238.1
107.5°	292.9	293.7	294.4	294.5	294.3	294.0	293.8	293.5
110°	330.9	331.8	332.7	332.9	332.4	332.0	331.6	331.1



TEST NUMBER: P332328-935

CATALOG NUMBER: S123RDIP-S775D1195U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	368.9	370.0	371.0	371.5	371.4	371.3	371.3	371.2
115°	426.6	426.8	427.1	427.1	426.8	426.6	426.4	426.2
117.5°	484.9	484.8	484.8	484.5	483.9	483.2	482.6	482.0
120°	523.7	523.6	523.3	523.0	522.5	522.1	521.7	521.2
122.5°	563.1	562.5	561.9	561.3	560.7	560.1	559.4	558.8
125°	621.5	620.6	619.7	618.8	617.9	617.0	616.1	615.3
127.5°	679.2	678.0	676.7	675.5	674.5	673.5	672.4	671.5
130°	717.5	716.6	715.7	714.5	712.9	711.4	709.8	708.3
132.5°	754.8	753.7	752.6	751.5	750.3	749.1	747.9	746.7
135°	810.5	809.6	808.7	808.0	807.6	807.2	806.8	806.3
137.5°	865.0	864.1	863.2	862.3	861.4	860.7	859.8	858.9
140°	900.9	900.7	900.4	899.6	898.0	896.5	894.9	893.4
142.5°	934.5	934.3	934.1	933.3	932.1	930.9	929.8	928.6
145°	984.0	983.7	983.5	982.9	982.1	981.1	980.2	979.4
147.5°	1030.6	1030.6	1030.6	1029.9	1028.6	1027.3	1025.9	1024.6
150°	1059.4	1059.4	1059.4	1058.8	1057.4	1056.1	1054.7	1053.4
152.5°	1085.7	1086.1	1086.4	1086.1	1084.9	1083.7	1082.5	1081.4
155°	1124.2	1125.1	1126.0	1125.7	1124.1	1122.6	1121.0	1119.4
157.5°	1157.3	1158.2	1159.2	1159.0	1157.8	1156.5	1155.3	1154.0
160°	1177.7	1178.8	1179.9	1180.0	1179.1	1178.2	1177.3	1176.5
162.5°	1196.9	1198.0	1199.1	1198.9	1197.5	1196.1	1194.6	1193.3
165°	1221.2	1222.4	1223.8	1223.7	1222.1	1220.6	1219.0	1217.5
167.5°	1240.8	1242.2	1243.5	1243.5	1242.2	1240.8	1239.4	1238.0
170°	1251.5	1253.2	1254.7	1254.7	1253.2	1251.5	1250.0	1248.4
172.5°	1260.1	1261.5	1262.8	1262.7	1261.1	1259.6	1258.0	1256.5
175°	1269.1	1270.5	1271.8	1271.7	1270.1	1268.6	1267.0	1265.5
177.5°	1273.2	1274.3	1275.3	1275.2	1274.0	1272.7	1271.5	1270.3
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5

(END OF REPORT)