

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332006

Luminaire Tested: **S123DIP-S1000D365U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332006
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D365U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5570.6 lumens
Efficiency: N/A
Efficacy: 128.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332006

CATALOG NUMBER: S123DIP-S1000D365U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332006

CATALOG NUMBER: S123DIP-S1000D365U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74
1	103	99	94	91	98	94	90	87	85	82	79	77	74	72	69	67	66	62
2	94	86	80	74	89	82	76	71	74	70	66	67	64	60	61	58	55	52
3	86	76	68	62	81	72	65	60	66	60	55	59	55	51	54	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	41	38
5	72	60	51	45	68	57	49	44	52	46	41	48	42	38	43	39	35	33
6	67	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	40	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	23	21
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17038	17038	17038
5°	17117	16883	17001
10°	17004	16736	16840
15°	16805	16547	16577
20°	16573	16276	16292
25°	16262	15954	15922
30°	15918	15597	15478
35°	15559	15219	15023
40°	15185	14802	14573
45°	14772	14420	14067
50°	14359	13949	13561
55°	13818	13461	13052
60°	13272	12893	12482
65°	12791	12271	11889
70°	12079	11566	11050
75°	11038	10643	10189
80°	9955	9534	9447
85°	8744	8410	8065



TEST NUMBER: P332006

CATALOG NUMBER: S123DIP-S1000D365U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.1	2.7
10°-20°	421.0	7.6
20°-30°	621.9	11.2
30°-40°	726.5	13.0
40°-50°	730.4	13.1
50°-60°	641.5	11.5
60°-70°	478.0	8.6
70°-80°	272.3	4.9
80°-90°	79.5	1.4
90°-100°	17.3	0.3
100°-110°	82.4	1.5
110°-120°	198.0	3.6
120°-130°	252.1	4.5
130°-140°	269.3	4.8
140°-150°	251.9	4.5
150°-160°	203.2	3.6
160°-170°	131.1	2.4
170°-180°	45.2	0.8
0°-30°	1192.0	21.4
0°-40°	1918.5	34.4
0°-60°	3290.4	59.1
0°-90°	4120.1	74.0
90°-120°	297.7	5.3
90°-150°	1071.0	19.2
90°-180°	1450.0	26.0
0°-180°	5570.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1583	1583	1583	1583	1583	
5°	1584	1577	1562	1575	1573	150
15°	1508	1502	1485	1495	1488	425
25°	1369	1360	1343	1344	1341	630
35°	1184	1175	1158	1150	1143	740
45°	970	964	947	932	924	749
55°	736	734	717	703	696	659
65°	502	495	482	471	467	495
75°	265	260	256	249	245	284
85°	71	68	68	65	65	78
90°	0	4	8	10	11	5
95°	22	8	11	13	13	27
105°	105	107	77	18	16	112
115°	198	200	203	206	208	195
125°	278	281	283	283	284	249
135°	347	349	350	351	350	267
145°	400	402	403	404	404	250
155°	441	440	440	442	440	203
165°	465	464	463	466	464	131
175°	476	474	474	476	474	45
180°	476	476	476	476	476	



TEST NUMBER: P332006

CATALOG NUMBER: S123DIP-S1000D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1588.3	1587.4	1586.4	1585.4	1584.5	1582.6	1580.0	1577.3	1574.7	1572.0	1574.4
5°	1584.2	1582.7	1581.2	1579.7	1578.2	1575.8	1572.5	1569.1	1565.8	1562.5	1565.5
7.5°	1568.7	1567.2	1565.7	1564.2	1562.7	1560.2	1556.8	1553.3	1549.9	1546.4	1549.1
10°	1555.7	1554.2	1552.6	1551.1	1549.6	1546.9	1543.0	1539.0	1535.1	1531.2	1533.9
12.5°	1538.2	1537.0	1535.7	1534.4	1533.2	1530.7	1527.0	1523.3	1519.6	1515.9	1517.9
15°	1508.0	1506.8	1505.6	1504.4	1503.2	1500.6	1496.7	1492.8	1488.8	1484.9	1487.3
17.5°	1472.9	1471.3	1469.8	1468.2	1466.6	1463.9	1459.9	1456.0	1452.1	1448.1	1449.8
20°	1446.8	1445.0	1443.2	1441.3	1439.5	1436.6	1432.7	1428.8	1424.9	1420.9	1422.1
22.5°	1417.4	1415.6	1413.8	1411.9	1410.1	1407.3	1403.3	1399.4	1395.5	1391.5	1392.5
25°	1369.2	1367.4	1365.6	1363.8	1361.9	1359.1	1355.1	1351.2	1347.3	1343.3	1343.6
27.5°	1317.8	1316.0	1314.2	1312.5	1310.7	1307.7	1303.5	1299.3	1295.0	1290.8	1291.0
30°	1280.7	1279.2	1277.7	1276.2	1274.7	1271.8	1267.6	1263.3	1259.1	1254.9	1254.9
32.5°	1243.7	1241.7	1239.7	1237.7	1235.7	1233.1	1229.8	1226.6	1223.3	1220.0	1218.3
35°	1184.1	1182.3	1180.5	1178.7	1176.8	1174.0	1170.0	1166.1	1162.2	1158.2	1156.4
37.5°	1123.1	1120.8	1118.5	1116.2	1113.9	1110.8	1106.8	1102.8	1098.8	1094.8	1092.6
40°	1080.7	1078.8	1077.0	1075.2	1073.4	1070.4	1066.1	1061.9	1057.7	1053.4	1051.0
42.5°	1038.2	1036.1	1034.1	1032.0	1030.0	1026.8	1022.6	1018.4	1014.1	1009.9	1007.5
45°	970.4	969.2	968.0	966.8	965.6	963.0	959.1	955.1	951.2	947.3	943.7
47.5°	903.2	901.4	899.7	897.9	896.2	893.4	889.8	886.1	882.4	878.7	875.1
50°	857.5	855.9	854.4	852.9	851.4	848.7	844.7	840.8	836.9	833.0	829.6
52.5°	809.5	808.5	807.5	806.5	805.4	802.8	798.7	794.5	790.3	786.1	783.3
55°	736.3	736.0	735.7	735.4	735.1	733.0	729.1	725.1	721.2	717.3	713.9
57.5°	666.6	665.6	664.6	663.6	662.5	660.4	657.3	654.1	651.0	647.9	644.9
60°	616.5	616.2	615.9	615.6	615.3	613.4	609.7	606.1	602.5	598.9	596.1
62.5°	571.9	571.1	570.3	569.5	568.8	566.6	562.9	559.3	555.7	552.0	549.3
65°	502.2	500.7	499.2	497.7	496.2	493.9	490.9	487.9	484.8	481.8	479.4
67.5°	428.5	427.1	425.8	424.5	423.1	421.3	419.0	416.7	414.4	412.1	410.0
70°	383.8	382.0	380.2	378.4	376.6	374.7	372.9	371.1	369.3	367.5	365.4
72.5°	337.0	335.7	334.3	333.0	331.7	330.0	327.9	325.9	323.8	321.7	319.9
75°	265.4	264.2	263.0	261.8	260.6	259.5	258.6	257.7	256.8	255.9	254.4
77.5°	202.0	201.3	200.6	200.0	199.3	198.4	197.4	196.3	195.2	194.1	193.1
80°	160.6	159.7	158.8	157.9	157.0	156.2	155.6	155.0	154.4	153.8	153.5
82.5°	120.3	120.1	120.0	119.8	119.6	119.4	119.3	119.2	119.1	119.0	118.4
85°	70.8	70.2	69.6	69.0	68.4	68.1	68.1	68.1	68.1	68.1	67.4
87.5°	28.4	27.8	27.2	26.7	26.1	25.8	25.8	25.7	25.7	25.7	25.5
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.4	6.4	7.5	8.5	8.8
92.5°	6.6	6.4	6.1	5.9	5.7	6.0	6.7	7.5	8.3	9.0	9.5
95°	21.6	18.3	15.1	11.9	8.7	7.5	8.4	9.2	10.1	11.0	11.5
97.5°	43.3	41.9	40.4	39.0	37.5	34.0	28.3	22.7	17.0	11.4	12.0
100°	59.7	61.3	62.9	64.4	66.0	60.7	48.4	36.2	23.9	11.7	12.3
102.5°	78.4	79.5	80.6	81.8	82.9	76.8	63.4	50.0	36.6	23.3	21.3
105°	105.3	106.2	107.0	107.9	108.8	105.7	98.6	91.5	84.5	77.4	63.5
107.5°	133.7	134.4	135.1	135.8	136.5	137.4	138.5	139.6	140.7	141.8	131.6
110°	152.7	153.3	153.9	154.5	155.2	155.9	156.8	157.6	158.5	159.4	156.8



TEST NUMBER: P332006

CATALOG NUMBER: S123DIP-S1000D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.7	171.3	171.9	172.4	173.0	173.7	174.6	175.5	176.3	177.2	177.2
115°	197.5	198.0	198.5	198.9	199.4	200.0	200.7	201.4	202.1	202.8	203.6
117.5°	223.5	224.1	224.6	225.2	225.8	226.3	226.6	227.0	227.4	227.7	228.3
120°	239.6	240.3	241.0	241.7	242.4	242.9	243.1	243.4	243.6	243.8	244.5
122.5°	256.0	256.6	257.1	257.7	258.3	258.7	259.0	259.3	259.6	259.9	260.4
125°	278.5	279.1	279.7	280.3	281.0	281.4	281.8	282.1	282.4	282.7	282.9
127.5°	300.2	300.9	301.5	302.1	302.7	303.2	303.6	304.0	304.4	304.7	305.0
130°	313.8	314.4	315.0	315.7	316.3	316.8	317.1	317.4	317.7	318.0	318.3
132.5°	326.8	327.4	328.1	328.7	329.3	329.7	330.0	330.3	330.5	330.8	331.1
135°	346.7	347.1	347.6	348.1	348.5	348.9	349.2	349.6	349.9	350.2	350.4
137.5°	363.6	364.2	364.8	365.4	366.0	366.4	366.6	366.7	366.9	367.1	367.5
140°	374.9	375.4	375.9	376.3	376.8	377.2	377.4	377.6	377.9	378.1	378.4
142.5°	385.4	385.9	386.3	386.8	387.3	387.6	387.9	388.1	388.3	388.6	388.8
145°	400.0	400.6	401.1	401.7	402.2	402.6	402.7	402.9	403.0	403.2	403.4
147.5°	413.8	414.2	414.5	414.9	415.2	415.5	415.7	415.8	416.0	416.1	416.3
150°	422.3	422.5	422.7	423.0	423.2	423.4	423.6	423.7	423.9	424.0	424.2
152.5°	429.9	430.0	430.1	430.2	430.3	430.5	430.5	430.6	430.7	430.8	431.1
155°	440.7	440.5	440.3	440.2	440.0	440.0	440.1	440.1	440.2	440.3	440.7
157.5°	449.0	449.0	449.0	448.9	448.9	448.9	448.8	448.7	448.6	448.6	449.0
160°	454.1	454.0	453.9	453.8	453.8	453.7	453.6	453.5	453.5	453.4	453.8
162.5°	458.9	458.7	458.5	458.3	458.1	457.9	457.8	457.8	457.7	457.6	458.1
165°	464.7	464.4	464.2	464.0	463.7	463.6	463.5	463.4	463.3	463.3	463.9
167.5°	469.2	468.9	468.6	468.3	467.9	467.8	467.8	467.8	467.8	467.8	468.4
170°	471.7	471.4	471.1	470.8	470.5	470.3	470.3	470.3	470.3	470.3	471.0
172.5°	473.4	473.1	472.7	472.3	471.9	471.8	471.8	471.9	472.0	472.0	472.7
175°	475.6	475.2	474.8	474.5	474.1	473.9	474.0	474.1	474.1	474.2	474.8
177.5°	476.2	475.9	475.6	475.3	474.9	474.8	474.9	474.9	475.0	475.1	475.6
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P332006

CATALOG NUMBER: S123DIP-S1000D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1576.8	1579.3	1581.7	1582.8	1582.5	1582.3	1582.0	1581.8
5°	1568.5	1571.5	1574.6	1575.8	1575.2	1574.6	1574.0	1573.4
7.5°	1551.9	1554.6	1557.3	1558.5	1558.1	1557.8	1557.4	1557.0
10°	1536.6	1539.3	1542.1	1543.1	1542.5	1541.9	1541.3	1540.7
12.5°	1519.9	1521.9	1523.9	1524.7	1524.4	1524.0	1523.6	1523.3
15°	1489.7	1492.1	1494.6	1494.9	1493.1	1491.2	1489.4	1487.6
17.5°	1451.5	1453.2	1454.9	1455.4	1454.8	1454.1	1453.4	1452.8
20°	1423.3	1424.6	1425.8	1425.9	1425.0	1424.1	1423.2	1422.3
22.5°	1393.5	1394.4	1395.4	1395.3	1394.2	1393.0	1391.9	1390.7
25°	1343.9	1344.3	1344.6	1344.3	1343.3	1342.4	1341.5	1340.6
27.5°	1291.3	1291.5	1291.8	1291.3	1290.2	1289.0	1287.9	1286.7
30°	1254.9	1254.9	1254.9	1253.8	1251.7	1249.6	1247.5	1245.3
32.5°	1216.6	1215.0	1213.3	1211.8	1210.7	1209.5	1208.4	1207.2
35°	1154.6	1152.8	1151.0	1149.3	1147.8	1146.3	1144.8	1143.3
37.5°	1090.5	1088.3	1086.1	1084.5	1083.6	1082.6	1081.6	1080.7
40°	1048.6	1046.2	1043.8	1041.9	1040.7	1039.5	1038.3	1037.1
42.5°	1005.0	1002.6	1000.2	998.4	997.2	996.0	994.8	993.6
45°	940.0	936.4	932.8	930.2	928.7	927.2	925.7	924.1
47.5°	871.5	868.0	864.4	862.0	860.6	859.3	858.0	856.6
50°	826.3	823.0	819.6	817.1	815.3	813.4	811.6	809.8
52.5°	780.4	777.6	774.8	772.4	770.6	768.8	767.0	765.2
55°	710.6	707.3	704.0	701.5	700.0	698.5	697.0	695.5
57.5°	641.9	639.0	636.0	633.6	631.9	630.1	628.4	626.6
60°	593.4	590.7	588.0	585.9	584.3	582.8	581.3	579.8
62.5°	546.6	543.9	541.1	539.3	538.2	537.2	536.2	535.2
65°	477.0	474.5	472.1	470.5	469.6	468.7	467.7	466.8
67.5°	407.9	405.8	403.7	402.0	400.7	399.4	398.1	396.9
70°	363.2	361.1	359.0	357.2	355.7	354.2	352.7	351.1
72.5°	318.0	316.1	314.2	312.9	312.1	311.3	310.6	309.8
75°	252.9	251.3	249.8	248.6	247.7	246.8	245.9	245.0
77.5°	192.0	191.0	190.0	189.5	189.5	189.5	189.5	189.5
80°	153.2	152.9	152.6	152.4	152.4	152.4	152.4	152.4
82.5°	117.9	117.3	116.8	116.4	116.1	115.9	115.7	115.4
85°	66.8	66.2	65.6	65.3	65.3	65.3	65.3	65.3
87.5°	25.3	25.1	24.9	24.9	24.9	24.9	25.0	25.0
90°	9.1	9.4	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	10.1	10.6	11.1	11.4	11.4	11.5	11.6	11.7
95°	12.1	12.6	13.2	13.4	13.4	13.4	13.4	13.4
97.5°	12.6	13.3	13.9	14.2	14.3	14.4	14.5	14.6
100°	12.9	13.5	14.2	14.5	14.6	14.7	14.8	14.8
102.5°	19.4	17.4	15.5	14.6	14.7	14.8	15.0	15.1
105°	49.6	35.7	21.8	14.9	15.1	15.2	15.4	15.5
107.5°	121.5	111.3	101.1	90.7	80.3	69.8	59.3	48.8
110°	154.2	151.6	149.0	142.1	130.9	119.6	108.4	97.2



TEST NUMBER: P332006

CATALOG NUMBER: S123DIP-S1000D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	177.3	177.3	177.4	176.2	173.8	171.5	169.1	166.7
115°	204.4	205.2	206.0	206.5	206.8	207.2	207.5	207.8
117.5°	229.0	229.6	230.2	230.6	230.6	230.7	230.8	230.8
120°	245.1	245.7	246.3	246.7	246.7	246.7	246.7	246.7
122.5°	260.8	261.3	261.7	261.9	262.0	262.1	262.1	262.2
125°	283.0	283.2	283.3	283.5	283.6	283.8	284.0	284.1
127.5°	305.2	305.5	305.8	305.8	305.6	305.5	305.3	305.2
130°	318.7	319.0	319.3	319.4	319.2	319.1	318.9	318.7
132.5°	331.4	331.7	332.0	332.1	331.8	331.6	331.4	331.2
135°	350.7	350.9	351.1	351.1	350.9	350.7	350.4	350.2
137.5°	367.8	368.2	368.6	368.7	368.5	368.4	368.2	368.1
140°	378.7	379.0	379.4	379.4	379.3	379.1	379.0	378.8
142.5°	389.1	389.3	389.6	389.6	389.4	389.1	388.9	388.7
145°	403.5	403.7	403.8	403.9	403.9	403.9	403.9	403.9
147.5°	416.4	416.6	416.8	416.7	416.3	415.9	415.6	415.2
150°	424.4	424.5	424.7	424.6	424.4	424.2	423.9	423.7
152.5°	431.4	431.7	432.0	431.9	431.6	431.2	430.8	430.5
155°	441.1	441.5	441.9	441.8	441.4	440.9	440.4	439.9
157.5°	449.5	450.0	450.5	450.4	449.8	449.2	448.5	447.9
160°	454.3	454.8	455.3	455.2	454.7	454.1	453.6	453.0
162.5°	458.7	459.2	459.7	459.8	459.3	458.8	458.3	457.8
165°	464.5	465.2	465.8	465.8	465.3	464.7	464.2	463.6
167.5°	469.0	469.7	470.3	470.3	469.7	469.0	468.4	467.8
170°	471.6	472.2	472.8	472.8	472.2	471.6	471.0	470.3
172.5°	473.3	473.9	474.5	474.5	473.8	473.1	472.4	471.7
175°	475.3	475.9	476.4	476.4	475.8	475.1	474.5	473.9
177.5°	476.1	476.6	477.1	477.0	476.4	475.8	475.1	474.5
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)